

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332527-840

Luminaire Tested: **SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332527-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5805.3 lumens
Efficiency: N/A
Efficacy: 137.6 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332527-840
CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	75	70	65	60	54	51	48	41	38	37	28	27	25	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4657	4657	4657	4657
5°	5485	4669	4122	4669
10°	6567	4649	3710	4649
15°	7770	4603	3408	4603
20°	8652	4554	3137	4554
25°	8792	4483	2950	4483
30°	7481	4416	2892	4416
35°	5752	4306	2893	4306
40°	4484	4176	2947	4176
45°	3738	3981	2997	3981
50°	3291	3743	3097	3743
55°	3015	3458	3222	3458
60°	2824	3202	3371	3202
65°	2628	2917	3498	2917
70°	2403	2634	3576	2634
75°	2149	2318	3534	2318
80°	1799	1901	3422	1901
85°	1325	1371	3270	1371



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.0
10°-20°	173.3	3.0
20°-30°	274.7	4.7
30°-40°	305.7	5.3
40°-50°	278.3	4.8
50°-60°	227.4	3.9
60°-70°	162.4	2.8
70°-80°	89.4	1.5
80°-90°	28.9	0.5
90°-100°	100.1	1.7
100°-110°	296.4	5.1
110°-120°	503.1	8.7
120°-130°	663.4	11.4
130°-140°	745.0	12.8
140°-150°	732.1	12.6
150°-160°	615.7	10.6
160°-170°	409.7	7.1
170°-180°	143.5	2.5
0°-30°	504.2	8.7
0°-40°	809.9	14.0
0°-60°	1315.6	22.7
0°-90°	1596.4	27.5
90°-120°	899.6	15.5
90°-150°	3040.1	52.4
90°-180°	4209.0	72.5
0°-180°	5805.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	577	577	577	577	577	
5°	677	576	509	576	677	69
15°	930	551	408	551	930	263
25°	987	503	331	503	987	435
35°	584	437	294	437	584	370
45°	327	349	262	349	327	258
55°	214	246	229	246	214	193
65°	138	153	183	153	138	136
75°	69	74	113	74	69	73
85°	14	15	35	15	14	18
90°	35	4	35	4	35	18
95°	93	70	93	70	93	97
105°	286	273	286	273	286	302
115°	507	512	507	512	507	501
125°	739	745	739	745	739	659
135°	962	961	962	961	962	743
145°	1169	1167	1169	1167	1169	731
155°	1336	1338	1336	1338	1336	615
165°	1452	1456	1452	1456	1452	409
175°	1508	1515	1508	1515	1508	143
180°	1517	1517	1517	1517	1517	



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	614.0	613.9	612.0	611.6	610.3	608.5	608.1	605.0	599.0	596.0	595.3
5°	676.8	681.7	675.4	674.2	673.5	665.6	661.6	656.8	645.8	639.3	634.3
7.5°	751.8	752.3	749.6	747.5	741.3	734.5	724.2	713.2	700.0	686.5	676.2
10°	801.1	803.0	799.9	799.5	787.3	779.6	764.4	751.4	736.6	720.1	705.1
12.5°	853.1	850.5	848.9	838.7	836.4	822.4	804.7	791.4	768.5	749.5	729.5
15°	929.7	924.4	921.1	907.1	900.1	880.7	861.8	847.3	817.4	788.9	767.4
17.5°	974.6	979.9	972.2	966.3	948.5	934.8	915.5	884.9	861.6	826.3	799.1
20°	1007.1	1007.6	1003.3	997.3	983.3	966.0	945.0	911.6	883.6	848.5	811.1
22.5°	1015.9	1016.0	1014.2	1008.7	997.9	984.0	962.8	934.8	901.0	862.8	825.5
25°	987.0	986.1	988.3	994.5	990.5	986.1	973.9	953.1	921.6	881.2	841.0
27.5°	879.8	886.5	898.6	913.8	928.6	939.8	942.9	938.7	919.2	886.0	843.8
30°	802.5	810.7	819.8	835.1	864.7	881.7	900.3	914.4	906.6	880.0	840.8
32.5°	717.7	719.7	733.2	750.5	777.7	810.3	839.9	868.6	878.1	864.1	831.4
35°	583.6	587.0	601.6	618.7	652.0	692.0	736.4	776.1	808.8	821.9	805.2
37.5°	476.3	485.8	496.1	514.6	543.9	579.9	626.0	677.4	726.2	758.9	764.5
40°	425.5	431.4	438.8	452.9	477.8	513.1	552.8	611.6	663.5	710.3	725.6
42.5°	385.3	388.8	393.3	406.1	425.0	460.2	496.4	548.2	600.2	656.2	681.9
45°	327.4	331.0	338.7	346.1	360.4	384.8	418.5	461.0	513.4	567.3	614.7
47.5°	285.7	287.9	292.5	300.4	312.7	328.7	356.1	391.6	440.1	492.6	543.0
50°	262.0	263.9	267.4	274.6	284.0	298.3	320.7	354.0	391.9	444.7	494.2
52.5°	243.2	244.0	246.6	251.5	258.9	270.9	289.4	316.9	352.2	399.3	448.6
55°	214.2	215.1	217.5	221.1	227.5	235.2	249.2	269.8	300.6	341.5	384.4
57.5°	190.3	191.0	192.9	194.3	199.7	205.8	216.7	231.4	254.7	289.4	327.6
60°	174.9	174.5	176.8	178.0	181.7	186.9	195.3	209.3	229.6	257.6	292.8
62.5°	160.1	159.4	161.4	163.0	165.0	169.5	176.3	187.3	203.9	229.1	259.5
65°	137.6	136.7	137.9	139.9	141.7	144.1	149.2	159.0	172.1	190.3	213.4
67.5°	115.2	116.2	116.4	117.3	118.5	121.7	125.1	132.1	141.4	155.9	175.5
70°	101.8	102.1	103.0	103.0	103.7	106.6	109.5	113.5	122.6	136.0	152.0
72.5°	88.5	89.5	89.1	89.8	90.4	92.3	94.3	98.3	105.9	115.9	129.5
75°	68.9	69.6	69.6	69.8	70.5	71.2	72.9	75.7	81.3	88.7	98.0
77.5°	50.2	50.3	50.6	51.5	51.5	52.6	53.8	56.1	58.9	63.9	69.7
80°	38.7	39.2	39.0	39.5	39.5	40.4	40.9	43.7	44.9	48.3	52.8
82.5°	28.4	28.9	28.8	29.5	29.9	30.1	30.7	31.9	33.1	36.1	37.9
85°	14.3	14.8	14.3	14.8	15.6	15.8	16.5	16.8	17.7	18.4	20.1
87.5°	11.2	11.7	11.6	11.7	12.0	11.9	11.8	11.3	11.8	11.6	12.0
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	52.1	51.8	51.5	51.2	50.8	50.2	49.3	48.4	47.4	46.5	45.0
95°	92.7	92.7	92.7	92.7	92.7	92.3	91.5	90.7	90.0	89.2	87.4
97.5°	145.2	145.2	145.2	145.2	145.2	144.8	143.8	142.9	142.0	141.0	138.9
100°	181.9	181.9	181.9	181.9	181.9	181.6	181.1	180.6	180.1	179.6	177.1
102.5°	223.2	223.0	222.8	222.6	222.3	221.9	221.2	220.4	219.6	218.9	216.8
105°	286.3	285.5	284.7	284.0	283.2	282.4	281.6	280.8	280.0	279.2	278.2
107.5°	347.8	347.8	347.9	347.9	348.0	347.6	346.9	346.2	345.5	344.7	344.6
110°	391.8	391.1	390.3	389.5	388.7	388.6	389.1	389.6	390.2	390.7	390.9



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	437.0	436.8	436.6	436.5	436.3	436.3	436.4	436.5	436.6	436.7	437.2
115°	506.9	507.2	507.4	507.7	507.9	508.2	508.4	508.7	509.0	509.2	509.7
117.5°	573.5	574.0	574.5	575.0	575.6	576.2	577.1	578.0	579.0	579.9	580.2
120°	624.2	623.7	623.1	622.6	622.1	622.5	623.8	625.1	626.4	627.7	628.4
122.5°	666.4	667.3	668.3	669.2	670.1	671.1	672.0	672.9	673.8	674.6	675.0
125°	739.1	739.6	740.2	740.7	741.2	741.7	742.3	742.8	743.4	743.9	744.1
127.5°	806.5	806.9	807.3	807.8	808.2	808.6	809.2	809.7	810.2	810.7	811.1
130°	850.6	851.6	852.7	853.7	854.7	855.6	856.1	856.6	857.2	857.7	857.7
132.5°	897.6	898.0	898.4	898.8	899.2	899.7	900.2	900.7	901.2	901.8	902.0
135°	962.1	962.8	963.6	964.4	965.2	965.8	966.3	966.9	967.5	968.0	968.0
137.5°	1029.9	1029.8	1029.6	1029.5	1029.3	1029.6	1030.2	1030.9	1031.6	1032.2	1031.8
140°	1071.2	1071.5	1071.7	1072.0	1072.3	1072.5	1072.8	1073.0	1073.3	1073.5	1073.5
142.5°	1112.5	1112.6	1112.6	1112.7	1112.7	1112.8	1112.8	1112.9	1112.9	1113.0	1113.2
145°	1168.6	1169.3	1170.1	1170.9	1171.6	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0
147.5°	1225.4	1225.6	1225.9	1226.2	1226.4	1226.6	1226.9	1227.1	1227.3	1227.5	1227.7
150°	1260.1	1260.3	1260.6	1260.8	1261.1	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1292.0	1292.6	1293.3	1294.0	1294.7	1294.7	1294.1	1293.4	1292.8	1292.2	1292.0
155°	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4	1336.6
157.5°	1376.0	1376.8	1377.8	1378.7	1379.6	1379.6	1378.8	1378.1	1377.3	1376.4	1376.5
160°	1398.6	1399.9	1401.1	1402.4	1403.7	1404.0	1403.2	1402.4	1401.7	1400.9	1401.1
162.5°	1422.0	1423.3	1424.6	1425.9	1427.2	1427.1	1425.7	1424.3	1422.9	1421.5	1421.8
165°	1452.5	1453.5	1454.6	1455.6	1456.6	1456.4	1454.8	1453.3	1451.7	1450.2	1450.7
167.5°	1474.3	1475.9	1477.5	1479.1	1480.8	1480.8	1479.3	1477.6	1476.1	1474.5	1474.5
170°	1486.5	1488.3	1490.2	1492.0	1493.8	1494.0	1492.4	1490.9	1489.2	1487.7	1487.4
172.5°	1496.8	1498.6	1500.5	1502.3	1504.2	1504.2	1502.4	1500.7	1498.8	1497.1	1497.0
175°	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6	1507.9
177.5°	1513.3	1514.9	1516.6	1518.2	1519.9	1520.0	1518.6	1517.1	1515.7	1514.2	1514.2
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	595.5	592.8	590.9	589.4	585.2	582.7	580.8	578.1	575.0	571.8	567.7
5°	629.2	621.2	615.2	606.1	597.5	590.4	582.9	576.2	568.2	559.3	552.8
7.5°	664.8	652.7	637.2	623.8	608.6	595.5	583.8	571.8	559.3	547.0	535.9
10°	687.4	671.9	654.6	634.3	615.2	598.2	582.5	567.1	552.3	537.6	524.8
12.5°	711.7	692.3	666.8	643.1	621.7	599.0	580.0	561.2	543.3	527.8	513.0
15°	744.3	716.3	686.9	655.1	626.9	600.4	574.3	550.7	530.6	510.0	495.6
17.5°	764.3	729.6	696.1	662.9	628.7	595.2	567.1	539.9	514.7	494.3	476.3
20°	777.5	743.1	701.3	668.0	627.4	593.0	560.5	530.1	503.8	482.1	463.4
22.5°	788.9	749.2	707.3	663.6	623.2	586.6	551.1	520.6	493.7	470.8	452.9
25°	795.2	749.5	704.1	660.6	614.7	571.5	539.2	503.3	474.6	450.5	431.4
27.5°	795.9	747.0	695.6	647.3	600.0	559.7	519.0	486.9	457.2	431.6	413.2
30°	793.8	742.9	687.6	635.3	587.7	544.0	508.6	473.7	443.3	418.0	398.9
32.5°	787.0	734.1	677.3	621.9	572.6	529.8	493.3	460.1	430.5	405.6	385.5
35°	767.7	715.3	654.9	597.2	546.8	503.6	470.6	436.9	407.3	383.6	364.3
37.5°	737.4	690.1	628.6	569.1	519.5	476.1	443.3	412.9	386.2	362.1	342.3
40°	711.0	669.4	607.7	549.7	496.1	454.8	424.2	396.3	369.7	347.0	328.1
42.5°	680.6	644.4	587.5	526.0	474.3	432.8	403.0	377.9	352.9	331.9	313.1
45°	626.4	602.5	549.0	492.1	438.3	399.1	370.7	348.7	327.7	307.1	291.3
47.5°	564.1	552.2	507.2	453.1	402.1	363.5	338.8	318.5	300.0	282.7	268.7
50°	522.2	516.4	477.6	425.5	376.7	340.3	315.5	298.0	282.3	267.0	253.8
52.5°	480.9	480.7	445.6	397.9	352.7	317.8	293.1	276.8	263.2	250.7	238.9
55°	417.8	424.4	397.0	354.5	314.1	282.5	260.2	245.7	236.1	225.9	217.0
57.5°	359.8	370.9	348.2	310.7	277.0	248.0	228.6	217.7	207.5	201.3	194.8
60°	321.9	332.4	314.8	283.3	251.5	226.6	208.1	198.3	189.6	185.2	180.7
62.5°	288.3	297.6	284.6	255.3	227.7	203.8	188.2	178.8	172.9	168.2	165.2
65°	240.2	248.1	236.8	215.6	191.9	172.8	160.2	152.7	147.0	145.1	141.7
67.5°	194.2	201.4	195.3	177.2	158.2	143.7	133.8	126.7	123.3	121.7	119.3
70°	166.8	174.0	167.5	151.8	137.1	125.0	115.6	111.6	108.1	107.3	104.0
72.5°	143.7	148.6	142.1	129.8	117.3	107.0	99.8	95.5	93.7	92.4	90.6
75°	107.8	112.1	107.8	98.3	89.4	82.2	76.0	74.3	72.2	71.5	70.3
77.5°	76.2	80.0	76.7	70.8	64.1	58.6	55.2	53.1	52.6	51.4	52.0
80°	58.3	60.7	57.6	53.5	48.3	44.4	42.1	40.9	39.5	39.0	39.9
82.5°	41.9	42.9	41.3	38.6	34.7	32.2	30.6	29.2	28.9	29.0	29.0
85°	21.7	21.5	21.3	18.9	17.7	16.1	15.0	14.8	14.5	15.0	15.6
87.5°	11.6	11.4	10.8	9.5	8.4	7.2	6.5	5.7	6.5	7.2	8.0
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	43.5	42.1	40.6	38.3	34.9	31.7	28.4	25.1	28.4	31.7	34.9
95°	85.5	83.7	81.9	79.8	77.5	75.1	72.7	70.4	72.7	75.1	77.5
97.5°	136.7	134.6	132.5	130.5	128.6	126.7	124.8	123.0	124.8	126.7	128.6
100°	174.8	172.5	170.2	168.4	167.3	166.3	165.3	164.3	165.3	166.3	167.3
102.5°	214.7	212.5	210.4	209.1	208.6	208.2	207.8	207.4	207.8	208.2	208.6
105°	277.1	276.1	275.1	274.4	274.2	273.9	273.7	273.4	273.7	273.9	274.2
107.5°	344.4	344.3	344.1	343.9	343.6	343.3	343.0	342.5	343.0	343.3	343.6
110°	391.2	391.5	391.7	391.6	391.1	390.5	390.0	389.5	390.0	390.5	391.1



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	438.1	438.6	438.8	438.7	438.6	438.5	438.3	438.5	438.6	438.7
115°	510.3	510.8	511.3	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5
117.5°	580.6	580.9	581.3	581.4	581.2	581.0	580.8	580.6	580.8	581.0	581.2
120°	629.2	630.1	630.9	630.7	629.7	628.6	627.5	626.5	627.5	628.6	629.7
122.5°	675.4	675.7	676.1	676.1	675.6	675.2	674.8	674.4	674.8	675.2	675.6
125°	744.4	744.7	744.9	745.0	745.0	745.0	745.0	745.0	745.0	745.0	745.0
127.5°	811.5	811.9	812.4	812.2	811.4	810.6	809.9	809.1	809.9	810.6	811.4
130°	857.7	857.7	857.7	857.3	856.5	855.7	855.0	854.1	855.0	855.7	856.5
132.5°	902.2	902.4	902.6	902.4	901.8	901.3	900.7	900.1	900.7	901.3	901.8
135°	968.0	968.0	968.0	967.1	965.6	964.0	962.5	960.9	962.5	964.0	965.6
137.5°	1031.4	1031.0	1030.6	1030.0	1029.3	1028.5	1027.8	1027.0	1027.8	1028.5	1029.3
140°	1073.5	1073.5	1073.5	1073.3	1072.8	1072.3	1071.7	1071.2	1071.7	1072.3	1072.8
142.5°	1113.4	1113.6	1113.8	1113.7	1113.1	1112.6	1112.1	1111.6	1112.1	1112.6	1113.1
145°	1172.8	1172.5	1172.3	1171.5	1170.5	1169.5	1168.4	1167.4	1168.4	1169.5	1170.5
147.5°	1227.9	1228.1	1228.3	1227.8	1226.5	1225.3	1224.1	1222.7	1224.1	1225.3	1226.5
150°	1261.2	1261.2	1261.2	1260.7	1259.7	1258.7	1257.6	1256.6	1257.6	1258.7	1259.7
152.5°	1291.8	1291.6	1291.4	1291.0	1290.3	1289.7	1289.1	1288.5	1289.1	1289.7	1290.3
155°	1336.9	1337.2	1337.4	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5
157.5°	1376.5	1376.6	1376.6	1377.0	1377.5	1377.9	1378.4	1378.8	1378.4	1377.9	1377.5
160°	1401.4	1401.7	1401.9	1402.2	1402.4	1402.7	1403.0	1403.2	1403.0	1402.7	1402.4
162.5°	1422.1	1422.3	1422.6	1423.0	1423.7	1424.4	1425.0	1425.7	1425.0	1424.4	1423.7
165°	1451.2	1451.7	1452.2	1452.9	1453.7	1454.4	1455.2	1456.0	1455.2	1454.4	1453.7
167.5°	1474.4	1474.4	1474.3	1474.9	1475.9	1477.0	1478.1	1479.3	1478.1	1477.0	1475.9
170°	1487.1	1486.9	1486.6	1487.1	1488.4	1489.8	1491.1	1492.4	1491.1	1489.8	1488.4
172.5°	1497.0	1496.9	1496.8	1497.4	1498.4	1499.5	1500.7	1501.8	1500.7	1499.5	1498.4
175°	1508.1	1508.4	1508.6	1509.4	1510.8	1512.1	1513.4	1514.7	1513.4	1512.1	1510.8
177.5°	1514.2	1514.2	1514.2	1514.7	1515.8	1516.8	1517.8	1518.9	1517.8	1516.8	1515.8
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	565.8	564.1	561.7	558.3	555.3	552.3	551.5	550.4	552.7	550.8	550.2
5°	547.3	542.3	535.8	528.5	524.1	518.0	516.7	514.3	511.9	511.7	509.3
7.5°	527.7	520.3	511.8	504.3	497.4	490.5	486.0	485.1	481.6	479.5	477.2
10°	515.0	505.9	496.1	489.0	480.9	473.7	468.7	465.9	463.4	460.8	458.4
12.5°	500.2	490.5	482.4	474.6	465.0	459.6	451.3	446.4	445.9	445.9	439.7
15°	482.8	473.2	460.8	449.8	444.5	434.0	429.5	423.7	420.2	416.6	413.7
17.5°	462.9	451.0	441.3	428.7	418.7	410.3	404.3	400.9	395.5	390.4	386.8
20°	450.5	437.9	427.6	414.1	403.2	392.9	387.9	383.1	379.1	374.8	370.7
22.5°	437.9	424.6	412.1	399.1	388.9	378.0	373.1	366.7	362.8	360.4	356.4
25°	418.0	403.6	389.3	376.9	366.4	356.8	350.4	345.4	341.0	339.1	336.5
27.5°	396.4	382.1	368.3	354.2	342.2	335.3	330.1	326.4	323.9	321.3	320.1
30°	382.6	367.8	353.0	339.8	328.9	321.9	317.2	314.6	312.7	311.4	310.2
32.5°	368.7	354.1	338.5	326.5	316.6	310.4	306.8	304.2	303.3	302.9	302.4
35°	346.3	331.5	317.2	306.4	297.1	294.7	291.5	290.1	289.6	291.3	292.1
37.5°	324.7	310.9	297.7	287.3	281.1	277.7	276.6	276.7	278.4	279.8	281.6
40°	310.7	297.3	284.9	275.8	270.0	267.9	267.4	268.6	270.5	272.3	274.2
42.5°	297.1	284.0	272.7	264.2	260.1	258.1	258.4	259.6	262.4	264.4	267.2
45°	276.1	265.1	254.1	247.1	243.8	244.3	244.3	246.4	249.0	252.2	255.3
47.5°	256.2	245.1	236.1	230.2	228.5	228.1	229.4	232.3	236.0	239.8	244.2
50°	242.9	232.3	224.4	219.1	217.2	217.9	219.8	222.5	227.0	231.9	236.4
52.5°	229.2	219.6	212.4	207.5	206.1	207.4	209.3	213.5	217.5	222.7	228.1
55°	208.1	200.1	194.3	190.8	190.3	191.0	193.1	197.6	203.4	209.8	215.1
57.5°	187.2	180.4	175.1	172.7	172.9	173.6	177.1	182.5	188.6	195.5	202.3
60°	173.0	166.8	162.5	160.6	160.9	162.3	166.6	171.6	179.3	185.9	193.1
62.5°	159.7	154.2	150.1	148.3	148.0	151.2	155.3	160.5	168.1	175.6	183.4
65°	138.1	133.8	130.5	129.6	130.3	132.7	137.9	144.8	151.3	159.2	167.3
67.5°	117.1	113.6	111.3	111.7	112.6	116.1	120.5	126.4	133.8	142.0	150.0
70°	103.7	100.4	98.5	98.7	100.2	104.4	108.3	114.2	122.1	130.5	137.1
72.5°	90.0	87.8	86.0	87.1	88.5	91.4	96.2	102.2	109.2	116.9	124.0
75°	69.1	69.1	68.2	68.9	71.0	73.8	77.5	83.6	90.6	96.8	102.5
77.5°	51.2	50.7	51.3	52.2	53.4	56.9	61.0	65.4	70.6	76.9	81.6
80°	39.2	39.5	40.6	42.1	42.5	45.1	49.5	53.5	57.6	62.8	67.4
82.5°	29.5	29.7	30.3	32.1	32.6	35.4	38.2	42.2	45.9	49.5	53.2
85°	16.1	16.1	17.2	18.0	19.1	21.0	22.7	25.1	28.5	30.8	34.4
87.5°	9.1	9.6	10.8	11.6	12.6	13.9	14.6	17.1	18.2	19.4	21.3
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	38.3	40.6	42.1	43.5	45.0	46.5	47.4	48.4	49.3	50.2	50.8
95°	79.8	81.9	83.7	85.5	87.4	89.2	90.0	90.7	91.5	92.3	92.7
97.5°	130.5	132.5	134.6	136.7	138.9	141.0	142.0	142.9	143.8	144.8	145.2
100°	168.4	170.2	172.5	174.8	177.1	179.6	180.1	180.6	181.1	181.6	181.9
102.5°	209.1	210.4	212.5	214.7	216.8	218.9	219.6	220.4	221.2	221.9	222.3
105°	274.4	275.1	276.1	277.1	278.2	279.2	280.0	280.8	281.6	282.4	283.2
107.5°	343.9	344.1	344.3	344.4	344.6	344.7	345.5	346.2	346.9	347.6	348.0
110°	391.6	391.7	391.5	391.2	390.9	390.7	390.2	389.6	389.1	388.6	388.7



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	438.8	438.6	438.1	437.7	437.2	436.7	436.6	436.5	436.4	436.3	436.3
115°	511.5	511.3	510.8	510.3	509.7	509.2	509.0	508.7	508.4	508.2	507.9
117.5°	581.4	581.3	580.9	580.6	580.2	579.9	579.0	578.0	577.1	576.2	575.6
120°	630.7	630.9	630.1	629.2	628.4	627.7	626.4	625.1	623.8	622.5	622.1
122.5°	676.1	676.1	675.7	675.4	675.0	674.6	673.8	672.9	672.0	671.1	670.1
125°	745.0	744.9	744.7	744.4	744.1	743.9	743.4	742.8	742.3	741.7	741.2
127.5°	812.2	812.4	811.9	811.5	811.1	810.7	810.2	809.7	809.2	808.6	808.2
130°	857.3	857.7	857.7	857.7	857.7	857.7	857.2	856.6	856.1	855.6	854.7
132.5°	902.4	902.6	902.4	902.2	902.0	901.8	901.2	900.7	900.2	899.7	899.2
135°	967.1	968.0	968.0	968.0	968.0	968.0	967.5	966.9	966.3	965.8	965.2
137.5°	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6	1030.9	1030.2	1029.6	1029.3
140°	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1073.0	1072.8	1072.5	1072.3
142.5°	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9	1112.9	1112.8	1112.8	1112.7
145°	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0	1172.8	1172.5	1172.3	1171.6
147.5°	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3	1227.1	1226.9	1226.6	1226.4
150°	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.1
152.5°	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8	1293.4	1294.1	1294.7	1294.7
155°	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5
157.5°	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3	1378.1	1378.8	1379.6	1379.6
160°	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7	1402.4	1403.2	1404.0	1403.7
162.5°	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9	1424.3	1425.7	1427.1	1427.2
165°	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7	1453.3	1454.8	1456.4	1456.6
167.5°	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1	1477.6	1479.3	1480.8	1480.8
170°	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2	1490.9	1492.4	1494.0	1493.8
172.5°	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8	1500.7	1502.4	1504.2	1504.2
175°	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9
177.5°	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7	1517.1	1518.6	1520.0	1519.9
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	549.8	549.5	548.1	547.9	548.1	549.5	549.8	550.2	550.8	552.7	550.4
5°	507.9	506.6	505.9	508.6	505.9	506.6	507.9	509.3	511.7	511.9	514.3
7.5°	476.3	475.3	473.2	472.5	473.2	475.3	476.3	477.2	479.5	481.6	485.1
10°	456.1	455.0	453.1	452.6	453.1	455.0	456.1	458.4	460.8	463.4	465.9
12.5°	436.5	434.6	434.2	434.7	434.2	434.6	436.5	439.7	445.9	445.9	446.4
15°	410.6	409.6	407.0	407.8	407.0	409.6	410.6	413.7	416.6	420.2	423.7
17.5°	385.1	384.0	380.7	383.5	380.7	384.0	385.1	386.8	390.4	395.5	400.9
20°	369.0	367.1	365.5	365.2	365.5	367.1	369.0	370.7	374.8	379.1	383.1
22.5°	353.8	352.0	351.8	350.3	351.8	352.0	353.8	356.4	360.4	362.8	366.7
25°	334.6	333.0	332.4	331.2	332.4	333.0	334.6	336.5	339.1	341.0	345.4
27.5°	319.9	319.1	318.2	318.6	318.2	319.1	319.9	320.1	321.3	323.9	326.4
30°	310.9	310.7	310.2	310.2	310.2	310.7	310.9	310.2	311.4	312.7	314.6
32.5°	303.5	303.5	303.8	303.8	303.8	303.5	303.5	302.4	302.9	303.3	304.2
35°	293.1	293.8	294.2	293.5	294.2	293.8	293.1	292.1	291.3	289.6	290.1
37.5°	283.6	284.3	285.0	285.8	285.0	284.3	283.6	281.6	279.8	278.4	276.7
40°	276.3	277.9	278.4	279.6	278.4	277.9	276.3	274.2	272.3	270.5	268.6
42.5°	269.4	271.2	272.5	272.8	272.5	271.2	269.4	267.2	264.4	262.4	259.6
45°	258.8	260.7	262.5	262.5	262.5	260.7	258.8	255.3	252.2	249.0	246.4
47.5°	247.9	250.6	252.4	252.8	252.4	250.6	247.9	244.2	239.8	236.0	232.3
50°	240.4	243.8	245.5	246.6	245.5	243.8	240.4	236.4	231.9	227.0	222.5
52.5°	233.2	236.5	238.7	239.3	238.7	236.5	233.2	228.1	222.7	217.5	213.5
55°	220.6	225.4	228.0	228.9	228.0	225.4	220.6	215.1	209.8	203.4	197.6
57.5°	208.7	213.2	216.2	216.9	216.2	213.2	208.7	202.3	195.5	188.6	182.5
60°	199.5	204.4	208.1	208.8	208.1	204.4	199.5	193.1	185.9	179.3	171.6
62.5°	190.2	195.2	198.6	200.5	198.6	195.2	190.2	183.4	175.6	168.1	160.5
65°	174.0	179.0	182.4	183.1	182.4	179.0	174.0	167.3	159.2	151.3	144.8
67.5°	156.3	161.4	163.5	164.9	163.5	161.4	156.3	150.0	142.0	133.8	126.4
70°	143.9	147.9	150.4	151.5	150.4	147.9	143.9	137.1	130.5	122.1	114.2
72.5°	129.8	134.0	136.7	137.0	136.7	134.0	129.8	124.0	116.9	109.2	102.2
75°	108.1	111.9	113.3	113.3	113.3	111.9	108.1	102.5	96.8	90.6	83.6
77.5°	85.5	87.5	89.3	89.7	89.3	87.5	85.5	81.6	76.9	70.6	65.4
80°	71.0	72.2	73.6	73.6	73.6	72.2	71.0	67.4	62.8	57.6	53.5
82.5°	56.0	57.1	58.5	58.3	58.5	57.1	56.0	53.2	49.5	45.9	42.2
85°	33.9	36.1	35.9	35.3	35.9	36.1	33.9	34.4	30.8	28.5	25.1
87.5°	22.0	22.3	23.0	23.5	23.0	22.3	22.0	21.3	19.4	18.2	17.1
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	51.2	51.5	51.8	52.1	51.8	51.5	51.2	50.8	50.2	49.3	48.4
95°	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.3	91.5	90.7
97.5°	145.2	145.2	145.2	145.2	145.2	145.2	145.2	145.2	144.8	143.8	142.9
100°	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.6	181.1	180.6
102.5°	222.6	222.8	223.0	223.2	223.0	222.8	222.6	222.3	221.9	221.2	220.4
105°	284.0	284.7	285.5	286.3	285.5	284.7	284.0	283.2	282.4	281.6	280.8
107.5°	347.9	347.9	347.8	347.8	347.8	347.9	347.9	348.0	347.6	346.9	346.2
110°	389.5	390.3	391.1	391.8	391.1	390.3	389.5	388.7	388.6	389.1	389.6



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	436.5	436.6	436.8	437.0	436.8	436.6	436.5	436.3	436.3	436.4	436.5
115°	507.7	507.4	507.2	506.9	507.2	507.4	507.7	507.9	508.2	508.4	508.7
117.5°	575.0	574.5	574.0	573.5	574.0	574.5	575.0	575.6	576.2	577.1	578.0
120°	622.6	623.1	623.7	624.2	623.7	623.1	622.6	622.1	622.5	623.8	625.1
122.5°	669.2	668.3	667.3	666.4	667.3	668.3	669.2	670.1	671.1	672.0	672.9
125°	740.7	740.2	739.6	739.1	739.6	740.2	740.7	741.2	741.7	742.3	742.8
127.5°	807.8	807.3	806.9	806.5	806.9	807.3	807.8	808.2	808.6	809.2	809.7
130°	853.7	852.7	851.6	850.6	851.6	852.7	853.7	854.7	855.6	856.1	856.6
132.5°	898.8	898.4	898.0	897.6	898.0	898.4	898.8	899.2	899.7	900.2	900.7
135°	964.4	963.6	962.8	962.1	962.8	963.6	964.4	965.2	965.8	966.3	966.9
137.5°	1029.5	1029.6	1029.8	1029.9	1029.8	1029.6	1029.5	1029.3	1029.6	1030.2	1030.9
140°	1072.0	1071.7	1071.5	1071.2	1071.5	1071.7	1072.0	1072.3	1072.5	1072.8	1073.0
142.5°	1112.7	1112.6	1112.6	1112.5	1112.6	1112.6	1112.7	1112.7	1112.8	1112.8	1112.9
145°	1170.9	1170.1	1169.3	1168.6	1169.3	1170.1	1170.9	1171.6	1172.3	1172.5	1172.8
147.5°	1226.2	1225.9	1225.6	1225.4	1225.6	1225.9	1226.2	1226.4	1226.6	1226.9	1227.1
150°	1260.8	1260.6	1260.3	1260.1	1260.3	1260.6	1260.8	1261.1	1261.2	1261.2	1261.2
152.5°	1294.0	1293.3	1292.6	1292.0	1292.6	1293.3	1294.0	1294.7	1294.7	1294.1	1293.4
155°	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5
157.5°	1378.7	1377.8	1376.8	1376.0	1376.8	1377.8	1378.7	1379.6	1379.6	1378.8	1378.1
160°	1402.4	1401.1	1399.9	1398.6	1399.9	1401.1	1402.4	1403.7	1404.0	1403.2	1402.4
162.5°	1425.9	1424.6	1423.3	1422.0	1423.3	1424.6	1425.9	1427.2	1427.1	1425.7	1424.3
165°	1455.6	1454.6	1453.5	1452.5	1453.5	1454.6	1455.6	1456.6	1456.4	1454.8	1453.3
167.5°	1479.1	1477.5	1475.9	1474.3	1475.9	1477.5	1479.1	1480.8	1480.8	1479.3	1477.6
170°	1492.0	1490.2	1488.3	1486.5	1488.3	1490.2	1492.0	1493.8	1494.0	1492.4	1490.9
172.5°	1502.3	1500.5	1498.6	1496.8	1498.6	1500.5	1502.3	1504.2	1504.2	1502.4	1500.7
175°	1513.1	1511.3	1509.4	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3
177.5°	1518.2	1516.6	1514.9	1513.3	1514.9	1516.6	1518.2	1519.9	1520.0	1518.6	1517.1
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	551.5	552.3	555.3	558.3	561.7	564.1	565.8	567.7	571.8	575.0	578.1
5°	516.7	518.0	524.1	528.5	535.8	542.3	547.3	552.8	559.3	568.2	576.2
7.5°	486.0	490.5	497.4	504.3	511.8	520.3	527.7	535.9	547.0	559.3	571.8
10°	468.7	473.7	480.9	489.0	496.1	505.9	515.0	524.8	537.6	552.3	567.1
12.5°	451.3	459.6	465.0	474.6	482.4	490.5	500.2	513.0	527.8	543.3	561.2
15°	429.5	434.0	444.5	449.8	460.8	473.2	482.8	495.6	510.0	530.6	550.7
17.5°	404.3	410.3	418.7	428.7	441.3	451.0	462.9	476.3	494.3	514.7	539.9
20°	387.9	392.9	403.2	414.1	427.6	437.9	450.5	463.4	482.1	503.8	530.1
22.5°	373.1	378.0	388.9	399.1	412.1	424.6	437.9	452.9	470.8	493.7	520.6
25°	350.4	356.8	366.4	376.9	389.3	403.6	418.0	431.4	450.5	474.6	503.3
27.5°	330.1	335.3	342.2	354.2	368.3	382.1	396.4	413.2	431.6	457.2	486.9
30°	317.2	321.9	328.9	339.8	353.0	367.8	382.6	398.9	418.0	443.3	473.7
32.5°	306.8	310.4	316.6	326.5	338.5	354.1	368.7	385.5	405.6	430.5	460.1
35°	291.5	294.7	297.1	306.4	317.2	331.5	346.3	364.3	383.6	407.3	436.9
37.5°	276.6	277.7	281.1	287.3	297.7	310.9	324.7	342.3	362.1	386.2	412.9
40°	267.4	267.9	270.0	275.8	284.9	297.3	310.7	328.1	347.0	369.7	396.3
42.5°	258.4	258.1	260.1	264.2	272.7	284.0	297.1	313.1	331.9	352.9	377.9
45°	244.3	244.3	243.8	247.1	254.1	265.1	276.1	291.3	307.1	327.7	348.7
47.5°	229.4	228.1	228.5	230.2	236.1	245.1	256.2	268.7	282.7	300.0	318.5
50°	219.8	217.9	217.2	219.1	224.4	232.3	242.9	253.8	267.0	282.3	298.0
52.5°	209.3	207.4	206.1	207.5	212.4	219.6	229.2	238.9	250.7	263.2	276.8
55°	193.1	191.0	190.3	190.8	194.3	200.1	208.1	217.0	225.9	236.1	245.7
57.5°	177.1	173.6	172.9	172.7	175.1	180.4	187.2	194.8	201.3	207.5	217.7
60°	166.6	162.3	160.9	160.6	162.5	166.8	173.0	180.7	185.2	189.6	198.3
62.5°	155.3	151.2	148.0	148.3	150.1	154.2	159.7	165.2	168.2	172.9	178.8
65°	137.9	132.7	130.3	129.6	130.5	133.8	138.1	141.7	145.1	147.0	152.7
67.5°	120.5	116.1	112.6	111.7	111.3	113.6	117.1	119.3	121.7	123.3	126.7
70°	108.3	104.4	100.2	98.7	98.5	100.4	103.7	104.0	107.3	108.1	111.6
72.5°	96.2	91.4	88.5	87.1	86.0	87.8	90.0	90.6	92.4	93.7	95.5
75°	77.5	73.8	71.0	68.9	68.2	69.1	69.1	70.3	71.5	72.2	74.3
77.5°	61.0	56.9	53.4	52.2	51.3	50.7	51.2	52.0	51.4	52.6	53.1
80°	49.5	45.1	42.5	42.1	40.6	39.5	39.2	39.9	39.0	39.5	40.9
82.5°	38.2	35.4	32.6	32.1	30.3	29.7	29.5	29.0	29.0	28.9	29.2
85°	22.7	21.0	19.1	18.0	17.2	16.1	16.1	15.6	15.0	14.5	14.8
87.5°	14.6	13.9	12.6	11.6	10.8	9.6	9.1	8.0	7.2	6.5	5.7
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	47.4	46.5	45.0	43.5	42.1	40.6	38.3	34.9	31.7	28.4	25.1
95°	90.0	89.2	87.4	85.5	83.7	81.9	79.8	77.5	75.1	72.7	70.4
97.5°	142.0	141.0	138.9	136.7	134.6	132.5	130.5	128.6	126.7	124.8	123.0
100°	180.1	179.6	177.1	174.8	172.5	170.2	168.4	167.3	166.3	165.3	164.3
102.5°	219.6	218.9	216.8	214.7	212.5	210.4	209.1	208.6	208.2	207.8	207.4
105°	280.0	279.2	278.2	277.1	276.1	275.1	274.4	274.2	273.9	273.7	273.4
107.5°	345.5	344.7	344.6	344.4	344.3	344.1	343.9	343.6	343.3	343.0	342.5
110°	390.2	390.7	390.9	391.2	391.5	391.7	391.6	391.1	390.5	390.0	389.5



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	436.6	436.7	437.2	437.7	438.1	438.6	438.8	438.7	438.6	438.5	438.3
115°	509.0	509.2	509.7	510.3	510.8	511.3	511.5	511.5	511.5	511.5	511.5
117.5°	579.0	579.9	580.2	580.6	580.9	581.3	581.4	581.2	581.0	580.8	580.6
120°	626.4	627.7	628.4	629.2	630.1	630.9	630.7	629.7	628.6	627.5	626.5
122.5°	673.8	674.6	675.0	675.4	675.7	676.1	676.1	675.6	675.2	674.8	674.4
125°	743.4	743.9	744.1	744.4	744.7	744.9	745.0	745.0	745.0	745.0	745.0
127.5°	810.2	810.7	811.1	811.5	811.9	812.4	812.2	811.4	810.6	809.9	809.1
130°	857.2	857.7	857.7	857.7	857.7	857.7	857.3	856.5	855.7	855.0	854.1
132.5°	901.2	901.8	902.0	902.2	902.4	902.6	902.4	901.8	901.3	900.7	900.1
135°	967.5	968.0	968.0	968.0	968.0	968.0	967.1	965.6	964.0	962.5	960.9
137.5°	1031.6	1032.2	1031.8	1031.4	1031.0	1030.6	1030.0	1029.3	1028.5	1027.8	1027.0
140°	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1072.8	1072.3	1071.7	1071.2
142.5°	1112.9	1113.0	1113.2	1113.4	1113.6	1113.8	1113.7	1113.1	1112.6	1112.1	1111.6
145°	1173.0	1173.3	1173.0	1172.8	1172.5	1172.3	1171.5	1170.5	1169.5	1168.4	1167.4
147.5°	1227.3	1227.5	1227.7	1227.9	1228.1	1228.3	1227.8	1226.5	1225.3	1224.1	1222.7
150°	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1260.7	1259.7	1258.7	1257.6	1256.6
152.5°	1292.8	1292.2	1292.0	1291.8	1291.6	1291.4	1291.0	1290.3	1289.7	1289.1	1288.5
155°	1337.4	1336.4	1336.6	1336.9	1337.2	1337.4	1337.5	1337.5	1337.5	1337.5	1337.5
157.5°	1377.3	1376.4	1376.5	1376.5	1376.6	1376.6	1377.0	1377.5	1377.9	1378.4	1378.8
160°	1401.7	1400.9	1401.1	1401.4	1401.7	1401.9	1402.2	1402.4	1402.7	1403.0	1403.2
162.5°	1422.9	1421.5	1421.8	1422.1	1422.3	1422.6	1423.0	1423.7	1424.4	1425.0	1425.7
165°	1451.7	1450.2	1450.7	1451.2	1451.7	1452.2	1452.9	1453.7	1454.4	1455.2	1456.0
167.5°	1476.1	1474.5	1474.5	1474.4	1474.4	1474.3	1474.9	1475.9	1477.0	1478.1	1479.3
170°	1489.2	1487.7	1487.4	1487.1	1486.9	1486.6	1487.1	1488.4	1489.8	1491.1	1492.4
172.5°	1498.8	1497.1	1497.0	1497.0	1496.9	1496.8	1497.4	1498.4	1499.5	1500.7	1501.8
175°	1509.4	1507.6	1507.9	1508.1	1508.4	1508.6	1509.4	1510.8	1512.1	1513.4	1514.7
177.5°	1515.7	1514.2	1514.2	1514.2	1514.2	1514.2	1514.7	1515.8	1516.8	1517.8	1518.9
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840
 CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	580.8	582.7	585.2	589.4	590.9	592.8	595.5	595.3	596.0	599.0	605.0
5°	582.9	590.4	597.5	606.1	615.2	621.2	629.2	634.3	639.3	645.8	656.8
7.5°	583.8	595.5	608.6	623.8	637.2	652.7	664.8	676.2	686.5	700.0	713.2
10°	582.5	598.2	615.2	634.3	654.6	671.9	687.4	705.1	720.1	736.6	751.4
12.5°	580.0	599.0	621.7	643.1	666.8	692.3	711.7	729.5	749.5	768.5	791.4
15°	574.3	600.4	626.9	655.1	686.9	716.3	744.3	767.4	788.9	817.4	847.3
17.5°	567.1	595.2	628.7	662.9	696.1	729.6	764.3	799.1	826.3	861.6	884.9
20°	560.5	593.0	627.4	668.0	701.3	743.1	777.5	811.1	848.5	883.6	911.6
22.5°	551.1	586.6	623.2	663.6	707.3	749.2	788.9	825.5	862.8	901.0	934.8
25°	539.2	571.5	614.7	660.6	704.1	749.5	795.2	841.0	881.2	921.6	953.1
27.5°	519.0	559.7	600.0	647.3	695.6	747.0	795.9	843.8	886.0	919.2	938.7
30°	508.6	544.0	587.7	635.3	687.6	742.9	793.8	840.8	880.0	906.6	914.4
32.5°	493.3	529.8	572.6	621.9	677.3	734.1	787.0	831.4	864.1	878.1	868.6
35°	470.6	503.6	546.8	597.2	654.9	715.3	767.7	805.2	821.9	808.8	776.1
37.5°	443.3	476.1	519.5	569.1	628.6	690.1	737.4	764.5	758.9	726.2	677.4
40°	424.2	454.8	496.1	549.7	607.7	669.4	711.0	725.6	710.3	663.5	611.6
42.5°	403.0	432.8	474.3	526.0	587.5	644.4	680.6	681.9	656.2	600.2	548.2
45°	370.7	399.1	438.3	492.1	549.0	602.5	626.4	614.7	567.3	513.4	461.0
47.5°	338.8	363.5	402.1	453.1	507.2	552.2	564.1	543.0	492.6	440.1	391.6
50°	315.5	340.3	376.7	425.5	477.6	516.4	522.2	494.2	444.7	391.9	354.0
52.5°	293.1	317.8	352.7	397.9	445.6	480.7	480.9	448.6	399.3	352.2	316.9
55°	260.2	282.5	314.1	354.5	397.0	424.4	417.8	384.4	341.5	300.6	269.8
57.5°	228.6	248.0	277.0	310.7	348.2	370.9	359.8	327.6	289.4	254.7	231.4
60°	208.1	226.6	251.5	283.3	314.8	332.4	321.9	292.8	257.6	229.6	209.3
62.5°	188.2	203.8	227.7	255.3	284.6	297.6	288.3	259.5	229.1	203.9	187.3
65°	160.2	172.8	191.9	215.6	236.8	248.1	240.2	213.4	190.3	172.1	159.0
67.5°	133.8	143.7	158.2	177.2	195.3	201.4	194.2	175.5	155.9	141.4	132.1
70°	115.6	125.0	137.1	151.8	167.5	174.0	166.8	152.0	136.0	122.6	113.5
72.5°	99.8	107.0	117.3	129.8	142.1	148.6	143.7	129.5	115.9	105.9	98.3
75°	76.0	82.2	89.4	98.3	107.8	112.1	107.8	98.0	88.7	81.3	75.7
77.5°	55.2	58.6	64.1	70.8	76.7	80.0	76.2	69.7	63.9	58.9	56.1
80°	42.1	44.4	48.3	53.5	57.6	60.7	58.3	52.8	48.3	44.9	43.7
82.5°	30.6	32.2	34.7	38.6	41.3	42.9	41.9	37.9	36.1	33.1	31.9
85°	15.0	16.1	17.7	18.9	21.3	21.5	21.7	20.1	18.4	17.7	16.8
87.5°	6.5	7.2	8.4	9.5	10.8	11.4	11.6	12.0	11.6	11.8	11.3
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	28.4	31.7	34.9	38.3	40.6	42.1	43.5	45.0	46.5	47.4	48.4
95°	72.7	75.1	77.5	79.8	81.9	83.7	85.5	87.4	89.2	90.0	90.7
97.5°	124.8	126.7	128.6	130.5	132.5	134.6	136.7	138.9	141.0	142.0	142.9
100°	165.3	166.3	167.3	168.4	170.2	172.5	174.8	177.1	179.6	180.1	180.6
102.5°	207.8	208.2	208.6	209.1	210.4	212.5	214.7	216.8	218.9	219.6	220.4
105°	273.7	273.9	274.2	274.4	275.1	276.1	277.1	278.2	279.2	280.0	280.8
107.5°	343.0	343.3	343.6	343.9	344.1	344.3	344.4	344.6	344.7	345.5	346.2
110°	390.0	390.5	391.1	391.6	391.7	391.5	391.2	390.9	390.7	390.2	389.6



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	438.5	438.6	438.7	438.8	438.6	438.1	437.7	437.2	436.7	436.6	436.5
115°	511.5	511.5	511.5	511.5	511.3	510.8	510.3	509.7	509.2	509.0	508.7
117.5°	580.8	581.0	581.2	581.4	581.3	580.9	580.6	580.2	579.9	579.0	578.0
120°	627.5	628.6	629.7	630.7	630.9	630.1	629.2	628.4	627.7	626.4	625.1
122.5°	674.8	675.2	675.6	676.1	676.1	675.7	675.4	675.0	674.6	673.8	672.9
125°	745.0	745.0	745.0	745.0	744.9	744.7	744.4	744.1	743.9	743.4	742.8
127.5°	809.9	810.6	811.4	812.2	812.4	811.9	811.5	811.1	810.7	810.2	809.7
130°	855.0	855.7	856.5	857.3	857.7	857.7	857.7	857.7	857.7	857.2	856.6
132.5°	900.7	901.3	901.8	902.4	902.6	902.4	902.2	902.0	901.8	901.2	900.7
135°	962.5	964.0	965.6	967.1	968.0	968.0	968.0	968.0	968.0	967.5	966.9
137.5°	1027.8	1028.5	1029.3	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6	1030.9
140°	1071.7	1072.3	1072.8	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1073.0
142.5°	1112.1	1112.6	1113.1	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9	1112.9
145°	1168.4	1169.5	1170.5	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0	1172.8
147.5°	1224.1	1225.3	1226.5	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3	1227.1
150°	1257.6	1258.7	1259.7	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1289.1	1289.7	1290.3	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8	1293.4
155°	1337.5	1337.5	1337.5	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4	1338.5
157.5°	1378.4	1377.9	1377.5	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3	1378.1
160°	1403.0	1402.7	1402.4	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7	1402.4
162.5°	1425.0	1424.4	1423.7	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9	1424.3
165°	1455.2	1454.4	1453.7	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7	1453.3
167.5°	1478.1	1477.0	1475.9	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1	1477.6
170°	1491.1	1489.8	1488.4	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2	1490.9
172.5°	1500.7	1499.5	1498.4	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8	1500.7
175°	1513.4	1512.1	1510.8	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4	1511.3
177.5°	1517.8	1516.8	1515.8	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7	1517.1
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	608.1	608.5	610.3	611.6	612.0	613.9	614.0
5°	661.6	665.6	673.5	674.2	675.4	681.7	676.8
7.5°	724.2	734.5	741.3	747.5	749.6	752.3	751.8
10°	764.4	779.6	787.3	799.5	799.9	803.0	801.1
12.5°	804.7	822.4	836.4	838.7	848.9	850.5	853.1
15°	861.8	880.7	900.1	907.1	921.1	924.4	929.7
17.5°	915.5	934.8	948.5	966.3	972.2	979.9	974.6
20°	945.0	966.0	983.3	997.3	1003.3	1007.6	1007.1
22.5°	962.8	984.0	997.9	1008.7	1014.2	1016.0	1015.9
25°	973.9	986.1	990.5	994.5	988.3	986.1	987.0
27.5°	942.9	939.8	928.6	913.8	898.6	886.5	879.8
30°	900.3	881.7	864.7	835.1	819.8	810.7	802.5
32.5°	839.9	810.3	777.7	750.5	733.2	719.7	717.7
35°	736.4	692.0	652.0	618.7	601.6	587.0	583.6
37.5°	626.0	579.9	543.9	514.6	496.1	485.8	476.3
40°	552.8	513.1	477.8	452.9	438.8	431.4	425.5
42.5°	496.4	460.2	425.0	406.1	393.3	388.8	385.3
45°	418.5	384.8	360.4	346.1	338.7	331.0	327.4
47.5°	356.1	328.7	312.7	300.4	292.5	287.9	285.7
50°	320.7	298.3	284.0	274.6	267.4	263.9	262.0
52.5°	289.4	270.9	258.9	251.5	246.6	244.0	243.2
55°	249.2	235.2	227.5	221.1	217.5	215.1	214.2
57.5°	216.7	205.8	199.7	194.3	192.9	191.0	190.3
60°	195.3	186.9	181.7	178.0	176.8	174.5	174.9
62.5°	176.3	169.5	165.0	163.0	161.4	159.4	160.1
65°	149.2	144.1	141.7	139.9	137.9	136.7	137.6
67.5°	125.1	121.7	118.5	117.3	116.4	116.2	115.2
70°	109.5	106.6	103.7	103.0	103.0	102.1	101.8
72.5°	94.3	92.3	90.4	89.8	89.1	89.5	88.5
75°	72.9	71.2	70.5	69.8	69.6	69.6	68.9
77.5°	53.8	52.6	51.5	51.5	50.6	50.3	50.2
80°	40.9	40.4	39.5	39.5	39.0	39.2	38.7
82.5°	30.7	30.1	29.9	29.5	28.8	28.9	28.4
85°	16.5	15.8	15.6	14.8	14.3	14.8	14.3
87.5°	11.8	11.9	12.0	11.7	11.6	11.7	11.2
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	49.3	50.2	50.8	51.2	51.5	51.8	52.1
95°	91.5	92.3	92.7	92.7	92.7	92.7	92.7
97.5°	143.8	144.8	145.2	145.2	145.2	145.2	145.2
100°	181.1	181.6	181.9	181.9	181.9	181.9	181.9
102.5°	221.2	221.9	222.3	222.6	222.8	223.0	223.2
105°	281.6	282.4	283.2	284.0	284.7	285.5	286.3
107.5°	346.9	347.6	348.0	347.9	347.9	347.8	347.8
110°	389.1	388.6	388.7	389.5	390.3	391.1	391.8



TEST NUMBER: P332527-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	436.4	436.3	436.3	436.5	436.6	436.8	437.0
115°	508.4	508.2	507.9	507.7	507.4	507.2	506.9
117.5°	577.1	576.2	575.6	575.0	574.5	574.0	573.5
120°	623.8	622.5	622.1	622.6	623.1	623.7	624.2
122.5°	672.0	671.1	670.1	669.2	668.3	667.3	666.4
125°	742.3	741.7	741.2	740.7	740.2	739.6	739.1
127.5°	809.2	808.6	808.2	807.8	807.3	806.9	806.5
130°	856.1	855.6	854.7	853.7	852.7	851.6	850.6
132.5°	900.2	899.7	899.2	898.8	898.4	898.0	897.6
135°	966.3	965.8	965.2	964.4	963.6	962.8	962.1
137.5°	1030.2	1029.6	1029.3	1029.5	1029.6	1029.8	1029.9
140°	1072.8	1072.5	1072.3	1072.0	1071.7	1071.5	1071.2
142.5°	1112.8	1112.8	1112.7	1112.7	1112.6	1112.6	1112.5
145°	1172.5	1172.3	1171.6	1170.9	1170.1	1169.3	1168.6
147.5°	1226.9	1226.6	1226.4	1226.2	1225.9	1225.6	1225.4
150°	1261.2	1261.2	1261.1	1260.8	1260.6	1260.3	1260.1
152.5°	1294.1	1294.7	1294.7	1294.0	1293.3	1292.6	1292.0
155°	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4
157.5°	1378.8	1379.6	1379.6	1378.7	1377.8	1376.8	1376.0
160°	1403.2	1404.0	1403.7	1402.4	1401.1	1399.9	1398.6
162.5°	1425.7	1427.1	1427.2	1425.9	1424.6	1423.3	1422.0
165°	1454.8	1456.4	1456.6	1455.6	1454.6	1453.5	1452.5
167.5°	1479.3	1480.8	1480.8	1479.1	1477.5	1475.9	1474.3
170°	1492.4	1494.0	1493.8	1492.0	1490.2	1488.3	1486.5
172.5°	1502.4	1504.2	1504.2	1502.3	1500.5	1498.6	1496.8
175°	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6
177.5°	1518.6	1520.0	1519.9	1518.2	1516.6	1514.9	1513.3
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0

(END OF REPORT)