

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332498-840

Luminaire Tested: **SA4XXDIP-C350D365U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332498-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2853.1 lumens  
Efficiency: N/A  
Efficacy: 140.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332498-840  
CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50	45				
2	90	82	76	71	83	76	71	66	66	61	58	56	53	50	46	44	42	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	59	48	41	35	41	36	31	36	31	28	30	26	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	2.0
10°-20°	158.3	5.5
20°-30°	233.0	8.2
30°-40°	270.8	9.5
40°-50°	270.9	9.5
50°-60°	236.9	8.3
60°-70°	175.9	6.2
70°-80°	100.0	3.5
80°-90°	29.8	1.0
90°-100°	131.2	4.6
100°-110°	273.1	9.6
110°-120°	244.6	8.6
120°-130°	205.8	7.2
130°-140°	171.6	6.0
140°-150°	131.1	4.6
150°-160°	92.1	3.2
160°-170°	54.2	1.9
170°-180°	17.6	0.6
0°-30°	447.4	15.7
0°-40°	718.3	25.2
0°-60°	1226.1	43.0
0°-90°	1531.8	53.7
90°-120°	648.9	22.7
90°-150°	1157.3	40.6
90°-180°	1321.0	46.3
0°-180°	2853.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	0	3	6	7	8	2
95°	12	37	291	144	87	13
105°	42	60	234	504	502	45
115°	74	92	209	401	482	73
125°	102	122	208	341	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	181	182	183	186	185	17
180°	182	182	182	182	182	



TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.0	10.1	10.2	10.2	10.2	10.1	10.4	10.3	10.4	10.5	10.4
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1
92.5°	4.0	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3
95°	11.8	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1
97.5°	21.1	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8
100°	27.2	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3
102.5°	32.8	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9
105°	41.8	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0
107.5°	51.6	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6
110°	58.2	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9



TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.4	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1
115°	73.5	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8
117.5°	82.9	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0
120°	89.3	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0
122.5°	94.9	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8
125°	102.4	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0
127.5°	109.1	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9
130°	112.8	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8
132.5°	116.5	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0
135°	121.7	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6
137.5°	126.9	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0
140°	130.7	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0
142.5°	134.6	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2
145°	140.3	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3
147.5°	146.6	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7
150°	150.6	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7
152.5°	154.3	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3
155°	159.6	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9
157.5°	164.6	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5
160°	167.7	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9
162.5°	170.6	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6
165°	173.8	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8
167.5°	177.0	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4
170°	178.4	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1
172.5°	179.9	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1
175°	181.3	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8
177.5°	182.0	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	10.5	10.5	10.6	10.6	10.7	10.7	10.7	10.7
90°	6.5	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	70.1	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	264.5	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	390.7	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	430.4	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	428.5	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	399.7	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	359.0	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	334.5	396.2	448.0	487.2	512.5	527.6	533.9	537.1





TEST NUMBER: P332498-840

CATALOG NUMBER: SA4XXDIP-C350D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.4	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	298.4	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	289.5	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	285.5	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	282.1	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	276.3	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	269.1	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	263.4	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	257.4	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	249.1	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	241.7	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	237.3	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	233.4	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	227.7	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	223.1	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	220.3	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	217.1	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	212.4	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	207.3	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	204.2	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	201.1	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	196.6	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	192.5	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	189.9	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	187.6	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.5	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.5	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)