

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332985-830

Luminaire Tested: **SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332985-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6100.3 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332985-830
CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70	67
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	63	60	57
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49
4	81	70	62	56	77	67	60	54	62	56	51	57	52	48	53	49	45	43
5	75	63	55	49	71	60	53	47	56	50	45	52	46	42	48	43	40	37
6	69	57	49	43	66	55	47	42	51	44	40	47	42	37	43	39	35	33
7	64	52	44	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	37	32	29	27
9	56	43	36	30	53	42	35	30	39	33	29	36	31	27	34	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15079	15079	15079	15079
5°	17490	15124	13367	15124
10°	20690	15058	11931	15058
15°	23901	14919	10252	14919
20°	26611	14728	9271	14728
25°	27470	14539	8607	14539
30°	24047	14311	8207	14311
35°	18719	13973	7965	13973
40°	14037	13585	7835	13585
45°	11082	12965	7767	12965
50°	9357	12248	7542	12248
55°	8156	11461	7139	11461
60°	7338	10643	6318	10643
65°	6470	9761	5435	9761
70°	5828	8847	4902	8847
75°	4885	7842	4177	7842
80°	4128	6681	3919	6681
85°	3483	5233	3483	5233



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	3.0
10°-20°	545.9	8.9
20°-30°	853.8	14.0
30°-40°	949.2	15.6
40°-50°	842.2	13.8
50°-60°	656.2	10.8
60°-70°	429.6	7.0
70°-80°	211.3	3.5
80°-90°	53.4	0.9
90°-100°	15.2	0.2
100°-110°	97.1	1.6
110°-120°	185.8	3.0
120°-130°	235.8	3.9
130°-140°	252.3	4.1
140°-150°	236.0	3.9
150°-160°	190.3	3.1
160°-170°	122.7	2.0
170°-180°	42.3	0.7
0°-30°	1580.7	25.9
0°-40°	2529.9	41.5
0°-60°	4028.3	66.0
0°-90°	4722.6	77.4
90°-120°	298.1	4.9
90°-150°	1022.3	16.8
90°-180°	1378.0	22.6
0°-180°	6100.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1868	1868	1868	1868	1868	
5°	2158	1866	1650	1866	2158	218
15°	2860	1785	1227	1785	2860	813
25°	3084	1632	966	1632	3084	1368
35°	1899	1418	808	1418	1899	1191
45°	971	1136	680	1136	971	769
55°	580	814	507	814	580	527
65°	339	511	284	511	339	341
75°	157	251	134	251	157	172
85°	38	56	38	56	38	43
90°	10	1	10	1	10	6
95°	10	18	10	18	10	8
105°	95	100	95	100	95	83
115°	188	187	188	187	188	187
125°	265	263	265	263	265	236
135°	329	326	329	326	329	253
145°	378	376	378	376	378	236
155°	412	413	412	413	412	190
165°	433	435	433	435	433	122
175°	443	445	443	445	443	42
180°	445	445	445	445	445	



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1970.1	1975.6	1970.1	1969.5	1963.5	1961.7	1959.3	1951.4	1937.0	1928.6	1930.4
5°	2158.2	2177.1	2166.5	2165.0	2148.5	2131.9	2121.4	2097.3	2071.7	2054.5	2040.1
7.5°	2375.9	2386.7	2380.1	2369.6	2342.8	2327.6	2303.2	2271.4	2225.5	2190.5	2158.4
10°	2524.0	2533.0	2530.1	2510.5	2490.9	2451.0	2428.5	2384.1	2326.1	2280.2	2237.3
12.5°	2669.7	2679.4	2652.9	2653.7	2616.7	2585.3	2549.5	2493.6	2426.7	2367.5	2313.8
15°	2859.7	2847.6	2847.6	2832.5	2791.2	2747.5	2710.7	2651.9	2567.7	2496.9	2422.4
17.5°	3008.3	3012.6	3006.3	2970.9	2938.4	2893.2	2825.6	2757.1	2678.9	2583.9	2507.7
20°	3097.5	3097.5	3090.7	3066.6	3024.4	2976.3	2903.3	2828.8	2729.4	2633.8	2548.1
22.5°	3133.6	3135.9	3128.0	3108.1	3070.2	3023.2	2961.1	2885.4	2783.0	2675.4	2569.2
25°	3083.9	3098.2	3099.6	3094.5	3083.2	3054.5	3001.1	2923.6	2831.8	2715.2	2600.8
27.5°	2831.3	2849.4	2865.2	2891.2	2925.8	2943.9	2946.3	2906.9	2826.8	2714.5	2599.4
30°	2579.6	2594.7	2643.6	2707.6	2757.3	2802.5	2841.6	2852.1	2807.0	2706.1	2584.9
32.5°	2300.4	2320.8	2369.7	2438.5	2521.3	2597.7	2685.7	2730.5	2729.3	2668.8	2556.6
35°	1899.4	1914.5	1959.6	2031.8	2131.2	2244.9	2384.1	2492.4	2566.2	2560.9	2492.4
37.5°	1531.8	1548.9	1594.5	1654.4	1750.7	1891.4	2026.1	2175.4	2311.8	2388.4	2365.5
40°	1332.0	1332.8	1377.1	1438.9	1529.2	1651.8	1798.6	1964.1	2116.1	2240.3	2264.4
42.5°	1174.2	1174.4	1203.7	1270.3	1335.3	1450.8	1590.8	1755.2	1933.2	2076.5	2140.3
45°	970.7	977.5	1001.6	1041.5	1092.7	1190.5	1302.6	1455.4	1654.8	1824.9	1931.0
47.5°	822.1	832.0	847.3	879.9	920.7	985.8	1078.6	1215.8	1378.0	1565.1	1716.1
50°	745.0	746.5	766.1	784.1	819.5	871.5	952.7	1067.1	1216.1	1395.9	1563.8
52.5°	678.8	678.4	690.2	713.1	741.9	782.3	847.9	952.1	1084.2	1245.5	1418.7
55°	579.5	583.2	592.2	610.3	632.2	660.7	712.7	790.9	894.8	1032.5	1189.8
57.5°	503.9	505.9	512.9	520.6	540.6	561.4	600.4	654.7	742.3	855.1	1001.6
60°	454.5	455.2	457.5	468.8	484.7	504.2	530.6	576.5	650.2	753.3	869.2
62.5°	406.3	407.7	411.2	419.4	431.7	445.2	472.8	509.6	570.7	658.7	763.2
65°	338.7	339.4	344.7	347.7	357.4	369.5	389.8	414.6	456.8	530.6	609.5
67.5°	283.0	283.0	283.2	287.3	294.1	302.1	314.2	334.1	365.9	411.2	480.9
70°	246.9	246.9	248.4	250.6	254.4	261.1	267.9	283.0	306.3	343.2	396.6
72.5°	213.1	213.7	215.2	215.7	217.6	223.2	228.2	237.8	255.1	283.0	326.1
75°	156.6	158.8	162.6	165.6	169.3	168.5	173.8	179.8	185.1	201.7	226.5
77.5°	116.5	115.3	115.7	118.3	118.8	119.5	123.3	127.9	131.9	139.7	148.5
80°	88.8	88.8	91.0	91.8	91.0	91.8	95.6	97.8	99.3	102.4	110.7
82.5°	67.1	68.3	67.6	68.3	68.8	69.6	72.7	73.1	74.6	75.9	79.4
85°	37.6	38.4	39.1	37.6	37.6	37.6	39.1	39.9	41.4	40.6	42.1
87.5°	15.3	14.6	15.2	15.2	15.7	15.1	15.6	16.7	15.4	15.9	15.8
90°	10.0	9.8	9.7	9.5	9.4	9.1	8.7	8.2	7.7	7.4	6.7
92.5°	9.2	9.1	9.1	9.1	9.0	8.9	8.4	7.9	7.5	7.1	6.5
95°	9.6	9.6	9.5	9.4	9.3	9.1	8.7	8.2	7.7	7.4	7.3
97.5°	9.3	9.2	9.1	9.1	9.0	9.0	9.0	8.9	8.9	8.8	17.1
100°	9.3	9.2	9.1	9.1	9.0	9.6	10.8	12.2	13.4	14.7	24.9
102.5°	9.6	9.6	9.5	9.5	9.5	16.3	29.9	43.5	57.0	70.6	71.9
105°	94.9	97.6	100.3	102.9	105.6	106.6	105.9	105.3	104.6	104.0	103.6
107.5°	132.3	132.1	131.8	131.5	131.2	130.9	130.5	130.3	129.9	129.6	129.0
110°	148.5	148.4	148.2	147.9	147.7	147.5	147.3	147.2	147.0	146.9	146.5



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	164.9	164.6	164.3	164.0	163.7	163.5	163.6	163.6	163.6	163.7	163.4
115°	188.5	188.5	188.5	188.5	188.5	188.5	188.3	188.1	188.0	187.8	187.9
117.5°	212.6	212.7	212.7	212.7	212.7	212.8	212.8	212.8	212.9	212.9	212.7
120°	227.8	228.0	228.1	228.3	228.5	228.5	228.3	228.1	228.0	227.8	227.9
122.5°	242.8	242.9	243.1	243.2	243.4	243.4	243.3	243.2	243.1	243.1	242.9
125°	265.1	265.0	265.0	264.9	264.9	264.7	264.5	264.3	264.0	263.8	264.0
127.5°	284.8	284.8	284.9	285.0	285.0	285.1	285.1	285.2	285.2	285.3	284.9
130°	298.1	298.1	298.1	298.1	298.1	298.1	298.0	297.9	297.8	297.8	297.6
132.5°	310.4	310.5	310.5	310.6	310.7	310.7	310.6	310.5	310.4	310.3	310.0
135°	328.8	328.7	328.5	328.3	328.2	328.0	327.9	327.7	327.6	327.4	327.2
137.5°	344.5	344.5	344.6	344.6	344.7	344.6	344.5	344.3	344.1	343.9	343.7
140°	355.4	355.3	355.2	355.2	355.2	355.0	354.8	354.5	354.3	354.1	353.9
142.5°	364.5	364.5	364.5	364.5	364.4	364.3	364.2	364.0	363.8	363.7	363.6
145°	378.4	378.2	378.1	378.0	377.8	377.7	377.7	377.6	377.5	377.4	377.4
147.5°	389.9	389.8	389.7	389.7	389.6	389.6	389.6	389.5	389.4	389.4	389.4
150°	397.4	397.3	397.3	397.2	397.1	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	403.8	403.9	403.9	403.9	404.0	404.0	403.8	403.7	403.6	403.5	403.6
155°	412.4	412.6	412.8	413.0	413.3	413.2	412.9	412.6	412.4	412.1	412.3
157.5°	419.6	420.0	420.4	420.8	421.1	421.1	420.8	420.4	420.0	419.6	419.8
160°	424.3	424.8	425.3	425.7	426.1	426.1	425.7	425.3	424.8	424.3	424.4
162.5°	428.1	428.6	429.1	429.6	430.1	430.2	429.7	429.2	428.9	428.4	428.5
165°	433.4	434.0	434.7	435.4	436.0	436.1	435.5	434.9	434.3	433.7	433.7
167.5°	437.3	438.0	438.8	439.5	440.3	440.3	439.7	439.0	438.4	437.7	437.7
170°	439.7	440.5	441.2	442.0	442.6	442.7	442.1	441.6	440.9	440.4	440.3
172.5°	441.0	441.9	442.6	443.5	444.2	444.3	443.7	443.2	442.5	442.0	441.9
175°	442.7	443.6	444.5	445.4	446.3	446.4	445.7	445.1	444.4	443.7	443.7
177.5°	443.7	444.5	445.2	445.9	446.6	446.8	446.3	445.8	445.4	444.8	444.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1924.4	1916.0	1911.8	1902.1	1890.6	1884.6	1879.2	1871.4	1861.1	1850.3	1842.5
5°	2022.0	2004.0	1981.4	1954.4	1930.2	1907.0	1886.6	1866.3	1843.0	1818.9	1794.8
7.5°	2122.3	2086.8	2048.4	2004.0	1960.8	1921.6	1885.4	1850.8	1811.7	1776.6	1744.6
10°	2192.2	2144.0	2090.6	2034.1	1977.6	1928.7	1880.6	1836.9	1788.8	1745.9	1709.8
12.5°	2248.7	2192.2	2127.9	2057.6	1989.7	1930.5	1875.2	1818.3	1763.5	1717.0	1668.9
15°	2342.6	2265.1	2178.6	2094.3	2006.3	1925.7	1851.2	1785.0	1722.6	1657.1	1611.2
17.5°	2407.3	2315.3	2210.1	2108.8	2004.8	1909.8	1823.8	1745.0	1672.9	1606.1	1551.4
20°	2445.7	2344.1	2227.5	2112.3	1995.7	1894.1	1801.6	1714.3	1639.7	1567.5	1511.1
22.5°	2467.4	2354.9	2227.5	2107.0	1986.1	1876.0	1774.4	1683.6	1602.4	1530.2	1467.7
25°	2474.4	2353.9	2223.7	2085.3	1952.9	1836.2	1730.8	1632.2	1541.9	1469.7	1403.4
27.5°	2464.7	2322.9	2189.6	2047.5	1910.8	1787.9	1677.3	1573.7	1483.3	1405.7	1337.8
30°	2450.2	2298.2	2155.2	2007.8	1869.3	1751.1	1634.5	1535.2	1441.1	1360.6	1292.1
32.5°	2418.9	2268.1	2114.3	1963.2	1823.0	1701.2	1590.5	1490.6	1398.4	1316.1	1243.3
35°	2356.9	2204.1	2037.1	1882.1	1744.4	1618.0	1514.1	1417.8	1329.7	1241.7	1164.9
37.5°	2275.2	2119.1	1952.9	1783.2	1645.3	1526.0	1430.7	1340.3	1254.3	1173.9	1088.9
40°	2198.2	2056.0	1884.3	1715.8	1574.3	1459.2	1371.1	1289.1	1202.6	1122.8	1037.7
42.5°	2104.9	1983.7	1810.3	1641.2	1501.5	1390.5	1308.5	1228.3	1149.6	1072.2	983.5
45°	1949.1	1857.3	1694.7	1532.2	1391.5	1281.6	1206.4	1135.6	1066.3	992.6	909.1
47.5°	1770.6	1708.4	1568.1	1401.7	1271.5	1172.6	1099.9	1042.1	983.5	909.8	836.5
50°	1646.5	1606.7	1471.2	1319.2	1195.0	1104.0	1029.4	975.2	926.3	855.6	790.1
52.5°	1514.1	1492.9	1378.5	1233.1	1113.1	1023.9	960.3	911.4	862.0	803.2	742.0
55°	1312.4	1323.7	1226.6	1101.0	988.1	912.9	854.9	814.3	772.1	722.5	675.0
57.5°	1106.3	1147.5	1082.3	971.9	866.2	796.6	753.0	718.8	683.4	642.2	601.7
60°	982.8	1017.4	980.5	883.4	790.9	726.2	685.6	659.2	623.9	586.3	555.3
62.5°	862.4	899.5	877.6	799.2	713.2	657.6	621.7	597.2	570.9	538.1	506.1
65°	711.1	735.2	724.7	670.5	609.5	562.1	529.0	511.0	486.9	462.8	434.2
67.5°	544.7	591.2	585.0	556.3	503.6	466.6	444.9	429.0	407.0	389.1	369.7
70°	447.8	490.7	489.9	466.6	438.0	403.3	388.3	374.8	355.2	337.9	322.1
72.5°	366.5	405.8	411.6	393.7	374.2	348.0	333.6	324.2	305.2	293.3	280.5
75°	256.7	285.2	292.8	292.8	283.7	270.1	257.4	251.4	237.8	227.2	219.7
77.5°	168.2	186.3	198.0	200.8	202.2	197.7	187.1	182.9	172.5	168.7	161.5
80°	118.9	130.9	144.5	149.0	152.8	151.3	146.8	143.7	133.9	130.2	127.1
82.5°	82.2	88.8	99.9	109.9	108.8	112.7	108.8	106.4	99.1	97.6	94.6
85°	42.9	43.6	45.1	51.9	55.7	57.2	58.0	56.5	54.2	54.2	48.9
87.5°	15.6	15.0	16.0	15.9	16.3	18.6	20.3	20.6	19.0	17.3	15.7
90°	6.1	5.6	5.0	4.2	3.5	2.6	1.8	1.0	1.8	2.6	3.5
92.5°	5.8	5.3	4.7	4.3	4.3	4.2	4.2	4.2	4.2	4.2	4.3
95°	7.2	7.1	7.1	8.3	10.7	13.3	15.8	18.3	15.8	13.3	10.7
97.5°	25.4	33.6	41.8	45.1	43.6	42.0	40.4	38.9	40.4	42.0	43.6
100°	35.1	45.3	55.5	59.9	58.6	57.3	56.0	54.7	56.0	57.3	58.6
102.5°	73.3	74.6	76.0	76.2	75.1	74.2	73.2	72.2	73.2	74.2	75.1
105°	103.2	102.8	102.5	102.1	101.6	101.1	100.7	100.3	100.7	101.1	101.6
107.5°	128.6	128.1	127.5	127.2	127.0	126.8	126.5	126.3	126.5	126.8	127.0
110°	146.0	145.5	145.2	144.8	144.6	144.3	144.1	143.9	144.1	144.3	144.6



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	163.2	163.1	162.9	162.6	162.1	161.7	161.4	161.0	161.4	161.7	162.1
115°	188.0	188.1	188.1	188.1	187.8	187.7	187.5	187.2	187.5	187.7	187.8
117.5°	212.6	212.4	212.3	212.1	211.8	211.4	211.1	210.8	211.1	211.4	211.8
120°	228.0	228.1	228.1	228.0	227.7	227.4	227.2	226.9	227.2	227.4	227.7
122.5°	242.8	242.7	242.6	242.5	242.3	242.1	242.0	241.8	242.0	242.1	242.3
125°	264.1	264.3	264.4	264.4	264.0	263.7	263.4	263.2	263.4	263.7	264.0
127.5°	284.6	284.3	283.9	283.7	283.6	283.5	283.5	283.4	283.5	283.5	283.6
130°	297.4	297.1	296.9	296.8	296.7	296.6	296.5	296.4	296.5	296.6	296.7
132.5°	309.7	309.4	309.2	309.0	308.9	308.7	308.6	308.5	308.6	308.7	308.9
135°	326.9	326.6	326.2	326.1	326.2	326.3	326.4	326.4	326.4	326.3	326.2
137.5°	343.3	343.0	342.7	342.5	342.4	342.4	342.4	342.3	342.4	342.4	342.4
140°	353.8	353.6	353.5	353.4	353.2	353.1	352.9	352.8	352.9	353.1	353.2
142.5°	363.5	363.4	363.4	363.2	362.9	362.6	362.3	362.1	362.3	362.6	362.9
145°	377.4	377.4	377.4	377.3	377.1	376.8	376.6	376.5	376.6	376.8	377.1
147.5°	389.5	389.6	389.6	389.5	389.1	388.6	388.2	387.8	388.2	388.6	389.1
150°	397.2	397.3	397.4	397.3	397.0	396.6	396.3	396.1	396.3	396.6	397.0
152.5°	403.7	403.9	404.0	404.0	403.7	403.5	403.2	403.0	403.2	403.5	403.7
155°	412.5	412.7	412.9	413.0	412.9	412.8	412.8	412.7	412.8	412.8	412.9
157.5°	420.1	420.4	420.6	420.8	420.8	420.8	420.8	420.9	420.8	420.8	420.8
160°	424.5	424.6	424.7	424.8	425.1	425.3	425.5	425.7	425.5	425.3	425.1
162.5°	428.5	428.6	428.7	428.9	429.1	429.4	429.7	430.0	429.7	429.4	429.1
165°	433.7	433.7	433.7	433.9	434.2	434.6	435.0	435.4	435.0	434.6	434.2
167.5°	437.8	437.8	437.9	438.1	438.5	438.8	439.2	439.6	439.2	438.8	438.5
170°	440.3	440.2	440.1	440.3	440.7	441.1	441.6	442.1	441.6	441.1	440.7
172.5°	441.9	441.8	441.7	441.9	442.3	442.7	443.2	443.7	443.2	442.7	442.3
175°	443.6	443.5	443.4	443.6	444.0	444.5	444.9	445.4	444.9	444.5	444.0
177.5°	444.6	444.5	444.3	444.5	444.9	445.4	445.7	446.2	445.7	445.4	444.9
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1834.1	1828.1	1820.2	1811.2	1800.4	1790.7	1786.5	1790.2	1792.0	1787.2	1786.5
5°	1778.2	1759.4	1744.4	1721.8	1703.7	1688.7	1678.2	1673.7	1675.2	1663.1	1660.1
7.5°	1715.5	1693.2	1668.5	1641.7	1616.7	1594.6	1583.0	1576.7	1564.0	1558.5	1549.4
10°	1675.2	1645.0	1621.0	1589.3	1560.8	1534.5	1521.6	1511.1	1498.3	1492.2	1479.5
12.5°	1633.6	1598.6	1572.2	1539.4	1510.1	1478.5	1466.2	1446.7	1426.6	1414.0	1397.6
15°	1575.1	1533.0	1500.5	1461.4	1426.8	1390.7	1358.3	1322.2	1308.6	1280.1	1263.5
17.5°	1506.6	1463.9	1423.8	1371.3	1317.9	1273.0	1238.5	1203.9	1183.2	1164.9	1156.5
20°	1461.4	1422.3	1366.6	1305.6	1246.2	1196.6	1168.7	1146.1	1123.5	1110.8	1101.7
22.5°	1418.7	1368.7	1304.0	1238.2	1178.7	1139.9	1116.3	1093.2	1074.8	1062.6	1050.6
25°	1347.1	1281.6	1213.1	1137.8	1097.2	1063.4	1037.7	1018.9	1007.7	991.8	985.8
27.5°	1273.5	1194.1	1118.6	1068.0	1025.7	994.7	972.4	958.3	944.0	933.9	926.0
30°	1216.8	1136.3	1068.6	1020.4	977.5	952.0	933.9	917.4	906.1	897.8	891.7
32.5°	1160.8	1080.3	1023.4	971.7	937.8	912.9	893.5	881.2	872.3	861.7	858.0
35°	1079.9	1008.4	958.8	912.1	877.4	854.9	839.8	827.1	819.5	816.5	814.3
37.5°	1002.1	943.5	890.1	851.9	821.0	803.2	785.5	779.2	774.0	768.6	771.1
40°	952.7	897.8	850.4	809.7	784.9	765.3	754.8	747.2	742.7	742.7	742.7
42.5°	909.9	856.2	810.0	773.6	748.8	732.3	720.5	714.2	712.7	712.1	715.7
45°	843.6	793.9	747.2	717.2	696.1	679.6	672.8	667.5	667.5	670.5	671.3
47.5°	777.8	731.3	693.8	660.2	640.8	630.5	624.6	621.9	622.2	625.2	628.7
50°	737.4	691.5	654.7	624.6	606.5	596.7	591.4	590.0	591.4	591.4	596.7
52.5°	693.5	652.4	616.1	590.9	570.4	561.3	558.4	556.3	557.1	559.6	561.8
55°	629.1	592.2	557.6	533.6	518.5	512.5	505.7	506.4	504.9	506.4	506.4
57.5°	564.6	531.4	499.3	480.1	466.8	458.2	450.7	452.9	450.6	450.3	449.1
60°	523.0	486.9	461.3	444.0	429.0	421.4	414.6	416.1	413.9	412.4	409.3
62.5°	477.9	447.8	423.4	406.7	394.6	385.9	379.1	377.6	372.4	367.2	360.6
65°	412.4	387.6	365.7	350.0	338.7	331.9	326.6	322.1	310.8	298.8	292.8
67.5°	348.7	330.8	310.5	297.1	287.9	279.1	269.0	261.3	250.7	244.1	240.3
70°	307.7	290.5	273.1	260.3	250.6	242.3	231.0	225.7	218.2	215.2	211.5
72.5°	268.6	252.5	236.5	224.9	214.4	208.0	199.2	193.9	190.6	189.4	185.6
75°	209.2	196.4	184.4	173.8	165.6	161.1	157.3	153.5	152.0	145.2	141.5
77.5°	152.6	144.2	136.7	129.1	123.3	120.3	113.0	108.7	106.1	102.9	102.2
80°	118.9	112.9	105.4	100.9	92.6	89.5	86.5	85.8	85.0	84.3	83.5
82.5°	89.4	83.4	75.9	73.1	70.9	69.1	67.3	66.5	65.8	66.3	66.1
85°	45.1	42.1	42.1	41.4	40.6	39.9	39.1	39.1	38.4	39.1	38.4
87.5°	15.9	15.5	15.6	14.5	15.2	15.3	14.8	14.9	15.6	14.4	14.5
90°	4.2	5.0	5.6	6.1	6.7	7.4	7.7	8.2	8.7	9.1	9.4
92.5°	4.3	4.7	5.3	5.8	6.5	7.1	7.5	7.9	8.4	8.9	9.0
95°	8.3	7.1	7.1	7.2	7.3	7.4	7.7	8.2	8.7	9.1	9.3
97.5°	45.1	41.8	33.6	25.4	17.1	8.8	8.9	8.9	9.0	9.0	9.0
100°	59.9	55.5	45.3	35.1	24.9	14.7	13.4	12.2	10.8	9.6	9.0
102.5°	76.2	76.0	74.6	73.3	71.9	70.6	57.0	43.5	29.9	16.3	9.5
105°	102.1	102.5	102.8	103.2	103.6	104.0	104.6	105.3	105.9	106.6	105.6
107.5°	127.2	127.5	128.1	128.6	129.0	129.6	129.9	130.3	130.5	130.9	131.2
110°	144.8	145.2	145.5	146.0	146.5	146.9	147.0	147.2	147.3	147.5	147.7



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	162.6	162.9	163.1	163.2	163.4	163.7	163.6	163.6	163.6	163.5	163.7
115°	188.1	188.1	188.1	188.0	187.9	187.8	188.0	188.1	188.3	188.5	188.5
117.5°	212.1	212.3	212.4	212.6	212.7	212.9	212.9	212.8	212.8	212.8	212.7
120°	228.0	228.1	228.1	228.0	227.9	227.8	228.0	228.1	228.3	228.5	228.5
122.5°	242.5	242.6	242.7	242.8	242.9	243.1	243.1	243.2	243.3	243.4	243.4
125°	264.4	264.4	264.3	264.1	264.0	263.8	264.0	264.3	264.5	264.7	264.9
127.5°	283.7	283.9	284.3	284.6	284.9	285.3	285.2	285.2	285.1	285.1	285.0
130°	296.8	296.9	297.1	297.4	297.6	297.8	297.8	297.9	298.0	298.1	298.1
132.5°	309.0	309.2	309.4	309.7	310.0	310.3	310.4	310.5	310.6	310.7	310.7
135°	326.1	326.2	326.6	326.9	327.2	327.4	327.6	327.7	327.9	328.0	328.2
137.5°	342.5	342.7	343.0	343.3	343.7	343.9	344.1	344.3	344.5	344.6	344.7
140°	353.4	353.5	353.6	353.8	353.9	354.1	354.3	354.5	354.8	355.0	355.2
142.5°	363.2	363.4	363.4	363.5	363.6	363.7	363.8	364.0	364.2	364.3	364.4
145°	377.3	377.4	377.4	377.4	377.4	377.4	377.5	377.6	377.7	377.7	377.8
147.5°	389.5	389.6	389.6	389.5	389.4	389.4	389.4	389.5	389.6	389.6	389.6
150°	397.3	397.4	397.3	397.2	397.1	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	404.0	404.0	403.9	403.7	403.6	403.5	403.6	403.7	403.8	404.0	404.0
155°	413.0	412.9	412.7	412.5	412.3	412.1	412.4	412.6	412.9	413.2	413.3
157.5°	420.8	420.6	420.4	420.1	419.8	419.6	420.0	420.4	420.8	421.1	421.1
160°	424.8	424.7	424.6	424.5	424.4	424.3	424.8	425.3	425.7	426.1	426.1
162.5°	428.9	428.7	428.6	428.5	428.5	428.4	428.9	429.2	429.7	430.2	430.1
165°	433.9	433.7	433.7	433.7	433.7	433.7	434.3	434.9	435.5	436.1	436.0
167.5°	438.1	437.9	437.8	437.8	437.7	437.7	438.4	439.0	439.7	440.3	440.3
170°	440.3	440.1	440.2	440.3	440.3	440.4	440.9	441.6	442.1	442.7	442.6
172.5°	441.9	441.7	441.8	441.9	441.9	442.0	442.5	443.2	443.7	444.3	444.2
175°	443.6	443.4	443.5	443.6	443.7	443.7	444.4	445.1	445.7	446.4	446.3
177.5°	444.5	444.3	444.5	444.6	444.7	444.8	445.4	445.8	446.3	446.8	446.6
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1782.9	1784.1	1779.9	1778.7	1779.9	1784.1	1782.9	1786.5	1787.2	1792.0	1790.2
5°	1654.1	1652.6	1648.8	1649.5	1648.8	1652.6	1654.1	1660.1	1663.1	1675.2	1673.7
7.5°	1543.9	1538.0	1539.6	1533.7	1539.6	1538.0	1543.9	1549.4	1558.5	1564.0	1576.7
10°	1476.5	1468.2	1461.4	1455.4	1461.4	1468.2	1476.5	1479.5	1492.2	1498.3	1511.1
12.5°	1384.4	1377.2	1368.1	1369.9	1368.1	1377.2	1384.4	1397.6	1414.0	1426.6	1446.7
15°	1253.7	1242.5	1224.4	1226.6	1224.4	1242.5	1253.7	1263.5	1280.1	1308.6	1322.2
17.5°	1143.1	1143.2	1135.0	1136.9	1135.0	1143.2	1143.1	1156.5	1164.9	1183.2	1203.9
20°	1085.9	1080.6	1081.4	1079.1	1081.4	1080.6	1085.9	1101.7	1110.8	1123.5	1146.1
22.5°	1046.1	1039.7	1034.4	1029.7	1034.4	1039.7	1046.1	1050.6	1062.6	1074.8	1093.2
25°	979.0	974.5	967.8	966.3	967.8	974.5	979.0	985.8	991.8	1007.7	1018.9
27.5°	920.0	919.2	916.4	912.9	916.4	919.2	920.0	926.0	933.9	944.0	958.3
30°	885.7	884.2	882.7	880.4	882.7	884.2	885.7	891.7	897.8	906.1	917.4
32.5°	855.1	854.1	852.6	852.8	852.6	854.1	855.1	858.0	861.7	872.3	881.2
35°	811.2	810.5	809.0	808.2	809.0	810.5	811.2	814.3	816.5	819.5	827.1
37.5°	770.3	772.2	771.4	771.2	771.4	772.2	770.3	771.1	768.6	774.0	779.2
40°	742.0	742.7	744.2	743.5	744.2	742.7	742.0	742.7	742.7	742.7	747.2
42.5°	718.5	718.7	720.8	718.2	720.8	718.7	718.5	715.7	712.1	712.7	714.2
45°	676.6	681.1	680.3	680.3	680.3	681.1	676.6	671.3	670.5	667.5	667.5
47.5°	630.7	634.5	635.6	635.5	635.6	634.5	630.7	628.7	625.2	622.2	621.9
50°	600.5	599.0	601.2	600.5	601.2	599.0	600.5	596.7	591.4	591.4	590.0
52.5°	563.8	564.1	563.9	563.2	563.9	564.1	563.8	561.8	559.6	557.1	556.3
55°	507.2	507.9	506.4	507.2	506.4	507.9	507.2	506.4	506.4	504.9	506.4
57.5°	445.8	442.1	443.7	441.9	443.7	442.1	445.8	449.1	450.3	450.6	452.9
60°	401.9	395.9	394.4	391.3	394.4	395.9	401.9	409.3	412.4	413.9	416.1
62.5°	352.5	348.3	343.2	345.5	343.2	348.3	352.5	360.6	367.2	372.4	377.6
65°	286.7	283.7	281.4	284.5	281.4	283.7	286.7	292.8	298.8	310.8	322.1
67.5°	237.3	235.7	235.7	234.2	235.7	235.7	237.3	240.3	244.1	250.7	261.3
70°	211.5	209.2	209.2	207.7	209.2	209.2	211.5	211.5	215.2	218.2	225.7
72.5°	184.9	182.8	183.3	182.4	183.3	182.8	184.9	185.6	189.4	190.6	193.9
75°	137.0	133.2	133.2	133.9	133.2	133.2	137.0	141.5	145.2	152.0	153.5
77.5°	102.2	101.4	102.5	101.1	102.5	101.4	102.2	102.2	102.9	106.1	108.7
80°	83.5	82.8	82.0	84.3	82.0	82.8	83.5	83.5	84.3	85.0	85.8
82.5°	64.8	64.8	64.6	67.4	64.6	64.8	64.8	66.1	66.3	65.8	66.5
85°	39.1	37.6	39.1	37.6	39.1	37.6	39.1	38.4	39.1	38.4	39.1
87.5°	15.7	15.2	14.6	15.3	14.6	15.2	15.7	14.5	14.4	15.6	14.9
90°	9.5	9.7	9.8	10.0	9.8	9.7	9.5	9.4	9.1	8.7	8.2
92.5°	9.1	9.1	9.1	9.2	9.1	9.1	9.1	9.0	8.9	8.4	7.9
95°	9.4	9.5	9.6	9.6	9.6	9.5	9.4	9.3	9.1	8.7	8.2
97.5°	9.1	9.1	9.2	9.3	9.2	9.1	9.1	9.0	9.0	9.0	8.9
100°	9.1	9.1	9.2	9.3	9.2	9.1	9.1	9.0	9.6	10.8	12.2
102.5°	9.5	9.5	9.6	9.6	9.6	9.5	9.5	9.5	16.3	29.9	43.5
105°	102.9	100.3	97.6	94.9	97.6	100.3	102.9	105.6	106.6	105.9	105.3
107.5°	131.5	131.8	132.1	132.3	132.1	131.8	131.5	131.2	130.9	130.5	130.3
110°	147.9	148.2	148.4	148.5	148.4	148.2	147.9	147.7	147.5	147.3	147.2



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	164.0	164.3	164.6	164.9	164.6	164.3	164.0	163.7	163.5	163.6	163.6
115°	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.5	188.3	188.1
117.5°	212.7	212.7	212.7	212.6	212.7	212.7	212.7	212.7	212.8	212.8	212.8
120°	228.3	228.1	228.0	227.8	228.0	228.1	228.3	228.5	228.5	228.3	228.1
122.5°	243.2	243.1	242.9	242.8	242.9	243.1	243.2	243.4	243.4	243.3	243.2
125°	264.9	265.0	265.0	265.1	265.0	265.0	264.9	264.9	264.7	264.5	264.3
127.5°	285.0	284.9	284.8	284.8	284.8	284.9	285.0	285.0	285.1	285.1	285.2
130°	298.1	298.1	298.1	298.1	298.1	298.1	298.1	298.1	298.1	298.0	297.9
132.5°	310.6	310.5	310.5	310.4	310.5	310.5	310.6	310.7	310.7	310.6	310.5
135°	328.3	328.5	328.7	328.8	328.7	328.5	328.3	328.2	328.0	327.9	327.7
137.5°	344.6	344.6	344.5	344.5	344.5	344.6	344.6	344.7	344.6	344.5	344.3
140°	355.2	355.2	355.3	355.4	355.3	355.2	355.2	355.2	355.0	354.8	354.5
142.5°	364.5	364.5	364.5	364.5	364.5	364.5	364.5	364.4	364.3	364.2	364.0
145°	378.0	378.1	378.2	378.4	378.2	378.1	378.0	377.8	377.7	377.7	377.6
147.5°	389.7	389.7	389.8	389.9	389.8	389.7	389.7	389.6	389.6	389.6	389.5
150°	397.2	397.3	397.3	397.4	397.3	397.3	397.2	397.1	397.1	397.1	397.1
152.5°	403.9	403.9	403.9	403.8	403.9	403.9	403.9	404.0	404.0	403.8	403.7
155°	413.0	412.8	412.6	412.4	412.6	412.8	413.0	413.3	413.2	412.9	412.6
157.5°	420.8	420.4	420.0	419.6	420.0	420.4	420.8	421.1	421.1	420.8	420.4
160°	425.7	425.3	424.8	424.3	424.8	425.3	425.7	426.1	426.1	425.7	425.3
162.5°	429.6	429.1	428.6	428.1	428.6	429.1	429.6	430.1	430.2	429.7	429.2
165°	435.4	434.7	434.0	433.4	434.0	434.7	435.4	436.0	436.1	435.5	434.9
167.5°	439.5	438.8	438.0	437.3	438.0	438.8	439.5	440.3	440.3	439.7	439.0
170°	442.0	441.2	440.5	439.7	440.5	441.2	442.0	442.6	442.7	442.1	441.6
172.5°	443.5	442.6	441.9	441.0	441.9	442.6	443.5	444.2	444.3	443.7	443.2
175°	445.4	444.5	443.6	442.7	443.6	444.5	445.4	446.3	446.4	445.7	445.1
177.5°	445.9	445.2	444.5	443.7	444.5	445.2	445.9	446.6	446.8	446.3	445.8
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1786.5	1790.7	1800.4	1811.2	1820.2	1828.1	1834.1	1842.5	1850.3	1861.1	1871.4
5°	1678.2	1688.7	1703.7	1721.8	1744.4	1759.4	1778.2	1794.8	1818.9	1843.0	1866.3
7.5°	1583.0	1594.6	1616.7	1641.7	1668.5	1693.2	1715.5	1744.6	1776.6	1811.7	1850.8
10°	1521.6	1534.5	1560.8	1589.3	1621.0	1645.0	1675.2	1709.8	1745.9	1788.8	1836.9
12.5°	1466.2	1478.5	1510.1	1539.4	1572.2	1598.6	1633.6	1668.9	1717.0	1763.5	1818.3
15°	1358.3	1390.7	1426.8	1461.4	1500.5	1533.0	1575.1	1611.2	1657.1	1722.6	1785.0
17.5°	1238.5	1273.0	1317.9	1371.3	1423.8	1463.9	1506.6	1551.4	1606.1	1672.9	1745.0
20°	1168.7	1196.6	1246.2	1305.6	1366.6	1422.3	1461.4	1511.1	1567.5	1639.7	1714.3
22.5°	1116.3	1139.9	1178.7	1238.2	1304.0	1368.7	1418.7	1467.7	1530.2	1602.4	1683.6
25°	1037.7	1063.4	1097.2	1137.8	1213.1	1281.6	1347.1	1403.4	1469.7	1541.9	1632.2
27.5°	972.4	994.7	1025.7	1068.0	1118.6	1194.1	1273.5	1337.8	1405.7	1483.3	1573.7
30°	933.9	952.0	977.5	1020.4	1068.6	1136.3	1216.8	1292.1	1360.6	1441.1	1535.2
32.5°	893.5	912.9	937.8	971.7	1023.4	1080.3	1160.8	1243.3	1316.1	1398.4	1490.6
35°	839.8	854.9	877.4	912.1	958.8	1008.4	1079.9	1164.9	1241.7	1329.7	1417.8
37.5°	785.5	803.2	821.0	851.9	890.1	943.5	1002.1	1088.9	1173.9	1254.3	1340.3
40°	754.8	765.3	784.9	809.7	850.4	897.8	952.7	1037.7	1122.8	1202.6	1289.1
42.5°	720.5	732.3	748.8	773.6	810.0	856.2	909.9	983.5	1072.2	1149.6	1228.3
45°	672.8	679.6	696.1	717.2	747.2	793.9	843.6	909.1	992.6	1066.3	1135.6
47.5°	624.6	630.5	640.8	660.2	693.8	731.3	777.8	836.5	909.8	983.5	1042.1
50°	591.4	596.7	606.5	624.6	654.7	691.5	737.4	790.1	855.6	926.3	975.2
52.5°	558.4	561.3	570.4	590.9	616.1	652.4	693.5	742.0	803.2	862.0	911.4
55°	505.7	512.5	518.5	533.6	557.6	592.2	629.1	675.0	722.5	772.1	814.3
57.5°	450.7	458.2	466.8	480.1	499.3	531.4	564.6	601.7	642.2	683.4	718.8
60°	414.6	421.4	429.0	444.0	461.3	486.9	523.0	555.3	586.3	623.9	659.2
62.5°	379.1	385.9	394.6	406.7	423.4	447.8	477.9	506.1	538.1	570.9	597.2
65°	326.6	331.9	338.7	350.0	365.7	387.6	412.4	434.2	462.8	486.9	511.0
67.5°	269.0	279.1	287.9	297.1	310.5	330.8	348.7	369.7	389.1	407.0	429.0
70°	231.0	242.3	250.6	260.3	273.1	290.5	307.7	322.1	337.9	355.2	374.8
72.5°	199.2	208.0	214.4	224.9	236.5	252.5	268.6	280.5	293.3	305.2	324.2
75°	157.3	161.1	165.6	173.8	184.4	196.4	209.2	219.7	227.2	237.8	251.4
77.5°	113.0	120.3	123.3	129.1	136.7	144.2	152.6	161.5	168.7	172.5	182.9
80°	86.5	89.5	92.6	100.9	105.4	112.9	118.9	127.1	130.2	133.9	143.7
82.5°	67.3	69.1	70.9	73.1	75.9	83.4	89.4	94.6	97.6	99.1	106.4
85°	39.1	39.9	40.6	41.4	42.1	42.1	45.1	48.9	54.2	54.2	56.5
87.5°	14.8	15.3	15.2	14.5	15.6	15.5	15.9	15.7	17.3	19.0	20.6
90°	7.7	7.4	6.7	6.1	5.6	5.0	4.2	3.5	2.6	1.8	1.0
92.5°	7.5	7.1	6.5	5.8	5.3	4.7	4.3	4.3	4.2	4.2	4.2
95°	7.7	7.4	7.3	7.2	7.1	7.1	8.3	10.7	13.3	15.8	18.3
97.5°	8.9	8.8	17.1	25.4	33.6	41.8	45.1	43.6	42.0	40.4	38.9
100°	13.4	14.7	24.9	35.1	45.3	55.5	59.9	58.6	57.3	56.0	54.7
102.5°	57.0	70.6	71.9	73.3	74.6	76.0	76.2	75.1	74.2	73.2	72.2
105°	104.6	104.0	103.6	103.2	102.8	102.5	102.1	101.6	101.1	100.7	100.3
107.5°	129.9	129.6	129.0	128.6	128.1	127.5	127.2	127.0	126.8	126.5	126.3
110°	147.0	146.9	146.5	146.0	145.5	145.2	144.8	144.6	144.3	144.1	143.9



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	163.6	163.7	163.4	163.2	163.1	162.9	162.6	162.1	161.7	161.4	161.0
115°	188.0	187.8	187.9	188.0	188.1	188.1	188.1	187.8	187.7	187.5	187.2
117.5°	212.9	212.9	212.7	212.6	212.4	212.3	212.1	211.8	211.4	211.1	210.8
120°	228.0	227.8	227.9	228.0	228.1	228.1	228.0	227.7	227.4	227.2	226.9
122.5°	243.1	243.1	242.9	242.8	242.7	242.6	242.5	242.3	242.1	242.0	241.8
125°	264.0	263.8	264.0	264.1	264.3	264.4	264.4	264.0	263.7	263.4	263.2
127.5°	285.2	285.3	284.9	284.6	284.3	283.9	283.7	283.6	283.5	283.5	283.4
130°	297.8	297.8	297.6	297.4	297.1	296.9	296.8	296.7	296.6	296.5	296.4
132.5°	310.4	310.3	310.0	309.7	309.4	309.2	309.0	308.9	308.7	308.6	308.5
135°	327.6	327.4	327.2	326.9	326.6	326.2	326.1	326.2	326.3	326.4	326.4
137.5°	344.1	343.9	343.7	343.3	343.0	342.7	342.5	342.4	342.4	342.4	342.3
140°	354.3	354.1	353.9	353.8	353.6	353.5	353.4	353.2	353.1	352.9	352.8
142.5°	363.8	363.7	363.6	363.5	363.4	363.4	363.2	362.9	362.6	362.3	362.1
145°	377.5	377.4	377.4	377.4	377.4	377.4	377.3	377.1	376.8	376.6	376.5
147.5°	389.4	389.4	389.4	389.5	389.6	389.6	389.5	389.1	388.6	388.2	387.8
150°	397.1	397.1	397.1	397.2	397.3	397.4	397.3	397.0	396.6	396.3	396.1
152.5°	403.6	403.5	403.6	403.7	403.9	404.0	404.0	403.7	403.5	403.2	403.0
155°	412.4	412.1	412.3	412.5	412.7	412.9	413.0	412.9	412.8	412.8	412.7
157.5°	420.0	419.6	419.8	420.1	420.4	420.6	420.8	420.8	420.8	420.8	420.9
160°	424.8	424.3	424.4	424.5	424.6	424.7	424.8	425.1	425.3	425.5	425.7
162.5°	428.9	428.4	428.5	428.5	428.6	428.7	428.9	429.1	429.4	429.7	430.0
165°	434.3	433.7	433.7	433.7	433.7	433.7	433.9	434.2	434.6	435.0	435.4
167.5°	438.4	437.7	437.7	437.8	437.8	437.9	438.1	438.5	438.8	439.2	439.6
170°	440.9	440.4	440.3	440.3	440.2	440.1	440.3	440.7	441.1	441.6	442.1
172.5°	442.5	442.0	441.9	441.9	441.8	441.7	441.9	442.3	442.7	443.2	443.7
175°	444.4	443.7	443.7	443.6	443.5	443.4	443.6	444.0	444.5	444.9	445.4
177.5°	445.4	444.8	444.7	444.6	444.5	444.3	444.5	444.9	445.4	445.7	446.2
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830
 CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1879.2	1884.6	1890.6	1902.1	1911.8	1916.0	1924.4	1930.4	1928.6	1937.0	1951.4
5°	1886.6	1907.0	1930.2	1954.4	1981.4	2004.0	2022.0	2040.1	2054.5	2071.7	2097.3
7.5°	1885.4	1921.6	1960.8	2004.0	2048.4	2086.8	2122.3	2158.4	2190.5	2225.5	2271.4
10°	1880.6	1928.7	1977.6	2034.1	2090.6	2144.0	2192.2	2237.3	2280.2	2326.1	2384.1
12.5°	1875.2	1930.5	1989.7	2057.6	2127.9	2192.2	2248.7	2313.8	2367.5	2426.7	2493.6
15°	1851.2	1925.7	2006.3	2094.3	2178.6	2265.1	2342.6	2422.4	2496.9	2567.7	2651.9
17.5°	1823.8	1909.8	2004.8	2108.8	2210.1	2315.3	2407.3	2507.7	2583.9	2678.9	2757.1
20°	1801.6	1894.1	1995.7	2112.3	2227.5	2344.1	2445.7	2548.1	2633.8	2729.4	2828.8
22.5°	1774.4	1876.0	1986.1	2107.0	2227.5	2354.9	2467.4	2569.2	2675.4	2783.0	2885.4
25°	1730.8	1836.2	1952.9	2085.3	2223.7	2353.9	2474.4	2600.8	2715.2	2831.8	2923.6
27.5°	1677.3	1787.9	1910.8	2047.5	2189.6	2322.9	2464.7	2599.4	2714.5	2826.8	2906.9
30°	1634.5	1751.1	1869.3	2007.8	2155.2	2298.2	2450.2	2584.9	2706.1	2807.0	2852.1
32.5°	1590.5	1701.2	1823.0	1963.2	2114.3	2268.1	2418.9	2556.6	2668.8	2729.3	2730.5
35°	1514.1	1618.0	1744.4	1882.1	2037.1	2204.1	2356.9	2492.4	2560.9	2566.2	2492.4
37.5°	1430.7	1526.0	1645.3	1783.2	1952.9	2119.1	2275.2	2365.5	2388.4	2311.8	2175.4
40°	1371.1	1459.2	1574.3	1715.8	1884.3	2056.0	2198.2	2264.4	2240.3	2116.1	1964.1
42.5°	1308.5	1390.5	1501.5	1641.2	1810.3	1983.7	2104.9	2140.3	2076.5	1933.2	1755.2
45°	1206.4	1281.6	1391.5	1532.2	1694.7	1857.3	1949.1	1931.0	1824.9	1654.8	1455.4
47.5°	1099.9	1172.6	1271.5	1401.7	1568.1	1708.4	1770.6	1716.1	1565.1	1378.0	1215.8
50°	1029.4	1104.0	1195.0	1319.2	1471.2	1606.7	1646.5	1563.8	1395.9	1216.1	1067.1
52.5°	960.3	1023.9	1113.1	1233.1	1378.5	1492.9	1514.1	1418.7	1245.5	1084.2	952.1
55°	854.9	912.9	988.1	1101.0	1226.6	1323.7	1312.4	1189.8	1032.5	894.8	790.9
57.5°	753.0	796.6	866.2	971.9	1082.3	1147.5	1106.3	1001.6	855.1	742.3	654.7
60°	685.6	726.2	790.9	883.4	980.5	1017.4	982.8	869.2	753.3	650.2	576.5
62.5°	621.7	657.6	713.2	799.2	877.6	899.5	862.4	763.2	658.7	570.7	509.6
65°	529.0	562.1	609.5	670.5	724.7	735.2	711.1	609.5	530.6	456.8	414.6
67.5°	444.9	466.6	503.6	556.3	585.0	591.2	544.7	480.9	411.2	365.9	334.1
70°	388.3	403.3	438.0	466.6	489.9	490.7	447.8	396.6	343.2	306.3	283.0
72.5°	333.6	348.0	374.2	393.7	411.6	405.8	366.5	326.1	283.0	255.1	237.8
75°	257.4	270.1	283.7	292.8	292.8	285.2	256.7	226.5	201.7	185.1	179.8
77.5°	187.1	197.7	202.2	200.8	198.0	186.3	168.2	148.5	139.7	131.9	127.9
80°	146.8	151.3	152.8	149.0	144.5	130.9	118.9	110.7	102.4	99.3	97.8
82.5°	108.8	112.7	108.8	109.9	99.9	88.8	82.2	79.4	75.9	74.6	73.1
85°	58.0	57.2	55.7	51.9	45.1	43.6	42.9	42.1	40.6	41.4	39.9
87.5°	20.3	18.6	16.3	15.9	16.0	15.0	15.6	15.8	15.9	15.4	16.7
90°	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7	8.2
92.5°	4.2	4.2	4.3	4.3	4.7	5.3	5.8	6.5	7.1	7.5	7.9
95°	15.8	13.3	10.7	8.3	7.1	7.1	7.2	7.3	7.4	7.7	8.2
97.5°	40.4	42.0	43.6	45.1	41.8	33.6	25.4	17.1	8.8	8.9	8.9
100°	56.0	57.3	58.6	59.9	55.5	45.3	35.1	24.9	14.7	13.4	12.2
102.5°	73.2	74.2	75.1	76.2	76.0	74.6	73.3	71.9	70.6	57.0	43.5
105°	100.7	101.1	101.6	102.1	102.5	102.8	103.2	103.6	104.0	104.6	105.3
107.5°	126.5	126.8	127.0	127.2	127.5	128.1	128.6	129.0	129.6	129.9	130.3
110°	144.1	144.3	144.6	144.8	145.2	145.5	146.0	146.5	146.9	147.0	147.2



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.4	161.7	162.1	162.6	162.9	163.1	163.2	163.4	163.7	163.6	163.6
115°	187.5	187.7	187.8	188.1	188.1	188.1	188.0	187.9	187.8	188.0	188.1
117.5°	211.1	211.4	211.8	212.1	212.3	212.4	212.6	212.7	212.9	212.9	212.8
120°	227.2	227.4	227.7	228.0	228.1	228.1	228.0	227.9	227.8	228.0	228.1
122.5°	242.0	242.1	242.3	242.5	242.6	242.7	242.8	242.9	243.1	243.1	243.2
125°	263.4	263.7	264.0	264.4	264.4	264.3	264.1	264.0	263.8	264.0	264.3
127.5°	283.5	283.5	283.6	283.7	283.9	284.3	284.6	284.9	285.3	285.2	285.2
130°	296.5	296.6	296.7	296.8	296.9	297.1	297.4	297.6	297.8	297.8	297.9
132.5°	308.6	308.7	308.9	309.0	309.2	309.4	309.7	310.0	310.3	310.4	310.5
135°	326.4	326.3	326.2	326.1	326.2	326.6	326.9	327.2	327.4	327.6	327.7
137.5°	342.4	342.4	342.4	342.5	342.7	343.0	343.3	343.7	343.9	344.1	344.3
140°	352.9	353.1	353.2	353.4	353.5	353.6	353.8	353.9	354.1	354.3	354.5
142.5°	362.3	362.6	362.9	363.2	363.4	363.4	363.5	363.6	363.7	363.8	364.0
145°	376.6	376.8	377.1	377.3	377.4	377.4	377.4	377.4	377.4	377.5	377.6
147.5°	388.2	388.6	389.1	389.5	389.6	389.6	389.5	389.4	389.4	389.4	389.5
150°	396.3	396.6	397.0	397.3	397.4	397.3	397.2	397.1	397.1	397.1	397.1
152.5°	403.2	403.5	403.7	404.0	404.0	403.9	403.7	403.6	403.5	403.6	403.7
155°	412.8	412.8	412.9	413.0	412.9	412.7	412.5	412.3	412.1	412.4	412.6
157.5°	420.8	420.8	420.8	420.8	420.6	420.4	420.1	419.8	419.6	420.0	420.4
160°	425.5	425.3	425.1	424.8	424.7	424.6	424.5	424.4	424.3	424.8	425.3
162.5°	429.7	429.4	429.1	428.9	428.7	428.6	428.5	428.5	428.4	428.9	429.2
165°	435.0	434.6	434.2	433.9	433.7	433.7	433.7	433.7	433.7	434.3	434.9
167.5°	439.2	438.8	438.5	438.1	437.9	437.8	437.8	437.7	437.7	438.4	439.0
170°	441.6	441.1	440.7	440.3	440.1	440.2	440.3	440.3	440.4	440.9	441.6
172.5°	443.2	442.7	442.3	441.9	441.7	441.8	441.9	441.9	442.0	442.5	443.2
175°	444.9	444.5	444.0	443.6	443.4	443.5	443.6	443.7	443.7	444.4	445.1
177.5°	445.7	445.4	444.9	444.5	444.3	444.5	444.6	444.7	444.8	445.4	445.8
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1959.3	1961.7	1963.5	1969.5	1970.1	1975.6	1970.1
5°	2121.4	2131.9	2148.5	2165.0	2166.5	2177.1	2158.2
7.5°	2303.2	2327.6	2342.8	2369.6	2380.1	2386.7	2375.9
10°	2428.5	2451.0	2490.9	2510.5	2530.1	2533.0	2524.0
12.5°	2549.5	2585.3	2616.7	2653.7	2652.9	2679.4	2669.7
15°	2710.7	2747.5	2791.2	2832.5	2847.6	2847.6	2859.7
17.5°	2825.6	2893.2	2938.4	2970.9	3006.3	3012.6	3008.3
20°	2903.3	2976.3	3024.4	3066.6	3090.7	3097.5	3097.5
22.5°	2961.1	3023.2	3070.2	3108.1	3128.0	3135.9	3133.6
25°	3001.1	3054.5	3083.2	3094.5	3099.6	3098.2	3083.9
27.5°	2946.3	2943.9	2925.8	2891.2	2865.2	2849.4	2831.3
30°	2841.6	2802.5	2757.3	2707.6	2643.6	2594.7	2579.6
32.5°	2685.7	2597.7	2521.3	2438.5	2369.7	2320.8	2300.4
35°	2384.1	2244.9	2131.2	2031.8	1959.6	1914.5	1899.4
37.5°	2026.1	1891.4	1750.7	1654.4	1594.5	1548.9	1531.8
40°	1798.6	1651.8	1529.2	1438.9	1377.1	1332.8	1332.0
42.5°	1590.8	1450.8	1335.3	1270.3	1203.7	1174.4	1174.2
45°	1302.6	1190.5	1092.7	1041.5	1001.6	977.5	970.7
47.5°	1078.6	985.8	920.7	879.9	847.3	832.0	822.1
50°	952.7	871.5	819.5	784.1	766.1	746.5	745.0
52.5°	847.9	782.3	741.9	713.1	690.2	678.4	678.8
55°	712.7	660.7	632.2	610.3	592.2	583.2	579.5
57.5°	600.4	561.4	540.6	520.6	512.9	505.9	503.9
60°	530.6	504.2	484.7	468.8	457.5	455.2	454.5
62.5°	472.8	445.2	431.7	419.4	411.2	407.7	406.3
65°	389.8	369.5	357.4	347.7	344.7	339.4	338.7
67.5°	314.2	302.1	294.1	287.3	283.2	283.0	283.0
70°	267.9	261.1	254.4	250.6	248.4	246.9	246.9
72.5°	228.2	223.2	217.6	215.7	215.2	213.7	213.1
75°	173.8	168.5	169.3	165.6	162.6	158.8	156.6
77.5°	123.3	119.5	118.8	118.3	115.7	115.3	116.5
80°	95.6	91.8	91.0	91.8	91.0	88.8	88.8
82.5°	72.7	69.6	68.8	68.3	67.6	68.3	67.1
85°	39.1	37.6	37.6	37.6	39.1	38.4	37.6
87.5°	15.6	15.1	15.7	15.2	15.2	14.6	15.3
90°	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	8.4	8.9	9.0	9.1	9.1	9.1	9.2
95°	8.7	9.1	9.3	9.4	9.5	9.6	9.6
97.5°	9.0	9.0	9.0	9.1	9.1	9.2	9.3
100°	10.8	9.6	9.0	9.1	9.1	9.2	9.3
102.5°	29.9	16.3	9.5	9.5	9.5	9.6	9.6
105°	105.9	106.6	105.6	102.9	100.3	97.6	94.9
107.5°	130.5	130.9	131.2	131.5	131.8	132.1	132.3
110°	147.3	147.5	147.7	147.9	148.2	148.4	148.5



TEST NUMBER: P332985-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	163.6	163.5	163.7	164.0	164.3	164.6	164.9
115°	188.3	188.5	188.5	188.5	188.5	188.5	188.5
117.5°	212.8	212.8	212.7	212.7	212.7	212.7	212.6
120°	228.3	228.5	228.5	228.3	228.1	228.0	227.8
122.5°	243.3	243.4	243.4	243.2	243.1	242.9	242.8
125°	264.5	264.7	264.9	264.9	265.0	265.0	265.1
127.5°	285.1	285.1	285.0	285.0	284.9	284.8	284.8
130°	298.0	298.1	298.1	298.1	298.1	298.1	298.1
132.5°	310.6	310.7	310.7	310.6	310.5	310.5	310.4
135°	327.9	328.0	328.2	328.3	328.5	328.7	328.8
137.5°	344.5	344.6	344.7	344.6	344.6	344.5	344.5
140°	354.8	355.0	355.2	355.2	355.2	355.3	355.4
142.5°	364.2	364.3	364.4	364.5	364.5	364.5	364.5
145°	377.7	377.7	377.8	378.0	378.1	378.2	378.4
147.5°	389.6	389.6	389.6	389.7	389.7	389.8	389.9
150°	397.1	397.1	397.1	397.2	397.3	397.3	397.4
152.5°	403.8	404.0	404.0	403.9	403.9	403.9	403.8
155°	412.9	413.2	413.3	413.0	412.8	412.6	412.4
157.5°	420.8	421.1	421.1	420.8	420.4	420.0	419.6
160°	425.7	426.1	426.1	425.7	425.3	424.8	424.3
162.5°	429.7	430.2	430.1	429.6	429.1	428.6	428.1
165°	435.5	436.1	436.0	435.4	434.7	434.0	433.4
167.5°	439.7	440.3	440.3	439.5	438.8	438.0	437.3
170°	442.1	442.7	442.6	442.0	441.2	440.5	439.7
172.5°	443.7	444.3	444.2	443.5	442.6	441.9	441.0
175°	445.7	446.4	446.3	445.4	444.5	443.6	442.7
177.5°	446.3	446.8	446.6	445.9	445.2	444.5	443.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4

(END OF REPORT)