

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332505-840

Luminaire Tested: **SA4XXDIP-C350D590U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332505-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D590U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3915.5 lumens
Efficiency: N/A
Efficacy: 152.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332505-840
CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.4
10°-20°	158.3	4.0
20°-30°	233.0	6.0
30°-40°	270.8	6.9
40°-50°	270.9	6.9
50°-60°	236.9	6.1
60°-70°	175.9	4.5
70°-80°	100.0	2.6
80°-90°	31.1	0.8
90°-100°	26.3	0.7
100°-110°	168.0	4.3
110°-120°	321.3	8.2
120°-130°	407.9	10.4
130°-140°	436.4	11.1
140°-150°	408.1	10.4
150°-160°	329.1	8.4
160°-170°	212.2	5.4
170°-180°	73.2	1.9
0°-30°	447.4	11.4
0°-40°	718.3	18.3
0°-60°	1226.1	31.3
0°-90°	1533.0	39.2
90°-120°	515.6	13.2
90°-150°	1767.9	45.2
90°-180°	2382.0	60.8
0°-180°	3915.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	2	8	13	16	17	3
95°	32	13	13	16	17	41
105°	173	177	180	183	164	181
115°	324	325	325	326	326	318
125°	455	457	456	458	459	406
135°	564	564	566	567	569	435
145°	651	653	653	653	654	407
155°	714	714	713	715	713	329
165°	753	750	750	754	749	213
175°	770	767	767	772	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.3	10.5	10.7	10.9	11.1	11.2	11.3	11.5	11.6	11.7	11.8
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	7.3	7.4	7.4	7.5	7.6	8.1	9.2	10.2	11.2	12.2	13.0
95°	31.7	27.4	23.0	18.6	14.2	12.1	12.3	12.4	12.5	12.6	13.4
97.5°	67.3	70.0	72.7	75.4	78.2	72.3	58.1	43.8	29.5	15.2	15.2
100°	94.4	96.7	99.1	101.4	103.7	96.0	78.4	60.7	43.0	25.3	23.1
102.5°	124.9	126.5	128.3	130.0	131.7	131.4	129.1	126.7	124.4	122.1	98.7
105°	173.4	174.2	174.9	175.7	176.4	177.1	177.8	178.4	179.0	179.8	180.9
107.5°	218.4	218.8	219.2	219.5	219.9	220.6	221.5	222.4	223.2	224.1	224.7
110°	248.8	249.2	249.6	250.0	250.3	251.0	251.8	252.5	253.3	254.1	254.3



TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.0	279.7	280.4	281.1	281.7	282.0	282.4	282.8	283.1	283.1
115°	323.8	324.2	324.5	324.9	325.3	325.4	325.3	325.2	325.0	324.9	325.2
117.5°	364.7	365.2	365.7	366.2	366.7	367.1	367.4	367.7	367.9	368.2	368.2
120°	392.3	392.8	393.3	393.8	394.4	394.6	394.5	394.3	394.2	394.0	394.3
122.5°	418.1	418.4	418.7	419.0	419.3	419.6	419.8	419.9	420.1	420.3	420.4
125°	455.0	455.6	456.2	456.7	457.2	457.3	457.0	456.8	456.5	456.3	456.7
127.5°	490.1	490.2	490.4	490.5	490.6	491.0	491.6	492.1	492.7	493.3	493.2
130°	512.7	512.8	512.9	513.1	513.2	513.4	513.8	514.2	514.6	515.0	515.1
132.5°	533.4	533.6	533.9	534.1	534.3	534.7	535.2	535.6	536.1	536.6	536.7
135°	564.5	564.4	564.3	564.1	564.0	564.2	564.7	565.2	565.7	566.2	566.5
137.5°	592.1	592.1	592.2	592.2	592.3	592.6	593.1	593.7	594.3	594.8	595.1
140°	610.1	610.3	610.6	610.8	611.1	611.3	611.6	611.9	612.1	612.4	612.7
142.5°	626.2	626.6	627.1	627.5	628.0	628.3	628.4	628.6	628.7	628.9	629.2
145°	651.0	651.4	651.7	652.1	652.5	652.7	652.7	652.7	652.7	652.7	652.8
147.5°	670.7	671.4	672.1	672.8	673.5	673.8	673.7	673.6	673.4	673.3	673.4
150°	684.9	685.4	686.0	686.5	687.0	687.2	687.0	686.9	686.8	686.6	686.6
152.5°	696.9	697.3	697.7	698.1	698.5	698.6	698.4	698.2	697.9	697.7	697.9
155°	713.8	713.9	714.0	714.1	714.3	714.1	713.8	713.4	713.0	712.6	713.1
157.5°	727.9	727.8	727.7	727.7	727.6	727.3	726.9	726.5	726.0	725.6	726.3
160°	736.2	735.8	735.4	735.1	734.7	734.4	734.3	734.2	734.0	733.9	734.7
162.5°	743.6	743.1	742.6	742.1	741.6	741.3	741.1	741.0	740.9	740.8	741.5
165°	752.9	752.2	751.6	750.9	750.3	750.0	750.0	750.0	750.0	750.0	751.0
167.5°	760.2	759.6	758.9	758.3	757.6	757.2	757.2	757.1	757.0	756.9	758.1
170°	764.5	763.7	762.9	762.1	761.3	761.0	761.1	761.2	761.4	761.5	762.5
172.5°	767.2	766.4	765.7	764.9	764.2	763.8	764.0	764.1	764.2	764.3	765.4
175°	770.2	769.4	768.6	767.9	767.1	766.8	766.9	767.1	767.2	767.3	768.4
177.5°	771.5	770.8	770.1	769.4	768.7	768.4	768.6	768.8	769.0	769.2	770.1
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	12.0	12.2	12.3	12.4	12.5	12.5	12.6	12.6
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	13.7	14.5	15.2	15.7	15.8	15.8	15.9	15.9
95°	14.2	14.9	15.8	16.2	16.4	16.5	16.6	16.7
97.5°	15.3	15.5	15.6	15.7	15.8	15.9	16.0	16.2
100°	21.0	18.8	16.7	15.7	15.8	15.9	16.0	16.2
102.5°	75.1	51.7	28.2	16.5	16.6	16.6	16.6	16.6
105°	182.1	183.2	184.3	182.6	178.0	173.4	168.7	164.2
107.5°	225.2	225.8	226.3	226.8	227.3	227.8	228.3	228.8
110°	254.6	254.8	255.1	255.4	255.8	256.1	256.5	256.9



TEST NUMBER: P332505-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	283.0	283.0	282.9	283.1	283.6	284.1	284.6	285.0
115°	325.4	325.7	325.9	326.1	326.1	326.1	326.1	326.1
117.5°	368.1	368.1	368.0	368.0	367.9	367.9	367.8	367.8
120°	394.6	394.8	395.1	395.1	394.8	394.6	394.3	394.0
122.5°	420.6	420.7	420.9	420.8	420.6	420.3	420.1	419.8
125°	457.0	457.4	457.8	458.1	458.2	458.3	458.4	458.6
127.5°	493.2	493.1	493.0	492.9	492.8	492.7	492.6	492.5
130°	515.2	515.3	515.5	515.5	515.5	515.5	515.5	515.5
132.5°	536.9	537.0	537.1	537.1	537.0	536.9	536.8	536.7
135°	566.7	567.0	567.2	567.5	567.7	568.0	568.4	568.6
137.5°	595.4	595.7	595.9	596.0	596.0	595.9	595.8	595.7
140°	613.1	613.5	613.9	614.1	614.3	614.4	614.5	614.6
142.5°	629.4	629.8	630.1	630.3	630.3	630.3	630.3	630.4
145°	652.9	653.1	653.2	653.4	653.6	653.9	654.2	654.4
147.5°	673.5	673.6	673.7	673.8	674.0	674.1	674.2	674.3
150°	686.6	686.6	686.6	686.7	686.8	687.0	687.1	687.2
152.5°	698.1	698.3	698.5	698.6	698.5	698.4	698.3	698.3
155°	713.6	714.1	714.6	714.7	714.3	713.9	713.6	713.2
157.5°	726.9	727.6	728.2	728.2	727.6	726.9	726.3	725.6
160°	735.4	736.2	737.0	737.0	736.2	735.4	734.7	733.9
162.5°	742.4	743.1	743.9	743.9	743.0	742.0	741.2	740.3
165°	752.0	753.1	754.2	754.1	752.9	751.7	750.6	749.4
167.5°	759.2	760.3	761.4	761.3	760.1	758.8	757.5	756.3
170°	763.6	764.6	765.7	765.5	764.3	763.0	761.6	760.4
172.5°	766.4	767.4	768.4	768.2	766.9	765.5	764.1	762.7
175°	769.6	770.7	771.9	771.7	770.2	768.6	767.1	765.6
177.5°	770.9	771.7	772.5	772.3	771.1	769.9	768.6	767.4
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2

(END OF REPORT)