

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332989-830

Luminaire Tested: **SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332989-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5737.5 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332989-830
CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	105	100	97	93	100	96	93	90	88	85	83	81	79	77	74	72	71	68
2	96	88	82	77	91	85	79	74	78	73	69	71	68	65	66	63	60	57
3	88	78	70	64	84	75	68	63	69	63	59	64	59	55	59	55	52	49
4	80	69	61	55	77	67	59	54	62	56	51	57	52	48	53	48	45	42
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	48	43	40	37
6	69	56	48	42	65	54	46	41	50	44	39	47	41	37	43	39	35	33
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	3.2
10°-20°	514.9	9.0
20°-30°	743.5	13.0
30°-40°	842.8	14.7
40°-50°	813.8	14.2
50°-60°	676.7	11.8
60°-70°	467.3	8.1
70°-80°	236.9	4.1
80°-90°	62.1	1.1
90°-100°	28.4	0.5
100°-110°	84.2	1.5
110°-120°	142.8	2.5
120°-130°	188.3	3.3
130°-140°	211.5	3.7
140°-150°	207.8	3.6
150°-160°	174.8	3.0
160°-170°	116.3	2.0
170°-180°	40.7	0.7
0°-30°	1443.1	25.2
0°-40°	2285.8	39.8
0°-60°	3776.4	65.8
0°-90°	4542.7	79.2
90°-120°	255.4	4.5
90°-150°	863.0	15.0
90°-180°	1195.0	20.8
0°-180°	5737.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	1	5	7	9	10	5
95°	20	23	25	26	26	22
105°	78	78	79	80	81	82
115°	145	145	145	144	144	143
125°	212	211	211	210	210	188
135°	273	275	275	274	273	211
145°	331	333	333	333	332	207
155°	380	380	379	380	379	175
165°	413	412	412	413	412	116
175°	430	428	428	430	428	41
180°	431	431	431	431	431	



TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	27.9	25.9	23.9	22.0	20.0	18.9	18.8	18.7	18.5	18.3	18.1
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	7.2	8.1	9.0	9.9	10.8	11.5	12.0	12.3	12.8	13.2	13.5
95°	20.0	20.6	21.3	22.0	22.6	23.3	23.8	24.3	24.8	25.4	25.5
97.5°	34.9	35.4	36.0	36.5	37.0	37.6	38.2	38.8	39.4	40.1	40.3
100°	46.7	46.9	47.2	47.5	47.8	48.3	48.9	49.7	50.3	51.0	51.1
102.5°	58.9	59.0	59.1	59.3	59.4	59.8	60.3	61.0	61.5	62.1	62.4
105°	77.6	77.7	77.8	77.9	77.9	78.0	78.4	78.7	79.0	79.3	79.5
107.5°	97.3	97.4	97.5	97.6	97.6	97.6	97.7	97.7	97.8	97.8	98.0
110°	110.6	110.7	110.8	111.0	111.1	111.2	111.1	111.0	110.9	110.9	110.7



TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	124.4	124.4	124.5	124.5	124.5	124.5	124.3	124.2	124.1	123.9	123.9
115°	145.2	145.2	145.2	145.2	145.2	145.2	145.0	144.9	144.7	144.6	144.5
117.5°	164.8	164.9	164.9	164.9	165.0	165.0	164.9	164.9	164.7	164.6	164.4
120°	177.9	178.1	178.4	178.7	179.1	179.1	178.9	178.6	178.4	178.2	177.9
122.5°	191.4	191.5	191.7	191.8	191.9	191.9	191.8	191.7	191.6	191.5	191.2
125°	211.5	211.5	211.5	211.5	211.5	211.4	211.4	211.3	211.2	211.1	211.0
127.5°	229.7	229.9	230.2	230.4	230.5	230.6	230.5	230.4	230.3	230.2	230.0
130°	242.5	242.7	242.9	243.2	243.4	243.5	243.5	243.5	243.5	243.5	243.4
132.5°	255.5	255.7	255.8	256.0	256.2	256.2	256.2	256.1	256.1	256.0	255.8
135°	272.8	273.2	273.6	274.1	274.6	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	291.5	291.8	292.0	292.2	292.4	292.6	292.7	292.8	292.9	293.0	292.8
140°	304.1	304.3	304.3	304.5	304.7	304.7	304.7	304.7	304.7	304.7	304.7
142.5°	315.6	315.7	315.8	315.9	316.1	316.2	316.1	316.0	316.0	315.9	315.9
145°	331.4	331.7	332.0	332.2	332.6	332.8	332.8	332.9	333.0	333.1	333.0
147.5°	347.1	347.5	347.8	348.2	348.6	348.6	348.6	348.6	348.6	348.5	348.4
150°	356.8	357.0	357.3	357.6	357.9	358.1	358.1	358.1	358.1	358.1	358.1
152.5°	365.8	366.0	366.1	366.3	366.5	366.6	366.6	366.7	366.7	366.8	367.0
155°	379.7	379.7	379.7	379.7	379.7	379.7	379.6	379.5	379.5	379.4	379.7
157.5°	391.4	391.2	391.2	391.1	390.9	390.8	390.8	390.8	390.8	390.8	391.0
160°	398.3	398.2	398.2	398.1	398.0	397.9	397.9	397.8	397.8	397.7	397.9
162.5°	404.7	404.5	404.4	404.2	404.0	403.9	403.8	403.7	403.6	403.5	404.0
165°	413.3	413.1	412.9	412.6	412.5	412.3	412.1	412.0	411.8	411.7	412.1
167.5°	419.9	419.6	419.3	419.0	418.7	418.5	418.6	418.6	418.6	418.6	419.1
170°	423.7	423.3	422.9	422.5	422.2	422.1	422.1	422.2	422.3	422.4	422.7
172.5°	426.3	426.0	425.7	425.4	425.1	424.9	424.9	425.0	425.0	425.0	425.5
175°	430.0	429.6	429.2	428.9	428.5	428.3	428.2	428.1	428.1	428.0	428.5
177.5°	431.2	430.9	430.6	430.3	430.0	429.9	429.9	429.9	429.9	429.9	430.3
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6



TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	18.0	17.8	17.6	17.6	18.0	18.3	18.6	18.9
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.8	13.9	14.2	14.4	14.5	14.6	14.7	14.8
95°	25.7	26.0	26.2	26.3	26.3	26.3	26.3	26.3
97.5°	40.5	40.8	41.1	41.2	41.2	41.2	41.2	41.2
100°	51.3	51.4	51.6	51.7	51.7	51.7	51.7	51.7
102.5°	62.6	62.8	63.0	63.2	63.2	63.2	63.2	63.3
105°	79.7	79.9	80.1	80.4	80.6	80.9	81.1	81.2
107.5°	98.3	98.5	98.7	98.8	98.8	98.8	98.8	98.7
110°	110.7	110.5	110.3	110.4	110.6	110.8	111.0	111.2



TEST NUMBER: P332989-830

CATALOG NUMBER: SA4XXRDIP-C1195D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	124.0
115°	144.4	144.3	144.2	144.2	144.1	144.0	143.9	143.9
117.5°	164.1	163.8	163.6	163.4	163.2	163.1	163.0	162.8
120°	177.5	177.1	176.7	176.6	176.7	176.9	177.0	177.2
122.5°	191.1	190.8	190.5	190.2	190.0	189.7	189.5	189.2
125°	210.8	210.8	210.6	210.4	210.3	210.1	210.0	209.8
127.5°	229.9	229.7	229.5	229.4	229.3	229.2	229.0	228.9
130°	243.2	243.0	242.9	242.6	242.3	242.0	241.8	241.5
132.5°	255.7	255.5	255.4	255.2	255.1	255.1	255.0	254.8
135°	274.5	274.4	274.2	274.0	273.8	273.5	273.3	273.1
137.5°	292.7	292.5	292.3	292.2	292.2	292.3	292.3	292.4
140°	304.6	304.5	304.4	304.3	304.3	304.3	304.2	304.1
142.5°	315.9	315.9	315.8	315.8	315.8	315.8	315.8	315.8
145°	332.9	332.8	332.8	332.6	332.4	332.2	332.0	331.8
147.5°	348.4	348.3	348.2	348.2	348.1	348.0	347.9	347.9
150°	358.1	358.1	358.1	358.0	358.0	357.9	357.8	357.7
152.5°	367.2	367.4	367.6	367.5	367.3	367.1	366.9	366.7
155°	379.9	380.2	380.5	380.5	380.2	379.9	379.7	379.4
157.5°	391.2	391.4	391.6	391.6	391.3	391.2	390.9	390.6
160°	398.1	398.3	398.6	398.5	398.1	397.8	397.4	397.0
162.5°	404.4	404.7	405.1	405.1	404.8	404.4	404.1	403.7
165°	412.6	413.0	413.4	413.5	413.2	412.9	412.6	412.4
167.5°	419.5	419.9	420.4	420.4	419.9	419.4	419.0	418.5
170°	423.2	423.7	424.1	424.0	423.6	423.0	422.5	422.0
172.5°	426.0	426.5	427.0	427.0	426.5	425.9	425.5	424.9
175°	429.0	429.5	430.1	430.1	429.5	429.0	428.5	428.0
177.5°	430.6	431.1	431.5	431.5	431.0	430.6	430.1	429.6
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6

(END OF REPORT)