

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332507-840

Luminaire Tested: **SA4XXDIP-C350D590U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332507-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3665.0 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332507-840
CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.5
10°-20°	158.3	4.3
20°-30°	233.0	6.4
30°-40°	270.8	7.4
40°-50°	270.9	7.4
50°-60°	236.9	6.5
60°-70°	175.9	4.8
70°-80°	100.0	2.7
80°-90°	30.5	0.8
90°-100°	211.8	5.8
100°-110°	440.8	12.0
110°-120°	394.8	10.8
120°-130°	332.1	9.1
130°-140°	276.9	7.6
140°-150°	211.5	5.8
150°-160°	148.7	4.1
160°-170°	87.5	2.4
170°-180°	28.5	0.8
0°-30°	447.4	12.2
0°-40°	718.3	19.6
0°-60°	1226.1	33.5
0°-90°	1532.4	41.8
90°-120°	1047.4	28.6
90°-150°	1868.0	51.0
90°-180°	2133.0	58.2
0°-180°	3665.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	1	5	10	12	12	2
95°	19	60	470	232	141	21
105°	67	98	378	814	810	72
115°	119	149	337	648	778	118
125°	165	196	335	551	621	147
135°	196	234	332	489	555	152
145°	226	259	331	412	453	142
155°	258	278	321	364	380	119
165°	280	289	308	326	331	79
175°	293	293	296	300	298	28
180°	293	293	293	293	293	



TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.1	10.2	10.5	10.5	10.5	10.4	11.0	11.0	11.1	11.2	11.1
90°	0.6	1.7	3.4	4.0	4.6	4.6	8.1	8.1	9.2	10.4	9.8
92.5°	6.6	9.6	14.9	22.0	30.4	42.4	71.7	116.3	160.0	182.7	152.2
95°	19.0	20.7	26.5	34.0	47.8	72.0	122.1	216.6	354.3	469.5	482.7
97.5°	34.1	34.1	39.1	45.9	57.9	78.2	116.7	194.7	331.6	494.5	606.5
100°	43.8	43.8	47.8	54.7	65.6	84.1	118.1	183.2	300.7	463.1	610.7
102.5°	53.0	53.9	57.5	63.9	74.4	91.9	122.7	180.0	279.9	424.0	576.0
105°	67.4	69.2	72.0	79.0	89.3	106.0	133.6	181.5	262.2	377.9	513.3
107.5°	83.3	84.4	87.4	94.7	104.6	121.1	146.4	190.0	258.9	352.1	462.6
110°	93.9	95.0	98.0	104.8	115.2	130.8	156.1	196.4	259.8	343.4	437.3



TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.0	105.2	108.6	115.0	125.3	140.9	165.3	203.4	262.6	339.2	422.9
115°	118.7	120.4	124.4	130.2	141.2	156.7	179.8	214.3	267.9	337.0	409.6
117.5°	133.9	135.5	139.1	145.4	155.6	171.8	193.7	225.5	273.5	336.4	403.6
120°	144.0	145.2	149.2	155.5	165.3	181.5	203.4	233.3	277.7	336.4	400.4
122.5°	153.2	154.4	158.4	164.3	175.0	190.7	212.6	240.7	281.9	336.0	396.7
125°	165.3	167.6	171.1	177.4	188.3	204.5	225.2	251.8	288.0	335.3	390.6
127.5°	176.0	177.9	182.1	189.2	200.7	216.9	237.0	261.4	293.0	334.0	382.4
130°	182.1	184.3	188.9	197.6	208.5	225.2	244.8	267.3	296.7	333.6	377.3
132.5°	188.0	189.9	195.9	204.1	215.9	231.7	251.3	273.3	299.9	333.1	372.7
135°	196.4	198.7	204.5	214.3	226.4	241.4	260.3	281.1	304.8	332.3	365.8
137.5°	204.9	207.0	213.4	222.7	235.3	249.5	267.3	286.7	307.6	332.2	359.8
140°	210.9	212.6	218.9	228.7	240.8	254.6	272.0	290.3	309.9	331.8	356.6
142.5°	217.3	219.0	224.9	234.2	245.9	259.2	276.1	293.1	311.7	331.8	353.9
145°	226.4	228.1	233.9	242.0	252.9	265.6	280.5	296.1	312.9	330.6	349.1
147.5°	236.6	237.2	242.3	250.5	259.7	271.1	285.2	298.7	313.4	328.6	344.9
150°	243.1	243.7	248.3	255.2	263.9	274.8	287.5	300.1	313.4	327.2	341.6
152.5°	249.1	249.2	253.8	260.2	268.0	278.0	289.3	301.0	312.5	324.9	337.9
155°	257.5	258.1	261.6	267.3	273.7	282.3	292.1	301.8	311.0	321.4	332.3
157.5°	265.7	265.7	268.9	273.4	278.9	285.7	294.1	301.8	309.6	317.9	326.8
160°	270.7	270.7	273.1	277.1	281.7	288.0	295.0	301.8	308.2	315.1	322.7
162.5°	275.4	274.9	276.7	280.3	284.5	289.4	295.9	301.8	306.8	312.4	318.9
165°	280.5	280.5	281.7	284.6	287.5	290.9	296.1	300.7	304.2	308.2	312.9
167.5°	285.7	285.2	285.7	287.9	289.5	292.2	296.0	299.3	301.4	304.1	307.3
170°	288.0	287.5	288.0	289.7	290.9	292.7	295.5	298.4	299.5	301.2	303.6
172.5°	290.3	289.7	289.8	291.1	291.9	293.1	295.1	297.5	297.7	298.5	300.3
175°	292.7	292.1	292.1	292.7	293.3	293.3	294.4	296.1	295.5	295.5	296.7
177.5°	293.7	293.3	292.8	293.3	293.3	293.3	293.7	294.6	293.7	293.7	294.2
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	11.2	11.4	11.5	11.5	11.6	11.7	11.6	11.6
90°	10.4	10.9	11.5	11.5	12.1	12.6	12.1	12.1
92.5°	113.1	85.1	67.8	56.2	49.4	46.4	44.3	44.3
95°	426.9	337.6	260.3	204.5	176.3	158.4	148.0	140.6
97.5°	630.7	597.5	541.2	481.0	439.7	405.0	387.7	375.7
100°	694.8	706.3	678.0	635.4	585.3	550.2	532.9	528.3
102.5°	691.6	748.7	756.9	739.1	708.3	682.9	664.7	661.0
105°	645.2	744.9	801.9	825.6	826.7	822.0	814.0	810.5
107.5°	579.5	685.5	765.9	817.2	845.7	858.8	864.5	866.1
110°	539.8	639.4	723.0	786.4	827.3	851.4	861.8	867.0



TEST NUMBER: P332507-840

CATALOG NUMBER: SA4XXDIP-C350D590U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	510.8	598.8	677.8	741.1	787.6	816.9	831.4	839.8
115°	481.6	552.5	619.9	675.2	720.6	755.3	773.7	778.3
117.5°	467.3	525.9	579.0	625.8	664.7	693.7	712.4	716.0
120°	460.9	514.4	560.5	601.4	634.3	659.6	674.6	681.0
122.5°	455.3	507.1	549.0	584.8	612.6	634.3	646.9	653.3
125°	445.9	495.4	535.1	566.8	589.9	606.6	617.5	621.0
127.5°	434.3	481.7	521.4	551.4	574.6	589.5	598.6	602.1
130°	425.2	470.7	509.8	540.4	564.0	578.3	587.6	591.1
132.5°	415.5	458.2	496.4	526.9	550.2	566.4	575.1	578.7
135°	402.1	439.6	474.6	503.5	526.5	542.7	551.9	555.3
137.5°	390.0	421.7	451.3	477.4	498.9	514.8	522.4	526.5
140°	383.0	410.2	436.1	460.3	480.5	493.1	501.2	505.8
142.5°	376.7	400.5	422.7	443.7	461.5	473.3	480.5	483.6
145°	367.5	387.1	404.5	420.5	434.9	444.7	450.5	453.3
147.5°	360.0	375.6	389.4	402.1	412.7	421.1	425.5	426.6
150°	355.5	368.7	380.2	390.6	399.8	407.3	410.7	411.3
152.5°	350.3	361.7	372.3	380.9	388.7	394.9	396.9	397.5
155°	342.7	351.9	360.6	367.5	373.3	377.9	379.6	379.6
157.5°	334.6	342.3	349.5	355.1	359.5	362.9	364.0	364.0
160°	329.5	335.9	342.1	346.8	350.2	353.8	354.3	354.3
162.5°	324.5	329.8	334.8	339.0	341.5	345.0	345.6	345.1
165°	317.4	320.8	324.9	327.8	330.1	332.3	331.8	331.2
167.5°	310.6	313.3	316.5	318.2	319.4	320.8	320.7	320.3
170°	306.5	308.2	310.5	312.3	313.4	314.0	313.4	313.4
172.5°	302.8	304.1	305.5	306.7	307.4	308.0	307.4	306.5
175°	297.8	298.4	299.5	299.5	299.5	300.7	299.5	298.4
177.5°	294.6	295.1	295.1	295.5	295.1	295.5	294.6	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3

(END OF REPORT)