

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332516-840

Luminaire Tested: **SA4XXDIP-C350D810U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332516-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4456.2 lumens
Efficiency: N/A
Efficacy: 142.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332516-840
CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	56	70	63	56	52	50	46	42	39	36	34	29	27	25	20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	28	32	27	24	26	22	19	19	17	15	12
8	52	40	32	27	46	36	29	25	30	24	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4816	4816	4816
5°	4830	4772	4807
10°	4800	4733	4757
15°	4741	4667	4679
20°	4665	4582	4587
25°	4577	4488	4475
30°	4470	4376	4336
35°	4357	4258	4202
40°	4241	4126	4051
45°	4120	3995	3919
50°	3986	3878	3758
55°	3842	3727	3606
60°	3696	3559	3450
65°	3534	3396	3261
70°	3352	3182	3059
75°	3072	2923	2848
80°	2734	2627	2552
85°	2399	2297	2251



TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	1.3
10°-20°	158.3	3.6
20°-30°	233.0	5.2
30°-40°	270.8	6.1
40°-50°	270.9	6.1
50°-60°	236.9	5.3
60°-70°	175.9	3.9
70°-80°	100.0	2.2
80°-90°	31.1	0.7
90°-100°	290.3	6.5
100°-110°	604.2	13.6
110°-120°	541.2	12.1
120°-130°	455.2	10.2
130°-140°	379.6	8.5
140°-150°	290.0	6.5
150°-160°	203.8	4.6
160°-170°	119.9	2.7
170°-180°	39.0	0.9
0°-30°	447.4	10.0
0°-40°	718.3	16.1
0°-60°	1226.1	27.5
0°-90°	1533.0	34.4
90°-120°	1435.7	32.2
90°-150°	2560.4	57.5
90°-180°	2923.0	65.6
0°-180°	4456.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	589	594	593	57
15°	567	565	558	561	560	160
25°	514	510	504	504	502	236
35°	442	439	432	429	426	276
45°	361	357	350	345	343	278
55°	273	271	265	259	256	244
65°	185	182	178	173	171	183
75°	98	96	94	92	91	105
85°	26	26	25	25	24	28
90°	1	6	14	16	17	3
95°	26	82	644	319	193	29
105°	92	134	518	1115	1111	99
115°	163	204	462	888	1067	161
125°	227	269	460	755	851	202
135°	269	321	456	670	761	208
145°	310	355	453	565	622	195
155°	353	381	441	499	520	163
165°	385	396	422	447	454	109
175°	401	402	405	411	409	38
180°	402	402	402	402	402	



TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	598.0	597.8	597.5	597.3	597.0	596.4	595.5	594.6	593.7	592.7	593.6
5°	596.0	595.6	595.2	594.8	594.4	593.6	592.4	591.3	590.1	588.9	590.1
7.5°	590.6	590.1	589.7	589.3	588.9	587.9	586.6	585.4	584.1	582.8	583.7
10°	585.5	585.1	584.7	584.3	583.9	583.0	581.6	580.2	578.9	577.4	578.2
12.5°	579.1	578.7	578.2	577.7	577.3	576.4	574.9	573.5	572.0	570.6	571.5
15°	567.3	566.9	566.5	566.1	565.7	564.7	563.1	561.5	559.9	558.4	559.0
17.5°	553.3	552.8	552.3	551.8	551.2	550.2	548.7	547.1	545.6	544.1	544.5
20°	543.0	542.5	542.0	541.4	540.9	539.9	538.3	536.6	535.0	533.4	533.8
22.5°	531.9	531.2	530.5	529.8	529.1	528.0	526.3	524.8	523.2	521.6	522.2
25°	513.8	513.1	512.4	511.6	510.9	509.8	508.3	506.8	505.3	503.8	503.9
27.5°	493.2	492.4	491.7	490.9	490.2	489.1	487.7	486.4	484.9	483.5	483.3
30°	479.5	478.6	477.8	476.9	476.1	474.9	473.5	472.1	470.8	469.4	469.0
32.5°	464.9	464.1	463.3	462.6	461.8	460.7	459.3	457.8	456.4	454.8	454.3
35°	442.1	441.4	440.7	439.9	439.2	438.1	436.6	435.0	433.6	432.1	431.4
37.5°	418.2	417.5	416.8	416.2	415.5	414.3	412.7	411.1	409.5	407.9	407.1
40°	402.4	401.6	400.8	399.9	399.1	397.9	396.3	394.7	393.0	391.5	390.4
42.5°	385.7	385.2	384.7	384.2	383.6	382.4	380.7	378.9	377.2	375.5	374.2
45°	360.9	360.1	359.4	358.7	357.9	356.7	355.0	353.3	351.6	349.9	348.7
47.5°	335.0	334.5	334.0	333.5	333.0	331.9	330.3	328.7	327.2	325.6	324.3
50°	317.4	317.0	316.6	316.1	315.7	314.8	313.3	311.7	310.2	308.8	307.3
52.5°	300.2	299.6	299.1	298.6	298.1	297.1	295.5	294.0	292.4	290.8	289.5
55°	273.0	272.7	272.3	272.0	271.7	270.7	269.2	267.8	266.3	264.8	263.6
57.5°	246.9	246.6	246.2	245.9	245.5	244.6	243.1	241.7	240.1	238.7	237.5
60°	228.9	228.4	227.9	227.3	226.8	225.9	224.5	223.1	221.8	220.4	219.4
62.5°	211.4	211.0	210.5	210.1	209.5	208.6	207.1	205.7	204.2	202.8	201.9
65°	185.0	184.5	183.9	183.4	182.9	182.1	181.0	180.0	178.8	177.8	176.7
67.5°	158.4	157.9	157.4	156.9	156.4	155.7	154.7	153.7	152.7	151.6	150.6
70°	142.0	141.2	140.5	139.8	139.0	138.1	137.3	136.5	135.6	134.8	133.9
72.5°	124.4	123.6	122.9	122.2	121.4	120.7	120.0	119.4	118.7	118.0	117.2
75°	98.5	98.0	97.5	96.8	96.3	95.8	95.3	94.7	94.2	93.7	93.3
77.5°	73.7	73.5	73.2	73.0	72.8	72.4	72.0	71.5	71.0	70.6	70.4
80°	58.8	58.5	58.2	57.9	57.6	57.3	57.1	56.9	56.7	56.5	56.1
82.5°	44.2	44.1	43.9	43.8	43.6	43.5	43.5	43.5	43.4	43.4	43.3
85°	25.9	25.9	25.9	25.9	25.9	25.8	25.4	25.2	25.0	24.8	24.8
87.5°	10.1	10.3	10.7	10.8	10.9	10.8	11.6	11.5	11.8	12.0	11.8
90°	0.8	2.3	4.7	5.6	6.4	6.4	11.0	11.0	12.6	14.2	13.4
92.5°	9.0	13.1	20.5	30.2	41.7	58.1	98.3	159.5	219.2	250.4	208.6
95°	26.1	28.4	36.4	46.6	65.5	98.7	167.4	296.9	485.6	643.6	661.8
97.5°	46.8	46.8	53.5	63.0	79.3	107.0	160.0	266.9	454.5	677.8	831.3
100°	60.0	60.0	65.5	75.0	90.0	115.3	161.9	251.2	412.2	634.9	837.0
102.5°	72.6	73.9	78.8	87.7	102.0	126.0	168.1	246.7	383.7	581.2	789.6
105°	92.4	94.7	98.7	108.2	122.4	145.3	183.2	248.7	359.3	518.0	703.6
107.5°	114.2	115.7	119.7	129.8	143.4	166.0	200.8	260.4	354.9	482.6	634.1
110°	128.8	130.3	134.2	143.7	157.9	179.3	214.0	269.2	356.1	470.6	599.4



TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.6	144.2	148.8	157.6	171.8	193.2	226.6	278.7	359.9	464.9	579.8
115°	162.7	165.0	170.6	178.4	193.5	214.8	246.4	293.8	367.2	461.9	561.4
117.5°	183.5	185.7	190.7	199.3	213.4	235.5	265.5	309.0	375.0	461.1	553.2
120°	197.4	198.9	204.5	213.2	226.6	248.7	278.7	319.8	380.6	461.1	548.8
122.5°	210.1	211.7	217.1	225.2	239.8	261.4	291.3	329.9	386.3	460.5	543.7
125°	226.6	229.7	234.5	243.2	258.2	280.3	308.7	345.1	394.9	459.6	535.3
127.5°	241.4	243.9	249.5	259.4	275.1	297.4	324.9	358.2	401.6	457.9	524.1
130°	249.5	252.7	259.0	270.8	285.9	308.7	335.6	366.4	406.7	457.2	517.3
132.5°	257.7	260.2	268.5	279.7	296.0	317.6	344.5	374.6	411.1	456.6	510.9
135°	269.2	272.5	280.3	293.8	310.3	330.8	356.9	385.4	417.7	455.7	501.4
137.5°	280.8	283.8	292.5	305.3	322.4	342.0	366.4	392.9	421.6	455.4	493.2
140°	289.0	291.3	300.0	313.5	330.0	349.0	372.7	398.0	424.9	454.8	488.8
142.5°	297.8	300.2	308.3	321.0	337.0	355.4	378.4	401.7	427.4	454.8	485.0
145°	310.3	312.7	320.6	331.6	346.7	364.1	384.6	405.9	428.8	453.2	478.5
147.5°	324.4	325.2	332.1	343.5	356.0	371.6	390.9	409.5	429.6	450.4	472.7
150°	333.3	334.1	340.3	349.8	361.6	376.7	394.0	411.4	429.6	448.5	468.3
152.5°	341.4	341.6	347.9	356.8	367.4	381.1	396.6	412.6	428.3	445.4	463.2
155°	352.9	353.8	358.5	366.4	375.1	386.9	400.3	413.7	426.4	440.6	455.7
157.5°	364.2	364.2	368.6	374.8	382.3	391.6	403.0	413.7	424.3	435.8	447.9
160°	371.1	371.1	374.3	379.8	386.2	394.9	404.2	413.7	422.4	431.9	442.2
162.5°	377.5	376.8	379.3	384.3	389.9	396.7	405.6	413.7	420.6	428.2	437.2
165°	384.6	384.6	386.2	390.1	394.0	398.8	405.9	412.2	417.0	422.4	428.8
167.5°	391.6	390.9	391.6	394.7	396.9	400.5	405.8	410.3	413.1	416.8	421.2
170°	394.9	394.0	394.9	397.2	398.8	401.1	405.1	409.0	410.6	412.9	416.2
172.5°	398.0	397.2	397.4	399.1	400.0	401.7	404.5	407.8	408.1	409.2	411.7
175°	401.1	400.3	400.3	401.1	401.9	401.9	403.5	405.9	405.1	405.1	406.7
177.5°	402.5	401.9	401.3	401.9	401.9	401.9	402.5	403.8	402.5	402.5	403.1
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	596.5	596.5	596.5	596.5	596.5	596.5	596.5	596.5
2.5°	594.4	595.3	596.1	596.5	596.4	596.3	596.2	596.1
5°	591.3	592.4	593.6	594.0	593.8	593.6	593.4	593.2
7.5°	584.6	585.6	586.5	586.9	586.8	586.6	586.5	586.4
10°	579.2	580.0	580.9	581.2	581.0	580.7	580.5	580.3
12.5°	572.4	573.3	574.3	574.6	574.3	574.0	573.7	573.4
15°	559.6	560.2	560.9	561.0	560.7	560.4	560.1	559.8
17.5°	544.9	545.3	545.7	545.8	545.6	545.4	545.2	545.0
20°	534.1	534.4	534.7	534.8	534.5	534.3	534.1	533.9
22.5°	522.7	523.3	523.9	524.0	523.6	523.2	522.8	522.5
25°	504.0	504.1	504.2	504.1	503.6	503.2	502.8	502.4
27.5°	483.0	482.8	482.5	482.1	481.6	481.1	480.5	480.0
30°	468.6	468.2	467.7	467.3	466.7	466.2	465.6	465.1
32.5°	453.8	453.3	452.8	452.3	451.8	451.2	450.7	450.2
35°	430.6	429.9	429.1	428.5	428.0	427.5	426.9	426.4
37.5°	406.3	405.5	404.7	403.9	403.2	402.5	401.8	401.1
40°	389.4	388.3	387.3	386.5	385.9	385.4	384.9	384.4
42.5°	372.9	371.7	370.5	369.7	369.3	369.0	368.6	368.3
45°	347.6	346.4	345.3	344.5	344.2	343.9	343.6	343.3
47.5°	323.0	321.6	320.3	319.3	318.5	317.7	316.9	316.1
50°	305.8	304.4	302.9	301.7	301.1	300.5	299.8	299.2
52.5°	288.2	286.9	285.6	284.5	283.7	282.9	282.1	281.2
55°	262.3	260.9	259.7	258.7	258.1	257.5	256.8	256.2
57.5°	236.3	235.1	233.9	233.0	232.4	231.8	231.2	230.5
60°	218.4	217.5	216.5	215.8	215.3	214.7	214.2	213.7
62.5°	201.1	200.2	199.2	198.5	198.0	197.5	197.0	196.4
65°	175.7	174.6	173.6	172.8	172.3	171.7	171.2	170.7
67.5°	149.6	148.6	147.5	146.9	146.8	146.6	146.5	146.3
70°	133.1	132.3	131.4	130.8	130.5	130.2	129.9	129.6
72.5°	116.6	115.9	115.2	114.7	114.4	114.1	113.8	113.5
75°	92.8	92.4	92.0	91.7	91.6	91.5	91.4	91.3
77.5°	70.3	70.2	70.1	69.9	69.6	69.3	69.0	68.8
80°	55.9	55.7	55.5	55.4	55.2	55.1	55.0	54.9
82.5°	43.1	43.0	42.9	42.8	42.7	42.5	42.4	42.3
85°	24.8	24.8	24.8	24.8	24.7	24.6	24.4	24.3
87.5°	12.0	12.2	12.3	12.3	12.5	12.6	12.5	12.5
90°	14.2	15.0	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	155.1	116.7	92.9	77.1	67.8	63.5	60.8	60.8
95°	585.1	462.7	356.9	280.3	241.7	217.1	203.0	192.7
97.5°	864.4	819.0	741.7	659.3	602.7	555.1	531.4	515.0
100°	952.3	968.1	929.4	871.0	802.2	754.1	730.4	724.1
102.5°	947.9	1026.2	1037.4	1013.1	971.0	936.0	911.1	906.1
105°	884.4	1021.0	1099.1	1131.6	1133.2	1126.8	1115.8	1111.1
107.5°	794.3	939.7	1049.8	1120.1	1159.2	1177.2	1185.1	1187.1
110°	739.9	876.5	991.0	1077.8	1133.9	1167.1	1181.3	1188.4



TEST NUMBER: P332516-840

CATALOG NUMBER: SA4XXDIP-C350D810U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	700.1	820.9	929.1	1015.9	1079.5	1119.7	1139.6	1151.1
115°	660.1	757.3	849.6	925.4	987.8	1035.2	1060.5	1066.8
117.5°	640.6	720.9	793.6	857.9	911.1	950.9	976.4	981.4
120°	631.7	705.2	768.3	824.4	869.4	904.1	924.6	933.3
122.5°	624.1	695.0	752.6	801.6	839.7	869.4	886.8	895.4
125°	611.2	679.1	733.6	777.0	808.6	831.5	846.5	851.2
127.5°	595.4	660.2	714.6	755.9	787.6	808.0	820.6	825.4
130°	582.8	645.1	698.8	740.6	773.1	792.8	805.5	810.2
132.5°	569.5	628.0	680.5	722.4	754.1	776.4	788.4	793.1
135°	551.2	602.5	650.7	690.1	721.8	743.9	756.5	761.2
137.5°	534.6	578.0	618.6	654.3	683.8	705.6	716.0	721.8
140°	525.1	562.2	597.7	631.0	658.5	675.9	687.0	693.3
142.5°	516.2	549.0	579.5	608.1	632.7	648.7	658.5	663.0
145°	503.8	530.7	554.3	576.4	596.2	609.6	617.5	621.5
147.5°	493.5	514.8	533.8	551.2	565.7	577.2	583.2	584.6
150°	487.2	505.3	521.2	535.3	548.1	558.3	563.0	563.8
152.5°	480.3	495.8	510.4	522.1	532.8	541.2	544.0	544.8
155°	469.8	482.5	494.3	503.8	511.7	518.0	520.4	520.4
157.5°	458.6	469.2	479.2	486.8	492.7	497.5	498.9	498.9
160°	451.7	460.4	469.1	475.3	480.1	484.8	485.6	485.6
162.5°	444.7	452.1	459.0	464.6	468.1	472.8	473.6	473.0
165°	435.0	439.8	445.4	449.3	452.4	455.7	454.8	454.0
167.5°	425.8	429.4	433.8	436.2	437.8	439.8	439.7	439.0
170°	420.1	422.4	425.7	428.0	429.6	430.3	429.6	429.6
172.5°	415.1	416.8	418.7	420.4	421.3	422.1	421.3	420.1
175°	408.3	409.0	410.6	410.6	410.6	412.2	410.6	409.0
177.5°	403.8	404.5	404.5	405.1	404.5	405.1	403.8	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9

(END OF REPORT)