

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333001-830

Luminaire Tested: **SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333001-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7187.6 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	57	53	55	51	48	48	45	43	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	30
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.6
10°-20°	514.9	7.2
20°-30°	743.5	10.3
30°-40°	842.8	11.7
40°-50°	813.8	11.3
50°-60°	676.7	9.4
60°-70°	467.3	6.5
70°-80°	236.9	3.3
80°-90°	63.6	0.9
90°-100°	62.8	0.9
100°-110°	186.2	2.6
110°-120°	316.0	4.4
120°-130°	416.6	5.8
130°-140°	467.9	6.5
140°-150°	459.8	6.4
150°-160°	386.7	5.4
160°-170°	257.3	3.6
170°-180°	90.1	1.3
0°-30°	1443.1	20.1
0°-40°	2285.8	31.8
0°-60°	3776.4	52.5
0°-90°	4544.2	63.2
90°-120°	565.0	7.9
90°-150°	1909.3	26.6
90°-180°	2643.0	36.8
0°-180°	7187.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	2	10	16	20	22	7
95°	44	51	56	58	58	49
105°	172	173	175	178	180	182
115°	321	321	320	319	318	317
125°	468	468	467	466	464	417
135°	604	608	608	606	604	467
145°	733	736	737	736	734	459
155°	840	840	839	842	839	386
165°	914	912	911	915	912	258
175°	951	948	947	952	947	90
180°	953	953	953	953	953	



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.2	26.4	24.6	22.8	21.0	20.1	20.1	20.1	20.1	20.1	20.0
90°	2.2	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2
92.5°	15.7	17.8	19.9	22.0	24.0	25.5	26.4	27.3	28.3	29.2	29.8
95°	44.2	45.7	47.1	48.6	50.1	51.5	52.6	53.7	54.9	56.0	56.5
97.5°	77.2	78.4	79.6	80.8	81.9	83.2	84.5	85.9	87.2	88.6	89.2
100°	103.2	103.8	104.4	105.1	105.8	106.9	108.3	109.8	111.2	112.7	113.1
102.5°	130.3	130.5	130.8	131.1	131.3	132.1	133.5	134.8	136.2	137.5	138.0
105°	171.7	171.8	172.0	172.2	172.4	172.8	173.4	174.1	174.7	175.4	175.9
107.5°	215.2	215.4	215.6	215.7	215.9	216.1	216.2	216.3	216.4	216.5	217.0
110°	244.7	245.0	245.2	245.6	245.9	246.0	245.9	245.7	245.5	245.3	245.1



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.3	275.3	275.4	275.5	275.6	275.4	275.1	274.8	274.6	274.3	274.2
115°	321.3	321.3	321.3	321.3	321.3	321.1	320.7	320.5	320.1	319.8	319.6
117.5°	364.6	364.8	364.9	365.0	365.1	365.0	364.9	364.6	364.4	364.2	363.6
120°	393.5	394.2	394.8	395.5	396.2	396.2	395.7	395.2	394.7	394.3	393.4
122.5°	423.6	423.8	424.0	424.3	424.6	424.6	424.4	424.1	424.0	423.7	423.1
125°	467.9	467.9	467.9	467.9	467.9	467.8	467.7	467.5	467.3	467.2	466.8
127.5°	508.1	508.6	509.2	509.6	510.1	510.2	509.9	509.7	509.4	509.2	508.9
130°	536.4	537.0	537.4	537.9	538.4	538.7	538.7	538.7	538.7	538.7	538.3
132.5°	565.3	565.7	566.1	566.4	566.8	566.8	566.8	566.7	566.5	566.4	566.0
135°	603.5	604.5	605.5	606.4	607.5	607.9	607.9	607.9	607.9	607.9	607.6
137.5°	645.1	645.5	645.9	646.4	646.9	647.2	647.5	647.8	648.0	648.3	647.9
140°	672.8	673.1	673.4	673.7	674.1	674.2	674.2	674.2	674.2	674.2	674.1
142.5°	698.1	698.4	698.8	699.1	699.5	699.6	699.4	699.3	699.1	699.0	699.0
145°	733.2	733.9	734.5	735.2	735.8	736.2	736.4	736.5	736.7	736.9	736.7
147.5°	768.0	768.7	769.5	770.3	771.1	771.5	771.3	771.2	771.0	770.9	770.8
150°	789.2	789.9	790.5	791.2	791.8	792.1	792.1	792.1	792.1	792.1	792.1
152.5°	809.3	809.6	810.0	810.4	810.8	811.1	811.2	811.3	811.4	811.6	812.0
155°	840.0	840.0	840.0	840.0	840.0	839.9	839.8	839.6	839.4	839.3	839.9
157.5°	866.0	865.6	865.3	865.1	864.8	864.6	864.6	864.6	864.5	864.5	865.0
160°	881.3	881.1	881.0	880.8	880.6	880.4	880.3	880.1	880.0	879.9	880.3
162.5°	895.4	895.0	894.6	894.2	893.7	893.4	893.2	893.2	893.0	892.8	893.7
165°	914.5	914.0	913.5	912.9	912.5	912.1	911.7	911.4	911.1	910.8	911.7
167.5°	929.1	928.3	927.7	927.0	926.3	926.0	926.0	926.0	926.0	926.0	927.1
170°	937.3	936.5	935.7	934.8	934.1	933.7	933.9	934.1	934.2	934.3	935.3
172.5°	943.2	942.5	941.8	941.1	940.5	940.1	940.2	940.2	940.2	940.3	941.3
175°	951.3	950.5	949.6	948.9	948.0	947.5	947.3	947.2	947.1	946.9	948.0
177.5°	953.9	953.3	952.6	952.0	951.3	951.0	951.0	951.0	951.0	951.0	951.9
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	20.0	19.9	19.8	20.0	20.3	20.6	20.9	21.3
90°	18.2	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	30.3	30.9	31.6	32.0	32.1	32.3	32.5	32.7
95°	57.0	57.5	58.0	58.2	58.2	58.2	58.2	58.2
97.5°	89.7	90.3	91.0	91.2	91.2	91.2	91.2	91.2
100°	113.4	113.8	114.0	114.2	114.2	114.2	114.2	114.2
102.5°	138.5	138.8	139.3	139.6	139.8	139.9	140.1	140.2
105°	176.3	176.8	177.3	177.9	178.3	178.8	179.3	179.8
107.5°	217.4	217.8	218.3	218.6	218.5	218.5	218.5	218.4
110°	244.7	244.4	244.0	244.1	244.7	245.2	245.6	246.1



TEST NUMBER: P333001-830

CATALOG NUMBER: SA4XXRDIP-C1195D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	274.1	274.1	274.0	274.0	274.1	274.2	274.3	274.4
115°	319.4	319.3	319.1	319.0	318.9	318.7	318.5	318.3
117.5°	363.1	362.5	361.9	361.5	361.2	360.8	360.5	360.1
120°	392.6	391.7	391.0	390.7	391.1	391.3	391.7	392.0
122.5°	422.5	422.1	421.5	420.9	420.3	419.7	419.1	418.6
125°	466.6	466.2	465.9	465.5	465.2	464.9	464.6	464.2
127.5°	508.5	508.2	507.8	507.6	507.3	507.1	506.8	506.5
130°	538.0	537.6	537.3	536.9	536.2	535.6	534.9	534.2
132.5°	565.7	565.3	565.1	564.8	564.5	564.2	563.9	563.7
135°	607.3	606.9	606.6	606.1	605.7	605.2	604.7	604.3
137.5°	647.4	647.1	646.6	646.4	646.5	646.6	646.7	646.9
140°	673.9	673.7	673.5	673.4	673.3	673.1	672.9	672.8
142.5°	698.9	698.9	698.9	698.8	698.8	698.8	698.7	698.7
145°	736.5	736.4	736.2	735.8	735.4	734.9	734.4	734.0
147.5°	770.6	770.5	770.3	770.2	770.1	769.9	769.8	769.6
150°	792.1	792.1	792.1	792.0	791.9	791.7	791.5	791.4
152.5°	812.4	812.8	813.1	813.1	812.8	812.3	811.9	811.4
155°	840.6	841.2	841.9	841.9	841.2	840.6	839.9	839.3
157.5°	865.4	866.0	866.5	866.4	865.9	865.3	864.8	864.2
160°	880.8	881.3	881.7	881.7	880.8	880.0	879.2	878.4
162.5°	894.6	895.4	896.4	896.4	895.5	894.8	893.9	893.1
165°	912.8	913.7	914.7	914.8	914.2	913.5	912.9	912.3
167.5°	928.0	929.1	930.0	930.0	929.0	927.9	927.0	926.0
170°	936.3	937.3	938.3	938.2	937.1	935.9	934.7	933.6
172.5°	942.4	943.6	944.7	944.7	943.6	942.4	941.2	940.1
175°	949.1	950.3	951.5	951.5	950.3	949.1	948.0	946.9
177.5°	952.8	953.8	954.7	954.6	953.6	952.5	951.5	950.4
180°	952.7	952.7	952.7	952.7	952.7	952.7	952.7	952.7

(END OF REPORT)