

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332616-840

Luminaire Tested: **SA4XXDIP-C795D1205U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332616-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8434.6 lumens
Efficiency: N/A
Efficacy: 148.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332616-840
CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	42				42
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42				36	
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36				31	
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30				26	
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26				23	
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23				20	
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20				17	
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18				15	
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16				14	
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15				13	
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10467	10467	10467	10467
5°	12327	10494	9263	10494
10°	14758	10449	8338	10449
15°	17462	10343	7658	10343
20°	19444	10234	7050	10234
25°	19759	10075	6631	10075
30°	16812	9923	6498	9923
35°	12925	9676	6500	9676
40°	10075	9385	6622	9385
45°	8401	8947	6734	8947
50°	7394	8411	6962	8411
55°	6773	7771	7241	7771
60°	6347	7198	7579	7198
65°	5908	6556	7859	6556
70°	5401	5922	8037	5922
75°	4825	5209	7941	5209
80°	4049	4268	7689	4268
85°	2983	3084	7364	3084



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.5
10°-20°	389.3	4.6
20°-30°	617.4	7.3
30°-40°	687.1	8.1
40°-50°	625.4	7.4
50°-60°	511.1	6.1
60°-70°	364.8	4.3
70°-80°	200.9	2.4
80°-90°	59.4	0.7
90°-100°	53.7	0.6
100°-110°	342.1	4.1
110°-120°	654.5	7.8
120°-130°	830.8	9.9
130°-140°	888.9	10.5
140°-150°	831.2	9.9
150°-160°	670.3	7.9
160°-170°	432.4	5.1
170°-180°	149.0	1.8
0°-30°	1133.0	13.4
0°-40°	1820.1	21.6
0°-60°	2956.5	35.1
0°-90°	3581.7	42.5
90°-120°	1050.3	12.5
90°-150°	3601.3	42.7
90°-180°	4853.0	57.5
0°-180°	8434.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1297	1297	1297	1297	1297	
5°	1521	1295	1143	1295	1521	155
15°	2089	1238	916	1238	2089	590
25°	2218	1131	744	1131	2218	978
35°	1312	982	660	982	1312	832
45°	736	784	590	784	736	580
55°	481	552	514	552	481	435
65°	309	343	411	343	309	306
75°	155	167	255	167	155	164
85°	32	33	80	33	32	40
90°	35	4	35	4	35	16
95°	34	64	34	64	34	27
105°	334	353	334	353	334	292
115°	664	659	664	659	664	657
125°	934	927	934	927	934	832
135°	1158	1150	1158	1150	1158	891
145°	1333	1326	1333	1326	1333	833
155°	1453	1454	1453	1454	1453	670
165°	1527	1534	1527	1534	1527	431
175°	1559	1569	1559	1569	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1379.9	1379.5	1375.1	1374.3	1371.3	1367.5	1366.5	1359.7	1345.9	1339.5	1337.8
5°	1521.1	1531.8	1517.8	1515.1	1513.5	1495.8	1486.6	1475.9	1451.2	1436.7	1425.4
7.5°	1689.5	1690.7	1684.7	1679.7	1666.1	1650.5	1627.4	1602.7	1573.3	1542.6	1519.5
10°	1800.3	1804.6	1797.7	1796.5	1769.2	1752.0	1717.6	1688.6	1655.3	1618.2	1584.4
12.5°	1917.2	1911.2	1907.6	1884.6	1879.6	1848.3	1808.3	1778.4	1727.1	1684.5	1639.4
15°	2089.3	2077.5	2069.9	2038.2	2022.7	1979.1	1936.7	1904.0	1836.8	1772.9	1724.5
17.5°	2190.2	2202.0	2184.6	2171.6	2131.3	2100.8	2057.5	1988.7	1936.2	1856.8	1795.8
20°	2263.3	2264.3	2254.7	2241.3	2209.6	2170.9	2123.6	2048.4	1985.6	1906.6	1822.9
22.5°	2283.0	2283.3	2279.2	2266.6	2242.6	2211.3	2163.6	2100.8	2024.7	1938.8	1855.1
25°	2218.2	2216.0	2220.9	2234.8	2225.6	2216.0	2188.6	2141.9	2071.0	1980.2	1890.0
27.5°	1977.1	1992.0	2019.2	2053.6	2086.7	2111.9	2119.0	2109.4	2065.5	1990.8	1896.3
30°	1803.5	1821.8	1842.2	1876.5	1943.2	1981.4	2023.2	2054.9	2037.2	1977.5	1889.5
32.5°	1612.8	1617.3	1647.6	1686.7	1747.7	1821.1	1887.4	1951.8	1973.2	1941.9	1868.5
35°	1311.5	1319.1	1351.8	1390.5	1465.2	1554.9	1654.8	1743.9	1817.5	1847.0	1809.5
37.5°	1070.3	1091.9	1115.0	1156.6	1222.3	1303.0	1406.8	1522.2	1631.8	1705.4	1717.8
40°	956.0	969.5	986.1	1017.7	1073.6	1153.2	1242.2	1374.4	1491.0	1596.2	1630.6
42.5°	865.8	873.6	883.8	912.5	955.0	1034.1	1115.5	1231.7	1348.8	1474.6	1532.2
45°	735.8	743.9	761.0	777.7	809.9	864.7	940.4	1036.0	1153.7	1275.1	1381.4
47.5°	642.0	647.1	657.3	675.1	702.5	738.6	800.2	880.1	989.1	1106.9	1220.2
50°	588.7	592.9	601.0	617.1	638.0	670.2	720.7	795.5	880.8	999.6	1110.6
52.5°	546.5	548.3	554.2	565.1	581.8	608.8	650.3	712.1	791.4	897.3	1008.0
55°	481.2	483.4	488.8	496.9	511.3	528.5	560.2	606.3	675.7	767.5	863.6
57.5°	427.5	429.0	433.5	436.7	448.6	462.5	487.0	519.9	572.4	650.3	736.1
60°	393.1	392.0	397.5	400.1	408.2	420.0	438.8	470.5	516.1	579.0	657.9
62.5°	359.6	358.1	362.6	366.2	370.8	380.9	396.3	421.1	458.2	514.9	583.2
65°	309.3	307.2	309.9	314.2	318.5	323.9	335.2	357.2	386.7	427.5	479.6
67.5°	258.8	261.2	261.6	263.7	266.2	273.5	281.2	296.8	317.6	350.3	394.5
70°	228.8	229.3	231.5	231.5	233.1	239.5	246.0	255.1	275.5	305.6	341.5
72.5°	198.7	201.0	200.2	201.9	203.0	207.3	212.1	220.8	238.1	260.4	290.8
75°	154.7	156.3	156.3	156.8	158.4	160.1	163.8	170.3	182.6	199.2	220.3
77.5°	112.8	113.0	113.7	115.7	115.7	118.3	121.1	126.2	132.3	143.7	156.5
80°	87.1	88.1	87.6	88.7	88.7	90.8	91.8	98.3	101.0	108.5	118.7
82.5°	63.8	64.8	64.7	66.2	67.2	67.6	69.1	71.6	74.3	81.0	85.1
85°	32.2	33.3	32.2	33.3	34.9	35.4	37.1	37.6	39.8	41.4	45.1
87.5°	16.5	17.7	17.6	17.9	18.7	18.9	19.0	18.3	19.7	19.8	21.1
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0	26.5	24.8	22.8
95°	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0	27.4	25.9	25.5
97.5°	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3	31.1	31.0	60.1
100°	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7	47.2	51.6	87.7
102.5°	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1	201.0	248.7	253.5
105°	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8	368.5	366.1	364.8
107.5°	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8	457.6	456.5	454.6
110°	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6	518.0	517.5	515.9



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4	576.5	576.6	575.9
115°	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9	662.4	661.8	662.1
117.5°	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8	749.9	750.0	749.5
120°	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6	802.8
122.5°	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8	856.5	856.2	855.8
125°	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9	930.1	929.4	929.9
127.5°	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.7	1004.9	1003.7
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6	1049.2	1049.0	1048.2
132.5°	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7	1093.4	1093.2	1092.2
135°	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5	1154.0	1153.5	1152.5
137.5°	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8	1212.2	1211.6	1210.5
140°	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9	1248.1	1247.4	1246.8
142.5°	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3	1281.7	1281.1	1280.8
145°	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0	1329.8	1329.5	1329.5
147.5°	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9	1371.7	1371.5	1371.7
150°	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7	1398.7	1398.7	1399.0
152.5°	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1	1421.7	1421.3	1421.7
155°	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6	1452.6	1451.5	1452.3
157.5°	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0	1478.9
160°	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9	1495.2
162.5°	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2	1510.6	1509.0	1509.2
165°	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0	1529.8	1527.8	1527.8
167.5°	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5	1544.2	1541.9	1542.1
170°	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4	1553.4	1551.3	1551.0
172.5°	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0	1558.9	1556.9	1556.6
175°	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7	1565.3	1563.0	1562.8
177.5°	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3	1568.6	1567.0	1566.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1338.2	1332.2	1327.9	1324.4	1315.0	1309.4	1305.1	1299.1	1292.2	1285.0	1275.9
5°	1414.1	1395.8	1382.5	1362.0	1342.7	1326.6	1310.0	1294.9	1276.7	1256.8	1242.2
7.5°	1494.0	1466.8	1432.0	1401.8	1367.9	1338.3	1311.9	1284.9	1256.7	1229.4	1204.4
10°	1544.7	1509.7	1471.1	1425.4	1382.5	1344.3	1308.9	1274.6	1241.2	1207.9	1179.4
12.5°	1599.2	1555.7	1498.5	1445.2	1397.0	1346.0	1303.3	1261.2	1221.0	1186.0	1152.8
15°	1672.4	1609.6	1543.6	1472.2	1408.8	1349.2	1290.6	1237.5	1192.3	1146.1	1113.9
17.5°	1717.5	1639.7	1564.2	1489.6	1412.9	1337.7	1274.6	1213.2	1156.7	1110.8	1070.2
20°	1747.2	1669.8	1575.8	1501.2	1409.9	1332.5	1259.5	1191.2	1132.2	1083.3	1041.4
22.5°	1772.9	1683.5	1589.5	1491.3	1400.4	1318.4	1238.4	1169.7	1109.4	1057.9	1017.7
25°	1786.9	1684.3	1582.3	1484.5	1381.4	1284.1	1211.6	1131.1	1066.6	1012.4	969.5
27.5°	1788.4	1678.7	1563.3	1454.6	1348.2	1257.7	1166.1	1094.2	1027.2	969.9	928.6
30°	1783.6	1669.3	1545.2	1427.5	1320.7	1222.4	1143.0	1064.5	996.3	939.4	896.4
32.5°	1768.6	1649.5	1522.0	1397.5	1286.8	1190.6	1108.5	1034.0	967.6	911.4	866.4
35°	1725.2	1607.5	1471.6	1342.2	1228.8	1131.7	1057.5	981.8	915.2	862.0	818.5
37.5°	1657.1	1550.7	1412.6	1278.7	1167.4	1069.8	996.3	927.9	867.8	813.7	769.2
40°	1597.8	1504.4	1365.8	1235.3	1115.0	1022.1	953.3	890.5	830.9	779.8	737.4
42.5°	1529.5	1448.0	1320.3	1182.0	1066.0	972.7	905.6	849.2	793.0	745.9	703.5
45°	1407.7	1354.0	1233.7	1105.9	985.0	897.0	833.0	783.7	736.4	690.1	654.7
47.5°	1267.6	1241.0	1139.7	1018.3	903.6	816.8	761.3	715.7	674.3	635.2	603.9
50°	1173.6	1160.6	1073.1	956.0	846.5	764.8	708.9	669.7	634.3	600.0	570.4
52.5°	1080.8	1080.3	1001.4	894.1	792.7	714.1	658.6	622.1	591.4	563.4	536.8
55°	938.9	953.8	892.1	796.5	705.7	634.8	584.9	552.1	530.7	507.6	487.7
57.5°	808.5	833.4	782.5	698.3	622.6	557.2	513.8	489.2	466.3	452.3	437.9
60°	723.5	747.1	707.3	636.4	565.0	509.2	467.8	445.8	425.9	416.3	406.1
62.5°	647.8	668.9	639.4	573.7	511.7	458.1	423.1	401.9	388.5	378.0	371.2
65°	539.8	557.4	532.3	484.4	431.3	388.3	359.8	343.2	330.3	326.0	318.5
67.5°	436.4	452.4	438.8	398.2	355.6	323.0	300.7	284.8	277.1	273.4	268.0
70°	374.9	391.0	376.5	341.0	308.3	280.9	259.9	250.9	242.8	241.2	233.6
72.5°	322.9	333.9	319.3	291.6	263.6	240.5	224.3	214.7	210.6	207.6	203.6
75°	242.3	251.9	242.3	220.8	200.9	184.8	170.8	167.0	162.2	160.6	157.9
77.5°	171.5	179.9	172.4	159.0	144.1	131.7	124.2	119.4	118.3	115.4	116.7
80°	131.1	136.4	129.5	120.3	108.5	99.9	94.5	91.8	88.7	87.6	89.7
82.5°	94.1	96.4	92.9	86.7	78.0	72.4	68.8	65.6	65.0	65.2	65.2
85°	48.9	48.4	47.8	42.4	39.8	36.0	33.8	33.3	32.7	33.8	34.9
87.5°	20.7	20.7	19.8	17.6	15.8	13.8	12.9	11.9	12.9	13.8	14.8
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7	14.9	15.1	15.2
95°	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5	55.6	46.8	38.0
97.5°	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0	142.6	148.1	153.6
100°	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5	197.1	201.9	206.5
102.5°	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4	257.8	261.3	264.7
105°	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1	354.8	356.3	357.9
107.5°	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9	445.8	446.6	447.3
110°	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0	507.7	508.5	509.3



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0	568.5	569.8	571.2
115°	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4	660.2	661.1	661.8
117.5°	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8	743.8	744.9	745.9
120°	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1	800.1	801.2	802.2
122.5°	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6	852.3	852.9	853.5
125°	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0	928.1	929.1	930.1
127.5°	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4	998.6	998.9	999.2
130°	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3	1044.6	1044.9	1045.1
132.5°	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6	1087.0	1087.5	1088.0
135°	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9	1149.7	1149.4	1149.1
137.5°	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1	1206.2	1206.3	1206.4
140°	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6	1243.1	1243.6	1244.3
142.5°	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5	1276.5	1277.4	1278.3
145°	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0	1326.8	1327.6	1328.3
147.5°	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0	1367.6	1369.0	1370.5
150°	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2	1396.2	1397.2	1398.4
152.5°	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6	1420.5	1421.3	1422.1
155°	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9	1454.1	1454.4	1454.6
157.5°	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7	1482.6	1482.4	1482.3
160°	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6	1498.8	1498.0	1497.3
162.5°	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6	1513.7	1512.7	1511.7
165°	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7	1532.4	1531.1	1529.7
167.5°	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6	1547.3	1546.0	1544.6
170°	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1	1555.6	1554.0	1552.5
172.5°	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8	1561.2	1559.6	1558.0
175°	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8	1567.3	1565.7	1564.2
177.5°	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7	1570.2	1568.7	1567.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1271.6	1267.8	1262.1	1254.5	1248.0	1241.1	1239.4	1236.8	1241.9	1237.7	1236.4
5°	1229.9	1218.6	1204.2	1187.5	1177.8	1163.9	1161.1	1155.8	1150.4	1149.9	1144.5
7.5°	1185.8	1169.2	1150.2	1133.3	1117.5	1102.3	1092.4	1090.1	1082.3	1077.6	1072.3
10°	1157.4	1137.0	1115.0	1098.8	1080.7	1064.5	1053.2	1046.8	1041.4	1035.5	1030.2
12.5°	1123.9	1102.2	1084.1	1066.6	1044.9	1032.7	1014.1	1003.0	1001.9	1002.0	988.1
15°	1084.9	1063.4	1035.5	1010.8	999.0	975.3	965.1	952.2	944.2	936.1	929.7
17.5°	1040.4	1013.6	991.8	963.4	940.9	922.1	908.7	900.9	888.8	877.4	869.1
20°	1012.4	983.9	960.9	930.8	906.1	882.9	871.7	860.9	851.8	842.1	833.0
22.5°	984.0	954.3	926.0	896.9	873.8	849.5	838.6	823.9	815.3	809.9	800.8
25°	939.4	907.2	874.9	847.0	823.3	801.8	787.4	776.1	766.4	762.1	756.2
27.5°	890.8	858.8	827.7	796.0	769.1	753.6	741.9	733.5	727.8	722.2	719.5
30°	859.9	826.6	793.2	763.8	739.0	723.5	712.7	706.8	702.5	699.8	697.1
32.5°	828.5	795.7	760.6	733.7	711.6	697.7	689.5	683.6	681.5	680.4	679.5
35°	778.2	745.0	712.7	688.5	667.6	662.3	655.2	652.1	651.0	654.7	656.3
37.5°	729.5	698.6	669.0	645.6	631.9	624.0	621.6	621.8	625.6	628.9	632.8
40°	698.2	668.1	640.3	619.8	606.9	602.1	601.0	603.7	607.9	611.8	616.0
42.5°	667.7	638.0	612.7	593.6	584.6	580.2	580.8	583.5	589.5	594.1	600.6
45°	620.4	595.6	570.9	555.3	547.9	548.9	548.9	553.7	559.7	566.6	573.6
47.5°	575.7	550.9	530.5	517.5	513.5	512.6	515.6	521.9	530.4	539.1	548.8
50°	545.6	522.0	504.3	492.5	488.2	489.8	494.1	500.0	510.2	521.0	531.2
52.5°	515.1	493.7	477.3	466.3	463.3	466.2	470.5	479.8	488.8	500.4	512.7
55°	467.8	449.5	436.7	428.6	427.5	429.1	433.9	444.1	457.1	471.6	483.4
57.5°	420.6	405.4	393.5	388.0	388.5	390.0	398.0	410.1	423.8	439.3	454.5
60°	388.9	374.9	365.3	360.9	361.4	364.7	374.4	385.7	402.8	417.9	433.9
62.5°	358.8	346.5	337.3	333.5	332.6	339.7	349.0	360.7	377.9	394.7	412.0
65°	310.4	300.7	293.3	291.1	292.8	298.1	309.9	325.5	340.0	357.7	376.0
67.5°	263.2	255.2	250.0	251.1	253.0	260.9	270.8	284.2	300.6	319.0	337.1
70°	233.1	225.6	221.3	221.8	225.0	234.7	243.3	256.7	274.5	293.3	308.3
72.5°	202.2	197.2	193.4	195.6	198.8	205.5	216.2	229.6	245.2	262.8	278.6
75°	155.2	155.2	153.1	154.7	159.6	165.9	174.0	187.9	203.6	217.5	230.5
77.5°	115.1	114.0	115.3	117.3	120.1	127.7	136.9	146.9	158.6	172.6	183.3
80°	88.1	88.7	91.3	94.5	95.6	101.5	111.2	120.3	129.5	141.3	151.5
82.5°	66.1	66.8	68.1	72.2	73.2	79.6	85.8	94.9	103.2	111.2	119.7
85°	36.0	36.0	38.7	40.3	42.9	47.3	51.0	56.4	63.9	69.3	77.4
87.5°	16.8	17.3	19.4	20.7	22.3	24.9	26.1	31.1	33.1	35.6	39.7
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0	29.6	31.1	32.0
95°	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0	30.5	32.1	33.0
97.5°	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3	31.4	31.6	31.8
100°	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7	38.4	33.9	31.8
102.5°	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1	105.3	57.5	33.6
105°	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8	373.1	375.5	371.9
107.5°	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8	459.9	461.0	462.1
110°	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6	519.1	519.6	520.2



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4	576.3	576.2	576.6
115°	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9	663.4	663.9	664.2
117.5°	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8	749.7	749.6	749.5
120°	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7	804.2	804.7	804.7
122.5°	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8	857.1	857.4	857.3
125°	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9	931.7	932.5	933.0
127.5°	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6	1004.4	1004.3	1004.1
130°	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6	1049.9	1050.1	1050.2
132.5°	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7	1094.0	1094.2	1094.2
135°	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5	1155.0	1155.6	1156.1
137.5°	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8	1213.4	1214.0	1214.2
140°	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9	1249.7	1250.5	1251.0
142.5°	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3	1282.8	1283.4	1283.7
145°	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0	1330.3	1330.5	1330.9
147.5°	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9	1372.1	1372.3	1372.5
150°	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7	1398.7	1398.7	1398.9
152.5°	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1	1422.5	1422.9	1423.0
155°	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6	1454.6	1455.7	1455.8
157.5°	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5
160°	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2
162.5°	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2	1513.7	1515.3	1515.2
165°	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0	1534.1	1536.1	1536.0
167.5°	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5	1548.7	1551.1	1550.8
170°	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4	1557.5	1559.6	1559.3
172.5°	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0	1563.2	1565.2	1564.9
175°	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7	1570.0	1572.4	1572.0
177.5°	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3	1572.0	1573.7	1573.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1235.5	1234.7	1231.6	1231.2	1231.6	1234.7	1235.5	1236.4	1237.7	1241.9	1236.8
5°	1141.3	1138.6	1137.0	1143.0	1137.0	1138.6	1141.3	1144.5	1149.9	1150.4	1155.8
7.5°	1070.3	1068.1	1063.4	1062.0	1063.4	1068.1	1070.3	1072.3	1077.6	1082.3	1090.1
10°	1024.7	1022.6	1018.3	1017.2	1018.3	1022.6	1024.7	1030.2	1035.5	1041.4	1046.8
12.5°	980.9	976.6	975.7	976.8	975.7	976.6	980.9	988.1	1002.0	1001.9	1003.0
15°	922.7	920.6	914.6	916.3	914.6	920.6	922.7	929.7	936.1	944.2	952.2
17.5°	865.4	862.7	855.6	861.9	855.6	862.7	865.4	869.1	877.4	888.8	900.9
20°	829.3	825.0	821.2	820.6	821.2	825.0	829.3	833.0	842.1	851.8	860.9
22.5°	794.9	791.0	790.7	787.2	790.7	791.0	794.9	800.8	809.9	815.3	823.9
25°	751.9	748.2	747.1	744.4	747.1	748.2	751.9	756.2	762.1	766.4	776.1
27.5°	718.9	717.1	715.2	716.0	715.2	717.1	718.9	719.5	722.2	727.8	733.5
30°	698.7	698.2	697.1	697.1	697.1	698.2	698.7	697.1	699.8	702.5	706.8
32.5°	682.0	681.9	682.6	682.6	682.6	681.9	682.0	679.5	680.4	681.5	683.6
35°	658.4	660.0	661.2	659.5	661.2	660.0	658.4	656.3	654.7	651.0	652.1
37.5°	637.2	638.8	640.4	642.2	640.4	638.8	637.2	632.8	628.9	625.6	621.8
40°	620.9	624.6	625.7	628.4	625.7	624.6	620.9	616.0	611.8	607.9	603.7
42.5°	605.4	609.6	612.4	612.9	612.4	609.6	605.4	600.6	594.1	589.5	583.5
45°	581.7	585.9	589.8	589.8	589.8	585.9	581.7	573.6	566.6	559.7	553.7
47.5°	557.0	563.3	567.0	568.0	567.0	563.3	557.0	548.8	539.1	530.4	521.9
50°	540.3	547.9	551.6	554.3	551.6	547.9	540.3	531.2	521.0	510.2	500.0
52.5°	524.0	531.5	536.5	538.0	536.5	531.5	524.0	512.7	500.4	488.8	479.8
55°	495.7	506.4	512.4	514.5	512.4	506.4	495.7	483.4	471.6	457.1	444.1
57.5°	469.1	479.0	485.8	487.5	485.8	479.0	469.1	454.5	439.3	423.8	410.1
60°	448.5	459.2	467.8	469.4	467.8	459.2	448.5	433.9	417.9	402.8	385.7
62.5°	427.4	438.6	446.4	450.5	446.4	438.6	427.4	412.0	394.7	377.9	360.7
65°	391.0	402.2	409.8	411.4	409.8	402.2	391.0	376.0	357.7	340.0	325.5
67.5°	351.2	362.5	367.5	370.6	367.5	362.5	351.2	337.1	319.0	300.6	284.2
70°	323.4	332.4	337.8	340.5	337.8	332.4	323.4	308.3	293.3	274.5	256.7
72.5°	291.5	301.0	307.3	307.8	307.3	301.0	291.5	278.6	262.8	245.2	229.6
75°	242.8	251.4	254.6	254.6	254.6	251.4	242.8	230.5	217.5	203.6	187.9
77.5°	192.2	196.6	200.7	201.5	200.7	196.6	192.2	183.3	172.6	158.6	146.9
80°	159.6	162.2	165.4	165.4	165.4	162.2	159.6	151.5	141.3	129.5	120.3
82.5°	126.0	128.3	131.5	131.1	131.5	128.3	126.0	119.7	111.2	103.2	94.9
85°	76.2	81.1	80.6	79.5	80.6	81.1	76.2	77.4	69.3	63.9	56.4
87.5°	41.1	41.6	43.0	44.0	43.0	41.6	41.1	39.7	35.6	33.1	31.1
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	32.1	32.2	32.3	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0
95°	33.2	33.5	33.7	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0
97.5°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3
100°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7
102.5°	33.6	33.7	33.7	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1
105°	362.5	353.1	343.9	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8
107.5°	463.1	464.1	465.0	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8
110°	521.0	521.8	522.6	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.6	578.7	579.7	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4
115°	664.2	664.2	664.2	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9
117.5°	749.4	749.3	749.2	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8
120°	804.2	803.7	803.1	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7
122.5°	856.8	856.3	855.7	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8
125°	933.2	933.5	933.8	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9
127.5°	1003.9	1003.7	1003.5	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6
132.5°	1094.0	1093.8	1093.6	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7
135°	1156.6	1157.1	1157.6	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5
137.5°	1214.1	1213.9	1213.7	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8
140°	1251.2	1251.5	1251.7	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9
142.5°	1283.8	1283.8	1283.9	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3
145°	1331.4	1331.9	1332.5	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0
147.5°	1372.8	1373.1	1373.3	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9
150°	1399.1	1399.4	1399.7	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7
152.5°	1422.9	1422.7	1422.6	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1
155°	1455.0	1454.2	1453.5	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6
157.5°	1482.1	1480.8	1479.4	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8
160°	1499.6	1498.0	1496.5	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0
162.5°	1513.4	1511.7	1509.8	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2
165°	1533.7	1531.3	1528.9	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0
167.5°	1548.3	1545.7	1543.1	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5
170°	1556.7	1554.1	1551.6	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4
172.5°	1562.1	1559.2	1556.4	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0
175°	1568.8	1565.7	1562.6	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7
177.5°	1570.7	1568.2	1565.7	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1239.4	1241.1	1248.0	1254.5	1262.1	1267.8	1271.6	1275.9	1285.0	1292.2	1299.1
5°	1161.1	1163.9	1177.8	1187.5	1204.2	1218.6	1229.9	1242.2	1256.8	1276.7	1294.9
7.5°	1092.4	1102.3	1117.5	1133.3	1150.2	1169.2	1185.8	1204.4	1229.4	1256.7	1284.9
10°	1053.2	1064.5	1080.7	1098.8	1115.0	1137.0	1157.4	1179.4	1207.9	1241.2	1274.6
12.5°	1014.1	1032.7	1044.9	1066.6	1084.1	1102.2	1123.9	1152.8	1186.0	1221.0	1261.2
15°	965.1	975.3	999.0	1010.8	1035.5	1063.4	1084.9	1113.9	1146.1	1192.3	1237.5
17.5°	908.7	922.1	940.9	963.4	991.8	1013.6	1040.4	1070.2	1110.8	1156.7	1213.2
20°	871.7	882.9	906.1	930.8	960.9	983.9	1012.4	1041.4	1083.3	1132.2	1191.2
22.5°	838.6	849.5	873.8	896.9	926.0	954.3	984.0	1017.7	1057.9	1109.4	1169.7
25°	787.4	801.8	823.3	847.0	874.9	907.2	939.4	969.5	1012.4	1066.6	1131.1
27.5°	741.9	753.6	769.1	796.0	827.7	858.8	890.8	928.6	969.9	1027.2	1094.2
30°	712.7	723.5	739.0	763.8	793.2	826.6	859.9	896.4	939.4	996.3	1064.5
32.5°	689.5	697.7	711.6	733.7	760.6	795.7	828.5	866.4	911.4	967.6	1034.0
35°	655.2	662.3	667.6	688.5	712.7	745.0	778.2	818.5	862.0	915.2	981.8
37.5°	621.6	624.0	631.9	645.6	669.0	698.6	729.5	769.2	813.7	867.8	927.9
40°	601.0	602.1	606.9	619.8	640.3	668.1	698.2	737.4	779.8	830.9	890.5
42.5°	580.8	580.2	584.6	593.6	612.7	638.0	667.7	703.5	745.9	793.0	849.2
45°	548.9	548.9	547.9	555.3	570.9	595.6	620.4	654.7	690.1	736.4	783.7
47.5°	515.6	512.6	513.5	517.5	530.5	550.9	575.7	603.9	635.2	674.3	715.7
50°	494.1	489.8	488.2	492.5	504.3	522.0	545.6	570.4	600.0	634.3	669.7
52.5°	470.5	466.2	463.3	466.3	477.3	493.7	515.1	536.8	563.4	591.4	622.1
55°	433.9	429.1	427.5	428.6	436.7	449.5	467.8	487.7	507.6	530.7	552.1
57.5°	398.0	390.0	388.5	388.0	393.5	405.4	420.6	437.9	452.3	466.3	489.2
60°	374.4	364.7	361.4	360.9	365.3	374.9	388.9	406.1	416.3	425.9	445.8
62.5°	349.0	339.7	332.6	333.5	337.3	346.5	358.8	371.2	378.0	388.5	401.9
65°	309.9	298.1	292.8	291.1	293.3	300.7	310.4	318.5	326.0	330.3	343.2
67.5°	270.8	260.9	253.0	251.1	250.0	255.2	263.2	268.0	273.4	277.1	284.8
70°	243.3	234.7	225.0	221.8	221.3	225.6	233.1	233.6	241.2	242.8	250.9
72.5°	216.2	205.5	198.8	195.6	193.4	197.2	202.2	203.6	207.6	210.6	214.7
75°	174.0	165.9	159.6	154.7	153.1	155.2	155.2	157.9	160.6	162.2	167.0
77.5°	136.9	127.7	120.1	117.3	115.3	114.0	115.1	116.7	115.4	118.3	119.4
80°	111.2	101.5	95.6	94.5	91.3	88.7	88.1	89.7	87.6	88.7	91.8
82.5°	85.8	79.6	73.2	72.2	68.1	66.8	66.1	65.2	65.2	65.0	65.6
85°	51.0	47.3	42.9	40.3	38.7	36.0	36.0	34.9	33.8	32.7	33.3
87.5°	26.1	24.9	22.3	20.7	19.4	17.3	16.8	14.8	13.8	12.9	11.9
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	26.5	24.8	22.8	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7
95°	27.4	25.9	25.5	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5
97.5°	31.1	31.0	60.1	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0
100°	47.2	51.6	87.7	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5
102.5°	201.0	248.7	253.5	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4
105°	368.5	366.1	364.8	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1
107.5°	457.6	456.5	454.6	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9
110°	518.0	517.5	515.9	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	576.5	576.6	575.9	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0
115°	662.4	661.8	662.1	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4
117.5°	749.9	750.0	749.5	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8
120°	803.1	802.6	802.8	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1
122.5°	856.5	856.2	855.8	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6
125°	930.1	929.4	929.9	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0
127.5°	1004.7	1004.9	1003.7	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4
130°	1049.2	1049.0	1048.2	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3
132.5°	1093.4	1093.2	1092.2	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6
135°	1154.0	1153.5	1152.5	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9
137.5°	1212.2	1211.6	1210.5	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1
140°	1248.1	1247.4	1246.8	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6
142.5°	1281.7	1281.1	1280.8	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5
145°	1329.8	1329.5	1329.5	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0
147.5°	1371.7	1371.5	1371.7	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0
150°	1398.7	1398.7	1399.0	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2
152.5°	1421.7	1421.3	1421.7	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6
155°	1452.6	1451.5	1452.3	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9
157.5°	1479.4	1478.0	1478.9	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7
160°	1496.5	1494.9	1495.2	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6
162.5°	1510.6	1509.0	1509.2	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6
165°	1529.8	1527.8	1527.8	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7
167.5°	1544.2	1541.9	1542.1	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6
170°	1553.4	1551.3	1551.0	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1
172.5°	1558.9	1556.9	1556.6	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8
175°	1565.3	1563.0	1562.8	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8
177.5°	1568.6	1567.0	1566.6	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1305.1	1309.4	1315.0	1324.4	1327.9	1332.2	1338.2	1337.8	1339.5	1345.9	1359.7
5°	1310.0	1326.6	1342.7	1362.0	1382.5	1395.8	1414.1	1425.4	1436.7	1451.2	1475.9
7.5°	1311.9	1338.3	1367.9	1401.8	1432.0	1466.8	1494.0	1519.5	1542.6	1573.3	1602.7
10°	1308.9	1344.3	1382.5	1425.4	1471.1	1509.7	1544.7	1584.4	1618.2	1655.3	1688.6
12.5°	1303.3	1346.0	1397.0	1445.2	1498.5	1555.7	1599.2	1639.4	1684.5	1727.1	1778.4
15°	1290.6	1349.2	1408.8	1472.2	1543.6	1609.6	1672.4	1724.5	1772.9	1836.8	1904.0
17.5°	1274.6	1337.7	1412.9	1489.6	1564.2	1639.7	1717.5	1795.8	1856.8	1936.2	1988.7
20°	1259.5	1332.5	1409.9	1501.2	1575.8	1669.8	1747.2	1822.9	1906.6	1985.6	2048.4
22.5°	1238.4	1318.4	1400.4	1491.3	1589.5	1683.5	1772.9	1855.1	1938.8	2024.7	2100.8
25°	1211.6	1284.1	1381.4	1484.5	1582.3	1684.3	1786.9	1890.0	1980.2	2071.0	2141.9
27.5°	1166.1	1257.7	1348.2	1454.6	1563.3	1678.7	1788.4	1896.3	1990.8	2065.5	2109.4
30°	1143.0	1222.4	1320.7	1427.5	1545.2	1669.3	1783.6	1889.5	1977.5	2037.2	2054.9
32.5°	1108.5	1190.6	1286.8	1397.5	1522.0	1649.5	1768.6	1868.5	1941.9	1973.2	1951.8
35°	1057.5	1131.7	1228.8	1342.2	1471.6	1607.5	1725.2	1809.5	1847.0	1817.5	1743.9
37.5°	996.3	1069.8	1167.4	1278.7	1412.6	1550.7	1657.1	1717.8	1705.4	1631.8	1522.2
40°	953.3	1022.1	1115.0	1235.3	1365.8	1504.4	1597.8	1630.6	1596.2	1491.0	1374.4
42.5°	905.6	972.7	1066.0	1182.0	1320.3	1448.0	1529.5	1532.2	1474.6	1348.8	1231.7
45°	833.0	897.0	985.0	1105.9	1233.7	1354.0	1407.7	1381.4	1275.1	1153.7	1036.0
47.5°	761.3	816.8	903.6	1018.3	1139.7	1241.0	1267.6	1220.2	1106.9	989.1	880.1
50°	708.9	764.8	846.5	956.0	1073.1	1160.6	1173.6	1110.6	999.6	880.8	795.5
52.5°	658.6	714.1	792.7	894.1	1001.4	1080.3	1080.8	1008.0	897.3	791.4	712.1
55°	584.9	634.8	705.7	796.5	892.1	953.8	938.9	863.6	767.5	675.7	606.3
57.5°	513.8	557.2	622.6	698.3	782.5	833.4	808.5	736.1	650.3	572.4	519.9
60°	467.8	509.2	565.0	636.4	707.3	747.1	723.5	657.9	579.0	516.1	470.5
62.5°	423.1	458.1	511.7	573.7	639.4	668.9	647.8	583.2	514.9	458.2	421.1
65°	359.8	388.3	431.3	484.4	532.3	557.4	539.8	479.6	427.5	386.7	357.2
67.5°	300.7	323.0	355.6	398.2	438.8	452.4	436.4	394.5	350.3	317.6	296.8
70°	259.9	280.9	308.3	341.0	376.5	391.0	374.9	341.5	305.6	275.5	255.1
72.5°	224.3	240.5	263.6	291.6	319.3	333.9	322.9	290.8	260.4	238.1	220.8
75°	170.8	184.8	200.9	220.8	242.3	251.9	242.3	220.3	199.2	182.6	170.3
77.5°	124.2	131.7	144.1	159.0	172.4	179.9	171.5	156.5	143.7	132.3	126.2
80°	94.5	99.9	108.5	120.3	129.5	136.4	131.1	118.7	108.5	101.0	98.3
82.5°	68.8	72.4	78.0	86.7	92.9	96.4	94.1	85.1	81.0	74.3	71.6
85°	33.8	36.0	39.8	42.4	47.8	48.4	48.9	45.1	41.4	39.8	37.6
87.5°	12.9	13.8	15.8	17.6	19.8	20.7	20.7	21.1	19.8	19.7	18.3
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0
95°	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0
97.5°	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3
100°	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7
102.5°	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1
105°	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8
107.5°	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8
110°	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4
115°	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9
117.5°	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8
120°	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7
122.5°	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8
125°	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9
127.5°	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6
130°	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6
132.5°	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7
135°	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5
137.5°	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8
140°	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9
142.5°	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3
145°	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0
147.5°	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9
150°	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7
152.5°	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1
155°	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6
157.5°	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8
160°	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0
162.5°	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2
165°	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0
167.5°	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5
170°	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4
172.5°	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0
175°	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7
177.5°	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1366.5	1367.5	1371.3	1374.3	1375.1	1379.5	1379.9
5°	1486.6	1495.8	1513.5	1515.1	1517.8	1531.8	1521.1
7.5°	1627.4	1650.5	1666.1	1679.7	1684.7	1690.7	1689.5
10°	1717.6	1752.0	1769.2	1796.5	1797.7	1804.6	1800.3
12.5°	1808.3	1848.3	1879.6	1884.6	1907.6	1911.2	1917.2
15°	1936.7	1979.1	2022.7	2038.2	2069.9	2077.5	2089.3
17.5°	2057.5	2100.8	2131.3	2171.6	2184.6	2202.0	2190.2
20°	2123.6	2170.9	2209.6	2241.3	2254.7	2264.3	2263.3
22.5°	2163.6	2211.3	2242.6	2266.6	2279.2	2283.3	2283.0
25°	2188.6	2216.0	2225.6	2234.8	2220.9	2216.0	2218.2
27.5°	2119.0	2111.9	2086.7	2053.6	2019.2	1992.0	1977.1
30°	2023.2	1981.4	1943.2	1876.5	1842.2	1821.8	1803.5
32.5°	1887.4	1821.1	1747.7	1686.7	1647.6	1617.3	1612.8
35°	1654.8	1554.9	1465.2	1390.5	1351.8	1319.1	1311.5
37.5°	1406.8	1303.0	1222.3	1156.6	1115.0	1091.9	1070.3
40°	1242.2	1153.2	1073.6	1017.7	986.1	969.5	956.0
42.5°	1115.5	1034.1	955.0	912.5	883.8	873.6	865.8
45°	940.4	864.7	809.9	777.7	761.0	743.9	735.8
47.5°	800.2	738.6	702.5	675.1	657.3	647.1	642.0
50°	720.7	670.2	638.0	617.1	601.0	592.9	588.7
52.5°	650.3	608.8	581.8	565.1	554.2	548.3	546.5
55°	560.2	528.5	511.3	496.9	488.8	483.4	481.2
57.5°	487.0	462.5	448.6	436.7	433.5	429.0	427.5
60°	438.8	420.0	408.2	400.1	397.5	392.0	393.1
62.5°	396.3	380.9	370.8	366.2	362.6	358.1	359.6
65°	335.2	323.9	318.5	314.2	309.9	307.2	309.3
67.5°	281.2	273.5	266.2	263.7	261.6	261.2	258.8
70°	246.0	239.5	233.1	231.5	231.5	229.3	228.8
72.5°	212.1	207.3	203.0	201.9	200.2	201.0	198.7
75°	163.8	160.1	158.4	156.8	156.3	156.3	154.7
77.5°	121.1	118.3	115.7	115.7	113.7	113.0	112.8
80°	91.8	90.8	88.7	88.7	87.6	88.1	87.1
82.5°	69.1	67.6	67.2	66.2	64.7	64.8	63.8
85°	37.1	35.4	34.9	33.3	32.2	33.3	32.2
87.5°	19.0	18.9	18.7	17.9	17.6	17.7	16.5
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	519.1	519.6	520.2	521.0	521.8	522.6	523.3



TEST NUMBER: P332616-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)