

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332869-830

Luminaire Tested: **SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332869-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2542.3 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332869-830
CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	2.2
10°-20°	152.6	6.0
20°-30°	220.4	8.7
30°-40°	249.8	9.8
40°-50°	241.2	9.5
50°-60°	200.6	7.9
60°-70°	138.5	5.4
70°-80°	70.2	2.8
80°-90°	19.3	0.8
90°-100°	28.4	1.1
100°-110°	84.2	3.3
110°-120°	142.8	5.6
120°-130°	188.3	7.4
130°-140°	211.5	8.3
140°-150°	207.8	8.2
150°-160°	174.8	6.9
160°-170°	116.3	4.6
170°-180°	40.7	1.6
0°-30°	427.8	16.8
0°-40°	677.6	26.7
0°-60°	1119.4	44.0
0°-90°	1347.5	53.0
90°-120°	255.4	10.0
90°-150°	863.0	33.9
90°-180°	1195.0	47.0
0°-180°	2542.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	1	5	7	9	10	2
95°	20	23	25	26	26	22
105°	78	78	79	80	81	82
115°	145	145	145	144	144	143
125°	212	211	211	210	210	188
135°	273	275	275	274	273	211
145°	331	333	333	333	332	207
155°	380	380	379	380	379	175
165°	413	412	412	413	412	116
175°	430	428	428	430	428	41
180°	431	431	431	431	431	



TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.4	7.9	7.4	7.0	6.5	6.3	6.3	6.4	6.4	6.5	6.5
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	7.2	8.1	9.0	9.9	10.8	11.5	12.0	12.3	12.8	13.2	13.5
95°	20.0	20.6	21.3	22.0	22.6	23.3	23.8	24.3	24.8	25.4	25.5
97.5°	34.9	35.4	36.0	36.5	37.0	37.6	38.2	38.8	39.4	40.1	40.3
100°	46.7	46.9	47.2	47.5	47.8	48.3	48.9	49.7	50.3	51.0	51.1
102.5°	58.9	59.0	59.1	59.3	59.4	59.8	60.3	61.0	61.5	62.1	62.4
105°	77.6	77.7	77.8	77.9	77.9	78.0	78.4	78.7	79.0	79.3	79.5
107.5°	97.3	97.4	97.5	97.6	97.6	97.6	97.7	97.7	97.8	97.8	98.0
110°	110.6	110.7	110.8	111.0	111.1	111.2	111.1	111.0	110.9	110.9	110.7



TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	124.4	124.4	124.5	124.5	124.5	124.5	124.3	124.2	124.1	123.9	123.9
115°	145.2	145.2	145.2	145.2	145.2	145.2	145.0	144.9	144.7	144.6	144.5
117.5°	164.8	164.9	164.9	164.9	165.0	165.0	164.9	164.9	164.7	164.6	164.4
120°	177.9	178.1	178.4	178.7	179.1	179.1	178.9	178.6	178.4	178.2	177.9
122.5°	191.4	191.5	191.7	191.8	191.9	191.9	191.8	191.7	191.6	191.5	191.2
125°	211.5	211.5	211.5	211.5	211.5	211.4	211.4	211.3	211.2	211.1	211.0
127.5°	229.7	229.9	230.2	230.4	230.5	230.6	230.5	230.4	230.3	230.2	230.0
130°	242.5	242.7	242.9	243.2	243.4	243.5	243.5	243.5	243.5	243.5	243.4
132.5°	255.5	255.7	255.8	256.0	256.2	256.2	256.2	256.1	256.1	256.0	255.8
135°	272.8	273.2	273.6	274.1	274.6	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	291.5	291.8	292.0	292.2	292.4	292.6	292.7	292.8	292.9	293.0	292.8
140°	304.1	304.3	304.3	304.5	304.7	304.7	304.7	304.7	304.7	304.7	304.7
142.5°	315.6	315.7	315.8	315.9	316.1	316.2	316.1	316.0	316.0	315.9	315.9
145°	331.4	331.7	332.0	332.2	332.6	332.8	332.8	332.9	333.0	333.1	333.0
147.5°	347.1	347.5	347.8	348.2	348.6	348.6	348.6	348.6	348.6	348.5	348.4
150°	356.8	357.0	357.3	357.6	357.9	358.1	358.1	358.1	358.1	358.1	358.1
152.5°	365.8	366.0	366.1	366.3	366.5	366.6	366.6	366.7	366.7	366.8	367.0
155°	379.7	379.7	379.7	379.7	379.7	379.7	379.6	379.5	379.5	379.4	379.7
157.5°	391.4	391.2	391.2	391.1	390.9	390.8	390.8	390.8	390.8	390.8	391.0
160°	398.3	398.2	398.2	398.1	398.0	397.9	397.9	397.8	397.8	397.7	397.9
162.5°	404.7	404.5	404.4	404.2	404.0	403.9	403.8	403.7	403.6	403.5	404.0
165°	413.3	413.1	412.9	412.6	412.5	412.3	412.1	412.0	411.8	411.7	412.1
167.5°	419.9	419.6	419.3	419.0	418.7	418.5	418.6	418.6	418.6	418.6	419.1
170°	423.7	423.3	422.9	422.5	422.2	422.1	422.1	422.2	422.3	422.4	422.7
172.5°	426.3	426.0	425.7	425.4	425.1	424.9	424.9	425.0	425.0	425.0	425.5
175°	430.0	429.6	429.2	428.9	428.5	428.3	428.2	428.1	428.1	428.0	428.5
177.5°	431.2	430.9	430.6	430.3	430.0	429.9	429.9	429.9	429.9	429.9	430.3
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6



TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	6.5	6.5	6.5	6.6	6.7	6.8	6.9	7.0
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.8	13.9	14.2	14.4	14.5	14.6	14.7	14.8
95°	25.7	26.0	26.2	26.3	26.3	26.3	26.3	26.3
97.5°	40.5	40.8	41.1	41.2	41.2	41.2	41.2	41.2
100°	51.3	51.4	51.6	51.7	51.7	51.7	51.7	51.7
102.5°	62.6	62.8	63.0	63.2	63.2	63.2	63.2	63.3
105°	79.7	79.9	80.1	80.4	80.6	80.9	81.1	81.2
107.5°	98.3	98.5	98.7	98.8	98.8	98.8	98.8	98.7
110°	110.7	110.5	110.3	110.4	110.6	110.8	111.0	111.2



TEST NUMBER: P332869-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	124.0
115°	144.4	144.3	144.2	144.2	144.1	144.0	143.9	143.9
117.5°	164.1	163.8	163.6	163.4	163.2	163.1	163.0	162.8
120°	177.5	177.1	176.7	176.6	176.7	176.9	177.0	177.2
122.5°	191.1	190.8	190.5	190.2	190.0	189.7	189.5	189.2
125°	210.8	210.8	210.6	210.4	210.3	210.1	210.0	209.8
127.5°	229.9	229.7	229.5	229.4	229.3	229.2	229.0	228.9
130°	243.2	243.0	242.9	242.6	242.3	242.0	241.8	241.5
132.5°	255.7	255.5	255.4	255.2	255.1	255.1	255.0	254.8
135°	274.5	274.4	274.2	274.0	273.8	273.5	273.3	273.1
137.5°	292.7	292.5	292.3	292.2	292.2	292.3	292.3	292.4
140°	304.6	304.5	304.4	304.3	304.3	304.3	304.2	304.1
142.5°	315.9	315.9	315.8	315.8	315.8	315.8	315.8	315.8
145°	332.9	332.8	332.8	332.6	332.4	332.2	332.0	331.8
147.5°	348.4	348.3	348.2	348.2	348.1	348.0	347.9	347.9
150°	358.1	358.1	358.1	358.0	358.0	357.9	357.8	357.7
152.5°	367.2	367.4	367.6	367.5	367.3	367.1	366.9	366.7
155°	379.9	380.2	380.5	380.5	380.2	379.9	379.7	379.4
157.5°	391.2	391.4	391.6	391.6	391.3	391.2	390.9	390.6
160°	398.1	398.3	398.6	398.5	398.1	397.8	397.4	397.0
162.5°	404.4	404.7	405.1	405.1	404.8	404.4	404.1	403.7
165°	412.6	413.0	413.4	413.5	413.2	412.9	412.6	412.4
167.5°	419.5	419.9	420.4	420.4	419.9	419.4	419.0	418.5
170°	423.2	423.7	424.1	424.0	423.6	423.0	422.5	422.0
172.5°	426.0	426.5	427.0	427.0	426.5	425.9	425.5	424.9
175°	429.0	429.5	430.1	430.1	429.5	429.0	428.5	428.0
177.5°	430.6	431.1	431.5	431.5	431.0	430.6	430.1	429.6
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6

(END OF REPORT)