

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332870-830

Luminaire Tested: **SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332870-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2580.3 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332870-830
CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332870-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42	38				
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32				
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28				
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24				
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22				
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19				
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17				
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16				
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332870-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	2.1
10°-20°	152.6	5.9
20°-30°	220.4	8.5
30°-40°	249.8	9.7
40°-50°	241.2	9.3
50°-60°	200.6	7.8
60°-70°	138.5	5.4
70°-80°	70.2	2.7
80°-90°	18.9	0.7
90°-100°	122.5	4.7
100°-110°	254.9	9.9
110°-120°	228.3	8.8
120°-130°	192.0	7.4
130°-140°	160.1	6.2
140°-150°	122.3	4.7
150°-160°	86.0	3.3
160°-170°	50.6	2.0
170°-180°	16.5	0.6
0°-30°	427.8	16.6
0°-40°	677.6	26.3
0°-60°	1119.4	43.4
0°-90°	1347.1	52.2
90°-120°	605.7	23.5
90°-150°	1080.2	41.9
90°-180°	1233.0	47.8
0°-180°	2580.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	0	3	6	7	7	2
95°	11	35	272	134	81	12
105°	39	56	218	471	469	42
115°	69	86	195	374	450	68
125°	96	114	194	319	359	85
135°	114	135	192	283	321	88
145°	131	150	191	238	262	82
155°	149	161	186	210	220	69
165°	162	167	178	189	192	46
175°	169	170	171	173	173	16
180°	170	170	170	170	170	



TEST NUMBER: P332870-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.3	7.7	7.4	6.8	6.2	5.8	6.1	6.1	6.1	6.2	6.0
90°	0.4	1.0	2.0	2.4	2.6	2.6	4.6	4.6	5.4	6.0	5.7
92.5°	3.8	5.6	8.7	12.7	17.6	24.5	41.5	67.3	92.5	105.7	88.0
95°	11.0	12.0	15.4	19.7	27.6	41.7	70.6	125.3	204.9	271.5	279.2
97.5°	19.7	19.7	22.6	26.6	33.5	45.1	67.5	112.6	191.7	286.0	350.7
100°	25.4	25.4	27.6	31.7	38.0	48.6	68.3	105.9	173.9	267.9	353.1
102.5°	30.6	31.2	33.3	36.9	43.1	53.2	71.0	104.1	161.9	245.2	333.1
105°	39.0	40.0	41.7	45.6	51.7	61.3	77.3	104.9	151.6	218.5	296.8
107.5°	48.2	48.8	50.5	54.8	60.5	70.0	84.6	109.9	149.7	203.6	267.5
110°	54.3	55.0	56.6	60.6	66.6	75.6	90.3	113.6	150.2	198.5	252.9



TEST NUMBER: P332870-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.1	60.8	62.8	66.4	72.5	81.4	95.6	117.6	151.8	196.1	244.6
115°	68.6	69.7	71.9	75.3	81.6	90.6	104.0	123.9	154.9	194.9	236.9
117.5°	77.4	78.3	80.4	84.1	90.0	99.3	112.0	130.4	158.2	194.5	233.4
120°	83.3	84.0	86.2	89.9	95.6	104.9	117.6	134.9	160.6	194.5	231.5
122.5°	88.6	89.3	91.6	95.0	101.2	110.3	122.9	139.2	163.0	194.3	229.4
125°	95.6	96.9	99.0	102.6	109.0	118.3	130.3	145.5	166.5	193.9	225.8
127.5°	101.8	102.8	105.3	109.4	116.0	125.5	137.0	151.1	169.5	193.1	221.1
130°	105.3	106.6	109.2	114.2	120.6	130.3	141.6	154.6	171.5	192.8	218.2
132.5°	108.8	109.8	113.3	118.0	124.9	133.9	145.3	158.1	173.4	192.7	215.6
135°	113.6	114.9	118.3	123.9	130.9	139.6	150.5	162.6	176.3	192.2	211.5
137.5°	118.5	119.7	123.4	128.8	136.0	144.3	154.6	165.8	177.9	192.2	208.1
140°	122.0	122.9	126.6	132.2	139.2	147.2	157.2	167.9	179.2	191.9	206.2
142.5°	125.6	126.7	130.1	135.4	142.1	149.9	159.7	169.5	180.3	191.9	204.6
145°	130.9	132.0	135.3	139.9	146.3	153.5	162.2	171.3	180.9	191.2	201.9
147.5°	136.9	137.1	140.2	144.9	150.1	156.7	164.9	172.8	181.3	190.0	199.4
150°	140.5	140.9	143.5	147.6	152.6	158.9	166.3	173.5	181.3	189.2	197.6
152.5°	144.0	144.1	146.8	150.5	155.0	160.8	167.3	174.1	180.7	187.8	195.4
155°	148.9	149.2	151.3	154.6	158.3	163.2	168.9	174.6	179.9	185.9	192.2
157.5°	153.6	153.6	155.5	158.1	161.3	165.2	170.0	174.6	179.0	183.8	189.0
160°	156.6	156.6	157.9	160.2	162.9	166.5	170.6	174.6	178.2	182.2	186.5
162.5°	159.2	159.0	160.0	162.1	164.5	167.4	171.1	174.6	177.4	180.6	184.5
165°	162.2	162.2	162.9	164.6	166.3	168.2	171.3	173.9	175.9	178.2	180.9
167.5°	165.2	164.9	165.2	166.5	167.4	169.0	171.2	173.1	174.3	175.8	177.7
170°	166.5	166.3	166.5	167.6	168.2	169.2	170.9	172.6	173.2	174.2	175.6
172.5°	167.9	167.6	167.6	168.3	168.7	169.5	170.6	172.0	172.2	172.6	173.7
175°	169.2	168.9	168.9	169.2	169.6	169.6	170.2	171.3	170.9	170.9	171.5
177.5°	169.8	169.6	169.3	169.6	169.6	169.6	169.8	170.3	169.8	169.8	170.1
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332870-830

CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	6.0	6.0	6.0	6.0	6.1	6.3	6.3	6.4
90°	6.0	6.3	6.7	6.7	7.0	7.4	7.0	7.0
92.5°	65.4	49.2	39.2	32.5	28.6	26.8	25.6	25.6
95°	246.9	195.2	150.5	118.3	101.9	91.6	85.6	81.2
97.5°	364.7	345.5	312.9	278.1	254.2	234.2	224.2	217.3
100°	401.7	408.4	392.1	367.4	338.5	318.1	308.1	305.5
102.5°	399.9	432.9	437.6	427.3	409.6	394.9	384.4	382.2
105°	373.1	430.7	463.7	477.4	478.1	475.3	470.7	468.7
107.5°	335.1	396.4	442.8	472.6	489.0	496.6	499.9	500.8
110°	312.2	369.8	418.1	454.7	478.3	492.4	498.3	501.3



TEST NUMBER: P332870-830
CATALOG NUMBER: SA4XXRDIP-C350D365U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	295.3	346.3	391.9	428.6	455.4	472.4	480.8	485.6
115°	278.5	319.4	358.4	390.4	416.7	436.7	447.4	450.1
117.5°	270.2	304.2	334.8	361.9	384.4	401.1	411.9	414.0
120°	266.5	297.5	324.1	347.8	366.7	381.4	390.1	393.8
122.5°	263.3	293.2	317.4	338.2	354.2	366.7	374.1	377.8
125°	257.9	286.4	309.4	327.8	341.1	350.8	357.1	359.1
127.5°	251.2	278.5	301.5	318.9	332.2	340.8	346.2	348.2
130°	245.8	272.2	294.8	312.5	326.1	334.4	339.8	341.8
132.5°	240.3	264.9	287.1	304.7	318.1	327.5	332.6	334.6
135°	232.5	254.2	274.5	291.2	304.4	313.8	319.1	321.1
137.5°	225.6	243.8	261.0	276.0	288.5	297.7	302.1	304.4
140°	221.5	237.1	252.1	266.2	277.9	285.1	289.8	292.5
142.5°	217.8	231.6	244.4	256.6	266.9	273.7	277.9	279.7
145°	212.5	223.9	233.8	243.2	251.5	257.1	260.5	262.1
147.5°	208.2	217.2	225.2	232.5	238.7	243.6	246.0	246.7
150°	205.6	213.2	219.9	225.8	231.2	235.5	237.5	237.8
152.5°	202.6	209.2	215.4	220.3	224.8	228.3	229.5	229.9
155°	198.2	203.5	208.5	212.5	215.8	218.5	219.5	219.5
157.5°	193.5	197.9	202.2	205.4	207.8	209.9	210.5	210.5
160°	190.6	194.2	197.8	200.6	202.6	204.5	204.9	204.9
162.5°	187.7	190.8	193.6	196.0	197.5	199.4	199.8	199.5
165°	183.5	185.6	187.8	189.5	190.9	192.2	191.9	191.5
167.5°	179.6	181.2	183.0	184.0	184.6	185.6	185.5	185.2
170°	177.2	178.2	179.6	180.6	181.3	181.5	181.3	181.3
172.5°	175.1	175.8	176.6	177.4	177.8	178.0	177.8	177.2
175°	172.2	172.6	173.2	173.2	173.2	173.9	173.2	172.6
177.5°	170.3	170.6	170.6	170.9	170.6	170.9	170.3	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6

(END OF REPORT)