

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332975-840

Luminaire Tested: **SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332975-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8114.9 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332975-840
CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	29	25	45	34	28	24	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13988	13988	13988	13988
5°	16226	14030	12400	14030
10°	19194	13969	11068	13969
15°	22172	13840	9510	13840
20°	24686	13662	8600	13662
25°	25483	13488	7985	13488
30°	22309	13276	7614	13276
35°	17366	12962	7389	12962
40°	13022	12603	7268	12603
45°	10282	12028	7205	12028
50°	8681	11362	6997	11362
55°	7567	10632	6622	10632
60°	6807	9875	5861	9875
65°	6002	9054	5041	9054
70°	5403	8207	4548	8207
75°	4529	7274	3877	7274
80°	3831	6197	3636	6197
85°	3233	4844	3233	4844



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	2.1
10°-20°	506.4	6.2
20°-30°	792.1	9.8
30°-40°	880.6	10.9
40°-50°	781.3	9.6
50°-60°	608.8	7.5
60°-70°	398.6	4.9
70°-80°	196.0	2.4
80°-90°	51.2	0.6
90°-100°	370.6	4.6
100°-110°	771.4	9.5
110°-120°	690.9	8.5
120°-130°	581.2	7.2
130°-140°	484.6	6.0
140°-150°	370.2	4.6
150°-160°	260.2	3.2
160°-170°	153.1	1.9
170°-180°	49.8	0.6
0°-30°	1466.4	18.1
0°-40°	2347.0	28.9
0°-60°	3737.0	46.1
0°-90°	4382.8	54.0
90°-120°	1833.0	22.6
90°-150°	3269.0	40.3
90°-180°	3732.0	46.0
0°-180°	8114.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1733	1733	1733	1733	1733	
5°	2002	1731	1530	1731	2002	203
15°	2653	1656	1138	1656	2653	754
25°	2861	1514	896	1514	2861	1269
35°	1762	1315	750	1315	1762	1105
45°	901	1054	631	1054	901	713
55°	538	755	470	755	538	489
65°	314	474	264	474	314	316
75°	145	233	124	233	145	160
85°	35	52	35	52	35	40
90°	21	1	21	1	21	19
95°	246	33	246	33	246	382
105°	1418	118	1418	118	1418	1402
115°	1362	208	1362	208	1362	1352
125°	1087	289	1087	289	1087	988
135°	972	344	972	344	972	750
145°	794	396	794	396	794	503
155°	664	451	664	451	664	310
165°	580	491	580	491	580	166
175°	522	512	522	512	522	51
180°	513	513	513	513	513	



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1827.7	1832.7	1827.7	1827.1	1821.6	1819.9	1817.7	1810.4	1797.0	1789.2	1790.8
5°	2002.3	2019.6	2009.9	2008.5	1993.2	1977.8	1968.0	1945.7	1922.0	1905.9	1892.6
7.5°	2204.1	2214.1	2208.1	2198.3	2173.4	2159.3	2136.7	2107.2	2064.7	2032.1	2002.4
10°	2341.5	2349.9	2347.1	2329.0	2310.8	2273.8	2252.8	2211.7	2157.9	2115.4	2075.5
12.5°	2476.7	2485.6	2461.0	2461.8	2427.5	2398.3	2365.1	2313.3	2251.2	2196.3	2146.5
15°	2652.9	2641.7	2641.7	2627.8	2589.3	2548.9	2514.7	2460.2	2382.0	2316.3	2247.3
17.5°	2790.9	2794.7	2789.0	2756.0	2725.9	2684.0	2621.3	2557.8	2485.2	2397.1	2326.4
20°	2873.5	2873.5	2867.2	2844.9	2805.8	2761.1	2693.4	2624.2	2532.1	2443.5	2363.9
22.5°	2907.0	2909.2	2901.8	2883.4	2848.2	2804.6	2746.9	2676.7	2581.8	2481.9	2383.4
25°	2860.9	2874.2	2875.6	2870.6	2860.2	2833.7	2784.1	2712.2	2627.1	2518.8	2412.7
27.5°	2626.7	2643.4	2658.1	2682.2	2714.3	2731.1	2733.3	2696.7	2622.4	2518.3	2411.5
30°	2393.2	2407.1	2452.6	2511.8	2557.9	2599.8	2636.2	2645.8	2604.0	2510.4	2398.0
32.5°	2134.0	2153.0	2198.4	2262.2	2338.9	2409.9	2491.4	2533.0	2531.9	2475.8	2371.8
35°	1762.1	1776.0	1818.0	1884.9	1977.1	2082.5	2211.7	2312.2	2380.6	2375.7	2312.2
37.5°	1421.1	1436.8	1479.1	1534.8	1624.2	1754.6	1879.7	2018.1	2144.7	2215.7	2194.4
40°	1235.7	1236.4	1277.6	1334.8	1418.6	1532.4	1668.5	1822.1	1963.1	2078.3	2100.6
42.5°	1089.3	1089.4	1116.7	1178.4	1238.8	1345.8	1475.8	1628.3	1793.3	1926.4	1985.6
45°	900.6	906.9	929.2	966.2	1013.7	1104.4	1208.4	1350.2	1535.2	1692.9	1791.4
47.5°	762.7	771.8	786.1	816.3	854.0	914.5	1000.6	1127.9	1278.4	1452.0	1592.1
50°	691.2	692.6	710.6	727.4	760.2	808.4	883.8	990.0	1128.1	1295.1	1450.7
52.5°	629.8	629.4	640.4	661.6	688.2	725.8	786.7	883.2	1005.8	1155.4	1316.1
55°	537.6	541.1	549.5	566.1	586.4	613.0	661.2	733.8	830.1	957.9	1103.8
57.5°	467.5	469.3	475.8	482.9	501.5	520.8	556.9	607.3	688.6	793.2	929.2
60°	421.6	422.3	424.4	434.9	449.6	467.8	492.2	534.7	603.2	698.8	806.4
62.5°	377.0	378.2	381.4	389.1	400.4	413.0	438.6	472.8	529.5	611.2	708.0
65°	314.2	314.9	319.7	322.6	331.6	342.7	361.6	384.7	423.7	492.2	565.5
67.5°	262.5	262.5	262.8	266.5	272.9	280.2	291.5	309.9	339.4	381.4	446.1
70°	228.9	228.9	230.4	232.5	236.0	242.3	248.5	262.5	284.2	318.3	367.9
72.5°	197.7	198.2	199.7	200.1	201.9	207.0	211.7	220.7	236.7	262.5	302.6
75°	145.2	147.3	150.8	153.6	157.0	156.4	161.3	166.8	171.8	187.1	210.2
77.5°	108.1	106.9	107.3	109.8	110.2	110.9	114.3	118.7	122.3	129.6	137.8
80°	82.4	82.4	84.4	85.1	84.4	85.1	88.7	90.8	92.2	94.9	102.6
82.5°	62.3	63.4	62.7	63.4	63.8	64.5	67.5	67.9	69.3	70.4	73.6
85°	34.9	35.6	36.3	34.9	34.9	34.9	36.3	37.0	38.4	37.7	39.1
87.5°	16.6	16.0	16.8	16.6	16.9	16.4	16.7	17.6	16.3	17.1	16.7
90°	21.2	21.2	22.2	21.2	20.2	20.2	19.2	18.2	17.2	18.2	16.2
92.5°	77.7	77.7	81.1	86.5	98.4	118.6	149.1	198.0	266.4	319.8	279.8
95°	246.0	259.1	277.2	308.5	357.9	455.7	590.8	747.0	844.9	821.6	620.1
97.5°	657.5	678.5	708.7	769.4	841.8	947.1	1045.6	1103.8	1061.4	865.4	580.3
100°	924.5	932.5	962.8	1024.3	1112.0	1186.6	1236.0	1215.9	1068.6	810.5	526.2
102.5°	1156.8	1163.3	1195.1	1239.6	1293.4	1324.5	1310.2	1210.2	1008.1	742.0	490.0
105°	1418.5	1424.5	1438.7	1446.7	1444.7	1403.3	1303.5	1129.1	898.3	661.4	458.7
107.5°	1515.7	1513.1	1503.0	1480.0	1430.2	1340.3	1199.7	1014.0	809.5	616.2	453.0
110°	1517.3	1508.2	1490.1	1447.7	1376.1	1265.3	1119.0	944.6	765.2	600.9	454.6



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1469.7	1455.0	1429.6	1378.4	1297.1	1186.2	1048.0	893.8	740.2	593.6	459.5
115°	1362.0	1353.9	1321.7	1261.2	1181.5	1084.8	966.8	842.8	716.8	589.8	468.8
117.5°	1252.9	1246.7	1214.1	1163.3	1095.3	1013.2	920.5	817.8	706.3	588.8	478.7
120°	1191.6	1180.5	1154.4	1109.9	1052.5	981.0	900.3	806.5	700.6	588.8	485.9
122.5°	1143.3	1132.2	1109.9	1072.1	1023.5	960.8	887.4	796.9	694.2	587.9	493.2
125°	1086.8	1080.8	1061.6	1032.4	992.0	936.5	867.0	780.3	683.6	586.7	504.1
127.5°	1053.7	1047.6	1031.6	1005.5	965.0	912.4	843.0	760.1	669.2	584.5	512.7
130°	1034.4	1028.3	1012.2	986.9	945.6	892.2	823.6	744.1	660.4	583.7	519.2
132.5°	1012.6	1006.5	991.2	962.8	922.3	868.8	801.9	727.1	652.3	582.9	524.8
135°	971.9	965.8	949.7	921.5	881.1	830.7	769.2	703.7	640.2	581.7	533.3
137.5°	921.5	914.2	900.9	873.0	835.4	789.8	738.0	682.6	629.7	581.5	538.4
140°	885.1	877.1	863.0	840.8	805.5	763.2	717.8	670.4	624.1	580.7	542.4
142.5°	846.5	840.8	828.3	807.7	776.5	739.8	700.8	659.1	619.2	580.7	545.6
145°	793.5	788.4	778.3	761.1	736.0	707.7	677.5	643.2	611.0	578.7	547.4
147.5°	746.4	744.7	737.0	722.3	703.7	681.6	657.3	630.1	603.5	575.0	548.5
150°	719.8	718.8	712.8	699.6	683.6	665.4	645.2	622.1	597.8	572.6	548.5
152.5°	695.6	694.6	690.9	680.3	666.6	651.7	633.1	613.2	591.4	568.6	546.8
155°	664.4	664.4	661.4	653.3	643.2	631.1	616.0	599.9	581.7	562.6	544.4
157.5°	636.9	636.9	635.1	629.0	621.5	611.8	599.1	585.5	571.8	556.3	541.8
160°	620.1	620.1	619.0	613.0	606.9	598.8	587.7	576.6	564.6	551.5	539.4
162.5°	603.9	604.7	603.7	597.6	593.2	585.9	577.2	567.7	558.2	546.6	536.9
165°	579.7	580.7	581.7	577.6	573.6	568.6	561.6	555.5	547.4	539.4	532.3
167.5°	560.6	561.4	561.6	559.0	556.9	553.9	548.3	543.6	537.8	532.1	527.5
170°	548.5	548.5	549.5	548.5	546.4	543.4	539.4	536.3	531.3	527.3	524.2
172.5°	536.3	538.0	539.0	538.0	536.7	534.5	532.1	529.9	525.6	522.4	521.0
175°	522.2	524.2	526.2	524.2	524.2	524.2	522.2	521.2	519.2	517.2	517.2
177.5°	513.9	515.5	517.2	516.3	517.2	516.3	516.3	515.5	514.7	513.9	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1785.2	1777.5	1773.5	1764.5	1753.9	1748.4	1743.3	1736.1	1726.6	1716.6	1709.3
5°	1875.8	1859.1	1838.2	1813.0	1790.7	1769.1	1750.2	1731.3	1709.7	1687.4	1665.1
7.5°	1968.8	1935.9	1900.3	1859.1	1819.1	1782.6	1749.1	1717.0	1680.6	1648.1	1618.5
10°	2033.7	1988.9	1939.3	1887.0	1834.6	1789.3	1744.6	1704.1	1659.4	1619.6	1586.1
12.5°	2086.2	2033.7	1974.0	1908.8	1845.8	1791.0	1739.6	1686.8	1636.0	1592.9	1548.1
15°	2173.2	2101.3	2021.0	1942.9	1861.2	1786.5	1717.4	1656.0	1598.0	1537.3	1494.7
17.5°	2233.1	2147.9	2050.2	1956.3	1859.8	1771.7	1691.9	1618.8	1552.0	1490.0	1439.3
20°	2268.9	2174.6	2066.5	1959.6	1851.4	1757.2	1671.3	1590.3	1521.3	1454.2	1401.8
22.5°	2289.0	2184.7	2066.5	1954.6	1842.5	1740.4	1646.2	1561.9	1486.6	1419.6	1361.6
25°	2295.4	2183.7	2063.0	1934.5	1811.6	1703.4	1605.7	1514.2	1430.5	1363.4	1302.0
27.5°	2286.5	2155.0	2031.2	1899.5	1772.7	1658.6	1556.0	1460.0	1376.0	1304.1	1241.1
30°	2273.1	2132.0	1999.4	1862.6	1734.1	1624.6	1516.3	1424.2	1336.9	1262.2	1198.7
32.5°	2244.0	2104.2	1961.5	1821.3	1691.1	1578.2	1475.5	1382.8	1297.3	1220.9	1153.5
35°	2186.6	2044.8	1889.9	1746.1	1618.2	1501.0	1404.6	1315.2	1233.6	1152.0	1080.7
37.5°	2110.7	1965.9	1811.8	1654.3	1526.4	1415.6	1327.3	1243.3	1163.7	1089.0	1010.2
40°	2039.2	1907.2	1748.1	1591.7	1460.5	1353.6	1272.0	1195.9	1115.6	1041.6	962.7
42.5°	1952.7	1840.3	1679.4	1522.5	1392.9	1290.0	1213.9	1139.4	1066.4	994.7	912.4
45°	1808.2	1722.9	1572.2	1421.4	1290.8	1188.9	1119.1	1053.5	989.3	920.8	843.3
47.5°	1642.5	1584.9	1454.7	1300.3	1179.5	1087.8	1020.4	966.7	912.4	844.0	776.1
50°	1527.5	1490.5	1364.8	1223.9	1108.6	1024.1	955.0	904.7	859.4	793.8	733.1
52.5°	1404.6	1384.9	1278.8	1144.0	1032.7	949.9	890.8	845.6	799.6	745.2	688.3
55°	1217.5	1228.0	1137.9	1021.4	916.7	846.9	793.0	755.4	716.3	670.2	626.2
57.5°	1026.2	1064.5	1004.0	901.7	803.5	739.0	698.5	666.8	634.0	595.8	558.3
60°	911.7	943.8	909.7	819.6	733.8	673.7	636.0	611.6	578.8	543.8	515.2
62.5°	800.0	834.4	814.2	741.4	661.7	610.1	576.8	554.0	529.6	499.2	469.4
65°	659.7	682.1	672.3	622.1	565.5	521.5	490.8	474.0	451.7	429.4	402.8
67.5°	505.3	548.5	542.7	516.0	467.2	432.8	412.7	397.9	377.6	360.9	343.0
70°	415.4	455.1	454.4	432.8	406.3	374.2	360.2	347.7	329.5	313.5	298.8
72.5°	340.0	376.5	381.8	365.3	347.1	322.9	309.4	300.7	283.2	272.2	260.2
75°	238.0	264.6	271.6	271.6	263.2	250.6	238.7	233.2	220.7	210.9	203.9
77.5°	156.1	172.9	183.8	186.2	187.5	183.3	173.6	169.7	160.0	156.5	149.9
80°	110.3	121.5	134.0	138.3	141.7	140.4	136.1	133.3	124.3	120.8	118.0
82.5°	76.2	82.4	92.7	101.9	101.0	104.6	101.0	98.8	91.9	90.6	87.9
85°	39.8	40.5	41.9	48.2	51.7	53.0	53.7	52.3	50.3	50.3	45.3
87.5°	16.3	15.7	15.6	15.6	16.0	18.0	19.0	19.2	17.9	16.9	15.3
90°	14.1	14.1	8.1	8.1	7.1	6.1	3.0	1.0	3.0	6.1	7.1
92.5°	203.7	125.4	74.2	53.2	38.5	26.3	16.8	11.5	16.8	26.3	38.5
95°	379.1	213.7	126.0	83.7	59.5	46.4	36.3	33.2	36.3	46.4	59.5
97.5°	340.7	204.3	136.7	101.2	80.5	68.4	59.7	59.7	59.7	68.4	80.5
100°	320.6	206.7	147.2	114.9	95.7	83.7	76.6	76.6	76.6	83.7	95.7
102.5°	315.0	214.7	160.9	130.3	111.9	100.6	94.3	92.7	94.3	100.6	111.9
105°	317.6	233.9	185.5	156.2	138.1	126.0	121.0	118.0	121.0	126.0	138.1
107.5°	332.4	256.3	211.9	183.1	165.7	152.8	147.8	145.8	147.8	152.8	165.7
110°	343.8	273.2	228.8	201.7	183.5	171.4	166.3	164.3	166.3	171.4	183.5



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.9	289.3	246.6	219.3	201.3	190.0	184.1	182.1	184.1	190.0	201.3
115°	375.1	314.6	274.2	247.0	227.8	217.7	210.7	207.7	210.7	217.7	227.8
117.5°	394.6	338.9	300.6	272.4	254.5	243.4	237.1	234.3	237.1	243.4	254.5
120°	408.3	355.9	317.6	289.3	272.2	261.2	254.1	252.1	254.1	261.2	272.2
122.5°	421.2	372.0	333.7	306.3	287.5	277.2	270.1	268.2	270.1	277.2	287.5
125°	440.6	394.2	357.9	329.6	310.5	299.4	293.4	289.3	293.4	299.4	310.5
127.5°	457.3	414.8	379.7	351.2	331.2	318.6	311.3	308.1	311.3	318.6	331.2
130°	467.8	428.5	394.2	365.0	345.8	330.6	322.7	318.6	322.7	330.6	345.8
132.5°	478.3	439.8	405.5	377.9	357.1	342.7	332.2	329.0	332.2	342.7	357.1
135°	492.0	455.7	422.4	396.2	375.1	357.9	347.8	343.8	347.8	357.9	375.1
137.5°	501.7	467.8	436.8	411.7	389.7	373.4	362.3	358.5	362.3	373.4	389.7
140°	508.1	475.8	445.7	421.4	400.2	383.1	372.0	369.0	372.0	383.1	400.2
142.5°	512.9	483.1	453.6	430.3	409.9	393.5	383.3	380.3	383.3	393.5	409.9
145°	518.2	491.0	464.7	442.6	423.4	409.3	399.2	396.2	399.2	409.3	423.4
147.5°	522.8	499.1	474.4	454.4	438.6	424.0	415.2	414.1	415.2	424.0	438.6
150°	525.2	503.1	480.9	461.7	446.7	434.5	426.5	425.5	426.5	434.5	446.7
152.5°	526.8	506.3	486.6	469.0	455.4	444.2	436.2	436.0	436.2	444.2	455.4
155°	528.3	511.1	494.0	478.9	467.8	457.7	451.6	450.6	451.6	457.7	467.8
157.5°	528.3	514.5	500.1	488.2	478.5	470.6	464.9	464.9	464.9	470.6	478.5
160°	528.3	516.1	504.1	493.0	484.9	477.9	473.8	473.8	473.8	477.9	484.9
162.5°	528.3	517.8	506.5	497.9	490.6	484.3	481.1	481.9	481.1	484.3	490.6
165°	526.2	518.2	509.1	503.1	498.1	493.0	491.0	491.0	491.0	493.0	498.1
167.5°	523.8	518.0	511.3	506.8	503.9	500.1	499.1	500.1	499.1	500.1	503.9
170°	522.2	517.2	512.1	509.1	507.2	504.1	503.1	504.1	503.1	504.1	507.2
172.5°	520.6	516.3	512.9	510.7	509.5	507.3	507.2	508.1	507.2	507.3	509.5
175°	518.2	515.1	513.1	513.1	512.1	511.1	511.1	512.1	511.1	511.1	512.1
177.5°	515.5	513.9	513.1	513.1	513.1	512.3	513.1	513.9	513.1	512.3	513.1
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1701.4	1695.9	1688.6	1680.2	1670.2	1661.2	1657.4	1660.7	1662.3	1657.9	1657.4
5°	1649.7	1632.2	1618.2	1597.3	1580.5	1566.6	1556.8	1552.7	1554.0	1542.9	1540.0
7.5°	1591.4	1570.7	1547.9	1523.0	1499.9	1479.4	1468.5	1462.7	1450.9	1445.8	1437.3
10°	1554.0	1526.1	1503.8	1474.4	1447.9	1423.5	1411.6	1401.8	1390.0	1384.4	1372.5
12.5°	1515.5	1483.1	1458.5	1428.1	1401.0	1371.5	1360.2	1342.1	1323.5	1311.8	1296.6
15°	1461.2	1422.1	1392.1	1355.7	1323.6	1290.1	1260.1	1226.6	1214.1	1187.5	1172.2
17.5°	1397.7	1358.0	1320.8	1272.1	1222.5	1180.9	1148.9	1116.8	1097.6	1080.7	1072.9
20°	1355.7	1319.5	1267.8	1211.2	1156.1	1110.0	1084.2	1063.3	1042.3	1030.5	1022.1
22.5°	1316.1	1269.7	1209.7	1148.7	1093.6	1057.5	1035.6	1014.1	997.0	985.7	974.6
25°	1249.6	1188.9	1125.4	1055.6	1017.8	986.4	962.7	945.2	934.8	920.1	914.5
27.5°	1181.3	1107.8	1037.7	990.8	951.5	922.8	902.1	889.0	875.8	866.4	859.1
30°	1128.8	1054.2	991.4	946.6	906.9	883.1	866.4	851.0	840.5	832.8	827.3
32.5°	1076.9	1002.2	949.5	901.4	870.0	846.9	829.0	817.5	809.3	799.3	796.0
35°	1001.8	935.4	889.4	846.2	814.1	793.0	779.1	767.2	760.2	757.5	755.4
37.5°	929.6	875.4	825.8	790.3	761.6	745.2	728.7	722.9	718.1	713.1	715.3
40°	883.8	832.8	788.9	751.1	728.1	710.0	700.2	693.3	689.0	689.0	689.0
42.5°	844.1	794.4	751.4	717.7	694.6	679.2	668.4	662.5	661.2	660.6	663.9
45°	782.6	736.5	693.3	665.3	645.8	630.4	624.1	619.2	619.2	622.1	622.7
47.5°	721.5	678.4	643.7	612.4	594.5	584.9	579.5	576.9	577.2	580.0	583.2
50°	684.2	641.6	607.3	579.5	562.7	553.6	548.8	547.3	548.8	548.8	553.6
52.5°	643.4	605.3	571.6	548.2	529.2	520.7	518.0	516.0	516.8	519.2	521.2
55°	583.6	549.5	517.4	494.9	481.0	475.4	469.2	469.8	468.5	469.8	469.8
57.5°	523.7	493.0	463.1	445.5	433.1	425.1	418.2	420.1	418.1	417.8	416.7
60°	485.2	451.7	428.0	411.9	397.9	390.9	384.7	386.1	384.0	382.5	379.8
62.5°	443.3	415.4	392.7	377.3	366.1	358.0	351.7	350.3	345.5	340.7	334.6
65°	382.5	359.5	339.3	324.7	314.2	307.9	303.0	298.8	288.3	277.1	271.6
67.5°	323.6	306.9	288.0	275.6	267.1	258.8	249.5	242.4	232.6	226.5	223.0
70°	285.5	269.4	253.4	241.6	232.5	224.8	214.3	209.4	202.5	199.7	196.2
72.5°	249.2	234.3	219.3	208.6	198.9	193.0	184.7	179.9	176.7	175.6	172.2
75°	194.1	182.2	171.1	161.3	153.6	149.4	145.9	142.4	141.0	134.7	131.3
77.5°	141.6	133.8	126.7	119.8	114.3	111.6	104.8	100.8	98.5	95.5	94.8
80°	110.3	104.7	97.8	93.5	85.8	83.1	80.3	79.6	78.9	78.2	77.5
82.5°	82.9	77.4	70.4	67.9	65.7	64.1	62.4	61.7	61.0	61.4	61.3
85°	41.9	39.1	39.1	38.4	37.7	37.0	36.3	36.3	35.6	36.3	35.6
87.5°	15.6	15.0	16.3	15.1	16.1	16.5	15.8	16.0	16.7	15.8	15.8
90°	8.1	8.1	14.1	14.1	16.2	18.2	17.2	18.2	19.2	20.2	20.2
92.5°	53.2	74.2	125.4	203.7	279.8	319.8	266.4	198.0	149.1	118.6	98.4
95°	83.7	126.0	213.7	379.1	620.1	821.6	844.9	747.0	590.8	455.7	357.9
97.5°	101.2	136.7	204.3	340.7	580.3	865.4	1061.4	1103.8	1045.6	947.1	841.8
100°	114.9	147.2	206.7	320.6	526.2	810.5	1068.6	1215.9	1236.0	1186.6	1112.0
102.5°	130.3	160.9	214.7	315.0	490.0	742.0	1008.1	1210.2	1310.2	1324.5	1293.4
105°	156.2	185.5	233.9	317.6	458.7	661.4	898.3	1129.1	1303.5	1403.3	1444.7
107.5°	183.1	211.9	256.3	332.4	453.0	616.2	809.5	1014.0	1199.7	1340.3	1430.2
110°	201.7	228.8	273.2	343.8	454.6	600.9	765.2	944.6	1119.0	1265.3	1376.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.3	246.6	289.3	355.9	459.5	593.6	740.2	893.8	1048.0	1186.2	1297.1
115°	247.0	274.2	314.6	375.1	468.8	589.8	716.8	842.8	966.8	1084.8	1181.5
117.5°	272.4	300.6	338.9	394.6	478.7	588.8	706.3	817.8	920.5	1013.2	1095.3
120°	289.3	317.6	355.9	408.3	485.9	588.8	700.6	806.5	900.3	981.0	1052.5
122.5°	306.3	333.7	372.0	421.2	493.2	587.9	694.2	796.9	887.4	960.8	1023.5
125°	329.6	357.9	394.2	440.6	504.1	586.7	683.6	780.3	867.0	936.5	992.0
127.5°	351.2	379.7	414.8	457.3	512.7	584.5	669.2	760.1	843.0	912.4	965.0
130°	365.0	394.2	428.5	467.8	519.2	583.7	660.4	744.1	823.6	892.2	945.6
132.5°	377.9	405.5	439.8	478.3	524.8	582.9	652.3	727.1	801.9	868.8	922.3
135°	396.2	422.4	455.7	492.0	533.3	581.7	640.2	703.7	769.2	830.7	881.1
137.5°	411.7	436.8	467.8	501.7	538.4	581.5	629.7	682.6	738.0	789.8	835.4
140°	421.4	445.7	475.8	508.1	542.4	580.7	624.1	670.4	717.8	763.2	805.5
142.5°	430.3	453.6	483.1	512.9	545.6	580.7	619.2	659.1	700.8	739.8	776.5
145°	442.6	464.7	491.0	518.2	547.4	578.7	611.0	643.2	677.5	707.7	736.0
147.5°	454.4	474.4	499.1	522.8	548.5	575.0	603.5	630.1	657.3	681.6	703.7
150°	461.7	480.9	503.1	525.2	548.5	572.6	597.8	622.1	645.2	665.4	683.6
152.5°	469.0	486.6	506.3	526.8	546.8	568.6	591.4	613.2	633.1	651.7	666.6
155°	478.9	494.0	511.1	528.3	544.4	562.6	581.7	599.9	616.0	631.1	643.2
157.5°	488.2	500.1	514.5	528.3	541.8	556.3	571.8	585.5	599.1	611.8	621.5
160°	493.0	504.1	516.1	528.3	539.4	551.5	564.6	576.6	587.7	598.8	606.9
162.5°	497.9	506.5	517.8	528.3	536.9	546.6	558.2	567.7	577.2	585.9	593.2
165°	503.1	509.1	518.2	526.2	532.3	539.4	547.4	555.5	561.6	568.6	573.6
167.5°	506.8	511.3	518.0	523.8	527.5	532.1	537.8	543.6	548.3	553.9	556.9
170°	509.1	512.1	517.2	522.2	524.2	527.3	531.3	536.3	539.4	543.4	546.4
172.5°	510.7	512.9	516.3	520.6	521.0	522.4	525.6	529.9	532.1	534.5	536.7
175°	513.1	513.1	515.1	518.2	517.2	517.2	519.2	521.2	522.2	524.2	524.2
177.5°	513.1	513.1	513.9	515.5	513.9	513.9	514.7	515.5	516.3	516.3	517.2
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1654.0	1655.1	1651.2	1650.1	1651.2	1655.1	1654.0	1657.4	1657.9	1662.3	1660.7
5°	1534.5	1533.1	1529.5	1530.2	1529.5	1533.1	1534.5	1540.0	1542.9	1554.0	1552.7
7.5°	1432.3	1426.8	1428.4	1422.8	1428.4	1426.8	1432.3	1437.3	1445.8	1450.9	1462.7
10°	1369.7	1362.0	1355.7	1350.2	1355.7	1362.0	1369.7	1372.5	1384.4	1390.0	1401.8
12.5°	1284.2	1277.7	1269.2	1270.9	1269.2	1277.7	1284.2	1296.6	1311.8	1323.5	1342.1
15°	1163.1	1152.6	1135.9	1137.9	1135.9	1152.6	1163.1	1172.2	1187.5	1214.1	1226.6
17.5°	1060.5	1060.6	1052.9	1054.7	1052.9	1060.6	1060.5	1072.9	1080.7	1097.6	1116.8
20°	1007.4	1002.5	1003.2	1001.1	1003.2	1002.5	1007.4	1022.1	1030.5	1042.3	1063.3
22.5°	970.6	964.5	959.7	955.3	959.7	964.5	970.6	974.6	985.7	997.0	1014.1
25°	908.3	904.0	897.8	896.4	897.8	904.0	908.3	914.5	920.1	934.8	945.2
27.5°	853.5	852.7	850.2	847.0	850.2	852.7	853.5	859.1	866.4	875.8	889.0
30°	821.7	820.3	818.9	816.8	818.9	820.3	821.7	827.3	832.8	840.5	851.0
32.5°	793.2	792.3	790.9	791.1	790.9	792.3	793.2	796.0	799.3	809.3	817.5
35°	752.6	751.8	750.5	749.8	750.5	751.8	752.6	755.4	757.5	760.2	767.2
37.5°	714.6	716.4	715.6	715.4	715.6	716.4	714.6	715.3	713.1	718.1	722.9
40°	688.3	689.0	690.4	689.7	690.4	689.0	688.3	689.0	689.0	689.0	693.3
42.5°	666.6	666.7	668.6	666.3	668.6	666.7	666.6	663.9	660.6	661.2	662.5
45°	627.6	631.8	631.1	631.1	631.1	631.8	627.6	622.7	622.1	619.2	619.2
47.5°	585.0	588.7	589.7	589.5	589.7	588.7	585.0	583.2	580.0	577.2	576.9
50°	557.1	555.7	557.8	557.1	557.8	555.7	557.1	553.6	548.8	548.8	547.3
52.5°	523.0	523.3	523.2	522.5	523.2	523.3	523.0	521.2	519.2	516.8	516.0
55°	470.5	471.2	469.8	470.5	469.8	471.2	470.5	469.8	469.8	468.5	469.8
57.5°	413.5	410.2	411.6	409.9	411.6	410.2	413.5	416.7	417.8	418.1	420.1
60°	372.8	367.2	365.8	363.0	365.8	367.2	372.8	379.8	382.5	384.0	386.1
62.5°	327.0	323.1	318.3	320.5	318.3	323.1	327.0	334.6	340.7	345.5	350.3
65°	266.0	263.2	261.1	263.9	261.1	263.2	266.0	271.6	277.1	288.3	298.8
67.5°	220.2	218.6	218.6	217.2	218.6	218.6	220.2	223.0	226.5	232.6	242.4
70°	196.2	194.1	194.1	192.7	194.1	194.1	196.2	196.2	199.7	202.5	209.4
72.5°	171.6	169.5	170.1	169.3	170.1	169.5	171.6	172.2	175.6	176.7	179.9
75°	127.0	123.6	123.6	124.3	123.6	123.6	127.0	131.3	134.7	141.0	142.4
77.5°	94.8	94.1	95.1	93.8	95.1	94.1	94.8	94.8	95.5	98.5	100.8
80°	77.5	76.7	76.1	78.2	76.1	76.7	77.5	77.5	78.2	78.9	79.6
82.5°	60.2	60.1	59.9	62.5	59.9	60.1	60.2	61.3	61.4	61.0	61.7
85°	36.3	34.9	36.3	34.9	36.3	34.9	36.3	35.6	36.3	35.6	36.3
87.5°	17.1	16.8	16.0	16.6	16.0	16.8	17.1	15.8	15.8	16.7	16.0
90°	21.2	22.2	21.2	21.2	21.2	22.2	21.2	20.2	20.2	19.2	18.2
92.5°	86.5	81.1	77.7	77.7	77.7	81.1	86.5	98.4	118.6	149.1	198.0
95°	308.5	277.2	259.1	246.0	259.1	277.2	308.5	357.9	455.7	590.8	747.0
97.5°	769.4	708.7	678.5	657.5	678.5	708.7	769.4	841.8	947.1	1045.6	1103.8
100°	1024.3	962.8	932.5	924.5	932.5	962.8	1024.3	1112.0	1186.6	1236.0	1215.9
102.5°	1239.6	1195.1	1163.3	1156.8	1163.3	1195.1	1239.6	1293.4	1324.5	1310.2	1210.2
105°	1446.7	1438.7	1424.5	1418.5	1424.5	1438.7	1446.7	1444.7	1403.3	1303.5	1129.1
107.5°	1480.0	1503.0	1513.1	1515.7	1513.1	1503.0	1480.0	1430.2	1340.3	1199.7	1014.0
110°	1447.7	1490.1	1508.2	1517.3	1508.2	1490.1	1447.7	1376.1	1265.3	1119.0	944.6



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1378.4	1429.6	1455.0	1469.7	1455.0	1429.6	1378.4	1297.1	1186.2	1048.0	893.8
115°	1261.2	1321.7	1353.9	1362.0	1353.9	1321.7	1261.2	1181.5	1084.8	966.8	842.8
117.5°	1163.3	1214.1	1246.7	1252.9	1246.7	1214.1	1163.3	1095.3	1013.2	920.5	817.8
120°	1109.9	1154.4	1180.5	1191.6	1180.5	1154.4	1109.9	1052.5	981.0	900.3	806.5
122.5°	1072.1	1109.9	1132.2	1143.3	1132.2	1109.9	1072.1	1023.5	960.8	887.4	796.9
125°	1032.4	1061.6	1080.8	1086.8	1080.8	1061.6	1032.4	992.0	936.5	867.0	780.3
127.5°	1005.5	1031.6	1047.6	1053.7	1047.6	1031.6	1005.5	965.0	912.4	843.0	760.1
130°	986.9	1012.2	1028.3	1034.4	1028.3	1012.2	986.9	945.6	892.2	823.6	744.1
132.5°	962.8	991.2	1006.5	1012.6	1006.5	991.2	962.8	922.3	868.8	801.9	727.1
135°	921.5	949.7	965.8	971.9	965.8	949.7	921.5	881.1	830.7	769.2	703.7
137.5°	873.0	900.9	914.2	921.5	914.2	900.9	873.0	835.4	789.8	738.0	682.6
140°	840.8	863.0	877.1	885.1	877.1	863.0	840.8	805.5	763.2	717.8	670.4
142.5°	807.7	828.3	840.8	846.5	840.8	828.3	807.7	776.5	739.8	700.8	659.1
145°	761.1	778.3	788.4	793.5	788.4	778.3	761.1	736.0	707.7	677.5	643.2
147.5°	722.3	737.0	744.7	746.4	744.7	737.0	722.3	703.7	681.6	657.3	630.1
150°	699.6	712.8	718.8	719.8	718.8	712.8	699.6	683.6	665.4	645.2	622.1
152.5°	680.3	690.9	694.6	695.6	694.6	690.9	680.3	666.6	651.7	633.1	613.2
155°	653.3	661.4	664.4	664.4	664.4	661.4	653.3	643.2	631.1	616.0	599.9
157.5°	629.0	635.1	636.9	636.9	636.9	635.1	629.0	621.5	611.8	599.1	585.5
160°	613.0	619.0	620.1	620.1	620.1	619.0	613.0	606.9	598.8	587.7	576.6
162.5°	597.6	603.7	604.7	603.9	604.7	603.7	597.6	593.2	585.9	577.2	567.7
165°	577.6	581.7	580.7	579.7	580.7	581.7	577.6	573.6	568.6	561.6	555.5
167.5°	559.0	561.6	561.4	560.6	561.4	561.6	559.0	556.9	553.9	548.3	543.6
170°	548.5	549.5	548.5	548.5	548.5	549.5	548.5	546.4	543.4	539.4	536.3
172.5°	538.0	539.0	538.0	536.3	538.0	539.0	538.0	536.7	534.5	532.1	529.9
175°	524.2	526.2	524.2	522.2	524.2	526.2	524.2	524.2	524.2	522.2	521.2
177.5°	516.3	517.2	515.5	513.9	515.5	517.2	516.3	517.2	516.3	516.3	515.5
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1657.4	1661.2	1670.2	1680.2	1688.6	1695.9	1701.4	1709.3	1716.6	1726.6	1736.1
5°	1556.8	1566.6	1580.5	1597.3	1618.2	1632.2	1649.7	1665.1	1687.4	1709.7	1731.3
7.5°	1468.5	1479.4	1499.9	1523.0	1547.9	1570.7	1591.4	1618.5	1648.1	1680.6	1717.0
10°	1411.6	1423.5	1447.9	1474.4	1503.8	1526.1	1554.0	1586.1	1619.6	1659.4	1704.1
12.5°	1360.2	1371.5	1401.0	1428.1	1458.5	1483.1	1515.5	1548.1	1592.9	1636.0	1686.8
15°	1260.1	1290.1	1323.6	1355.7	1392.1	1422.1	1461.2	1494.7	1537.3	1598.0	1656.0
17.5°	1148.9	1180.9	1222.5	1272.1	1320.8	1358.0	1397.7	1439.3	1490.0	1552.0	1618.8
20°	1084.2	1110.0	1156.1	1211.2	1267.8	1319.5	1355.7	1401.8	1454.2	1521.3	1590.3
22.5°	1035.6	1057.5	1093.6	1148.7	1209.7	1269.7	1316.1	1361.6	1419.6	1486.6	1561.9
25°	962.7	986.4	1017.8	1055.6	1125.4	1188.9	1249.6	1302.0	1363.4	1430.5	1514.2
27.5°	902.1	922.8	951.5	990.8	1037.7	1107.8	1181.3	1241.1	1304.1	1376.0	1460.0
30°	866.4	883.1	906.9	946.6	991.4	1054.2	1128.8	1198.7	1262.2	1336.9	1424.2
32.5°	829.0	846.9	870.0	901.4	949.5	1002.2	1076.9	1153.5	1220.9	1297.3	1382.8
35°	779.1	793.0	814.1	846.2	889.4	935.4	1001.8	1080.7	1152.0	1233.6	1315.2
37.5°	728.7	745.2	761.6	790.3	825.8	875.4	929.6	1010.2	1089.0	1163.7	1243.3
40°	700.2	710.0	728.1	751.1	788.9	832.8	883.8	962.7	1041.6	1115.6	1195.9
42.5°	668.4	679.2	694.6	717.7	751.4	794.4	844.1	912.4	994.7	1066.4	1139.4
45°	624.1	630.4	645.8	665.3	693.3	736.5	782.6	843.3	920.8	989.3	1053.5
47.5°	579.5	584.9	594.5	612.4	643.7	678.4	721.5	776.1	844.0	912.4	966.7
50°	548.8	553.6	562.7	579.5	607.3	641.6	684.2	733.1	793.8	859.4	904.7
52.5°	518.0	520.7	529.2	548.2	571.6	605.3	643.4	688.3	745.2	799.6	845.6
55°	469.2	475.4	481.0	494.9	517.4	549.5	583.6	626.2	670.2	716.3	755.4
57.5°	418.2	425.1	433.1	445.5	463.1	493.0	523.7	558.3	595.8	634.0	666.8
60°	384.7	390.9	397.9	411.9	428.0	451.7	485.2	515.2	543.8	578.8	611.6
62.5°	351.7	358.0	366.1	377.3	392.7	415.4	443.3	469.4	499.2	529.6	554.0
65°	303.0	307.9	314.2	324.7	339.3	359.5	382.5	402.8	429.4	451.7	474.0
67.5°	249.5	258.8	267.1	275.6	288.0	306.9	323.6	343.0	360.9	377.6	397.9
70°	214.3	224.8	232.5	241.6	253.4	269.4	285.5	298.8	313.5	329.5	347.7
72.5°	184.7	193.0	198.9	208.6	219.3	234.3	249.2	260.2	272.2	283.2	300.7
75°	145.9	149.4	153.6	161.3	171.1	182.2	194.1	203.9	210.9	220.7	233.2
77.5°	104.8	111.6	114.3	119.8	126.7	133.8	141.6	149.9	156.5	160.0	169.7
80°	80.3	83.1	85.8	93.5	97.8	104.7	110.3	118.0	120.8	124.3	133.3
82.5°	62.4	64.1	65.7	67.9	70.4	77.4	82.9	87.9	90.6	91.9	98.8
85°	36.3	37.0	37.7	38.4	39.1	39.1	41.9	45.3	50.3	50.3	52.3
87.5°	15.8	16.5	16.1	15.1	16.3	15.0	15.6	15.3	16.9	17.9	19.2
90°	17.2	18.2	16.2	14.1	14.1	8.1	8.1	7.1	6.1	3.0	1.0
92.5°	266.4	319.8	279.8	203.7	125.4	74.2	53.2	38.5	26.3	16.8	11.5
95°	844.9	821.6	620.1	379.1	213.7	126.0	83.7	59.5	46.4	36.3	33.2
97.5°	1061.4	865.4	580.3	340.7	204.3	136.7	101.2	80.5	68.4	59.7	59.7
100°	1068.6	810.5	526.2	320.6	206.7	147.2	114.9	95.7	83.7	76.6	76.6
102.5°	1008.1	742.0	490.0	315.0	214.7	160.9	130.3	111.9	100.6	94.3	92.7
105°	898.3	661.4	458.7	317.6	233.9	185.5	156.2	138.1	126.0	121.0	118.0
107.5°	809.5	616.2	453.0	332.4	256.3	211.9	183.1	165.7	152.8	147.8	145.8
110°	765.2	600.9	454.6	343.8	273.2	228.8	201.7	183.5	171.4	166.3	164.3



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	740.2	593.6	459.5	355.9	289.3	246.6	219.3	201.3	190.0	184.1	182.1
115°	716.8	589.8	468.8	375.1	314.6	274.2	247.0	227.8	217.7	210.7	207.7
117.5°	706.3	588.8	478.7	394.6	338.9	300.6	272.4	254.5	243.4	237.1	234.3
120°	700.6	588.8	485.9	408.3	355.9	317.6	289.3	272.2	261.2	254.1	252.1
122.5°	694.2	587.9	493.2	421.2	372.0	333.7	306.3	287.5	277.2	270.1	268.2
125°	683.6	586.7	504.1	440.6	394.2	357.9	329.6	310.5	299.4	293.4	289.3
127.5°	669.2	584.5	512.7	457.3	414.8	379.7	351.2	331.2	318.6	311.3	308.1
130°	660.4	583.7	519.2	467.8	428.5	394.2	365.0	345.8	330.6	322.7	318.6
132.5°	652.3	582.9	524.8	478.3	439.8	405.5	377.9	357.1	342.7	332.2	329.0
135°	640.2	581.7	533.3	492.0	455.7	422.4	396.2	375.1	357.9	347.8	343.8
137.5°	629.7	581.5	538.4	501.7	467.8	436.8	411.7	389.7	373.4	362.3	358.5
140°	624.1	580.7	542.4	508.1	475.8	445.7	421.4	400.2	383.1	372.0	369.0
142.5°	619.2	580.7	545.6	512.9	483.1	453.6	430.3	409.9	393.5	383.3	380.3
145°	611.0	578.7	547.4	518.2	491.0	464.7	442.6	423.4	409.3	399.2	396.2
147.5°	603.5	575.0	548.5	522.8	499.1	474.4	454.4	438.6	424.0	415.2	414.1
150°	597.8	572.6	548.5	525.2	503.1	480.9	461.7	446.7	434.5	426.5	425.5
152.5°	591.4	568.6	546.8	526.8	506.3	486.6	469.0	455.4	444.2	436.2	436.0
155°	581.7	562.6	544.4	528.3	511.1	494.0	478.9	467.8	457.7	451.6	450.6
157.5°	571.8	556.3	541.8	528.3	514.5	500.1	488.2	478.5	470.6	464.9	464.9
160°	564.6	551.5	539.4	528.3	516.1	504.1	493.0	484.9	477.9	473.8	473.8
162.5°	558.2	546.6	536.9	528.3	517.8	506.5	497.9	490.6	484.3	481.1	481.9
165°	547.4	539.4	532.3	526.2	518.2	509.1	503.1	498.1	493.0	491.0	491.0
167.5°	537.8	532.1	527.5	523.8	518.0	511.3	506.8	503.9	500.1	499.1	500.1
170°	531.3	527.3	524.2	522.2	517.2	512.1	509.1	507.2	504.1	503.1	504.1
172.5°	525.6	522.4	521.0	520.6	516.3	512.9	510.7	509.5	507.3	507.2	508.1
175°	519.2	517.2	517.2	518.2	515.1	513.1	513.1	512.1	511.1	511.1	512.1
177.5°	514.7	513.9	513.9	515.5	513.9	513.1	513.1	513.1	512.3	513.1	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1743.3	1748.4	1753.9	1764.5	1773.5	1777.5	1785.2	1790.8	1789.2	1797.0	1810.4
5°	1750.2	1769.1	1790.7	1813.0	1838.2	1859.1	1875.8	1892.6	1905.9	1922.0	1945.7
7.5°	1749.1	1782.6	1819.1	1859.1	1900.3	1935.9	1968.8	2002.4	2032.1	2064.7	2107.2
10°	1744.6	1789.3	1834.6	1887.0	1939.3	1988.9	2033.7	2075.5	2115.4	2157.9	2211.7
12.5°	1739.6	1791.0	1845.8	1908.8	1974.0	2033.7	2086.2	2146.5	2196.3	2251.2	2313.3
15°	1717.4	1786.5	1861.2	1942.9	2021.0	2101.3	2173.2	2247.3	2316.3	2382.0	2460.2
17.5°	1691.9	1771.7	1859.8	1956.3	2050.2	2147.9	2233.1	2326.4	2397.1	2485.2	2557.8
20°	1671.3	1757.2	1851.4	1959.6	2066.5	2174.6	2268.9	2363.9	2443.5	2532.1	2624.2
22.5°	1646.2	1740.4	1842.5	1954.6	2066.5	2184.7	2289.0	2383.4	2481.9	2581.8	2676.7
25°	1605.7	1703.4	1811.6	1934.5	2063.0	2183.7	2295.4	2412.7	2518.8	2627.1	2712.2
27.5°	1556.0	1658.6	1772.7	1899.5	2031.2	2155.0	2286.5	2411.5	2518.3	2622.4	2696.7
30°	1516.3	1624.6	1734.1	1862.6	1999.4	2132.0	2273.1	2398.0	2510.4	2604.0	2645.8
32.5°	1475.5	1578.2	1691.1	1821.3	1961.5	2104.2	2244.0	2371.8	2475.8	2531.9	2533.0
35°	1404.6	1501.0	1618.2	1746.1	1889.9	2044.8	2186.6	2312.2	2375.7	2380.6	2312.2
37.5°	1327.3	1415.6	1526.4	1654.3	1811.8	1965.9	2110.7	2194.4	2215.7	2144.7	2018.1
40°	1272.0	1353.6	1460.5	1591.7	1748.1	1907.2	2039.2	2100.6	2078.3	1963.1	1822.1
42.5°	1213.9	1290.0	1392.9	1522.5	1679.4	1840.3	1952.7	1985.6	1926.4	1793.3	1628.3
45°	1119.1	1188.9	1290.8	1421.4	1572.2	1722.9	1808.2	1791.4	1692.9	1535.2	1350.2
47.5°	1020.4	1087.8	1179.5	1300.3	1454.7	1584.9	1642.5	1592.1	1452.0	1278.4	1127.9
50°	955.0	1024.1	1108.6	1223.9	1364.8	1490.5	1527.5	1450.7	1295.1	1128.1	990.0
52.5°	890.8	949.9	1032.7	1144.0	1278.8	1384.9	1404.6	1316.1	1155.4	1005.8	883.2
55°	793.0	846.9	916.7	1021.4	1137.9	1228.0	1217.5	1103.8	957.9	830.1	733.8
57.5°	698.5	739.0	803.5	901.7	1004.0	1064.5	1026.2	929.2	793.2	688.6	607.3
60°	636.0	673.7	733.8	819.6	909.7	943.8	911.7	806.4	698.8	603.2	534.7
62.5°	576.8	610.1	661.7	741.4	814.2	834.4	800.0	708.0	611.2	529.5	472.8
65°	490.8	521.5	565.5	622.1	672.3	682.1	659.7	565.5	492.2	423.7	384.7
67.5°	412.7	432.8	467.2	516.0	542.7	548.5	505.3	446.1	381.4	339.4	309.9
70°	360.2	374.2	406.3	432.8	454.4	455.1	415.4	367.9	318.3	284.2	262.5
72.5°	309.4	322.9	347.1	365.3	381.8	376.5	340.0	302.6	262.5	236.7	220.7
75°	238.7	250.6	263.2	271.6	271.6	264.6	238.0	210.2	187.1	171.8	166.8
77.5°	173.6	183.3	187.5	186.2	183.8	172.9	156.1	137.8	129.6	122.3	118.7
80°	136.1	140.4	141.7	138.3	134.0	121.5	110.3	102.6	94.9	92.2	90.8
82.5°	101.0	104.6	101.0	101.9	92.7	82.4	76.2	73.6	70.4	69.3	67.9
85°	53.7	53.0	51.7	48.2	41.9	40.5	39.8	39.1	37.7	38.4	37.0
87.5°	19.0	18.0	16.0	15.6	15.6	15.7	16.3	16.7	17.1	16.3	17.6
90°	3.0	6.1	7.1	8.1	8.1	14.1	14.1	16.2	18.2	17.2	18.2
92.5°	16.8	26.3	38.5	53.2	74.2	125.4	203.7	279.8	319.8	266.4	198.0
95°	36.3	46.4	59.5	83.7	126.0	213.7	379.1	620.1	821.6	844.9	747.0
97.5°	59.7	68.4	80.5	101.2	136.7	204.3	340.7	580.3	865.4	1061.4	1103.8
100°	76.6	83.7	95.7	114.9	147.2	206.7	320.6	526.2	810.5	1068.6	1215.9
102.5°	94.3	100.6	111.9	130.3	160.9	214.7	315.0	490.0	742.0	1008.1	1210.2
105°	121.0	126.0	138.1	156.2	185.5	233.9	317.6	458.7	661.4	898.3	1129.1
107.5°	147.8	152.8	165.7	183.1	211.9	256.3	332.4	453.0	616.2	809.5	1014.0
110°	166.3	171.4	183.5	201.7	228.8	273.2	343.8	454.6	600.9	765.2	944.6



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	184.1	190.0	201.3	219.3	246.6	289.3	355.9	459.5	593.6	740.2	893.8
115°	210.7	217.7	227.8	247.0	274.2	314.6	375.1	468.8	589.8	716.8	842.8
117.5°	237.1	243.4	254.5	272.4	300.6	338.9	394.6	478.7	588.8	706.3	817.8
120°	254.1	261.2	272.2	289.3	317.6	355.9	408.3	485.9	588.8	700.6	806.5
122.5°	270.1	277.2	287.5	306.3	333.7	372.0	421.2	493.2	587.9	694.2	796.9
125°	293.4	299.4	310.5	329.6	357.9	394.2	440.6	504.1	586.7	683.6	780.3
127.5°	311.3	318.6	331.2	351.2	379.7	414.8	457.3	512.7	584.5	669.2	760.1
130°	322.7	330.6	345.8	365.0	394.2	428.5	467.8	519.2	583.7	660.4	744.1
132.5°	332.2	342.7	357.1	377.9	405.5	439.8	478.3	524.8	582.9	652.3	727.1
135°	347.8	357.9	375.1	396.2	422.4	455.7	492.0	533.3	581.7	640.2	703.7
137.5°	362.3	373.4	389.7	411.7	436.8	467.8	501.7	538.4	581.5	629.7	682.6
140°	372.0	383.1	400.2	421.4	445.7	475.8	508.1	542.4	580.7	624.1	670.4
142.5°	383.3	393.5	409.9	430.3	453.6	483.1	512.9	545.6	580.7	619.2	659.1
145°	399.2	409.3	423.4	442.6	464.7	491.0	518.2	547.4	578.7	611.0	643.2
147.5°	415.2	424.0	438.6	454.4	474.4	499.1	522.8	548.5	575.0	603.5	630.1
150°	426.5	434.5	446.7	461.7	480.9	503.1	525.2	548.5	572.6	597.8	622.1
152.5°	436.2	444.2	455.4	469.0	486.6	506.3	526.8	546.8	568.6	591.4	613.2
155°	451.6	457.7	467.8	478.9	494.0	511.1	528.3	544.4	562.6	581.7	599.9
157.5°	464.9	470.6	478.5	488.2	500.1	514.5	528.3	541.8	556.3	571.8	585.5
160°	473.8	477.9	484.9	493.0	504.1	516.1	528.3	539.4	551.5	564.6	576.6
162.5°	481.1	484.3	490.6	497.9	506.5	517.8	528.3	536.9	546.6	558.2	567.7
165°	491.0	493.0	498.1	503.1	509.1	518.2	526.2	532.3	539.4	547.4	555.5
167.5°	499.1	500.1	503.9	506.8	511.3	518.0	523.8	527.5	532.1	537.8	543.6
170°	503.1	504.1	507.2	509.1	512.1	517.2	522.2	524.2	527.3	531.3	536.3
172.5°	507.2	507.3	509.5	510.7	512.9	516.3	520.6	521.0	522.4	525.6	529.9
175°	511.1	511.1	512.1	513.1	513.1	515.1	518.2	517.2	517.2	519.2	521.2
177.5°	513.1	512.3	513.1	513.1	513.1	513.9	515.5	513.9	513.9	514.7	515.5
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1817.7	1819.9	1821.6	1827.1	1827.7	1832.7	1827.7
5°	1968.0	1977.8	1993.2	2008.5	2009.9	2019.6	2002.3
7.5°	2136.7	2159.3	2173.4	2198.3	2208.1	2214.1	2204.1
10°	2252.8	2273.8	2310.8	2329.0	2347.1	2349.9	2341.5
12.5°	2365.1	2398.3	2427.5	2461.8	2461.0	2485.6	2476.7
15°	2514.7	2548.9	2589.3	2627.8	2641.7	2641.7	2652.9
17.5°	2621.3	2684.0	2725.9	2756.0	2789.0	2794.7	2790.9
20°	2693.4	2761.1	2805.8	2844.9	2867.2	2873.5	2873.5
22.5°	2746.9	2804.6	2848.2	2883.4	2901.8	2909.2	2907.0
25°	2784.1	2833.7	2860.2	2870.6	2875.6	2874.2	2860.9
27.5°	2733.3	2731.1	2714.3	2682.2	2658.1	2643.4	2626.7
30°	2636.2	2599.8	2557.9	2511.8	2452.6	2407.1	2393.2
32.5°	2491.4	2409.9	2338.9	2262.2	2198.4	2153.0	2134.0
35°	2211.7	2082.5	1977.1	1884.9	1818.0	1776.0	1762.1
37.5°	1879.7	1754.6	1624.2	1534.8	1479.1	1436.8	1421.1
40°	1668.5	1532.4	1418.6	1334.8	1277.6	1236.4	1235.7
42.5°	1475.8	1345.8	1238.8	1178.4	1116.7	1089.4	1089.3
45°	1208.4	1104.4	1013.7	966.2	929.2	906.9	900.6
47.5°	1000.6	914.5	854.0	816.3	786.1	771.8	762.7
50°	883.8	808.4	760.2	727.4	710.6	692.6	691.2
52.5°	786.7	725.8	688.2	661.6	640.4	629.4	629.8
55°	661.2	613.0	586.4	566.1	549.5	541.1	537.6
57.5°	556.9	520.8	501.5	482.9	475.8	469.3	467.5
60°	492.2	467.8	449.6	434.9	424.4	422.3	421.6
62.5°	438.6	413.0	400.4	389.1	381.4	378.2	377.0
65°	361.6	342.7	331.6	322.6	319.7	314.9	314.2
67.5°	291.5	280.2	272.9	266.5	262.8	262.5	262.5
70°	248.5	242.3	236.0	232.5	230.4	228.9	228.9
72.5°	211.7	207.0	201.9	200.1	199.7	198.2	197.7
75°	161.3	156.4	157.0	153.6	150.8	147.3	145.2
77.5°	114.3	110.9	110.2	109.8	107.3	106.9	108.1
80°	88.7	85.1	84.4	85.1	84.4	82.4	82.4
82.5°	67.5	64.5	63.8	63.4	62.7	63.4	62.3
85°	36.3	34.9	34.9	34.9	36.3	35.6	34.9
87.5°	16.7	16.4	16.9	16.6	16.8	16.0	16.6
90°	19.2	20.2	20.2	21.2	22.2	21.2	21.2
92.5°	149.1	118.6	98.4	86.5	81.1	77.7	77.7
95°	590.8	455.7	357.9	308.5	277.2	259.1	246.0
97.5°	1045.6	947.1	841.8	769.4	708.7	678.5	657.5
100°	1236.0	1186.6	1112.0	1024.3	962.8	932.5	924.5
102.5°	1310.2	1324.5	1293.4	1239.6	1195.1	1163.3	1156.8
105°	1303.5	1403.3	1444.7	1446.7	1438.7	1424.5	1418.5
107.5°	1199.7	1340.3	1430.2	1480.0	1503.0	1513.1	1515.7
110°	1119.0	1265.3	1376.1	1447.7	1490.1	1508.2	1517.3



TEST NUMBER: P332975-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1048.0	1186.2	1297.1	1378.4	1429.6	1455.0	1469.7
115°	966.8	1084.8	1181.5	1261.2	1321.7	1353.9	1362.0
117.5°	920.5	1013.2	1095.3	1163.3	1214.1	1246.7	1252.9
120°	900.3	981.0	1052.5	1109.9	1154.4	1180.5	1191.6
122.5°	887.4	960.8	1023.5	1072.1	1109.9	1132.2	1143.3
125°	867.0	936.5	992.0	1032.4	1061.6	1080.8	1086.8
127.5°	843.0	912.4	965.0	1005.5	1031.6	1047.6	1053.7
130°	823.6	892.2	945.6	986.9	1012.2	1028.3	1034.4
132.5°	801.9	868.8	922.3	962.8	991.2	1006.5	1012.6
135°	769.2	830.7	881.1	921.5	949.7	965.8	971.9
137.5°	738.0	789.8	835.4	873.0	900.9	914.2	921.5
140°	717.8	763.2	805.5	840.8	863.0	877.1	885.1
142.5°	700.8	739.8	776.5	807.7	828.3	840.8	846.5
145°	677.5	707.7	736.0	761.1	778.3	788.4	793.5
147.5°	657.3	681.6	703.7	722.3	737.0	744.7	746.4
150°	645.2	665.4	683.6	699.6	712.8	718.8	719.8
152.5°	633.1	651.7	666.6	680.3	690.9	694.6	695.6
155°	616.0	631.1	643.2	653.3	661.4	664.4	664.4
157.5°	599.1	611.8	621.5	629.0	635.1	636.9	636.9
160°	587.7	598.8	606.9	613.0	619.0	620.1	620.1
162.5°	577.2	585.9	593.2	597.6	603.7	604.7	603.9
165°	561.6	568.6	573.6	577.6	581.7	580.7	579.7
167.5°	548.3	553.9	556.9	559.0	561.6	561.4	560.6
170°	539.4	543.4	546.4	548.5	549.5	548.5	548.5
172.5°	532.1	534.5	536.7	538.0	539.0	538.0	536.3
175°	522.2	524.2	524.2	524.2	526.2	524.2	522.2
177.5°	516.3	516.3	517.2	516.3	517.2	515.5	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1

(END OF REPORT)