

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332875-830

Luminaire Tested: **SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332875-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3276.7 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332875-830
CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35				
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30				
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	25				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19				
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20	17				
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	14				
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	14	12				
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.7
10°-20°	152.6	4.7
20°-30°	220.4	6.7
30°-40°	249.8	7.6
40°-50°	241.2	7.4
50°-60°	200.6	6.1
60°-70°	138.5	4.2
70°-80°	70.2	2.1
80°-90°	20.1	0.6
90°-100°	45.8	1.4
100°-110°	135.8	4.1
110°-120°	230.5	7.0
120°-130°	304.0	9.3
130°-140°	341.4	10.4
140°-150°	335.4	10.2
150°-160°	282.1	8.6
160°-170°	187.7	5.7
170°-180°	65.7	2.0
0°-30°	427.8	13.1
0°-40°	677.6	20.7
0°-60°	1119.4	34.2
0°-90°	1348.2	41.1
90°-120°	412.2	12.6
90°-150°	1392.9	42.5
90°-180°	1928.0	58.8
0°-180°	3276.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	2	7	12	15	16	3
95°	32	37	41	42	42	36
105°	125	126	128	130	131	133
115°	234	234	233	233	232	231
125°	341	341	341	340	339	304
135°	440	443	444	442	441	340
145°	535	537	538	537	536	335
155°	613	613	612	614	612	282
165°	667	666	664	667	666	188
175°	694	691	691	694	691	66
180°	695	695	695	695	695	



TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.6	8.2	7.8	7.4	7.1	6.9	7.1	7.2	7.3	7.4	7.4
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	11.5	13.0	14.5	16.0	17.5	18.6	19.3	20.0	20.6	21.3	21.7
95°	32.2	33.4	34.4	35.4	36.6	37.5	38.4	39.2	40.1	40.8	41.2
97.5°	56.4	57.2	58.1	58.9	59.8	60.7	61.6	62.7	63.6	64.7	65.0
100°	75.2	75.8	76.3	76.7	77.2	77.9	79.0	80.1	81.2	82.3	82.5
102.5°	95.0	95.2	95.4	95.6	95.8	96.4	97.4	98.3	99.3	100.3	100.7
105°	125.3	125.4	125.5	125.6	125.7	126.0	126.5	127.0	127.4	127.9	128.3
107.5°	156.9	157.1	157.2	157.4	157.6	157.7	157.7	157.8	157.9	158.0	158.3
110°	178.5	178.7	179.0	179.2	179.5	179.5	179.4	179.3	179.2	179.0	178.8



TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	200.9	200.9	201.0	201.0	201.0	201.0	200.8	200.5	200.3	200.1	200.0
115°	234.4	234.4	234.4	234.4	234.4	234.2	234.0	233.8	233.6	233.3	233.2
117.5°	266.0	266.1	266.2	266.3	266.4	266.4	266.2	266.0	265.8	265.7	265.2
120°	287.1	287.6	288.0	288.5	289.0	289.1	288.7	288.3	287.9	287.6	287.0
122.5°	309.0	309.2	309.3	309.5	309.7	309.8	309.6	309.4	309.2	309.2	308.7
125°	341.4	341.4	341.4	341.4	341.4	341.3	341.2	341.1	340.9	340.8	340.5
127.5°	370.7	371.1	371.5	371.8	372.1	372.2	372.0	371.8	371.6	371.5	371.3
130°	391.3	391.7	392.1	392.5	392.8	392.9	392.9	392.9	392.9	392.9	392.8
132.5°	412.5	412.7	412.9	413.2	413.5	413.6	413.5	413.4	413.3	413.2	412.9
135°	440.3	441.0	441.7	442.4	443.2	443.5	443.5	443.5	443.5	443.5	443.3
137.5°	470.6	470.9	471.3	471.6	471.9	472.2	472.4	472.6	472.8	473.0	472.7
140°	490.8	491.1	491.3	491.5	491.7	491.9	491.9	491.9	491.9	491.9	491.7
142.5°	509.3	509.5	509.8	510.0	510.3	510.3	510.2	510.1	510.0	509.9	509.9
145°	534.9	535.4	535.8	536.3	536.8	537.1	537.2	537.3	537.4	537.5	537.4
147.5°	560.2	560.8	561.4	561.9	562.6	562.8	562.7	562.6	562.5	562.4	562.3
150°	575.7	576.3	576.7	577.2	577.7	577.9	577.9	577.9	577.9	577.9	577.9
152.5°	590.4	590.7	591.0	591.3	591.5	591.7	591.8	591.9	592.0	592.1	592.4
155°	612.8	612.8	612.8	612.8	612.8	612.7	612.7	612.6	612.5	612.3	612.7
157.5°	631.8	631.5	631.3	631.1	630.9	630.7	630.7	630.7	630.7	630.7	631.0
160°	642.9	642.8	642.7	642.6	642.4	642.3	642.2	642.2	642.0	641.9	642.2
162.5°	653.3	653.0	652.6	652.3	652.1	651.8	651.7	651.6	651.5	651.3	652.0
165°	667.1	666.8	666.4	666.1	665.7	665.4	665.2	665.0	664.7	664.5	665.2
167.5°	677.8	677.3	676.7	676.3	675.8	675.5	675.5	675.6	675.6	675.6	676.4
170°	683.8	683.2	682.6	682.0	681.4	681.2	681.3	681.4	681.6	681.6	682.4
172.5°	688.1	687.6	687.1	686.6	686.1	685.9	685.9	685.9	685.9	686.0	686.7
175°	694.0	693.4	692.9	692.2	691.6	691.3	691.2	691.1	690.9	690.8	691.6
177.5°	696.0	695.5	695.0	694.6	694.0	693.8	693.8	693.8	693.8	693.8	694.5
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1



TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	7.4	7.5	7.6	7.7	7.8	8.0	8.1	8.2
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	22.1	22.6	23.0	23.3	23.5	23.6	23.8	23.8
95°	41.6	41.9	42.3	42.5	42.5	42.5	42.5	42.5
97.5°	65.5	65.9	66.4	66.5	66.5	66.5	66.5	66.5
100°	82.8	82.9	83.2	83.3	83.3	83.3	83.3	83.3
102.5°	100.9	101.3	101.6	101.9	102.0	102.1	102.2	102.3
105°	128.7	129.0	129.4	129.7	130.1	130.4	130.8	131.2
107.5°	158.6	158.9	159.3	159.5	159.4	159.4	159.4	159.4
110°	178.5	178.3	178.0	178.1	178.5	178.8	179.2	179.6



TEST NUMBER: P332875-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	200.0	199.9	199.9	199.9	200.0	200.0	200.1	200.2
115°	233.1	233.0	232.8	232.7	232.6	232.4	232.3	232.2
117.5°	264.9	264.5	264.0	263.7	263.4	263.3	263.0	262.8
120°	286.4	285.8	285.2	285.0	285.3	285.5	285.8	286.0
122.5°	308.3	307.9	307.5	307.1	306.6	306.2	305.8	305.4
125°	340.4	340.1	339.9	339.6	339.4	339.1	338.9	338.7
127.5°	371.0	370.8	370.5	370.3	370.1	369.9	369.8	369.6
130°	392.5	392.3	392.0	391.6	391.2	390.7	390.2	389.7
132.5°	412.7	412.5	412.3	412.0	411.8	411.6	411.4	411.2
135°	443.0	442.8	442.5	442.2	441.9	441.5	441.2	440.8
137.5°	472.3	472.0	471.7	471.6	471.6	471.7	471.8	471.9
140°	491.6	491.5	491.4	491.3	491.2	491.1	491.0	490.8
142.5°	509.9	509.9	509.8	509.8	509.8	509.8	509.7	509.7
145°	537.3	537.2	537.1	536.9	536.5	536.1	535.7	535.5
147.5°	562.2	562.1	562.0	561.9	561.8	561.7	561.6	561.5
150°	577.9	577.9	577.9	577.9	577.7	577.6	577.5	577.4
152.5°	592.7	593.0	593.2	593.2	593.0	592.6	592.3	592.0
155°	613.2	613.7	614.3	614.3	613.7	613.2	612.7	612.3
157.5°	631.4	631.8	632.2	632.1	631.7	631.3	630.8	630.5
160°	642.6	642.9	643.3	643.2	642.6	642.0	641.4	640.8
162.5°	652.6	653.3	653.9	653.9	653.4	652.7	652.1	651.6
165°	665.9	666.6	667.3	667.4	666.9	666.5	666.0	665.5
167.5°	677.0	677.8	678.5	678.4	677.8	677.0	676.3	675.5
170°	683.1	683.8	684.5	684.5	683.6	682.8	681.9	681.1
172.5°	687.6	688.4	689.2	689.2	688.3	687.5	686.6	685.9
175°	692.5	693.3	694.1	694.1	693.3	692.5	691.6	690.8
177.5°	695.1	695.8	696.4	696.4	695.7	694.9	694.1	693.3
180°	695.1	695.1	695.1	695.1	695.1	695.1	695.1	695.1

(END OF REPORT)