

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332876-830

Luminaire Tested: **SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332876-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3338.1 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332876-830
CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25	22
5	67	56	48	42	61	51	44	39	43	37	33	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	28	24	22	22	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.6
10°-20°	152.6	4.6
20°-30°	220.4	6.6
30°-40°	249.8	7.5
40°-50°	241.2	7.2
50°-60°	200.6	6.0
60°-70°	138.5	4.1
70°-80°	70.2	2.1
80°-90°	19.5	0.6
90°-100°	197.7	5.9
100°-110°	411.4	12.3
110°-120°	368.5	11.0
120°-130°	310.0	9.3
130°-140°	258.4	7.7
140°-150°	197.4	5.9
150°-160°	138.8	4.2
160°-170°	81.6	2.4
170°-180°	26.6	0.8
0°-30°	427.8	12.8
0°-40°	677.6	20.3
0°-60°	1119.4	33.5
0°-90°	1347.7	40.4
90°-120°	977.6	29.3
90°-150°	1743.4	52.2
90°-180°	1990.0	59.6
0°-180°	3338.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	1	4	10	11	11	2
95°	18	56	438	217	131	20
105°	63	91	353	760	756	67
115°	111	139	314	604	726	110
125°	154	183	313	514	580	137
135°	183	218	310	456	518	142
145°	211	242	309	385	423	133
155°	240	259	300	340	354	111
165°	262	270	288	305	309	74
175°	273	274	276	280	278	26
180°	274	274	274	274	274	



TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.3	7.9	7.5	7.1	6.5	6.2	6.8	6.7	6.8	7.0	6.8
90°	0.6	1.6	3.2	3.8	4.3	4.3	7.5	7.5	8.6	9.7	9.1
92.5°	6.1	9.0	13.9	20.5	28.4	39.6	66.9	108.6	149.3	170.5	142.0
95°	17.7	19.3	24.7	31.8	44.6	67.2	114.0	202.2	330.6	438.2	450.5
97.5°	31.9	31.9	36.5	42.9	54.0	73.0	109.0	181.7	309.5	461.6	566.1
100°	40.9	40.9	44.6	51.1	61.3	78.5	110.2	171.0	280.7	432.3	570.0
102.5°	49.5	50.3	53.6	59.7	69.5	85.8	114.5	168.0	261.3	395.8	537.6
105°	62.9	64.6	67.2	73.7	83.3	99.0	124.7	169.4	244.7	352.7	479.1
107.5°	77.8	78.8	81.5	88.4	97.6	113.0	136.7	177.3	241.7	328.7	431.8
110°	87.7	88.7	91.4	97.8	107.5	122.1	145.7	183.3	242.5	320.5	408.1



TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.1	98.2	101.3	107.4	117.0	131.5	154.3	189.8	245.1	316.6	394.7
115°	110.7	112.4	116.1	121.5	131.8	146.3	167.8	200.0	250.1	314.5	382.3
117.5°	125.0	126.5	129.8	135.7	145.2	160.3	180.8	210.5	255.2	314.0	376.7
120°	134.4	135.5	139.2	145.2	154.3	169.4	189.8	217.7	259.2	314.0	373.7
122.5°	143.0	144.1	147.9	153.4	163.3	178.0	198.4	224.6	263.1	313.6	370.2
125°	154.3	156.5	159.7	165.6	175.8	190.9	210.2	235.0	268.8	312.9	364.6
127.5°	164.3	166.1	169.9	176.6	187.3	202.5	221.2	243.9	273.4	311.7	356.9
130°	169.9	172.0	176.3	184.5	194.6	210.2	228.5	249.5	276.9	311.3	352.1
132.5°	175.5	177.2	182.9	190.5	201.5	216.2	234.5	255.1	279.9	310.9	347.9
135°	183.3	185.5	190.9	200.0	211.3	225.3	243.0	262.4	284.5	310.2	341.4
137.5°	191.2	193.2	199.2	207.8	219.6	232.9	249.5	267.6	287.1	310.1	335.8
140°	196.8	198.4	204.3	213.5	224.7	237.6	253.8	271.0	289.3	309.7	332.8
142.5°	202.8	204.4	209.9	218.6	229.5	242.0	257.7	273.5	291.0	309.7	330.3
145°	211.3	212.9	218.3	225.8	236.0	247.9	261.8	276.4	292.0	308.6	325.8
147.5°	220.8	221.4	226.1	233.8	242.4	253.1	266.2	278.8	292.5	306.7	321.9
150°	226.9	227.4	231.8	238.2	246.3	256.5	268.3	280.1	292.5	305.4	318.9
152.5°	232.5	232.6	236.9	242.9	250.2	259.5	270.0	281.0	291.6	303.2	315.4
155°	240.3	240.9	244.1	249.5	255.4	263.4	272.6	281.7	290.3	300.0	310.2
157.5°	248.0	248.0	251.0	255.1	260.3	266.6	274.5	281.7	289.0	296.7	305.0
160°	252.7	252.7	254.9	258.6	262.9	268.8	275.3	281.7	287.7	294.1	301.1
162.5°	257.0	256.6	258.3	261.6	265.5	270.1	276.2	281.7	286.3	291.5	297.7
165°	261.8	261.8	262.9	265.6	268.3	271.5	276.4	280.7	283.9	287.7	292.0
167.5°	266.6	266.2	266.6	268.7	270.2	272.7	276.3	279.4	281.3	283.8	286.8
170°	268.8	268.3	268.8	270.4	271.5	273.1	275.8	278.5	279.6	281.2	283.3
172.5°	271.0	270.4	270.5	271.7	272.4	273.5	275.4	277.7	277.9	278.6	280.3
175°	273.1	272.6	272.6	273.1	273.7	273.7	274.8	276.4	275.8	275.8	276.9
177.5°	274.1	273.7	273.2	273.7	273.7	273.7	274.1	274.9	274.1	274.1	274.6
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7



TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	6.8	6.8	6.8	6.8	7.0	7.2	7.2	7.3
90°	9.7	10.2	10.7	10.7	11.3	11.8	11.3	11.3
92.5°	105.6	79.5	63.2	52.5	46.1	43.3	41.4	41.4
95°	398.4	315.1	243.0	190.9	164.6	147.9	138.2	131.2
97.5°	588.6	557.7	505.1	448.9	410.4	378.0	361.8	350.6
100°	648.5	659.2	632.8	593.0	546.3	513.5	497.4	493.0
102.5°	645.5	698.8	706.4	689.8	661.1	637.3	620.4	616.9
105°	602.2	695.2	748.5	770.5	771.6	767.2	759.7	756.5
107.5°	540.8	639.8	714.8	762.7	789.3	801.5	806.9	808.3
110°	503.8	596.8	674.8	734.0	772.1	794.7	804.4	809.2



TEST NUMBER: P332876-830

CATALOG NUMBER: SA4XXRDIP-C350D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	476.7	558.9	632.6	691.7	735.1	762.4	776.0	783.8
115°	449.5	515.7	578.5	630.2	672.6	704.9	722.1	726.4
117.5°	436.1	490.9	540.4	584.1	620.4	647.4	664.9	668.3
120°	430.2	480.1	523.1	561.3	592.0	615.7	629.6	635.6
122.5°	425.0	473.3	512.4	545.8	571.7	592.0	603.8	609.7
125°	416.1	462.4	499.5	529.0	550.5	566.2	576.4	579.6
127.5°	405.4	449.6	486.6	514.6	536.3	550.2	558.7	561.9
130°	396.8	439.3	475.8	504.4	526.4	539.8	548.5	551.7
132.5°	387.8	427.6	463.4	491.8	513.5	528.7	536.8	540.1
135°	375.3	410.3	443.0	470.0	491.4	506.5	515.1	518.3
137.5°	364.0	393.6	421.2	445.5	465.6	480.5	487.6	491.4
140°	357.5	382.9	407.0	429.6	448.5	460.2	467.8	472.1
142.5°	351.6	373.8	394.5	414.2	430.7	441.8	448.5	451.4
145°	343.0	361.3	377.5	392.5	406.0	415.1	420.5	423.1
147.5°	336.0	350.5	363.4	375.3	385.2	393.0	397.1	398.1
150°	331.8	344.1	354.9	364.6	373.2	380.1	383.3	383.9
152.5°	327.0	337.6	347.5	355.5	362.8	368.5	370.4	371.0
155°	319.9	328.5	336.6	343.0	348.5	352.7	354.3	354.3
157.5°	312.3	319.5	326.2	331.4	335.5	338.7	339.7	339.7
160°	307.6	313.5	319.3	323.7	326.9	330.2	330.6	330.6
162.5°	302.8	307.8	312.5	316.4	318.8	322.0	322.5	322.1
165°	296.2	299.4	303.2	305.9	308.1	310.2	309.7	309.2
167.5°	289.9	292.4	295.4	297.0	298.1	299.4	299.4	299.0
170°	286.1	287.7	289.8	291.4	292.5	293.0	292.5	292.5
172.5°	282.6	283.8	285.1	286.3	286.9	287.5	286.9	286.1
175°	278.0	278.5	279.6	279.6	279.6	280.7	279.6	278.5
177.5°	274.9	275.4	275.4	275.8	275.4	275.8	274.9	274.1
180°	273.7	273.7	273.7	273.7	273.7	273.7	273.7	273.7

(END OF REPORT)