

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332937-830

Luminaire Tested: **SA4XXRDIP-C795D810U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332937-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6195.7 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332937-830
CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	45	44	42	37
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	24	22	19
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10044	10044	10044	10044
5°	11651	10075	8904	10075
10°	13782	10030	7947	10030
15°	15921	9937	6829	9937
20°	17725	9810	6176	9810
25°	18299	9685	5734	9685
30°	16018	9533	5466	9533
35°	12470	9307	5306	9307
40°	9351	9049	5220	9049
45°	7383	8636	5174	8636
50°	6232	8160	5024	8160
55°	5433	7633	4756	7633
60°	4887	7090	4209	7090
65°	4309	6502	3620	6502
70°	3880	5894	3267	5894
75°	3250	5221	2785	5221
80°	2752	4454	2613	4454
85°	2325	3483	2325	3483



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	1.9
10°-20°	363.6	5.9
20°-30°	568.8	9.2
30°-40°	632.3	10.2
40°-50°	561.0	9.1
50°-60°	437.1	7.1
60°-70°	286.2	4.6
70°-80°	140.7	2.3
80°-90°	37.6	0.6
90°-100°	33.7	0.5
100°-110°	214.9	3.5
110°-120°	411.0	6.6
120°-130°	521.8	8.4
130°-140°	558.3	9.0
140°-150°	522.1	8.4
150°-160°	421.0	6.8
160°-170°	271.5	4.4
170°-180°	93.6	1.5
0°-30°	1052.9	17.0
0°-40°	1685.2	27.2
0°-60°	2683.3	43.3
0°-90°	3147.8	50.8
90°-120°	659.6	10.6
90°-150°	2261.8	36.5
90°-180°	3048.0	49.2
0°-180°	6195.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1244	1244	1244	1244	1244	
5°	1438	1243	1099	1243	1438	145
15°	1905	1189	817	1189	1905	542
25°	2054	1087	644	1087	2054	911
35°	1265	944	538	944	1265	793
45°	647	756	453	756	647	512
55°	386	542	338	542	386	351
65°	226	340	190	340	226	227
75°	104	167	89	167	104	115
85°	25	38	25	38	25	29
90°	22	2	22	2	22	11
95°	21	40	21	40	21	17
105°	210	222	210	222	210	183
115°	417	414	417	414	417	413
125°	587	582	587	582	587	522
135°	727	722	727	722	727	560
145°	837	833	837	833	837	523
155°	912	913	912	913	912	421
165°	959	963	959	963	959	271
175°	979	985	979	985	979	93
180°	985	985	985	985	985	



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1312.3	1316.0	1312.3	1311.9	1308.0	1306.7	1305.1	1300.0	1290.2	1284.7	1285.9
5°	1437.7	1450.2	1443.2	1442.2	1431.2	1420.1	1413.1	1397.0	1380.0	1368.5	1359.0
7.5°	1582.6	1589.9	1585.5	1578.4	1560.6	1550.5	1534.2	1513.1	1482.5	1459.2	1437.8
10°	1681.3	1687.3	1685.3	1672.3	1659.3	1632.7	1617.6	1588.1	1549.4	1518.9	1490.3
12.5°	1778.3	1784.8	1767.1	1767.7	1743.0	1722.1	1698.3	1661.0	1616.5	1577.1	1541.2
15°	1904.9	1896.9	1896.9	1886.8	1859.3	1830.1	1805.6	1766.5	1710.3	1663.2	1613.6
17.5°	2003.9	2006.7	2002.6	1979.0	1957.3	1927.2	1882.2	1836.5	1784.4	1721.2	1670.5
20°	2063.2	2063.2	2058.8	2042.7	2014.7	1982.5	1933.9	1884.3	1818.2	1754.4	1697.3
22.5°	2087.4	2089.0	2083.6	2070.4	2045.1	2013.8	1972.5	1922.0	1853.8	1782.2	1711.4
25°	2054.3	2063.8	2064.7	2061.2	2053.7	2034.7	1999.1	1947.5	1886.3	1808.6	1732.4
27.5°	1886.0	1898.0	1908.6	1925.9	1949.0	1961.0	1962.6	1936.4	1883.0	1808.2	1731.5
30°	1718.3	1728.4	1761.0	1803.6	1836.7	1866.8	1892.8	1899.9	1869.8	1802.6	1721.9
32.5°	1532.3	1546.0	1578.6	1624.4	1679.5	1730.4	1788.9	1818.8	1818.1	1777.7	1703.1
35°	1265.3	1275.3	1305.3	1353.5	1419.7	1495.3	1588.1	1660.2	1709.4	1705.8	1660.2
37.5°	1020.4	1031.7	1062.2	1102.0	1166.2	1259.9	1349.6	1449.1	1539.9	1590.9	1575.7
40°	887.3	887.8	917.4	958.5	1018.6	1100.3	1198.1	1308.3	1409.6	1492.3	1508.4
42.5°	782.2	782.3	801.8	846.1	889.5	966.4	1059.7	1169.2	1287.7	1383.3	1425.8
45°	646.7	651.2	667.2	693.8	727.8	793.1	867.7	969.5	1102.3	1215.6	1286.3
47.5°	547.6	554.2	564.4	586.1	613.2	656.7	718.4	809.8	917.9	1042.5	1143.1
50°	496.2	497.3	510.3	522.4	545.9	580.5	634.6	710.8	810.0	929.9	1041.7
52.5°	452.1	451.9	459.8	475.0	494.2	521.1	564.9	634.2	722.3	829.6	945.0
55°	386.0	388.5	394.5	406.5	421.0	440.2	474.7	526.9	596.1	687.8	792.5
57.5°	335.6	337.0	341.7	346.8	360.1	374.0	399.9	436.1	494.5	569.6	667.2
60°	302.7	303.3	304.8	312.3	322.8	335.8	353.4	384.0	433.1	501.8	579.0
62.5°	270.7	271.5	273.9	279.4	287.6	296.5	314.9	339.5	380.1	438.8	508.4
65°	225.6	226.1	229.6	231.6	238.1	246.1	259.7	276.2	304.3	353.4	406.0
67.5°	188.5	188.5	188.7	191.4	195.9	201.2	209.3	222.5	243.7	273.9	320.3
70°	164.4	164.4	165.4	166.9	169.5	173.9	178.4	188.5	204.1	228.6	264.2
72.5°	141.9	142.3	143.4	143.6	145.0	148.6	152.0	158.4	169.9	188.5	217.3
75°	104.2	105.8	108.3	110.3	112.8	112.3	115.8	119.8	123.3	134.3	150.9
77.5°	77.6	76.8	77.1	78.8	79.1	79.6	82.1	85.2	87.8	93.0	99.0
80°	59.2	59.2	60.7	61.2	60.7	61.2	63.6	65.1	66.2	68.1	73.7
82.5°	44.7	45.5	45.1	45.5	45.8	46.3	48.4	48.7	49.8	50.5	52.9
85°	25.1	25.5	26.1	25.1	25.1	25.1	26.1	26.6	27.6	27.1	28.1
87.5°	13.3	12.8	13.1	13.0	13.4	12.8	13.1	13.7	12.6	12.9	12.6
90°	22.1	21.8	21.5	21.1	20.8	20.2	19.1	18.2	17.2	16.2	14.9
92.5°	20.4	20.3	20.2	20.2	20.1	19.5	18.6	17.6	16.6	15.6	14.3
95°	21.4	21.2	21.0	20.9	20.7	20.2	19.1	18.2	17.2	16.2	16.0
97.5°	20.6	20.5	20.3	20.2	20.0	19.9	19.8	19.7	19.5	19.4	37.7
100°	20.6	20.5	20.3	20.2	20.0	21.3	24.0	26.9	29.6	32.4	55.0
102.5°	21.2	21.2	21.1	21.1	21.1	36.1	66.2	96.1	126.2	156.3	159.2
105°	210.0	215.9	221.8	227.7	233.7	235.8	234.3	232.9	231.4	229.9	229.1
107.5°	292.8	292.1	291.4	290.9	290.2	289.5	288.8	288.1	287.4	286.7	285.6
110°	328.7	328.2	327.7	327.3	326.7	326.3	326.0	325.6	325.4	325.0	324.0



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.7	364.0	363.4	362.8	362.1	361.8	361.9	362.0	362.1	362.1	361.7
115°	417.2	417.2	417.2	417.2	417.2	417.0	416.6	416.3	415.9	415.7	415.8
117.5°	470.5	470.5	470.6	470.7	470.7	470.8	470.9	470.9	471.0	471.1	470.7
120°	504.1	504.4	504.7	505.1	505.4	505.4	505.1	504.7	504.4	504.1	504.3
122.5°	537.1	537.4	537.7	538.1	538.4	538.5	538.3	538.1	537.9	537.7	537.4
125°	586.6	586.4	586.3	586.2	586.0	585.6	585.1	584.7	584.2	583.7	584.0
127.5°	630.1	630.3	630.4	630.5	630.7	630.7	630.8	630.9	631.0	631.1	630.4
130°	659.6	659.6	659.6	659.6	659.6	659.5	659.3	659.2	659.0	658.8	658.4
132.5°	686.7	686.8	686.9	687.1	687.2	687.2	687.0	686.9	686.7	686.5	685.9
135°	727.4	727.1	726.7	726.4	726.0	725.8	725.4	725.1	724.7	724.4	723.8
137.5°	762.1	762.2	762.3	762.4	762.5	762.4	762.0	761.7	761.4	761.0	760.3
140°	786.4	786.2	786.0	785.9	785.7	785.3	784.9	784.4	783.9	783.3	783.1
142.5°	806.3	806.3	806.3	806.3	806.3	806.1	805.7	805.3	805.0	804.6	804.5
145°	837.2	836.9	836.5	836.2	835.8	835.7	835.5	835.3	835.2	835.0	835.0
147.5°	862.7	862.5	862.3	862.2	862.0	861.9	861.8	861.7	861.5	861.4	861.5
150°	879.2	879.0	878.8	878.7	878.5	878.4	878.4	878.4	878.4	878.4	878.6
152.5°	893.3	893.4	893.5	893.6	893.7	893.6	893.4	893.2	892.9	892.6	892.9
155°	912.4	912.9	913.3	913.8	914.4	914.3	913.6	912.9	912.3	911.6	912.1
157.5°	928.3	929.2	930.0	930.9	931.7	931.7	930.9	930.0	929.2	928.3	928.9
160°	938.9	939.9	940.8	941.9	942.8	942.8	941.9	940.8	939.9	938.9	939.1
162.5°	947.2	948.3	949.3	950.5	951.6	951.7	950.6	949.7	948.8	947.7	947.9
165°	958.8	960.3	961.8	963.2	964.7	964.8	963.5	962.1	960.8	959.5	959.5
167.5°	967.5	969.1	970.7	972.4	974.0	974.1	972.7	971.3	969.8	968.4	968.5
170°	972.8	974.4	976.1	977.7	979.3	979.5	978.2	976.9	975.5	974.3	974.1
172.5°	975.7	977.5	979.3	981.1	982.8	983.1	981.8	980.4	979.1	977.8	977.6
175°	979.4	981.4	983.4	985.3	987.3	987.5	986.1	984.6	983.1	981.7	981.5
177.5°	981.8	983.4	985.0	986.5	988.1	988.4	987.3	986.3	985.1	984.1	983.9
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1281.9	1276.3	1273.5	1267.1	1259.4	1255.4	1251.8	1246.6	1239.7	1232.6	1227.3
5°	1346.9	1334.9	1319.8	1301.8	1285.8	1270.3	1256.7	1243.2	1227.7	1211.5	1195.5
7.5°	1413.7	1390.1	1364.5	1334.9	1306.2	1280.0	1255.9	1232.8	1206.7	1183.5	1162.2
10°	1460.2	1428.1	1392.5	1355.0	1317.4	1284.8	1252.7	1223.6	1191.6	1163.0	1138.9
12.5°	1497.9	1460.2	1417.4	1370.6	1325.4	1286.0	1249.1	1211.2	1174.7	1143.7	1111.6
15°	1560.5	1508.8	1451.2	1395.1	1336.4	1282.8	1233.1	1189.0	1147.5	1103.8	1073.3
17.5°	1603.5	1542.2	1472.2	1404.7	1335.4	1272.1	1214.9	1162.3	1114.4	1069.8	1033.4
20°	1629.2	1561.5	1483.8	1407.1	1329.4	1261.7	1200.0	1141.9	1092.3	1044.1	1006.5
22.5°	1643.6	1568.7	1483.8	1403.4	1323.0	1249.7	1182.0	1121.4	1067.4	1019.3	977.7
25°	1648.2	1568.0	1481.3	1389.0	1300.8	1223.1	1152.9	1087.3	1027.1	979.0	934.9
27.5°	1641.8	1547.4	1458.5	1363.9	1272.8	1190.9	1117.3	1048.3	988.1	936.4	891.2
30°	1632.2	1530.9	1435.7	1337.4	1245.2	1166.5	1088.7	1022.6	960.0	906.3	860.7
32.5°	1611.3	1510.9	1408.3	1307.8	1214.3	1133.2	1059.5	993.0	931.5	876.7	828.2
35°	1570.0	1468.3	1357.0	1253.7	1162.0	1077.7	1008.6	944.4	885.8	827.1	776.0
37.5°	1515.6	1411.6	1300.9	1187.8	1096.0	1016.5	953.0	892.8	835.6	782.0	725.4
40°	1464.2	1369.5	1255.2	1142.9	1048.7	971.9	913.3	858.7	801.1	747.9	691.3
42.5°	1402.0	1321.4	1205.9	1093.2	1000.1	926.2	871.7	818.2	765.7	714.3	655.2
45°	1298.4	1237.2	1128.9	1020.6	926.9	853.7	803.5	756.4	710.3	661.2	605.6
47.5°	1179.4	1138.0	1044.5	933.7	847.0	781.1	732.6	694.2	655.2	606.1	557.2
50°	1096.8	1070.3	980.0	878.7	796.1	735.4	685.8	649.7	617.1	570.0	526.3
52.5°	1008.6	994.5	918.2	821.4	741.5	682.0	639.6	607.2	574.2	535.1	494.3
55°	874.2	881.7	817.1	733.4	658.2	608.0	569.5	542.3	514.3	481.3	449.7
57.5°	736.9	764.3	721.0	647.4	576.9	530.7	501.6	478.8	455.2	427.8	400.9
60°	654.7	677.7	653.2	588.5	526.9	483.7	456.7	439.1	415.6	390.5	369.9
62.5°	574.5	599.2	584.6	532.3	475.1	438.0	414.2	397.8	380.3	358.4	337.1
65°	473.7	489.7	482.8	446.7	406.0	374.5	352.4	340.4	324.3	308.3	289.3
67.5°	362.8	393.8	389.7	370.5	335.5	310.8	296.3	285.7	271.1	259.2	246.2
70°	298.2	326.9	326.3	310.8	291.7	268.7	258.6	249.7	236.6	225.1	214.5
72.5°	244.1	270.3	274.2	262.3	249.2	231.8	222.2	215.9	203.3	195.4	186.9
75°	171.0	190.0	195.0	195.0	189.0	179.9	171.4	167.4	158.4	151.4	146.4
77.5°	112.1	124.1	132.0	133.7	134.7	131.7	124.6	121.8	114.9	112.4	107.5
80°	79.2	87.2	96.2	99.2	101.8	100.8	97.7	95.8	89.3	86.7	84.7
82.5°	54.8	59.2	66.5	73.1	72.5	75.1	72.5	70.9	66.0	65.0	63.1
85°	28.6	29.0	30.1	34.6	37.1	38.1	38.6	37.6	36.1	36.1	32.6
87.5°	12.3	11.7	12.3	11.9	12.0	13.2	14.0	14.0	13.2	12.3	11.6
90°	13.6	12.3	10.9	9.4	7.6	5.8	4.1	2.2	4.1	5.8	7.6
92.5°	13.0	11.7	10.4	9.7	9.6	9.5	9.4	9.3	9.4	9.5	9.6
95°	15.9	15.7	15.6	18.3	23.8	29.4	35.0	40.5	35.0	29.4	23.8
97.5°	56.0	74.3	92.6	100.0	96.5	93.0	89.5	86.1	89.5	93.0	96.5
100°	77.7	100.2	122.8	132.6	129.7	126.8	123.9	120.8	123.9	126.8	129.7
102.5°	162.1	165.0	168.1	168.4	166.3	164.1	161.9	159.8	161.9	164.1	166.3
105°	228.3	227.4	226.7	225.7	224.8	223.8	222.8	221.8	222.8	223.8	224.8
107.5°	284.5	283.3	282.2	281.4	281.0	280.4	279.9	279.5	279.9	280.4	281.0
110°	323.0	322.1	321.0	320.4	319.8	319.3	318.9	318.4	318.9	319.3	319.8



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	361.2	360.8	360.3	359.7	358.7	357.9	356.9	356.1	356.9	357.9	358.7
115°	415.9	416.1	416.3	416.1	415.7	415.2	414.6	414.2	414.6	415.2	415.7
117.5°	470.3	470.0	469.7	469.1	468.4	467.8	467.1	466.5	467.1	467.8	468.4
120°	504.4	504.5	504.7	504.4	503.9	503.2	502.6	501.9	502.6	503.2	503.9
122.5°	537.2	537.0	536.8	536.5	536.0	535.6	535.3	534.9	535.3	535.6	536.0
125°	584.4	584.7	584.9	584.8	584.2	583.5	582.9	582.2	582.9	583.5	584.2
127.5°	629.6	628.9	628.1	627.6	627.5	627.4	627.2	627.0	627.2	627.4	627.5
130°	657.9	657.3	656.9	656.6	656.4	656.2	656.1	655.9	656.1	656.2	656.4
132.5°	685.3	684.7	684.1	683.6	683.3	683.1	682.7	682.4	682.7	683.1	683.3
135°	723.1	722.5	721.8	721.6	721.7	721.9	722.1	722.3	722.1	721.9	721.7
137.5°	759.6	758.8	758.1	757.7	757.6	757.6	757.5	757.4	757.5	757.6	757.6
140°	782.8	782.4	782.1	781.7	781.5	781.1	780.8	780.4	780.8	781.1	781.5
142.5°	804.3	804.0	803.8	803.4	802.9	802.3	801.6	801.1	801.6	802.3	802.9
145°	835.0	835.0	835.0	834.7	834.2	833.8	833.3	832.7	833.3	833.8	834.2
147.5°	861.7	861.9	862.0	861.7	860.7	859.8	858.9	858.0	858.9	859.8	860.7
150°	878.8	878.9	879.1	878.8	878.3	877.6	876.9	876.3	876.9	877.6	878.3
152.5°	893.2	893.5	893.8	893.7	893.2	892.6	892.1	891.6	892.1	892.6	893.2
155°	912.6	913.1	913.6	913.8	913.6	913.4	913.2	913.1	913.2	913.4	913.6
157.5°	929.4	929.9	930.5	930.9	930.9	931.0	931.1	931.2	931.1	931.0	930.9
160°	939.2	939.4	939.5	939.9	940.4	940.8	941.3	941.9	941.3	940.8	940.4
162.5°	948.1	948.2	948.4	948.8	949.4	950.0	950.6	951.3	950.6	950.0	949.4
165°	959.5	959.5	959.5	960.0	960.7	961.6	962.4	963.2	962.4	961.6	960.7
167.5°	968.6	968.7	968.7	969.2	970.1	970.9	971.8	972.6	971.8	970.9	970.1
170°	973.9	973.7	973.6	974.0	975.0	976.0	976.9	978.0	976.9	976.0	975.0
172.5°	977.5	977.3	977.1	977.6	978.5	979.5	980.5	981.5	980.5	979.5	978.5
175°	981.3	981.2	981.0	981.4	982.4	983.4	984.3	985.3	984.3	983.4	982.4
177.5°	983.6	983.4	983.1	983.4	984.3	985.2	986.2	987.1	986.2	985.2	984.3
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1221.7	1217.7	1212.5	1206.5	1199.3	1192.9	1190.1	1192.4	1193.6	1190.4	1190.1
5°	1184.5	1172.0	1162.0	1146.9	1134.9	1124.8	1117.9	1114.8	1115.9	1107.9	1105.8
7.5°	1142.7	1127.8	1111.4	1093.6	1076.9	1062.2	1054.5	1050.3	1041.8	1038.1	1032.0
10°	1115.9	1095.8	1079.8	1058.7	1039.6	1022.1	1013.6	1006.5	998.1	994.0	985.5
12.5°	1088.2	1064.9	1047.3	1025.4	1006.0	984.8	976.7	963.7	950.4	941.9	930.9
15°	1049.1	1021.2	999.6	973.5	950.5	926.3	904.8	880.7	871.8	852.7	841.7
17.5°	1003.5	975.1	948.4	913.4	877.9	848.0	825.0	801.9	788.2	776.0	770.3
20°	973.5	947.4	910.3	869.7	830.1	797.0	778.4	763.5	748.4	739.9	733.9
22.5°	945.0	911.7	868.6	824.8	785.2	759.3	743.6	728.1	716.0	707.8	699.7
25°	897.3	853.7	808.0	757.9	730.8	708.3	691.3	678.7	671.2	660.7	656.7
27.5°	848.3	795.4	745.1	711.4	683.2	662.6	647.7	638.3	628.8	622.1	616.9
30°	810.6	757.0	711.8	679.8	651.2	634.1	622.1	611.1	603.5	598.0	594.0
32.5°	773.3	719.6	681.7	647.2	624.7	608.0	595.2	587.0	581.1	574.0	571.6
35°	719.3	671.8	638.7	607.6	584.5	569.5	559.4	550.9	545.9	543.8	542.3
37.5°	667.5	628.5	593.0	567.4	546.9	535.1	523.2	519.1	515.6	512.0	513.6
40°	634.6	598.0	566.5	539.4	522.8	509.8	502.8	497.8	494.7	494.7	494.7
42.5°	606.1	570.3	539.6	515.3	498.8	487.8	479.9	475.7	474.7	474.3	476.7
45°	561.9	528.9	497.8	477.7	463.6	452.6	448.2	444.6	444.6	446.7	447.1
47.5°	518.1	487.1	462.2	439.7	426.9	420.0	416.0	414.2	414.4	416.5	418.8
50°	491.3	460.7	436.1	416.0	404.1	397.5	394.0	393.0	394.0	394.0	397.5
52.5°	461.9	434.6	410.5	393.6	379.9	373.8	371.9	370.5	371.2	372.8	374.3
55°	419.1	394.5	371.5	355.4	345.3	341.4	336.9	337.3	336.4	337.3	337.3
57.5°	376.1	354.0	332.5	319.8	311.0	305.2	300.3	301.7	300.2	300.0	299.2
60°	348.4	324.3	307.3	295.8	285.7	280.7	276.2	277.2	275.7	274.7	272.7
62.5°	318.3	298.2	282.0	270.9	262.9	257.0	252.5	251.6	248.1	244.6	240.3
65°	274.7	258.2	243.6	233.1	225.6	221.0	217.5	214.5	207.0	199.0	195.0
67.5°	232.3	220.4	206.8	197.9	191.8	185.9	179.2	174.1	167.0	162.6	160.1
70°	205.0	193.5	182.0	173.4	166.9	161.5	153.9	150.4	145.3	143.4	140.8
72.5°	179.0	168.2	157.5	149.8	142.9	138.6	132.6	129.1	127.0	126.1	123.7
75°	139.4	130.8	122.8	115.8	110.3	107.3	104.8	102.3	101.2	96.7	94.3
77.5°	101.7	96.0	91.0	86.1	82.1	80.1	75.3	72.4	70.7	68.6	68.1
80°	79.2	75.2	70.2	67.2	61.6	59.7	57.7	57.1	56.6	56.2	55.6
82.5°	59.6	55.5	50.5	48.7	47.2	46.0	44.8	44.3	43.8	44.1	44.0
85°	30.1	28.1	28.1	27.6	27.1	26.6	26.1	26.1	25.5	26.1	25.5
87.5°	11.9	11.8	12.1	11.5	12.2	12.4	12.3	12.4	13.1	12.4	12.5
90°	9.4	10.9	12.3	13.6	14.9	16.2	17.2	18.2	19.1	20.2	20.8
92.5°	9.7	10.4	11.7	13.0	14.3	15.6	16.6	17.6	18.6	19.5	20.1
95°	18.3	15.6	15.7	15.9	16.0	16.2	17.2	18.2	19.1	20.2	20.7
97.5°	100.0	92.6	74.3	56.0	37.7	19.4	19.5	19.7	19.8	19.9	20.0
100°	132.6	122.8	100.2	77.7	55.0	32.4	29.6	26.9	24.0	21.3	20.0
102.5°	168.4	168.1	165.0	162.1	159.2	156.3	126.2	96.1	66.2	36.1	21.1
105°	225.7	226.7	227.4	228.3	229.1	229.9	231.4	232.9	234.3	235.8	233.7
107.5°	281.4	282.2	283.3	284.5	285.6	286.7	287.4	288.1	288.8	289.5	290.2
110°	320.4	321.0	322.1	323.0	324.0	325.0	325.4	325.6	326.0	326.3	326.7



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	359.7	360.3	360.8	361.2	361.7	362.1	362.1	362.0	361.9	361.8	362.1
115°	416.1	416.3	416.1	415.9	415.8	415.7	415.9	416.3	416.6	417.0	417.2
117.5°	469.1	469.7	470.0	470.3	470.7	471.1	471.0	470.9	470.9	470.8	470.7
120°	504.4	504.7	504.5	504.4	504.3	504.1	504.4	504.7	505.1	505.4	505.4
122.5°	536.5	536.8	537.0	537.2	537.4	537.7	537.9	538.1	538.3	538.5	538.4
125°	584.8	584.9	584.7	584.4	584.0	583.7	584.2	584.7	585.1	585.6	586.0
127.5°	627.6	628.1	628.9	629.6	630.4	631.1	631.0	630.9	630.8	630.7	630.7
130°	656.6	656.9	657.3	657.9	658.4	658.8	659.0	659.2	659.3	659.5	659.6
132.5°	683.6	684.1	684.7	685.3	685.9	686.5	686.7	686.9	687.0	687.2	687.2
135°	721.6	721.8	722.5	723.1	723.8	724.4	724.7	725.1	725.4	725.8	726.0
137.5°	757.7	758.1	758.8	759.6	760.3	761.0	761.4	761.7	762.0	762.4	762.5
140°	781.7	782.1	782.4	782.8	783.1	783.3	783.9	784.4	784.9	785.3	785.7
142.5°	803.4	803.8	804.0	804.3	804.5	804.6	805.0	805.3	805.7	806.1	806.3
145°	834.7	835.0	835.0	835.0	835.0	835.0	835.2	835.3	835.5	835.7	835.8
147.5°	861.7	862.0	861.9	861.7	861.5	861.4	861.5	861.7	861.8	861.9	862.0
150°	878.8	879.1	878.9	878.8	878.6	878.4	878.4	878.4	878.4	878.4	878.5
152.5°	893.7	893.8	893.5	893.2	892.9	892.6	892.9	893.2	893.4	893.6	893.7
155°	913.8	913.6	913.1	912.6	912.1	911.6	912.3	912.9	913.6	914.3	914.4
157.5°	930.9	930.5	929.9	929.4	928.9	928.3	929.2	930.0	930.9	931.7	931.7
160°	939.9	939.5	939.4	939.2	939.1	938.9	939.9	940.8	941.9	942.8	942.8
162.5°	948.8	948.4	948.2	948.1	947.9	947.7	948.8	949.7	950.6	951.7	951.6
165°	960.0	959.5	959.5	959.5	959.5	959.5	960.8	962.1	963.5	964.8	964.7
167.5°	969.2	968.7	968.7	968.6	968.5	968.4	969.8	971.3	972.7	974.1	974.0
170°	974.0	973.6	973.7	973.9	974.1	974.3	975.5	976.9	978.2	979.5	979.3
172.5°	977.6	977.1	977.3	977.5	977.6	977.8	979.1	980.4	981.8	983.1	982.8
175°	981.4	981.0	981.2	981.3	981.5	981.7	983.1	984.6	986.1	987.5	987.3
177.5°	983.4	983.1	983.4	983.6	983.9	984.1	985.1	986.3	987.3	988.4	988.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1187.6	1188.5	1185.6	1184.8	1185.6	1188.5	1187.6	1190.1	1190.4	1193.6	1192.4
5°	1101.8	1100.8	1098.3	1098.8	1098.3	1100.8	1101.8	1105.8	1107.9	1115.9	1114.8
7.5°	1028.4	1024.5	1025.6	1021.6	1025.6	1024.5	1028.4	1032.0	1038.1	1041.8	1050.3
10°	983.5	978.0	973.5	969.5	973.5	978.0	983.5	985.5	994.0	998.1	1006.5
12.5°	922.2	917.5	911.3	912.6	911.3	917.5	922.2	930.9	941.9	950.4	963.7
15°	835.1	827.6	815.6	817.1	815.6	827.6	835.1	841.7	852.7	871.8	880.7
17.5°	761.5	761.6	756.0	757.3	756.0	761.6	761.5	770.3	776.0	788.2	801.9
20°	723.3	719.8	720.3	718.9	720.3	719.8	723.3	733.9	739.9	748.4	763.5
22.5°	696.9	692.6	689.1	686.0	689.1	692.6	696.9	699.7	707.8	716.0	728.1
25°	652.1	649.1	644.6	643.7	644.6	649.1	652.1	656.7	660.7	671.2	678.7
27.5°	612.8	612.3	610.5	608.1	610.5	612.3	612.8	616.9	622.1	628.8	638.3
30°	590.0	589.0	588.0	586.4	588.0	589.0	590.0	594.0	598.0	603.5	611.1
32.5°	569.6	568.9	568.0	568.1	568.0	568.9	569.6	571.6	574.0	581.1	587.0
35°	540.4	539.9	538.9	538.4	538.9	539.9	540.4	542.3	543.8	545.9	550.9
37.5°	513.1	514.4	513.8	513.7	513.8	514.4	513.1	513.6	512.0	515.6	519.1
40°	494.3	494.7	495.8	495.3	495.8	494.7	494.3	494.7	494.7	494.7	497.8
42.5°	478.6	478.7	480.1	478.4	480.1	478.7	478.6	476.7	474.3	474.7	475.7
45°	450.6	453.6	453.2	453.2	453.2	453.6	450.6	447.1	446.7	444.6	444.6
47.5°	420.1	422.6	423.4	423.3	423.4	422.6	420.1	418.8	416.5	414.4	414.2
50°	400.0	399.0	400.5	400.0	400.5	399.0	400.0	397.5	394.0	394.0	393.0
52.5°	375.6	375.8	375.7	375.1	375.7	375.8	375.6	374.3	372.8	371.2	370.5
55°	337.9	338.4	337.3	337.9	337.3	338.4	337.9	337.3	337.3	336.4	337.3
57.5°	297.0	294.5	295.6	294.4	295.6	294.5	297.0	299.2	300.0	300.2	301.7
60°	267.7	263.6	262.7	260.7	262.7	263.6	267.7	272.7	274.7	275.7	277.2
62.5°	234.8	232.0	228.6	230.2	228.6	232.0	234.8	240.3	244.6	248.1	251.6
65°	191.0	189.0	187.5	189.5	187.5	189.0	191.0	195.0	199.0	207.0	214.5
67.5°	158.1	157.0	157.0	156.0	157.0	157.0	158.1	160.1	162.6	167.0	174.1
70°	140.8	139.4	139.4	138.4	139.4	139.4	140.8	140.8	143.4	145.3	150.4
72.5°	123.2	121.7	122.2	121.5	122.2	121.7	123.2	123.7	126.1	127.0	129.1
75°	91.2	88.7	88.7	89.3	88.7	88.7	91.2	94.3	96.7	101.2	102.3
77.5°	68.1	67.6	68.2	67.4	68.2	67.6	68.1	68.1	68.6	70.7	72.4
80°	55.6	55.1	54.7	56.2	54.7	55.1	55.6	55.6	56.2	56.6	57.1
82.5°	43.2	43.1	43.0	45.0	43.0	43.1	43.2	44.0	44.1	43.8	44.3
85°	26.1	25.1	26.1	25.1	26.1	25.1	26.1	25.5	26.1	25.5	26.1
87.5°	13.5	13.1	12.8	13.3	12.8	13.1	13.5	12.5	12.4	13.1	12.4
90°	21.1	21.5	21.8	22.1	21.8	21.5	21.1	20.8	20.2	19.1	18.2
92.5°	20.2	20.2	20.3	20.4	20.3	20.2	20.2	20.1	19.5	18.6	17.6
95°	20.9	21.0	21.2	21.4	21.2	21.0	20.9	20.7	20.2	19.1	18.2
97.5°	20.2	20.3	20.5	20.6	20.5	20.3	20.2	20.0	19.9	19.8	19.7
100°	20.2	20.3	20.5	20.6	20.5	20.3	20.2	20.0	21.3	24.0	26.9
102.5°	21.1	21.1	21.2	21.2	21.2	21.1	21.1	21.1	36.1	66.2	96.1
105°	227.7	221.8	215.9	210.0	215.9	221.8	227.7	233.7	235.8	234.3	232.9
107.5°	290.9	291.4	292.1	292.8	292.1	291.4	290.9	290.2	289.5	288.8	288.1
110°	327.3	327.7	328.2	328.7	328.2	327.7	327.3	326.7	326.3	326.0	325.6



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	362.8	363.4	364.0	364.7	364.0	363.4	362.8	362.1	361.8	361.9	362.0
115°	417.2	417.2	417.2	417.2	417.2	417.2	417.2	417.2	417.0	416.6	416.3
117.5°	470.7	470.6	470.5	470.5	470.5	470.6	470.7	470.7	470.8	470.9	470.9
120°	505.1	504.7	504.4	504.1	504.4	504.7	505.1	505.4	505.4	505.1	504.7
122.5°	538.1	537.7	537.4	537.1	537.4	537.7	538.1	538.4	538.5	538.3	538.1
125°	586.2	586.3	586.4	586.6	586.4	586.3	586.2	586.0	585.6	585.1	584.7
127.5°	630.5	630.4	630.3	630.1	630.3	630.4	630.5	630.7	630.7	630.8	630.9
130°	659.6	659.6	659.6	659.6	659.6	659.6	659.6	659.6	659.5	659.3	659.2
132.5°	687.1	686.9	686.8	686.7	686.8	686.9	687.1	687.2	687.2	687.0	686.9
135°	726.4	726.7	727.1	727.4	727.1	726.7	726.4	726.0	725.8	725.4	725.1
137.5°	762.4	762.3	762.2	762.1	762.2	762.3	762.4	762.5	762.4	762.0	761.7
140°	785.9	786.0	786.2	786.4	786.2	786.0	785.9	785.7	785.3	784.9	784.4
142.5°	806.3	806.3	806.3	806.3	806.3	806.3	806.3	806.3	806.1	805.7	805.3
145°	836.2	836.5	836.9	837.2	836.9	836.5	836.2	835.8	835.7	835.5	835.3
147.5°	862.2	862.3	862.5	862.7	862.5	862.3	862.2	862.0	861.9	861.8	861.7
150°	878.7	878.8	879.0	879.2	879.0	878.8	878.7	878.5	878.4	878.4	878.4
152.5°	893.6	893.5	893.4	893.3	893.4	893.5	893.6	893.7	893.6	893.4	893.2
155°	913.8	913.3	912.9	912.4	912.9	913.3	913.8	914.4	914.3	913.6	912.9
157.5°	930.9	930.0	929.2	928.3	929.2	930.0	930.9	931.7	931.7	930.9	930.0
160°	941.9	940.8	939.9	938.9	939.9	940.8	941.9	942.8	942.8	941.9	940.8
162.5°	950.5	949.3	948.3	947.2	948.3	949.3	950.5	951.6	951.7	950.6	949.7
165°	963.2	961.8	960.3	958.8	960.3	961.8	963.2	964.7	964.8	963.5	962.1
167.5°	972.4	970.7	969.1	967.5	969.1	970.7	972.4	974.0	974.1	972.7	971.3
170°	977.7	976.1	974.4	972.8	974.4	976.1	977.7	979.3	979.5	978.2	976.9
172.5°	981.1	979.3	977.5	975.7	977.5	979.3	981.1	982.8	983.1	981.8	980.4
175°	985.3	983.4	981.4	979.4	981.4	983.4	985.3	987.3	987.5	986.1	984.6
177.5°	986.5	985.0	983.4	981.8	983.4	985.0	986.5	988.1	988.4	987.3	986.3
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1190.1	1192.9	1199.3	1206.5	1212.5	1217.7	1221.7	1227.3	1232.6	1239.7	1246.6
5°	1117.9	1124.8	1134.9	1146.9	1162.0	1172.0	1184.5	1195.5	1211.5	1227.7	1243.2
7.5°	1054.5	1062.2	1076.9	1093.6	1111.4	1127.8	1142.7	1162.2	1183.5	1206.7	1232.8
10°	1013.6	1022.1	1039.6	1058.7	1079.8	1095.8	1115.9	1138.9	1163.0	1191.6	1223.6
12.5°	976.7	984.8	1006.0	1025.4	1047.3	1064.9	1088.2	1111.6	1143.7	1174.7	1211.2
15°	904.8	926.3	950.5	973.5	999.6	1021.2	1049.1	1073.3	1103.8	1147.5	1189.0
17.5°	825.0	848.0	877.9	913.4	948.4	975.1	1003.5	1033.4	1069.8	1114.4	1162.3
20°	778.4	797.0	830.1	869.7	910.3	947.4	973.5	1006.5	1044.1	1092.3	1141.9
22.5°	743.6	759.3	785.2	824.8	868.6	911.7	945.0	977.7	1019.3	1067.4	1121.4
25°	691.3	708.3	730.8	757.9	808.0	853.7	897.3	934.9	979.0	1027.1	1087.3
27.5°	647.7	662.6	683.2	711.4	745.1	795.4	848.3	891.2	936.4	988.1	1048.3
30°	622.1	634.1	651.2	679.8	711.8	757.0	810.6	860.7	906.3	960.0	1022.6
32.5°	595.2	608.0	624.7	647.2	681.7	719.6	773.3	828.2	876.7	931.5	993.0
35°	559.4	569.5	584.5	607.6	638.7	671.8	719.3	776.0	827.1	885.8	944.4
37.5°	523.2	535.1	546.9	567.4	593.0	628.5	667.5	725.4	782.0	835.6	892.8
40°	502.8	509.8	522.8	539.4	566.5	598.0	634.6	691.3	747.9	801.1	858.7
42.5°	479.9	487.8	498.8	515.3	539.6	570.3	606.1	655.2	714.3	765.7	818.2
45°	448.2	452.6	463.6	477.7	497.8	528.9	561.9	605.6	661.2	710.3	756.4
47.5°	416.0	420.0	426.9	439.7	462.2	487.1	518.1	557.2	606.1	655.2	694.2
50°	394.0	397.5	404.1	416.0	436.1	460.7	491.3	526.3	570.0	617.1	649.7
52.5°	371.9	373.8	379.9	393.6	410.5	434.6	461.9	494.3	535.1	574.2	607.2
55°	336.9	341.4	345.3	355.4	371.5	394.5	419.1	449.7	481.3	514.3	542.3
57.5°	300.3	305.2	311.0	319.8	332.5	354.0	376.1	400.9	427.8	455.2	478.8
60°	276.2	280.7	285.7	295.8	307.3	324.3	348.4	369.9	390.5	415.6	439.1
62.5°	252.5	257.0	262.9	270.9	282.0	298.2	318.3	337.1	358.4	380.3	397.8
65°	217.5	221.0	225.6	233.1	243.6	258.2	274.7	289.3	308.3	324.3	340.4
67.5°	179.2	185.9	191.8	197.9	206.8	220.4	232.3	246.2	259.2	271.1	285.7
70°	153.9	161.5	166.9	173.4	182.0	193.5	205.0	214.5	225.1	236.6	249.7
72.5°	132.6	138.6	142.9	149.8	157.5	168.2	179.0	186.9	195.4	203.3	215.9
75°	104.8	107.3	110.3	115.8	122.8	130.8	139.4	146.4	151.4	158.4	167.4
77.5°	75.3	80.1	82.1	86.1	91.0	96.0	101.7	107.5	112.4	114.9	121.8
80°	57.7	59.7	61.6	67.2	70.2	75.2	79.2	84.7	86.7	89.3	95.8
82.5°	44.8	46.0	47.2	48.7	50.5	55.5	59.6	63.1	65.0	66.0	70.9
85°	26.1	26.6	27.1	27.6	28.1	28.1	30.1	32.6	36.1	36.1	37.6
87.5°	12.3	12.4	12.2	11.5	12.1	11.8	11.9	11.6	12.3	13.2	14.0
90°	17.2	16.2	14.9	13.6	12.3	10.9	9.4	7.6	5.8	4.1	2.2
92.5°	16.6	15.6	14.3	13.0	11.7	10.4	9.7	9.6	9.5	9.4	9.3
95°	17.2	16.2	16.0	15.9	15.7	15.6	18.3	23.8	29.4	35.0	40.5
97.5°	19.5	19.4	37.7	56.0	74.3	92.6	100.0	96.5	93.0	89.5	86.1
100°	29.6	32.4	55.0	77.7	100.2	122.8	132.6	129.7	126.8	123.9	120.8
102.5°	126.2	156.3	159.2	162.1	165.0	168.1	168.4	166.3	164.1	161.9	159.8
105°	231.4	229.9	229.1	228.3	227.4	226.7	225.7	224.8	223.8	222.8	221.8
107.5°	287.4	286.7	285.6	284.5	283.3	282.2	281.4	281.0	280.4	279.9	279.5
110°	325.4	325.0	324.0	323.0	322.1	321.0	320.4	319.8	319.3	318.9	318.4



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	362.1	362.1	361.7	361.2	360.8	360.3	359.7	358.7	357.9	356.9	356.1
115°	415.9	415.7	415.8	415.9	416.1	416.3	416.1	415.7	415.2	414.6	414.2
117.5°	471.0	471.1	470.7	470.3	470.0	469.7	469.1	468.4	467.8	467.1	466.5
120°	504.4	504.1	504.3	504.4	504.5	504.7	504.4	503.9	503.2	502.6	501.9
122.5°	537.9	537.7	537.4	537.2	537.0	536.8	536.5	536.0	535.6	535.3	534.9
125°	584.2	583.7	584.0	584.4	584.7	584.9	584.8	584.2	583.5	582.9	582.2
127.5°	631.0	631.1	630.4	629.6	628.9	628.1	627.6	627.5	627.4	627.2	627.0
130°	659.0	658.8	658.4	657.9	657.3	656.9	656.6	656.4	656.2	656.1	655.9
132.5°	686.7	686.5	685.9	685.3	684.7	684.1	683.6	683.3	683.1	682.7	682.4
135°	724.7	724.4	723.8	723.1	722.5	721.8	721.6	721.7	721.9	722.1	722.3
137.5°	761.4	761.0	760.3	759.6	758.8	758.1	757.7	757.6	757.6	757.5	757.4
140°	783.9	783.3	783.1	782.8	782.4	782.1	781.7	781.5	781.1	780.8	780.4
142.5°	805.0	804.6	804.5	804.3	804.0	803.8	803.4	802.9	802.3	801.6	801.1
145°	835.2	835.0	835.0	835.0	835.0	835.0	834.7	834.2	833.8	833.3	832.7
147.5°	861.5	861.4	861.5	861.7	861.9	862.0	861.7	860.7	859.8	858.9	858.0
150°	878.4	878.4	878.6	878.8	878.9	879.1	878.8	878.3	877.6	876.9	876.3
152.5°	892.9	892.6	892.9	893.2	893.5	893.8	893.7	893.2	892.6	892.1	891.6
155°	912.3	911.6	912.1	912.6	913.1	913.6	913.8	913.6	913.4	913.2	913.1
157.5°	929.2	928.3	928.9	929.4	929.9	930.5	930.9	930.9	931.0	931.1	931.2
160°	939.9	938.9	939.1	939.2	939.4	939.5	939.9	940.4	940.8	941.3	941.9
162.5°	948.8	947.7	947.9	948.1	948.2	948.4	948.8	949.4	950.0	950.6	951.3
165°	960.8	959.5	959.5	959.5	959.5	959.5	960.0	960.7	961.6	962.4	963.2
167.5°	969.8	968.4	968.5	968.6	968.7	968.7	969.2	970.1	970.9	971.8	972.6
170°	975.5	974.3	974.1	973.9	973.7	973.6	974.0	975.0	976.0	976.9	978.0
172.5°	979.1	977.8	977.6	977.5	977.3	977.1	977.6	978.5	979.5	980.5	981.5
175°	983.1	981.7	981.5	981.3	981.2	981.0	981.4	982.4	983.4	984.3	985.3
177.5°	985.1	984.1	983.9	983.6	983.4	983.1	983.4	984.3	985.2	986.2	987.1
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1251.8	1255.4	1259.4	1267.1	1273.5	1276.3	1281.9	1285.9	1284.7	1290.2	1300.0
5°	1256.7	1270.3	1285.8	1301.8	1319.8	1334.9	1346.9	1359.0	1368.5	1380.0	1397.0
7.5°	1255.9	1280.0	1306.2	1334.9	1364.5	1390.1	1413.7	1437.8	1459.2	1482.5	1513.1
10°	1252.7	1284.8	1317.4	1355.0	1392.5	1428.1	1460.2	1490.3	1518.9	1549.4	1588.1
12.5°	1249.1	1286.0	1325.4	1370.6	1417.4	1460.2	1497.9	1541.2	1577.1	1616.5	1661.0
15°	1233.1	1282.8	1336.4	1395.1	1451.2	1508.8	1560.5	1613.6	1663.2	1710.3	1766.5
17.5°	1214.9	1272.1	1335.4	1404.7	1472.2	1542.2	1603.5	1670.5	1721.2	1784.4	1836.5
20°	1200.0	1261.7	1329.4	1407.1	1483.8	1561.5	1629.2	1697.3	1754.4	1818.2	1884.3
22.5°	1182.0	1249.7	1323.0	1403.4	1483.8	1568.7	1643.6	1711.4	1782.2	1853.8	1922.0
25°	1152.9	1223.1	1300.8	1389.0	1481.3	1568.0	1648.2	1732.4	1808.6	1886.3	1947.5
27.5°	1117.3	1190.9	1272.8	1363.9	1458.5	1547.4	1641.8	1731.5	1808.2	1883.0	1936.4
30°	1088.7	1166.5	1245.2	1337.4	1435.7	1530.9	1632.2	1721.9	1802.6	1869.8	1899.9
32.5°	1059.5	1133.2	1214.3	1307.8	1408.3	1510.9	1611.3	1703.1	1777.7	1818.1	1818.8
35°	1008.6	1077.7	1162.0	1253.7	1357.0	1468.3	1570.0	1660.2	1705.8	1709.4	1660.2
37.5°	953.0	1016.5	1096.0	1187.8	1300.9	1411.6	1515.6	1575.7	1590.9	1539.9	1449.1
40°	913.3	971.9	1048.7	1142.9	1255.2	1369.5	1464.2	1508.4	1492.3	1409.6	1308.3
42.5°	871.7	926.2	1000.1	1093.2	1205.9	1321.4	1402.0	1425.8	1383.3	1287.7	1169.2
45°	803.5	853.7	926.9	1020.6	1128.9	1237.2	1298.4	1286.3	1215.6	1102.3	969.5
47.5°	732.6	781.1	847.0	933.7	1044.5	1138.0	1179.4	1143.1	1042.5	917.9	809.8
50°	685.8	735.4	796.1	878.7	980.0	1070.3	1096.8	1041.7	929.9	810.0	710.8
52.5°	639.6	682.0	741.5	821.4	918.2	994.5	1008.6	945.0	829.6	722.3	634.2
55°	569.5	608.0	658.2	733.4	817.1	881.7	874.2	792.5	687.8	596.1	526.9
57.5°	501.6	530.7	576.9	647.4	721.0	764.3	736.9	667.2	569.6	494.5	436.1
60°	456.7	483.7	526.9	588.5	653.2	677.7	654.7	579.0	501.8	433.1	384.0
62.5°	414.2	438.0	475.1	532.3	584.6	599.2	574.5	508.4	438.8	380.1	339.5
65°	352.4	374.5	406.0	446.7	482.8	489.7	473.7	406.0	353.4	304.3	276.2
67.5°	296.3	310.8	335.5	370.5	389.7	393.8	362.8	320.3	273.9	243.7	222.5
70°	258.6	268.7	291.7	310.8	326.3	326.9	298.2	264.2	228.6	204.1	188.5
72.5°	222.2	231.8	249.2	262.3	274.2	270.3	244.1	217.3	188.5	169.9	158.4
75°	171.4	179.9	189.0	195.0	195.0	190.0	171.0	150.9	134.3	123.3	119.8
77.5°	124.6	131.7	134.7	133.7	132.0	124.1	112.1	99.0	93.0	87.8	85.2
80°	97.7	100.8	101.8	99.2	96.2	87.2	79.2	73.7	68.1	66.2	65.1
82.5°	72.5	75.1	72.5	73.1	66.5	59.2	54.8	52.9	50.5	49.8	48.7
85°	38.6	38.1	37.1	34.6	30.1	29.0	28.6	28.1	27.1	27.6	26.6
87.5°	14.0	13.2	12.0	11.9	12.3	11.7	12.3	12.6	12.9	12.6	13.7
90°	4.1	5.8	7.6	9.4	10.9	12.3	13.6	14.9	16.2	17.2	18.2
92.5°	9.4	9.5	9.6	9.7	10.4	11.7	13.0	14.3	15.6	16.6	17.6
95°	35.0	29.4	23.8	18.3	15.6	15.7	15.9	16.0	16.2	17.2	18.2
97.5°	89.5	93.0	96.5	100.0	92.6	74.3	56.0	37.7	19.4	19.5	19.7
100°	123.9	126.8	129.7	132.6	122.8	100.2	77.7	55.0	32.4	29.6	26.9
102.5°	161.9	164.1	166.3	168.4	168.1	165.0	162.1	159.2	156.3	126.2	96.1
105°	222.8	223.8	224.8	225.7	226.7	227.4	228.3	229.1	229.9	231.4	232.9
107.5°	279.9	280.4	281.0	281.4	282.2	283.3	284.5	285.6	286.7	287.4	288.1
110°	318.9	319.3	319.8	320.4	321.0	322.1	323.0	324.0	325.0	325.4	325.6



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.9	357.9	358.7	359.7	360.3	360.8	361.2	361.7	362.1	362.1	362.0
115°	414.6	415.2	415.7	416.1	416.3	416.1	415.9	415.8	415.7	415.9	416.3
117.5°	467.1	467.8	468.4	469.1	469.7	470.0	470.3	470.7	471.1	471.0	470.9
120°	502.6	503.2	503.9	504.4	504.7	504.5	504.4	504.3	504.1	504.4	504.7
122.5°	535.3	535.6	536.0	536.5	536.8	537.0	537.2	537.4	537.7	537.9	538.1
125°	582.9	583.5	584.2	584.8	584.9	584.7	584.4	584.0	583.7	584.2	584.7
127.5°	627.2	627.4	627.5	627.6	628.1	628.9	629.6	630.4	631.1	631.0	630.9
130°	656.1	656.2	656.4	656.6	656.9	657.3	657.9	658.4	658.8	659.0	659.2
132.5°	682.7	683.1	683.3	683.6	684.1	684.7	685.3	685.9	686.5	686.7	686.9
135°	722.1	721.9	721.7	721.6	721.8	722.5	723.1	723.8	724.4	724.7	725.1
137.5°	757.5	757.6	757.6	757.7	758.1	758.8	759.6	760.3	761.0	761.4	761.7
140°	780.8	781.1	781.5	781.7	782.1	782.4	782.8	783.1	783.3	783.9	784.4
142.5°	801.6	802.3	802.9	803.4	803.8	804.0	804.3	804.5	804.6	805.0	805.3
145°	833.3	833.8	834.2	834.7	835.0	835.0	835.0	835.0	835.0	835.2	835.3
147.5°	858.9	859.8	860.7	861.7	862.0	861.9	861.7	861.5	861.4	861.5	861.7
150°	876.9	877.6	878.3	878.8	879.1	878.9	878.8	878.6	878.4	878.4	878.4
152.5°	892.1	892.6	893.2	893.7	893.8	893.5	893.2	892.9	892.6	892.9	893.2
155°	913.2	913.4	913.6	913.8	913.6	913.1	912.6	912.1	911.6	912.3	912.9
157.5°	931.1	931.0	930.9	930.9	930.5	929.9	929.4	928.9	928.3	929.2	930.0
160°	941.3	940.8	940.4	939.9	939.5	939.4	939.2	939.1	938.9	939.9	940.8
162.5°	950.6	950.0	949.4	948.8	948.4	948.2	948.1	947.9	947.7	948.8	949.7
165°	962.4	961.6	960.7	960.0	959.5	959.5	959.5	959.5	959.5	960.8	962.1
167.5°	971.8	970.9	970.1	969.2	968.7	968.7	968.6	968.5	968.4	969.8	971.3
170°	976.9	976.0	975.0	974.0	973.6	973.7	973.9	974.1	974.3	975.5	976.9
172.5°	980.5	979.5	978.5	977.6	977.1	977.3	977.5	977.6	977.8	979.1	980.4
175°	984.3	983.4	982.4	981.4	981.0	981.2	981.3	981.5	981.7	983.1	984.6
177.5°	986.2	985.2	984.3	983.4	983.1	983.4	983.6	983.9	984.1	985.1	986.3
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2	1244.2
2.5°	1305.1	1306.7	1308.0	1311.9	1312.3	1316.0	1312.3
5°	1413.1	1420.1	1431.2	1442.2	1443.2	1450.2	1437.7
7.5°	1534.2	1550.5	1560.6	1578.4	1585.5	1589.9	1582.6
10°	1617.6	1632.7	1659.3	1672.3	1685.3	1687.3	1681.3
12.5°	1698.3	1722.1	1743.0	1767.7	1767.1	1784.8	1778.3
15°	1805.6	1830.1	1859.3	1886.8	1896.9	1896.9	1904.9
17.5°	1882.2	1927.2	1957.3	1979.0	2002.6	2006.7	2003.9
20°	1933.9	1982.5	2014.7	2042.7	2058.8	2063.2	2063.2
22.5°	1972.5	2013.8	2045.1	2070.4	2083.6	2089.0	2087.4
25°	1999.1	2034.7	2053.7	2061.2	2064.7	2063.8	2054.3
27.5°	1962.6	1961.0	1949.0	1925.9	1908.6	1898.0	1886.0
30°	1892.8	1866.8	1836.7	1803.6	1761.0	1728.4	1718.3
32.5°	1788.9	1730.4	1679.5	1624.4	1578.6	1546.0	1532.3
35°	1588.1	1495.3	1419.7	1353.5	1305.3	1275.3	1265.3
37.5°	1349.6	1259.9	1166.2	1102.0	1062.2	1031.7	1020.4
40°	1198.1	1100.3	1018.6	958.5	917.4	887.8	887.3
42.5°	1059.7	966.4	889.5	846.1	801.8	782.3	782.2
45°	867.7	793.1	727.8	693.8	667.2	651.2	646.7
47.5°	718.4	656.7	613.2	586.1	564.4	554.2	547.6
50°	634.6	580.5	545.9	522.4	510.3	497.3	496.2
52.5°	564.9	521.1	494.2	475.0	459.8	451.9	452.1
55°	474.7	440.2	421.0	406.5	394.5	388.5	386.0
57.5°	399.9	374.0	360.1	346.8	341.7	337.0	335.6
60°	353.4	335.8	322.8	312.3	304.8	303.3	302.7
62.5°	314.9	296.5	287.6	279.4	273.9	271.5	270.7
65°	259.7	246.1	238.1	231.6	229.6	226.1	225.6
67.5°	209.3	201.2	195.9	191.4	188.7	188.5	188.5
70°	178.4	173.9	169.5	166.9	165.4	164.4	164.4
72.5°	152.0	148.6	145.0	143.6	143.4	142.3	141.9
75°	115.8	112.3	112.8	110.3	108.3	105.8	104.2
77.5°	82.1	79.6	79.1	78.8	77.1	76.8	77.6
80°	63.6	61.2	60.7	61.2	60.7	59.2	59.2
82.5°	48.4	46.3	45.8	45.5	45.1	45.5	44.7
85°	26.1	25.1	25.1	25.1	26.1	25.5	25.1
87.5°	13.1	12.8	13.4	13.0	13.1	12.8	13.3
90°	19.1	20.2	20.8	21.1	21.5	21.8	22.1
92.5°	18.6	19.5	20.1	20.2	20.2	20.3	20.4
95°	19.1	20.2	20.7	20.9	21.0	21.2	21.4
97.5°	19.8	19.9	20.0	20.2	20.3	20.5	20.6
100°	24.0	21.3	20.0	20.2	20.3	20.5	20.6
102.5°	66.2	36.1	21.1	21.1	21.1	21.2	21.2
105°	234.3	235.8	233.7	227.7	221.8	215.9	210.0
107.5°	288.8	289.5	290.2	290.9	291.4	292.1	292.8
110°	326.0	326.3	326.7	327.3	327.7	328.2	328.7



TEST NUMBER: P332937-830

CATALOG NUMBER: SA4XXRDIP-C795D810U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	361.9	361.8	362.1	362.8	363.4	364.0	364.7
115°	416.6	417.0	417.2	417.2	417.2	417.2	417.2
117.5°	470.9	470.8	470.7	470.7	470.6	470.5	470.5
120°	505.1	505.4	505.4	505.1	504.7	504.4	504.1
122.5°	538.3	538.5	538.4	538.1	537.7	537.4	537.1
125°	585.1	585.6	586.0	586.2	586.3	586.4	586.6
127.5°	630.8	630.7	630.7	630.5	630.4	630.3	630.1
130°	659.3	659.5	659.6	659.6	659.6	659.6	659.6
132.5°	687.0	687.2	687.2	687.1	686.9	686.8	686.7
135°	725.4	725.8	726.0	726.4	726.7	727.1	727.4
137.5°	762.0	762.4	762.5	762.4	762.3	762.2	762.1
140°	784.9	785.3	785.7	785.9	786.0	786.2	786.4
142.5°	805.7	806.1	806.3	806.3	806.3	806.3	806.3
145°	835.5	835.7	835.8	836.2	836.5	836.9	837.2
147.5°	861.8	861.9	862.0	862.2	862.3	862.5	862.7
150°	878.4	878.4	878.5	878.7	878.8	879.0	879.2
152.5°	893.4	893.6	893.7	893.6	893.5	893.4	893.3
155°	913.6	914.3	914.4	913.8	913.3	912.9	912.4
157.5°	930.9	931.7	931.7	930.9	930.0	929.2	928.3
160°	941.9	942.8	942.8	941.9	940.8	939.9	938.9
162.5°	950.6	951.7	951.6	950.5	949.3	948.3	947.2
165°	963.5	964.8	964.7	963.2	961.8	960.3	958.8
167.5°	972.7	974.1	974.0	972.4	970.7	969.1	967.5
170°	978.2	979.5	979.3	977.7	976.1	974.4	972.8
172.5°	981.8	983.1	982.8	981.1	979.3	977.5	975.7
175°	986.1	987.5	987.3	985.3	983.4	981.4	979.4
177.5°	987.3	988.4	988.1	986.5	985.0	983.4	981.8
180°	985.3	985.3	985.3	985.3	985.3	985.3	985.3

(END OF REPORT)