

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332987-840

Luminaire Tested: **SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332987-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6380.8 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	105	101	97	94	100	97	93	90	89	86	84	81	79	77	75	73	72	68
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	67	64	61	58
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53	50
4	81	70	62	56	77	68	60	55	63	57	52	58	53	49	54	50	46	44
5	75	63	55	49	71	61	53	48	57	50	45	52	47	43	49	44	41	38
6	69	57	49	43	66	55	47	42	51	45	40	48	42	38	44	40	36	34
7	64	52	44	38	62	50	43	37	47	40	36	44	38	34	41	36	32	30
8	60	47	40	34	57	46	38	33	43	37	32	40	35	31	37	33	29	27
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27	25
10	53	40	33	28	50	39	32	27	37	30	26	34	29	25	32	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16156	16156	16156	16156
5°	18739	16204	14323	16204
10°	22168	16133	12782	16133
15°	25607	15984	10984	15984
20°	28511	15779	9933	15779
25°	29432	15577	9222	15577
30°	25765	15333	8793	15333
35°	20056	14970	8535	14970
40°	15039	14556	8395	14556
45°	11875	13891	8322	13891
50°	10025	13123	8081	13123
55°	8739	12279	7648	12279
60°	7863	11404	6770	11404
65°	6930	10457	5822	10457
70°	6243	9477	5254	9477
75°	5231	8400	4476	8400
80°	4421	7159	4198	7159
85°	3733	5604	3733	5604



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.9	3.0
10°-20°	584.9	9.2
20°-30°	914.8	14.3
30°-40°	1017.0	15.9
40°-50°	902.3	14.1
50°-60°	703.1	11.0
60°-70°	460.3	7.2
70°-80°	226.4	3.5
80°-90°	56.9	0.9
90°-100°	131.2	2.1
100°-110°	273.1	4.3
110°-120°	244.6	3.8
120°-130°	205.8	3.2
130°-140°	171.6	2.7
140°-150°	131.1	2.1
150°-160°	92.1	1.4
160°-170°	54.2	0.8
170°-180°	17.6	0.3
0°-30°	1693.6	26.5
0°-40°	2710.6	42.5
0°-60°	4316.0	67.6
0°-90°	5059.6	79.3
90°-120°	648.9	10.2
90°-150°	1157.3	18.1
90°-180°	1321.0	20.7
0°-180°	6380.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2001	2001	2001	2001	2001	
5°	2312	2000	1767	2000	2312	234
15°	3064	1912	1314	1912	3064	871
25°	3304	1749	1035	1749	3304	1466
35°	2035	1519	866	1519	2035	1276
45°	1040	1217	729	1217	1040	824
55°	621	872	543	872	621	565
65°	363	547	305	547	363	365
75°	168	269	144	269	168	185
85°	40	60	40	60	40	46
90°	8	0	8	0	8	8
95°	87	12	87	12	87	135
105°	502	42	502	42	502	496
115°	482	74	482	74	482	479
125°	385	102	385	102	385	350
135°	344	122	344	122	344	266
145°	281	140	281	140	281	178
155°	235	160	235	160	235	110
165°	205	174	205	174	205	59
175°	185	181	185	181	185	18
180°	182	182	182	182	182	



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2110.8	2116.7	2110.8	2110.2	2103.8	2101.8	2099.2	2090.8	2075.4	2066.4	2068.3
5°	2312.4	2332.6	2321.3	2319.7	2302.0	2284.2	2272.9	2247.2	2219.7	2201.2	2185.9
7.5°	2545.6	2557.2	2550.1	2538.8	2510.1	2493.9	2467.7	2433.7	2384.5	2346.9	2312.6
10°	2704.3	2713.9	2710.8	2689.8	2668.8	2626.1	2601.9	2554.4	2492.2	2443.1	2397.1
12.5°	2860.3	2870.7	2842.4	2843.3	2803.6	2770.0	2731.6	2671.7	2600.0	2536.6	2479.0
15°	3063.9	3051.0	3051.0	3034.8	2990.5	2943.8	2904.3	2841.4	2751.1	2675.2	2595.5
17.5°	3223.2	3227.7	3221.1	3183.1	3148.3	3099.9	3027.5	2954.1	2870.2	2768.4	2686.8
20°	3318.7	3318.7	3311.4	3285.6	3240.5	3188.9	3110.7	3030.8	2924.4	2822.0	2730.1
22.5°	3357.4	3359.9	3351.4	3330.1	3289.5	3239.1	3172.6	3091.5	2981.8	2866.5	2752.7
25°	3304.2	3319.5	3321.0	3315.5	3303.4	3272.7	3215.5	3132.4	3034.0	2909.1	2786.5
27.5°	3033.5	3052.9	3069.9	3097.8	3134.8	3154.2	3156.7	3114.5	3028.7	2908.4	2785.1
30°	2763.9	2780.1	2832.5	2901.0	2954.3	3002.6	3044.5	3055.9	3007.5	2899.4	2769.6
32.5°	2464.7	2486.6	2539.0	2612.7	2701.4	2783.3	2877.5	2925.5	2924.3	2859.4	2739.3
35°	2035.1	2051.2	2099.6	2177.0	2283.4	2405.2	2554.4	2670.4	2749.5	2743.8	2670.4
37.5°	1641.2	1659.5	1708.4	1772.5	1875.7	2026.5	2170.8	2330.8	2476.9	2559.0	2534.5
40°	1427.1	1427.9	1475.5	1541.7	1638.4	1769.8	1927.0	2104.4	2267.2	2400.3	2426.1
42.5°	1258.1	1258.3	1289.7	1361.0	1430.7	1554.4	1704.5	1880.6	2071.2	2224.8	2293.2
45°	1040.1	1047.3	1073.2	1115.9	1170.7	1275.6	1395.6	1559.3	1773.0	1955.2	2068.9
47.5°	880.8	891.4	907.9	942.7	986.4	1056.2	1155.6	1302.6	1476.4	1676.9	1838.7
50°	798.2	799.8	820.8	840.1	878.1	933.7	1020.8	1143.3	1302.9	1495.6	1675.5
52.5°	727.3	726.9	739.5	764.1	794.9	838.2	908.5	1020.1	1161.6	1334.4	1520.0
55°	620.9	624.9	634.5	653.9	677.3	707.9	763.6	847.4	958.7	1106.2	1274.8
57.5°	539.9	542.0	549.6	557.7	579.3	601.5	643.3	701.5	795.4	916.1	1073.2
60°	487.0	487.8	490.2	502.3	519.3	540.2	568.5	617.6	696.6	807.1	931.3
62.5°	435.4	436.9	440.6	449.4	462.5	477.0	506.5	546.0	611.5	705.8	817.7
65°	362.8	363.7	369.3	372.5	382.9	395.9	417.7	444.2	489.4	568.5	653.1
67.5°	303.2	303.2	303.5	307.8	315.1	323.7	336.7	358.0	392.0	440.6	515.2
70°	264.5	264.5	266.1	268.5	272.6	279.7	287.0	303.2	328.2	367.7	425.0
72.5°	228.3	228.9	230.6	231.1	233.2	239.1	244.5	254.8	273.4	303.2	349.4
75°	167.7	170.2	174.2	177.4	181.4	180.6	186.2	192.7	198.3	216.1	242.7
77.5°	124.8	123.5	124.0	126.7	127.2	128.1	132.1	137.0	141.3	149.7	159.2
80°	95.1	95.1	97.6	98.4	97.6	98.4	102.4	104.8	106.4	109.7	118.6
82.5°	71.9	73.2	72.4	73.2	73.7	74.5	77.9	78.4	80.0	81.3	85.0
85°	40.3	41.1	41.9	40.3	40.3	40.3	41.9	42.7	44.3	43.5	45.1
87.5°	15.7	15.0	15.8	15.7	16.3	15.7	16.2	17.4	16.1	16.8	16.7
90°	7.5	7.5	7.9	7.5	7.2	7.2	6.8	6.5	6.1	6.5	5.8
92.5°	27.5	27.5	28.7	30.6	34.8	42.0	52.7	70.1	94.3	113.2	99.1
95°	87.1	91.7	98.2	109.2	126.7	161.3	209.1	264.5	299.1	290.8	219.5
97.5°	232.8	240.2	251.0	272.4	298.0	335.3	370.2	390.7	375.8	306.4	205.4
100°	327.3	330.1	340.8	362.6	393.6	420.1	437.6	430.4	378.3	287.0	186.3
102.5°	409.5	411.8	423.1	438.9	457.9	468.9	463.8	428.5	356.9	262.7	173.5
105°	502.2	504.3	509.3	512.2	511.5	496.9	461.5	399.7	318.0	234.1	162.4
107.5°	536.5	535.6	532.1	523.9	506.3	474.4	424.7	359.0	286.6	218.1	160.4
110°	537.1	533.9	527.6	512.5	487.2	448.0	396.2	334.5	270.9	212.7	161.0



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	520.3	515.1	506.1	488.0	459.2	419.9	371.0	316.4	262.1	210.2	162.7
115°	482.2	479.4	467.9	446.5	418.3	384.1	342.2	298.4	253.8	208.8	165.9
117.5°	443.5	441.3	429.8	411.8	387.8	358.7	325.9	289.5	250.0	208.4	169.5
120°	421.9	418.0	408.7	392.9	372.6	347.3	318.7	285.5	248.0	208.4	172.1
122.5°	404.8	400.8	392.9	379.5	362.3	340.1	314.2	282.1	245.8	208.1	174.6
125°	384.8	382.6	375.9	365.5	351.2	331.5	306.9	276.3	242.0	207.7	178.4
127.5°	373.0	370.9	365.2	356.0	341.6	323.1	298.4	269.1	236.9	206.9	181.6
130°	366.2	364.1	358.3	349.4	334.8	315.9	291.6	263.4	233.8	206.6	183.8
132.5°	358.5	356.4	350.9	340.8	326.5	307.6	283.9	257.4	231.0	206.4	185.8
135°	344.1	341.9	336.2	326.2	311.9	294.1	272.4	249.1	226.6	205.9	188.8
137.5°	326.2	323.7	318.9	309.1	295.7	279.6	261.3	241.7	223.0	205.9	190.6
140°	313.4	310.5	305.5	297.7	285.2	270.1	254.1	237.3	221.0	205.6	192.0
142.5°	299.6	297.7	293.3	286.0	274.9	261.9	248.1	233.4	219.2	205.6	193.2
145°	280.8	279.1	275.5	269.4	260.5	250.5	239.8	227.7	216.3	204.9	193.8
147.5°	264.3	263.6	260.9	255.7	249.1	241.3	232.7	223.1	213.7	203.6	194.2
150°	254.8	254.5	252.4	247.7	242.0	235.6	228.4	220.3	211.7	202.7	194.2
152.5°	246.3	245.9	244.6	240.9	236.0	230.8	224.2	217.1	209.3	201.3	193.6
155°	235.2	235.2	234.1	231.3	227.7	223.4	218.0	212.4	205.9	199.1	192.8
157.5°	225.5	225.5	224.9	222.7	220.0	216.6	212.1	207.3	202.5	196.9	191.8
160°	219.5	219.5	219.1	217.0	214.9	212.0	208.0	204.2	199.9	195.2	191.0
162.5°	213.8	214.1	213.7	211.6	210.1	207.4	204.4	201.1	197.6	193.5	190.1
165°	205.2	205.6	205.9	204.5	203.1	201.3	198.8	196.6	193.8	191.0	188.4
167.5°	198.4	198.7	198.8	197.8	197.1	196.1	194.1	192.5	190.4	188.3	186.7
170°	194.2	194.2	194.5	194.2	193.5	192.4	191.0	189.9	188.1	186.6	185.6
172.5°	189.9	190.5	190.8	190.5	190.1	189.2	188.3	187.6	186.1	184.9	184.5
175°	184.9	185.6	186.3	185.6	185.6	185.6	184.9	184.5	183.8	183.1	183.1
177.5°	182.0	182.5	183.1	182.8	183.1	182.8	182.8	182.5	182.3	182.0	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2061.8	2052.9	2048.3	2038.0	2025.7	2019.2	2013.5	2005.1	1994.1	1982.5	1974.1
5°	2166.5	2147.2	2122.9	2094.0	2068.1	2043.2	2021.3	1999.6	1974.6	1948.8	1923.0
7.5°	2273.9	2235.8	2194.7	2147.2	2100.8	2058.8	2020.0	1983.0	1941.1	1903.5	1869.3
10°	2348.7	2297.1	2239.9	2179.4	2118.9	2066.5	2014.9	1968.1	1916.5	1870.6	1831.9
12.5°	2409.3	2348.7	2279.9	2204.5	2131.8	2068.4	2009.1	1948.1	1889.5	1839.7	1788.1
15°	2509.9	2426.9	2334.2	2243.9	2149.6	2063.3	1983.5	1912.5	1845.6	1775.4	1726.3
17.5°	2579.2	2480.6	2367.9	2259.4	2148.0	2046.2	1954.1	1869.7	1792.4	1720.8	1662.2
20°	2620.4	2511.5	2386.6	2263.2	2138.3	2029.4	1930.3	1836.7	1756.9	1679.5	1619.0
22.5°	2643.6	2523.1	2386.6	2257.5	2128.0	2010.0	1901.2	1803.8	1716.9	1639.5	1572.6
25°	2651.1	2522.0	2382.6	2234.2	2092.3	1967.3	1854.4	1748.8	1652.0	1574.7	1503.7
27.5°	2640.8	2488.8	2346.0	2193.7	2047.3	1915.6	1797.1	1686.1	1589.2	1506.1	1433.4
30°	2625.2	2462.4	2309.2	2151.2	2002.8	1876.2	1751.2	1644.9	1544.1	1457.7	1384.4
32.5°	2591.7	2430.1	2265.3	2103.4	1953.2	1822.7	1704.1	1597.1	1498.2	1410.1	1332.1
35°	2525.3	2361.6	2182.6	2016.5	1869.0	1733.5	1622.2	1519.0	1424.7	1330.4	1248.1
37.5°	2437.7	2270.5	2092.4	1910.6	1762.8	1635.0	1532.9	1436.0	1343.9	1257.8	1166.7
40°	2355.2	2202.8	2018.9	1838.4	1686.8	1563.4	1469.1	1381.2	1288.5	1203.0	1111.9
42.5°	2255.2	2125.4	1939.6	1758.4	1608.7	1489.9	1402.0	1316.1	1231.7	1148.8	1053.8
45°	2088.3	1989.9	1815.7	1641.6	1490.9	1373.1	1292.5	1216.7	1142.5	1063.5	974.0
47.5°	1897.0	1830.4	1680.1	1501.8	1362.3	1256.4	1178.5	1116.5	1053.8	974.8	896.3
50°	1764.1	1721.4	1576.3	1413.4	1280.4	1182.9	1103.0	1044.9	992.5	916.8	846.6
52.5°	1622.2	1599.5	1476.9	1321.2	1192.7	1097.0	1028.9	976.5	923.5	860.6	795.0
55°	1406.1	1418.3	1314.2	1179.6	1058.6	978.1	915.9	872.4	827.3	774.1	723.3
57.5°	1185.3	1229.4	1159.6	1041.4	928.1	853.5	806.8	770.1	732.3	688.1	644.7
60°	1053.0	1090.0	1050.6	946.5	847.4	778.1	734.6	706.3	668.4	628.1	595.0
62.5°	924.0	963.7	940.3	856.3	764.2	704.6	666.1	639.9	611.7	576.5	542.2
65°	761.9	787.7	776.5	718.4	653.1	602.3	566.8	547.4	521.7	495.8	465.2
67.5°	583.6	633.4	626.8	596.0	539.6	499.9	476.7	459.6	436.1	416.9	396.1
70°	479.8	525.7	524.9	499.9	469.3	432.1	416.1	401.5	380.5	362.0	345.1
72.5°	392.6	434.7	441.0	421.8	400.9	372.8	357.4	347.4	327.0	314.3	300.5
75°	275.0	305.6	313.7	313.7	304.0	289.4	275.8	269.3	254.8	243.5	235.4
77.5°	180.3	199.7	212.2	215.1	216.6	211.8	200.5	195.9	184.8	180.8	173.0
80°	127.3	140.3	154.8	159.7	163.7	162.1	157.2	154.0	143.5	139.5	136.2
82.5°	88.1	95.1	107.0	117.8	116.5	120.8	116.5	114.0	106.1	104.6	101.4
85°	45.9	46.8	48.4	55.6	59.7	61.3	62.1	60.5	58.1	58.1	52.4
87.5°	16.5	15.9	16.7	16.7	17.3	19.8	21.5	22.0	20.2	18.5	16.7
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	72.1	44.4	26.3	18.9	13.6	9.3	6.0	4.0	6.0	9.3	13.6
95°	134.2	75.6	44.6	29.6	21.1	16.5	12.8	11.8	12.8	16.5	21.1
97.5°	120.7	72.3	48.4	35.9	28.5	24.2	21.1	21.1	21.1	24.2	28.5
100°	113.5	73.2	52.1	40.7	33.9	29.6	27.2	27.2	27.2	29.6	33.9
102.5°	111.5	76.0	57.0	46.2	39.6	35.6	33.4	32.8	33.4	35.6	39.6
105°	112.4	82.8	65.6	55.3	48.9	44.6	42.8	41.8	42.8	44.6	48.9
107.5°	117.8	90.7	75.0	64.8	58.7	54.1	52.3	51.6	52.3	54.1	58.7
110°	121.7	96.7	81.0	71.4	64.9	60.7	58.9	58.2	58.9	60.7	64.9



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.0	102.4	87.3	77.7	71.2	67.3	65.1	64.4	65.1	67.3	71.2
115°	132.8	111.4	97.0	87.5	80.7	77.1	74.6	73.5	74.6	77.1	80.7
117.5°	139.7	120.0	106.4	96.4	90.1	86.1	83.9	82.9	83.9	86.1	90.1
120°	144.5	126.0	112.4	102.4	96.3	92.4	90.0	89.3	90.0	92.4	96.3
122.5°	149.2	131.7	118.2	108.5	101.8	98.2	95.6	94.9	95.6	98.2	101.8
125°	155.9	139.6	126.7	116.7	110.0	106.0	103.8	102.4	103.8	106.0	110.0
127.5°	161.9	146.8	134.4	124.3	117.2	112.8	110.2	109.1	110.2	112.8	117.2
130°	165.6	151.7	139.6	129.2	122.4	117.0	114.2	112.8	114.2	117.0	122.4
132.5°	169.4	155.7	143.5	133.8	126.4	121.4	117.6	116.5	117.6	121.4	126.4
135°	174.2	161.3	149.6	140.3	132.8	126.7	123.1	121.7	123.1	126.7	132.8
137.5°	177.6	165.6	154.6	145.7	137.9	132.2	128.3	126.9	128.3	132.2	137.9
140°	179.9	168.4	157.7	149.2	141.7	135.6	131.7	130.7	131.7	135.6	141.7
142.5°	181.6	171.1	160.6	152.3	145.1	139.4	135.7	134.6	135.7	139.4	145.1
145°	183.5	173.8	164.5	156.7	149.9	144.9	141.4	140.3	141.4	144.9	149.9
147.5°	185.1	176.6	167.9	160.9	155.2	150.2	146.9	146.6	146.9	150.2	155.2
150°	185.9	178.1	170.3	163.5	158.1	153.8	151.0	150.6	151.0	153.8	158.1
152.5°	186.5	179.3	172.3	166.0	161.3	157.2	154.4	154.3	154.4	157.2	161.3
155°	187.0	181.0	174.9	169.6	165.6	162.1	159.9	159.6	159.9	162.1	165.6
157.5°	187.0	182.2	177.0	172.8	169.4	166.6	164.6	164.6	164.6	166.6	169.4
160°	187.0	182.8	178.4	174.5	171.7	169.2	167.7	167.7	167.7	169.2	171.7
162.5°	187.0	183.3	179.4	176.2	173.7	171.5	170.4	170.6	170.4	171.5	173.7
165°	186.3	183.5	180.3	178.1	176.3	174.5	173.8	173.8	173.8	174.5	176.3
167.5°	185.4	183.4	181.1	179.4	178.3	177.0	176.6	177.0	176.6	177.0	178.3
170°	184.9	183.1	181.3	180.3	179.6	178.4	178.1	178.4	178.1	178.4	179.6
172.5°	184.3	182.8	181.6	180.8	180.4	179.6	179.6	179.9	179.6	179.6	180.4
175°	183.5	182.4	181.7	181.7	181.3	181.0	181.0	181.3	181.0	181.0	181.3
177.5°	182.5	182.0	181.7	181.7	181.7	181.4	181.7	182.0	181.7	181.4	181.7
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1965.1	1958.6	1950.3	1940.6	1928.9	1918.6	1914.1	1918.0	1920.0	1914.8	1914.1
5°	1905.2	1885.1	1869.0	1844.8	1825.4	1809.3	1798.1	1793.2	1794.8	1781.9	1778.7
7.5°	1838.1	1814.1	1787.7	1759.0	1732.2	1708.5	1696.1	1689.3	1675.7	1669.8	1660.0
10°	1794.8	1762.5	1736.8	1702.8	1672.2	1644.1	1630.3	1619.0	1605.3	1598.8	1585.2
12.5°	1750.3	1712.8	1684.5	1649.3	1618.0	1584.1	1570.9	1550.0	1528.5	1515.0	1497.4
15°	1687.6	1642.4	1607.7	1565.8	1528.7	1490.1	1455.3	1416.6	1402.1	1371.5	1353.7
17.5°	1614.2	1568.4	1525.5	1469.3	1412.0	1363.9	1327.0	1289.9	1267.7	1248.1	1239.1
20°	1565.8	1523.9	1464.2	1398.9	1335.2	1282.0	1252.1	1228.0	1203.8	1190.1	1180.4
22.5°	1520.0	1466.4	1397.1	1326.7	1262.9	1221.3	1196.1	1171.2	1151.5	1138.5	1125.6
25°	1443.3	1373.1	1299.7	1219.1	1175.6	1139.3	1111.9	1091.7	1079.6	1062.7	1056.2
27.5°	1364.4	1279.4	1198.5	1144.3	1098.9	1065.7	1041.9	1026.7	1011.4	1000.6	992.2
30°	1303.7	1217.5	1144.9	1093.3	1047.3	1020.0	1000.6	982.9	970.8	961.9	955.4
32.5°	1243.7	1157.5	1096.5	1041.1	1004.8	978.1	957.4	944.1	934.6	923.2	919.3
35°	1157.0	1080.5	1027.2	977.2	940.1	915.9	899.8	886.2	878.1	874.8	872.4
37.5°	1073.7	1010.9	953.7	912.7	879.7	860.6	841.6	834.9	829.3	823.5	826.2
40°	1020.8	961.9	911.1	867.6	840.9	820.0	808.7	800.6	795.8	795.8	795.8
42.5°	974.9	917.4	867.9	828.9	802.2	784.6	771.9	765.2	763.6	763.0	766.8
45°	903.8	850.6	800.6	768.4	745.8	728.1	720.8	715.2	715.2	718.4	719.2
47.5°	833.3	783.6	743.4	707.3	686.6	675.5	669.2	666.3	666.6	669.8	673.6
50°	790.1	740.9	701.5	669.2	649.8	639.3	633.7	632.2	633.7	633.7	639.3
52.5°	743.1	699.0	660.1	633.1	611.2	601.4	598.2	596.0	596.9	599.6	602.0
55°	674.1	634.5	597.4	571.7	555.5	549.1	541.8	542.6	541.0	542.6	542.6
57.5°	604.9	569.4	534.9	514.4	500.2	490.9	482.9	485.2	482.8	482.5	481.2
60°	560.4	521.7	494.2	475.7	459.6	451.5	444.2	445.9	443.4	441.8	438.6
62.5°	512.0	479.8	453.6	435.8	422.8	413.4	406.2	404.6	399.0	393.4	386.4
65°	441.8	415.3	391.8	375.0	362.8	355.6	349.9	345.1	333.0	320.1	313.7
67.5°	373.7	354.5	332.6	318.3	308.5	299.0	288.2	279.9	268.6	261.6	257.5
70°	329.7	311.2	292.7	278.9	268.5	259.6	247.5	241.9	233.8	230.6	226.6
72.5°	287.8	270.5	253.4	241.0	229.7	222.9	213.4	207.7	204.2	202.9	198.8
75°	224.2	210.5	197.5	186.2	177.4	172.6	168.5	164.5	162.9	155.6	151.6
77.5°	163.5	154.5	146.4	138.4	132.1	128.9	121.1	116.4	113.7	110.3	109.5
80°	127.3	121.0	112.9	108.1	99.2	95.9	92.7	91.9	91.1	90.3	89.5
82.5°	95.8	89.4	81.3	78.4	75.9	74.0	72.1	71.3	70.5	71.0	70.8
85°	48.4	45.1	45.1	44.3	43.5	42.7	41.9	41.9	41.1	41.9	41.1
87.5°	16.7	16.1	16.5	15.1	16.0	16.2	15.5	15.5	16.2	14.9	14.9
90°	2.8	2.8	4.9	4.9	5.8	6.5	6.1	6.5	6.8	7.2	7.2
92.5°	18.9	26.3	44.4	72.1	99.1	113.2	94.3	70.1	52.7	42.0	34.8
95°	29.6	44.6	75.6	134.2	219.5	290.8	299.1	264.5	209.1	161.3	126.7
97.5°	35.9	48.4	72.3	120.7	205.4	306.4	375.8	390.7	370.2	335.3	298.0
100°	40.7	52.1	73.2	113.5	186.3	287.0	378.3	430.4	437.6	420.1	393.6
102.5°	46.2	57.0	76.0	111.5	173.5	262.7	356.9	428.5	463.8	468.9	457.9
105°	55.3	65.6	82.8	112.4	162.4	234.1	318.0	399.7	461.5	496.9	511.5
107.5°	64.8	75.0	90.7	117.8	160.4	218.1	286.6	359.0	424.7	474.4	506.3
110°	71.4	81.0	96.7	121.7	161.0	212.7	270.9	334.5	396.2	448.0	487.2



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	77.7	87.3	102.4	126.0	162.7	210.2	262.1	316.4	371.0	419.9	459.2
115°	87.5	97.0	111.4	132.8	165.9	208.8	253.8	298.4	342.2	384.1	418.3
117.5°	96.4	106.4	120.0	139.7	169.5	208.4	250.0	289.5	325.9	358.7	387.8
120°	102.4	112.4	126.0	144.5	172.1	208.4	248.0	285.5	318.7	347.3	372.6
122.5°	108.5	118.2	131.7	149.2	174.6	208.1	245.8	282.1	314.2	340.1	362.3
125°	116.7	126.7	139.6	155.9	178.4	207.7	242.0	276.3	306.9	331.5	351.2
127.5°	124.3	134.4	146.8	161.9	181.6	206.9	236.9	269.1	298.4	323.1	341.6
130°	129.2	139.6	151.7	165.6	183.8	206.6	233.8	263.4	291.6	315.9	334.8
132.5°	133.8	143.5	155.7	169.4	185.8	206.4	231.0	257.4	283.9	307.6	326.5
135°	140.3	149.6	161.3	174.2	188.8	205.9	226.6	249.1	272.4	294.1	311.9
137.5°	145.7	154.6	165.6	177.6	190.6	205.9	223.0	241.7	261.3	279.6	295.7
140°	149.2	157.7	168.4	179.9	192.0	205.6	221.0	237.3	254.1	270.1	285.2
142.5°	152.3	160.6	171.1	181.6	193.2	205.6	219.2	233.4	248.1	261.9	274.9
145°	156.7	164.5	173.8	183.5	193.8	204.9	216.3	227.7	239.8	250.5	260.5
147.5°	160.9	167.9	176.6	185.1	194.2	203.6	213.7	223.1	232.7	241.3	249.1
150°	163.5	170.3	178.1	185.9	194.2	202.7	211.7	220.3	228.4	235.6	242.0
152.5°	166.0	172.3	179.3	186.5	193.6	201.3	209.3	217.1	224.2	230.8	236.0
155°	169.6	174.9	181.0	187.0	192.8	199.1	205.9	212.4	218.0	223.4	227.7
157.5°	172.8	177.0	182.2	187.0	191.8	196.9	202.5	207.3	212.1	216.6	220.0
160°	174.5	178.4	182.8	187.0	191.0	195.2	199.9	204.2	208.0	212.0	214.9
162.5°	176.2	179.4	183.3	187.0	190.1	193.5	197.6	201.1	204.4	207.4	210.1
165°	178.1	180.3	183.5	186.3	188.4	191.0	193.8	196.6	198.8	201.3	203.1
167.5°	179.4	181.1	183.4	185.4	186.7	188.3	190.4	192.5	194.1	196.1	197.1
170°	180.3	181.3	183.1	184.9	185.6	186.6	188.1	189.9	191.0	192.4	193.5
172.5°	180.8	181.6	182.8	184.3	184.5	184.9	186.1	187.6	188.3	189.2	190.1
175°	181.7	181.7	182.4	183.5	183.1	183.1	183.8	184.5	184.9	185.6	185.6
177.5°	181.7	181.7	182.0	182.5	182.0	182.0	182.3	182.5	182.8	182.8	183.1
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1910.3	1911.6	1907.0	1905.7	1907.0	1911.6	1910.3	1914.1	1914.8	1920.0	1918.0
5°	1772.2	1770.6	1766.6	1767.4	1766.6	1770.6	1772.2	1778.7	1781.9	1794.8	1793.2
7.5°	1654.2	1647.9	1649.6	1643.3	1649.6	1647.9	1654.2	1660.0	1669.8	1675.7	1689.3
10°	1582.0	1573.1	1565.8	1559.3	1565.8	1573.1	1582.0	1585.2	1598.8	1605.3	1619.0
12.5°	1483.3	1475.6	1465.8	1467.7	1465.8	1475.6	1483.3	1497.4	1515.0	1528.5	1550.0
15°	1343.2	1331.2	1311.8	1314.2	1311.8	1331.2	1343.2	1353.7	1371.5	1402.1	1416.6
17.5°	1224.8	1224.9	1216.1	1218.1	1216.1	1224.9	1224.8	1239.1	1248.1	1267.7	1289.9
20°	1163.5	1157.8	1158.6	1156.2	1158.6	1157.8	1163.5	1180.4	1190.1	1203.8	1228.0
22.5°	1120.8	1114.0	1108.3	1103.3	1108.3	1114.0	1120.8	1125.6	1138.5	1151.5	1171.2
25°	1048.9	1044.1	1036.9	1035.3	1036.9	1044.1	1048.9	1056.2	1062.7	1079.6	1091.7
27.5°	985.7	984.8	981.9	978.2	981.9	984.8	985.7	992.2	1000.6	1011.4	1026.7
30°	949.0	947.4	945.7	943.3	945.7	947.4	949.0	955.4	961.9	970.8	982.9
32.5°	916.1	915.1	913.5	913.7	913.5	915.1	916.1	919.3	923.2	934.6	944.1
35°	869.2	868.4	866.8	866.0	866.8	868.4	869.2	872.4	874.8	878.1	886.2
37.5°	825.4	827.4	826.5	826.3	826.5	827.4	825.4	826.2	823.5	829.3	834.9
40°	795.0	795.8	797.4	796.6	797.4	795.8	795.0	795.8	795.8	795.8	800.6
42.5°	769.8	770.0	772.2	769.5	772.2	770.0	769.8	766.8	763.0	763.6	765.2
45°	724.9	729.7	728.9	728.9	728.9	729.7	724.9	719.2	718.4	715.2	715.2
47.5°	675.7	679.8	681.0	680.9	681.0	679.8	675.7	673.6	669.8	666.6	666.3
50°	643.4	641.8	644.2	643.4	644.2	641.8	643.4	639.3	633.7	633.7	632.2
52.5°	604.1	604.4	604.2	603.4	604.2	604.4	604.1	602.0	599.6	596.9	596.0
55°	543.4	544.2	542.6	543.4	542.6	544.2	543.4	542.6	542.6	541.0	542.6
57.5°	477.7	473.7	475.3	473.4	475.3	473.7	477.7	481.2	482.5	482.8	485.2
60°	430.6	424.1	422.5	419.3	422.5	424.1	430.6	438.6	441.8	443.4	445.9
62.5°	377.7	373.1	367.7	370.2	367.7	373.1	377.7	386.4	393.4	399.0	404.6
65°	307.2	304.0	301.5	304.8	301.5	304.0	307.2	313.7	320.1	333.0	345.1
67.5°	254.3	252.6	252.6	251.0	252.6	252.6	254.3	257.5	261.6	268.6	279.9
70°	226.6	224.2	224.2	222.6	224.2	224.2	226.6	226.6	230.6	233.8	241.9
72.5°	198.1	195.8	196.4	195.4	196.4	195.8	198.1	198.8	202.9	204.2	207.7
75°	146.7	142.7	142.7	143.5	142.7	142.7	146.7	151.6	155.6	162.9	164.5
77.5°	109.5	108.7	109.8	108.4	109.8	108.7	109.5	109.5	110.3	113.7	116.4
80°	89.5	88.7	87.9	90.3	87.9	88.7	89.5	89.5	90.3	91.1	91.9
82.5°	69.5	69.4	69.2	72.2	69.2	69.4	69.5	70.8	71.0	70.5	71.3
85°	41.9	40.3	41.9	40.3	41.9	40.3	41.9	41.1	41.9	41.1	41.9
87.5°	16.4	15.8	15.0	15.7	15.0	15.8	16.4	14.9	14.9	16.2	15.5
90°	7.5	7.9	7.5	7.5	7.5	7.9	7.5	7.2	7.2	6.8	6.5
92.5°	30.6	28.7	27.5	27.5	27.5	28.7	30.6	34.8	42.0	52.7	70.1
95°	109.2	98.2	91.7	87.1	91.7	98.2	109.2	126.7	161.3	209.1	264.5
97.5°	272.4	251.0	240.2	232.8	240.2	251.0	272.4	298.0	335.3	370.2	390.7
100°	362.6	340.8	330.1	327.3	330.1	340.8	362.6	393.6	420.1	437.6	430.4
102.5°	438.9	423.1	411.8	409.5	411.8	423.1	438.9	457.9	468.9	463.8	428.5
105°	512.2	509.3	504.3	502.2	504.3	509.3	512.2	511.5	496.9	461.5	399.7
107.5°	523.9	532.1	535.6	536.5	535.6	532.1	523.9	506.3	474.4	424.7	359.0
110°	512.5	527.6	533.9	537.1	533.9	527.6	512.5	487.2	448.0	396.2	334.5



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	488.0	506.1	515.1	520.3	515.1	506.1	488.0	459.2	419.9	371.0	316.4
115°	446.5	467.9	479.4	482.2	479.4	467.9	446.5	418.3	384.1	342.2	298.4
117.5°	411.8	429.8	441.3	443.5	441.3	429.8	411.8	387.8	358.7	325.9	289.5
120°	392.9	408.7	418.0	421.9	418.0	408.7	392.9	372.6	347.3	318.7	285.5
122.5°	379.5	392.9	400.8	404.8	400.8	392.9	379.5	362.3	340.1	314.2	282.1
125°	365.5	375.9	382.6	384.8	382.6	375.9	365.5	351.2	331.5	306.9	276.3
127.5°	356.0	365.2	370.9	373.0	370.9	365.2	356.0	341.6	323.1	298.4	269.1
130°	349.4	358.3	364.1	366.2	364.1	358.3	349.4	334.8	315.9	291.6	263.4
132.5°	340.8	350.9	356.4	358.5	356.4	350.9	340.8	326.5	307.6	283.9	257.4
135°	326.2	336.2	341.9	344.1	341.9	336.2	326.2	311.9	294.1	272.4	249.1
137.5°	309.1	318.9	323.7	326.2	323.7	318.9	309.1	295.7	279.6	261.3	241.7
140°	297.7	305.5	310.5	313.4	310.5	305.5	297.7	285.2	270.1	254.1	237.3
142.5°	286.0	293.3	297.7	299.6	297.7	293.3	286.0	274.9	261.9	248.1	233.4
145°	269.4	275.5	279.1	280.8	279.1	275.5	269.4	260.5	250.5	239.8	227.7
147.5°	255.7	260.9	263.6	264.3	263.6	260.9	255.7	249.1	241.3	232.7	223.1
150°	247.7	252.4	254.5	254.8	254.5	252.4	247.7	242.0	235.6	228.4	220.3
152.5°	240.9	244.6	245.9	246.3	245.9	244.6	240.9	236.0	230.8	224.2	217.1
155°	231.3	234.1	235.2	235.2	235.2	234.1	231.3	227.7	223.4	218.0	212.4
157.5°	222.7	224.9	225.5	225.5	225.5	224.9	222.7	220.0	216.6	212.1	207.3
160°	217.0	219.1	219.5	219.5	219.5	219.1	217.0	214.9	212.0	208.0	204.2
162.5°	211.6	213.7	214.1	213.8	214.1	213.7	211.6	210.1	207.4	204.4	201.1
165°	204.5	205.9	205.6	205.2	205.6	205.9	204.5	203.1	201.3	198.8	196.6
167.5°	197.8	198.8	198.7	198.4	198.7	198.8	197.8	197.1	196.1	194.1	192.5
170°	194.2	194.5	194.2	194.2	194.2	194.5	194.2	193.5	192.4	191.0	189.9
172.5°	190.5	190.8	190.5	189.9	190.5	190.8	190.5	190.1	189.2	188.3	187.6
175°	185.6	186.3	185.6	184.9	185.6	186.3	185.6	185.6	185.6	184.9	184.5
177.5°	182.8	183.1	182.5	182.0	182.5	183.1	182.8	183.1	182.8	182.8	182.5
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	1914.1	1918.6	1928.9	1940.6	1950.3	1958.6	1965.1	1974.1	1982.5	1994.1	2005.1
5°	1798.1	1809.3	1825.4	1844.8	1869.0	1885.1	1905.2	1923.0	1948.8	1974.6	1999.6
7.5°	1696.1	1708.5	1732.2	1759.0	1787.7	1814.1	1838.1	1869.3	1903.5	1941.1	1983.0
10°	1630.3	1644.1	1672.2	1702.8	1736.8	1762.5	1794.8	1831.9	1870.6	1916.5	1968.1
12.5°	1570.9	1584.1	1618.0	1649.3	1684.5	1712.8	1750.3	1788.1	1839.7	1889.5	1948.1
15°	1455.3	1490.1	1528.7	1565.8	1607.7	1642.4	1687.6	1726.3	1775.4	1845.6	1912.5
17.5°	1327.0	1363.9	1412.0	1469.3	1525.5	1568.4	1614.2	1662.2	1720.8	1792.4	1869.7
20°	1252.1	1282.0	1335.2	1398.9	1464.2	1523.9	1565.8	1619.0	1679.5	1756.9	1836.7
22.5°	1196.1	1221.3	1262.9	1326.7	1397.1	1466.4	1520.0	1572.6	1639.5	1716.9	1803.8
25°	1111.9	1139.3	1175.6	1219.1	1299.7	1373.1	1443.3	1503.7	1574.7	1652.0	1748.8
27.5°	1041.9	1065.7	1098.9	1144.3	1198.5	1279.4	1364.4	1433.4	1506.1	1589.2	1686.1
30°	1000.6	1020.0	1047.3	1093.3	1144.9	1217.5	1303.7	1384.4	1457.7	1544.1	1644.9
32.5°	957.4	978.1	1004.8	1041.1	1096.5	1157.5	1243.7	1332.1	1410.1	1498.2	1597.1
35°	899.8	915.9	940.1	977.2	1027.2	1080.5	1157.0	1248.1	1330.4	1424.7	1519.0
37.5°	841.6	860.6	879.7	912.7	953.7	1010.9	1073.7	1166.7	1257.8	1343.9	1436.0
40°	808.7	820.0	840.9	867.6	911.1	961.9	1020.8	1111.9	1203.0	1288.5	1381.2
42.5°	771.9	784.6	802.2	828.9	867.9	917.4	974.9	1053.8	1148.8	1231.7	1316.1
45°	720.8	728.1	745.8	768.4	800.6	850.6	903.8	974.0	1063.5	1142.5	1216.7
47.5°	669.2	675.5	686.6	707.3	743.4	783.6	833.3	896.3	974.8	1053.8	1116.5
50°	633.7	639.3	649.8	669.2	701.5	740.9	790.1	846.6	916.8	992.5	1044.9
52.5°	598.2	601.4	611.2	633.1	660.1	699.0	743.1	795.0	860.6	923.5	976.5
55°	541.8	549.1	555.5	571.7	597.4	634.5	674.1	723.3	774.1	827.3	872.4
57.5°	482.9	490.9	500.2	514.4	534.9	569.4	604.9	644.7	688.1	732.3	770.1
60°	444.2	451.5	459.6	475.7	494.2	521.7	560.4	595.0	628.1	668.4	706.3
62.5°	406.2	413.4	422.8	435.8	453.6	479.8	512.0	542.2	576.5	611.7	639.9
65°	349.9	355.6	362.8	375.0	391.8	415.3	441.8	465.2	495.8	521.7	547.4
67.5°	288.2	299.0	308.5	318.3	332.6	354.5	373.7	396.1	416.9	436.1	459.6
70°	247.5	259.6	268.5	278.9	292.7	311.2	329.7	345.1	362.0	380.5	401.5
72.5°	213.4	222.9	229.7	241.0	253.4	270.5	287.8	300.5	314.3	327.0	347.4
75°	168.5	172.6	177.4	186.2	197.5	210.5	224.2	235.4	243.5	254.8	269.3
77.5°	121.1	128.9	132.1	138.4	146.4	154.5	163.5	173.0	180.8	184.8	195.9
80°	92.7	95.9	99.2	108.1	112.9	121.0	127.3	136.2	139.5	143.5	154.0
82.5°	72.1	74.0	75.9	78.4	81.3	89.4	95.8	101.4	104.6	106.1	114.0
85°	41.9	42.7	43.5	44.3	45.1	45.1	48.4	52.4	58.1	58.1	60.5
87.5°	15.5	16.2	16.0	15.1	16.5	16.1	16.7	16.7	18.5	20.2	22.0
90°	6.1	6.5	5.8	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	94.3	113.2	99.1	72.1	44.4	26.3	18.9	13.6	9.3	6.0	4.0
95°	299.1	290.8	219.5	134.2	75.6	44.6	29.6	21.1	16.5	12.8	11.8
97.5°	375.8	306.4	205.4	120.7	72.3	48.4	35.9	28.5	24.2	21.1	21.1
100°	378.3	287.0	186.3	113.5	73.2	52.1	40.7	33.9	29.6	27.2	27.2
102.5°	356.9	262.7	173.5	111.5	76.0	57.0	46.2	39.6	35.6	33.4	32.8
105°	318.0	234.1	162.4	112.4	82.8	65.6	55.3	48.9	44.6	42.8	41.8
107.5°	286.6	218.1	160.4	117.8	90.7	75.0	64.8	58.7	54.1	52.3	51.6
110°	270.9	212.7	161.0	121.7	96.7	81.0	71.4	64.9	60.7	58.9	58.2



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	262.1	210.2	162.7	126.0	102.4	87.3	77.7	71.2	67.3	65.1	64.4
115°	253.8	208.8	165.9	132.8	111.4	97.0	87.5	80.7	77.1	74.6	73.5
117.5°	250.0	208.4	169.5	139.7	120.0	106.4	96.4	90.1	86.1	83.9	82.9
120°	248.0	208.4	172.1	144.5	126.0	112.4	102.4	96.3	92.4	90.0	89.3
122.5°	245.8	208.1	174.6	149.2	131.7	118.2	108.5	101.8	98.2	95.6	94.9
125°	242.0	207.7	178.4	155.9	139.6	126.7	116.7	110.0	106.0	103.8	102.4
127.5°	236.9	206.9	181.6	161.9	146.8	134.4	124.3	117.2	112.8	110.2	109.1
130°	233.8	206.6	183.8	165.6	151.7	139.6	129.2	122.4	117.0	114.2	112.8
132.5°	231.0	206.4	185.8	169.4	155.7	143.5	133.8	126.4	121.4	117.6	116.5
135°	226.6	205.9	188.8	174.2	161.3	149.6	140.3	132.8	126.7	123.1	121.7
137.5°	223.0	205.9	190.6	177.6	165.6	154.6	145.7	137.9	132.2	128.3	126.9
140°	221.0	205.6	192.0	179.9	168.4	157.7	149.2	141.7	135.6	131.7	130.7
142.5°	219.2	205.6	193.2	181.6	171.1	160.6	152.3	145.1	139.4	135.7	134.6
145°	216.3	204.9	193.8	183.5	173.8	164.5	156.7	149.9	144.9	141.4	140.3
147.5°	213.7	203.6	194.2	185.1	176.6	167.9	160.9	155.2	150.2	146.9	146.6
150°	211.7	202.7	194.2	185.9	178.1	170.3	163.5	158.1	153.8	151.0	150.6
152.5°	209.3	201.3	193.6	186.5	179.3	172.3	166.0	161.3	157.2	154.4	154.3
155°	205.9	199.1	192.8	187.0	181.0	174.9	169.6	165.6	162.1	159.9	159.6
157.5°	202.5	196.9	191.8	187.0	182.2	177.0	172.8	169.4	166.6	164.6	164.6
160°	199.9	195.2	191.0	187.0	182.8	178.4	174.5	171.7	169.2	167.7	167.7
162.5°	197.6	193.5	190.1	187.0	183.3	179.4	176.2	173.7	171.5	170.4	170.6
165°	193.8	191.0	188.4	186.3	183.5	180.3	178.1	176.3	174.5	173.8	173.8
167.5°	190.4	188.3	186.7	185.4	183.4	181.1	179.4	178.3	177.0	176.6	177.0
170°	188.1	186.6	185.6	184.9	183.1	181.3	180.3	179.6	178.4	178.1	178.4
172.5°	186.1	184.9	184.5	184.3	182.8	181.6	180.8	180.4	179.6	179.6	179.9
175°	183.8	183.1	183.1	183.5	182.4	181.7	181.7	181.3	181.0	181.0	181.3
177.5°	182.3	182.0	182.0	182.5	182.0	181.7	181.7	181.7	181.4	181.7	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2013.5	2019.2	2025.7	2038.0	2048.3	2052.9	2061.8	2068.3	2066.4	2075.4	2090.8
5°	2021.3	2043.2	2068.1	2094.0	2122.9	2147.2	2166.5	2185.9	2201.2	2219.7	2247.2
7.5°	2020.0	2058.8	2100.8	2147.2	2194.7	2235.8	2273.9	2312.6	2346.9	2384.5	2433.7
10°	2014.9	2066.5	2118.9	2179.4	2239.9	2297.1	2348.7	2397.1	2443.1	2492.2	2554.4
12.5°	2009.1	2068.4	2131.8	2204.5	2279.9	2348.7	2409.3	2479.0	2536.6	2600.0	2671.7
15°	1983.5	2063.3	2149.6	2243.9	2334.2	2426.9	2509.9	2595.5	2675.2	2751.1	2841.4
17.5°	1954.1	2046.2	2148.0	2259.4	2367.9	2480.6	2579.2	2686.8	2768.4	2870.2	2954.1
20°	1930.3	2029.4	2138.3	2263.2	2386.6	2511.5	2620.4	2730.1	2822.0	2924.4	3030.8
22.5°	1901.2	2010.0	2128.0	2257.5	2386.6	2523.1	2643.6	2752.7	2866.5	2981.8	3091.5
25°	1854.4	1967.3	2092.3	2234.2	2382.6	2522.0	2651.1	2786.5	2909.1	3034.0	3132.4
27.5°	1797.1	1915.6	2047.3	2193.7	2346.0	2488.8	2640.8	2785.1	2908.4	3028.7	3114.5
30°	1751.2	1876.2	2002.8	2151.2	2309.2	2462.4	2625.2	2769.6	2899.4	3007.5	3055.9
32.5°	1704.1	1822.7	1953.2	2103.4	2265.3	2430.1	2591.7	2739.3	2859.4	2924.3	2925.5
35°	1622.2	1733.5	1869.0	2016.5	2182.6	2361.6	2525.3	2670.4	2743.8	2749.5	2670.4
37.5°	1532.9	1635.0	1762.8	1910.6	2092.4	2270.5	2437.7	2534.5	2559.0	2476.9	2330.8
40°	1469.1	1563.4	1686.8	1838.4	2018.9	2202.8	2355.2	2426.1	2400.3	2267.2	2104.4
42.5°	1402.0	1489.9	1608.7	1758.4	1939.6	2125.4	2255.2	2293.2	2224.8	2071.2	1880.6
45°	1292.5	1373.1	1490.9	1641.6	1815.7	1989.9	2088.3	2068.9	1955.2	1773.0	1559.3
47.5°	1178.5	1256.4	1362.3	1501.8	1680.1	1830.4	1897.0	1838.7	1676.9	1476.4	1302.6
50°	1103.0	1182.9	1280.4	1413.4	1576.3	1721.4	1764.1	1675.5	1495.6	1302.9	1143.3
52.5°	1028.9	1097.0	1192.7	1321.2	1476.9	1599.5	1622.2	1520.0	1334.4	1161.6	1020.1
55°	915.9	978.1	1058.6	1179.6	1314.2	1418.3	1406.1	1274.8	1106.2	958.7	847.4
57.5°	806.8	853.5	928.1	1041.4	1159.6	1229.4	1185.3	1073.2	916.1	795.4	701.5
60°	734.6	778.1	847.4	946.5	1050.6	1090.0	1053.0	931.3	807.1	696.6	617.6
62.5°	666.1	704.6	764.2	856.3	940.3	963.7	924.0	817.7	705.8	611.5	546.0
65°	566.8	602.3	653.1	718.4	776.5	787.7	761.9	653.1	568.5	489.4	444.2
67.5°	476.7	499.9	539.6	596.0	626.8	633.4	583.6	515.2	440.6	392.0	358.0
70°	416.1	432.1	469.3	499.9	524.9	525.7	479.8	425.0	367.7	328.2	303.2
72.5°	357.4	372.8	400.9	421.8	441.0	434.7	392.6	349.4	303.2	273.4	254.8
75°	275.8	289.4	304.0	313.7	313.7	305.6	275.0	242.7	216.1	198.3	192.7
77.5°	200.5	211.8	216.6	215.1	212.2	199.7	180.3	159.2	149.7	141.3	137.0
80°	157.2	162.1	163.7	159.7	154.8	140.3	127.3	118.6	109.7	106.4	104.8
82.5°	116.5	120.8	116.5	117.8	107.0	95.1	88.1	85.0	81.3	80.0	78.4
85°	62.1	61.3	59.7	55.6	48.4	46.8	45.9	45.1	43.5	44.3	42.7
87.5°	21.5	19.8	17.3	16.7	16.7	15.9	16.5	16.7	16.8	16.1	17.4
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1	6.5
92.5°	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3	70.1
95°	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1	264.5
97.5°	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8	390.7
100°	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3	430.4
102.5°	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9	428.5
105°	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0	399.7
107.5°	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6	359.0
110°	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9	334.5



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1	316.4
115°	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8	298.4
117.5°	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0	289.5
120°	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0	285.5
122.5°	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8	282.1
125°	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0	276.3
127.5°	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9	269.1
130°	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8	263.4
132.5°	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0	257.4
135°	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6	249.1
137.5°	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0	241.7
140°	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0	237.3
142.5°	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2	233.4
145°	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3	227.7
147.5°	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7	223.1
150°	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7	220.3
152.5°	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3	217.1
155°	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9	212.4
157.5°	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5	207.3
160°	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9	204.2
162.5°	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6	201.1
165°	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8	196.6
167.5°	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4	192.5
170°	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1	189.9
172.5°	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1	187.6
175°	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8	184.5
177.5°	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3	182.5
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2	2001.2
2.5°	2099.2	2101.8	2103.8	2110.2	2110.8	2116.7	2110.8
5°	2272.9	2284.2	2302.0	2319.7	2321.3	2332.6	2312.4
7.5°	2467.7	2493.9	2510.1	2538.8	2550.1	2557.2	2545.6
10°	2601.9	2626.1	2668.8	2689.8	2710.8	2713.9	2704.3
12.5°	2731.6	2770.0	2803.6	2843.3	2842.4	2870.7	2860.3
15°	2904.3	2943.8	2990.5	3034.8	3051.0	3051.0	3063.9
17.5°	3027.5	3099.9	3148.3	3183.1	3221.1	3227.7	3223.2
20°	3110.7	3188.9	3240.5	3285.6	3311.4	3318.7	3318.7
22.5°	3172.6	3239.1	3289.5	3330.1	3351.4	3359.9	3357.4
25°	3215.5	3272.7	3303.4	3315.5	3321.0	3319.5	3304.2
27.5°	3156.7	3154.2	3134.8	3097.8	3069.9	3052.9	3033.5
30°	3044.5	3002.6	2954.3	2901.0	2832.5	2780.1	2763.9
32.5°	2877.5	2783.3	2701.4	2612.7	2539.0	2486.6	2464.7
35°	2554.4	2405.2	2283.4	2177.0	2099.6	2051.2	2035.1
37.5°	2170.8	2026.5	1875.7	1772.5	1708.4	1659.5	1641.2
40°	1927.0	1769.8	1638.4	1541.7	1475.5	1427.9	1427.1
42.5°	1704.5	1554.4	1430.7	1361.0	1289.7	1258.3	1258.1
45°	1395.6	1275.6	1170.7	1115.9	1073.2	1047.3	1040.1
47.5°	1155.6	1056.2	986.4	942.7	907.9	891.4	880.8
50°	1020.8	933.7	878.1	840.1	820.8	799.8	798.2
52.5°	908.5	838.2	794.9	764.1	739.5	726.9	727.3
55°	763.6	707.9	677.3	653.9	634.5	624.9	620.9
57.5°	643.3	601.5	579.3	557.7	549.6	542.0	539.9
60°	568.5	540.2	519.3	502.3	490.2	487.8	487.0
62.5°	506.5	477.0	462.5	449.4	440.6	436.9	435.4
65°	417.7	395.9	382.9	372.5	369.3	363.7	362.8
67.5°	336.7	323.7	315.1	307.8	303.5	303.2	303.2
70°	287.0	279.7	272.6	268.5	266.1	264.5	264.5
72.5°	244.5	239.1	233.2	231.1	230.6	228.9	228.3
75°	186.2	180.6	181.4	177.4	174.2	170.2	167.7
77.5°	132.1	128.1	127.2	126.7	124.0	123.5	124.8
80°	102.4	98.4	97.6	98.4	97.6	95.1	95.1
82.5°	77.9	74.5	73.7	73.2	72.4	73.2	71.9
85°	41.9	40.3	40.3	40.3	41.9	41.1	40.3
87.5°	16.2	15.7	16.3	15.7	15.8	15.0	15.7
90°	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	396.2	448.0	487.2	512.5	527.6	533.9	537.1



TEST NUMBER: P332987-840

CATALOG NUMBER: SA4XXRDIP-C1195D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)