

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332994-840

Luminaire Tested: **SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332994-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7250.4 lumens  
Efficiency: N/A  
Efficacy: 131.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332994-840  
CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	93	86	80	74	88	81	76	71	72	68	65	64	61	58	57	54	52	49				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42				
4	78	67	59	53	73	64	57	51	57	52	47	51	47	43	46	42	39	36				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28				
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25				
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22				
9	54	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.8	2.7
10°-20°	551.7	7.6
20°-30°	796.6	11.0
30°-40°	903.0	12.5
40°-50°	872.0	12.0
50°-60°	725.1	10.0
60°-70°	500.7	6.9
70°-80°	253.8	3.5
80°-90°	67.3	0.9
90°-100°	26.3	0.4
100°-110°	168.0	2.3
110°-120°	321.3	4.4
120°-130°	407.9	5.6
130°-140°	436.4	6.0
140°-150°	408.1	5.6
150°-160°	329.1	4.5
160°-170°	212.2	2.9
170°-180°	73.2	1.0
0°-30°	1546.1	21.3
0°-40°	2449.1	33.8
0°-60°	4046.2	55.8
0°-90°	4868.0	67.1
90°-120°	515.6	7.1
90°-150°	1767.9	24.4
90°-180°	2382.0	32.9
0°-180°	7250.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	2	8	13	16	17	6
95°	32	13	13	16	17	41
105°	173	177	180	183	164	181
115°	324	325	325	326	326	318
125°	455	457	456	458	459	406
135°	564	564	566	567	569	435
145°	651	653	653	653	654	407
155°	714	714	713	715	713	329
165°	753	750	750	754	749	213
175°	770	767	767	772	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.0	28.0	26.0	23.9	22.0	20.9	20.8	20.8	20.7	20.6	20.5
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	7.3	7.4	7.4	7.5	7.6	8.1	9.2	10.2	11.2	12.2	13.0
95°	31.7	27.4	23.0	18.6	14.2	12.1	12.3	12.4	12.5	12.6	13.4
97.5°	67.3	70.0	72.7	75.4	78.2	72.3	58.1	43.8	29.5	15.2	15.2
100°	94.4	96.7	99.1	101.4	103.7	96.0	78.4	60.7	43.0	25.3	23.1
102.5°	124.9	126.5	128.3	130.0	131.7	131.4	129.1	126.7	124.4	122.1	98.7
105°	173.4	174.2	174.9	175.7	176.4	177.1	177.8	178.4	179.0	179.8	180.9
107.5°	218.4	218.8	219.2	219.5	219.9	220.6	221.5	222.4	223.2	224.1	224.7
110°	248.8	249.2	249.6	250.0	250.3	251.0	251.8	252.5	253.3	254.1	254.3



TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.0	279.7	280.4	281.1	281.7	282.0	282.4	282.8	283.1	283.1
115°	323.8	324.2	324.5	324.9	325.3	325.4	325.3	325.2	325.0	324.9	325.2
117.5°	364.7	365.2	365.7	366.2	366.7	367.1	367.4	367.7	367.9	368.2	368.2
120°	392.3	392.8	393.3	393.8	394.4	394.6	394.5	394.3	394.2	394.0	394.3
122.5°	418.1	418.4	418.7	419.0	419.3	419.6	419.8	419.9	420.1	420.3	420.4
125°	455.0	455.6	456.2	456.7	457.2	457.3	457.0	456.8	456.5	456.3	456.7
127.5°	490.1	490.2	490.4	490.5	490.6	491.0	491.6	492.1	492.7	493.3	493.2
130°	512.7	512.8	512.9	513.1	513.2	513.4	513.8	514.2	514.6	515.0	515.1
132.5°	533.4	533.6	533.9	534.1	534.3	534.7	535.2	535.6	536.1	536.6	536.7
135°	564.5	564.4	564.3	564.1	564.0	564.2	564.7	565.2	565.7	566.2	566.5
137.5°	592.1	592.1	592.2	592.2	592.3	592.6	593.1	593.7	594.3	594.8	595.1
140°	610.1	610.3	610.6	610.8	611.1	611.3	611.6	611.9	612.1	612.4	612.7
142.5°	626.2	626.6	627.1	627.5	628.0	628.3	628.4	628.6	628.7	628.9	629.2
145°	651.0	651.4	651.7	652.1	652.5	652.7	652.7	652.7	652.7	652.7	652.8
147.5°	670.7	671.4	672.1	672.8	673.5	673.8	673.7	673.6	673.4	673.3	673.4
150°	684.9	685.4	686.0	686.5	687.0	687.2	687.0	686.9	686.8	686.6	686.6
152.5°	696.9	697.3	697.7	698.1	698.5	698.6	698.4	698.2	697.9	697.7	697.9
155°	713.8	713.9	714.0	714.1	714.3	714.1	713.8	713.4	713.0	712.6	713.1
157.5°	727.9	727.8	727.7	727.7	727.6	727.3	726.9	726.5	726.0	725.6	726.3
160°	736.2	735.8	735.4	735.1	734.7	734.4	734.3	734.2	734.0	733.9	734.7
162.5°	743.6	743.1	742.6	742.1	741.6	741.3	741.1	741.0	740.9	740.8	741.5
165°	752.9	752.2	751.6	750.9	750.3	750.0	750.0	750.0	750.0	750.0	751.0
167.5°	760.2	759.6	758.9	758.3	757.6	757.2	757.2	757.1	757.0	756.9	758.1
170°	764.5	763.7	762.9	762.1	761.3	761.0	761.1	761.2	761.4	761.5	762.5
172.5°	767.2	766.4	765.7	764.9	764.2	763.8	764.0	764.1	764.2	764.3	765.4
175°	770.2	769.4	768.6	767.9	767.1	766.8	766.9	767.1	767.2	767.3	768.4
177.5°	771.5	770.8	770.1	769.4	768.7	768.4	768.6	768.8	769.0	769.2	770.1
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	20.3	20.2	20.1	20.2	20.5	20.8	21.2	21.5
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	13.7	14.5	15.2	15.7	15.8	15.8	15.9	15.9
95°	14.2	14.9	15.8	16.2	16.4	16.5	16.6	16.7
97.5°	15.3	15.5	15.6	15.7	15.8	15.9	16.0	16.2
100°	21.0	18.8	16.7	15.7	15.8	15.9	16.0	16.2
102.5°	75.1	51.7	28.2	16.5	16.6	16.6	16.6	16.6
105°	182.1	183.2	184.3	182.6	178.0	173.4	168.7	164.2
107.5°	225.2	225.8	226.3	226.8	227.3	227.8	228.3	228.8
110°	254.6	254.8	255.1	255.4	255.8	256.1	256.5	256.9





TEST NUMBER: P332994-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	283.0	283.0	282.9	283.1	283.6	284.1	284.6	285.0
115°	325.4	325.7	325.9	326.1	326.1	326.1	326.1	326.1
117.5°	368.1	368.1	368.0	368.0	367.9	367.9	367.8	367.8
120°	394.6	394.8	395.1	395.1	394.8	394.6	394.3	394.0
122.5°	420.6	420.7	420.9	420.8	420.6	420.3	420.1	419.8
125°	457.0	457.4	457.8	458.1	458.2	458.3	458.4	458.6
127.5°	493.2	493.1	493.0	492.9	492.8	492.7	492.6	492.5
130°	515.2	515.3	515.5	515.5	515.5	515.5	515.5	515.5
132.5°	536.9	537.0	537.1	537.1	537.0	536.9	536.8	536.7
135°	566.7	567.0	567.2	567.5	567.7	568.0	568.4	568.6
137.5°	595.4	595.7	595.9	596.0	596.0	595.9	595.8	595.7
140°	613.1	613.5	613.9	614.1	614.3	614.4	614.5	614.6
142.5°	629.4	629.8	630.1	630.3	630.3	630.3	630.3	630.4
145°	652.9	653.1	653.2	653.4	653.6	653.9	654.2	654.4
147.5°	673.5	673.6	673.7	673.8	674.0	674.1	674.2	674.3
150°	686.6	686.6	686.6	686.7	686.8	687.0	687.1	687.2
152.5°	698.1	698.3	698.5	698.6	698.5	698.4	698.3	698.3
155°	713.6	714.1	714.6	714.7	714.3	713.9	713.6	713.2
157.5°	726.9	727.6	728.2	728.2	727.6	726.9	726.3	725.6
160°	735.4	736.2	737.0	737.0	736.2	735.4	734.7	733.9
162.5°	742.4	743.1	743.9	743.9	743.0	742.0	741.2	740.3
165°	752.0	753.1	754.2	754.1	752.9	751.7	750.6	749.4
167.5°	759.2	760.3	761.4	761.3	760.1	758.8	757.5	756.3
170°	763.6	764.6	765.7	765.5	764.3	763.0	761.6	760.4
172.5°	766.4	767.4	768.4	768.2	766.9	765.5	764.1	762.7
175°	769.6	770.7	771.9	771.7	770.2	768.6	767.1	765.6
177.5°	770.9	771.7	772.5	772.3	771.1	769.9	768.6	767.4
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2

(END OF REPORT)