

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332892-840

Luminaire Tested: **SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332892-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6299.8 lumens
Efficiency: N/A
Efficacy: 149.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23				23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27				20	
2	84	77	71	66	74	68	63	59	53	49	47	38	36	34	25	23	23				17	
3	76	67	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19				14	
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17				12	
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15				11	
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13				9	
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11				8	
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	12	10				8	
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9				7	
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8				6	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	0.9
10°-20°	163.5	2.6
20°-30°	236.1	3.7
30°-40°	267.7	4.2
40°-50°	258.5	4.1
50°-60°	214.9	3.4
60°-70°	148.4	2.4
70°-80°	75.2	1.2
80°-90°	23.8	0.4
90°-100°	53.7	0.9
100°-110°	342.1	5.4
110°-120°	654.5	10.4
120°-130°	830.8	13.2
130°-140°	888.9	14.1
140°-150°	831.2	13.2
150°-160°	670.3	10.6
160°-170°	432.4	6.9
170°-180°	149.0	2.4
0°-30°	458.3	7.3
0°-40°	726.0	11.5
0°-60°	1199.4	19.0
0°-90°	1446.9	23.0
90°-120°	1050.3	16.7
90°-150°	3601.3	57.2
90°-180°	4853.0	77.0
0°-180°	6299.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	4	16	26	33	35	4
95°	64	27	26	33	34	83
105°	353	360	366	374	334	370
115°	659	663	662	664	664	649
125°	927	931	929	933	934	827
135°	1150	1149	1154	1156	1158	886
145°	1326	1329	1330	1331	1333	828
155°	1454	1455	1452	1456	1453	670
165°	1534	1528	1528	1536	1527	433
175°	1569	1562	1563	1572	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.5	9.4	9.3	9.2	9.1	9.2	9.5	9.9	10.2	10.5	10.7
90°	3.5	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4
92.5°	14.7	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5
95°	64.5	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4
97.5°	137.0	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1
100°	192.5	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2
102.5°	254.4	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0
105°	353.1	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5
107.5°	444.9	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6
110°	507.0	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.0	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5
115°	659.4	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4
117.5°	742.8	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9
120°	799.1	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1
122.5°	851.6	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5
125°	927.0	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1
127.5°	998.4	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7
130°	1044.3	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2
132.5°	1086.6	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4
135°	1149.9	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0
137.5°	1206.1	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2
140°	1242.6	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1
142.5°	1275.5	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7
145°	1326.0	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8
147.5°	1366.0	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7
150°	1395.2	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7
152.5°	1419.6	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7
155°	1453.9	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6
157.5°	1482.7	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4
160°	1499.6	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5
162.5°	1514.6	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6
165°	1533.7	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8
167.5°	1548.6	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2
170°	1557.1	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4
172.5°	1562.8	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9
175°	1568.8	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3
177.5°	1571.7	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	11.0	11.2	11.4	11.6	11.8	12.0	12.2	12.4
90°	29.0	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	28.0	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	29.0	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.3	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	42.7	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	153.1	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	370.8	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	458.8	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	518.6	519.1	519.6	520.2	521.0	521.8	522.6	523.3



TEST NUMBER: P332892-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.4	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	662.9	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.8	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	856.8	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	930.9	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.6	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.6	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1093.7	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1154.5	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1212.8	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1248.9	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.3	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.0	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1371.9	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.1	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1453.6	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1512.2	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1532.0	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1546.5	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1555.4	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1561.0	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1567.7	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1570.3	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)