

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332869-840

Luminaire Tested: **SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332869-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2723.9 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332869-840
CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	2.2
10°-20°	163.5	6.0
20°-30°	236.1	8.7
30°-40°	267.7	9.8
40°-50°	258.5	9.5
50°-60°	214.9	7.9
60°-70°	148.4	5.4
70°-80°	75.2	2.8
80°-90°	20.7	0.8
90°-100°	30.4	1.1
100°-110°	90.2	3.3
110°-120°	153.0	5.6
120°-130°	201.8	7.4
130°-140°	226.6	8.3
140°-150°	222.7	8.2
150°-160°	187.3	6.9
160°-170°	124.6	4.6
170°-180°	43.6	1.6
0°-30°	458.3	16.8
0°-40°	726.0	26.7
0°-60°	1199.4	44.0
0°-90°	1443.7	53.0
90°-120°	273.6	10.0
90°-150°	924.6	33.9
90°-180°	1280.0	47.0
0°-180°	2723.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	1	5	8	10	11	3
95°	21	25	27	28	28	24
105°	83	84	85	86	87	88
115°	156	156	155	154	154	153
125°	227	227	226	226	225	202
135°	292	294	294	294	293	226
145°	355	356	357	356	356	222
155°	407	407	406	408	406	187
165°	443	442	441	443	442	125
175°	461	459	459	461	459	44
180°	461	461	461	461	461	



TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.0	8.5	8.0	7.5	7.0	6.8	6.8	6.9	6.9	7.0	7.0
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	7.7	8.7	9.6	10.6	11.6	12.3	12.8	13.2	13.7	14.1	14.4
95°	21.4	22.1	22.8	23.5	24.2	24.9	25.4	26.1	26.6	27.2	27.4
97.5°	37.4	38.0	38.6	39.1	39.7	40.3	40.9	41.6	42.2	42.9	43.2
100°	50.0	50.3	50.6	50.9	51.2	51.7	52.4	53.2	53.9	54.6	54.7
102.5°	63.1	63.2	63.3	63.5	63.6	64.0	64.6	65.3	65.9	66.6	66.9
105°	83.1	83.2	83.3	83.4	83.4	83.6	84.0	84.3	84.6	84.9	85.1
107.5°	104.2	104.3	104.4	104.5	104.6	104.6	104.7	104.7	104.8	104.8	105.0
110°	118.5	118.7	118.8	119.0	119.1	119.2	119.1	119.0	118.9	118.9	118.7



TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.3	133.3	133.4	133.4	133.4	133.4	133.2	133.1	133.0	132.8	132.8
115°	155.6	155.6	155.6	155.6	155.6	155.5	155.3	155.2	155.0	154.9	154.8
117.5°	176.5	176.6	176.7	176.7	176.8	176.8	176.7	176.6	176.4	176.3	176.1
120°	190.6	190.9	191.2	191.5	191.9	191.9	191.7	191.4	191.2	191.0	190.6
122.5°	205.1	205.2	205.4	205.5	205.6	205.6	205.5	205.4	205.3	205.2	204.9
125°	226.6	226.6	226.6	226.6	226.6	226.5	226.5	226.4	226.3	226.2	226.1
127.5°	246.1	246.3	246.6	246.8	247.0	247.1	247.0	246.8	246.7	246.6	246.4
130°	259.8	260.0	260.2	260.5	260.7	260.8	260.8	260.8	260.8	260.8	260.7
132.5°	273.8	274.0	274.1	274.3	274.5	274.5	274.5	274.4	274.4	274.3	274.1
135°	292.3	292.8	293.2	293.7	294.2	294.4	294.4	294.4	294.4	294.4	294.3
137.5°	312.4	312.7	312.9	313.1	313.3	313.5	313.6	313.7	313.9	314.0	313.8
140°	325.8	326.0	326.1	326.3	326.5	326.5	326.5	326.5	326.5	326.5	326.5
142.5°	338.1	338.2	338.4	338.5	338.7	338.8	338.7	338.6	338.6	338.5	338.5
145°	355.1	355.4	355.7	356.0	356.4	356.6	356.6	356.7	356.8	356.9	356.8
147.5°	371.9	372.3	372.6	373.0	373.4	373.5	373.5	373.4	373.4	373.3	373.2
150°	382.2	382.5	382.8	383.1	383.4	383.6	383.6	383.6	383.6	383.6	383.6
152.5°	391.9	392.1	392.2	392.4	392.6	392.7	392.8	392.9	392.9	393.0	393.2
155°	406.8	406.8	406.8	406.8	406.8	406.8	406.7	406.6	406.6	406.5	406.8
157.5°	419.4	419.2	419.1	419.0	418.8	418.7	418.7	418.7	418.7	418.7	418.9
160°	426.8	426.7	426.7	426.6	426.5	426.4	426.4	426.3	426.2	426.1	426.4
162.5°	433.6	433.4	433.2	433.0	432.8	432.7	432.6	432.5	432.4	432.3	432.8
165°	442.8	442.6	442.4	442.1	441.9	441.7	441.5	441.4	441.2	441.1	441.5
167.5°	449.9	449.6	449.3	448.9	448.6	448.4	448.5	448.5	448.5	448.5	449.0
170°	453.9	453.5	453.1	452.7	452.3	452.2	452.2	452.3	452.4	452.5	452.9
172.5°	456.8	456.5	456.1	455.8	455.4	455.2	455.2	455.3	455.3	455.3	455.9
175°	460.7	460.3	459.9	459.5	459.1	458.9	458.8	458.7	458.7	458.6	459.1
177.5°	462.0	461.7	461.3	461.0	460.7	460.6	460.6	460.6	460.6	460.6	461.0
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	7.0	7.0	7.0	7.1	7.2	7.3	7.4	7.5
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.7	14.9	15.2	15.5	15.6	15.7	15.8	15.9
95°	27.6	27.9	28.1	28.2	28.2	28.2	28.2	28.2
97.5°	43.4	43.7	44.0	44.1	44.1	44.1	44.1	44.1
100°	54.9	55.0	55.2	55.3	55.3	55.3	55.3	55.3
102.5°	67.1	67.3	67.5	67.7	67.7	67.8	67.8	67.9
105°	85.4	85.6	85.8	86.1	86.3	86.6	86.8	87.1
107.5°	105.3	105.5	105.7	105.8	105.8	105.8	105.8	105.7
110°	118.6	118.4	118.2	118.3	118.5	118.8	119.0	119.2



TEST NUMBER: P332869-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.8	132.7	132.7	132.7	132.8	132.8	132.8	132.9
115°	154.7	154.6	154.5	154.5	154.4	154.3	154.2	154.2
117.5°	175.8	175.5	175.3	175.1	174.9	174.7	174.6	174.4
120°	190.2	189.8	189.3	189.2	189.3	189.6	189.7	189.9
122.5°	204.7	204.4	204.1	203.8	203.6	203.3	203.0	202.7
125°	225.9	225.8	225.6	225.4	225.3	225.1	225.0	224.8
127.5°	246.3	246.1	245.9	245.8	245.7	245.6	245.4	245.3
130°	260.5	260.3	260.2	259.9	259.6	259.3	259.0	258.7
132.5°	274.0	273.8	273.7	273.5	273.4	273.3	273.2	273.0
135°	294.1	294.0	293.8	293.6	293.4	293.1	292.9	292.7
137.5°	313.6	313.4	313.2	313.1	313.1	313.2	313.2	313.3
140°	326.4	326.3	326.2	326.1	326.1	326.0	325.9	325.8
142.5°	338.5	338.5	338.4	338.4	338.4	338.4	338.4	338.4
145°	356.7	356.6	356.6	356.4	356.2	355.9	355.7	355.5
147.5°	373.2	373.1	373.0	373.0	372.9	372.8	372.7	372.7
150°	383.6	383.6	383.6	383.5	383.5	383.4	383.3	383.2
152.5°	393.4	393.6	393.8	393.7	393.5	393.3	393.1	392.9
155°	407.1	407.4	407.7	407.7	407.4	407.1	406.8	406.5
157.5°	419.1	419.4	419.6	419.6	419.3	419.1	418.8	418.5
160°	426.6	426.8	427.1	427.0	426.6	426.2	425.8	425.4
162.5°	433.2	433.6	434.0	434.0	433.7	433.3	432.9	432.5
165°	442.0	442.5	442.9	443.0	442.7	442.4	442.1	441.8
167.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
170°	453.4	453.9	454.4	454.3	453.8	453.2	452.7	452.1
172.5°	456.5	457.0	457.5	457.5	457.0	456.4	455.9	455.2
175°	459.7	460.2	460.8	460.8	460.2	459.7	459.1	458.6
177.5°	461.4	461.9	462.3	462.3	461.8	461.3	460.8	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)