

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332882-840

Luminaire Tested: **SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332882-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4367.7 lumens  
Efficiency: N/A  
Efficacy: 140.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28				
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24				
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20				
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22	18				
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15				
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12				
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	23	27	22	19	22	18	16	16	14	12	10				
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	1.3
10°-20°	163.5	3.7
20°-30°	236.1	5.4
30°-40°	267.7	6.1
40°-50°	258.5	5.9
50°-60°	214.9	4.9
60°-70°	148.4	3.4
70°-80°	75.2	1.7
80°-90°	21.5	0.5
90°-100°	290.3	6.6
100°-110°	604.2	13.8
110°-120°	541.2	12.4
120°-130°	455.2	10.4
130°-140°	379.6	8.7
140°-150°	290.0	6.6
150°-160°	203.8	4.7
160°-170°	119.9	2.7
170°-180°	39.0	0.9
0°-30°	458.3	10.5
0°-40°	726.0	16.6
0°-60°	1199.4	27.5
0°-90°	1444.5	33.1
90°-120°	1435.7	32.9
90°-150°	2560.4	58.6
90°-180°	2923.0	66.9
0°-180°	4367.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	1	6	14	16	17	3
95°	26	82	644	319	193	29
105°	92	134	518	1115	1111	99
115°	163	204	462	888	1067	161
125°	227	269	460	755	851	202
135°	269	321	456	670	761	208
145°	310	355	453	565	622	195
155°	353	381	441	499	520	163
165°	385	396	422	447	454	109
175°	401	402	405	411	409	38
180°	402	402	402	402	402	



TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.0	8.6	8.4	7.9	7.4	7.0	7.8	7.8	8.0	8.2	8.0
90°	0.8	2.3	4.7	5.6	6.4	6.4	11.0	11.0	12.6	14.2	13.4
92.5°	9.0	13.1	20.5	30.2	41.7	58.1	98.3	159.5	219.2	250.4	208.6
95°	26.1	28.4	36.4	46.6	65.5	98.7	167.4	296.9	485.6	643.6	661.8
97.5°	46.8	46.8	53.5	63.0	79.3	107.0	160.0	266.9	454.5	677.8	831.3
100°	60.0	60.0	65.5	75.0	90.0	115.3	161.9	251.2	412.2	634.9	837.0
102.5°	72.6	73.9	78.8	87.7	102.0	126.0	168.1	246.7	383.7	581.2	789.6
105°	92.4	94.7	98.7	108.2	122.4	145.3	183.2	248.7	359.3	518.0	703.6
107.5°	114.2	115.7	119.7	129.8	143.4	166.0	200.8	260.4	354.9	482.6	634.1
110°	128.8	130.3	134.2	143.7	157.9	179.3	214.0	269.2	356.1	470.6	599.4



TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.6	144.2	148.8	157.6	171.8	193.2	226.6	278.7	359.9	464.9	579.8
115°	162.7	165.0	170.6	178.4	193.5	214.8	246.4	293.8	367.2	461.9	561.4
117.5°	183.5	185.7	190.7	199.3	213.4	235.5	265.5	309.0	375.0	461.1	553.2
120°	197.4	198.9	204.5	213.2	226.6	248.7	278.7	319.8	380.6	461.1	548.8
122.5°	210.1	211.7	217.1	225.2	239.8	261.4	291.3	329.9	386.3	460.5	543.7
125°	226.6	229.7	234.5	243.2	258.2	280.3	308.7	345.1	394.9	459.6	535.3
127.5°	241.4	243.9	249.5	259.4	275.1	297.4	324.9	358.2	401.6	457.9	524.1
130°	249.5	252.7	259.0	270.8	285.9	308.7	335.6	366.4	406.7	457.2	517.3
132.5°	257.7	260.2	268.5	279.7	296.0	317.6	344.5	374.6	411.1	456.6	510.9
135°	269.2	272.5	280.3	293.8	310.3	330.8	356.9	385.4	417.7	455.7	501.4
137.5°	280.8	283.8	292.5	305.3	322.4	342.0	366.4	392.9	421.6	455.4	493.2
140°	289.0	291.3	300.0	313.5	330.0	349.0	372.7	398.0	424.9	454.8	488.8
142.5°	297.8	300.2	308.3	321.0	337.0	355.4	378.4	401.7	427.4	454.8	485.0
145°	310.3	312.7	320.6	331.6	346.7	364.1	384.6	405.9	428.8	453.2	478.5
147.5°	324.4	325.2	332.1	343.5	356.0	371.6	390.9	409.5	429.6	450.4	472.7
150°	333.3	334.1	340.3	349.8	361.6	376.7	394.0	411.4	429.6	448.5	468.3
152.5°	341.4	341.6	347.9	356.8	367.4	381.1	396.6	412.6	428.3	445.4	463.2
155°	352.9	353.8	358.5	366.4	375.1	386.9	400.3	413.7	426.4	440.6	455.7
157.5°	364.2	364.2	368.6	374.8	382.3	391.6	403.0	413.7	424.3	435.8	447.9
160°	371.1	371.1	374.3	379.8	386.2	394.9	404.2	413.7	422.4	431.9	442.2
162.5°	377.5	376.8	379.3	384.3	389.9	396.7	405.6	413.7	420.6	428.2	437.2
165°	384.6	384.6	386.2	390.1	394.0	398.8	405.9	412.2	417.0	422.4	428.8
167.5°	391.6	390.9	391.6	394.7	396.9	400.5	405.8	410.3	413.1	416.8	421.2
170°	394.9	394.0	394.9	397.2	398.8	401.1	405.1	409.0	410.6	412.9	416.2
172.5°	398.0	397.2	397.4	399.1	400.0	401.7	404.5	407.8	408.1	409.2	411.7
175°	401.1	400.3	400.3	401.1	401.9	401.9	403.5	405.9	405.1	405.1	406.7
177.5°	402.5	401.9	401.3	401.9	401.9	401.9	402.5	403.8	402.5	402.5	403.1
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	8.0	8.1	8.2	8.2	8.4	8.7	8.6	8.7
90°	14.2	15.0	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	155.1	116.7	92.9	77.1	67.8	63.5	60.8	60.8
95°	585.1	462.7	356.9	280.3	241.7	217.1	203.0	192.7
97.5°	864.4	819.0	741.7	659.3	602.7	555.1	531.4	515.0
100°	952.3	968.1	929.4	871.0	802.2	754.1	730.4	724.1
102.5°	947.9	1026.2	1037.4	1013.1	971.0	936.0	911.1	906.1
105°	884.4	1021.0	1099.1	1131.6	1133.2	1126.8	1115.8	1111.1
107.5°	794.3	939.7	1049.8	1120.1	1159.2	1177.2	1185.1	1187.1
110°	739.9	876.5	991.0	1077.8	1133.9	1167.1	1181.3	1188.4





TEST NUMBER: P332882-840

CATALOG NUMBER: SA4XXRDIP-C350D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	700.1	820.9	929.1	1015.9	1079.5	1119.7	1139.6	1151.1
115°	660.1	757.3	849.6	925.4	987.8	1035.2	1060.5	1066.8
117.5°	640.6	720.9	793.6	857.9	911.1	950.9	976.4	981.4
120°	631.7	705.2	768.3	824.4	869.4	904.1	924.6	933.3
122.5°	624.1	695.0	752.6	801.6	839.7	869.4	886.8	895.4
125°	611.2	679.1	733.6	777.0	808.6	831.5	846.5	851.2
127.5°	595.4	660.2	714.6	755.9	787.6	808.0	820.6	825.4
130°	582.8	645.1	698.8	740.6	773.1	792.8	805.5	810.2
132.5°	569.5	628.0	680.5	722.4	754.1	776.4	788.4	793.1
135°	551.2	602.5	650.7	690.1	721.8	743.9	756.5	761.2
137.5°	534.6	578.0	618.6	654.3	683.8	705.6	716.0	721.8
140°	525.1	562.2	597.7	631.0	658.5	675.9	687.0	693.3
142.5°	516.2	549.0	579.5	608.1	632.7	648.7	658.5	663.0
145°	503.8	530.7	554.3	576.4	596.2	609.6	617.5	621.5
147.5°	493.5	514.8	533.8	551.2	565.7	577.2	583.2	584.6
150°	487.2	505.3	521.2	535.3	548.1	558.3	563.0	563.8
152.5°	480.3	495.8	510.4	522.1	532.8	541.2	544.0	544.8
155°	469.8	482.5	494.3	503.8	511.7	518.0	520.4	520.4
157.5°	458.6	469.2	479.2	486.8	492.7	497.5	498.9	498.9
160°	451.7	460.4	469.1	475.3	480.1	484.8	485.6	485.6
162.5°	444.7	452.1	459.0	464.6	468.1	472.8	473.6	473.0
165°	435.0	439.8	445.4	449.3	452.4	455.7	454.8	454.0
167.5°	425.8	429.4	433.8	436.2	437.8	439.8	439.7	439.0
170°	420.1	422.4	425.7	428.0	429.6	430.3	429.6	429.6
172.5°	415.1	416.8	418.7	420.4	421.3	422.1	421.3	420.1
175°	408.3	409.0	410.6	410.6	410.6	412.2	410.6	409.0
177.5°	403.8	404.5	404.5	405.1	404.5	405.1	403.8	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9

(END OF REPORT)