

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332498-930

Luminaire Tested: **SA4XXDIP-C350D365U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332498-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2303.4 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332498-930
CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50	45				
2	90	82	76	71	83	76	71	66	66	61	58	56	53	50	46	44	42	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	59	48	41	35	41	36	31	36	31	28	30	26	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	2.0
10°-20°	127.8	5.5
20°-30°	188.1	8.2
30°-40°	218.7	9.5
40°-50°	218.7	9.5
50°-60°	191.3	8.3
60°-70°	142.1	6.2
70°-80°	80.7	3.5
80°-90°	24.1	1.0
90°-100°	105.9	4.6
100°-110°	220.5	9.6
110°-120°	197.5	8.6
120°-130°	166.1	7.2
130°-140°	138.5	6.0
140°-150°	105.8	4.6
150°-160°	74.4	3.2
160°-170°	43.7	1.9
170°-180°	14.2	0.6
0°-30°	361.2	15.7
0°-40°	579.9	25.2
0°-60°	989.8	43.0
0°-90°	1236.7	53.7
90°-120°	523.9	22.7
90°-150°	934.3	40.6
90°-180°	1067.0	46.3
0°-180°	2303.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	0	2	5	6	6	2
95°	10	30	235	116	70	11
105°	34	49	189	407	405	36
115°	59	74	169	324	389	59
125°	83	98	168	276	311	74
135°	98	117	166	245	278	76
145°	113	130	165	206	227	71
155°	129	139	161	182	190	59
165°	140	145	154	163	166	40
175°	146	147	148	150	149	14
180°	147	147	147	147	147	



TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.1	8.2	8.2	8.2	8.2	8.2	8.4	8.3	8.4	8.5	8.4
90°	0.3	0.9	1.7	2.0	2.3	2.3	4.0	4.0	4.6	5.2	4.9
92.5°	3.3	4.8	7.5	11.0	15.2	21.2	35.9	58.2	80.0	91.4	76.1
95°	9.5	10.4	13.3	17.0	23.9	36.0	61.1	108.4	177.2	234.8	241.5
97.5°	17.0	17.0	19.6	23.0	28.9	39.1	58.4	97.4	165.8	247.4	303.4
100°	21.9	21.9	23.9	27.4	32.9	42.1	59.1	91.6	150.4	231.7	305.4
102.5°	26.5	27.0	28.8	32.0	37.3	46.0	61.4	90.0	140.1	212.1	288.1
105°	33.8	34.6	36.0	39.5	44.7	53.0	66.9	90.7	131.1	189.0	256.7
107.5°	41.7	42.2	43.7	47.4	52.3	60.6	73.2	95.1	129.5	176.1	231.4
110°	47.0	47.5	49.0	52.4	57.6	65.4	78.1	98.2	130.0	171.7	218.7



TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.0	52.6	54.3	57.5	62.7	70.4	82.7	101.7	131.3	169.7	211.6
115°	59.4	60.3	62.2	65.1	70.6	78.4	89.9	107.2	134.0	168.6	204.9
117.5°	66.9	67.8	69.5	72.7	77.9	85.9	96.9	112.8	136.8	168.3	201.9
120°	72.1	72.6	74.6	77.8	82.7	90.7	101.7	116.7	138.9	168.3	200.2
122.5°	76.6	77.2	79.2	82.2	87.6	95.4	106.3	120.4	141.0	168.0	198.4
125°	82.7	83.8	85.6	88.8	94.2	102.3	112.7	125.9	144.1	167.7	195.3
127.5°	88.1	88.9	91.1	94.7	100.4	108.5	118.5	130.7	146.6	167.1	191.3
130°	91.1	92.2	94.5	98.8	104.3	112.7	122.5	133.7	148.4	166.8	188.7
132.5°	94.1	95.0	98.0	102.1	108.0	115.9	125.7	136.7	150.0	166.6	186.5
135°	98.2	99.4	102.3	107.2	113.2	120.7	130.2	140.6	152.5	166.2	183.0
137.5°	102.5	103.5	106.7	111.4	117.6	124.8	133.7	143.4	153.8	166.2	180.0
140°	105.5	106.3	109.5	114.4	120.4	127.3	136.0	145.2	155.0	166.0	178.4
142.5°	108.7	109.6	112.5	117.2	122.9	129.6	138.1	146.6	156.0	166.0	177.0
145°	113.2	114.1	117.0	121.0	126.5	132.8	140.3	148.1	156.5	165.4	174.6
147.5°	118.4	118.6	121.2	125.3	129.9	135.6	142.6	149.4	156.8	164.4	172.5
150°	121.6	121.9	124.2	127.7	132.0	137.5	143.8	150.1	156.8	163.6	170.9
152.5°	124.6	124.7	126.9	130.2	134.0	139.1	144.7	150.6	156.3	162.5	169.0
155°	128.8	129.1	130.9	133.7	136.9	141.2	146.1	151.0	155.6	160.8	166.2
157.5°	132.9	132.9	134.5	136.7	139.5	142.9	147.1	151.0	154.8	159.0	163.5
160°	135.4	135.4	136.6	138.6	140.9	144.1	147.6	151.0	154.2	157.6	161.3
162.5°	137.7	137.5	138.4	140.2	142.3	144.8	148.0	151.0	153.4	156.2	159.6
165°	140.3	140.3	140.9	142.4	143.8	145.5	148.1	150.4	152.1	154.2	156.5
167.5°	142.9	142.6	142.9	144.0	144.8	146.2	148.1	149.7	150.7	152.1	153.7
170°	144.1	143.8	144.1	145.0	145.5	146.3	147.8	149.3	149.9	150.7	151.9
172.5°	145.2	145.0	145.0	145.6	145.9	146.6	147.6	148.8	149.0	149.3	150.3
175°	146.3	146.1	146.1	146.3	146.7	146.7	147.2	148.1	147.8	147.8	148.4
177.5°	146.9	146.7	146.4	146.7	146.7	146.7	146.9	147.3	146.9	146.9	147.2
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	8.5	8.5	8.6	8.6	8.6	8.6	8.6	8.6
90°	5.2	5.5	5.8	5.8	6.0	6.4	6.0	6.0
92.5°	56.6	42.6	33.9	28.1	24.7	23.2	22.2	22.2
95°	213.5	168.8	130.2	102.3	88.1	79.2	74.0	70.3
97.5°	315.4	298.9	270.7	240.6	219.9	202.6	194.0	187.9
100°	347.5	353.3	339.2	317.8	292.8	275.2	266.5	264.2
102.5°	345.9	374.5	378.5	369.7	354.3	341.6	332.5	330.6
105°	322.7	372.6	401.1	412.9	413.5	411.2	407.2	405.4
107.5°	289.8	342.9	383.0	408.8	423.0	429.6	432.4	433.2
110°	270.0	319.8	361.7	393.3	413.8	425.9	431.0	433.7



TEST NUMBER: P332498-930

CATALOG NUMBER: SA4XXDIP-C350D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.4	299.5	339.0	370.7	394.0	408.6	415.9	420.0
115°	240.9	276.3	310.1	337.7	360.4	377.7	387.0	389.3
117.5°	233.7	263.1	289.6	313.1	332.5	347.0	356.3	358.1
120°	230.5	257.3	280.4	300.8	317.2	330.0	337.5	340.6
122.5°	227.7	253.6	274.6	292.5	306.4	317.2	323.6	326.8
125°	223.1	247.8	267.7	283.6	295.1	303.5	308.9	310.6
127.5°	217.3	240.9	260.8	275.8	287.4	294.8	299.5	301.2
130°	212.6	235.5	255.0	270.3	282.1	289.3	293.9	295.6
132.5°	207.8	229.2	248.3	263.6	275.2	283.3	287.7	289.4
135°	201.1	219.9	237.4	251.8	263.3	271.4	276.1	277.8
137.5°	195.1	210.9	225.8	238.7	249.6	257.5	261.3	263.3
140°	191.6	205.1	218.1	230.2	240.4	246.6	250.7	253.0
142.5°	188.4	200.3	211.4	221.9	230.9	236.8	240.4	241.9
145°	183.8	193.6	202.3	210.3	217.5	222.4	225.3	226.7
147.5°	180.1	187.8	194.8	201.1	206.4	210.7	212.8	213.4
150°	177.8	184.4	190.2	195.3	200.0	203.7	205.5	205.7
152.5°	175.3	181.0	186.3	190.5	194.4	197.5	198.5	198.9
155°	171.5	176.0	180.3	183.8	186.7	189.0	189.9	189.9
157.5°	167.4	171.2	174.9	177.7	179.8	181.6	182.1	182.1
160°	164.9	168.0	171.1	173.5	175.2	176.9	177.2	177.2
162.5°	162.3	165.0	167.5	169.6	170.8	172.5	172.8	172.6
165°	158.7	160.5	162.5	164.0	165.1	166.2	166.0	165.7
167.5°	155.4	156.7	158.3	159.1	159.7	160.5	160.5	160.2
170°	153.3	154.2	155.3	156.2	156.8	157.0	156.8	156.8
172.5°	151.5	152.1	152.8	153.4	153.8	154.0	153.8	153.3
175°	149.0	149.3	149.9	149.9	149.9	150.4	149.9	149.3
177.5°	147.3	147.6	147.6	147.8	147.6	147.8	147.3	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7

(END OF REPORT)