

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332900-840

Luminaire Tested: **SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332900-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3693.4 lumens  
Efficiency: N/A  
Efficacy: 134.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332900-840  
CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	71	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.4	2.6
10°-20°	268.8	7.3
20°-30°	388.2	10.5
30°-40°	440.0	11.9
40°-50°	424.9	11.5
50°-60°	353.4	9.6
60°-70°	244.0	6.6
70°-80°	123.7	3.3
80°-90°	32.7	0.9
90°-100°	131.2	3.6
100°-110°	273.1	7.4
110°-120°	244.6	6.6
120°-130°	205.8	5.6
130°-140°	171.6	4.6
140°-150°	131.1	3.5
150°-160°	92.1	2.5
160°-170°	54.2	1.5
170°-180°	17.6	0.5
0°-30°	753.5	20.4
0°-40°	1193.5	32.3
0°-60°	1971.8	53.4
0°-90°	2372.2	64.2
90°-120°	648.9	17.6
90°-150°	1157.3	31.3
90°-180°	1321.0	35.8
0°-180°	3693.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	0	3	6	7	8	3
95°	12	37	291	144	87	13
105°	42	60	234	504	502	45
115°	74	92	209	401	482	73
125°	102	122	208	341	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	181	182	183	186	185	17
180°	182	182	182	182	182	



TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	14.5	13.5	12.6	11.6	10.6	9.9	10.2	10.1	10.1	10.1	9.9
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1
92.5°	4.0	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3
95°	11.8	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1
97.5°	21.1	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8
100°	27.2	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3
102.5°	32.8	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9
105°	41.8	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0
107.5°	51.6	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6
110°	58.2	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9



TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.4	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1
115°	73.5	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8
117.5°	82.9	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0
120°	89.3	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0
122.5°	94.9	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8
125°	102.4	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0
127.5°	109.1	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9
130°	112.8	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8
132.5°	116.5	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0
135°	121.7	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6
137.5°	126.9	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0
140°	130.7	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0
142.5°	134.6	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2
145°	140.3	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3
147.5°	146.6	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7
150°	150.6	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7
152.5°	154.3	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3
155°	159.6	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9
157.5°	164.6	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5
160°	167.7	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9
162.5°	170.6	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6
165°	173.8	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8
167.5°	177.0	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4
170°	178.4	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1
172.5°	179.9	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1
175°	181.3	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8
177.5°	182.0	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	9.8	9.7	9.7	9.7	9.9	10.1	10.2	10.3
90°	6.5	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	70.1	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	264.5	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	390.7	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	430.4	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	428.5	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	399.7	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	359.0	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	334.5	396.2	448.0	487.2	512.5	527.6	533.9	537.1





TEST NUMBER: P332900-840

CATALOG NUMBER: SA4XXRDIP-C575D365U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.4	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	298.4	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	289.5	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	285.5	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	282.1	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	276.3	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	269.1	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	263.4	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	257.4	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	249.1	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	241.7	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	237.3	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	233.4	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	227.7	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	223.1	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	220.3	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	217.1	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	212.4	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	207.3	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	204.2	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	201.1	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	196.6	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	192.5	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	189.9	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	187.6	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.5	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.5	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)