

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515-930

Luminaire Tested: **SA4XXDIP-C350D810U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332515-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3524.9 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332515-930  
CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21				
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	1.3
10°-20°	127.8	3.6
20°-30°	188.1	5.3
30°-40°	218.7	6.2
40°-50°	218.7	6.2
50°-60°	191.3	5.4
60°-70°	142.1	4.0
70°-80°	80.7	2.3
80°-90°	25.8	0.7
90°-100°	54.4	1.5
100°-110°	161.0	4.6
110°-120°	273.3	7.8
120°-130°	360.4	10.2
130°-140°	404.7	11.5
140°-150°	397.7	11.3
150°-160°	334.5	9.5
160°-170°	222.6	6.3
170°-180°	77.9	2.2
0°-30°	361.2	10.2
0°-40°	579.9	16.5
0°-60°	989.8	28.1
0°-90°	1238.4	35.1
90°-120°	488.7	13.9
90°-150°	1651.5	46.9
90°-180°	2287.0	64.9
0°-180°	3524.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	2	9	14	18	19	4
95°	38	44	48	50	50	43
105°	148	149	152	154	156	158
115°	278	278	277	276	275	274
125°	405	405	404	403	402	361
135°	522	526	526	524	523	404
145°	634	637	637	637	635	397
155°	727	727	726	728	726	334
165°	791	789	788	791	789	223
175°	823	820	819	823	819	78
180°	824	824	824	824	824	



TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.4	8.6	8.9	9.1	9.4	9.6	9.7	9.9	10.0	10.2	10.4
90°	1.9	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8
92.5°	13.6	15.4	17.2	19.0	20.8	22.1	22.8	23.6	24.5	25.3	25.8
95°	38.2	39.5	40.8	42.1	43.4	44.5	45.5	46.5	47.5	48.4	48.8
97.5°	66.8	67.8	68.8	69.9	70.8	72.0	73.1	74.3	75.4	76.6	77.1
100°	89.3	89.8	90.3	90.9	91.5	92.5	93.7	95.0	96.2	97.5	97.8
102.5°	112.7	112.9	113.2	113.4	113.6	114.3	115.4	116.6	117.8	119.0	119.4
105°	148.5	148.6	148.8	149.0	149.1	149.4	150.0	150.6	151.2	151.7	152.1
107.5°	186.1	186.3	186.5	186.6	186.8	186.9	187.0	187.1	187.2	187.3	187.7
110°	211.7	211.9	212.1	212.5	212.7	212.8	212.7	212.5	212.4	212.2	212.0



TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	238.1	238.1	238.2	238.3	238.4	238.2	238.0	237.7	237.5	237.3	237.2
115°	277.9	277.9	277.9	277.9	277.9	277.8	277.4	277.2	276.9	276.6	276.5
117.5°	315.4	315.5	315.6	315.7	315.8	315.8	315.6	315.4	315.2	315.0	314.5
120°	340.4	341.0	341.5	342.1	342.7	342.7	342.3	341.9	341.4	341.0	340.3
122.5°	366.4	366.6	366.8	367.0	367.3	367.3	367.1	366.9	366.7	366.5	366.0
125°	404.7	404.7	404.7	404.7	404.7	404.6	404.6	404.4	404.2	404.1	403.8
127.5°	439.5	439.9	440.4	440.8	441.2	441.3	441.1	440.9	440.7	440.4	440.2
130°	464.0	464.5	464.9	465.3	465.7	465.9	465.9	465.9	465.9	465.9	465.6
132.5°	489.0	489.3	489.7	489.9	490.2	490.3	490.2	490.2	490.0	489.9	489.6
135°	522.0	522.9	523.7	524.6	525.5	525.9	525.9	525.9	525.9	525.9	525.5
137.5°	558.0	558.4	558.7	559.1	559.5	559.9	560.1	560.4	560.5	560.8	560.4
140°	582.0	582.2	582.5	582.8	583.1	583.2	583.2	583.2	583.2	583.2	583.1
142.5°	603.9	604.1	604.5	604.7	605.0	605.1	605.0	604.9	604.7	604.6	604.6
145°	634.2	634.8	635.4	635.9	636.5	636.8	637.0	637.1	637.2	637.4	637.2
147.5°	664.3	665.0	665.6	666.3	667.0	667.3	667.2	667.1	666.9	666.8	666.8
150°	682.7	683.2	683.8	684.4	684.9	685.2	685.2	685.2	685.2	685.2	685.2
152.5°	700.0	700.3	700.7	701.0	701.3	701.6	701.6	701.8	701.9	702.1	702.4
155°	726.6	726.6	726.6	726.6	726.6	726.5	726.4	726.3	726.1	726.0	726.5
157.5°	749.1	748.8	748.5	748.3	748.0	747.9	747.9	747.9	747.8	747.8	748.2
160°	762.3	762.1	762.1	761.9	761.7	761.6	761.5	761.3	761.2	761.1	761.5
162.5°	774.5	774.2	773.8	773.5	773.1	772.8	772.7	772.6	772.4	772.3	773.1
165°	791.0	790.6	790.2	789.7	789.3	789.0	788.6	788.4	788.1	787.8	788.6
167.5°	803.6	803.0	802.4	801.8	801.3	801.0	801.0	801.0	801.0	801.0	801.9
170°	810.7	810.1	809.3	808.6	808.0	807.6	807.8	808.0	808.0	808.2	809.0
172.5°	815.9	815.3	814.6	814.1	813.5	813.2	813.3	813.3	813.3	813.3	814.2
175°	822.9	822.1	821.4	820.8	820.0	819.6	819.5	819.3	819.2	819.0	820.0
177.5°	825.2	824.6	824.0	823.5	822.9	822.6	822.6	822.6	822.6	822.6	823.4
180°	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1



TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	10.5	10.8	10.9	11.0	11.1	11.1	11.2	11.3
90°	15.7	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	26.3	26.7	27.3	27.6	27.8	28.0	28.1	28.3
95°	49.3	49.7	50.1	50.4	50.4	50.4	50.4	50.4
97.5°	77.6	78.1	78.7	78.9	78.9	78.9	78.9	78.9
100°	98.1	98.4	98.7	98.8	98.8	98.8	98.8	98.8
102.5°	119.8	120.1	120.5	120.7	120.9	121.0	121.2	121.2
105°	152.5	153.0	153.4	153.8	154.3	154.7	155.1	155.6
107.5°	188.1	188.4	188.8	189.1	189.0	189.0	189.0	188.9
110°	211.7	211.4	211.1	211.2	211.7	212.1	212.5	212.9





TEST NUMBER: P332515-930

CATALOG NUMBER: SA4XXDIP-C350D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.1	237.1	237.0	237.0	237.1	237.2	237.3	237.3
115°	276.3	276.2	276.1	275.9	275.8	275.7	275.5	275.3
117.5°	314.1	313.6	313.1	312.7	312.4	312.1	311.9	311.5
120°	339.6	338.8	338.2	337.9	338.3	338.5	338.8	339.1
122.5°	365.5	365.1	364.6	364.1	363.5	363.1	362.6	362.1
125°	403.6	403.2	403.0	402.7	402.4	402.1	401.9	401.5
127.5°	439.9	439.6	439.3	439.0	438.8	438.6	438.4	438.1
130°	465.4	465.0	464.8	464.4	463.8	463.3	462.7	462.1
132.5°	489.3	489.0	488.8	488.5	488.3	488.0	487.8	487.6
135°	525.3	525.0	524.7	524.3	523.9	523.5	523.1	522.7
137.5°	560.0	559.7	559.3	559.1	559.2	559.3	559.4	559.5
140°	582.9	582.8	582.6	582.5	582.4	582.2	582.0	582.0
142.5°	604.5	604.5	604.5	604.5	604.5	604.5	604.4	604.4
145°	637.1	637.0	636.8	636.5	636.1	635.7	635.3	634.9
147.5°	666.6	666.5	666.3	666.3	666.1	665.9	665.9	665.7
150°	685.2	685.2	685.2	685.1	685.0	684.9	684.7	684.5
152.5°	702.7	703.0	703.4	703.4	703.0	702.6	702.3	701.9
155°	727.1	727.7	728.2	728.2	727.7	727.1	726.5	726.0
157.5°	748.6	749.1	749.5	749.4	749.0	748.5	748.0	747.5
160°	761.9	762.3	762.7	762.6	761.9	761.2	760.5	759.8
162.5°	773.8	774.5	775.3	775.3	774.6	774.0	773.2	772.5
165°	789.5	790.4	791.2	791.3	790.8	790.2	789.6	789.1
167.5°	802.7	803.6	804.5	804.5	803.6	802.7	801.8	801.0
170°	809.9	810.7	811.6	811.5	810.6	809.6	808.5	807.6
172.5°	815.2	816.2	817.2	817.2	816.2	815.1	814.2	813.2
175°	821.0	822.0	823.0	823.0	822.0	821.0	820.0	819.0
177.5°	824.2	825.0	825.8	825.7	824.8	823.9	823.0	822.1
180°	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1

(END OF REPORT)