

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332949-840

Luminaire Tested: **SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332949-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8227.1 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332949-840
CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	23
5	68	56	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	16
8	53	42	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.6
10°-20°	389.6	4.7
20°-30°	609.4	7.4
30°-40°	677.4	8.2
40°-50°	601.0	7.3
50°-60°	468.4	5.7
60°-70°	306.6	3.7
70°-80°	150.8	1.8
80°-90°	41.7	0.5
90°-100°	53.7	0.7
100°-110°	342.1	4.2
110°-120°	654.5	8.0
120°-130°	830.8	10.1
130°-140°	888.9	10.8
140°-150°	831.2	10.1
150°-160°	670.3	8.1
160°-170°	432.4	5.3
170°-180°	149.0	1.8
0°-30°	1128.1	13.7
0°-40°	1805.6	21.9
0°-60°	2875.0	34.9
0°-90°	3374.2	41.0
90°-120°	1050.3	12.8
90°-150°	3601.3	43.8
90°-180°	4853.0	59.0
0°-180°	8227.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	35	4	35	4	35	16
95°	34	64	34	64	34	27
105°	334	353	334	353	334	292
115°	664	659	664	659	664	657
125°	934	927	934	927	934	832
135°	1158	1150	1158	1150	1158	891
145°	1333	1326	1333	1326	1333	833
155°	1453	1454	1453	1454	1453	670
165°	1527	1534	1527	1534	1527	431
175°	1559	1569	1559	1569	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	16.5	16.0	16.3	16.2	16.5	15.9	16.0	16.6	15.3	15.5	15.0
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0	26.5	24.8	22.8
95°	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0	27.4	25.9	25.5
97.5°	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3	31.1	31.0	60.1
100°	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7	47.2	51.6	87.7
102.5°	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1	201.0	248.7	253.5
105°	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8	368.5	366.1	364.8
107.5°	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8	457.6	456.5	454.6
110°	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6	518.0	517.5	515.9



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4	576.5	576.6	575.9
115°	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9	662.4	661.8	662.1
117.5°	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8	749.9	750.0	749.5
120°	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6	802.8
122.5°	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8	856.5	856.2	855.8
125°	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9	930.1	929.4	929.9
127.5°	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.7	1004.9	1003.7
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6	1049.2	1049.0	1048.2
132.5°	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7	1093.4	1093.2	1092.2
135°	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5	1154.0	1153.5	1152.5
137.5°	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8	1212.2	1211.6	1210.5
140°	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9	1248.1	1247.4	1246.8
142.5°	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3	1281.7	1281.1	1280.8
145°	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0	1329.8	1329.5	1329.5
147.5°	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9	1371.7	1371.5	1371.7
150°	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7	1398.7	1398.7	1399.0
152.5°	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1	1421.7	1421.3	1421.7
155°	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6	1452.6	1451.5	1452.3
157.5°	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0	1478.9
160°	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9	1495.2
162.5°	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2	1510.6	1509.0	1509.2
165°	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0	1529.8	1527.8	1527.8
167.5°	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5	1544.2	1541.9	1542.1
170°	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4	1553.4	1551.3	1551.0
172.5°	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0	1558.9	1556.9	1556.6
175°	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7	1565.3	1563.0	1562.8
177.5°	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3	1568.6	1567.0	1566.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	14.6	13.8	14.2	13.7	13.6	14.7	15.5	15.3	14.6	13.8	13.1
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7	14.9	15.1	15.2
95°	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5	55.6	46.8	38.0
97.5°	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0	142.6	148.1	153.6
100°	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5	197.1	201.9	206.5
102.5°	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4	257.8	261.3	264.7
105°	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1	354.8	356.3	357.9
107.5°	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9	445.8	446.6	447.3
110°	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0	507.7	508.5	509.3



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0	568.5	569.8	571.2
115°	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4	660.2	661.1	661.8
117.5°	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8	743.8	744.9	745.9
120°	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1	800.1	801.2	802.2
122.5°	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6	852.3	852.9	853.5
125°	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0	928.1	929.1	930.1
127.5°	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4	998.6	998.9	999.2
130°	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3	1044.6	1044.9	1045.1
132.5°	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6	1087.0	1087.5	1088.0
135°	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9	1149.7	1149.4	1149.1
137.5°	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1	1206.2	1206.3	1206.4
140°	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6	1243.1	1243.6	1244.3
142.5°	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5	1276.5	1277.4	1278.3
145°	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0	1326.8	1327.6	1328.3
147.5°	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0	1367.6	1369.0	1370.5
150°	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2	1396.2	1397.2	1398.4
152.5°	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6	1420.5	1421.3	1422.1
155°	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9	1454.1	1454.4	1454.6
157.5°	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7	1482.6	1482.4	1482.3
160°	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6	1498.8	1498.0	1497.3
162.5°	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6	1513.7	1512.7	1511.7
165°	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7	1532.4	1531.1	1529.7
167.5°	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6	1547.3	1546.0	1544.6
170°	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1	1555.6	1554.0	1552.5
172.5°	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8	1561.2	1559.6	1558.0
175°	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8	1567.3	1565.7	1564.2
177.5°	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7	1570.2	1568.7	1567.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	13.7	13.8	14.2	13.7	14.6	15.0	14.9	15.2	16.0	15.5	15.7
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0	29.6	31.1	32.0
95°	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0	30.5	32.1	33.0
97.5°	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3	31.4	31.6	31.8
100°	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7	38.4	33.9	31.8
102.5°	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1	105.3	57.5	33.6
105°	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8	373.1	375.5	371.9
107.5°	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8	459.9	461.0	462.1
110°	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6	519.1	519.6	520.2



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4	576.3	576.2	576.6
115°	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9	663.4	663.9	664.2
117.5°	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8	749.7	749.6	749.5
120°	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7	804.2	804.7	804.7
122.5°	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8	857.1	857.4	857.3
125°	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9	931.7	932.5	933.0
127.5°	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6	1004.4	1004.3	1004.1
130°	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6	1049.9	1050.1	1050.2
132.5°	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7	1094.0	1094.2	1094.2
135°	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5	1155.0	1155.6	1156.1
137.5°	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8	1213.4	1214.0	1214.2
140°	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9	1249.7	1250.5	1251.0
142.5°	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3	1282.8	1283.4	1283.7
145°	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0	1330.3	1330.5	1330.9
147.5°	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9	1372.1	1372.3	1372.5
150°	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7	1398.7	1398.7	1398.9
152.5°	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1	1422.5	1422.9	1423.0
155°	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6	1454.6	1455.7	1455.8
157.5°	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5
160°	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2
162.5°	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2	1513.7	1515.3	1515.2
165°	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0	1534.1	1536.1	1536.0
167.5°	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5	1548.7	1551.1	1550.8
170°	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4	1557.5	1559.6	1559.3
172.5°	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0	1563.2	1565.2	1564.9
175°	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7	1570.0	1572.4	1572.0
177.5°	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3	1572.0	1573.7	1573.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	16.6	16.3	16.0	16.5	16.0	16.3	16.6	15.7	15.5	16.0	15.2
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	32.1	32.2	32.3	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0
95°	33.2	33.5	33.7	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0
97.5°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3
100°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7
102.5°	33.6	33.7	33.7	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1
105°	362.5	353.1	343.9	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8
107.5°	463.1	464.1	465.0	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8
110°	521.0	521.8	522.6	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.6	578.7	579.7	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4
115°	664.2	664.2	664.2	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9
117.5°	749.4	749.3	749.2	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8
120°	804.2	803.7	803.1	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7
122.5°	856.8	856.3	855.7	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8
125°	933.2	933.5	933.8	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9
127.5°	1003.9	1003.7	1003.5	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6
132.5°	1094.0	1093.8	1093.6	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7
135°	1156.6	1157.1	1157.6	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5
137.5°	1214.1	1213.9	1213.7	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8
140°	1251.2	1251.5	1251.7	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9
142.5°	1283.8	1283.8	1283.9	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3
145°	1331.4	1331.9	1332.5	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0
147.5°	1372.8	1373.1	1373.3	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9
150°	1399.1	1399.4	1399.7	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7
152.5°	1422.9	1422.7	1422.6	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1
155°	1455.0	1454.2	1453.5	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6
157.5°	1482.1	1480.8	1479.4	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8
160°	1499.6	1498.0	1496.5	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0
162.5°	1513.4	1511.7	1509.8	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2
165°	1533.7	1531.3	1528.9	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0
167.5°	1548.3	1545.7	1543.1	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5
170°	1556.7	1554.1	1551.6	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4
172.5°	1562.1	1559.2	1556.4	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0
175°	1568.8	1565.7	1562.6	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7
177.5°	1570.7	1568.2	1565.7	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	14.9	15.0	14.6	13.7	14.2	13.8	13.7	13.1	13.8	14.6	15.3
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	26.5	24.8	22.8	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7
95°	27.4	25.9	25.5	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5
97.5°	31.1	31.0	60.1	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0
100°	47.2	51.6	87.7	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5
102.5°	201.0	248.7	253.5	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4
105°	368.5	366.1	364.8	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1
107.5°	457.6	456.5	454.6	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9
110°	518.0	517.5	515.9	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	576.5	576.6	575.9	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0
115°	662.4	661.8	662.1	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4
117.5°	749.9	750.0	749.5	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8
120°	803.1	802.6	802.8	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1
122.5°	856.5	856.2	855.8	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6
125°	930.1	929.4	929.9	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0
127.5°	1004.7	1004.9	1003.7	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4
130°	1049.2	1049.0	1048.2	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3
132.5°	1093.4	1093.2	1092.2	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6
135°	1154.0	1153.5	1152.5	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9
137.5°	1212.2	1211.6	1210.5	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1
140°	1248.1	1247.4	1246.8	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6
142.5°	1281.7	1281.1	1280.8	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5
145°	1329.8	1329.5	1329.5	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0
147.5°	1371.7	1371.5	1371.7	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0
150°	1398.7	1398.7	1399.0	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2
152.5°	1421.7	1421.3	1421.7	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6
155°	1452.6	1451.5	1452.3	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9
157.5°	1479.4	1478.0	1478.9	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7
160°	1496.5	1494.9	1495.2	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6
162.5°	1510.6	1509.0	1509.2	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6
165°	1529.8	1527.8	1527.8	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7
167.5°	1544.2	1541.9	1542.1	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6
170°	1553.4	1551.3	1551.0	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1
172.5°	1558.9	1556.9	1556.6	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8
175°	1565.3	1563.0	1562.8	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8
177.5°	1568.6	1567.0	1566.6	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	15.5	14.7	13.6	13.7	14.2	13.8	14.6	15.0	15.5	15.3	16.6
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0
95°	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0
97.5°	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3
100°	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7
102.5°	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1
105°	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8
107.5°	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8
110°	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4
115°	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9
117.5°	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8
120°	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7
122.5°	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8
125°	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9
127.5°	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6
130°	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6
132.5°	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7
135°	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5
137.5°	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8
140°	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9
142.5°	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3
145°	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0
147.5°	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9
150°	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7
152.5°	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1
155°	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6
157.5°	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8
160°	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0
162.5°	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2
165°	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0
167.5°	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5
170°	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4
172.5°	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0
175°	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7
177.5°	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	16.0	15.9	16.5	16.2	16.3	16.0	16.5
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	519.1	519.6	520.2	521.0	521.8	522.6	523.3



TEST NUMBER: P332949-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)