

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332951-840

Luminaire Tested: **SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332951-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7717.0 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	40	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	1.7
10°-20°	389.6	5.0
20°-30°	609.4	7.9
30°-40°	677.4	8.8
40°-50°	601.0	7.8
50°-60°	468.4	6.1
60°-70°	306.6	4.0
70°-80°	150.8	2.0
80°-90°	40.5	0.5
90°-100°	431.4	5.6
100°-110°	897.9	11.6
110°-120°	804.2	10.4
120°-130°	676.5	8.8
130°-140°	564.1	7.3
140°-150°	430.9	5.6
150°-160°	302.9	3.9
160°-170°	178.2	2.3
170°-180°	58.0	0.8
0°-30°	1128.1	14.6
0°-40°	1805.6	23.4
0°-60°	2875.0	37.3
0°-90°	3372.9	43.7
90°-120°	2133.5	27.6
90°-150°	3805.0	49.3
90°-180°	4344.0	56.3
0°-180°	7717.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	25	1	25	1	25	21
95°	286	39	286	39	286	444
105°	1651	137	1651	137	1651	1632
115°	1585	242	1585	242	1585	1574
125°	1265	337	1265	337	1265	1149
135°	1131	400	1131	400	1131	873
145°	924	461	924	461	924	585
155°	773	524	773	524	773	361
165°	675	572	675	572	675	193
175°	608	596	608	596	608	59
180°	597	597	597	597	597	



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	14.3	13.9	14.6	14.3	14.5	14.1	14.3	14.9	13.8	14.5	14.0
90°	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1	20.0	21.1	18.8
92.5°	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5	310.0	372.2	325.8
95°	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5	983.4	956.3	721.6
97.5°	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8	1235.5	1007.3	675.4
100°	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2	1243.9	943.4	612.6
102.5°	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7	1173.5	863.6	570.3
105°	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2	1045.5	769.8	533.9
107.5°	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2	942.3	717.2	527.4
110°	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5	890.7	699.4	529.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4	861.5	690.9	534.8
115°	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0	834.4	686.5	545.6
117.5°	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9	822.1	685.3	557.1
120°	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8	815.6	685.3	565.6
122.5°	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5	808.1	684.4	574.1
125°	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3	795.6	683.0	586.7
127.5°	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7	778.9	680.3	596.8
130°	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1	768.6	679.4	604.3
132.5°	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3	759.2	678.5	610.9
135°	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1	745.2	677.1	620.8
137.5°	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5	733.0	676.8	626.6
140°	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3	726.4	675.9	631.4
142.5°	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2	720.7	675.9	635.1
145°	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7	711.1	673.6	637.2
147.5°	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5	702.5	669.3	638.3
150°	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1	695.9	666.5	638.3
152.5°	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7	688.3	661.9	636.5
155°	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2	677.1	654.8	633.7
157.5°	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6	665.6	647.5	630.7
160°	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3	657.1	641.9	627.8
162.5°	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9	649.6	636.2	625.0
165°	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6	637.2	627.8	619.6
167.5°	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8	625.9	619.4	614.0
170°	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3	618.4	613.7	610.2
172.5°	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7	611.9	608.0	606.4
175°	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7	604.3	602.0	602.0
177.5°	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1	599.2	598.2	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	13.6	13.1	12.6	12.6	12.8	14.3	14.8	14.8	14.0	13.4	12.4
90°	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2	3.5	7.1	8.2
92.5°	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3	19.5	30.5	44.8
95°	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7	42.2	54.0	69.3
97.5°	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5	69.5	79.6	93.6
100°	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2	89.2	97.4	111.5
102.5°	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0	109.9	117.1	130.3
105°	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3	140.8	146.7	160.8
107.5°	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7	172.0	177.9	192.9
110°	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3	193.6	199.4	213.6



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0	214.3	221.1	234.2
115°	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8	245.3	253.5	265.2
117.5°	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7	276.0	283.3	296.2
120°	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4	295.7	304.0	316.8
122.5°	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1	314.5	322.8	334.7
125°	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8	341.4	348.5	361.4
127.5°	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6	362.3	370.8	385.6
130°	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8	375.5	384.9	402.5
132.5°	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0	386.8	399.0	415.7
135°	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1	404.9	416.6	436.6
137.5°	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3	421.7	434.6	453.6
140°	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5	433.0	446.0	465.9
142.5°	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6	446.2	458.1	477.2
145°	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2	464.7	476.5	492.8
147.5°	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0	483.2	493.5	510.5
150°	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2	496.3	505.7	519.9
152.5°	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4	507.7	517.1	530.2
155°	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5	525.7	532.7	544.5
157.5°	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2	541.2	547.8	556.9
160°	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5	551.5	556.2	564.4
162.5°	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9	560.0	563.7	571.0
165°	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5	571.5	573.8	579.7
167.5°	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1	580.9	582.1	586.5
170°	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7	585.5	586.7	590.3
172.5°	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4	590.3	590.5	593.1
175°	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1	594.9	594.9	596.1
177.5°	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2	597.3	596.3	597.3
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	12.6	12.2	13.6	12.7	13.6	14.1	13.4	13.6	14.3	13.7	13.7
90°	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1	22.3	23.4	23.4
92.5°	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5	173.4	138.0	114.5
95°	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5	687.6	530.4	416.6
97.5°	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8	1217.1	1102.4	979.9
100°	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2	1438.7	1381.2	1294.3
102.5°	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7	1525.0	1541.7	1505.5
105°	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2	1517.3	1633.5	1681.5
107.5°	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2	1396.4	1560.0	1664.7
110°	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5	1302.5	1472.7	1601.7



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4	1219.9	1380.7	1509.7
115°	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0	1125.4	1262.6	1375.3
117.5°	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9	1071.4	1179.3	1274.9
120°	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8	1047.9	1141.8	1225.1
122.5°	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5	1032.9	1118.3	1191.3
125°	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3	1009.2	1090.1	1154.7
127.5°	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7	981.3	1062.0	1123.3
130°	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1	958.8	1038.5	1100.8
132.5°	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3	933.4	1011.3	1073.5
135°	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1	895.3	966.9	1025.6
137.5°	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5	859.0	919.3	972.3
140°	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3	835.5	888.3	937.6
142.5°	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2	815.8	861.1	903.8
145°	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7	788.6	823.7	856.7
147.5°	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5	765.1	793.2	819.1
150°	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1	751.0	774.5	795.6
152.5°	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7	736.9	758.5	775.9
155°	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2	717.0	734.6	748.7
157.5°	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6	697.3	712.1	723.4
160°	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3	684.1	697.0	706.4
162.5°	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9	672.0	682.1	690.4
165°	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6	653.6	661.9	667.7
167.5°	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8	638.1	644.7	648.2
170°	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3	627.8	632.5	636.0
172.5°	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7	619.4	622.2	624.7
175°	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7	607.8	610.2	610.2
177.5°	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1	601.1	601.1	602.0
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	14.8	14.6	13.9	14.3	13.9	14.6	14.8	13.7	13.7	14.3	13.6
90°	24.6	25.9	24.6	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1
92.5°	100.7	94.3	90.4	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5
95°	359.1	322.8	301.5	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5
97.5°	895.5	825.0	789.7	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8
100°	1192.2	1120.6	1085.5	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2
102.5°	1442.9	1391.0	1353.9	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7
105°	1683.9	1674.6	1658.1	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2
107.5°	1722.6	1749.4	1761.1	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2
110°	1685.1	1734.3	1755.5	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1604.4	1664.0	1693.5	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4
115°	1468.0	1538.4	1576.0	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0
117.5°	1353.9	1413.1	1451.1	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9
120°	1292.0	1343.6	1374.1	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8
122.5°	1247.9	1292.0	1317.8	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5
125°	1201.6	1235.7	1258.0	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3
127.5°	1170.4	1200.7	1219.5	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7
130°	1148.8	1178.1	1196.9	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1
132.5°	1120.6	1153.8	1171.5	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3
135°	1072.6	1105.4	1124.2	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1
137.5°	1016.2	1048.6	1064.1	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5
140°	978.7	1004.5	1020.9	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3
142.5°	940.2	964.1	978.7	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2
145°	886.0	905.9	917.7	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7
147.5°	840.7	857.8	866.8	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5
150°	814.4	829.6	836.7	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1
152.5°	791.8	804.3	808.5	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7
155°	760.4	769.8	773.4	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2
157.5°	732.3	739.3	741.4	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6
160°	713.5	720.5	721.6	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3
162.5°	695.6	702.7	703.9	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9
165°	672.4	677.1	675.9	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6
167.5°	650.6	653.6	653.4	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8
170°	638.3	639.5	638.3	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3
172.5°	626.1	627.3	626.1	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7
175°	610.2	612.6	610.2	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7
177.5°	601.1	602.0	600.1	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	13.4	14.1	13.6	12.7	13.6	12.2	12.6	12.4	13.4	14.0	14.8
90°	20.0	21.1	18.8	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2
92.5°	310.0	372.2	325.8	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3
95°	983.4	956.3	721.6	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7
97.5°	1235.5	1007.3	675.4	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5
100°	1243.9	943.4	612.6	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2
102.5°	1173.5	863.6	570.3	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0
105°	1045.5	769.8	533.9	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3
107.5°	942.3	717.2	527.4	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7
110°	890.7	699.4	529.3	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	861.5	690.9	534.8	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0
115°	834.4	686.5	545.6	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8
117.5°	822.1	685.3	557.1	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7
120°	815.6	685.3	565.6	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4
122.5°	808.1	684.4	574.1	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1
125°	795.6	683.0	586.7	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8
127.5°	778.9	680.3	596.8	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6
130°	768.6	679.4	604.3	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8
132.5°	759.2	678.5	610.9	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0
135°	745.2	677.1	620.8	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1
137.5°	733.0	676.8	626.6	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3
140°	726.4	675.9	631.4	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5
142.5°	720.7	675.9	635.1	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6
145°	711.1	673.6	637.2	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2
147.5°	702.5	669.3	638.3	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0
150°	695.9	666.5	638.3	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2
152.5°	688.3	661.9	636.5	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4
155°	677.1	654.8	633.7	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5
157.5°	665.6	647.5	630.7	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2
160°	657.1	641.9	627.8	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5
162.5°	649.6	636.2	625.0	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9
165°	637.2	627.8	619.6	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5
167.5°	625.9	619.4	614.0	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1
170°	618.4	613.7	610.2	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7
172.5°	611.9	608.0	606.4	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4
175°	604.3	602.0	602.0	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1
177.5°	599.2	598.2	598.2	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	14.8	14.3	12.8	12.6	12.6	13.1	13.6	14.0	14.5	13.8	14.9
90°	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1
92.5°	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5
95°	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5
97.5°	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8
100°	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2
102.5°	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7
105°	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2
107.5°	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2
110°	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4
115°	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0
117.5°	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9
120°	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8
122.5°	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5
125°	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3
127.5°	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7
130°	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1
132.5°	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3
135°	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1
137.5°	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5
140°	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3
142.5°	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2
145°	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7
147.5°	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5
150°	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1
152.5°	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7
155°	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2
157.5°	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6
160°	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3
162.5°	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9
165°	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6
167.5°	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8
170°	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3
172.5°	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7
175°	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7
177.5°	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	14.3	14.1	14.5	14.3	14.6	13.9	14.3
90°	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1



TEST NUMBER: P332951-840

CATALOG NUMBER: SA4XXRDIP-C795D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)