

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332552-930

Luminaire Tested: **SA4XXDIP-C575D590U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332552-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3754.8 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332552-930  
CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				54
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46				46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	44	43	38				38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32				32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28				28
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24				24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21				21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19				19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	2.0
10°-20°	210.1	5.6
20°-30°	309.2	8.2
30°-40°	359.5	9.6
40°-50°	359.5	9.6
50°-60°	314.5	8.4
60°-70°	233.5	6.2
70°-80°	132.7	3.5
80°-90°	39.6	1.1
90°-100°	171.0	4.6
100°-110°	355.9	9.5
110°-120°	318.7	8.5
120°-130°	268.1	7.1
130°-140°	223.6	6.0
140°-150°	170.8	4.5
150°-160°	120.0	3.2
160°-170°	70.6	1.9
170°-180°	23.0	0.6
0°-30°	593.9	15.8
0°-40°	953.4	25.4
0°-60°	1627.3	43.3
0°-90°	2033.1	54.1
90°-120°	845.6	22.5
90°-150°	1508.1	40.2
90°-180°	1722.0	45.9
0°-180°	3754.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	0	4	8	9	10	3
95°	15	48	379	188	114	17
105°	54	79	305	657	654	58
115°	96	120	272	523	628	95
125°	134	159	271	445	501	119
135°	159	189	268	395	448	123
145°	183	209	267	333	366	115
155°	208	224	260	294	306	96
165°	226	234	249	263	267	64
175°	236	237	239	242	241	22
180°	237	237	237	237	237	



TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.3	13.4	13.5	13.5	13.5	13.4	13.9	13.7	13.8	13.9	13.8
90°	0.5	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9
92.5°	5.3	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9
95°	15.3	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7
97.5°	27.6	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7
100°	35.4	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0
102.5°	42.8	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0
105°	54.4	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4
107.5°	67.3	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5
110°	75.8	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0



TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4
115°	95.8	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7
117.5°	108.1	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9
120°	116.3	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3
122.5°	123.7	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2
125°	133.5	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4
127.5°	142.1	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8
130°	147.0	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6
132.5°	151.8	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9
135°	158.6	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3
137.5°	165.4	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5
140°	170.2	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9
142.5°	175.5	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7
145°	182.8	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8
147.5°	191.0	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4
150°	196.2	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8
152.5°	201.1	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8
155°	207.9	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3
157.5°	214.5	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8
160°	218.6	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5
162.5°	222.3	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5
165°	226.5	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6
167.5°	230.6	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1
170°	232.5	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1
172.5°	234.4	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5
175°	236.3	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5
177.5°	237.1	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	13.9	13.9	14.0	14.0	14.1	14.3	14.1	14.1
90°	8.4	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	91.3	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	344.6	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	509.2	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	560.9	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	558.3	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	520.9	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	467.8	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	435.8	516.2	583.7	634.9	667.9	687.4	695.8	699.9





TEST NUMBER: P332552-930

CATALOG NUMBER: SA4XXDIP-C575D590U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	412.4	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	388.8	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	377.2	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	372.1	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	367.6	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	360.0	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	350.7	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	343.2	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	335.4	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	324.7	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	314.9	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	309.2	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	304.1	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	296.7	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	290.7	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	287.0	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	282.8	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	276.7	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	270.1	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	266.0	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	262.0	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	256.2	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	250.8	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	247.4	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	244.4	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.4	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	237.8	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)