

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332934-840

Luminaire Tested: **SA4XXRDIP-C795D590U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332934-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5625.8 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332934-840
CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11326	11326	11326
5°	11351	11212	11281
10°	11280	11077	11077
15°	11150	10845	10764
20°	10972	10539	10345
25°	10745	10180	9922
30°	10523	9803	9392
35°	10279	9411	8861
40°	9985	8965	8286
45°	9712	8524	7702
50°	9403	8013	7082
55°	9071	7484	6410
60°	8707	6902	5724
65°	8373	6178	5049
70°	7886	5375	4286
75°	7271	4457	3484
80°	6341	3394	3199
85°	5372	3084	2881



TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	2.3
10°-20°	367.5	6.5
20°-30°	530.6	9.4
30°-40°	601.5	10.7
40°-50°	580.8	10.3
50°-60°	483.0	8.6
60°-70°	333.5	5.9
70°-80°	169.1	3.0
80°-90°	45.6	0.8
90°-100°	26.3	0.5
100°-110°	168.0	3.0
110°-120°	321.3	5.7
120°-130°	407.9	7.3
130°-140°	436.4	7.8
140°-150°	408.1	7.3
150°-160°	329.1	5.8
160°-170°	212.2	3.8
170°-180°	73.2	1.3
0°-30°	1029.9	18.3
0°-40°	1631.4	29.0
0°-60°	2695.2	47.9
0°-90°	3243.4	57.7
90°-120°	515.6	9.2
90°-150°	1767.9	31.4
90°-180°	2382.0	42.3
0°-180°	5625.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1401	1396	1384	1394	1392	133
15°	1334	1324	1298	1295	1288	376
25°	1206	1186	1143	1125	1114	556
35°	1043	1008	955	919	899	651
45°	851	810	747	696	675	656
55°	644	600	532	478	455	576
65°	438	391	323	279	264	433
75°	233	193	143	119	112	246
85°	58	38	33	31	31	65
90°	2	8	13	16	17	4
95°	32	13	13	16	17	41
105°	173	177	180	183	164	181
115°	324	325	325	326	326	318
125°	455	457	456	458	459	406
135°	564	564	566	567	569	435
145°	651	653	653	653	654	407
155°	714	714	713	715	713	329
165°	753	750	750	754	749	213
175°	770	767	767	772	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1406.3	1405.5	1404.7	1404.0	1403.2	1401.8	1399.7	1397.7	1395.5	1393.4	1395.5
5°	1400.7	1399.8	1398.8	1397.9	1396.8	1395.0	1392.1	1389.3	1386.3	1383.5	1385.9
7.5°	1388.1	1387.0	1386.0	1385.0	1384.0	1381.7	1378.0	1374.2	1370.5	1366.8	1368.3
10°	1376.0	1374.8	1373.6	1372.4	1371.2	1368.5	1364.2	1359.9	1355.6	1351.3	1352.2
12.5°	1360.5	1359.2	1357.8	1356.3	1355.0	1351.8	1346.8	1341.6	1336.6	1331.5	1332.1
15°	1334.1	1332.0	1329.8	1327.7	1325.5	1321.5	1315.5	1309.5	1303.5	1297.6	1297.1
17.5°	1302.1	1299.0	1295.9	1292.8	1289.7	1284.5	1277.4	1270.2	1263.0	1255.9	1254.6
20°	1277.2	1274.0	1271.0	1267.9	1264.8	1259.2	1251.0	1242.9	1234.8	1226.7	1224.8
22.5°	1249.7	1246.2	1242.7	1239.2	1235.8	1229.6	1220.9	1212.2	1203.6	1194.9	1192.0
25°	1206.3	1201.9	1197.7	1193.4	1189.1	1182.0	1172.3	1162.5	1152.7	1142.9	1138.8
27.5°	1160.7	1155.4	1149.9	1144.6	1139.1	1131.3	1120.7	1110.3	1099.8	1089.4	1084.4
30°	1128.9	1123.0	1117.0	1111.1	1105.1	1096.5	1085.3	1074.1	1062.8	1051.6	1045.6
32.5°	1095.4	1088.7	1082.0	1075.2	1068.5	1059.3	1047.7	1036.1	1024.5	1012.9	1006.0
35°	1043.0	1035.4	1027.7	1020.1	1012.5	1002.7	990.8	978.8	966.8	954.9	946.8
37.5°	986.9	979.1	971.2	963.3	955.4	944.9	931.7	918.5	905.2	892.0	882.9
40°	947.5	939.6	931.7	923.8	915.9	905.1	891.5	878.0	864.3	850.7	840.7
42.5°	909.6	901.3	893.1	884.8	876.6	865.4	851.2	837.0	822.8	808.6	798.4
45°	850.7	841.9	833.0	824.3	815.4	803.9	789.5	775.2	760.8	746.6	734.9
47.5°	789.9	780.8	771.7	762.5	753.5	741.4	726.6	711.7	696.8	681.9	669.7
50°	748.7	739.4	730.0	720.7	711.4	699.1	683.9	668.6	653.3	638.0	626.1
52.5°	706.6	697.5	688.3	679.2	670.1	657.7	642.1	626.4	610.8	595.1	583.0
55°	644.5	634.9	625.4	615.8	606.3	593.8	578.2	562.7	547.2	531.7	519.3
57.5°	583.1	573.1	563.2	553.3	543.3	530.7	515.4	500.2	484.9	469.6	457.1
60°	539.3	529.7	520.2	510.6	501.0	488.7	473.3	458.1	442.8	427.5	415.1
62.5°	499.7	489.8	479.9	469.9	460.0	447.2	431.5	415.9	400.2	384.6	373.0
65°	438.3	428.0	417.7	407.5	397.2	384.5	369.1	353.9	338.6	323.4	313.1
67.5°	374.5	364.7	354.8	345.0	335.1	323.2	308.9	294.8	280.5	266.4	257.5
70°	334.1	324.1	314.0	304.0	294.0	282.2	268.5	254.9	241.4	227.7	219.8
72.5°	291.1	282.1	273.0	263.9	254.8	243.9	231.1	218.1	205.3	192.5	185.7
75°	233.1	224.3	215.4	206.6	197.7	187.7	176.5	165.3	154.1	142.9	137.3
77.5°	174.2	166.7	159.3	151.8	144.2	135.9	126.9	117.9	108.8	99.7	96.4
80°	136.4	129.5	122.6	115.6	108.8	101.7	94.5	87.4	80.2	73.0	72.3
82.5°	103.8	97.5	91.1	84.7	78.4	73.1	69.1	64.9	60.8	56.8	56.1
85°	58.0	53.2	48.5	43.7	38.9	36.2	35.4	34.7	34.0	33.3	32.8
87.5°	20.1	18.9	17.6	16.4	15.1	14.5	14.5	14.5	14.5	14.5	14.5
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	7.3	7.4	7.4	7.5	7.6	8.1	9.2	10.2	11.2	12.2	13.0
95°	31.7	27.4	23.0	18.6	14.2	12.1	12.3	12.4	12.5	12.6	13.4
97.5°	67.3	70.0	72.7	75.4	78.2	72.3	58.1	43.8	29.5	15.2	15.2
100°	94.4	96.7	99.1	101.4	103.7	96.0	78.4	60.7	43.0	25.3	23.1
102.5°	124.9	126.5	128.3	130.0	131.7	131.4	129.1	126.7	124.4	122.1	98.7
105°	173.4	174.2	174.9	175.7	176.4	177.1	177.8	178.4	179.0	179.8	180.9
107.5°	218.4	218.8	219.2	219.5	219.9	220.6	221.5	222.4	223.2	224.1	224.7
110°	248.8	249.2	249.6	250.0	250.3	251.0	251.8	252.5	253.3	254.1	254.3



TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.0	279.7	280.4	281.1	281.7	282.0	282.4	282.8	283.1	283.1
115°	323.8	324.2	324.5	324.9	325.3	325.4	325.3	325.2	325.0	324.9	325.2
117.5°	364.7	365.2	365.7	366.2	366.7	367.1	367.4	367.7	367.9	368.2	368.2
120°	392.3	392.8	393.3	393.8	394.4	394.6	394.5	394.3	394.2	394.0	394.3
122.5°	418.1	418.4	418.7	419.0	419.3	419.6	419.8	419.9	420.1	420.3	420.4
125°	455.0	455.6	456.2	456.7	457.2	457.3	457.0	456.8	456.5	456.3	456.7
127.5°	490.1	490.2	490.4	490.5	490.6	491.0	491.6	492.1	492.7	493.3	493.2
130°	512.7	512.8	512.9	513.1	513.2	513.4	513.8	514.2	514.6	515.0	515.1
132.5°	533.4	533.6	533.9	534.1	534.3	534.7	535.2	535.6	536.1	536.6	536.7
135°	564.5	564.4	564.3	564.1	564.0	564.2	564.7	565.2	565.7	566.2	566.5
137.5°	592.1	592.1	592.2	592.2	592.3	592.6	593.1	593.7	594.3	594.8	595.1
140°	610.1	610.3	610.6	610.8	611.1	611.3	611.6	611.9	612.1	612.4	612.7
142.5°	626.2	626.6	627.1	627.5	628.0	628.3	628.4	628.6	628.7	628.9	629.2
145°	651.0	651.4	651.7	652.1	652.5	652.7	652.7	652.7	652.7	652.7	652.8
147.5°	670.7	671.4	672.1	672.8	673.5	673.8	673.7	673.6	673.4	673.3	673.4
150°	684.9	685.4	686.0	686.5	687.0	687.2	687.0	686.9	686.8	686.6	686.6
152.5°	696.9	697.3	697.7	698.1	698.5	698.6	698.4	698.2	697.9	697.7	697.9
155°	713.8	713.9	714.0	714.1	714.3	714.1	713.8	713.4	713.0	712.6	713.1
157.5°	727.9	727.8	727.7	727.7	727.6	727.3	726.9	726.5	726.0	725.6	726.3
160°	736.2	735.8	735.4	735.1	734.7	734.4	734.3	734.2	734.0	733.9	734.7
162.5°	743.6	743.1	742.6	742.1	741.6	741.3	741.1	741.0	740.9	740.8	741.5
165°	752.9	752.2	751.6	750.9	750.3	750.0	750.0	750.0	750.0	750.0	751.0
167.5°	760.2	759.6	758.9	758.3	757.6	757.2	757.2	757.1	757.0	756.9	758.1
170°	764.5	763.7	762.9	762.1	761.3	761.0	761.1	761.2	761.4	761.5	762.5
172.5°	767.2	766.4	765.7	764.9	764.2	763.8	764.0	764.1	764.2	764.3	765.4
175°	770.2	769.4	768.6	767.9	767.1	766.8	766.9	767.1	767.2	767.3	768.4
177.5°	771.5	770.8	770.1	769.4	768.7	768.4	768.6	768.8	769.0	769.2	770.1
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1397.7	1399.7	1401.8	1402.8	1402.6	1402.4	1402.2	1402.0
5°	1388.3	1390.7	1393.1	1394.0	1393.5	1393.1	1392.6	1392.1
7.5°	1369.8	1371.4	1372.9	1373.2	1372.5	1371.7	1371.0	1370.2
10°	1353.2	1354.1	1355.1	1355.1	1354.1	1353.2	1352.2	1351.3
12.5°	1332.7	1333.2	1333.8	1333.4	1332.1	1330.8	1329.4	1328.1
15°	1296.7	1296.2	1295.7	1294.6	1292.9	1291.2	1289.6	1287.9
17.5°	1253.2	1251.9	1250.5	1248.6	1246.1	1243.5	1241.0	1238.5
20°	1222.8	1220.9	1219.0	1216.6	1213.5	1210.3	1207.2	1204.2
22.5°	1189.2	1186.3	1183.5	1180.7	1178.2	1175.7	1173.2	1170.6
25°	1134.8	1130.7	1126.7	1123.5	1121.1	1118.7	1116.3	1113.9
27.5°	1079.3	1074.4	1069.3	1065.1	1061.7	1058.2	1054.8	1051.4
30°	1039.7	1033.7	1027.7	1022.8	1019.1	1015.2	1011.4	1007.5
32.5°	999.1	992.2	985.2	980.0	976.3	972.7	969.1	965.4
35°	938.7	930.6	922.5	916.3	912.0	907.7	903.3	899.1
37.5°	873.8	864.7	855.7	849.0	844.8	840.4	836.2	831.8
40°	830.7	820.6	810.6	803.4	799.2	794.9	790.6	786.3
42.5°	788.2	778.0	767.8	760.4	755.9	751.4	747.0	742.5
45°	723.2	711.4	699.7	691.8	687.4	683.2	678.8	674.6
47.5°	657.6	645.5	633.4	624.9	620.3	615.5	610.8	606.0
50°	614.2	602.3	590.3	582.1	577.5	573.0	568.5	563.9
52.5°	570.9	558.8	546.5	538.2	533.4	528.7	524.0	519.3
55°	506.9	494.4	482.1	473.6	469.1	464.5	460.0	455.4
57.5°	444.4	431.8	419.2	411.2	407.8	404.3	400.9	397.5
60°	402.7	390.3	377.9	369.7	366.0	362.1	358.3	354.5
62.5°	361.6	350.2	338.7	331.4	328.4	325.4	322.2	319.2
65°	302.8	292.6	282.3	275.7	272.9	269.9	267.1	264.3
67.5°	248.7	239.9	231.1	225.1	222.0	218.7	215.6	212.5
70°	212.0	204.1	196.2	191.1	188.7	186.3	183.9	181.6
72.5°	179.0	172.3	165.5	161.1	159.0	156.7	154.5	152.3
75°	131.9	126.4	120.9	117.4	116.0	114.6	113.1	111.7
77.5°	93.3	90.1	86.8	85.0	84.6	84.2	83.8	83.3
80°	71.6	70.9	70.2	69.7	69.5	69.2	69.0	68.8
82.5°	55.6	55.1	54.6	54.2	54.0	53.7	53.5	53.3
85°	32.3	31.9	31.4	31.1	31.1	31.1	31.1	31.1
87.5°	14.4	14.4	14.4	14.5	14.7	15.0	15.2	15.5
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	13.7	14.5	15.2	15.7	15.8	15.8	15.9	15.9
95°	14.2	14.9	15.8	16.2	16.4	16.5	16.6	16.7
97.5°	15.3	15.5	15.6	15.7	15.8	15.9	16.0	16.2
100°	21.0	18.8	16.7	15.7	15.8	15.9	16.0	16.2
102.5°	75.1	51.7	28.2	16.5	16.6	16.6	16.6	16.6
105°	182.1	183.2	184.3	182.6	178.0	173.4	168.7	164.2
107.5°	225.2	225.8	226.3	226.8	227.3	227.8	228.3	228.8
110°	254.6	254.8	255.1	255.4	255.8	256.1	256.5	256.9



TEST NUMBER: P332934-840

CATALOG NUMBER: SA4XXRDIP-C795D590U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	283.0	283.0	282.9	283.1	283.6	284.1	284.6	285.0
115°	325.4	325.7	325.9	326.1	326.1	326.1	326.1	326.1
117.5°	368.1	368.1	368.0	368.0	367.9	367.9	367.8	367.8
120°	394.6	394.8	395.1	395.1	394.8	394.6	394.3	394.0
122.5°	420.6	420.7	420.9	420.8	420.6	420.3	420.1	419.8
125°	457.0	457.4	457.8	458.1	458.2	458.3	458.4	458.6
127.5°	493.2	493.1	493.0	492.9	492.8	492.7	492.6	492.5
130°	515.2	515.3	515.5	515.5	515.5	515.5	515.5	515.5
132.5°	536.9	537.0	537.1	537.1	537.0	536.9	536.8	536.7
135°	566.7	567.0	567.2	567.5	567.7	568.0	568.4	568.6
137.5°	595.4	595.7	595.9	596.0	596.0	595.9	595.8	595.7
140°	613.1	613.5	613.9	614.1	614.3	614.4	614.5	614.6
142.5°	629.4	629.8	630.1	630.3	630.3	630.3	630.3	630.4
145°	652.9	653.1	653.2	653.4	653.6	653.9	654.2	654.4
147.5°	673.5	673.6	673.7	673.8	674.0	674.1	674.2	674.3
150°	686.6	686.6	686.6	686.7	686.8	687.0	687.1	687.2
152.5°	698.1	698.3	698.5	698.6	698.5	698.4	698.3	698.3
155°	713.6	714.1	714.6	714.7	714.3	713.9	713.6	713.2
157.5°	726.9	727.6	728.2	728.2	727.6	726.9	726.3	725.6
160°	735.4	736.2	737.0	737.0	736.2	735.4	734.7	733.9
162.5°	742.4	743.1	743.9	743.9	743.0	742.0	741.2	740.3
165°	752.0	753.1	754.2	754.1	752.9	751.7	750.6	749.4
167.5°	759.2	760.3	761.4	761.3	760.1	758.8	757.5	756.3
170°	763.6	764.6	765.7	765.5	764.3	763.0	761.6	760.4
172.5°	766.4	767.4	768.4	768.2	766.9	765.5	764.1	762.7
175°	769.6	770.7	771.9	771.7	770.2	768.6	767.1	765.6
177.5°	770.9	771.7	772.5	772.3	771.1	769.9	768.6	767.4
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2

(END OF REPORT)