

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332940-840

Luminaire Tested: **SA4XXRDIP-C795D810U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332940-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6509.8 lumens
Efficiency: N/A
Efficacy: 141.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43				
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36				
3	82	72	65	60	75	67	61	56	57	52	49	48	45	42	39	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23				
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21				
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11326	11326	11326
5°	11351	11212	11281
10°	11280	11077	11077
15°	11150	10845	10764
20°	10972	10539	10345
25°	10745	10180	9922
30°	10523	9803	9392
35°	10279	9411	8861
40°	9985	8965	8286
45°	9712	8524	7702
50°	9403	8013	7082
55°	9071	7484	6410
60°	8707	6902	5724
65°	8373	6178	5049
70°	7886	5375	4286
75°	7271	4457	3484
80°	6341	3394	3199
85°	5372	3084	2881



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	2.0
10°-20°	367.5	5.6
20°-30°	530.6	8.2
30°-40°	601.5	9.2
40°-50°	580.8	8.9
50°-60°	483.0	7.4
60°-70°	333.5	5.1
70°-80°	169.1	2.6
80°-90°	46.4	0.7
90°-100°	36.1	0.6
100°-110°	230.2	3.5
110°-120°	440.4	6.8
120°-130°	559.1	8.6
130°-140°	598.2	9.2
140°-150°	559.3	8.6
150°-160°	451.1	6.9
160°-170°	290.9	4.5
170°-180°	100.3	1.5
0°-30°	1029.9	15.8
0°-40°	1631.4	25.1
0°-60°	2695.2	41.4
0°-90°	3244.2	49.8
90°-120°	706.7	10.9
90°-150°	2423.3	37.2
90°-180°	3266.0	50.2
0°-180°	6509.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1401	1396	1384	1394	1392	133
15°	1334	1324	1298	1295	1288	376
25°	1206	1186	1143	1125	1114	556
35°	1043	1008	955	919	899	651
45°	851	810	747	696	675	656
55°	644	600	532	478	455	576
65°	438	391	323	279	264	433
75°	233	193	143	119	112	246
85°	58	38	33	31	31	65
90°	2	11	17	22	24	5
95°	43	18	17	22	23	56
105°	238	242	246	252	225	249
115°	444	446	445	447	447	437
125°	624	627	625	628	628	557
135°	774	773	776	778	779	596
145°	892	894	895	895	897	557
155°	978	979	977	980	978	451
165°	1032	1028	1028	1034	1027	292
175°	1056	1051	1052	1058	1049	100
180°	1056	1056	1056	1056	1056	



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1406.3	1405.5	1404.7	1404.0	1403.2	1401.8	1399.7	1397.7	1395.5	1393.4	1395.5
5°	1400.7	1399.8	1398.8	1397.9	1396.8	1395.0	1392.1	1389.3	1386.3	1383.5	1385.9
7.5°	1388.1	1387.0	1386.0	1385.0	1384.0	1381.7	1378.0	1374.2	1370.5	1366.8	1368.3
10°	1376.0	1374.8	1373.6	1372.4	1371.2	1368.5	1364.2	1359.9	1355.6	1351.3	1352.2
12.5°	1360.5	1359.2	1357.8	1356.3	1355.0	1351.8	1346.8	1341.6	1336.6	1331.5	1332.1
15°	1334.1	1332.0	1329.8	1327.7	1325.5	1321.5	1315.5	1309.5	1303.5	1297.6	1297.1
17.5°	1302.1	1299.0	1295.9	1292.8	1289.7	1284.5	1277.4	1270.2	1263.0	1255.9	1254.6
20°	1277.2	1274.0	1271.0	1267.9	1264.8	1259.2	1251.0	1242.9	1234.8	1226.7	1224.8
22.5°	1249.7	1246.2	1242.7	1239.2	1235.8	1229.6	1220.9	1212.2	1203.6	1194.9	1192.0
25°	1206.3	1201.9	1197.7	1193.4	1189.1	1182.0	1172.3	1162.5	1152.7	1142.9	1138.8
27.5°	1160.7	1155.4	1149.9	1144.6	1139.1	1131.3	1120.7	1110.3	1099.8	1089.4	1084.4
30°	1128.9	1123.0	1117.0	1111.1	1105.1	1096.5	1085.3	1074.1	1062.8	1051.6	1045.6
32.5°	1095.4	1088.7	1082.0	1075.2	1068.5	1059.3	1047.7	1036.1	1024.5	1012.9	1006.0
35°	1043.0	1035.4	1027.7	1020.1	1012.5	1002.7	990.8	978.8	966.8	954.9	946.8
37.5°	986.9	979.1	971.2	963.3	955.4	944.9	931.7	918.5	905.2	892.0	882.9
40°	947.5	939.6	931.7	923.8	915.9	905.1	891.5	878.0	864.3	850.7	840.7
42.5°	909.6	901.3	893.1	884.8	876.6	865.4	851.2	837.0	822.8	808.6	798.4
45°	850.7	841.9	833.0	824.3	815.4	803.9	789.5	775.2	760.8	746.6	734.9
47.5°	789.9	780.8	771.7	762.5	753.5	741.4	726.6	711.7	696.8	681.9	669.7
50°	748.7	739.4	730.0	720.7	711.4	699.1	683.9	668.6	653.3	638.0	626.1
52.5°	706.6	697.5	688.3	679.2	670.1	657.7	642.1	626.4	610.8	595.1	583.0
55°	644.5	634.9	625.4	615.8	606.3	593.8	578.2	562.7	547.2	531.7	519.3
57.5°	583.1	573.1	563.2	553.3	543.3	530.7	515.4	500.2	484.9	469.6	457.1
60°	539.3	529.7	520.2	510.6	501.0	488.7	473.3	458.1	442.8	427.5	415.1
62.5°	499.7	489.8	479.9	469.9	460.0	447.2	431.5	415.9	400.2	384.6	373.0
65°	438.3	428.0	417.7	407.5	397.2	384.5	369.1	353.9	338.6	323.4	313.1
67.5°	374.5	364.7	354.8	345.0	335.1	323.2	308.9	294.8	280.5	266.4	257.5
70°	334.1	324.1	314.0	304.0	294.0	282.2	268.5	254.9	241.4	227.7	219.8
72.5°	291.1	282.1	273.0	263.9	254.8	243.9	231.1	218.1	205.3	192.5	185.7
75°	233.1	224.3	215.4	206.6	197.7	187.7	176.5	165.3	154.1	142.9	137.3
77.5°	174.2	166.7	159.3	151.8	144.2	135.9	126.9	117.9	108.8	99.7	96.4
80°	136.4	129.5	122.6	115.6	108.8	101.7	94.5	87.4	80.2	73.0	72.3
82.5°	103.8	97.5	91.1	84.7	78.4	73.1	69.1	64.9	60.8	56.8	56.1
85°	58.0	53.2	48.5	43.7	38.9	36.2	35.4	34.7	34.0	33.3	32.8
87.5°	20.2	19.1	18.0	16.8	15.7	15.1	15.2	15.3	15.5	15.6	15.6
90°	2.3	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4
92.5°	10.0	10.1	10.2	10.3	10.4	11.1	12.5	13.9	15.3	16.8	17.8
95°	43.4	37.5	31.5	25.5	19.6	16.7	16.9	17.1	17.2	17.4	18.4
97.5°	92.2	95.9	99.7	103.4	107.1	99.2	79.6	60.0	40.4	20.8	20.9
100°	129.5	132.7	135.8	139.0	142.1	131.6	107.3	83.2	59.0	34.7	31.7
102.5°	171.2	173.5	175.8	178.1	180.5	180.1	176.8	173.7	170.6	167.4	135.2
105°	237.6	238.7	239.7	240.9	241.9	242.9	243.7	244.6	245.5	246.3	247.9
107.5°	299.4	299.9	300.4	301.0	301.5	302.4	303.6	304.8	306.0	307.2	307.9
110°	341.1	341.6	342.1	342.6	343.3	344.0	345.1	346.1	347.2	348.2	348.6



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.4	383.4	384.4	385.4	386.1	386.6	387.0	387.5	388.0	388.0
115°	443.7	444.2	444.8	445.4	445.9	446.1	445.9	445.7	445.6	445.4	445.7
117.5°	499.8	500.5	501.2	501.9	502.6	503.2	503.5	503.9	504.3	504.7	504.6
120°	537.8	538.5	539.2	539.9	540.5	540.8	540.6	540.5	540.3	540.1	540.5
122.5°	573.1	573.5	573.9	574.3	574.8	575.1	575.3	575.6	575.8	576.1	576.3
125°	623.8	624.5	625.2	625.9	626.6	626.7	626.4	626.1	625.7	625.4	625.9
127.5°	671.8	672.0	672.2	672.4	672.5	673.0	673.8	674.6	675.4	676.2	676.1
130°	702.8	703.0	703.1	703.3	703.5	703.8	704.3	704.9	705.4	705.9	706.1
132.5°	731.1	731.4	731.8	732.2	732.5	733.0	733.6	734.3	734.9	735.6	735.8
135°	773.9	773.7	773.5	773.3	773.2	773.4	774.1	774.8	775.5	776.2	776.5
137.5°	811.5	811.6	811.7	811.7	811.8	812.2	813.0	813.9	814.6	815.4	815.8
140°	836.2	836.6	836.9	837.3	837.6	838.0	838.3	838.7	839.0	839.3	839.9
142.5°	858.3	858.9	859.6	860.2	860.8	861.2	861.4	861.7	861.9	862.1	862.5
145°	892.2	892.8	893.3	893.8	894.3	894.6	894.6	894.6	894.6	894.6	894.8
147.5°	919.3	920.3	921.2	922.2	923.2	923.6	923.4	923.2	923.0	922.9	923.0
150°	938.9	939.6	940.3	941.0	941.6	941.9	941.7	941.6	941.4	941.2	941.2
152.5°	955.2	955.8	956.3	956.9	957.6	957.7	957.4	957.0	956.6	956.3	956.6
155°	978.4	978.5	978.7	978.9	979.1	978.9	978.4	977.8	977.2	976.7	977.4
157.5°	997.7	997.6	997.5	997.4	997.3	996.9	996.3	995.8	995.2	994.6	995.5
160°	1009.2	1008.6	1008.0	1007.5	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0
162.5°	1019.3	1018.5	1017.8	1017.2	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5
165°	1032.0	1031.2	1030.3	1029.4	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5
167.5°	1042.1	1041.2	1040.3	1039.4	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1
170°	1047.8	1046.7	1045.7	1044.6	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2
172.5°	1051.6	1050.6	1049.5	1048.4	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0
175°	1055.7	1054.6	1053.6	1052.6	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3
177.5°	1057.6	1056.6	1055.6	1054.6	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1397.7	1399.7	1401.8	1402.8	1402.6	1402.4	1402.2	1402.0
5°	1388.3	1390.7	1393.1	1394.0	1393.5	1393.1	1392.6	1392.1
7.5°	1369.8	1371.4	1372.9	1373.2	1372.5	1371.7	1371.0	1370.2
10°	1353.2	1354.1	1355.1	1355.1	1354.1	1353.2	1352.2	1351.3
12.5°	1332.7	1333.2	1333.8	1333.4	1332.1	1330.8	1329.4	1328.1
15°	1296.7	1296.2	1295.7	1294.6	1292.9	1291.2	1289.6	1287.9
17.5°	1253.2	1251.9	1250.5	1248.6	1246.1	1243.5	1241.0	1238.5
20°	1222.8	1220.9	1219.0	1216.6	1213.5	1210.3	1207.2	1204.2
22.5°	1189.2	1186.3	1183.5	1180.7	1178.2	1175.7	1173.2	1170.6
25°	1134.8	1130.7	1126.7	1123.5	1121.1	1118.7	1116.3	1113.9
27.5°	1079.3	1074.4	1069.3	1065.1	1061.7	1058.2	1054.8	1051.4
30°	1039.7	1033.7	1027.7	1022.8	1019.1	1015.2	1011.4	1007.5
32.5°	999.1	992.2	985.2	980.0	976.3	972.7	969.1	965.4
35°	938.7	930.6	922.5	916.3	912.0	907.7	903.3	899.1
37.5°	873.8	864.7	855.7	849.0	844.8	840.4	836.2	831.8
40°	830.7	820.6	810.6	803.4	799.2	794.9	790.6	786.3
42.5°	788.2	778.0	767.8	760.4	755.9	751.4	747.0	742.5
45°	723.2	711.4	699.7	691.8	687.4	683.2	678.8	674.6
47.5°	657.6	645.5	633.4	624.9	620.3	615.5	610.8	606.0
50°	614.2	602.3	590.3	582.1	577.5	573.0	568.5	563.9
52.5°	570.9	558.8	546.5	538.2	533.4	528.7	524.0	519.3
55°	506.9	494.4	482.1	473.6	469.1	464.5	460.0	455.4
57.5°	444.4	431.8	419.2	411.2	407.8	404.3	400.9	397.5
60°	402.7	390.3	377.9	369.7	366.0	362.1	358.3	354.5
62.5°	361.6	350.2	338.7	331.4	328.4	325.4	322.2	319.2
65°	302.8	292.6	282.3	275.7	272.9	269.9	267.1	264.3
67.5°	248.7	239.9	231.1	225.1	222.0	218.7	215.6	212.5
70°	212.0	204.1	196.2	191.1	188.7	186.3	183.9	181.6
72.5°	179.0	172.3	165.5	161.1	159.0	156.7	154.5	152.3
75°	131.9	126.4	120.9	117.4	116.0	114.6	113.1	111.7
77.5°	93.3	90.1	86.8	85.0	84.6	84.2	83.8	83.3
80°	71.6	70.9	70.2	69.7	69.5	69.2	69.0	68.8
82.5°	55.6	55.1	54.6	54.2	54.0	53.7	53.5	53.3
85°	32.3	31.9	31.4	31.1	31.1	31.1	31.1	31.1
87.5°	15.6	15.6	15.6	15.8	16.0	16.3	16.5	16.8
90°	19.5	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	18.9	19.9	20.9	21.5	21.6	21.6	21.7	21.8
95°	19.5	20.5	21.6	22.2	22.4	22.5	22.7	22.9
97.5°	21.1	21.2	21.3	21.4	21.6	21.7	21.9	22.1
100°	28.8	25.8	22.8	21.4	21.6	21.7	21.9	22.1
102.5°	103.0	70.9	38.7	22.6	22.6	22.6	22.7	22.7
105°	249.5	251.1	252.7	250.3	244.0	237.6	231.4	225.0
107.5°	308.7	309.4	310.2	310.9	311.6	312.3	313.0	313.7
110°	348.9	349.3	349.6	350.0	350.6	351.1	351.6	352.1



TEST NUMBER: P332940-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.9	387.8	387.7	388.0	388.7	389.4	390.0	390.7
115°	446.1	446.4	446.8	447.0	447.0	447.0	447.0	447.0
117.5°	504.5	504.5	504.4	504.3	504.3	504.2	504.1	504.1
120°	540.8	541.2	541.5	541.5	541.2	540.8	540.5	540.1
122.5°	576.5	576.7	576.9	576.8	576.5	576.1	575.8	575.4
125°	626.4	626.9	627.4	627.8	628.0	628.1	628.3	628.5
127.5°	676.0	675.9	675.8	675.7	675.5	675.4	675.3	675.1
130°	706.3	706.4	706.6	706.7	706.7	706.7	706.7	706.7
132.5°	736.0	736.1	736.3	736.3	736.2	736.0	735.9	735.8
135°	776.9	777.2	777.6	777.9	778.3	778.6	779.0	779.3
137.5°	816.1	816.5	816.9	817.0	816.9	816.8	816.7	816.6
140°	840.4	840.9	841.4	841.8	842.0	842.1	842.3	842.5
142.5°	862.8	863.2	863.6	863.8	863.8	863.9	863.9	863.9
145°	894.9	895.1	895.3	895.5	896.0	896.3	896.7	897.0
147.5°	923.2	923.3	923.4	923.6	923.8	923.9	924.1	924.3
150°	941.2	941.2	941.2	941.3	941.5	941.6	941.8	942.0
152.5°	956.9	957.3	957.5	957.6	957.5	957.4	957.3	957.2
155°	978.2	978.9	979.6	979.7	979.1	978.6	978.1	977.5
157.5°	996.4	997.3	998.3	998.3	997.3	996.4	995.5	994.6
160°	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9
162.5°	1017.5	1018.5	1019.7	1019.6	1018.3	1017.1	1016.0	1014.8
165°	1030.9	1032.3	1033.7	1033.6	1032.0	1030.5	1028.9	1027.2
167.5°	1040.7	1042.2	1043.7	1043.6	1041.9	1040.1	1038.3	1036.6
170°	1046.6	1048.0	1049.5	1049.2	1047.5	1045.8	1044.0	1042.3
172.5°	1050.5	1051.9	1053.3	1053.0	1051.2	1049.2	1047.3	1045.4
175°	1054.9	1056.5	1058.0	1057.8	1055.7	1053.6	1051.5	1049.4
177.5°	1056.7	1057.8	1058.9	1058.6	1056.9	1055.3	1053.6	1051.9
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7

(END OF REPORT)