

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332656-940

Luminaire Tested: **SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332656-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6949.4 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

### Luminous Intensity Polar Plot





TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	45	40				
2	88	80	73	68	80	74	68	63	62	58	54	51	48	46	42	39	37	33				
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31	27				
4	73	61	53	47	67	57	50	44	48	42	38	40	36	32	32	29	27	23				
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23	20				
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20	17				
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18	15				
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16	13				
9	49	36	29	24	45	34	27	22	29	23	20	24	20	17	20	17	14	12				
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8888	8888	8888
5°	8916	8686	8711
10°	8861	8544	8538
15°	8782	8380	8334
20°	8662	8198	8135
25°	8527	7995	7918
30°	8381	7793	7693
35°	8216	7585	7497
40°	8083	7388	7292
45°	7887	7207	7117
50°	7721	6996	6931
55°	7549	6799	6714
60°	7282	6547	6515
65°	6989	6278	6271
70°	6633	5968	5986
75°	6136	5628	5730
80°	5588	5302	5476
85°	4893	5013	5328



TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.3	1.5
10°-20°	298.7	4.3
20°-30°	451.7	6.5
30°-40°	546.5	7.9
40°-50°	577.7	8.3
50°-60°	543.7	7.8
60°-70°	451.1	6.5
70°-80°	316.9	4.6
80°-90°	182.6	2.6
90°-100°	182.3	2.6
100°-110°	303.6	4.4
110°-120°	434.5	6.3
120°-130°	533.0	7.7
130°-140°	578.1	8.3
140°-150°	558.0	8.0
150°-160°	467.1	6.7
160°-170°	310.8	4.5
170°-180°	108.8	1.6
0°-30°	854.6	12.3
0°-40°	1401.1	20.2
0°-60°	2522.6	36.3
0°-90°	3473.2	50.0
90°-120°	920.4	13.2
90°-150°	2589.4	37.3
90°-180°	3476.0	50.0
0°-180°	6949.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1101	1101	1101	1101	1101	
5°	1102	1098	1090	1099	1098	105
15°	1057	1058	1054	1065	1064	298
25°	967	974	978	991	992	445
35°	846	860	873	889	894	529
45°	705	729	752	772	779	545
55°	552	579	615	639	647	492
65°	382	422	464	493	504	379
75°	212	258	309	343	355	226
85°	65	117	173	208	222	70
90°	22	82	142	181	194	16
95°	70	119	175	210	222	72
105°	218	245	293	326	339	233
115°	396	408	444	469	478	390
125°	570	571	599	620	626	508
135°	731	737	745	763	768	566
145°	887	889	890	896	899	555
155°	1015	1015	1014	1017	1014	467
165°	1105	1102	1100	1105	1102	311
175°	1149	1145	1144	1149	1144	109
180°	1151	1151	1151	1151	1151	



TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0
2.5°	1104.9	1104.3	1103.6	1103.0	1102.2	1101.1	1099.3	1097.6	1095.8	1094.0	1095.6
5°	1102.2	1101.4	1100.5	1099.7	1098.9	1097.5	1095.6	1093.7	1091.8	1089.8	1092.1
7.5°	1092.8	1092.3	1091.8	1091.4	1090.8	1089.8	1088.2	1086.6	1085.0	1083.4	1085.9
10°	1084.9	1084.7	1084.4	1084.1	1083.9	1083.0	1081.6	1080.3	1078.9	1077.5	1080.0
12.5°	1074.1	1074.1	1074.0	1073.9	1073.9	1073.4	1072.5	1071.5	1070.6	1069.6	1071.9
15°	1056.6	1056.9	1057.1	1057.4	1057.7	1057.4	1056.6	1055.8	1054.9	1054.1	1056.6
17.5°	1032.7	1033.5	1034.3	1035.1	1036.0	1036.3	1036.1	1036.0	1035.8	1035.6	1038.1
20°	1015.9	1016.7	1017.5	1018.3	1019.2	1019.8	1020.0	1020.3	1020.6	1020.8	1023.6
22.5°	997.1	998.2	999.3	1000.3	1001.3	1002.1	1002.6	1003.1	1003.5	1004.1	1006.8
25°	966.6	968.2	969.8	971.5	973.1	974.4	975.2	976.1	976.9	977.7	980.7
27.5°	932.6	935.0	937.4	939.8	942.2	944.1	945.3	946.6	947.8	949.0	951.9
30°	909.9	912.0	914.3	916.4	918.6	920.7	922.6	924.5	926.4	928.4	931.4
32.5°	885.2	887.9	890.5	893.1	895.7	898.1	900.3	902.4	904.6	906.7	910.1
35°	845.8	849.1	852.3	855.6	858.9	861.9	864.7	867.4	870.1	872.9	876.7
37.5°	806.0	809.9	813.6	817.4	821.2	824.7	828.1	831.5	835.0	838.4	842.2
40°	780.4	784.0	787.6	791.1	794.7	798.3	802.2	806.0	809.9	813.7	817.8
42.5°	750.8	754.8	758.8	762.9	766.8	771.1	775.5	780.1	784.5	789.1	793.6
45°	705.2	710.4	715.6	720.9	726.0	731.2	736.5	741.6	746.8	752.1	756.7
47.5°	661.6	666.9	672.3	677.7	683.1	688.8	694.7	700.8	706.9	712.8	717.6
50°	630.0	636.1	642.0	648.1	654.1	660.1	666.2	672.2	678.2	684.2	689.7
52.5°	598.4	604.5	610.5	616.5	622.6	629.0	635.9	642.8	649.7	656.7	662.1
55°	552.3	558.1	563.8	569.6	575.3	582.3	590.6	598.8	607.0	615.2	620.7
57.5°	500.8	507.9	515.1	522.2	529.3	536.9	545.1	553.3	561.4	569.6	576.1
60°	467.3	474.4	481.5	488.7	495.8	503.8	512.9	521.9	530.9	540.0	546.3
62.5°	434.7	442.5	450.3	458.1	465.8	474.2	483.3	492.3	501.4	510.4	516.7
65°	382.2	390.9	399.8	408.5	417.2	426.3	435.6	445.0	454.2	463.6	470.4
67.5°	331.6	341.0	350.3	359.6	368.9	378.5	388.5	398.5	408.5	418.5	425.4
70°	297.1	306.5	315.8	325.0	334.4	344.3	354.6	365.1	375.5	385.9	393.3
72.5°	263.6	273.1	282.7	292.2	301.8	312.0	323.1	334.1	345.3	356.3	363.5
75°	212.0	222.2	232.3	242.5	252.6	263.4	274.9	286.4	297.9	309.4	317.1
77.5°	164.0	174.7	185.5	196.2	207.0	218.3	230.4	242.5	254.5	266.5	274.3
80°	134.4	145.3	156.3	167.3	178.3	189.8	201.8	213.8	225.9	237.9	246.2
82.5°	104.8	116.2	127.6	139.0	150.3	162.1	174.2	186.2	198.3	210.4	218.7
85°	65.4	76.9	88.4	99.9	111.4	123.3	135.6	147.9	160.2	172.6	180.8
87.5°	37.0	48.6	60.3	71.9	83.5	95.4	107.7	120.1	132.4	144.7	152.9
90°	22.4	35.5	48.7	61.8	74.9	88.2	101.6	114.9	128.3	141.6	150.8
92.5°	37.8	50.1	62.5	74.8	87.2	99.9	112.7	125.6	138.5	151.4	159.8
95°	69.5	80.3	91.0	101.9	112.7	124.4	137.1	149.6	162.3	174.9	182.9
97.5°	107.8	117.0	126.3	135.5	144.6	155.6	168.4	181.1	193.9	206.6	214.5
100°	138.1	146.1	154.0	161.9	169.9	180.0	192.5	204.9	217.4	229.9	237.6
102.5°	170.9	177.5	184.0	190.6	197.2	206.5	218.6	230.7	242.7	254.9	262.6
105°	218.5	224.2	229.8	235.5	241.2	249.5	260.4	271.3	282.3	293.2	300.7
107.5°	270.7	275.4	280.2	284.9	289.6	296.9	306.6	316.3	326.0	335.7	343.0
110°	305.3	309.6	313.8	318.1	322.3	329.1	338.5	347.9	357.3	366.7	372.6



TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	341.4	344.9	348.4	351.9	355.3	361.4	370.2	379.1	387.8	396.6	402.6
115°	395.5	397.9	400.4	402.9	405.3	410.7	419.1	427.5	435.9	444.3	450.0
117.5°	447.5	449.2	450.8	452.5	454.1	458.9	466.7	474.7	482.5	490.4	495.4
120°	481.4	483.0	484.6	486.2	487.9	492.4	499.7	507.1	514.4	521.8	526.3
122.5°	517.7	518.3	518.7	519.2	519.7	523.5	530.7	538.0	545.2	552.5	557.2
125°	570.1	569.8	569.5	569.3	569.0	572.2	578.9	585.5	592.2	598.8	603.6
127.5°	618.5	618.8	619.1	619.4	619.7	622.4	627.3	632.2	637.2	642.1	646.7
130°	651.7	651.9	652.3	652.6	652.9	655.3	659.7	664.1	668.4	672.8	677.3
132.5°	686.5	686.7	686.9	687.1	687.2	688.9	692.3	695.6	699.0	702.3	706.7
135°	731.4	732.6	733.8	734.9	736.2	737.7	739.7	741.5	743.5	745.4	749.4
137.5°	781.6	781.9	782.2	782.5	782.7	783.5	784.7	786.0	787.2	788.5	792.0
140°	815.1	815.2	815.3	815.5	815.6	815.7	816.0	816.3	816.6	816.9	820.2
142.5°	844.7	845.1	845.4	845.7	846.1	846.1	845.8	845.4	845.1	844.8	847.8
145°	886.8	887.3	887.9	888.4	888.9	889.2	889.5	889.7	889.8	890.0	891.5
147.5°	928.8	929.5	930.2	930.9	931.6	931.8	931.7	931.5	931.3	931.2	931.2
150°	954.5	955.0	955.5	956.0	956.5	956.8	956.8	956.8	956.8	956.8	956.8
152.5°	977.7	978.1	978.6	978.9	979.4	979.6	979.8	980.0	980.2	980.3	980.8
155°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.6	1014.3	1014.1	1014.0	1013.8	1014.6
157.5°	1046.0	1045.6	1045.3	1044.9	1044.6	1044.4	1044.3	1044.3	1044.3	1044.2	1044.8
160°	1064.5	1064.3	1064.1	1063.9	1063.7	1063.5	1063.3	1063.1	1062.9	1062.7	1063.3
162.5°	1081.6	1081.1	1080.6	1080.0	1079.5	1079.1	1079.0	1078.8	1078.6	1078.3	1079.4
165°	1104.6	1103.9	1103.4	1102.8	1102.2	1101.7	1101.3	1100.9	1100.5	1100.1	1101.3
167.5°	1122.2	1121.3	1120.5	1119.7	1118.8	1118.5	1118.5	1118.6	1118.6	1118.7	1119.8
170°	1132.1	1131.1	1130.2	1129.2	1128.2	1127.7	1128.0	1128.2	1128.4	1128.5	1129.8
172.5°	1139.2	1138.4	1137.6	1136.8	1136.0	1135.5	1135.6	1135.6	1135.7	1135.7	1137.0
175°	1149.1	1148.1	1147.1	1146.1	1145.1	1144.5	1144.3	1144.1	1143.9	1143.7	1145.1
177.5°	1152.3	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.8
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8



TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0	1101.0
2.5°	1097.2	1098.7	1100.2	1100.8	1100.6	1100.4	1100.2	1100.0
5°	1094.2	1096.4	1098.7	1099.6	1099.3	1099.0	1098.8	1098.5
7.5°	1088.4	1090.8	1093.3	1094.4	1094.1	1093.9	1093.6	1093.3
10°	1082.4	1084.9	1087.4	1088.5	1088.2	1088.0	1087.7	1087.4
12.5°	1074.2	1076.4	1078.6	1079.8	1079.7	1079.6	1079.6	1079.5
15°	1059.1	1061.5	1064.0	1065.1	1064.8	1064.5	1064.3	1064.0
17.5°	1040.6	1043.2	1045.7	1046.9	1046.6	1046.4	1046.2	1046.0
20°	1026.3	1029.0	1031.8	1033.1	1033.1	1033.1	1033.1	1033.1
22.5°	1009.5	1012.3	1015.0	1016.6	1017.1	1017.4	1017.9	1018.3
25°	983.7	986.7	989.7	991.4	991.7	991.9	992.2	992.5
27.5°	954.7	957.4	960.3	961.8	962.2	962.5	962.8	963.1
30°	934.4	937.4	940.4	942.2	942.7	943.3	943.9	944.4
32.5°	913.6	917.0	920.5	922.5	923.0	923.5	924.1	924.7
35°	880.6	884.4	888.2	890.6	891.4	892.2	893.0	893.9
37.5°	846.1	850.1	853.9	856.3	857.2	858.1	858.9	859.8
40°	821.9	826.0	830.2	832.8	833.8	834.9	836.1	837.1
42.5°	798.2	802.7	807.3	809.9	810.8	811.7	812.6	813.4
45°	761.3	766.1	770.7	773.7	775.1	776.4	777.8	779.2
47.5°	722.5	727.3	732.2	735.4	737.0	738.7	740.3	742.0
50°	695.2	700.7	706.1	709.7	711.4	713.0	714.6	716.3
52.5°	667.6	673.1	678.6	682.1	683.8	685.4	687.1	688.7
55°	626.2	631.7	637.1	640.7	642.3	644.0	645.6	647.3
57.5°	582.6	589.2	595.7	599.7	601.2	602.8	604.3	605.8
60°	552.6	558.9	565.2	569.4	571.7	573.8	576.0	578.2
62.5°	523.0	529.3	535.7	539.8	542.1	544.2	546.4	548.7
65°	477.2	484.1	491.0	495.5	497.7	499.9	502.0	504.3
67.5°	432.4	439.3	446.3	450.8	453.0	455.1	457.3	459.4
70°	400.6	408.0	415.4	420.2	422.0	424.0	425.9	427.8
72.5°	370.7	377.8	385.0	389.7	391.8	394.0	396.1	398.2
75°	324.8	332.4	340.1	345.2	347.7	350.2	352.6	355.1
77.5°	282.1	289.9	297.7	302.9	305.5	308.2	310.8	313.4
80°	254.4	262.6	270.8	276.0	278.2	280.4	282.6	284.8
82.5°	227.2	235.7	244.1	249.5	251.9	254.3	256.7	259.1
85°	189.0	197.2	205.5	211.0	213.7	216.4	219.2	221.9
87.5°	161.0	169.2	177.5	182.8	185.3	187.8	190.3	192.7
90°	159.9	169.1	178.2	184.0	186.6	189.2	191.8	194.4
92.5°	168.3	176.7	185.1	190.6	193.0	195.5	197.9	200.3
95°	190.9	198.9	206.9	212.1	214.5	217.0	219.5	221.9
97.5°	222.4	230.2	238.2	243.3	245.7	248.0	250.4	252.7
100°	245.5	253.2	261.0	265.9	267.8	269.7	271.6	273.6
102.5°	270.3	278.0	285.8	290.8	293.1	295.4	297.7	300.0
105°	308.1	315.5	323.0	328.1	330.9	333.7	336.4	339.2
107.5°	350.3	357.6	364.9	369.5	371.4	373.4	375.3	377.2
110°	378.4	384.4	390.3	394.7	397.4	400.2	403.0	405.7





TEST NUMBER: P332656-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-D1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.6	414.6	420.6	424.8	427.1	429.4	431.7	434.0
115°	455.8	461.7	467.5	471.4	473.1	474.7	476.4	478.2
117.5°	500.4	505.5	510.5	513.9	515.8	517.5	519.3	521.1
120°	530.7	535.3	539.8	543.3	545.9	548.5	551.1	553.7
122.5°	562.0	566.9	571.7	574.7	576.0	577.2	578.5	579.8
125°	608.4	613.2	618.0	621.1	622.3	623.6	624.8	626.1
127.5°	651.2	655.8	660.3	663.3	664.9	666.5	668.0	669.5
130°	681.9	686.4	691.0	693.7	694.5	695.4	696.2	697.1
132.5°	711.0	715.3	719.6	722.5	723.7	725.1	726.4	727.7
135°	753.4	757.3	761.3	763.8	764.9	766.0	767.0	768.0
137.5°	795.5	799.0	802.5	804.9	806.4	807.9	809.4	810.8
140°	823.6	827.0	830.3	832.6	833.7	834.9	836.1	837.3
142.5°	851.0	854.1	857.1	859.3	860.3	861.5	862.6	863.7
145°	893.0	894.4	895.8	896.8	897.3	897.8	898.3	898.8
147.5°	931.3	931.4	931.4	931.7	932.5	933.2	933.8	934.5
150°	956.8	956.8	956.8	956.7	956.5	956.3	956.1	955.9
152.5°	981.2	981.7	982.2	982.2	981.7	981.1	980.6	980.1
155°	1015.4	1016.1	1016.9	1016.9	1016.1	1015.4	1014.6	1013.8
157.5°	1045.4	1046.0	1046.6	1046.5	1045.9	1045.2	1044.6	1043.8
160°	1063.9	1064.5	1065.1	1064.9	1063.9	1062.9	1061.9	1061.0
162.5°	1080.5	1081.6	1082.6	1082.7	1081.7	1080.8	1079.8	1078.7
165°	1102.5	1103.7	1104.8	1105.0	1104.3	1103.5	1102.7	1101.9
167.5°	1121.0	1122.2	1123.4	1123.4	1122.1	1120.9	1119.6	1118.5
170°	1131.0	1132.1	1133.4	1133.2	1131.8	1130.4	1129.1	1127.7
172.5°	1138.4	1139.7	1141.1	1141.0	1139.7	1138.3	1136.9	1135.5
175°	1146.5	1147.9	1149.2	1149.2	1147.9	1146.5	1145.1	1143.7
177.5°	1150.9	1152.0	1153.2	1153.1	1151.8	1150.5	1149.2	1148.0
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8

(END OF REPORT)