

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332615-930

Luminaire Tested: **SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332615-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5792.6 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332615-930
CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8737	8737	8737
5°	8763	8658	8721
10°	8708	8588	8630
15°	8603	8466	8487
20°	8463	8314	8322
25°	8304	8141	8118
30°	8108	7938	7866
35°	7906	7727	7624
40°	7695	7484	7347
45°	7476	7247	7108
50°	7232	7036	6818
55°	6970	6763	6542
60°	6707	6455	6260
65°	6411	6162	5914
70°	6080	5773	5549
75°	5571	5303	5168
80°	4956	4756	4635
85°	4335	4177	4094



TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	1.8
10°-20°	287.2	5.0
20°-30°	422.7	7.3
30°-40°	491.4	8.5
40°-50°	491.4	8.5
50°-60°	429.8	7.4
60°-70°	319.2	5.5
70°-80°	181.4	3.1
80°-90°	54.6	0.9
90°-100°	299.2	5.2
100°-110°	622.8	10.8
110°-120°	557.8	9.6
120°-130°	469.2	8.1
130°-140°	391.2	6.8
140°-150°	298.9	5.2
150°-160°	210.1	3.6
160°-170°	123.6	2.1
170°-180°	40.2	0.7
0°-30°	811.8	14.0
0°-40°	1303.1	22.5
0°-60°	2224.4	38.4
0°-90°	2779.6	48.0
90°-120°	1479.8	25.5
90°-150°	2639.2	45.6
90°-180°	3013.0	52.0
0°-180°	5792.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1081	1078	1068	1077	1076	103
15°	1029	1025	1013	1018	1016	290
25°	932	926	914	915	911	429
35°	802	796	784	778	774	501
45°	655	648	635	626	623	505
55°	495	492	480	470	465	443
65°	336	331	323	314	310	332
75°	179	174	170	167	166	190
85°	47	47	45	45	44	52
90°	1	6	15	16	17	4
95°	27	85	663	328	199	30
105°	95	138	534	1150	1145	102
115°	168	210	476	915	1100	166
125°	234	278	474	778	877	208
135°	278	330	470	691	785	214
145°	320	366	467	583	641	201
155°	364	393	454	514	536	168
165°	396	409	436	461	468	112
175°	413	414	418	423	422	39
180°	414	414	414	414	414	



TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1085.1	1084.6	1084.1	1083.7	1083.2	1082.1	1080.4	1078.7	1077.0	1075.4	1076.8
5°	1081.4	1080.7	1079.9	1079.1	1078.3	1076.8	1074.7	1072.6	1070.5	1068.4	1070.5
7.5°	1071.4	1070.6	1069.8	1069.0	1068.3	1066.7	1064.4	1062.0	1059.6	1057.3	1059.0
10°	1062.3	1061.6	1060.8	1060.1	1059.2	1057.6	1055.1	1052.6	1050.1	1047.6	1049.1
12.5°	1050.5	1049.8	1049.0	1048.2	1047.5	1045.7	1043.1	1040.4	1037.8	1035.1	1036.8
15°	1029.4	1028.6	1027.8	1027.0	1026.3	1024.5	1021.6	1018.7	1015.8	1012.9	1014.1
17.5°	1003.9	1002.9	1001.9	1001.0	1000.0	998.2	995.5	992.7	989.9	987.2	988.0
20°	985.1	984.1	983.3	982.3	981.3	979.3	976.5	973.5	970.7	967.8	968.4
22.5°	965.1	963.8	962.5	961.2	959.9	957.9	955.0	952.1	949.2	946.3	947.4
25°	932.2	930.9	929.5	928.2	926.8	924.8	922.1	919.4	916.7	914.0	914.2
27.5°	894.8	893.4	892.0	890.6	889.2	887.3	884.8	882.3	879.8	877.3	876.8
30°	869.8	868.3	866.7	865.2	863.6	861.6	859.1	856.6	854.1	851.6	850.8
32.5°	843.4	842.0	840.7	839.3	837.9	835.8	833.2	830.5	827.9	825.2	824.3
35°	802.2	800.8	799.5	798.1	796.8	794.8	792.1	789.4	786.7	784.0	782.6
37.5°	758.6	757.4	756.2	755.0	753.7	751.6	748.8	745.8	743.0	740.0	738.6
40°	730.2	728.6	727.1	725.5	724.0	721.8	718.9	716.0	713.1	710.2	708.3
42.5°	699.7	698.7	697.8	696.9	695.9	693.9	690.7	687.5	684.3	681.1	678.9
45°	654.8	653.4	652.1	650.7	649.4	647.1	644.1	641.0	637.9	634.8	632.7
47.5°	607.7	606.8	605.9	605.0	604.1	602.2	599.3	596.5	593.6	590.8	588.3
50°	575.8	575.0	574.3	573.5	572.7	571.0	568.3	565.7	562.9	560.2	557.5
52.5°	544.6	543.7	542.7	541.8	540.9	539.0	536.1	533.3	530.4	527.6	525.2
55°	495.2	494.6	494.0	493.4	492.8	491.2	488.5	485.8	483.1	480.5	478.1
57.5°	448.0	447.4	446.7	446.1	445.4	443.7	441.1	438.4	435.8	433.1	430.9
60°	415.4	414.4	413.4	412.5	411.6	409.8	407.3	404.8	402.3	399.8	398.0
62.5°	383.5	382.7	381.9	381.1	380.3	378.5	375.9	373.2	370.6	367.9	366.3
65°	335.6	334.7	333.7	332.7	331.7	330.3	328.4	326.4	324.5	322.6	320.7
67.5°	287.4	286.5	285.6	284.7	283.9	282.5	280.6	278.8	277.0	275.1	273.2
70°	257.6	256.2	254.9	253.5	252.2	250.7	249.2	247.6	246.1	244.6	243.0
72.5°	225.7	224.3	223.0	221.6	220.2	219.0	217.8	216.5	215.2	214.0	212.8
75°	178.6	177.7	176.8	175.8	174.8	173.8	172.8	171.9	171.0	170.0	169.2
77.5°	133.7	133.3	132.9	132.5	132.0	131.4	130.5	129.7	128.8	128.0	127.8
80°	106.6	106.1	105.5	104.9	104.4	103.9	103.5	103.1	102.7	102.3	101.9
82.5°	80.3	80.1	79.7	79.5	79.2	79.1	79.0	78.9	78.8	78.8	78.5
85°	46.8	46.8	46.8	46.8	46.8	46.6	46.2	45.9	45.5	45.1	45.1
87.5°	18.2	18.3	18.7	18.8	18.8	18.6	19.4	19.2	19.4	19.6	19.4
90°	0.8	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9
92.5°	9.3	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1
95°	26.8	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1
97.5°	48.2	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9
100°	61.9	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7
102.5°	74.8	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9
105°	95.2	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2
107.5°	117.7	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5
110°	132.6	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8



TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6
115°	167.7	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7
117.5°	189.1	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2
120°	203.5	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7
122.5°	216.5	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4
125°	233.6	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9
127.5°	248.7	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3
130°	257.2	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1
132.5°	265.6	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6
135°	277.5	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8
137.5°	289.4	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3
140°	297.9	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9
142.5°	307.0	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9
145°	319.8	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3
147.5°	334.4	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2
150°	343.5	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7
152.5°	352.0	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4
155°	363.8	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6
157.5°	375.4	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6
160°	382.5	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8
162.5°	389.1	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6
165°	396.4	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0
167.5°	403.7	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1
170°	407.0	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9
172.5°	410.2	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4
175°	413.4	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1
177.5°	414.9	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1078.4	1079.9	1081.5	1082.2	1082.1	1081.9	1081.7	1081.6
5°	1072.6	1074.7	1076.8	1077.7	1077.3	1077.0	1076.6	1076.2
7.5°	1060.7	1062.4	1064.0	1064.8	1064.6	1064.4	1064.1	1063.9
10°	1050.7	1052.2	1053.8	1054.3	1053.9	1053.5	1053.2	1052.8
12.5°	1038.5	1040.2	1041.9	1042.4	1042.0	1041.4	1040.8	1040.3
15°	1015.2	1016.4	1017.5	1017.8	1017.2	1016.7	1016.1	1015.5
17.5°	988.7	989.4	990.2	990.3	989.9	989.5	989.2	988.8
20°	969.0	969.6	970.1	970.2	969.8	969.5	969.1	968.7
22.5°	948.4	949.4	950.5	950.6	949.9	949.3	948.5	947.9
25°	914.4	914.6	914.8	914.5	913.8	913.0	912.2	911.4
27.5°	876.4	875.9	875.4	874.7	873.8	872.8	871.8	870.8
30°	850.0	849.3	848.5	847.7	846.7	845.7	844.7	843.8
32.5°	823.4	822.5	821.6	820.6	819.6	818.6	817.7	816.8
35°	781.3	779.9	778.5	777.4	776.4	775.5	774.5	773.6
37.5°	737.1	735.6	734.3	732.9	731.6	730.3	729.0	727.7
40°	706.4	704.5	702.5	701.1	700.1	699.2	698.2	697.2
42.5°	676.6	674.4	672.1	670.7	670.1	669.4	668.8	668.1
45°	630.6	628.4	626.3	625.0	624.4	623.8	623.2	622.6
47.5°	586.0	583.6	581.1	579.3	577.8	576.3	574.9	573.4
50°	554.8	552.1	549.4	547.5	546.3	545.2	544.0	542.9
52.5°	522.9	520.4	518.0	516.2	514.7	513.2	511.8	510.3
55°	475.8	473.5	471.2	469.4	468.3	467.2	465.9	464.8
57.5°	428.7	426.5	424.3	422.7	421.5	420.4	419.3	418.2
60°	396.3	394.6	392.8	391.5	390.5	389.6	388.6	387.7
62.5°	364.7	363.1	361.6	360.3	359.3	358.3	357.4	356.4
65°	318.8	316.8	314.9	313.5	312.5	311.5	310.5	309.6
67.5°	271.4	269.5	267.7	266.6	266.4	266.1	265.8	265.5
70°	241.5	239.9	238.4	237.3	236.8	236.2	235.6	235.1
72.5°	211.6	210.3	209.1	208.2	207.6	207.0	206.4	205.9
75°	168.4	167.6	166.9	166.4	166.2	166.0	165.8	165.7
77.5°	127.5	127.3	127.1	126.7	126.2	125.7	125.2	124.7
80°	101.6	101.2	100.8	100.5	100.3	100.1	100.0	99.7
82.5°	78.3	78.0	77.8	77.6	77.5	77.2	77.0	76.8
85°	45.1	45.1	45.1	45.0	44.8	44.6	44.4	44.2
87.5°	19.6	19.7	19.9	19.9	20.1	20.2	20.1	20.1
90°	14.7	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	159.9	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	603.1	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	891.1	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	981.6	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	977.1	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	911.6	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	818.6	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	762.6	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0



TEST NUMBER: P332615-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.6	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	680.4	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	660.2	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	651.1	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	643.4	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	630.0	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	613.7	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	600.7	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	587.0	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	568.1	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	551.1	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	541.3	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	532.1	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	519.3	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	508.7	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	502.2	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	495.0	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	484.3	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	472.7	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	465.5	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	458.4	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	448.5	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	438.9	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	433.0	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	427.8	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	420.8	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.2	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)