

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332658-940

Luminaire Tested: **SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332658-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7633.3 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332658-940
CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	44
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41	36
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	1.9
10°-20°	408.3	5.3
20°-30°	600.9	7.9
30°-40°	698.6	9.2
40°-50°	698.6	9.2
50°-60°	611.1	8.0
60°-70°	453.8	5.9
70°-80°	257.8	3.4
80°-90°	77.8	1.0
90°-100°	40.7	0.5
100°-110°	259.5	3.4
110°-120°	496.5	6.5
120°-130°	630.3	8.3
130°-140°	674.3	8.8
140°-150°	630.6	8.3
150°-160°	508.5	6.7
160°-170°	328.0	4.3
170°-180°	113.0	1.5
0°-30°	1154.1	15.1
0°-40°	1852.6	24.3
0°-60°	3162.3	41.4
0°-90°	3951.8	51.8
90°-120°	796.7	10.4
90°-150°	2731.9	35.8
90°-180°	3681.0	48.2
0°-180°	7633.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	3	12	20	25	27	6
95°	49	20	20	25	26	63
105°	268	273	278	284	254	280
115°	500	503	502	504	504	492
125°	703	706	705	708	709	628
135°	872	872	875	877	879	672
145°	1006	1008	1008	1010	1011	628
155°	1103	1104	1101	1104	1102	508
165°	1163	1159	1159	1165	1158	329
175°	1190	1185	1186	1193	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	26.2	26.4	26.6	26.8	27.0	27.2	27.3	27.4	27.5	27.6	27.8
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	11.2	11.3	11.4	11.6	11.7	12.6	14.1	15.7	17.3	18.9	20.1
95°	49.0	42.3	35.5	28.8	22.0	18.8	19.0	19.2	19.4	19.6	20.8
97.5°	104.0	108.2	112.4	116.5	120.7	111.8	89.7	67.7	45.6	23.5	23.6
100°	146.0	149.5	153.1	156.7	160.2	148.4	121.1	93.8	66.4	39.1	35.8
102.5°	193.0	195.6	198.2	200.8	203.4	203.0	199.4	195.8	192.3	188.7	152.4
105°	268.0	269.1	270.3	271.5	272.7	273.8	274.7	275.7	276.8	277.8	279.6
107.5°	337.5	338.1	338.8	339.3	339.9	340.9	342.2	343.6	344.9	346.3	347.1
110°	384.6	385.1	385.8	386.3	386.9	387.8	389.0	390.2	391.4	392.5	393.0



TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.2	431.2	432.3	433.4	434.4	435.2	435.8	436.3	436.8	437.4	437.4
115°	500.2	500.9	501.5	502.0	502.7	502.8	502.7	502.5	502.2	502.0	502.5
117.5°	563.5	564.3	565.1	565.9	566.7	567.2	567.7	568.1	568.6	569.0	568.9
120°	606.2	607.0	607.8	608.6	609.4	609.7	609.5	609.3	609.0	608.9	609.3
122.5°	646.0	646.6	647.0	647.5	648.0	648.4	648.6	648.9	649.2	649.4	649.7
125°	703.2	704.0	704.8	705.6	706.4	706.6	706.2	705.8	705.4	705.0	705.6
127.5°	757.3	757.5	757.8	758.0	758.1	758.7	759.6	760.5	761.4	762.3	762.2
130°	792.3	792.5	792.6	792.8	793.0	793.4	794.1	794.6	795.2	795.9	796.0
132.5°	824.3	824.7	825.0	825.4	825.7	826.3	827.1	827.8	828.5	829.3	829.5
135°	872.4	872.2	872.0	871.7	871.6	871.8	872.6	873.4	874.2	875.0	875.4
137.5°	914.9	915.0	915.1	915.2	915.3	915.7	916.6	917.5	918.3	919.2	919.6
140°	942.7	943.1	943.5	943.9	944.2	944.7	945.0	945.5	945.8	946.3	946.8
142.5°	967.6	968.3	969.0	969.7	970.4	970.9	971.2	971.4	971.6	971.9	972.3
145°	1005.8	1006.5	1007.1	1007.6	1008.3	1008.5	1008.5	1008.5	1008.5	1008.5	1008.8
147.5°	1036.3	1037.4	1038.6	1039.6	1040.8	1041.3	1041.0	1040.8	1040.6	1040.4	1040.6
150°	1058.4	1059.2	1060.0	1060.8	1061.6	1061.8	1061.7	1061.5	1061.3	1061.0	1061.0
152.5°	1076.9	1077.5	1078.2	1078.8	1079.4	1079.6	1079.2	1078.9	1078.5	1078.2	1078.5
155°	1103.0	1103.1	1103.3	1103.5	1103.7	1103.5	1103.0	1102.3	1101.7	1101.2	1101.9
157.5°	1124.8	1124.7	1124.5	1124.4	1124.4	1123.9	1123.3	1122.6	1122.0	1121.2	1122.3
160°	1137.6	1137.0	1136.5	1135.9	1135.2	1134.9	1134.7	1134.4	1134.3	1134.1	1135.2
162.5°	1149.1	1148.3	1147.5	1146.7	1146.0	1145.6	1145.3	1145.1	1145.0	1144.8	1145.9
165°	1163.4	1162.4	1161.5	1160.5	1159.5	1159.0	1159.0	1159.0	1159.0	1159.0	1160.6
167.5°	1174.8	1173.8	1172.8	1171.8	1170.7	1170.2	1170.0	1169.9	1169.8	1169.7	1171.4
170°	1181.2	1180.1	1178.8	1177.7	1176.5	1176.0	1176.2	1176.4	1176.6	1176.8	1178.4
172.5°	1185.5	1184.4	1183.1	1182.0	1180.8	1180.3	1180.4	1180.7	1180.9	1181.1	1182.7
175°	1190.2	1189.0	1187.8	1186.6	1185.4	1184.9	1185.1	1185.4	1185.5	1185.7	1187.5
177.5°	1192.3	1191.1	1190.1	1189.0	1187.8	1187.5	1187.8	1188.1	1188.4	1188.7	1190.0
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2



TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	28.1	28.3	28.5	28.7	28.8	28.9	28.9	29.0
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	21.2	22.5	23.6	24.3	24.3	24.4	24.5	24.6
95°	21.9	23.2	24.3	25.1	25.2	25.4	25.6	25.8
97.5°	23.7	23.9	24.0	24.2	24.3	24.5	24.7	25.0
100°	32.5	29.1	25.7	24.2	24.3	24.5	24.7	25.0
102.5°	116.2	79.9	43.6	25.5	25.5	25.6	25.6	25.7
105°	281.3	283.0	284.8	282.2	275.1	268.0	260.8	253.7
107.5°	348.0	348.9	349.7	350.5	351.3	352.0	352.8	353.6
110°	393.3	393.8	394.1	394.7	395.2	395.8	396.5	397.0



TEST NUMBER: P332658-940

CATALOG NUMBER: SA4XXDIP-C1020D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	437.3	437.2	437.1	437.5	438.2	439.0	439.7	440.4
115°	502.8	503.3	503.6	503.8	503.8	503.8	503.8	503.8
117.5°	568.8	568.7	568.6	568.6	568.6	568.5	568.4	568.3
120°	609.7	610.0	610.5	610.5	610.0	609.7	609.3	608.9
122.5°	650.0	650.1	650.4	650.3	650.0	649.5	649.2	648.7
125°	706.2	706.8	707.4	707.8	708.0	708.2	708.4	708.6
127.5°	762.1	762.0	761.9	761.7	761.6	761.4	761.3	761.1
130°	796.2	796.4	796.6	796.7	796.7	796.7	796.7	796.7
132.5°	829.6	829.9	830.1	830.1	829.9	829.7	829.6	829.5
135°	875.8	876.2	876.6	877.0	877.4	877.8	878.2	878.6
137.5°	920.1	920.5	921.0	921.0	921.0	920.9	920.7	920.6
140°	947.4	948.1	948.6	949.0	949.2	949.4	949.6	949.9
142.5°	972.8	973.2	973.7	973.8	973.9	973.9	974.0	974.0
145°	1009.0	1009.1	1009.3	1009.7	1010.0	1010.4	1010.8	1011.2
147.5°	1040.7	1040.9	1041.1	1041.3	1041.4	1041.6	1041.9	1042.1
150°	1061.0	1061.0	1061.0	1061.1	1061.4	1061.6	1061.8	1061.9
152.5°	1078.8	1079.1	1079.4	1079.5	1079.4	1079.3	1079.1	1079.1
155°	1102.7	1103.5	1104.3	1104.4	1103.8	1103.2	1102.6	1102.1
157.5°	1123.3	1124.4	1125.3	1125.3	1124.4	1123.3	1122.3	1121.2
160°	1136.5	1137.6	1138.8	1138.8	1137.6	1136.5	1135.2	1134.1
162.5°	1147.1	1148.3	1149.5	1149.4	1148.1	1146.7	1145.4	1144.1
165°	1162.2	1163.8	1165.3	1165.2	1163.4	1161.6	1159.8	1158.1
167.5°	1173.1	1174.9	1176.6	1176.5	1174.6	1172.6	1170.5	1168.6
170°	1180.0	1181.5	1183.1	1182.9	1181.0	1179.0	1177.0	1175.0
172.5°	1184.3	1185.8	1187.4	1187.1	1185.0	1182.9	1180.7	1178.6
175°	1189.3	1191.1	1192.8	1192.5	1190.2	1187.8	1185.4	1183.0
177.5°	1191.2	1192.5	1193.8	1193.5	1191.6	1189.7	1187.8	1185.9
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2

(END OF REPORT)