

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332668-940

Luminaire Tested: **SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332668-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7668.8 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332668-940
CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	1.9
10°-20°	408.3	5.3
20°-30°	600.9	7.8
30°-40°	698.6	9.1
40°-50°	698.6	9.1
50°-60°	611.1	8.0
60°-70°	453.8	5.9
70°-80°	257.8	3.4
80°-90°	78.4	1.0
90°-100°	88.4	1.2
100°-110°	261.7	3.4
110°-120°	444.2	5.8
120°-130°	585.7	7.6
130°-140°	657.8	8.6
140°-150°	646.4	8.4
150°-160°	543.7	7.1
160°-170°	361.7	4.7
170°-180°	126.7	1.7
0°-30°	1154.1	15.0
0°-40°	1852.6	24.2
0°-60°	3162.3	41.2
0°-90°	3952.4	51.5
90°-120°	794.3	10.4
90°-150°	2684.3	35.0
90°-180°	3716.0	48.5
0°-180°	7668.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	3	14	23	29	31	7
95°	62	71	79	82	82	69
105°	241	243	247	250	253	256
115°	452	452	450	449	448	445
125°	658	658	657	655	653	586
135°	848	854	855	853	850	656
145°	1031	1035	1036	1035	1032	645
155°	1181	1181	1180	1184	1180	543
165°	1286	1283	1280	1286	1282	362
175°	1338	1332	1331	1338	1331	127
180°	1340	1340	1340	1340	1340	



TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	26.3	26.6	26.8	27.1	27.4	27.6	27.8	27.9	28.1	28.3	28.5
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	22.2	25.1	28.0	30.9	33.8	35.8	37.2	38.4	39.8	41.0	41.8
95°	62.2	64.2	66.3	68.4	70.4	72.3	73.9	75.5	77.1	78.7	79.5
97.5°	108.6	110.2	111.9	113.5	115.2	117.0	118.9	120.7	122.6	124.5	125.4
100°	145.1	146.0	146.9	147.8	148.7	150.3	152.3	154.4	156.4	158.5	159.0
102.5°	183.2	183.5	183.9	184.2	184.7	185.7	187.6	189.6	191.5	193.3	193.9
105°	241.4	241.7	241.8	242.1	242.3	242.9	243.8	244.7	245.7	246.6	247.3
107.5°	302.5	302.8	303.1	303.4	303.6	303.8	304.0	304.1	304.3	304.3	305.1
110°	343.9	344.4	344.8	345.4	345.8	345.9	345.7	345.4	345.2	345.0	344.6



TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.0	387.2	387.3	387.4	387.4	387.3	386.8	386.5	386.0	385.6	385.5
115°	451.7	451.7	451.7	451.7	451.7	451.5	451.0	450.6	450.0	449.6	449.4
117.5°	512.6	512.8	513.0	513.2	513.4	513.3	512.9	512.6	512.3	512.0	511.2
120°	553.2	554.1	555.1	556.0	556.9	557.1	556.3	555.6	554.9	554.3	553.1
122.5°	595.5	595.8	596.2	596.6	597.0	597.0	596.6	596.4	596.0	595.7	594.9
125°	657.8	657.8	657.8	657.8	657.8	657.7	657.5	657.3	657.0	656.8	656.4
127.5°	714.4	715.2	715.8	716.5	717.2	717.4	716.9	716.6	716.2	715.9	715.4
130°	754.2	754.9	755.5	756.3	757.0	757.3	757.3	757.3	757.3	757.3	756.9
132.5°	794.8	795.3	795.9	796.3	796.8	797.0	796.8	796.7	796.5	796.3	795.8
135°	848.5	849.9	851.2	852.7	854.0	854.7	854.7	854.7	854.7	854.7	854.3
137.5°	906.9	907.6	908.2	908.8	909.5	910.0	910.3	910.7	911.1	911.4	910.9
140°	945.8	946.3	946.8	947.3	947.7	947.9	947.9	947.9	947.9	947.9	947.7
142.5°	981.5	982.0	982.4	982.8	983.4	983.5	983.3	983.1	982.9	982.8	982.7
145°	1030.8	1031.7	1032.7	1033.6	1034.5	1035.1	1035.3	1035.5	1035.7	1036.0	1035.7
147.5°	1079.7	1080.8	1081.9	1083.0	1084.1	1084.6	1084.4	1084.2	1084.1	1083.9	1083.7
150°	1109.6	1110.4	1111.4	1112.3	1113.2	1113.7	1113.7	1113.7	1113.7	1113.7	1113.7
152.5°	1137.7	1138.3	1138.8	1139.3	1140.0	1140.3	1140.5	1140.7	1140.9	1141.0	1141.6
155°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.9	1180.7	1180.4	1180.2	1180.0	1180.9
157.5°	1217.5	1217.1	1216.7	1216.3	1215.8	1215.6	1215.6	1215.5	1215.5	1215.4	1216.1
160°	1239.0	1238.9	1238.6	1238.3	1238.1	1237.9	1237.7	1237.4	1237.2	1237.0	1237.7
162.5°	1258.9	1258.3	1257.8	1257.1	1256.5	1256.2	1255.9	1255.7	1255.4	1255.2	1256.4
165°	1285.7	1285.0	1284.2	1283.6	1282.9	1282.3	1281.8	1281.4	1280.9	1280.5	1281.8
167.5°	1306.2	1305.2	1304.2	1303.2	1302.3	1301.8	1301.9	1301.9	1302.0	1302.0	1303.4
170°	1317.8	1316.6	1315.5	1314.3	1313.1	1312.7	1313.0	1313.1	1313.4	1313.7	1315.0
172.5°	1326.1	1325.1	1324.1	1323.1	1322.2	1321.7	1321.8	1321.9	1321.9	1322.0	1323.5
175°	1337.5	1336.3	1335.2	1334.0	1332.8	1332.1	1331.9	1331.7	1331.5	1331.2	1332.8
177.5°	1341.2	1340.2	1339.3	1338.5	1337.5	1337.0	1337.0	1337.0	1337.0	1337.0	1338.4
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5



TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	28.8	29.1	29.3	29.5	29.6	29.7	29.8	29.9
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	42.7	43.5	44.3	44.9	45.2	45.5	45.7	46.0
95°	80.1	80.8	81.5	81.9	81.9	81.9	81.9	81.9
97.5°	126.2	127.0	127.9	128.2	128.2	128.2	128.2	128.2
100°	159.4	159.9	160.3	160.6	160.6	160.6	160.6	160.6
102.5°	194.6	195.3	195.9	196.3	196.5	196.7	196.9	197.1
105°	248.0	248.6	249.3	250.0	250.7	251.4	252.1	252.8
107.5°	305.7	306.3	306.9	307.3	307.2	307.2	307.1	307.1
110°	344.0	343.6	343.1	343.2	343.9	344.6	345.4	346.0



TEST NUMBER: P332668-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.3	385.2	385.2	385.4	385.5	385.7	385.8
115°	449.2	448.9	448.7	448.4	448.3	448.0	447.8	447.5
117.5°	510.4	509.6	508.8	508.3	507.7	507.3	506.8	506.4
120°	552.0	550.8	549.7	549.3	549.7	550.2	550.7	551.2
122.5°	594.1	593.3	592.5	591.7	590.9	590.1	589.2	588.4
125°	655.9	655.4	655.0	654.5	654.1	653.6	653.1	652.6
127.5°	715.0	714.5	714.0	713.6	713.3	712.8	712.5	712.1
130°	756.3	755.9	755.5	754.7	753.9	753.0	752.0	751.1
132.5°	795.3	794.9	794.4	794.0	793.6	793.3	792.9	792.6
135°	853.8	853.3	852.8	852.3	851.6	850.9	850.2	849.5
137.5°	910.3	909.6	909.1	908.8	909.0	909.1	909.3	909.4
140°	947.4	947.3	947.0	946.8	946.6	946.3	946.1	945.8
142.5°	982.7	982.6	982.6	982.5	982.5	982.4	982.4	982.3
145°	1035.5	1035.3	1035.1	1034.6	1033.9	1033.2	1032.5	1031.9
147.5°	1083.5	1083.3	1083.1	1082.9	1082.7	1082.4	1082.2	1082.0
150°	1113.7	1113.7	1113.7	1113.6	1113.3	1113.1	1112.9	1112.7
152.5°	1142.1	1142.7	1143.3	1143.3	1142.6	1142.0	1141.4	1140.9
155°	1181.9	1182.8	1183.7	1183.7	1182.8	1181.9	1180.9	1180.0
157.5°	1216.8	1217.5	1218.2	1218.2	1217.4	1216.6	1215.8	1215.0
160°	1238.3	1239.0	1239.7	1239.5	1238.3	1237.2	1236.1	1234.9
162.5°	1257.7	1258.9	1260.2	1260.3	1259.1	1257.9	1256.8	1255.6
165°	1283.3	1284.6	1286.0	1286.2	1285.3	1284.4	1283.4	1282.5
167.5°	1304.8	1306.2	1307.5	1307.5	1306.1	1304.7	1303.2	1301.8
170°	1316.4	1317.8	1319.2	1319.0	1317.4	1315.8	1314.2	1312.6
172.5°	1325.1	1326.6	1328.2	1328.2	1326.5	1324.9	1323.3	1321.7
175°	1334.4	1336.1	1337.7	1337.7	1336.1	1334.4	1332.8	1331.2
177.5°	1339.6	1341.0	1342.2	1342.1	1340.6	1339.2	1337.7	1336.2
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5

(END OF REPORT)