

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332633-940

Luminaire Tested: **SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332633-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5115.9 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332633-940  
CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	92	99	95	91	88	86	84	81	79	77	75	72	70	68	65
2	95	87	80	75	90	83	77	72	76	71	67	69	65	62	63	60	58	54
3	86	76	69	62	82	73	66	60	67	61	56	61	57	53	56	52	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	49	45	50	46	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34
6	67	54	46	40	64	52	44	39	48	42	37	44	39	35	41	36	33	30
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	37	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	34	30	26	24
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.9	2.8
10°-20°	408.3	8.0
20°-30°	600.9	11.7
30°-40°	698.6	13.7
40°-50°	698.6	13.7
50°-60°	611.1	11.9
60°-70°	453.8	8.9
70°-80°	257.8	5.0
80°-90°	75.3	1.5
90°-100°	115.9	2.3
100°-110°	241.1	4.7
110°-120°	216.0	4.2
120°-130°	181.7	3.6
130°-140°	151.5	3.0
140°-150°	115.7	2.3
150°-160°	81.3	1.6
160°-170°	47.8	0.9
170°-180°	15.6	0.3
0°-30°	1154.1	22.6
0°-40°	1852.6	36.2
0°-60°	3162.3	61.8
0°-90°	3949.3	77.2
90°-120°	573.0	11.2
90°-150°	1021.9	20.0
90°-180°	1167.0	22.8
0°-180°	5115.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	0	2	6	6	7	4
95°	10	33	257	127	77	12
105°	37	53	207	445	443	39
115°	65	81	184	354	426	64
125°	90	108	183	301	340	80
135°	108	128	182	268	304	83
145°	124	142	181	226	248	78
155°	141	152	176	199	208	65
165°	154	158	169	178	181	43
175°	160	160	162	164	163	15
180°	160	160	160	160	160	



TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	25.7	25.6	25.6	25.4	25.2	25.1	25.2	25.0	24.9	24.8	24.7
90°	0.4	1.0	1.9	2.2	2.5	2.5	4.4	4.4	5.1	5.7	5.4
92.5°	3.6	5.3	8.2	12.0	16.7	23.2	39.2	63.7	87.5	100.0	83.3
95°	10.4	11.3	14.5	18.6	26.1	39.4	66.8	118.5	193.9	256.8	264.1
97.5°	18.6	18.6	21.4	25.1	31.7	42.7	63.8	106.6	181.4	270.5	331.8
100°	24.0	24.0	26.1	30.0	35.9	46.0	64.6	100.2	164.5	253.4	334.0
102.5°	29.0	29.5	31.5	35.0	40.8	50.3	67.1	98.4	153.2	231.9	315.1
105°	36.9	37.8	39.4	43.2	48.9	58.0	73.1	99.2	143.4	206.7	280.8
107.5°	45.6	46.2	47.8	51.8	57.2	66.3	80.1	104.0	141.6	192.6	253.1
110°	51.4	52.0	53.6	57.3	63.0	71.5	85.4	107.5	142.1	187.8	239.2



TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.9	57.5	59.4	62.9	68.6	77.0	90.4	111.3	143.7	185.6	231.4
115°	64.9	65.9	68.0	71.2	77.2	85.7	98.4	117.3	146.5	184.4	224.1
117.5°	73.2	74.1	76.1	79.5	85.2	94.0	105.9	123.3	149.6	184.0	220.8
120°	78.8	79.5	81.6	85.1	90.4	99.2	111.3	127.6	151.9	184.0	219.0
122.5°	83.8	84.4	86.7	89.9	95.8	104.3	116.3	131.7	154.2	183.8	217.0
125°	90.4	91.7	93.6	97.1	103.1	111.9	123.2	137.7	157.6	183.4	213.7
127.5°	96.3	97.3	99.6	103.5	109.8	118.7	129.7	142.9	160.3	182.7	209.2
130°	99.6	100.9	103.3	108.1	114.0	123.2	133.9	146.2	162.3	182.4	206.4
132.5°	102.9	103.9	107.2	111.6	118.2	126.7	137.5	149.5	164.1	182.3	203.9
135°	107.5	108.7	111.9	117.3	123.9	132.1	142.4	153.8	166.7	181.8	200.1
137.5°	112.1	113.2	116.7	121.8	128.7	136.5	146.2	156.9	168.3	181.8	196.9
140°	115.4	116.3	119.8	125.1	131.7	139.3	148.7	158.8	169.5	181.6	195.1
142.5°	118.9	119.8	123.1	128.1	134.5	141.8	151.1	160.3	170.6	181.6	193.6
145°	123.9	124.8	128.0	132.3	138.4	145.3	153.5	162.0	171.1	180.9	191.0
147.5°	129.5	129.7	132.6	137.1	142.0	148.3	156.0	163.5	171.5	179.8	188.7
150°	133.0	133.3	135.8	139.6	144.4	150.3	157.3	164.2	171.5	179.0	186.9
152.5°	136.3	136.3	138.8	142.4	146.6	152.1	158.3	164.7	170.9	177.7	184.9
155°	140.9	141.2	143.1	146.2	149.7	154.4	159.8	165.1	170.2	175.8	181.8
157.5°	145.3	145.3	147.1	149.5	152.6	156.3	160.9	165.1	169.3	173.9	178.8
160°	148.1	148.1	149.4	151.6	154.1	157.6	161.4	165.1	168.6	172.4	176.5
162.5°	150.6	150.4	151.4	153.4	155.6	158.4	161.8	165.1	167.8	170.9	174.5
165°	153.5	153.5	154.1	155.7	157.3	159.2	162.0	164.5	166.4	168.6	171.1
167.5°	156.3	156.0	156.3	157.5	158.4	159.9	161.9	163.7	164.9	166.3	168.1
170°	157.6	157.3	157.6	158.5	159.2	160.1	161.7	163.3	163.9	164.8	166.1
172.5°	158.8	158.5	158.5	159.3	159.6	160.3	161.4	162.7	162.9	163.3	164.3
175°	160.1	159.8	159.8	160.1	160.4	160.4	161.0	162.0	161.7	161.7	162.3
177.5°	160.7	160.4	160.2	160.4	160.4	160.4	160.7	161.1	160.7	160.7	161.0
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	24.8	24.9	25.0	25.0	25.0	25.1	25.0	25.0
90°	5.7	6.0	6.3	6.3	6.6	7.0	6.6	6.6
92.5°	61.9	46.5	37.1	30.8	27.0	25.3	24.3	24.3
95°	233.5	184.7	142.4	111.9	96.4	86.7	81.0	76.9
97.5°	345.0	326.9	296.0	263.1	240.5	221.6	212.1	205.5
100°	380.0	386.4	371.0	347.6	320.2	301.0	291.5	289.0
102.5°	378.4	409.6	414.0	404.3	387.5	373.6	363.6	361.6
105°	352.9	407.5	438.7	451.7	452.3	449.7	445.3	443.4
107.5°	317.0	375.1	418.9	447.1	462.6	469.8	473.0	473.8
110°	295.3	349.8	395.6	430.2	452.5	465.8	471.4	474.3





TEST NUMBER: P332633-940

CATALOG NUMBER: SA4XXDIP-C1020D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.4	327.6	370.8	405.5	430.9	446.9	454.9	459.4
115°	263.5	302.2	339.1	369.3	394.2	413.1	423.3	425.8
117.5°	255.7	287.8	316.7	342.4	363.6	379.5	389.7	391.6
120°	252.1	281.4	306.7	329.0	347.0	360.9	369.1	372.6
122.5°	249.1	277.4	300.3	319.9	335.1	347.0	353.9	357.4
125°	244.0	271.0	292.7	310.1	322.7	331.9	337.9	339.7
127.5°	237.6	263.5	285.3	301.7	314.3	322.4	327.5	329.4
130°	232.6	257.5	278.9	295.6	308.5	316.4	321.5	323.3
132.5°	227.3	250.7	271.6	288.3	301.0	309.9	314.7	316.6
135°	220.0	240.5	259.7	275.4	288.0	296.9	301.9	303.8
137.5°	213.4	230.7	246.9	261.1	273.0	281.6	285.8	288.0
140°	209.6	224.4	238.5	251.8	262.9	269.7	274.2	276.7
142.5°	206.1	219.1	231.2	242.7	252.5	259.0	262.9	264.6
145°	201.1	211.8	221.2	230.1	237.9	243.3	246.5	248.0
147.5°	197.0	205.5	213.0	220.0	225.8	230.4	232.7	233.4
150°	194.5	201.7	208.0	213.7	218.7	222.8	224.7	225.0
152.5°	191.7	198.0	203.8	208.4	212.7	216.0	217.1	217.5
155°	187.5	192.5	197.2	201.1	204.2	206.7	207.7	207.7
157.5°	183.1	187.3	191.3	194.3	196.6	198.6	199.1	199.1
160°	180.3	183.7	187.2	189.8	191.6	193.5	193.9	193.9
162.5°	177.5	180.5	183.2	185.5	186.8	188.7	189.0	188.8
165°	173.6	175.6	177.7	179.3	180.6	181.8	181.6	181.2
167.5°	170.0	171.4	173.2	174.1	174.7	175.6	175.5	175.2
170°	167.6	168.6	169.9	170.9	171.5	171.7	171.5	171.5
172.5°	165.7	166.3	167.1	167.8	168.2	168.4	168.2	167.6
175°	162.9	163.3	163.9	163.9	163.9	164.5	163.9	163.3
177.5°	161.1	161.4	161.4	161.7	161.4	161.7	161.1	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4

(END OF REPORT)