

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332976-930

Luminaire Tested: **SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332976-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6770.5 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43				
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27				
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23				
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15				
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.0
10°-20°	385.6	5.7
20°-30°	556.9	8.2
30°-40°	631.2	9.3
40°-50°	609.5	9.0
50°-60°	506.9	7.5
60°-70°	350.0	5.2
70°-80°	177.4	2.6
80°-90°	48.7	0.7
90°-100°	37.2	0.5
100°-110°	237.3	3.5
110°-120°	453.9	6.7
120°-130°	576.3	8.5
130°-140°	616.6	9.1
140°-150°	576.6	8.5
150°-160°	464.9	6.9
160°-170°	299.9	4.4
170°-180°	103.4	1.5
0°-30°	1080.8	16.0
0°-40°	1712.0	25.3
0°-60°	2828.4	41.8
0°-90°	3404.5	50.3
90°-120°	728.5	10.8
90°-150°	2497.9	36.9
90°-180°	3366.0	49.7
0°-180°	6770.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	69
90°	2	11	18	23	24	5
95°	45	19	18	23	24	58
105°	245	250	254	259	232	256
115°	457	460	459	461	461	450
125°	643	646	645	647	648	574
135°	798	797	800	802	803	614
145°	920	922	922	923	924	574
155°	1008	1009	1007	1010	1008	465
165°	1064	1060	1060	1065	1059	300
175°	1088	1084	1084	1090	1082	104
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.2	20.1	18.8	17.6	16.4	15.8	16.0	16.1	16.1	16.2	16.2
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	10.3	10.4	10.4	10.6	10.7	11.5	12.9	14.3	15.8	17.3	18.3
95°	44.8	38.6	32.4	26.3	20.1	17.2	17.4	17.5	17.7	17.9	19.0
97.5°	95.1	98.9	102.7	106.6	110.4	102.2	82.0	61.9	41.7	21.5	21.6
100°	133.5	136.7	140.0	143.2	146.5	135.7	110.7	85.8	60.7	35.8	32.8
102.5°	176.4	178.9	181.2	183.6	186.0	185.6	182.3	179.0	175.8	172.5	139.3
105°	245.0	246.1	247.1	248.3	249.3	250.3	251.2	252.1	253.1	254.0	255.6
107.5°	308.6	309.2	309.7	310.2	310.8	311.7	312.9	314.1	315.4	316.6	317.4
110°	351.6	352.1	352.7	353.2	353.8	354.6	355.6	356.8	357.8	358.9	359.3



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.3	394.3	395.3	396.2	397.2	397.9	398.4	398.9	399.4	399.9	399.9
115°	457.4	458.0	458.5	459.0	459.6	459.7	459.6	459.4	459.2	459.0	459.4
117.5°	515.2	515.9	516.7	517.4	518.1	518.6	519.0	519.4	519.8	520.2	520.2
120°	554.2	555.0	555.7	556.4	557.2	557.4	557.3	557.1	556.8	556.7	557.1
122.5°	590.7	591.2	591.6	592.0	592.5	592.8	593.0	593.3	593.5	593.8	594.0
125°	642.9	643.7	644.4	645.1	645.9	646.0	645.7	645.3	645.0	644.6	645.1
127.5°	692.4	692.6	692.8	693.0	693.2	693.7	694.6	695.4	696.2	697.0	696.9
130°	724.4	724.6	724.7	724.9	725.0	725.5	726.0	726.5	727.1	727.7	727.8
132.5°	753.7	754.0	754.3	754.6	755.0	755.5	756.2	756.8	757.5	758.2	758.4
135°	797.6	797.4	797.3	797.0	796.9	797.1	797.9	798.6	799.3	800.1	800.4
137.5°	836.5	836.6	836.7	836.7	836.8	837.2	838.0	838.9	839.6	840.4	840.8
140°	861.9	862.3	862.7	863.0	863.3	863.7	864.1	864.5	864.8	865.2	865.7
142.5°	884.7	885.3	886.0	886.6	887.3	887.7	887.9	888.2	888.4	888.6	889.0
145°	919.7	920.2	920.8	921.3	921.9	922.1	922.1	922.1	922.1	922.1	922.3
147.5°	947.5	948.5	949.6	950.6	951.6	952.0	951.8	951.6	951.5	951.3	951.5
150°	967.7	968.4	969.1	969.9	970.6	970.9	970.7	970.5	970.4	970.1	970.1
152.5°	984.6	985.2	985.8	986.3	986.9	987.1	986.8	986.4	986.1	985.8	986.1
155°	1008.4	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5
157.5°	1028.4	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1
160°	1040.2	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0
162.5°	1050.6	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7
165°	1063.7	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1
167.5°	1074.2	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1
170°	1080.0	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4
172.5°	1083.9	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3
175°	1088.2	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7
177.5°	1090.1	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	16.2	16.2	16.3	16.4	16.7	17.0	17.2	17.5
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	19.4	20.5	21.6	22.2	22.3	22.3	22.4	22.5
95°	20.1	21.2	22.3	22.9	23.1	23.2	23.4	23.6
97.5°	21.7	21.9	21.9	22.1	22.3	22.4	22.6	22.8
100°	29.7	26.6	23.5	22.1	22.3	22.4	22.6	22.8
102.5°	106.2	73.1	39.9	23.3	23.3	23.4	23.4	23.5
105°	257.2	258.8	260.4	258.0	251.5	245.0	238.5	232.0
107.5°	318.2	319.0	319.8	320.5	321.2	321.9	322.6	323.3
110°	359.6	360.0	360.4	360.9	361.3	361.9	362.5	363.0



TEST NUMBER: P332976-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.8	399.7	399.7	400.0	400.6	401.4	402.0	402.7
115°	459.7	460.2	460.5	460.6	460.6	460.6	460.6	460.6
117.5°	520.1	520.0	519.9	519.9	519.8	519.8	519.7	519.6
120°	557.4	557.7	558.2	558.2	557.7	557.4	557.1	556.7
122.5°	594.3	594.4	594.7	594.6	594.3	593.9	593.5	593.1
125°	645.7	646.2	646.8	647.1	647.3	647.5	647.7	647.8
127.5°	696.8	696.7	696.6	696.4	696.3	696.2	696.0	695.9
130°	728.0	728.1	728.3	728.5	728.5	728.5	728.5	728.5
132.5°	758.6	758.8	759.0	759.0	758.8	758.6	758.6	758.4
135°	800.8	801.1	801.5	801.8	802.3	802.6	802.9	803.3
137.5°	841.2	841.6	842.0	842.1	842.0	842.0	841.8	841.7
140°	866.3	866.8	867.3	867.7	867.9	868.0	868.2	868.5
142.5°	889.4	889.8	890.2	890.4	890.5	890.5	890.6	890.6
145°	922.5	922.7	922.8	923.2	923.5	923.8	924.2	924.5
147.5°	951.5	951.7	951.9	952.0	952.2	952.4	952.6	952.8
150°	970.1	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.3	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.2	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1048.8	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1062.6	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1072.6	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1078.9	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1082.8	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1087.4	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1089.2	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)