

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332677-940

Luminaire Tested: **SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332677-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5691.7 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332677-940
CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71	67
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	60	56
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51	48
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44	41
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	47	42	38	36
6	68	55	46	40	64	53	45	39	49	42	37	46	40	35	42	37	34	31
7	63	50	41	35	60	48	40	35	45	38	33	42	36	31	39	34	30	28
8	58	45	37	32	56	44	36	31	41	34	30	38	32	28	36	31	27	25
9	54	42	34	28	52	40	33	28	38	31	27	35	30	25	33	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	33	27	23	31	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	2.9
10°-20°	471.5	8.3
20°-30°	694.0	12.2
30°-40°	806.8	14.2
40°-50°	806.8	14.2
50°-60°	705.8	12.4
60°-70°	524.1	9.2
70°-80°	297.8	5.2
80°-90°	87.2	1.5
90°-100°	26.9	0.5
100°-110°	79.6	1.4
110°-120°	135.1	2.4
120°-130°	178.2	3.1
130°-140°	200.1	3.5
140°-150°	196.6	3.5
150°-160°	165.4	2.9
160°-170°	110.0	1.9
170°-180°	38.5	0.7
0°-30°	1332.9	23.4
0°-40°	2139.7	37.6
0°-60°	3652.3	64.2
0°-90°	4561.3	80.1
90°-120°	241.6	4.2
90°-150°	816.5	14.3
90°-180°	1130.0	19.9
0°-180°	5691.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	1	4	7	9	10	5
95°	19	22	24	25	25	21
105°	73	74	75	76	77	78
115°	137	137	137	136	136	135
125°	200	200	200	199	198	178
135°	258	260	260	259	258	200
145°	314	315	315	315	314	196
155°	359	359	359	360	359	165
165°	391	390	390	391	390	110
175°	407	405	405	407	405	39
180°	407	407	407	407	407	



TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	29.8	29.7	29.6	29.5	29.4	29.2	29.2	29.0	28.9	28.7	28.8
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	6.8	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8
95°	18.9	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2
97.5°	33.0	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2
100°	44.1	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3
102.5°	55.7	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0
105°	73.4	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2
107.5°	92.0	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7
110°	104.6	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8



TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.7	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7
117.5°	155.9	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5
120°	168.3	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3
122.5°	181.1	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9
125°	200.1	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7
127.5°	217.3	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6
130°	229.4	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2
132.5°	241.7	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0
135°	258.1	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8
137.5°	275.8	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1
140°	287.7	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3
142.5°	298.5	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9
145°	313.5	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	328.4	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6
150°	337.5	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.1	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2
155°	359.2	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2
157.5°	370.3	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9
160°	376.8	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5
162.5°	382.9	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2
165°	391.0	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9
167.5°	397.3	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5
170°	400.8	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9
172.5°	403.3	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5
175°	406.8	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4
177.5°	408.0	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	28.9	29.0	29.1	29.2	29.2	29.2	29.2	29.2
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.0	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.3	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.3	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.5	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.2	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.4	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.0	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.7	104.5	104.3	104.4	104.6	104.9	105.0	105.2



TEST NUMBER: P332677-940

CATALOG NUMBER: SA4XXDIP-C1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.6	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.2	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.9	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.7	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.5	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.5	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	230.1	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.9	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.7	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.9	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.2	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	315.0	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.6	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.4	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.1	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.7	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.5	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.3	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	396.9	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.4	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.1	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.4	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)