

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332965-930

Luminaire Tested: **SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332965-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5071.3 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332965-930
CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	93	86	80	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	41				
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	45	42	39	36				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28				
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25				
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22				
9	53	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.7
10°-20°	385.6	7.6
20°-30°	556.9	11.0
30°-40°	631.2	12.4
40°-50°	609.5	12.0
50°-60°	506.9	10.0
60°-70°	350.0	6.9
70°-80°	177.4	3.5
80°-90°	47.3	0.9
90°-100°	39.7	0.8
100°-110°	117.5	2.3
110°-120°	199.4	3.9
120°-130°	262.9	5.2
130°-140°	295.3	5.8
140°-150°	290.2	5.7
150°-160°	244.0	4.8
160°-170°	162.4	3.2
170°-180°	56.9	1.1
0°-30°	1080.8	21.3
0°-40°	1712.0	33.8
0°-60°	2828.4	55.8
0°-90°	3403.1	67.1
90°-120°	356.5	7.0
90°-150°	1204.9	23.8
90°-180°	1668.0	32.9
0°-180°	5071.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	68
90°	1	6	10	13	14	5
95°	28	32	35	37	37	31
105°	108	109	111	112	114	115
115°	203	203	202	201	201	200
125°	295	295	295	294	293	263
135°	381	384	384	383	381	295
145°	463	464	465	464	463	289
155°	530	530	530	531	530	244
165°	577	576	575	577	576	163
175°	600	598	598	600	598	57
180°	601	601	601	601	601	



TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.0	19.6	18.3	16.9	15.5	14.8	14.8	14.8	14.7	14.7	14.6
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	9.9	11.3	12.6	13.9	15.2	16.1	16.7	17.3	17.9	18.4	18.8
95°	27.9	28.9	29.8	30.7	31.6	32.4	33.2	33.9	34.7	35.3	35.6
97.5°	48.8	49.5	50.2	51.0	51.7	52.5	53.3	54.2	55.0	55.9	56.3
100°	65.1	65.6	66.0	66.4	66.8	67.4	68.3	69.3	70.2	71.2	71.3
102.5°	82.2	82.3	82.5	82.7	82.8	83.4	84.2	85.0	85.9	86.7	87.1
105°	108.4	108.4	108.5	108.7	108.8	109.0	109.4	109.8	110.2	110.6	111.0
107.5°	135.7	135.9	136.0	136.2	136.3	136.4	136.4	136.5	136.6	136.6	136.9
110°	154.4	154.6	154.8	155.0	155.2	155.2	155.2	155.1	155.0	154.8	154.7



TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	173.7	173.7	173.8	173.8	173.9	173.8	173.7	173.4	173.3	173.1	173.0
115°	202.8	202.8	202.8	202.8	202.8	202.6	202.4	202.2	202.0	201.8	201.7
117.5°	230.1	230.2	230.2	230.3	230.4	230.4	230.2	230.1	229.9	229.8	229.4
120°	248.3	248.7	249.2	249.6	250.0	250.1	249.7	249.4	249.1	248.7	248.3
122.5°	267.3	267.4	267.6	267.7	267.9	268.0	267.8	267.7	267.5	267.4	267.0
125°	295.3	295.3	295.3	295.3	295.3	295.2	295.1	295.1	294.9	294.8	294.6
127.5°	320.7	321.0	321.3	321.6	321.9	322.0	321.8	321.6	321.5	321.3	321.1
130°	338.5	338.8	339.2	339.5	339.7	339.9	339.9	339.9	339.9	339.9	339.7
132.5°	356.8	357.0	357.2	357.4	357.7	357.8	357.7	357.6	357.5	357.4	357.2
135°	380.8	381.5	382.0	382.7	383.4	383.6	383.6	383.6	383.6	383.6	383.4
137.5°	407.1	407.3	407.6	407.9	408.2	408.5	408.6	408.8	409.0	409.1	408.9
140°	424.5	424.8	424.9	425.2	425.3	425.5	425.5	425.5	425.5	425.5	425.3
142.5°	440.5	440.8	441.0	441.2	441.4	441.4	441.3	441.2	441.2	441.1	441.1
145°	462.7	463.1	463.5	463.9	464.3	464.6	464.7	464.8	464.9	465.0	464.9
147.5°	484.6	485.1	485.6	486.1	486.7	486.8	486.7	486.7	486.6	486.5	486.4
150°	498.0	498.5	498.9	499.3	499.7	499.9	499.9	499.9	499.9	499.9	499.9
152.5°	510.7	510.9	511.2	511.4	511.7	511.8	511.9	512.0	512.1	512.2	512.4
155°	530.1	530.1	530.1	530.1	530.1	530.0	529.9	529.9	529.8	529.6	530.0
157.5°	546.5	546.3	546.1	545.9	545.8	545.6	545.6	545.6	545.6	545.5	545.8
160°	556.1	556.0	556.0	555.9	555.7	555.6	555.5	555.5	555.3	555.2	555.5
162.5°	565.1	564.8	564.5	564.3	564.0	563.8	563.7	563.6	563.5	563.4	563.9
165°	577.1	576.7	576.4	576.2	575.8	575.6	575.4	575.2	574.9	574.8	575.4
167.5°	586.3	585.9	585.4	585.0	584.6	584.3	584.3	584.4	584.4	584.4	585.1
170°	591.5	591.0	590.4	590.0	589.4	589.2	589.3	589.4	589.5	589.6	590.3
172.5°	595.2	594.8	594.4	593.9	593.5	593.3	593.3	593.3	593.3	593.4	594.0
175°	600.3	599.8	599.3	598.8	598.3	597.9	597.9	597.8	597.6	597.5	598.3
177.5°	602.0	601.6	601.2	600.8	600.3	600.1	600.1	600.1	600.1	600.1	600.7
180°	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3



TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	14.5	14.4	14.3	14.4	14.7	14.9	15.2	15.4
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	19.2	19.6	19.9	20.1	20.3	20.4	20.5	20.6
95°	36.0	36.3	36.6	36.8	36.8	36.8	36.8	36.8
97.5°	56.7	57.0	57.4	57.6	57.6	57.6	57.6	57.6
100°	71.6	71.7	72.0	72.1	72.1	72.1	72.1	72.1
102.5°	87.3	87.6	87.9	88.1	88.2	88.3	88.4	88.5
105°	111.3	111.6	111.9	112.2	112.5	112.8	113.2	113.5
107.5°	137.2	137.5	137.8	137.9	137.9	137.9	137.9	137.9
110°	154.4	154.3	154.0	154.1	154.4	154.7	155.0	155.3



TEST NUMBER: P332965-930

CATALOG NUMBER: SA4XXRDIP-C1020D590U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.0	172.9	172.9	172.9	173.0	173.0	173.1	173.2
115°	201.6	201.5	201.4	201.3	201.2	201.1	201.0	200.9
117.5°	229.1	228.8	228.4	228.1	227.9	227.7	227.5	227.3
120°	247.8	247.2	246.7	246.5	246.8	247.0	247.2	247.4
122.5°	266.7	266.4	266.0	265.6	265.2	264.9	264.5	264.2
125°	294.4	294.2	294.0	293.8	293.6	293.3	293.2	292.9
127.5°	320.9	320.7	320.5	320.3	320.2	320.0	319.8	319.7
130°	339.5	339.3	339.1	338.8	338.3	337.9	337.5	337.1
132.5°	357.0	356.8	356.6	356.4	356.2	356.0	355.9	355.7
135°	383.2	383.0	382.8	382.5	382.2	381.9	381.6	381.3
137.5°	408.5	408.3	408.1	407.9	408.0	408.1	408.1	408.2
140°	425.3	425.2	425.1	424.9	424.9	424.8	424.7	424.5
142.5°	441.1	441.1	441.0	441.0	441.0	441.0	440.9	440.9
145°	464.8	464.7	464.6	464.4	464.1	463.7	463.4	463.2
147.5°	486.3	486.2	486.2	486.1	486.0	485.8	485.8	485.7
150°	499.9	499.9	499.9	499.9	499.7	499.6	499.5	499.5
152.5°	512.7	512.9	513.1	513.1	512.9	512.6	512.3	512.1
155°	530.4	530.8	531.3	531.3	530.8	530.4	530.0	529.6
157.5°	546.2	546.5	546.8	546.7	546.4	546.1	545.7	545.4
160°	555.9	556.1	556.4	556.4	555.9	555.3	554.8	554.3
162.5°	564.5	565.1	565.7	565.7	565.2	564.6	564.1	563.6
165°	576.0	576.6	577.2	577.3	576.9	576.5	576.1	575.7
167.5°	585.6	586.3	586.9	586.9	586.3	585.6	585.0	584.3
170°	590.8	591.5	592.1	592.1	591.3	590.6	589.9	589.1
172.5°	594.8	595.5	596.1	596.1	595.4	594.7	593.9	593.3
175°	599.0	599.7	600.4	600.4	599.7	599.0	598.3	597.5
177.5°	601.3	601.9	602.4	602.4	601.8	601.1	600.4	599.7
180°	601.3	601.3	601.3	601.3	601.3	601.3	601.3	601.3

(END OF REPORT)