

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332686-940

Luminaire Tested: **SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332686-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6386.6 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332686-940
CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332686-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332686-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	2.6
10°-20°	471.5	7.4
20°-30°	694.0	10.9
30°-40°	806.8	12.6
40°-50°	806.8	12.6
50°-60°	705.8	11.1
60°-70°	524.1	8.2
70°-80°	297.8	4.7
80°-90°	87.9	1.4
90°-100°	43.4	0.7
100°-110°	128.5	2.0
110°-120°	218.1	3.4
120°-130°	287.6	4.5
130°-140°	322.9	5.1
140°-150°	317.3	5.0
150°-160°	266.9	4.2
160°-170°	177.6	2.8
170°-180°	62.2	1.0
0°-30°	1332.9	20.9
0°-40°	2139.7	33.5
0°-60°	3652.3	57.2
0°-90°	4562.1	71.4
90°-120°	389.9	6.1
90°-150°	1317.8	20.6
90°-180°	1824.0	28.6
0°-180°	6386.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	2	7	11	14	15	6
95°	30	35	39	40	40	34
105°	118	119	121	123	124	126
115°	222	222	221	220	220	219
125°	323	323	322	321	320	288
135°	416	419	420	419	417	322
145°	506	508	508	508	507	317
155°	580	580	579	581	579	267
165°	631	630	629	631	630	178
175°	657	654	654	657	654	62
180°	658	658	658	658	658	



TEST NUMBER: P332686-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	30.0	30.0	29.9	29.9	29.9	29.9	29.8	29.7	29.6	29.6	29.7
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	10.9	12.3	13.7	15.2	16.6	17.6	18.3	18.9	19.5	20.2	20.5
95°	30.5	31.6	32.5	33.5	34.6	35.5	36.3	37.1	37.9	38.6	39.0
97.5°	53.3	54.1	54.9	55.7	56.5	57.4	58.3	59.3	60.2	61.2	61.5
100°	71.2	71.7	72.1	72.6	73.0	73.7	74.7	75.8	76.8	77.8	78.0
102.5°	89.9	90.1	90.2	90.4	90.6	91.2	92.1	93.0	94.0	94.9	95.2
105°	118.5	118.6	118.7	118.9	119.0	119.2	119.7	120.1	120.6	121.0	121.4
107.5°	148.5	148.6	148.7	148.9	149.1	149.2	149.2	149.3	149.4	149.5	149.7
110°	168.9	169.1	169.3	169.5	169.8	169.8	169.7	169.6	169.5	169.3	169.2



TEST NUMBER: P332686-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	190.0	190.0	190.1	190.1	190.2	190.1	189.9	189.7	189.5	189.3	189.2
115°	221.8	221.8	221.8	221.8	221.8	221.6	221.4	221.1	221.0	220.7	220.6
117.5°	251.6	251.7	251.8	251.9	252.0	252.0	251.8	251.6	251.5	251.4	250.9
120°	271.6	272.1	272.5	273.0	273.4	273.5	273.1	272.8	272.4	272.1	271.5
122.5°	292.3	292.5	292.7	292.8	293.0	293.1	292.9	292.7	292.6	292.5	292.0
125°	323.0	323.0	323.0	323.0	323.0	322.9	322.8	322.7	322.5	322.4	322.2
127.5°	350.7	351.1	351.4	351.8	352.0	352.1	352.0	351.8	351.6	351.4	351.2
130°	370.2	370.6	371.0	371.3	371.6	371.8	371.8	371.8	371.8	371.8	371.6
132.5°	390.2	390.5	390.7	390.9	391.2	391.3	391.2	391.1	391.0	390.9	390.7
135°	416.5	417.2	417.9	418.6	419.3	419.5	419.5	419.5	419.5	419.5	419.4
137.5°	445.2	445.5	445.9	446.1	446.5	446.7	446.9	447.1	447.3	447.5	447.2
140°	464.3	464.6	464.8	465.0	465.2	465.4	465.4	465.4	465.4	465.4	465.2
142.5°	481.8	482.1	482.3	482.5	482.8	482.8	482.7	482.6	482.5	482.4	482.4
145°	506.0	506.5	506.9	507.4	507.8	508.1	508.3	508.4	508.5	508.5	508.5
147.5°	530.0	530.6	531.1	531.6	532.3	532.4	532.4	532.3	532.2	532.1	532.0
150°	544.7	545.2	545.6	546.1	546.5	546.7	546.7	546.7	546.7	546.7	546.7
152.5°	558.6	558.8	559.1	559.4	559.6	559.8	559.9	560.0	560.1	560.2	560.4
155°	579.8	579.8	579.8	579.8	579.8	579.7	579.6	579.5	579.4	579.3	579.7
157.5°	597.7	597.4	597.3	597.1	596.9	596.7	596.7	596.7	596.7	596.6	597.0
160°	608.2	608.1	608.1	608.0	607.8	607.7	607.6	607.5	607.3	607.3	607.6
162.5°	618.0	617.8	617.4	617.2	616.9	616.6	616.5	616.4	616.4	616.2	616.8
165°	631.2	630.8	630.4	630.2	629.8	629.5	629.3	629.1	628.8	628.7	629.3
167.5°	641.2	640.8	640.2	639.8	639.4	639.1	639.1	639.2	639.2	639.2	639.9
170°	646.9	646.4	645.8	645.2	644.6	644.4	644.5	644.6	644.8	644.9	645.6
172.5°	650.9	650.5	650.1	649.6	649.1	648.9	648.9	648.9	648.9	649.0	649.7
175°	656.6	656.0	655.5	654.9	654.3	654.0	653.9	653.8	653.6	653.5	654.3
177.5°	658.4	658.0	657.5	657.1	656.6	656.4	656.4	656.4	656.4	656.4	657.0
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6



TEST NUMBER: P332686-940
 CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	29.9	30.0	30.1	30.2	30.2	30.3	30.3	30.4
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	21.0	21.4	21.8	22.0	22.2	22.3	22.5	22.6
95°	39.3	39.7	40.0	40.2	40.2	40.2	40.2	40.2
97.5°	62.0	62.3	62.8	63.0	63.0	63.0	63.0	63.0
100°	78.3	78.5	78.7	78.8	78.8	78.8	78.8	78.8
102.5°	95.5	95.9	96.1	96.4	96.5	96.6	96.7	96.8
105°	121.7	122.1	122.4	122.7	123.1	123.4	123.8	124.1
107.5°	150.1	150.3	150.7	150.9	150.8	150.8	150.8	150.8
110°	168.9	168.7	168.4	168.5	168.9	169.2	169.5	169.9



TEST NUMBER: P332686-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	189.2	189.1	189.1	189.1	189.2	189.2	189.3	189.4
115°	220.5	220.4	220.3	220.2	220.1	219.9	219.8	219.7
117.5°	250.6	250.2	249.8	249.5	249.2	249.1	248.8	248.6
120°	271.0	270.4	269.8	269.7	269.9	270.1	270.4	270.5
122.5°	291.7	291.3	290.9	290.5	290.1	289.7	289.3	288.9
125°	322.0	321.7	321.6	321.3	321.1	320.8	320.7	320.4
127.5°	351.0	350.8	350.5	350.4	350.2	350.0	349.8	349.6
130°	371.3	371.1	370.9	370.5	370.1	369.6	369.2	368.7
132.5°	390.5	390.2	390.0	389.8	389.6	389.4	389.2	389.1
135°	419.1	418.9	418.7	418.4	418.0	417.7	417.4	417.1
137.5°	446.8	446.6	446.3	446.1	446.2	446.3	446.4	446.5
140°	465.1	465.0	464.9	464.8	464.7	464.6	464.5	464.3
142.5°	482.4	482.4	482.3	482.3	482.3	482.3	482.2	482.2
145°	508.4	508.3	508.1	507.9	507.6	507.2	506.8	506.6
147.5°	531.9	531.8	531.7	531.6	531.5	531.4	531.3	531.2
150°	546.7	546.7	546.7	546.7	546.5	546.4	546.4	546.3
152.5°	560.7	561.0	561.2	561.2	561.0	560.6	560.4	560.1
155°	580.1	580.6	581.1	581.1	580.6	580.1	579.7	579.3
157.5°	597.4	597.7	598.1	598.0	597.6	597.3	596.8	596.5
160°	608.0	608.2	608.6	608.5	608.0	607.3	606.8	606.3
162.5°	617.4	618.0	618.7	618.7	618.1	617.5	617.0	616.4
165°	630.0	630.6	631.3	631.4	631.0	630.5	630.1	629.6
167.5°	640.5	641.2	641.9	641.9	641.2	640.5	639.8	639.1
170°	646.2	646.9	647.6	647.6	646.8	646.0	645.2	644.4
172.5°	650.5	651.3	652.0	652.0	651.2	650.4	649.6	648.9
175°	655.1	655.9	656.7	656.7	655.9	655.1	654.3	653.5
177.5°	657.6	658.3	658.9	658.9	658.2	657.5	656.7	655.9
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6

(END OF REPORT)