

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332971-930

Luminaire Tested: **SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332971-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5690.3 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51				
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	49	47	43				
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37				
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32				
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28				
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25				
7	60	48	40	35	56	45	38	33	40	34	30	36	31	27	31	27	24	22				
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20				
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18				
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11885	11885	11885
5°	11912	11766	11839
10°	11837	11625	11625
15°	11701	11381	11295
20°	11515	11059	10856
25°	11276	10684	10413
30°	11044	10288	9857
35°	10787	9876	9298
40°	10478	9409	8696
45°	10193	8944	8082
50°	9868	8410	7433
55°	9520	7854	6726
60°	9137	7245	6006
65°	8785	6481	5297
70°	8275	5641	4497
75°	7629	4676	3656
80°	6657	3561	3357
85°	5641	3242	3029



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.4
10°-20°	385.6	6.8
20°-30°	556.9	9.8
30°-40°	631.2	11.1
40°-50°	609.5	10.7
50°-60°	506.9	8.9
60°-70°	350.0	6.2
70°-80°	177.4	3.1
80°-90°	48.0	0.8
90°-100°	54.4	1.0
100°-110°	161.0	2.8
110°-120°	273.3	4.8
120°-130°	360.4	6.3
130°-140°	404.7	7.1
140°-150°	397.7	7.0
150°-160°	334.5	5.9
160°-170°	222.6	3.9
170°-180°	77.9	1.4
0°-30°	1080.8	19.0
0°-40°	1712.0	30.1
0°-60°	2828.4	49.7
0°-90°	3403.8	59.8
90°-120°	488.7	8.6
90°-150°	1651.5	29.0
90°-180°	2287.0	40.2
0°-180°	5690.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1470	1465	1452	1462	1461	139
15°	1400	1389	1362	1359	1352	394
25°	1266	1244	1199	1181	1169	583
35°	1094	1057	1002	965	944	684
45°	893	850	783	730	708	688
55°	676	630	558	501	478	605
65°	460	410	339	293	277	454
75°	245	202	150	125	117	258
85°	61	39	35	33	33	69
90°	2	9	14	18	19	5
95°	38	44	48	50	50	43
105°	148	149	152	154	156	158
115°	278	278	277	276	275	274
125°	405	405	404	403	402	361
135°	522	526	526	524	523	404
145°	634	637	637	637	635	397
155°	727	727	726	728	726	334
165°	791	789	788	791	789	223
175°	823	820	819	823	819	78
180°	824	824	824	824	824	



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1475.8	1475.0	1474.1	1473.4	1472.6	1471.0	1468.8	1466.6	1464.4	1462.2	1464.4
5°	1469.9	1468.9	1467.9	1466.9	1465.9	1463.9	1460.9	1457.9	1454.9	1451.9	1454.4
7.5°	1456.6	1455.6	1454.5	1453.4	1452.4	1449.9	1446.0	1442.1	1438.2	1434.3	1435.9
10°	1444.0	1442.8	1441.4	1440.2	1439.0	1436.1	1431.6	1427.1	1422.5	1418.1	1419.0
12.5°	1427.8	1426.3	1424.8	1423.4	1422.0	1418.5	1413.2	1407.9	1402.6	1397.3	1397.9
15°	1400.0	1397.7	1395.5	1393.3	1391.0	1386.7	1380.5	1374.2	1368.0	1361.7	1361.2
17.5°	1366.4	1363.2	1359.9	1356.7	1353.4	1348.0	1340.5	1333.0	1325.5	1317.9	1316.5
20°	1340.3	1337.0	1333.7	1330.5	1327.2	1321.4	1312.9	1304.3	1295.8	1287.3	1285.3
22.5°	1311.4	1307.7	1304.1	1300.5	1296.8	1290.4	1281.3	1272.2	1263.1	1253.9	1250.9
25°	1265.9	1261.3	1256.9	1252.4	1247.8	1240.5	1230.2	1219.9	1209.7	1199.4	1195.1
27.5°	1218.1	1212.4	1206.8	1201.1	1195.5	1187.2	1176.2	1165.2	1154.2	1143.2	1138.0
30°	1184.7	1178.4	1172.2	1166.0	1159.7	1150.6	1138.9	1127.1	1115.3	1103.6	1097.3
32.5°	1149.6	1142.5	1135.4	1128.4	1121.3	1111.7	1099.5	1087.4	1075.1	1063.0	1055.7
35°	1094.5	1086.5	1078.5	1070.5	1062.5	1052.2	1039.7	1027.2	1014.6	1002.1	993.6
37.5°	1035.7	1027.4	1019.2	1010.9	1002.7	991.6	977.7	963.8	949.9	936.0	926.5
40°	994.3	985.9	977.7	969.4	961.2	949.9	935.6	921.3	907.0	892.8	882.2
42.5°	954.6	945.9	937.2	928.5	919.9	908.1	893.2	878.3	863.5	848.6	837.9
45°	892.8	883.5	874.2	865.0	855.7	843.5	828.5	813.5	798.4	783.4	771.2
47.5°	829.0	819.4	809.8	800.3	790.7	778.1	762.5	746.8	731.2	715.6	702.9
50°	785.7	775.9	766.1	756.4	746.6	733.7	717.7	701.6	685.6	669.6	657.0
52.5°	741.5	731.9	722.4	712.8	703.2	690.2	673.8	657.4	640.9	624.5	611.8
55°	676.4	666.3	656.3	646.3	636.3	623.1	606.8	590.5	574.3	558.0	544.9
57.5°	611.9	601.4	591.0	580.6	570.2	556.9	541.0	524.9	508.8	492.8	479.6
60°	565.9	555.9	545.8	535.8	525.8	512.7	496.8	480.7	464.6	448.7	435.6
62.5°	524.4	514.0	503.5	493.1	482.7	469.3	452.8	436.4	420.0	403.6	391.5
65°	459.9	449.1	438.4	427.6	416.9	403.4	387.4	371.4	355.3	339.3	328.6
67.5°	393.0	382.6	372.3	362.0	351.6	339.1	324.2	309.3	294.4	279.6	270.3
70°	350.6	340.1	329.5	319.0	308.5	296.1	281.8	267.5	253.2	239.0	230.7
72.5°	305.5	296.0	286.4	277.0	267.4	255.9	242.5	228.9	215.5	202.0	194.9
75°	244.6	235.4	226.1	216.8	207.6	197.0	185.2	173.5	161.7	149.9	144.1
77.5°	182.9	175.0	167.1	159.2	151.4	142.7	133.1	123.7	114.1	104.6	101.3
80°	143.2	135.9	128.7	121.4	114.1	106.7	99.2	91.7	84.1	76.6	75.9
82.5°	108.9	102.2	95.6	88.9	82.3	76.7	72.5	68.2	63.8	59.5	58.9
85°	60.9	55.8	50.9	45.8	40.8	37.9	37.2	36.4	35.7	35.0	34.4
87.5°	21.1	19.8	18.5	17.3	16.0	15.3	15.3	15.4	15.4	15.4	15.4
90°	1.9	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8
92.5°	13.6	15.4	17.2	19.0	20.8	22.1	22.8	23.6	24.5	25.3	25.8
95°	38.2	39.5	40.8	42.1	43.4	44.5	45.5	46.5	47.5	48.4	48.8
97.5°	66.8	67.8	68.8	69.9	70.8	72.0	73.1	74.3	75.4	76.6	77.1
100°	89.3	89.8	90.3	90.9	91.5	92.5	93.7	95.0	96.2	97.5	97.8
102.5°	112.7	112.9	113.2	113.4	113.6	114.3	115.4	116.6	117.8	119.0	119.4
105°	148.5	148.6	148.8	149.0	149.1	149.4	150.0	150.6	151.2	151.7	152.1
107.5°	186.1	186.3	186.5	186.6	186.8	186.9	187.0	187.1	187.2	187.3	187.7
110°	211.7	211.9	212.1	212.5	212.7	212.8	212.7	212.5	212.4	212.2	212.0



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	238.1	238.1	238.2	238.3	238.4	238.2	238.0	237.7	237.5	237.3	237.2
115°	277.9	277.9	277.9	277.9	277.9	277.8	277.4	277.2	276.9	276.6	276.5
117.5°	315.4	315.5	315.6	315.7	315.8	315.8	315.6	315.4	315.2	315.0	314.5
120°	340.4	341.0	341.5	342.1	342.7	342.7	342.3	341.9	341.4	341.0	340.3
122.5°	366.4	366.6	366.8	367.0	367.3	367.3	367.1	366.9	366.7	366.5	366.0
125°	404.7	404.7	404.7	404.7	404.7	404.6	404.6	404.4	404.2	404.1	403.8
127.5°	439.5	439.9	440.4	440.8	441.2	441.3	441.1	440.9	440.7	440.4	440.2
130°	464.0	464.5	464.9	465.3	465.7	465.9	465.9	465.9	465.9	465.9	465.6
132.5°	489.0	489.3	489.7	489.9	490.2	490.3	490.2	490.2	490.0	489.9	489.6
135°	522.0	522.9	523.7	524.6	525.5	525.9	525.9	525.9	525.9	525.9	525.5
137.5°	558.0	558.4	558.7	559.1	559.5	559.9	560.1	560.4	560.5	560.8	560.4
140°	582.0	582.2	582.5	582.8	583.1	583.2	583.2	583.2	583.2	583.2	583.1
142.5°	603.9	604.1	604.5	604.7	605.0	605.1	605.0	604.9	604.7	604.6	604.6
145°	634.2	634.8	635.4	635.9	636.5	636.8	637.0	637.1	637.2	637.4	637.2
147.5°	664.3	665.0	665.6	666.3	667.0	667.3	667.2	667.1	666.9	666.8	666.8
150°	682.7	683.2	683.8	684.4	684.9	685.2	685.2	685.2	685.2	685.2	685.2
152.5°	700.0	700.3	700.7	701.0	701.3	701.6	701.6	701.8	701.9	702.1	702.4
155°	726.6	726.6	726.6	726.6	726.6	726.5	726.4	726.3	726.1	726.0	726.5
157.5°	749.1	748.8	748.5	748.3	748.0	747.9	747.9	747.9	747.8	747.8	748.2
160°	762.3	762.1	762.1	761.9	761.7	761.6	761.5	761.3	761.2	761.1	761.5
162.5°	774.5	774.2	773.8	773.5	773.1	772.8	772.7	772.6	772.4	772.3	773.1
165°	791.0	790.6	790.2	789.7	789.3	789.0	788.6	788.4	788.1	787.8	788.6
167.5°	803.6	803.0	802.4	801.8	801.3	801.0	801.0	801.0	801.0	801.0	801.9
170°	810.7	810.1	809.3	808.6	808.0	807.6	807.8	808.0	808.0	808.2	809.0
172.5°	815.9	815.3	814.6	814.1	813.5	813.2	813.3	813.3	813.3	813.3	814.2
175°	822.9	822.1	821.4	820.8	820.0	819.6	819.5	819.3	819.2	819.0	820.0
177.5°	825.2	824.6	824.0	823.5	822.9	822.6	822.6	822.6	822.6	822.6	823.4
180°	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1466.6	1468.8	1471.0	1472.1	1471.9	1471.7	1471.5	1471.3
5°	1456.9	1459.4	1461.9	1462.9	1462.4	1461.9	1461.4	1460.9
7.5°	1437.5	1439.1	1440.7	1441.1	1440.3	1439.5	1438.7	1437.9
10°	1420.1	1421.1	1422.0	1422.0	1421.1	1420.1	1419.0	1418.1
12.5°	1398.5	1399.1	1399.7	1399.3	1397.9	1396.5	1395.1	1393.8
15°	1360.7	1360.2	1359.7	1358.5	1356.8	1355.0	1353.3	1351.5
17.5°	1315.2	1313.8	1312.4	1310.3	1307.7	1305.0	1302.4	1299.7
20°	1283.3	1281.3	1279.3	1276.7	1273.4	1270.2	1266.9	1263.6
22.5°	1247.9	1244.9	1241.9	1239.1	1236.4	1233.8	1231.1	1228.5
25°	1190.8	1186.6	1182.3	1178.9	1176.5	1173.9	1171.4	1169.0
27.5°	1132.7	1127.5	1122.2	1117.8	1114.2	1110.5	1106.9	1103.3
30°	1091.0	1084.8	1078.5	1073.3	1069.3	1065.4	1061.4	1057.4
32.5°	1048.5	1041.2	1034.0	1028.4	1024.6	1020.8	1017.0	1013.2
35°	985.0	976.6	968.0	961.6	957.0	952.5	948.0	943.5
37.5°	917.0	907.5	898.0	891.0	886.5	881.9	877.4	872.9
40°	871.7	861.2	850.7	843.2	838.7	834.1	829.6	825.2
42.5°	827.1	816.4	805.7	798.0	793.3	788.6	783.8	779.2
45°	758.9	746.6	734.3	725.9	721.5	716.9	712.4	707.9
47.5°	690.2	677.4	664.6	655.8	650.9	645.9	640.9	636.0
50°	644.5	632.0	619.5	610.8	606.1	601.3	596.6	591.8
52.5°	599.0	586.3	573.6	564.8	559.8	554.8	549.8	544.9
55°	531.9	518.9	505.9	497.0	492.2	487.5	482.7	477.9
57.5°	466.4	453.1	439.9	431.5	427.9	424.3	420.7	417.1
60°	422.6	409.5	396.6	388.0	384.0	380.0	376.0	372.0
62.5°	379.5	367.5	355.5	347.8	344.6	341.4	338.2	335.0
65°	317.7	307.0	296.2	289.3	286.3	283.3	280.3	277.3
67.5°	261.0	251.8	242.5	236.2	232.8	229.6	226.2	223.0
70°	222.4	214.2	205.9	200.5	198.0	195.5	193.0	190.5
72.5°	187.8	180.8	173.7	169.1	166.7	164.4	162.2	159.9
75°	138.4	132.6	126.9	123.3	121.7	120.3	118.7	117.2
77.5°	97.9	94.6	91.2	89.3	88.8	88.4	87.9	87.5
80°	75.2	74.4	73.6	73.1	72.9	72.6	72.4	72.2
82.5°	58.4	57.9	57.3	56.9	56.7	56.4	56.2	55.9
85°	33.9	33.4	32.9	32.7	32.7	32.7	32.7	32.7
87.5°	15.4	15.3	15.3	15.4	15.7	15.9	16.2	16.5
90°	15.7	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	26.3	26.7	27.3	27.6	27.8	28.0	28.1	28.3
95°	49.3	49.7	50.1	50.4	50.4	50.4	50.4	50.4
97.5°	77.6	78.1	78.7	78.9	78.9	78.9	78.9	78.9
100°	98.1	98.4	98.7	98.8	98.8	98.8	98.8	98.8
102.5°	119.8	120.1	120.5	120.7	120.9	121.0	121.2	121.2
105°	152.5	153.0	153.4	153.8	154.3	154.7	155.1	155.6
107.5°	188.1	188.4	188.8	189.1	189.0	189.0	189.0	188.9
110°	211.7	211.4	211.1	211.2	211.7	212.1	212.5	212.9



TEST NUMBER: P332971-930

CATALOG NUMBER: SA4XXRDIP-C1020D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.1	237.1	237.0	237.0	237.1	237.2	237.3	237.3
115°	276.3	276.2	276.1	275.9	275.8	275.7	275.5	275.3
117.5°	314.1	313.6	313.1	312.7	312.4	312.1	311.9	311.5
120°	339.6	338.8	338.2	337.9	338.3	338.5	338.8	339.1
122.5°	365.5	365.1	364.6	364.1	363.5	363.1	362.6	362.1
125°	403.6	403.2	403.0	402.7	402.4	402.1	401.9	401.5
127.5°	439.9	439.6	439.3	439.0	438.8	438.6	438.4	438.1
130°	465.4	465.0	464.8	464.4	463.8	463.3	462.7	462.1
132.5°	489.3	489.0	488.8	488.5	488.3	488.0	487.8	487.6
135°	525.3	525.0	524.7	524.3	523.9	523.5	523.1	522.7
137.5°	560.0	559.7	559.3	559.1	559.2	559.3	559.4	559.5
140°	582.9	582.8	582.6	582.5	582.4	582.2	582.0	582.0
142.5°	604.5	604.5	604.5	604.5	604.5	604.5	604.4	604.4
145°	637.1	637.0	636.8	636.5	636.1	635.7	635.3	634.9
147.5°	666.6	666.5	666.3	666.3	666.1	665.9	665.9	665.7
150°	685.2	685.2	685.2	685.1	685.0	684.9	684.7	684.5
152.5°	702.7	703.0	703.4	703.4	703.0	702.6	702.3	701.9
155°	727.1	727.7	728.2	728.2	727.7	727.1	726.5	726.0
157.5°	748.6	749.1	749.5	749.4	749.0	748.5	748.0	747.5
160°	761.9	762.3	762.7	762.6	761.9	761.2	760.5	759.8
162.5°	773.8	774.5	775.3	775.3	774.6	774.0	773.2	772.5
165°	789.5	790.4	791.2	791.3	790.8	790.2	789.6	789.1
167.5°	802.7	803.6	804.5	804.5	803.6	802.7	801.8	801.0
170°	809.9	810.7	811.6	811.5	810.6	809.6	808.5	807.6
172.5°	815.2	816.2	817.2	817.2	816.2	815.1	814.2	813.2
175°	821.0	822.0	823.0	823.0	822.0	821.0	820.0	819.0
177.5°	824.2	825.0	825.8	825.7	824.8	823.9	823.0	822.1
180°	824.1	824.1	824.1	824.1	824.1	824.1	824.1	824.1

(END OF REPORT)