

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332523-940

Luminaire Tested: **SA4XXDIP-C350D1035U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332523-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5036.7 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332523-940
CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	88	85	81	83	79	76	73	62	59	58	46	44	43	31	30	29	23				23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21	16				16
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18	14				14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12				12
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10				10
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12	9				9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11	8				8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7				7
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.0
10°-20°	139.8	2.8
20°-30°	205.7	4.1
30°-40°	239.2	4.7
40°-50°	239.2	4.7
50°-60°	209.2	4.2
60°-70°	155.4	3.1
70°-80°	88.3	1.8
80°-90°	28.9	0.6
90°-100°	40.7	0.8
100°-110°	259.5	5.2
110°-120°	496.5	9.9
120°-130°	630.3	12.5
130°-140°	674.3	13.4
140°-150°	630.6	12.5
150°-160°	508.5	10.1
160°-170°	328.0	6.5
170°-180°	113.0	2.2
0°-30°	395.1	7.8
0°-40°	634.2	12.6
0°-60°	1082.6	21.5
0°-90°	1355.2	26.9
90°-120°	796.7	15.8
90°-150°	2731.9	54.2
90°-180°	3681.0	73.1
0°-180°	5036.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	3	12	20	25	27	4
95°	49	20	20	25	26	63
105°	268	273	278	284	254	280
115°	500	503	502	504	504	492
125°	703	706	705	708	709	628
135°	872	872	875	877	879	672
145°	1006	1008	1008	1010	1011	628
155°	1103	1104	1101	1104	1102	508
165°	1163	1159	1159	1165	1158	329
175°	1190	1185	1186	1193	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	9.3	9.6	10.1	10.4	10.8	11.1	11.3	11.5	11.8	12.0	12.2
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	11.2	11.3	11.4	11.6	11.7	12.6	14.1	15.7	17.3	18.9	20.1
95°	49.0	42.3	35.5	28.8	22.0	18.8	19.0	19.2	19.4	19.6	20.8
97.5°	104.0	108.2	112.4	116.5	120.7	111.8	89.7	67.7	45.6	23.5	23.6
100°	146.0	149.5	153.1	156.7	160.2	148.4	121.1	93.8	66.4	39.1	35.8
102.5°	193.0	195.6	198.2	200.8	203.4	203.0	199.4	195.8	192.3	188.7	152.4
105°	268.0	269.1	270.3	271.5	272.7	273.8	274.7	275.7	276.8	277.8	279.6
107.5°	337.5	338.1	338.8	339.3	339.9	340.9	342.2	343.6	344.9	346.3	347.1
110°	384.6	385.1	385.8	386.3	386.9	387.8	389.0	390.2	391.4	392.5	393.0



TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.2	431.2	432.3	433.4	434.4	435.2	435.8	436.3	436.8	437.4	437.4
115°	500.2	500.9	501.5	502.0	502.7	502.8	502.7	502.5	502.2	502.0	502.5
117.5°	563.5	564.3	565.1	565.9	566.7	567.2	567.7	568.1	568.6	569.0	568.9
120°	606.2	607.0	607.8	608.6	609.4	609.7	609.5	609.3	609.0	608.9	609.3
122.5°	646.0	646.6	647.0	647.5	648.0	648.4	648.6	648.9	649.2	649.4	649.7
125°	703.2	704.0	704.8	705.6	706.4	706.6	706.2	705.8	705.4	705.0	705.6
127.5°	757.3	757.5	757.8	758.0	758.1	758.7	759.6	760.5	761.4	762.3	762.2
130°	792.3	792.5	792.6	792.8	793.0	793.4	794.1	794.6	795.2	795.9	796.0
132.5°	824.3	824.7	825.0	825.4	825.7	826.3	827.1	827.8	828.5	829.3	829.5
135°	872.4	872.2	872.0	871.7	871.6	871.8	872.6	873.4	874.2	875.0	875.4
137.5°	914.9	915.0	915.1	915.2	915.3	915.7	916.6	917.5	918.3	919.2	919.6
140°	942.7	943.1	943.5	943.9	944.2	944.7	945.0	945.5	945.8	946.3	946.8
142.5°	967.6	968.3	969.0	969.7	970.4	970.9	971.2	971.4	971.6	971.9	972.3
145°	1005.8	1006.5	1007.1	1007.6	1008.3	1008.5	1008.5	1008.5	1008.5	1008.5	1008.8
147.5°	1036.3	1037.4	1038.6	1039.6	1040.8	1041.3	1041.0	1040.8	1040.6	1040.4	1040.6
150°	1058.4	1059.2	1060.0	1060.8	1061.6	1061.8	1061.7	1061.5	1061.3	1061.0	1061.0
152.5°	1076.9	1077.5	1078.2	1078.8	1079.4	1079.6	1079.2	1078.9	1078.5	1078.2	1078.5
155°	1103.0	1103.1	1103.3	1103.5	1103.7	1103.5	1103.0	1102.3	1101.7	1101.2	1101.9
157.5°	1124.8	1124.7	1124.5	1124.4	1124.4	1123.9	1123.3	1122.6	1122.0	1121.2	1122.3
160°	1137.6	1137.0	1136.5	1135.9	1135.2	1134.9	1134.7	1134.4	1134.3	1134.1	1135.2
162.5°	1149.1	1148.3	1147.5	1146.7	1146.0	1145.6	1145.3	1145.1	1145.0	1144.8	1145.9
165°	1163.4	1162.4	1161.5	1160.5	1159.5	1159.0	1159.0	1159.0	1159.0	1159.0	1160.6
167.5°	1174.8	1173.8	1172.8	1171.8	1170.7	1170.2	1170.0	1169.9	1169.8	1169.7	1171.4
170°	1181.2	1180.1	1178.8	1177.7	1176.5	1176.0	1176.2	1176.4	1176.6	1176.8	1178.4
172.5°	1185.5	1184.4	1183.1	1182.0	1180.8	1180.3	1180.4	1180.7	1180.9	1181.1	1182.7
175°	1190.2	1189.0	1187.8	1186.6	1185.4	1184.9	1185.1	1185.4	1185.5	1185.7	1187.5
177.5°	1192.3	1191.1	1190.1	1189.0	1187.8	1187.5	1187.8	1188.1	1188.4	1188.7	1190.0
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2



TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	12.5	12.8	12.9	13.1	13.2	13.3	13.4	13.5
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	21.2	22.5	23.6	24.3	24.3	24.4	24.5	24.6
95°	21.9	23.2	24.3	25.1	25.2	25.4	25.6	25.8
97.5°	23.7	23.9	24.0	24.2	24.3	24.5	24.7	25.0
100°	32.5	29.1	25.7	24.2	24.3	24.5	24.7	25.0
102.5°	116.2	79.9	43.6	25.5	25.5	25.6	25.6	25.7
105°	281.3	283.0	284.8	282.2	275.1	268.0	260.8	253.7
107.5°	348.0	348.9	349.7	350.5	351.3	352.0	352.8	353.6
110°	393.3	393.8	394.1	394.7	395.2	395.8	396.5	397.0



TEST NUMBER: P332523-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	437.3	437.2	437.1	437.5	438.2	439.0	439.7	440.4
115°	502.8	503.3	503.6	503.8	503.8	503.8	503.8	503.8
117.5°	568.8	568.7	568.6	568.6	568.6	568.5	568.4	568.3
120°	609.7	610.0	610.5	610.5	610.0	609.7	609.3	608.9
122.5°	650.0	650.1	650.4	650.3	650.0	649.5	649.2	648.7
125°	706.2	706.8	707.4	707.8	708.0	708.2	708.4	708.6
127.5°	762.1	762.0	761.9	761.7	761.6	761.4	761.3	761.1
130°	796.2	796.4	796.6	796.7	796.7	796.7	796.7	796.7
132.5°	829.6	829.9	830.1	830.1	829.9	829.7	829.6	829.5
135°	875.8	876.2	876.6	877.0	877.4	877.8	878.2	878.6
137.5°	920.1	920.5	921.0	921.0	921.0	920.9	920.7	920.6
140°	947.4	948.1	948.6	949.0	949.2	949.4	949.6	949.9
142.5°	972.8	973.2	973.7	973.8	973.9	973.9	974.0	974.0
145°	1009.0	1009.1	1009.3	1009.7	1010.0	1010.4	1010.8	1011.2
147.5°	1040.7	1040.9	1041.1	1041.3	1041.4	1041.6	1041.9	1042.1
150°	1061.0	1061.0	1061.0	1061.1	1061.4	1061.6	1061.8	1061.9
152.5°	1078.8	1079.1	1079.4	1079.5	1079.4	1079.3	1079.1	1079.1
155°	1102.7	1103.5	1104.3	1104.4	1103.8	1103.2	1102.6	1102.1
157.5°	1123.3	1124.4	1125.3	1125.3	1124.4	1123.3	1122.3	1121.2
160°	1136.5	1137.6	1138.8	1138.8	1137.6	1136.5	1135.2	1134.1
162.5°	1147.1	1148.3	1149.5	1149.4	1148.1	1146.7	1145.4	1144.1
165°	1162.2	1163.8	1165.3	1165.2	1163.4	1161.6	1159.8	1158.1
167.5°	1173.1	1174.9	1176.6	1176.5	1174.6	1172.6	1170.5	1168.6
170°	1180.0	1181.5	1183.1	1182.9	1181.0	1179.0	1177.0	1175.0
172.5°	1184.3	1185.8	1187.4	1187.1	1185.0	1182.9	1180.7	1178.6
175°	1189.3	1191.1	1192.8	1192.5	1190.2	1187.8	1185.4	1183.0
177.5°	1191.2	1192.5	1193.8	1193.5	1191.6	1189.7	1187.8	1185.9
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2

(END OF REPORT)