

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333014-930

Luminaire Tested: **SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P333014-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7438.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333014-930
CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.1
10°-20°	445.4	6.0
20°-30°	643.1	8.6
30°-40°	729.0	9.8
40°-50°	704.0	9.5
50°-60°	585.4	7.9
60°-70°	404.2	5.4
70°-80°	204.9	2.8
80°-90°	55.2	0.7
90°-100°	348.3	4.7
100°-110°	724.9	9.7
110°-120°	649.3	8.7
120°-130°	546.2	7.3
130°-140°	455.4	6.1
140°-150°	347.9	4.7
150°-160°	244.5	3.3
160°-170°	143.8	1.9
170°-180°	46.8	0.6
0°-30°	1248.2	16.8
0°-40°	1977.3	26.6
0°-60°	3266.6	43.9
0°-90°	3930.9	52.8
90°-120°	1722.5	23.2
90°-150°	3071.9	41.3
90°-180°	3507.0	47.1
0°-180°	7438.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	8	17	19	20	5
95°	31	99	772	382	231	35
105°	111	161	622	1338	1333	118
115°	195	245	554	1065	1280	193
125°	272	323	551	906	1021	242
135°	323	385	547	804	913	250
145°	372	426	544	678	746	234
155°	424	457	529	599	624	195
165°	461	476	507	537	545	130
175°	481	482	486	493	491	46
180°	482	482	482	482	482	



TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.1	22.7	21.4	19.7	18.1	17.0	17.9	17.7	17.9	18.0	17.6
90°	1.0	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1
92.5°	10.8	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3
95°	31.2	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9
97.5°	56.1	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4
100°	72.0	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2
102.5°	87.2	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4
105°	110.9	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1
107.5°	137.0	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8
110°	154.4	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1



TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.1	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5
115°	195.2	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6
117.5°	220.1	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7
120°	236.8	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4
122.5°	252.0	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4
125°	271.9	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3
127.5°	289.5	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8
130°	299.4	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5
132.5°	309.2	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9
135°	323.0	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6
137.5°	336.9	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7
140°	346.7	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4
142.5°	357.3	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9
145°	372.3	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1
147.5°	389.1	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1
150°	399.8	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8
152.5°	409.6	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7
155°	423.5	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7
157.5°	436.9	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4
160°	445.2	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5
162.5°	452.8	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5
165°	461.4	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5
167.5°	469.9	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3
170°	473.7	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3
172.5°	477.4	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0
175°	481.3	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9
177.5°	483.0	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	17.5	17.4	17.4	17.4	17.9	18.3	18.3	18.6
90°	17.0	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	186.1	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	702.0	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	1037.2	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1142.6	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1137.3	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1061.0	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	952.8	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	887.7	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P333014-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	839.9	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	792.0	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	768.5	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	757.9	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	748.8	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	733.3	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	714.3	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	699.2	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	683.2	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	661.3	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	641.4	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	630.0	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	619.4	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	604.5	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	592.2	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	584.6	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	576.2	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	563.7	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	550.2	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	541.9	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	533.5	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	522.0	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	510.9	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	504.0	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	497.9	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	489.8	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	484.5	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)