

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332994-930

Luminaire Tested: **SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332994-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5853.5 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332994-930  
CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57
2	93	86	80	74	88	81	76	71	72	68	65	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	73	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22
9	54	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.7	2.7
10°-20°	445.4	7.6
20°-30°	643.1	11.0
30°-40°	729.0	12.5
40°-50°	704.0	12.0
50°-60°	585.4	10.0
60°-70°	404.2	6.9
70°-80°	204.9	3.5
80°-90°	54.4	0.9
90°-100°	21.3	0.4
100°-110°	135.6	2.3
110°-120°	259.4	4.4
120°-130°	329.3	5.6
130°-140°	352.3	6.0
140°-150°	329.4	5.6
150°-160°	265.7	4.5
160°-170°	171.4	2.9
170°-180°	59.1	1.0
0°-30°	1248.2	21.3
0°-40°	1977.3	33.8
0°-60°	3266.6	55.8
0°-90°	3930.1	67.1
90°-120°	416.3	7.1
90°-150°	1427.3	24.4
90°-180°	1923.0	32.9
0°-180°	5853.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	6	10	13	14	5
95°	26	11	10	13	14	33
105°	140	143	145	148	133	146
115°	261	263	262	263	263	257
125°	367	369	368	370	370	328
135°	456	455	457	458	459	351
145°	526	527	527	527	528	328
155°	576	577	575	577	576	266
165°	608	606	606	609	605	172
175°	622	619	620	623	618	59
180°	622	622	622	622	622	



TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.2	22.6	21.0	19.3	17.8	16.9	16.8	16.8	16.7	16.6	16.6
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	5.9	6.0	6.0	6.0	6.1	6.5	7.4	8.2	9.0	9.9	10.5
95°	25.6	22.1	18.6	15.0	11.5	9.8	9.9	10.0	10.1	10.2	10.8
97.5°	54.3	56.5	58.7	60.9	63.1	58.4	46.9	35.4	23.8	12.3	12.3
100°	76.2	78.1	80.0	81.9	83.7	77.5	63.3	49.0	34.7	20.5	18.7
102.5°	100.9	102.2	103.5	104.9	106.3	106.1	104.2	102.3	100.4	98.6	79.7
105°	140.0	140.6	141.2	141.9	142.4	143.0	143.6	144.1	144.6	145.1	146.0
107.5°	176.3	176.7	177.0	177.2	177.6	178.1	178.8	179.5	180.2	180.9	181.4
110°	200.9	201.2	201.5	201.9	202.1	202.6	203.3	203.8	204.5	205.1	205.3



TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.3	225.8	226.4	227.0	227.4	227.6	228.0	228.3	228.5	228.5
115°	261.4	261.7	262.0	262.3	262.6	262.7	262.6	262.5	262.4	262.3	262.5
117.5°	294.4	294.8	295.2	295.6	296.0	296.4	296.6	296.9	297.0	297.3	297.3
120°	316.7	317.2	317.6	318.0	318.4	318.5	318.5	318.3	318.2	318.1	318.3
122.5°	337.5	337.8	338.0	338.3	338.5	338.8	338.9	339.0	339.2	339.3	339.4
125°	367.4	367.8	368.3	368.7	369.1	369.2	368.9	368.8	368.5	368.4	368.7
127.5°	395.7	395.7	395.9	396.0	396.1	396.4	396.9	397.3	397.8	398.3	398.2
130°	413.9	414.0	414.1	414.3	414.3	414.5	414.8	415.2	415.5	415.8	415.9
132.5°	430.6	430.8	431.0	431.2	431.4	431.7	432.1	432.4	432.8	433.3	433.3
135°	455.8	455.7	455.6	455.4	455.3	455.5	455.9	456.3	456.7	457.1	457.4
137.5°	478.0	478.0	478.1	478.1	478.2	478.4	478.8	479.3	479.8	480.2	480.5
140°	492.5	492.7	492.9	493.1	493.3	493.5	493.7	494.0	494.2	494.4	494.6
142.5°	505.6	505.9	506.3	506.6	507.0	507.3	507.4	507.5	507.6	507.8	508.0
145°	525.5	525.9	526.1	526.4	526.8	526.9	526.9	526.9	526.9	526.9	527.0
147.5°	541.4	542.0	542.6	543.2	543.7	544.0	543.9	543.8	543.6	543.6	543.6
150°	552.9	553.3	553.8	554.2	554.6	554.8	554.6	554.6	554.5	554.3	554.3
152.5°	562.6	563.0	563.3	563.6	563.9	564.0	563.9	563.7	563.5	563.3	563.5
155°	576.3	576.3	576.4	576.5	576.7	576.5	576.3	575.9	575.6	575.3	575.7
157.5°	587.7	587.6	587.5	587.5	587.4	587.2	586.9	586.5	586.1	585.8	586.4
160°	594.4	594.0	593.7	593.5	593.1	592.9	592.8	592.7	592.6	592.5	593.1
162.5°	600.3	599.9	599.5	599.2	598.8	598.5	598.3	598.3	598.2	598.1	598.7
165°	607.8	607.3	606.8	606.3	605.8	605.5	605.5	605.5	605.5	605.5	606.3
167.5°	613.8	613.3	612.7	612.2	611.6	611.3	611.3	611.2	611.1	611.1	612.0
170°	617.2	616.5	615.9	615.3	614.7	614.4	614.5	614.6	614.7	614.8	615.6
172.5°	619.4	618.7	618.2	617.5	616.9	616.6	616.8	616.9	616.9	617.0	617.9
175°	621.8	621.2	620.5	620.0	619.3	619.1	619.1	619.3	619.4	619.5	620.4
177.5°	622.9	622.3	621.7	621.2	620.6	620.4	620.5	620.7	620.9	621.0	621.7
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8



TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	16.4	16.3	16.2	16.3	16.6	16.8	17.1	17.4
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	11.1	11.7	12.3	12.6	12.7	12.7	12.8	12.8
95°	11.5	12.1	12.7	13.0	13.2	13.3	13.4	13.5
97.5°	12.4	12.5	12.6	12.6	12.7	12.8	12.9	13.0
100°	17.0	15.2	13.5	12.6	12.7	12.8	12.9	13.0
102.5°	60.7	41.7	22.7	13.3	13.4	13.4	13.4	13.4
105°	147.0	147.9	148.8	147.4	143.7	140.0	136.2	132.6
107.5°	181.8	182.3	182.7	183.1	183.5	183.9	184.3	184.7
110°	205.5	205.7	205.9	206.2	206.5	206.8	207.1	207.4





TEST NUMBER: P332994-930

CATALOG NUMBER: SA4XXRDIP-C1195D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	228.4	228.4	228.5	228.9	229.3	229.8	230.1
115°	262.7	262.9	263.1	263.3	263.3	263.3	263.3	263.3
117.5°	297.2	297.2	297.1	297.1	297.0	297.0	296.9	296.9
120°	318.5	318.7	318.9	318.9	318.7	318.5	318.3	318.1
122.5°	339.6	339.7	339.8	339.7	339.6	339.3	339.2	338.9
125°	368.9	369.2	369.6	369.8	369.9	370.0	370.1	370.2
127.5°	398.2	398.1	398.0	397.9	397.9	397.8	397.7	397.6
130°	416.0	416.0	416.2	416.2	416.2	416.2	416.2	416.2
132.5°	433.5	433.6	433.7	433.7	433.6	433.5	433.4	433.3
135°	457.5	457.8	458.0	458.2	458.4	458.6	458.9	459.0
137.5°	480.7	480.9	481.1	481.2	481.2	481.1	481.0	480.9
140°	495.0	495.3	495.6	495.8	495.9	496.0	496.1	496.2
142.5°	508.2	508.4	508.7	508.8	508.8	508.8	508.8	508.9
145°	527.1	527.3	527.3	527.5	527.7	527.9	528.2	528.3
147.5°	543.7	543.8	543.9	544.0	544.1	544.2	544.3	544.4
150°	554.3	554.3	554.3	554.4	554.5	554.6	554.7	554.8
152.5°	563.6	563.8	563.9	564.0	563.9	563.9	563.8	563.8
155°	576.1	576.5	576.9	577.0	576.7	576.3	576.1	575.8
157.5°	586.9	587.4	587.9	587.9	587.4	586.9	586.4	585.8
160°	593.7	594.4	595.0	595.0	594.4	593.7	593.1	592.5
162.5°	599.3	599.9	600.5	600.5	599.8	599.1	598.4	597.7
165°	607.2	608.0	608.9	608.8	607.8	606.9	606.0	605.0
167.5°	612.9	613.8	614.7	614.7	613.7	612.6	611.6	610.6
170°	616.4	617.3	618.2	618.0	617.0	616.0	614.9	613.9
172.5°	618.7	619.5	620.4	620.2	619.1	618.0	616.9	615.7
175°	621.3	622.2	623.2	623.1	621.8	620.5	619.3	618.1
177.5°	622.4	623.1	623.7	623.5	622.6	621.6	620.5	619.5
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8

(END OF REPORT)