

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333002-930

Luminaire Tested: **SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333002-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6290.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333002-930
CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	74	86	80	74	70	70	66	63	62	58	56	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	55	51	48	48	45	42	39
4	77	66	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	59	51	45	66	56	49	43	50	44	40	44	39	36	39	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	32	35	31	28	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.5
10°-20°	445.4	7.1
20°-30°	643.1	10.2
30°-40°	729.0	11.6
40°-50°	704.0	11.2
50°-60°	585.4	9.3
60°-70°	404.2	6.4
70°-80°	204.9	3.3
80°-90°	54.4	0.9
90°-100°	234.4	3.7
100°-110°	487.8	7.8
110°-120°	436.9	6.9
120°-130°	367.5	5.8
130°-140°	306.4	4.9
140°-150°	234.1	3.7
150°-160°	164.6	2.6
160°-170°	96.8	1.5
170°-180°	31.5	0.5
0°-30°	1248.2	19.8
0°-40°	1977.3	31.4
0°-60°	3266.6	51.9
0°-90°	3930.1	62.5
90°-120°	1159.1	18.4
90°-150°	2067.1	32.9
90°-180°	2360.0	37.5
0°-180°	6290.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	5	12	13	13	4
95°	21	66	520	257	156	24
105°	75	108	418	900	897	80
115°	131	165	373	716	861	130
125°	183	217	371	610	687	163
135°	217	259	368	541	615	168
145°	250	287	366	456	502	157
155°	285	308	356	403	420	131
165°	310	320	341	361	367	88
175°	324	324	327	332	330	31
180°	324	324	324	324	324	



TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.1	22.5	21.0	19.3	17.5	16.6	17.0	16.8	16.9	16.9	16.6
90°	0.7	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8
92.5°	7.3	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4
95°	21.0	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3
97.5°	37.7	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2
100°	48.4	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7
102.5°	58.6	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5
105°	74.6	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0
107.5°	92.2	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9
110°	104.0	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9



TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.1	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1
115°	131.3	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2
117.5°	148.1	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6
120°	159.4	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0
122.5°	169.6	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0
125°	183.0	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2
127.5°	194.9	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1
130°	201.5	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6
132.5°	208.1	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5
135°	217.4	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8
137.5°	226.7	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2
140°	233.3	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6
142.5°	240.4	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6
145°	250.5	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3
147.5°	261.9	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6
150°	269.0	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1
152.5°	275.7	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0
155°	284.9	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9
157.5°	294.0	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6
160°	299.6	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0
162.5°	304.8	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9
165°	310.5	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2
167.5°	316.2	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1
170°	318.8	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0
172.5°	321.3	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4
175°	323.8	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3
177.5°	325.0	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	16.4	16.3	16.2	16.2	16.6	17.0	17.0	17.3
90°	11.5	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	125.2	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	472.4	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	697.9	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	768.8	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	765.2	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	714.0	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	641.2	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	597.4	707.6	800.1	870.2	915.4	942.2	953.7	959.4



TEST NUMBER: P333002-930

CATALOG NUMBER: SA4XXRDIP-C1195D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	565.2	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	533.0	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	517.1	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	510.0	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	503.9	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	493.4	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	480.7	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	470.5	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	459.7	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	445.0	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	431.6	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	424.0	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	416.8	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	406.8	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	398.4	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	393.3	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	387.8	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	379.3	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	370.2	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	364.7	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	359.1	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	351.2	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	343.7	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	339.2	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	335.1	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	329.6	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.0	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)