

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332546-940

Luminaire Tested: **SA4XXDIP-C575D590U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332546-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4195.3 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332546-940
CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47																				
2	91	83	77	72	84	77	72	68	67	63	59	57	54	52	48	46	44	40																				
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34																				
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29																				
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26																				
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23																				
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20																				
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	27	23	20	18																				
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16																				
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.9
10°-20°	251.5	6.0
20°-30°	398.8	9.5
30°-40°	443.8	10.6
40°-50°	404.0	9.6
50°-60°	330.1	7.9
60°-70°	235.7	5.6
70°-80°	129.8	3.1
80°-90°	36.9	0.9
90°-100°	187.0	4.5
100°-110°	389.2	9.3
110°-120°	348.6	8.3
120°-130°	293.2	7.0
130°-140°	244.5	5.8
140°-150°	186.8	4.5
150°-160°	131.3	3.1
160°-170°	77.2	1.8
170°-180°	25.1	0.6
0°-30°	731.9	17.4
0°-40°	1175.7	28.0
0°-60°	1909.9	45.5
0°-90°	2312.2	55.1
90°-120°	924.8	22.0
90°-150°	1649.4	39.3
90°-180°	1883.0	44.9
0°-180°	4195.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	11	0	11	0	11	9
95°	124	17	124	17	124	193
105°	716	60	716	60	716	708
115°	687	105	687	105	687	682
125°	548	146	548	146	548	498
135°	490	173	490	173	490	379
145°	400	200	400	200	400	254
155°	335	227	335	227	335	156
165°	292	248	292	248	292	84
175°	264	258	264	258	264	26
180°	259	259	259	259	259	



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	8.2	9.1	9.2	9.4	9.8	10.1	10.3	9.9	10.9	11.2	12.2
90°	10.7	10.7	11.1	10.7	10.2	10.2	9.6	9.2	8.6	9.2	8.1
92.5°	39.1	39.1	40.9	43.6	49.7	59.8	75.2	99.9	134.4	161.3	141.2
95°	124.1	130.7	139.9	155.7	180.6	229.9	298.1	376.9	426.2	414.6	312.8
97.5°	331.7	342.3	357.6	388.3	424.7	477.9	527.6	556.9	535.6	436.7	292.8
100°	466.5	470.6	485.8	516.8	561.1	598.7	623.7	613.5	539.2	408.9	265.6
102.5°	583.6	586.9	603.0	625.4	652.6	668.3	661.1	610.6	508.6	374.4	247.2
105°	715.7	718.7	725.9	730.0	729.0	708.1	657.7	569.7	453.3	333.7	231.5
107.5°	764.7	763.4	758.3	746.7	721.6	676.3	605.3	511.7	408.5	310.9	228.6
110°	765.5	761.0	751.8	730.5	694.4	638.4	564.6	476.6	386.1	303.2	229.4



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	741.5	734.1	721.3	695.4	654.4	598.5	528.8	451.0	373.4	299.5	231.8
115°	687.2	683.1	666.9	636.3	596.2	547.3	487.9	425.3	361.7	297.6	236.6
117.5°	632.2	629.0	612.5	586.9	552.6	511.2	464.4	412.6	356.4	297.0	241.5
120°	601.3	595.7	582.5	560.1	531.0	494.9	454.2	407.0	353.6	297.0	245.2
122.5°	576.8	571.2	560.1	540.9	516.4	484.7	447.7	402.1	350.3	296.7	248.9
125°	548.3	545.3	535.7	520.8	500.5	472.5	437.5	393.7	344.9	296.0	254.3
127.5°	531.6	528.6	520.5	507.4	486.9	460.4	425.3	383.5	337.7	294.9	258.7
130°	521.9	518.9	510.7	498.0	477.2	450.1	415.6	375.4	333.1	294.5	262.0
132.5°	511.0	507.8	500.2	485.8	465.3	438.4	404.6	366.8	329.1	294.1	264.8
135°	490.4	487.3	479.2	464.9	444.6	419.1	388.2	355.1	323.0	293.5	269.1
137.5°	464.9	461.3	454.6	440.5	421.5	398.5	372.4	344.4	317.7	293.4	271.6
140°	446.7	442.6	435.4	424.3	406.4	385.0	362.2	338.2	314.9	293.0	273.7
142.5°	427.0	424.3	417.9	407.5	391.8	373.3	353.7	332.6	312.5	293.0	275.3
145°	400.3	397.8	392.7	384.1	371.3	357.1	341.8	324.5	308.3	291.9	276.3
147.5°	376.7	375.7	371.8	364.4	355.1	343.8	331.6	317.9	304.5	290.2	276.7
150°	363.2	362.7	359.6	353.0	344.9	335.7	325.6	313.9	301.7	288.9	276.7
152.5°	351.0	350.4	348.7	343.2	336.4	328.8	319.4	309.3	298.4	286.9	275.9
155°	335.2	335.2	333.7	329.7	324.5	318.4	310.8	302.6	293.5	283.8	274.6
157.5°	321.4	321.4	320.5	317.4	313.5	308.6	302.3	295.4	288.6	280.7	273.4
160°	312.8	312.8	312.4	309.2	306.2	302.1	296.6	291.0	284.9	278.2	272.2
162.5°	304.7	305.1	304.6	301.6	299.3	295.6	291.2	286.5	281.6	275.8	270.9
165°	292.5	293.0	293.5	291.5	289.4	286.9	283.3	280.3	276.3	272.2	268.6
167.5°	282.9	283.2	283.3	282.0	281.0	279.5	276.6	274.3	271.3	268.5	266.2
170°	276.7	276.7	277.2	276.7	275.7	274.2	272.2	270.6	268.0	266.0	264.5
172.5°	270.6	271.4	272.0	271.4	270.8	269.7	268.5	267.3	265.2	263.6	262.9
175°	263.5	264.5	265.6	264.5	264.5	264.5	263.5	263.0	262.0	260.9	260.9
177.5°	259.3	260.1	260.9	260.6	260.9	260.6	260.6	260.1	259.8	259.3	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	11.9	12.2	11.3	10.3	9.3	8.4	7.8	7.3	7.8	8.4	8.7
90°	7.1	7.1	4.1	4.1	3.6	3.0	1.5	0.5	1.5	3.0	3.6
92.5°	102.7	63.3	37.5	26.8	19.4	13.2	8.5	5.8	8.5	13.2	19.4
95°	191.3	107.8	63.6	42.2	30.1	23.4	18.3	16.8	18.3	23.4	30.1
97.5°	171.9	103.1	69.0	51.1	40.6	34.5	30.1	30.1	30.1	34.5	40.6
100°	161.8	104.2	74.3	58.0	48.3	42.2	38.7	38.7	38.7	42.2	48.3
102.5°	158.9	108.3	81.1	65.7	56.4	50.7	47.6	46.8	47.6	50.7	56.4
105°	160.2	118.0	93.6	78.8	69.7	63.6	61.1	59.5	61.1	63.6	69.7
107.5°	167.7	129.3	106.9	92.4	83.6	77.1	74.5	73.6	74.5	77.1	83.6
110°	173.4	137.9	115.5	101.7	92.6	86.5	83.9	82.9	83.9	86.5	92.6



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	146.0	124.4	110.7	101.6	95.9	92.9	91.8	92.9	95.9	101.6
115°	189.2	158.7	138.4	124.7	114.9	109.9	106.3	104.8	106.3	109.9	114.9
117.5°	199.1	171.0	151.7	137.4	128.4	122.8	119.7	118.2	119.7	122.8	128.4
120°	206.0	179.6	160.2	146.0	137.3	131.7	128.2	127.2	128.2	131.7	137.3
122.5°	212.5	187.7	168.4	154.5	145.1	139.9	136.3	135.3	136.3	139.9	145.1
125°	222.3	198.9	180.6	166.3	156.7	151.1	148.0	146.0	148.0	151.1	156.7
127.5°	230.8	209.3	191.5	177.2	167.1	160.8	157.1	155.4	157.1	160.8	167.1
130°	236.0	216.2	198.9	184.1	174.5	166.8	162.7	160.8	162.7	166.8	174.5
132.5°	241.3	221.9	204.6	190.6	180.2	173.0	167.6	166.0	167.6	173.0	180.2
135°	248.3	229.9	213.1	199.9	189.2	180.6	175.5	173.4	175.5	180.6	189.2
137.5°	253.2	236.0	220.3	207.8	196.6	188.4	182.8	180.9	182.8	188.4	196.6
140°	256.4	240.1	224.8	212.6	202.0	193.3	187.7	186.2	187.7	193.3	202.0
142.5°	258.8	243.8	228.9	217.1	206.8	198.6	193.4	191.9	193.4	198.6	206.8
145°	261.4	247.7	234.5	223.3	213.7	206.5	201.4	199.9	201.4	206.5	213.7
147.5°	263.8	251.8	239.4	229.3	221.2	213.9	209.5	208.9	209.5	213.9	221.2
150°	265.0	253.9	242.6	233.0	225.3	219.3	215.2	214.6	215.2	219.3	225.3
152.5°	265.8	255.5	245.5	236.7	229.8	224.1	220.1	220.0	220.1	224.1	229.8
155°	266.5	257.9	249.2	241.7	236.0	231.0	227.9	227.4	227.9	231.0	236.0
157.5°	266.5	259.7	252.3	246.3	241.4	237.5	234.6	234.6	234.6	237.5	241.4
160°	266.5	260.5	254.3	248.7	244.7	241.1	239.1	239.1	239.1	241.1	244.7
162.5°	266.5	261.3	255.6	251.2	247.5	244.3	242.7	243.2	242.7	244.3	247.5
165°	265.6	261.4	256.9	253.9	251.3	248.7	247.7	247.7	247.7	248.7	251.3
167.5°	264.3	261.4	258.0	255.7	254.2	252.3	251.8	252.3	251.8	252.3	254.2
170°	263.5	260.9	258.4	256.9	255.8	254.3	253.9	254.3	253.9	254.3	255.8
172.5°	262.7	260.6	258.8	257.7	257.1	255.9	255.8	256.4	255.8	255.9	257.1
175°	261.4	259.9	259.0	259.0	258.4	257.9	257.9	258.4	257.9	257.9	258.4
177.5°	260.1	259.3	259.0	259.0	259.0	258.5	259.0	259.3	259.0	258.5	259.0
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	9.7	9.7	11.4	11.9	13.0	14.6	15.1	18.2	19.4	20.9	23.4
90°	4.1	4.1	7.1	7.1	8.1	9.2	8.6	9.2	9.6	10.2	10.2
92.5°	26.8	37.5	63.3	102.7	141.2	161.3	134.4	99.9	75.2	59.8	49.7
95°	42.2	63.6	107.8	191.3	312.8	414.6	426.2	376.9	298.1	229.9	180.6
97.5°	51.1	69.0	103.1	171.9	292.8	436.7	535.6	556.9	527.6	477.9	424.7
100°	58.0	74.3	104.2	161.8	265.6	408.9	539.2	613.5	623.7	598.7	561.1
102.5°	65.7	81.1	108.3	158.9	247.2	374.4	508.6	610.6	661.1	668.3	652.6
105°	78.8	93.6	118.0	160.2	231.5	333.7	453.3	569.7	657.7	708.1	729.0
107.5°	92.4	106.9	129.3	167.7	228.6	310.9	408.5	511.7	605.3	676.3	721.6
110°	101.7	115.5	137.9	173.4	229.4	303.2	386.1	476.6	564.6	638.4	694.4



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.7	124.4	146.0	179.6	231.8	299.5	373.4	451.0	528.8	598.5	654.4
115°	124.7	138.4	158.7	189.2	236.6	297.6	361.7	425.3	487.9	547.3	596.2
117.5°	137.4	151.7	171.0	199.1	241.5	297.0	356.4	412.6	464.4	511.2	552.6
120°	146.0	160.2	179.6	206.0	245.2	297.0	353.6	407.0	454.2	494.9	531.0
122.5°	154.5	168.4	187.7	212.5	248.9	296.7	350.3	402.1	447.7	484.7	516.4
125°	166.3	180.6	198.9	222.3	254.3	296.0	344.9	393.7	437.5	472.5	500.5
127.5°	177.2	191.5	209.3	230.8	258.7	294.9	337.7	383.5	425.3	460.4	486.9
130°	184.1	198.9	216.2	236.0	262.0	294.5	333.1	375.4	415.6	450.1	477.2
132.5°	190.6	204.6	221.9	241.3	264.8	294.1	329.1	366.8	404.6	438.4	465.3
135°	199.9	213.1	229.9	248.3	269.1	293.5	323.0	355.1	388.2	419.1	444.6
137.5°	207.8	220.3	236.0	253.2	271.6	293.4	317.7	344.4	372.4	398.5	421.5
140°	212.6	224.8	240.1	256.4	273.7	293.0	314.9	338.2	362.2	385.0	406.4
142.5°	217.1	228.9	243.8	258.8	275.3	293.0	312.5	332.6	353.7	373.3	391.8
145°	223.3	234.5	247.7	261.4	276.3	291.9	308.3	324.5	341.8	357.1	371.3
147.5°	229.3	239.4	251.8	263.8	276.7	290.2	304.5	317.9	331.6	343.8	355.1
150°	233.0	242.6	253.9	265.0	276.7	288.9	301.7	313.9	325.6	335.7	344.9
152.5°	236.7	245.5	255.5	265.8	275.9	286.9	298.4	309.3	319.4	328.8	336.4
155°	241.7	249.2	257.9	266.5	274.6	283.8	293.5	302.6	310.8	318.4	324.5
157.5°	246.3	252.3	259.7	266.5	273.4	280.7	288.6	295.4	302.3	308.6	313.5
160°	248.7	254.3	260.5	266.5	272.2	278.2	284.9	291.0	296.6	302.1	306.2
162.5°	251.2	255.6	261.3	266.5	270.9	275.8	281.6	286.5	291.2	295.6	299.3
165°	253.9	256.9	261.4	265.6	268.6	272.2	276.3	280.3	283.3	286.9	289.4
167.5°	255.7	258.0	261.4	264.3	266.2	268.5	271.3	274.3	276.6	279.5	281.0
170°	256.9	258.4	260.9	263.5	264.5	266.0	268.0	270.6	272.2	274.2	275.7
172.5°	257.7	258.8	260.6	262.7	262.9	263.6	265.2	267.3	268.5	269.7	270.8
175°	259.0	259.0	259.9	261.4	260.9	260.9	262.0	263.0	263.5	264.5	264.5
177.5°	259.0	259.0	259.3	260.1	259.3	259.3	259.8	260.1	260.6	260.6	260.9
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	24.3	24.7	25.4	26.0	25.4	24.7	24.3	23.4	20.9	19.4	18.2
90°	10.7	11.1	10.7	10.7	10.7	11.1	10.7	10.2	10.2	9.6	9.2
92.5°	43.6	40.9	39.1	39.1	39.1	40.9	43.6	49.7	59.8	75.2	99.9
95°	155.7	139.9	130.7	124.1	130.7	139.9	155.7	180.6	229.9	298.1	376.9
97.5°	388.3	357.6	342.3	331.7	342.3	357.6	388.3	424.7	477.9	527.6	556.9
100°	516.8	485.8	470.6	466.5	470.6	485.8	516.8	561.1	598.7	623.7	613.5
102.5°	625.4	603.0	586.9	583.6	586.9	603.0	625.4	652.6	668.3	661.1	610.6
105°	730.0	725.9	718.7	715.7	718.7	725.9	730.0	729.0	708.1	657.7	569.7
107.5°	746.7	758.3	763.4	764.7	763.4	758.3	746.7	721.6	676.3	605.3	511.7
110°	730.5	751.8	761.0	765.5	761.0	751.8	730.5	694.4	638.4	564.6	476.6



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	695.4	721.3	734.1	741.5	734.1	721.3	695.4	654.4	598.5	528.8	451.0
115°	636.3	666.9	683.1	687.2	683.1	666.9	636.3	596.2	547.3	487.9	425.3
117.5°	586.9	612.5	629.0	632.2	629.0	612.5	586.9	552.6	511.2	464.4	412.6
120°	560.1	582.5	595.7	601.3	595.7	582.5	560.1	531.0	494.9	454.2	407.0
122.5°	540.9	560.1	571.2	576.8	571.2	560.1	540.9	516.4	484.7	447.7	402.1
125°	520.8	535.7	545.3	548.3	545.3	535.7	520.8	500.5	472.5	437.5	393.7
127.5°	507.4	520.5	528.6	531.6	528.6	520.5	507.4	486.9	460.4	425.3	383.5
130°	498.0	510.7	518.9	521.9	518.9	510.7	498.0	477.2	450.1	415.6	375.4
132.5°	485.8	500.2	507.8	511.0	507.8	500.2	485.8	465.3	438.4	404.6	366.8
135°	464.9	479.2	487.3	490.4	487.3	479.2	464.9	444.6	419.1	388.2	355.1
137.5°	440.5	454.6	461.3	464.9	461.3	454.6	440.5	421.5	398.5	372.4	344.4
140°	424.3	435.4	442.6	446.7	442.6	435.4	424.3	406.4	385.0	362.2	338.2
142.5°	407.5	417.9	424.3	427.0	424.3	417.9	407.5	391.8	373.3	353.7	332.6
145°	384.1	392.7	397.8	400.3	397.8	392.7	384.1	371.3	357.1	341.8	324.5
147.5°	364.4	371.8	375.7	376.7	375.7	371.8	364.4	355.1	343.8	331.6	317.9
150°	353.0	359.6	362.7	363.2	362.7	359.6	353.0	344.9	335.7	325.6	313.9
152.5°	343.2	348.7	350.4	351.0	350.4	348.7	343.2	336.4	328.8	319.4	309.3
155°	329.7	333.7	335.2	335.2	335.2	333.7	329.7	324.5	318.4	310.8	302.6
157.5°	317.4	320.5	321.4	321.4	321.4	320.5	317.4	313.5	308.6	302.3	295.4
160°	309.2	312.4	312.8	312.8	312.8	312.4	309.2	306.2	302.1	296.6	291.0
162.5°	301.6	304.6	305.1	304.7	305.1	304.6	301.6	299.3	295.6	291.2	286.5
165°	291.5	293.5	293.0	292.5	293.0	293.5	291.5	289.4	286.9	283.3	280.3
167.5°	282.0	283.3	283.2	282.9	283.2	283.3	282.0	281.0	279.5	276.6	274.3
170°	276.7	277.2	276.7	276.7	276.7	277.2	276.7	275.7	274.2	272.2	270.6
172.5°	271.4	272.0	271.4	270.6	271.4	272.0	271.4	270.8	269.7	268.5	267.3
175°	264.5	265.6	264.5	263.5	264.5	265.6	264.5	264.5	264.5	263.5	263.0
177.5°	260.6	260.9	260.1	259.3	260.1	260.9	260.6	260.9	260.6	260.6	260.1
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940
 CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	15.1	14.6	13.0	11.9	11.4	9.7	9.7	8.7	8.4	7.8	7.3
90°	8.6	9.2	8.1	7.1	7.1	4.1	4.1	3.6	3.0	1.5	0.5
92.5°	134.4	161.3	141.2	102.7	63.3	37.5	26.8	19.4	13.2	8.5	5.8
95°	426.2	414.6	312.8	191.3	107.8	63.6	42.2	30.1	23.4	18.3	16.8
97.5°	535.6	436.7	292.8	171.9	103.1	69.0	51.1	40.6	34.5	30.1	30.1
100°	539.2	408.9	265.6	161.8	104.2	74.3	58.0	48.3	42.2	38.7	38.7
102.5°	508.6	374.4	247.2	158.9	108.3	81.1	65.7	56.4	50.7	47.6	46.8
105°	453.3	333.7	231.5	160.2	118.0	93.6	78.8	69.7	63.6	61.1	59.5
107.5°	408.5	310.9	228.6	167.7	129.3	106.9	92.4	83.6	77.1	74.5	73.6
110°	386.1	303.2	229.4	173.4	137.9	115.5	101.7	92.6	86.5	83.9	82.9



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	373.4	299.5	231.8	179.6	146.0	124.4	110.7	101.6	95.9	92.9	91.8
115°	361.7	297.6	236.6	189.2	158.7	138.4	124.7	114.9	109.9	106.3	104.8
117.5°	356.4	297.0	241.5	199.1	171.0	151.7	137.4	128.4	122.8	119.7	118.2
120°	353.6	297.0	245.2	206.0	179.6	160.2	146.0	137.3	131.7	128.2	127.2
122.5°	350.3	296.7	248.9	212.5	187.7	168.4	154.5	145.1	139.9	136.3	135.3
125°	344.9	296.0	254.3	222.3	198.9	180.6	166.3	156.7	151.1	148.0	146.0
127.5°	337.7	294.9	258.7	230.8	209.3	191.5	177.2	167.1	160.8	157.1	155.4
130°	333.1	294.5	262.0	236.0	216.2	198.9	184.1	174.5	166.8	162.7	160.8
132.5°	329.1	294.1	264.8	241.3	221.9	204.6	190.6	180.2	173.0	167.6	166.0
135°	323.0	293.5	269.1	248.3	229.9	213.1	199.9	189.2	180.6	175.5	173.4
137.5°	317.7	293.4	271.6	253.2	236.0	220.3	207.8	196.6	188.4	182.8	180.9
140°	314.9	293.0	273.7	256.4	240.1	224.8	212.6	202.0	193.3	187.7	186.2
142.5°	312.5	293.0	275.3	258.8	243.8	228.9	217.1	206.8	198.6	193.4	191.9
145°	308.3	291.9	276.3	261.4	247.7	234.5	223.3	213.7	206.5	201.4	199.9
147.5°	304.5	290.2	276.7	263.8	251.8	239.4	229.3	221.2	213.9	209.5	208.9
150°	301.7	288.9	276.7	265.0	253.9	242.6	233.0	225.3	219.3	215.2	214.6
152.5°	298.4	286.9	275.9	265.8	255.5	245.5	236.7	229.8	224.1	220.1	220.0
155°	293.5	283.8	274.6	266.5	257.9	249.2	241.7	236.0	231.0	227.9	227.4
157.5°	288.6	280.7	273.4	266.5	259.7	252.3	246.3	241.4	237.5	234.6	234.6
160°	284.9	278.2	272.2	266.5	260.5	254.3	248.7	244.7	241.1	239.1	239.1
162.5°	281.6	275.8	270.9	266.5	261.3	255.6	251.2	247.5	244.3	242.7	243.2
165°	276.3	272.2	268.6	265.6	261.4	256.9	253.9	251.3	248.7	247.7	247.7
167.5°	271.3	268.5	266.2	264.3	261.4	258.0	255.7	254.2	252.3	251.8	252.3
170°	268.0	266.0	264.5	263.5	260.9	258.4	256.9	255.8	254.3	253.9	254.3
172.5°	265.2	263.6	262.9	262.7	260.6	258.8	257.7	257.1	255.9	255.8	256.4
175°	262.0	260.9	260.9	261.4	259.9	259.0	259.0	258.4	257.9	257.9	258.4
177.5°	259.8	259.3	259.3	260.1	259.3	259.0	259.0	259.0	258.5	259.0	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	7.8	8.4	9.3	10.3	11.3	12.2	11.9	12.2	11.2	10.9	9.9
90°	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6	9.2
92.5°	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4	99.9
95°	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2	376.9
97.5°	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6	556.9
100°	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2	613.5
102.5°	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6	610.6
105°	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3	569.7
107.5°	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5	511.7
110°	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1	476.6



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4	451.0
115°	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7	425.3
117.5°	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4	412.6
120°	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6	407.0
122.5°	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3	402.1
125°	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9	393.7
127.5°	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7	383.5
130°	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1	375.4
132.5°	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1	366.8
135°	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0	355.1
137.5°	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7	344.4
140°	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9	338.2
142.5°	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5	332.6
145°	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3	324.5
147.5°	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5	317.9
150°	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7	313.9
152.5°	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4	309.3
155°	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5	302.6
157.5°	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6	295.4
160°	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9	291.0
162.5°	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6	286.5
165°	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3	280.3
167.5°	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3	274.3
170°	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0	270.6
172.5°	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2	267.3
175°	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0	263.0
177.5°	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8	260.1
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	10.3	10.1	9.8	9.4	9.2	9.1	8.2
90°	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	564.6	638.4	694.4	730.5	751.8	761.0	765.5



TEST NUMBER: P332546-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)