

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332620-940

Luminaire Tested: **SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332620-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6607.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	40
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	39	38	32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	32	26
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	26	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	19	16
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15	12
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12	10
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6838	6838	6838
5°	6859	6683	6702
10°	6817	6573	6568
15°	6756	6446	6411
20°	6664	6307	6259
25°	6560	6151	6092
30°	6448	5995	5919
35°	6321	5835	5768
40°	6219	5684	5610
45°	6067	5543	5475
50°	5939	5383	5333
55°	5808	5231	5164
60°	5601	5036	5013
65°	5376	4829	4824
70°	5101	4592	4605
75°	4723	4331	4407
80°	4295	4081	4213
85°	3763	3857	4101



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	1.2
10°-20°	229.8	3.5
20°-30°	347.5	5.3
30°-40°	420.4	6.4
40°-50°	444.5	6.7
50°-60°	418.3	6.3
60°-70°	347.1	5.3
70°-80°	243.8	3.7
80°-90°	141.8	2.1
90°-100°	170.2	2.6
100°-110°	322.3	4.9
110°-120°	484.9	7.3
120°-130°	608.7	9.2
130°-140°	667.7	10.1
140°-150°	648.4	9.8
150°-160°	543.7	8.2
160°-170°	361.7	5.5
170°-180°	126.7	1.9
0°-30°	657.5	10.0
0°-40°	1077.9	16.3
0°-60°	1940.7	29.4
0°-90°	2673.4	40.5
90°-120°	977.4	14.8
90°-150°	2902.2	43.9
90°-180°	3934.0	59.5
0°-180°	6607.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	847	847	847	847	847	
5°	848	845	838	846	845	80
15°	813	814	811	819	818	229
25°	744	749	752	762	764	342
35°	651	662	672	684	688	407
45°	542	561	578	594	599	419
55°	425	445	473	492	498	378
65°	294	324	357	379	388	291
75°	163	198	238	264	273	174
85°	50	90	133	160	171	54
90°	18	68	117	149	160	14
95°	74	115	161	189	198	79
105°	250	271	309	335	347	266
115°	457	467	494	513	520	451
125°	662	662	683	699	703	590
135°	850	857	863	876	879	658
145°	1032	1035	1036	1040	1041	646
155°	1181	1181	1180	1184	1180	543
165°	1286	1283	1280	1286	1282	362
175°	1338	1332	1331	1338	1331	127
180°	1340	1340	1340	1340	1340	



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	847.0	847.0	847.0	847.0	847.0	847.0	847.0	847.0	847.0	847.0	847.0
2.5°	850.1	849.5	849.0	848.6	848.0	847.1	845.7	844.4	843.0	841.7	842.8
5°	847.9	847.3	846.7	846.1	845.4	844.4	842.8	841.4	839.9	838.5	840.2
7.5°	840.7	840.3	840.0	839.6	839.2	838.4	837.2	836.0	834.7	833.6	835.4
10°	834.6	834.5	834.3	834.0	833.8	833.2	832.1	831.1	830.0	828.9	830.9
12.5°	826.3	826.3	826.3	826.2	826.2	825.8	825.1	824.3	823.6	822.9	824.7
15°	812.9	813.1	813.2	813.5	813.7	813.5	812.9	812.3	811.5	810.9	812.9
17.5°	794.4	795.0	795.7	796.4	797.0	797.2	797.1	797.0	796.8	796.7	798.7
20°	781.6	782.2	782.8	783.5	784.1	784.5	784.7	784.9	785.2	785.3	787.5
22.5°	767.1	767.9	768.7	769.5	770.3	771.0	771.3	771.7	772.0	772.5	774.5
25°	743.6	744.8	746.2	747.4	748.7	749.7	750.3	750.9	751.5	752.2	754.5
27.5°	717.5	719.3	721.1	723.0	724.9	726.3	727.3	728.2	729.2	730.1	732.3
30°	700.0	701.7	703.4	705.1	706.8	708.3	709.8	711.2	712.7	714.2	716.5
32.5°	681.0	683.1	685.1	687.1	689.1	690.9	692.6	694.2	695.9	697.5	700.2
35°	650.7	653.2	655.8	658.3	660.8	663.1	665.2	667.4	669.4	671.5	674.5
37.5°	620.1	623.0	626.0	628.8	631.8	634.5	637.1	639.7	642.4	645.0	648.0
40°	600.4	603.2	605.8	608.6	611.4	614.2	617.2	620.1	623.0	626.0	629.2
42.5°	577.7	580.7	583.8	586.8	590.0	593.2	596.6	600.1	603.6	607.0	610.6
45°	542.5	546.5	550.5	554.6	558.6	562.6	566.6	570.6	574.5	578.5	582.2
47.5°	509.0	513.1	517.2	521.4	525.5	529.9	534.5	539.1	543.8	548.4	552.1
50°	484.6	489.3	493.9	498.6	503.2	507.8	512.5	517.1	521.7	526.4	530.7
52.5°	460.4	465.0	469.7	474.3	478.9	483.9	489.2	494.5	499.9	505.2	509.3
55°	424.9	429.4	433.8	438.2	442.6	448.0	454.3	460.7	467.0	473.3	477.5
57.5°	385.3	390.7	396.3	401.7	407.2	413.0	419.4	425.6	431.9	438.2	443.2
60°	359.4	365.0	370.4	375.9	381.4	387.6	394.6	401.5	408.5	415.4	420.3
62.5°	334.4	340.5	346.4	352.4	358.4	364.9	371.8	378.8	385.8	392.7	397.5
65°	294.0	300.8	307.6	314.2	321.0	328.0	335.1	342.3	349.5	356.6	361.9
67.5°	255.1	262.3	269.5	276.6	283.8	291.2	298.9	306.6	314.2	321.9	327.3
70°	228.5	235.8	242.9	250.1	257.3	264.8	272.9	280.9	288.8	296.9	302.6
72.5°	202.8	210.1	217.5	224.8	232.1	240.0	248.6	257.1	265.6	274.1	279.6
75°	163.2	170.9	178.7	186.5	194.3	202.7	211.5	220.3	229.3	238.1	244.0
77.5°	126.2	134.4	142.7	151.0	159.2	168.0	177.3	186.5	195.8	205.1	211.1
80°	103.3	111.8	120.2	128.7	137.1	146.0	155.2	164.5	173.8	183.1	189.4
82.5°	80.6	89.3	98.2	106.9	115.7	124.8	134.0	143.3	152.6	161.8	168.3
85°	50.3	59.1	67.9	76.9	85.7	94.9	104.3	113.8	123.3	132.8	139.1
87.5°	28.7	37.8	46.9	56.0	65.1	74.5	84.1	93.7	103.3	112.9	119.2
90°	18.3	29.2	40.2	51.2	62.2	73.0	84.0	94.9	105.8	116.7	124.2
92.5°	36.6	47.1	57.6	68.0	78.6	89.0	99.3	109.7	120.0	130.4	137.1
95°	74.5	83.6	92.6	101.6	110.6	120.2	130.5	140.7	151.0	161.2	167.6
97.5°	119.8	127.4	135.1	142.7	150.3	159.3	169.9	180.3	190.7	201.2	207.5
100°	155.5	161.8	168.3	174.7	181.1	189.4	199.7	210.0	220.3	230.6	236.7
102.5°	193.6	198.8	203.9	209.1	214.3	221.9	231.8	241.7	251.6	261.6	267.8
105°	249.9	254.4	258.8	263.2	267.7	274.3	283.0	291.8	300.4	309.2	315.1
107.5°	310.9	314.6	318.3	322.1	325.8	331.4	338.9	346.4	353.9	361.5	367.3
110°	351.5	355.0	358.4	361.8	365.2	370.4	377.6	384.8	391.9	399.0	403.4



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.9	396.5	399.3	402.0	404.7	409.4	416.0	422.6	429.3	435.9	440.4
115°	457.4	459.3	461.2	463.1	464.9	469.0	475.4	481.6	487.9	494.2	498.6
117.5°	518.1	519.4	520.8	522.1	523.4	527.0	533.0	539.0	544.9	550.9	554.5
120°	557.9	559.5	561.1	562.6	564.2	567.7	573.1	578.5	583.9	589.3	592.5
122.5°	600.2	600.7	601.2	601.7	602.2	605.2	610.6	616.1	621.5	627.0	630.4
125°	661.6	661.5	661.2	661.0	660.8	663.3	668.2	673.3	678.3	683.4	686.9
127.5°	718.0	718.5	719.0	719.4	720.0	722.0	725.7	729.4	733.1	736.7	740.0
130°	757.1	757.5	758.0	758.5	758.9	760.9	764.3	767.7	771.0	774.4	777.8
132.5°	797.6	798.0	798.3	798.5	798.8	800.2	802.7	805.3	807.8	810.3	813.4
135°	850.3	851.8	853.1	854.5	855.9	857.3	858.8	860.2	861.7	863.3	866.1
137.5°	908.8	909.3	909.6	910.1	910.5	911.3	912.4	913.5	914.5	915.6	918.1
140°	947.7	948.0	948.2	948.5	948.8	949.0	949.2	949.4	949.6	949.9	952.3
142.5°	982.7	983.0	983.5	983.9	984.3	984.4	984.1	983.7	983.5	983.1	985.5
145°	1031.8	1032.4	1033.1	1033.8	1034.6	1035.1	1035.3	1035.5	1035.7	1036.0	1037.1
147.5°	1080.7	1081.6	1082.4	1083.3	1084.2	1084.6	1084.4	1084.2	1084.1	1083.9	1083.9
150°	1110.4	1111.2	1111.9	1112.6	1113.3	1113.7	1113.7	1113.7	1113.7	1113.7	1113.7
152.5°	1137.9	1138.4	1138.9	1139.4	1140.0	1140.3	1140.5	1140.7	1140.9	1141.0	1141.6
155°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.9	1180.7	1180.4	1180.2	1180.0	1180.9
157.5°	1217.5	1217.1	1216.7	1216.3	1215.8	1215.6	1215.6	1215.5	1215.5	1215.4	1216.1
160°	1239.0	1238.9	1238.6	1238.3	1238.1	1237.9	1237.7	1237.4	1237.2	1237.0	1237.7
162.5°	1258.9	1258.3	1257.8	1257.1	1256.5	1256.2	1255.9	1255.7	1255.4	1255.2	1256.4
165°	1285.7	1285.0	1284.2	1283.6	1282.9	1282.3	1281.8	1281.4	1280.9	1280.5	1281.8
167.5°	1306.2	1305.2	1304.2	1303.2	1302.3	1301.8	1301.9	1301.9	1302.0	1302.0	1303.4
170°	1317.8	1316.6	1315.5	1314.3	1313.1	1312.7	1313.0	1313.1	1313.4	1313.7	1315.0
172.5°	1326.1	1325.1	1324.1	1323.1	1322.2	1321.7	1321.8	1321.9	1321.9	1322.0	1323.5
175°	1337.5	1336.3	1335.2	1334.0	1332.8	1332.1	1331.9	1331.7	1331.5	1331.2	1332.8
177.5°	1341.2	1340.2	1339.3	1338.5	1337.5	1337.0	1337.0	1337.0	1337.0	1337.0	1338.4
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	847.0	847.0	847.0	847.0	847.0	847.0	847.0	847.0
2.5°	844.0	845.3	846.4	846.9	846.8	846.6	846.4	846.2
5°	841.9	843.6	845.2	846.0	845.7	845.5	845.3	845.1
7.5°	837.3	839.2	841.2	842.0	841.8	841.5	841.3	841.2
10°	832.8	834.6	836.6	837.4	837.2	837.0	836.8	836.6
12.5°	826.3	828.1	829.8	830.6	830.6	830.5	830.5	830.5
15°	814.8	816.6	818.5	819.4	819.2	818.9	818.8	818.5
17.5°	800.6	802.5	804.5	805.4	805.2	805.0	804.9	804.7
20°	789.5	791.7	793.8	794.9	794.9	794.9	794.9	794.9
22.5°	776.7	778.7	780.9	782.1	782.5	782.7	783.1	783.5
25°	756.8	759.1	761.4	762.7	762.9	763.1	763.3	763.6
27.5°	734.4	736.6	738.8	739.9	740.2	740.5	740.7	740.9
30°	718.8	721.1	723.4	724.9	725.3	725.7	726.1	726.6
32.5°	702.8	705.5	708.1	709.7	710.1	710.5	711.0	711.4
35°	677.4	680.4	683.3	685.1	685.7	686.3	687.1	687.7
37.5°	650.9	654.0	656.9	658.8	659.4	660.1	660.8	661.5
40°	632.3	635.5	638.6	640.6	641.5	642.3	643.2	644.0
42.5°	614.0	617.5	621.0	623.1	623.8	624.5	625.2	625.8
45°	585.8	589.3	592.9	595.2	596.3	597.4	598.4	599.4
47.5°	555.8	559.5	563.3	565.7	567.0	568.3	569.5	570.8
50°	534.8	539.0	543.2	546.0	547.2	548.6	549.8	551.1
52.5°	513.6	517.8	522.0	524.8	526.0	527.3	528.5	529.9
55°	481.7	486.0	490.2	492.9	494.2	495.4	496.7	497.9
57.5°	448.3	453.3	458.3	461.4	462.5	463.7	464.9	466.1
60°	425.2	430.0	434.8	438.1	439.8	441.5	443.2	444.9
62.5°	402.3	407.2	412.1	415.4	417.1	418.7	420.4	422.0
65°	367.2	372.5	377.7	381.2	382.9	384.6	386.2	387.9
67.5°	332.6	338.0	343.3	346.8	348.5	350.1	351.8	353.4
70°	308.3	314.0	319.7	323.2	324.7	326.2	327.6	329.1
72.5°	285.2	290.7	296.2	299.8	301.4	303.1	304.7	306.4
75°	249.9	255.7	261.7	265.6	267.5	269.4	271.3	273.1
77.5°	217.0	223.0	229.0	233.0	235.1	237.0	239.1	241.1
80°	195.7	202.1	208.4	212.3	214.0	215.7	217.4	219.1
82.5°	174.8	181.3	187.8	192.0	193.8	195.6	197.5	199.4
85°	145.4	151.8	158.1	162.3	164.4	166.5	168.6	170.8
87.5°	125.6	132.1	138.4	142.6	144.5	146.5	148.5	150.3
90°	131.7	139.2	146.7	151.5	153.6	155.8	157.9	160.1
92.5°	143.9	150.7	157.5	161.8	163.8	165.8	167.7	169.7
95°	174.0	180.4	186.8	190.9	192.8	194.7	196.6	198.5
97.5°	213.8	220.3	226.6	230.7	232.5	234.3	236.1	237.9
100°	242.9	249.1	255.2	259.0	260.5	262.0	263.4	264.9
102.5°	273.9	280.1	286.2	290.3	292.1	293.9	295.8	297.6
105°	321.1	327.1	333.0	337.2	339.6	342.0	344.3	346.7
107.5°	373.1	379.0	384.8	388.4	389.9	391.4	392.9	394.3
110°	407.8	412.2	416.6	420.0	422.3	424.7	427.1	429.4



TEST NUMBER: P332620-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	445.1	449.6	454.2	457.4	459.2	461.1	462.9	464.8
115°	503.0	507.4	511.8	514.6	515.9	517.1	518.4	519.6
117.5°	558.0	561.7	565.3	567.7	568.9	570.2	571.4	572.6
120°	595.5	598.5	601.6	604.2	606.4	608.5	610.6	612.8
122.5°	633.8	637.3	640.7	642.7	643.5	644.2	644.9	645.5
125°	690.5	694.0	697.6	699.7	700.5	701.3	702.1	702.9
127.5°	743.4	746.7	750.1	752.2	753.3	754.4	755.5	756.5
130°	781.0	784.3	787.7	789.5	789.9	790.2	790.6	790.9
132.5°	816.6	819.7	823.0	825.0	825.9	826.8	827.7	828.6
135°	869.1	872.0	874.9	876.6	877.2	877.8	878.3	878.9
137.5°	920.6	923.1	925.5	927.4	928.5	929.8	930.9	932.2
140°	954.8	957.3	959.8	961.5	962.3	963.1	964.0	964.8
142.5°	987.8	990.2	992.6	994.2	995.0	995.9	996.7	997.5
145°	1038.0	1039.1	1040.1	1040.7	1040.9	1041.0	1041.2	1041.3
147.5°	1083.8	1083.8	1083.8	1084.0	1084.4	1084.9	1085.3	1085.7
150°	1113.7	1113.7	1113.7	1113.6	1113.3	1113.1	1112.9	1112.7
152.5°	1142.1	1142.7	1143.3	1143.3	1142.6	1142.0	1141.4	1140.9
155°	1181.9	1182.8	1183.7	1183.7	1182.8	1181.9	1180.9	1180.0
157.5°	1216.8	1217.5	1218.2	1218.2	1217.4	1216.6	1215.8	1215.0
160°	1238.3	1239.0	1239.7	1239.5	1238.3	1237.2	1236.1	1234.9
162.5°	1257.7	1258.9	1260.2	1260.3	1259.1	1257.9	1256.8	1255.6
165°	1283.3	1284.6	1286.0	1286.2	1285.3	1284.4	1283.4	1282.5
167.5°	1304.8	1306.2	1307.5	1307.5	1306.1	1304.7	1303.2	1301.8
170°	1316.4	1317.8	1319.2	1319.0	1317.4	1315.8	1314.2	1312.6
172.5°	1325.1	1326.6	1328.2	1328.2	1326.5	1324.9	1323.3	1321.7
175°	1334.4	1336.1	1337.7	1337.7	1336.1	1334.4	1332.8	1331.2
177.5°	1339.6	1341.0	1342.2	1342.1	1340.6	1339.2	1337.7	1336.2
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5

(END OF REPORT)