

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332898-930

Luminaire Tested: **SA4XXRDIP-C575D365U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332898-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3107.1 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332898-930
CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	2.5
10°-20°	217.0	7.0
20°-30°	313.4	10.1
30°-40°	355.3	11.4
40°-50°	343.1	11.0
50°-60°	285.3	9.2
60°-70°	197.0	6.3
70°-80°	99.8	3.2
80°-90°	26.7	0.9
90°-100°	13.2	0.4
100°-110°	84.0	2.7
110°-120°	160.7	5.2
120°-130°	204.0	6.6
130°-140°	218.3	7.0
140°-150°	204.1	6.6
150°-160°	164.6	5.3
160°-170°	106.2	3.4
170°-180°	36.6	1.2
0°-30°	608.3	19.6
0°-40°	963.6	31.0
0°-60°	1591.9	51.2
0°-90°	1915.5	61.6
90°-120°	257.9	8.3
90°-150°	884.3	28.5
90°-180°	1192.0	38.4
0°-180°	3107.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	1	4	6	8	9	2
95°	16	7	6	8	8	20
105°	87	88	90	92	82	91
115°	162	163	162	163	163	159
125°	228	229	228	229	229	203
135°	282	282	283	284	284	217
145°	326	326	326	327	327	203
155°	357	357	356	357	357	165
165°	377	375	375	377	375	106
175°	385	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	11.8	11.1	10.4	9.5	8.8	8.4	8.4	8.4	8.4	8.4	8.3
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	3.7	3.7	3.7	3.8	3.8	4.1	4.6	5.1	5.6	6.1	6.5
95°	15.8	13.7	11.5	9.3	7.2	6.1	6.1	6.2	6.3	6.4	6.7
97.5°	33.7	35.0	36.4	37.7	39.1	36.2	29.0	21.9	14.8	7.6	7.7
100°	47.3	48.4	49.6	50.7	51.9	48.0	39.2	30.3	21.5	12.7	11.6
102.5°	62.5	63.3	64.2	65.0	65.9	65.7	64.6	63.4	62.2	61.1	49.3
105°	86.7	87.1	87.5	87.9	88.3	88.6	88.9	89.3	89.6	89.9	90.5
107.5°	109.3	109.4	109.7	109.8	110.1	110.3	110.8	111.2	111.6	112.1	112.3
110°	124.5	124.7	124.8	125.1	125.2	125.6	125.9	126.3	126.7	127.1	127.2



TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.3	139.6	139.9	140.2	140.6	140.9	141.0	141.2	141.4	141.6	141.5
115°	161.9	162.2	162.3	162.5	162.7	162.7	162.7	162.7	162.6	162.5	162.7
117.5°	182.4	182.6	182.9	183.2	183.4	183.6	183.8	183.9	184.0	184.2	184.2
120°	196.2	196.5	196.7	197.0	197.2	197.3	197.3	197.2	197.1	197.1	197.2
122.5°	209.1	209.3	209.5	209.6	209.8	209.9	209.9	210.0	210.1	210.3	210.3
125°	227.6	227.9	228.1	228.4	228.7	228.7	228.6	228.4	228.4	228.2	228.4
127.5°	245.2	245.2	245.2	245.3	245.4	245.6	245.9	246.1	246.5	246.8	246.7
130°	256.4	256.5	256.6	256.7	256.7	256.8	257.0	257.2	257.4	257.6	257.6
132.5°	266.8	266.9	267.0	267.2	267.3	267.4	267.7	267.9	268.2	268.4	268.5
135°	282.3	282.3	282.3	282.2	282.1	282.2	282.5	282.7	283.0	283.2	283.4
137.5°	296.1	296.2	296.2	296.2	296.3	296.4	296.7	296.9	297.3	297.5	297.7
140°	305.2	305.2	305.4	305.5	305.7	305.7	305.9	306.1	306.1	306.3	306.5
142.5°	313.2	313.4	313.6	313.9	314.1	314.3	314.4	314.5	314.5	314.6	314.7
145°	325.6	325.8	326.0	326.2	326.4	326.4	326.4	326.4	326.4	326.4	326.5
147.5°	335.4	335.8	336.1	336.6	336.9	337.0	337.0	336.9	336.8	336.8	336.8
150°	342.6	342.8	343.1	343.4	343.6	343.7	343.6	343.6	343.5	343.5	343.5
152.5°	348.6	348.8	349.0	349.2	349.4	349.4	349.4	349.2	349.1	349.0	349.1
155°	357.0	357.1	357.1	357.2	357.3	357.2	357.0	356.8	356.6	356.4	356.7
157.5°	364.1	364.0	364.0	363.9	363.9	363.8	363.6	363.4	363.1	363.0	363.3
160°	368.3	368.0	367.9	367.7	367.5	367.4	367.3	367.2	367.1	367.0	367.5
162.5°	371.9	371.7	371.5	371.2	371.0	370.8	370.7	370.6	370.6	370.6	371.0
165°	376.6	376.3	375.9	375.6	375.3	375.1	375.1	375.1	375.1	375.1	375.7
167.5°	380.3	379.9	379.6	379.3	379.0	378.8	378.7	378.7	378.6	378.6	379.2
170°	382.4	382.0	381.6	381.2	380.8	380.7	380.7	380.8	380.8	380.9	381.4
172.5°	383.8	383.4	382.9	382.6	382.2	382.0	382.1	382.2	382.2	382.3	382.8
175°	385.2	384.8	384.5	384.1	383.7	383.5	383.6	383.7	383.8	383.8	384.4
177.5°	386.0	385.6	385.2	384.8	384.5	384.3	384.5	384.6	384.7	384.7	385.2
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2



TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	8.3	8.2	8.2	8.3	8.4	8.6	8.7	8.8
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	6.8	7.3	7.7	7.8	7.9	7.9	7.9	8.0
95°	7.1	7.5	7.9	8.1	8.2	8.2	8.3	8.3
97.5°	7.7	7.7	7.7	7.8	7.9	7.9	8.0	8.1
100°	10.5	9.4	8.3	7.8	7.9	7.9	8.0	8.1
102.5°	37.6	25.8	14.1	8.2	8.2	8.2	8.3	8.3
105°	91.1	91.6	92.2	91.3	89.0	86.7	84.4	82.1
107.5°	112.7	112.9	113.2	113.5	113.7	114.0	114.2	114.5
110°	127.3	127.4	127.6	127.8	127.9	128.2	128.3	128.5



TEST NUMBER: P332898-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	141.5	141.5	141.5	141.6	141.9	142.1	142.4	142.6
115°	162.7	162.9	163.1	163.1	163.1	163.1	163.1	163.1
117.5°	184.1	184.1	184.1	184.0	184.0	184.0	184.0	183.9
120°	197.3	197.5	197.6	197.6	197.5	197.3	197.2	197.1
122.5°	210.3	210.4	210.5	210.5	210.3	210.3	210.1	210.0
125°	228.6	228.8	228.9	229.1	229.2	229.3	229.3	229.3
127.5°	246.7	246.6	246.6	246.5	246.5	246.5	246.4	246.4
130°	257.7	257.8	257.9	257.9	257.9	257.9	257.9	257.9
132.5°	268.6	268.6	268.7	268.7	268.6	268.6	268.6	268.5
135°	283.5	283.6	283.7	283.9	284.0	284.1	284.3	284.4
137.5°	297.8	298.0	298.1	298.2	298.1	298.1	298.0	298.0
140°	306.6	306.9	307.0	307.2	307.3	307.3	307.4	307.4
142.5°	314.9	315.0	315.1	315.2	315.3	315.3	315.3	315.3
145°	326.6	326.7	326.7	326.8	326.9	327.1	327.2	327.3
147.5°	336.9	337.0	337.0	337.0	337.1	337.1	337.2	337.3
150°	343.5	343.5	343.5	343.5	343.6	343.6	343.6	343.7
152.5°	349.2	349.3	349.4	349.4	349.4	349.4	349.4	349.3
155°	356.9	357.2	357.4	357.5	357.3	357.1	356.9	356.7
157.5°	363.6	363.9	364.3	364.3	363.9	363.6	363.3	363.0
160°	367.9	368.3	368.6	368.6	368.3	367.9	367.5	367.0
162.5°	371.3	371.7	372.1	372.0	371.6	371.2	370.7	370.3
165°	376.2	376.7	377.2	377.2	376.6	376.0	375.4	374.9
167.5°	379.8	380.3	380.8	380.8	380.2	379.5	378.9	378.3
170°	382.0	382.5	382.9	382.9	382.3	381.6	381.0	380.3
172.5°	383.4	383.8	384.3	384.3	383.6	382.9	382.2	381.5
175°	385.0	385.6	386.1	386.0	385.2	384.5	383.7	382.9
177.5°	385.6	386.0	386.5	386.3	385.7	385.1	384.5	383.8
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2

(END OF REPORT)