

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332899-930

Luminaire Tested: **SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332899-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2949.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332899-930
CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	58	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	2.6
10°-20°	217.0	7.4
20°-30°	313.4	10.6
30°-40°	355.3	12.0
40°-50°	343.1	11.6
50°-60°	285.3	9.7
60°-70°	197.0	6.7
70°-80°	99.8	3.4
80°-90°	26.7	0.9
90°-100°	24.6	0.8
100°-110°	72.8	2.5
110°-120°	123.5	4.2
120°-130°	162.9	5.5
130°-140°	182.9	6.2
140°-150°	179.8	6.1
150°-160°	151.2	5.1
160°-170°	100.6	3.4
170°-180°	35.2	1.2
0°-30°	608.3	20.6
0°-40°	963.6	32.7
0°-60°	1591.9	54.0
0°-90°	1915.5	65.0
90°-120°	220.9	7.5
90°-150°	746.5	25.3
90°-180°	1034.0	35.1
0°-180°	2949.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	1	4	6	8	9	3
95°	17	20	22	23	23	19
105°	67	67	69	69	70	71
115°	126	126	125	125	124	124
125°	183	183	183	182	182	163
135°	236	238	238	237	236	182
145°	287	288	288	288	287	179
155°	328	328	328	329	328	151
165°	358	357	356	358	357	101
175°	372	371	370	372	370	35
180°	372	372	372	372	372	



TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	11.8	11.1	10.4	9.5	8.8	8.4	8.4	8.4	8.4	8.4	8.3
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	6.2	7.0	7.7	8.6	9.4	9.9	10.4	10.7	11.1	11.4	11.7
95°	17.3	17.9	18.4	19.0	19.6	20.1	20.5	21.0	21.4	21.9	22.1
97.5°	30.2	30.7	31.1	31.6	32.0	32.5	33.0	33.6	34.1	34.7	34.9
100°	40.4	40.6	40.8	41.1	41.3	41.7	42.3	43.0	43.5	44.1	44.2
102.5°	51.0	51.0	51.1	51.3	51.4	51.7	52.2	52.7	53.2	53.7	54.0
105°	67.1	67.2	67.3	67.3	67.3	67.5	67.8	68.1	68.3	68.6	68.7
107.5°	84.1	84.2	84.3	84.4	84.5	84.5	84.5	84.5	84.6	84.6	84.8
110°	95.6	95.8	95.9	96.0	96.1	96.2	96.1	96.0	96.0	96.0	95.8



TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.6	107.6	107.7	107.7	107.7	107.7	107.5	107.5	107.4	107.2	107.2
115°	125.6	125.6	125.6	125.6	125.6	125.6	125.4	125.3	125.1	125.1	125.0
117.5°	142.5	142.6	142.7	142.7	142.8	142.8	142.7	142.6	142.4	142.4	142.2
120°	153.8	154.1	154.3	154.6	154.9	154.9	154.7	154.5	154.3	154.2	153.8
122.5°	165.6	165.7	165.8	165.9	166.0	166.0	165.9	165.8	165.8	165.7	165.4
125°	183.0	183.0	183.0	183.0	183.0	182.9	182.9	182.8	182.7	182.6	182.5
127.5°	198.7	198.9	199.1	199.3	199.4	199.5	199.4	199.3	199.2	199.1	198.9
130°	209.8	209.9	210.1	210.3	210.5	210.6	210.6	210.6	210.6	210.6	210.5
132.5°	221.0	221.2	221.3	221.4	221.6	221.6	221.6	221.5	221.5	221.4	221.3
135°	235.9	236.4	236.7	237.1	237.5	237.7	237.7	237.7	237.7	237.7	237.6
137.5°	252.2	252.4	252.6	252.7	252.9	253.1	253.2	253.2	253.4	253.5	253.3
140°	263.0	263.2	263.3	263.4	263.6	263.6	263.6	263.6	263.6	263.6	263.6
142.5°	273.0	273.0	273.2	273.3	273.5	273.5	273.5	273.4	273.4	273.3	273.3
145°	286.7	286.9	287.1	287.4	287.7	287.9	287.9	288.0	288.0	288.1	288.0
147.5°	300.3	300.6	300.8	301.2	301.5	301.6	301.6	301.5	301.5	301.4	301.3
150°	308.6	308.8	309.1	309.3	309.6	309.7	309.7	309.7	309.7	309.7	309.7
152.5°	316.4	316.6	316.7	316.8	317.0	317.1	317.2	317.2	317.2	317.3	317.5
155°	328.4	328.4	328.4	328.4	328.4	328.4	328.3	328.2	328.2	328.2	328.4
157.5°	338.6	338.4	338.3	338.3	338.1	338.0	338.0	338.0	338.0	338.0	338.2
160°	344.5	344.5	344.5	344.4	344.3	344.2	344.2	344.1	344.1	344.0	344.2
162.5°	350.1	349.9	349.8	349.6	349.4	349.4	349.3	349.2	349.1	349.0	349.4
165°	357.5	357.3	357.2	356.9	356.8	356.6	356.4	356.4	356.2	356.1	356.4
167.5°	363.2	363.0	362.7	362.4	362.2	362.0	362.1	362.1	362.1	362.1	362.5
170°	366.5	366.2	365.8	365.5	365.2	365.1	365.1	365.2	365.3	365.3	365.7
172.5°	368.8	368.5	368.2	367.9	367.7	367.5	367.5	367.6	367.6	367.6	368.0
175°	371.9	371.6	371.3	371.0	370.6	370.5	370.4	370.3	370.3	370.2	370.6
177.5°	373.0	372.8	372.4	372.2	371.9	371.9	371.9	371.9	371.9	371.9	372.2
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5



TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	8.3	8.2	8.2	8.3	8.4	8.6	8.7	8.8
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.9	12.1	12.3	12.5	12.6	12.6	12.7	12.8
95°	22.3	22.5	22.7	22.7	22.7	22.7	22.7	22.7
97.5°	35.1	35.3	35.5	35.6	35.6	35.6	35.6	35.6
100°	44.4	44.4	44.6	44.7	44.7	44.7	44.7	44.7
102.5°	54.1	54.3	54.5	54.6	54.6	54.7	54.7	54.8
105°	69.0	69.1	69.3	69.5	69.7	70.0	70.1	70.3
107.5°	85.0	85.2	85.4	85.4	85.4	85.4	85.4	85.4
110°	95.7	95.6	95.4	95.5	95.6	95.9	96.0	96.2



TEST NUMBER: P332899-930

CATALOG NUMBER: SA4XXRDIP-C575D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	107.2	107.1	107.1	107.1	107.2	107.2	107.2	107.3
115°	124.9	124.8	124.7	124.7	124.7	124.6	124.5	124.5
117.5°	141.9	141.7	141.5	141.4	141.2	141.0	141.0	140.8
120°	153.5	153.2	152.9	152.8	152.9	153.0	153.1	153.3
122.5°	165.3	165.0	164.8	164.5	164.4	164.1	163.9	163.6
125°	182.4	182.3	182.1	182.0	181.9	181.7	181.6	181.5
127.5°	198.9	198.7	198.5	198.4	198.4	198.3	198.1	198.0
130°	210.3	210.2	210.1	209.9	209.6	209.4	209.1	208.9
132.5°	221.2	221.0	220.9	220.8	220.7	220.6	220.5	220.4
135°	237.4	237.3	237.2	237.0	236.8	236.6	236.4	236.3
137.5°	253.2	253.0	252.8	252.7	252.7	252.8	252.8	252.9
140°	263.5	263.4	263.3	263.3	263.3	263.2	263.1	263.0
142.5°	273.3	273.3	273.2	273.2	273.2	273.2	273.2	273.2
145°	288.0	287.9	287.9	287.7	287.6	287.3	287.1	287.0
147.5°	301.3	301.3	301.2	301.2	301.1	301.0	300.9	300.9
150°	309.7	309.7	309.7	309.7	309.7	309.6	309.5	309.4
152.5°	317.6	317.8	318.0	317.9	317.7	317.6	317.4	317.2
155°	328.6	328.9	329.1	329.1	328.9	328.6	328.4	328.2
157.5°	338.3	338.6	338.8	338.8	338.5	338.3	338.1	337.9
160°	344.4	344.5	344.8	344.7	344.4	344.1	343.7	343.4
162.5°	349.8	350.1	350.4	350.4	350.2	349.8	349.5	349.2
165°	356.9	357.3	357.6	357.7	357.4	357.2	356.9	356.7
167.5°	362.9	363.2	363.6	363.6	363.2	362.8	362.4	362.0
170°	366.1	366.5	366.9	366.8	366.4	365.9	365.5	365.0
172.5°	368.5	368.9	369.3	369.3	368.9	368.4	368.0	367.5
175°	371.1	371.5	372.0	372.0	371.5	371.1	370.6	370.2
177.5°	372.5	372.9	373.2	373.2	372.8	372.4	372.0	371.6
180°	372.5	372.5	372.5	372.5	372.5	372.5	372.5	372.5

(END OF REPORT)