

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332910-930

Luminaire Tested: **SA4XXRDIP-C575D810U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332910-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4553.2 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.7
10°-20°	217.0	4.8
20°-30°	313.4	6.9
30°-40°	355.3	7.8
40°-50°	343.1	7.5
50°-60°	285.3	6.3
60°-70°	197.0	4.3
70°-80°	99.8	2.2
80°-90°	28.1	0.6
90°-100°	29.1	0.6
100°-110°	185.9	4.1
110°-120°	355.6	7.8
120°-130°	451.4	9.9
130°-140°	482.9	10.6
140°-150°	451.6	9.9
150°-160°	364.2	8.0
160°-170°	234.9	5.2
170°-180°	81.0	1.8
0°-30°	608.3	13.4
0°-40°	963.6	21.2
0°-60°	1591.9	35.0
0°-90°	1916.8	42.1
90°-120°	570.6	12.5
90°-150°	1956.4	43.0
90°-180°	2636.0	57.9
0°-180°	4553.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	2	9	14	18	19	3
95°	35	15	14	18	18	45
105°	192	196	199	203	182	201
115°	358	360	360	361	361	352
125°	504	506	505	507	507	449
135°	625	624	627	628	629	481
145°	720	722	722	723	724	450
155°	790	790	789	791	789	364
165°	833	830	830	834	829	235
175°	852	849	849	854	847	81
180°	852	852	852	852	852	



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.1	11.5	10.8	10.3	9.7	9.5	9.5	9.7	9.8	9.9	9.9
90°	1.9	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8
92.5°	8.1	8.2	8.2	8.3	8.4	9.0	10.1	11.3	12.4	13.5	14.3
95°	35.1	30.2	25.4	20.6	15.8	13.5	13.6	13.8	13.9	14.0	14.8
97.5°	74.4	77.5	80.5	83.5	86.5	80.1	64.2	48.4	32.6	16.8	16.9
100°	104.5	107.1	109.7	112.2	114.7	106.2	86.7	67.2	47.6	28.0	25.6
102.5°	138.2	140.1	141.9	143.8	145.7	145.4	142.8	140.2	137.7	135.2	109.2
105°	191.8	192.7	193.6	194.4	195.3	196.1	196.7	197.5	198.2	198.9	200.2
107.5°	241.7	242.1	242.6	243.0	243.4	244.1	245.1	246.1	247.0	248.0	248.6
110°	275.4	275.8	276.2	276.6	277.1	277.7	278.6	279.4	280.3	281.1	281.4



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	308.8	309.6	310.3	311.1	311.7	312.1	312.4	312.8	313.2	313.2
115°	358.2	358.7	359.1	359.5	360.0	360.1	360.0	359.8	359.7	359.5	359.8
117.5°	403.5	404.1	404.6	405.2	405.8	406.3	406.5	406.8	407.2	407.5	407.4
120°	434.1	434.7	435.3	435.9	436.3	436.6	436.4	436.3	436.2	436.0	436.3
122.5°	462.7	463.0	463.3	463.7	464.1	464.3	464.5	464.7	464.9	465.1	465.3
125°	503.6	504.2	504.8	505.3	505.9	506.0	505.7	505.5	505.2	504.9	505.3
127.5°	542.3	542.5	542.7	542.8	542.9	543.3	544.0	544.6	545.3	545.9	545.8
130°	567.4	567.5	567.6	567.8	567.9	568.2	568.6	569.1	569.5	569.9	570.1
132.5°	590.3	590.5	590.8	591.1	591.3	591.7	592.2	592.8	593.3	593.9	594.0
135°	624.8	624.6	624.4	624.3	624.2	624.4	624.9	625.5	626.1	626.6	626.9
137.5°	655.2	655.3	655.3	655.3	655.4	655.7	656.4	657.0	657.6	658.3	658.6
140°	675.1	675.4	675.6	676.0	676.2	676.5	676.8	677.1	677.4	677.6	678.1
142.5°	692.9	693.4	694.0	694.5	695.0	695.3	695.5	695.7	695.9	696.0	696.3
145°	720.3	720.8	721.2	721.6	722.0	722.3	722.3	722.3	722.3	722.3	722.4
147.5°	742.2	743.0	743.7	744.5	745.3	745.7	745.5	745.3	745.2	745.1	745.2
150°	758.0	758.6	759.1	759.7	760.2	760.4	760.3	760.2	760.0	759.9	759.9
152.5°	771.2	771.7	772.1	772.6	773.1	773.1	772.9	772.7	772.3	772.1	772.3
155°	789.9	789.9	790.1	790.3	790.4	790.3	789.9	789.4	789.0	788.6	789.1
157.5°	805.5	805.4	805.4	805.3	805.2	804.9	804.4	804.0	803.5	803.0	803.7
160°	814.7	814.2	813.8	813.4	813.0	812.7	812.6	812.4	812.3	812.1	813.0
162.5°	822.9	822.3	821.7	821.3	820.7	820.4	820.2	820.1	819.9	819.8	820.7
165°	833.2	832.5	831.8	831.0	830.4	830.0	830.0	830.0	830.0	830.0	831.1
167.5°	841.3	840.6	839.8	839.1	838.4	838.0	837.9	837.8	837.7	837.6	838.9
170°	846.0	845.1	844.2	843.3	842.5	842.2	842.3	842.4	842.6	842.8	843.8
172.5°	849.0	848.2	847.3	846.4	845.6	845.2	845.4	845.5	845.6	845.8	846.9
175°	852.3	851.4	850.6	849.8	848.9	848.6	848.7	848.8	849.0	849.1	850.4
177.5°	853.9	853.0	852.2	851.4	850.7	850.4	850.6	850.8	851.1	851.3	852.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	10.0	10.1	10.1	10.3	10.4	10.6	10.8	10.9
90°	15.7	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	15.2	16.1	16.9	17.4	17.4	17.4	17.5	17.6
95°	15.7	16.6	17.4	17.9	18.1	18.2	18.3	18.5
97.5°	17.0	17.1	17.2	17.3	17.4	17.5	17.7	17.9
100°	23.2	20.8	18.4	17.3	17.4	17.5	17.7	17.9
102.5°	83.2	57.2	31.2	18.3	18.3	18.3	18.3	18.3
105°	201.5	202.7	204.0	202.1	197.0	191.8	186.8	181.6
107.5°	249.2	249.8	250.5	251.0	251.6	252.1	252.7	253.2
110°	281.7	282.0	282.3	282.6	283.1	283.5	283.9	284.3



TEST NUMBER: P332910-930

CATALOG NUMBER: SA4XXRDIP-C575D810U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.2	313.1	313.0	313.2	313.8	314.4	314.9	315.4
115°	360.1	360.4	360.7	360.9	360.9	360.9	360.9	360.9
117.5°	407.3	407.3	407.2	407.2	407.2	407.1	407.0	407.0
120°	436.6	436.9	437.2	437.2	436.9	436.6	436.3	436.0
122.5°	465.5	465.6	465.8	465.7	465.5	465.1	464.9	464.6
125°	505.7	506.1	506.5	506.9	507.0	507.1	507.3	507.4
127.5°	545.8	545.7	545.6	545.5	545.4	545.3	545.2	545.0
130°	570.2	570.3	570.5	570.5	570.5	570.5	570.5	570.5
132.5°	594.2	594.3	594.4	594.4	594.4	594.2	594.1	594.0
135°	627.2	627.5	627.8	628.0	628.4	628.6	628.9	629.2
137.5°	658.8	659.2	659.5	659.6	659.5	659.4	659.3	659.3
140°	678.5	678.9	679.3	679.6	679.8	679.9	680.0	680.2
142.5°	696.6	696.9	697.2	697.4	697.4	697.5	697.5	697.5
145°	722.5	722.7	722.8	723.0	723.3	723.6	723.9	724.1
147.5°	745.3	745.4	745.5	745.7	745.8	745.9	746.1	746.2
150°	759.9	759.9	759.9	759.9	760.1	760.2	760.3	760.5
152.5°	772.6	772.8	773.0	773.1	773.0	772.9	772.8	772.7
155°	789.7	790.3	790.8	790.9	790.4	790.0	789.6	789.2
157.5°	804.5	805.2	805.9	805.9	805.2	804.5	803.7	803.0
160°	813.8	814.7	815.5	815.5	814.7	813.8	813.0	812.1
162.5°	821.5	822.3	823.2	823.1	822.1	821.2	820.3	819.3
165°	832.3	833.4	834.5	834.5	833.2	831.9	830.6	829.3
167.5°	840.2	841.4	842.6	842.5	841.1	839.7	838.3	836.9
170°	845.0	846.1	847.3	847.1	845.7	844.3	842.9	841.5
172.5°	848.1	849.2	850.4	850.1	848.6	847.1	845.5	844.0
175°	851.7	853.0	854.2	854.0	852.3	850.6	848.9	847.2
177.5°	853.1	854.0	854.9	854.7	853.3	852.0	850.6	849.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3

(END OF REPORT)