

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332600-940

Luminaire Tested: **SA4XXDIP-C795D810U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332600-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5741.7 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332600-940
CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	88	92	88	85	82	76	73	71	65	63	61	54	53	52	47				
2	90	83	77	72	84	77	72	68	67	63	59	57	54	52	48	46	44	40				
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34				
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29				
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26				
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	31	28	25	23				
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20				
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18				
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16				
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9243	9243	9243	9243
5°	10884	9266	8178	9266
10°	13032	9225	7363	9225
15°	15419	9132	6761	9132
20°	17169	9037	6225	9037
25°	17446	8897	5855	8897
30°	14845	8763	5738	8763
35°	11413	8544	5740	8544
40°	8897	8286	5848	8286
45°	7418	7900	5946	7900
50°	6528	7428	6148	7428
55°	5980	6861	6394	6861
60°	5604	6355	6692	6355
65°	5217	5788	6940	5788
70°	4770	5228	7098	5228
75°	4261	4601	7012	4601
80°	3575	3770	6792	3770
85°	2631	2723	6502	2723



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	1.9
10°-20°	343.8	6.0
20°-30°	545.1	9.5
30°-40°	606.7	10.6
40°-50°	552.2	9.6
50°-60°	451.3	7.9
60°-70°	322.2	5.6
70°-80°	177.4	3.1
80°-90°	50.4	0.9
90°-100°	256.3	4.5
100°-110°	533.5	9.3
110°-120°	477.9	8.3
120°-130°	402.0	7.0
130°-140°	335.1	5.8
140°-150°	256.1	4.5
150°-160°	180.0	3.1
160°-170°	105.9	1.8
170°-180°	34.4	0.6
0°-30°	1000.4	17.4
0°-40°	1607.1	28.0
0°-60°	2610.6	45.5
0°-90°	3160.6	55.0
90°-120°	1267.7	22.1
90°-150°	2260.9	39.4
90°-180°	2581.0	45.0
0°-180°	5741.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1145	1145	1145	1145	1145	
5°	1343	1143	1009	1143	1343	137
15°	1845	1093	809	1093	1845	521
25°	1959	999	657	999	1959	863
35°	1158	867	582	867	1158	735
45°	650	692	521	692	650	512
55°	425	488	454	488	425	384
65°	273	303	363	303	273	270
75°	137	148	225	148	137	145
85°	28	29	70	29	28	35
90°	15	1	15	1	15	13
95°	170	23	170	23	170	264
105°	981	82	981	82	981	970
115°	942	144	942	144	942	935
125°	752	200	752	200	752	683
135°	672	238	672	238	672	519
145°	549	274	549	274	549	348
155°	460	312	460	312	460	214
165°	401	340	401	340	401	115
175°	361	354	361	354	361	35
180°	355	355	355	355	355	



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1218.4	1218.1	1214.2	1213.5	1210.9	1207.5	1206.7	1200.6	1188.5	1182.8	1181.2
5°	1343.1	1352.5	1340.2	1337.8	1336.4	1320.8	1312.7	1303.2	1281.4	1268.6	1258.6
7.5°	1491.8	1492.9	1487.6	1483.2	1471.1	1457.4	1437.0	1415.1	1389.2	1362.1	1341.8
10°	1589.7	1593.5	1587.3	1586.4	1562.2	1547.0	1516.6	1491.0	1461.6	1428.9	1399.0
12.5°	1692.9	1687.6	1684.4	1664.1	1659.7	1632.0	1596.7	1570.3	1525.0	1487.4	1447.6
15°	1844.9	1834.4	1827.7	1799.7	1786.0	1747.6	1710.1	1681.2	1621.9	1565.5	1522.8
17.5°	1933.9	1944.4	1929.0	1917.5	1882.0	1855.0	1816.8	1756.0	1709.7	1639.6	1585.7
20°	1998.5	1999.4	1990.9	1979.1	1951.1	1916.9	1875.2	1808.7	1753.3	1683.6	1609.6
22.5°	2015.9	2016.2	2012.5	2001.4	1980.2	1952.6	1910.5	1855.0	1787.8	1712.0	1638.1
25°	1958.6	1956.8	1961.1	1973.4	1965.2	1956.8	1932.5	1891.3	1828.7	1748.6	1668.8
27.5°	1745.8	1758.9	1783.0	1813.3	1842.5	1864.8	1871.1	1862.6	1823.8	1757.9	1674.5
30°	1592.5	1608.6	1626.7	1657.0	1715.8	1749.5	1786.5	1814.5	1798.8	1746.1	1668.4
32.5°	1424.1	1428.1	1454.8	1489.3	1543.2	1608.0	1666.6	1723.4	1742.3	1714.7	1649.8
35°	1158.1	1164.8	1193.6	1227.8	1293.8	1373.0	1461.2	1539.9	1604.8	1630.9	1597.8
37.5°	945.0	964.1	984.5	1021.3	1079.3	1150.6	1242.2	1344.1	1440.9	1505.8	1516.8
40°	844.2	856.0	870.8	898.7	948.0	1018.2	1096.9	1213.6	1316.5	1409.4	1439.8
42.5°	764.5	771.4	780.4	805.7	843.3	913.1	985.0	1087.6	1191.0	1302.1	1352.9
45°	649.7	656.8	672.0	686.7	715.2	763.6	830.4	914.8	1018.7	1125.9	1219.8
47.5°	566.9	571.4	580.4	596.1	620.3	652.2	706.6	777.1	873.3	977.4	1077.5
50°	519.8	523.5	530.7	544.9	563.4	591.8	636.4	702.4	777.8	882.6	980.7
52.5°	482.6	484.1	489.4	499.0	513.7	537.6	574.2	628.7	698.8	792.3	890.1
55°	424.9	426.9	431.6	438.7	451.5	466.6	494.6	535.4	596.6	677.7	762.6
57.5°	377.5	378.8	382.8	385.6	396.1	408.4	430.0	459.1	505.4	574.2	650.0
60°	347.1	346.2	351.0	353.3	360.4	370.9	387.4	415.4	455.8	511.2	580.9
62.5°	317.5	316.2	320.2	323.3	327.4	336.4	349.9	371.8	404.6	454.7	515.0
65°	273.1	271.3	273.7	277.4	281.2	286.0	296.0	315.4	341.4	377.5	423.5
67.5°	228.5	230.6	231.0	232.8	235.1	241.5	248.3	262.1	280.4	309.3	348.3
70°	202.1	202.5	204.4	204.4	205.8	211.5	217.2	225.2	243.3	269.8	301.6
72.5°	175.5	177.5	176.7	178.3	179.2	183.1	187.3	194.9	210.3	230.0	256.8
75°	136.6	138.0	138.0	138.5	139.9	141.3	144.6	150.3	161.2	175.9	194.5
77.5°	99.6	99.8	100.4	102.2	102.2	104.4	106.9	111.5	116.8	126.9	138.2
80°	76.9	77.8	77.3	78.3	78.3	80.2	81.1	86.8	89.2	95.8	104.8
82.5°	56.4	57.2	57.2	58.5	59.3	59.7	61.0	63.2	65.6	71.5	75.2
85°	28.4	29.4	28.4	29.4	30.9	31.3	32.7	33.2	35.1	36.6	39.9
87.5°	11.2	12.4	12.6	12.8	13.4	13.8	14.0	13.6	14.9	15.4	16.7
90°	14.6	14.6	15.3	14.6	13.9	13.9	13.3	12.6	11.9	12.6	11.1
92.5°	53.7	53.7	56.1	59.8	68.0	82.0	103.1	137.0	184.2	221.1	193.6
95°	170.1	179.2	191.7	213.4	247.5	315.1	408.6	516.7	584.3	568.3	428.8
97.5°	454.8	469.2	490.2	532.2	582.2	655.0	723.2	763.3	734.1	598.5	401.4
100°	639.4	645.0	665.8	708.4	769.1	820.6	854.8	840.9	739.0	560.6	364.0
102.5°	800.0	804.5	826.5	857.4	894.6	916.1	906.2	837.0	697.2	513.2	338.9
105°	981.1	985.3	995.0	1000.6	999.2	970.5	901.5	781.0	621.3	457.4	317.3
107.5°	1048.2	1046.4	1039.5	1023.6	989.1	926.9	829.7	701.3	559.9	426.1	313.3
110°	1049.4	1043.1	1030.6	1001.2	951.7	875.0	773.9	653.4	529.2	415.5	314.4



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1016.5	1006.3	988.7	953.2	897.1	820.4	724.9	618.2	511.9	410.5	317.8
115°	942.0	936.4	914.1	872.3	817.2	750.2	668.7	582.9	495.7	407.9	324.2
117.5°	866.6	862.2	839.6	804.5	757.5	700.7	636.6	565.6	488.5	407.2	331.1
120°	824.1	816.5	798.3	767.7	727.9	678.4	622.7	557.8	484.6	407.2	336.1
122.5°	790.7	783.0	767.7	741.5	707.8	664.5	613.7	551.1	480.1	406.6	341.1
125°	751.6	747.4	734.2	714.0	686.1	647.7	599.7	539.7	472.7	405.8	348.7
127.5°	728.8	724.6	713.5	695.4	667.4	631.0	583.0	525.8	462.8	404.3	354.6
130°	715.4	711.2	700.1	682.6	654.0	617.1	569.6	514.6	456.7	403.7	359.1
132.5°	700.3	696.2	685.5	665.8	637.8	600.9	554.6	502.8	451.1	403.1	363.0
135°	672.2	668.0	656.8	637.3	609.4	574.5	532.0	486.7	442.7	402.3	368.8
137.5°	637.3	632.2	623.0	603.8	577.7	546.3	510.4	472.1	435.5	402.2	372.3
140°	612.2	606.6	596.8	581.5	557.1	527.8	496.4	463.7	431.6	401.6	375.1
142.5°	585.4	581.5	572.8	558.7	537.0	511.7	484.7	455.8	428.3	401.6	377.4
145°	548.8	545.3	538.2	526.5	509.0	489.5	468.6	444.9	422.5	400.2	378.6
147.5°	516.2	515.0	509.7	499.5	486.7	471.4	454.6	435.8	417.4	397.7	379.3
150°	497.8	497.1	492.9	483.9	472.7	460.2	446.2	430.2	413.5	396.0	379.3
152.5°	481.1	480.4	477.9	470.5	461.0	450.7	437.8	424.1	409.0	393.2	378.2
155°	459.5	459.5	457.4	451.8	444.9	436.5	426.1	414.8	402.3	389.1	376.5
157.5°	440.5	440.5	439.3	435.1	429.8	423.1	414.3	404.9	395.5	384.8	374.7
160°	428.8	428.8	428.1	423.9	419.7	414.2	406.5	398.9	390.5	381.4	373.0
162.5°	417.7	418.2	417.5	413.3	410.3	405.3	399.2	392.7	386.0	378.1	371.4
165°	400.9	401.6	402.3	399.5	396.7	393.2	388.3	384.1	378.6	373.0	368.2
167.5°	387.6	388.3	388.3	386.6	385.1	383.1	379.2	375.9	371.9	368.0	364.8
170°	379.3	379.3	380.0	379.3	377.9	375.9	373.0	371.0	367.5	364.6	362.6
172.5°	371.0	372.0	372.7	372.0	371.2	369.7	368.0	366.5	363.6	361.3	360.3
175°	361.1	362.6	364.0	362.6	362.6	362.6	361.1	360.5	359.1	357.7	357.7
177.5°	355.4	356.6	357.7	357.1	357.7	357.1	357.1	356.6	356.0	355.4	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1181.6	1176.3	1172.5	1169.5	1161.2	1156.2	1152.4	1147.1	1141.0	1134.6	1126.6
5°	1248.7	1232.5	1220.8	1202.7	1185.6	1171.4	1156.7	1143.4	1127.3	1109.7	1096.9
7.5°	1319.2	1295.2	1264.4	1237.8	1207.8	1181.7	1158.4	1134.5	1109.6	1085.6	1063.5
10°	1364.0	1333.1	1299.0	1258.6	1220.8	1187.0	1155.7	1125.4	1096.0	1066.6	1041.4
12.5°	1412.1	1373.7	1323.2	1276.1	1233.6	1188.6	1150.8	1113.7	1078.2	1047.2	1017.9
15°	1476.8	1421.3	1363.0	1299.9	1243.9	1191.3	1139.6	1092.7	1052.8	1012.0	983.6
17.5°	1516.5	1447.9	1381.2	1315.3	1247.6	1181.2	1125.4	1071.2	1021.4	980.8	944.9
20°	1542.7	1474.4	1391.4	1325.5	1244.9	1176.6	1112.1	1051.9	999.7	956.5	919.5
22.5°	1565.5	1486.6	1403.6	1316.8	1236.5	1164.1	1093.5	1032.9	979.6	934.2	898.7
25°	1577.8	1487.2	1397.1	1310.8	1219.8	1133.9	1069.9	998.8	941.8	893.9	856.0
27.5°	1579.1	1482.3	1380.4	1284.4	1190.4	1110.5	1029.7	966.2	907.0	856.4	819.9
30°	1574.9	1474.0	1364.4	1260.5	1166.2	1079.4	1009.2	940.0	879.8	829.5	791.5
32.5°	1561.7	1456.5	1343.9	1233.9	1136.2	1051.3	978.8	913.0	854.3	804.8	765.0
35°	1523.3	1419.4	1299.4	1185.2	1085.0	999.3	933.8	866.9	808.2	761.2	722.7
37.5°	1463.2	1369.3	1247.3	1129.1	1030.8	944.6	879.8	819.3	766.2	718.5	679.2
40°	1410.9	1328.4	1206.0	1090.7	984.5	902.5	841.8	786.3	733.7	688.6	651.1
42.5°	1350.6	1278.6	1165.8	1043.7	941.3	858.9	799.7	749.8	700.3	658.6	621.2
45°	1243.0	1195.6	1089.3	976.5	869.8	792.0	735.6	692.0	650.2	609.4	578.1
47.5°	1119.3	1095.8	1006.4	899.2	797.9	721.2	672.3	632.0	595.4	560.9	533.2
50°	1036.3	1024.8	947.5	844.2	747.4	675.3	626.0	591.4	560.1	529.8	503.6
52.5°	954.3	953.9	884.2	789.5	700.0	630.5	581.6	549.3	522.2	497.5	474.0
55°	829.0	842.2	787.7	703.3	623.1	560.5	516.5	487.5	468.6	448.2	430.6
57.5°	713.9	735.9	691.0	616.6	549.7	492.0	453.7	431.9	411.7	399.4	386.6
60°	638.8	659.7	624.6	562.0	498.9	449.6	413.0	393.6	376.0	367.6	358.6
62.5°	572.0	590.7	564.6	506.6	451.8	404.5	373.6	354.9	343.0	333.8	327.8
65°	476.6	492.2	470.0	427.8	380.8	342.9	317.7	303.0	291.7	287.8	281.2
67.5°	385.3	399.5	387.4	351.6	314.0	285.2	265.6	251.5	244.7	241.4	236.7
70°	331.0	345.3	332.4	301.1	272.2	248.1	229.5	221.5	214.4	212.9	206.3
72.5°	285.1	294.8	282.0	257.5	232.7	212.4	198.0	189.6	185.9	183.3	179.8
75°	213.9	222.4	213.9	194.9	177.4	163.2	150.8	147.5	143.2	141.8	139.5
77.5°	151.4	158.8	152.2	140.4	127.2	116.3	109.7	105.4	104.4	101.9	103.1
80°	115.7	120.5	114.3	106.2	95.8	88.2	83.5	81.1	78.3	77.3	79.2
82.5°	83.1	85.2	82.0	76.6	68.8	63.9	60.7	58.0	57.4	57.6	57.6
85°	43.2	42.7	42.2	37.5	35.1	31.7	29.9	29.4	28.9	29.9	30.9
87.5°	16.4	16.8	15.5	14.0	12.8	11.5	10.7	10.0	10.7	11.5	11.9
90°	9.7	9.7	5.6	5.6	4.9	4.2	2.1	0.7	2.1	4.2	4.9
92.5°	140.8	86.8	51.3	36.8	26.7	18.1	11.6	7.9	11.6	18.1	26.7
95°	262.2	147.8	87.1	57.9	41.1	32.1	25.1	23.0	25.1	32.1	41.1
97.5°	235.7	141.2	94.5	70.0	55.6	47.3	41.3	41.3	41.3	47.3	55.6
100°	221.8	142.9	101.8	79.5	66.3	57.9	53.0	53.0	53.0	57.9	66.3
102.5°	217.8	148.5	111.3	90.1	77.4	69.6	65.3	64.1	65.3	69.6	77.4
105°	219.6	161.8	128.3	108.1	95.5	87.1	83.6	81.6	83.6	87.1	95.5
107.5°	230.0	177.3	146.6	126.6	114.6	105.7	102.2	100.9	102.2	105.7	114.6
110°	237.7	189.0	158.3	139.5	126.9	118.5	115.0	113.7	115.0	118.5	126.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.1	200.1	170.6	151.7	139.2	131.3	127.3	125.9	127.3	131.3	139.2
115°	259.4	217.6	189.7	170.9	157.6	150.6	145.7	143.7	145.7	150.6	157.6
117.5°	272.9	234.4	207.9	188.4	176.0	168.4	164.0	162.0	164.0	168.4	176.0
120°	282.4	246.1	219.6	200.1	188.2	180.6	175.7	174.3	175.7	180.6	188.2
122.5°	291.3	257.3	230.8	211.8	198.9	191.7	186.9	185.5	186.9	191.7	198.9
125°	304.7	272.6	247.5	228.0	214.7	207.1	202.9	200.1	202.9	207.1	214.7
127.5°	316.3	286.9	262.6	242.9	229.1	220.3	215.3	213.1	215.3	220.3	229.1
130°	323.5	296.3	272.6	252.4	239.2	228.7	223.1	220.3	223.1	228.7	239.2
132.5°	330.7	304.2	280.4	261.4	247.0	237.1	229.8	227.6	229.8	237.1	247.0
135°	340.3	315.1	292.1	274.0	259.4	247.5	240.6	237.7	240.6	247.5	259.4
137.5°	347.0	323.5	302.0	284.7	269.6	258.2	250.6	248.0	250.6	258.2	269.6
140°	351.4	329.1	308.2	291.4	276.8	264.9	257.3	255.2	257.3	264.9	276.8
142.5°	354.7	334.1	313.8	297.6	283.5	272.2	265.1	263.0	265.1	272.2	283.5
145°	358.4	339.6	321.5	306.1	292.8	283.1	276.1	274.0	276.1	283.1	292.8
147.5°	361.6	345.2	328.1	314.3	303.3	293.3	287.1	286.4	287.1	293.3	303.3
150°	363.3	347.9	332.6	319.3	308.9	300.5	295.0	294.3	295.0	300.5	308.9
152.5°	364.4	350.2	336.5	324.4	315.0	307.2	301.7	301.5	301.7	307.2	315.0
155°	365.3	353.5	341.6	331.2	323.5	316.6	312.4	311.7	312.4	316.6	323.5
157.5°	365.3	355.9	345.8	337.6	330.9	325.5	321.6	321.6	321.6	325.5	330.9
160°	365.3	357.0	348.7	341.0	335.4	330.5	327.7	327.7	327.7	330.5	335.4
162.5°	365.3	358.1	350.3	344.3	339.3	334.9	332.7	333.3	332.7	334.9	339.3
165°	364.0	358.4	352.1	347.9	344.5	341.0	339.6	339.6	339.6	341.0	344.5
167.5°	362.3	358.3	353.7	350.4	348.5	345.8	345.2	345.8	345.2	345.8	348.5
170°	361.1	357.7	354.2	352.1	350.7	348.7	347.9	348.7	347.9	348.7	350.7
172.5°	360.1	357.1	354.7	353.2	352.4	350.9	350.7	351.4	350.7	350.9	352.4
175°	358.4	356.3	354.9	354.9	354.2	353.5	353.5	354.2	353.5	353.5	354.2
177.5°	356.6	355.4	354.9	354.9	354.9	354.4	354.9	355.4	354.9	354.4	354.9
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1122.8	1119.5	1114.5	1107.7	1102.0	1095.9	1094.4	1092.1	1096.6	1092.9	1091.7
5°	1086.0	1076.0	1063.3	1048.6	1040.0	1027.7	1025.3	1020.6	1015.8	1015.4	1010.6
7.5°	1047.0	1032.4	1015.7	1000.7	986.8	973.3	964.6	962.6	955.6	951.5	946.8
10°	1022.0	1004.0	984.5	970.3	954.2	940.0	930.0	924.3	919.5	914.4	909.6
12.5°	992.4	973.2	957.3	941.8	922.7	911.9	895.5	885.6	884.7	884.8	872.4
15°	958.0	939.0	914.4	892.5	882.1	861.2	852.2	840.8	833.7	826.6	820.9
17.5°	918.6	895.0	875.7	850.7	830.8	814.2	802.4	795.5	784.8	774.7	767.4
20°	893.9	868.8	848.5	821.9	800.0	779.6	769.7	760.2	752.2	743.6	735.6
22.5°	868.9	842.7	817.7	791.9	771.6	750.1	740.5	727.5	719.9	715.2	707.1
25°	829.5	801.0	772.6	747.9	727.0	708.0	695.3	685.3	676.7	673.0	667.7
27.5°	786.6	758.3	730.8	702.8	679.1	665.4	655.1	647.6	642.7	637.7	635.3
30°	759.3	729.9	700.4	674.4	652.6	638.8	629.3	624.1	620.3	618.0	615.5
32.5°	731.6	702.6	671.6	647.8	628.3	616.1	608.9	603.6	601.7	600.8	600.0
35°	687.2	657.8	629.3	608.0	589.5	584.8	578.5	575.8	574.8	578.1	579.5
37.5°	644.2	616.9	590.8	570.1	557.9	551.0	548.8	549.0	552.4	555.4	558.7
40°	616.5	590.0	565.3	547.2	535.9	531.6	530.7	533.1	536.8	540.2	543.9
42.5°	589.6	563.4	541.0	524.1	516.2	512.3	512.8	515.2	520.5	524.6	530.3
45°	547.8	525.9	504.1	490.4	483.8	484.6	484.6	488.9	494.2	500.3	506.5
47.5°	508.4	486.4	468.4	456.9	453.4	452.6	455.3	460.8	468.3	476.0	484.6
50°	481.8	460.9	445.3	434.9	431.1	432.5	436.3	441.5	450.5	460.0	469.0
52.5°	454.9	436.0	421.4	411.7	409.1	411.6	415.4	423.7	431.6	441.8	452.7
55°	413.0	396.9	385.6	378.4	377.5	378.9	383.2	392.2	403.6	416.4	426.9
57.5°	371.4	357.9	347.5	342.6	343.0	344.4	351.4	362.1	374.3	387.9	401.4
60°	343.4	331.0	322.5	318.7	319.1	322.0	330.6	340.5	355.7	369.0	383.2
62.5°	316.8	305.9	297.8	294.4	293.7	300.0	308.2	318.5	333.7	348.5	363.8
65°	274.1	265.6	259.0	257.1	258.5	263.2	273.7	287.4	300.2	315.8	332.0
67.5°	232.4	225.3	220.8	221.7	223.4	230.4	239.2	250.9	265.5	281.7	297.7
70°	205.8	199.2	195.4	195.8	198.7	207.2	214.8	226.7	242.4	259.0	272.2
72.5°	178.5	174.2	170.8	172.7	175.6	181.5	190.9	202.8	216.5	232.0	246.0
75°	137.1	137.1	135.2	136.6	140.9	146.5	153.6	165.9	179.8	192.1	203.5
77.5°	101.7	100.7	101.8	103.6	106.0	112.8	120.9	129.7	140.1	152.4	161.8
80°	77.8	78.3	80.6	83.5	84.4	89.6	98.2	106.2	114.3	124.8	133.8
82.5°	58.4	58.9	60.1	63.8	64.6	70.3	75.8	83.8	91.1	98.2	105.7
85°	31.7	31.7	34.2	35.6	37.9	41.7	45.0	49.8	56.4	61.2	68.3
87.5°	13.3	13.3	15.6	16.4	17.7	20.0	20.6	24.9	26.6	28.6	32.0
90°	5.6	5.6	9.7	9.7	11.1	12.6	11.9	12.6	13.3	13.9	13.9
92.5°	36.8	51.3	86.8	140.8	193.6	221.1	184.2	137.0	103.1	82.0	68.0
95°	57.9	87.1	147.8	262.2	428.8	568.3	584.3	516.7	408.6	315.1	247.5
97.5°	70.0	94.5	141.2	235.7	401.4	598.5	734.1	763.3	723.2	655.0	582.2
100°	79.5	101.8	142.9	221.8	364.0	560.6	739.0	840.9	854.8	820.6	769.1
102.5°	90.1	111.3	148.5	217.8	338.9	513.2	697.2	837.0	906.2	916.1	894.6
105°	108.1	128.3	161.8	219.6	317.3	457.4	621.3	781.0	901.5	970.5	999.2
107.5°	126.6	146.6	177.3	230.0	313.3	426.1	559.9	701.3	829.7	926.9	989.1
110°	139.5	158.3	189.0	237.7	314.4	415.5	529.2	653.4	773.9	875.0	951.7



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	151.7	170.6	200.1	246.1	317.8	410.5	511.9	618.2	724.9	820.4	897.1
115°	170.9	189.7	217.6	259.4	324.2	407.9	495.7	582.9	668.7	750.2	817.2
117.5°	188.4	207.9	234.4	272.9	331.1	407.2	488.5	565.6	636.6	700.7	757.5
120°	200.1	219.6	246.1	282.4	336.1	407.2	484.6	557.8	622.7	678.4	727.9
122.5°	211.8	230.8	257.3	291.3	341.1	406.6	480.1	551.1	613.7	664.5	707.8
125°	228.0	247.5	272.6	304.7	348.7	405.8	472.7	539.7	599.7	647.7	686.1
127.5°	242.9	262.6	286.9	316.3	354.6	404.3	462.8	525.8	583.0	631.0	667.4
130°	252.4	272.6	296.3	323.5	359.1	403.7	456.7	514.6	569.6	617.1	654.0
132.5°	261.4	280.4	304.2	330.7	363.0	403.1	451.1	502.8	554.6	600.9	637.8
135°	274.0	292.1	315.1	340.3	368.8	402.3	442.7	486.7	532.0	574.5	609.4
137.5°	284.7	302.0	323.5	347.0	372.3	402.2	435.5	472.1	510.4	546.3	577.7
140°	291.4	308.2	329.1	351.4	375.1	401.6	431.6	463.7	496.4	527.8	557.1
142.5°	297.6	313.8	334.1	354.7	377.4	401.6	428.3	455.8	484.7	511.7	537.0
145°	306.1	321.5	339.6	358.4	378.6	400.2	422.5	444.9	468.6	489.5	509.0
147.5°	314.3	328.1	345.2	361.6	379.3	397.7	417.4	435.8	454.6	471.4	486.7
150°	319.3	332.6	347.9	363.3	379.3	396.0	413.5	430.2	446.2	460.2	472.7
152.5°	324.4	336.5	350.2	364.4	378.2	393.2	409.0	424.1	437.8	450.7	461.0
155°	331.2	341.6	353.5	365.3	376.5	389.1	402.3	414.8	426.1	436.5	444.9
157.5°	337.6	345.8	355.9	365.3	374.7	384.8	395.5	404.9	414.3	423.1	429.8
160°	341.0	348.7	357.0	365.3	373.0	381.4	390.5	398.9	406.5	414.2	419.7
162.5°	344.3	350.3	358.1	365.3	371.4	378.1	386.0	392.7	399.2	405.3	410.3
165°	347.9	352.1	358.4	364.0	368.2	373.0	378.6	384.1	388.3	393.2	396.7
167.5°	350.4	353.7	358.3	362.3	364.8	368.0	371.9	375.9	379.2	383.1	385.1
170°	352.1	354.2	357.7	361.1	362.6	364.6	367.5	371.0	373.0	375.9	377.9
172.5°	353.2	354.7	357.1	360.1	360.3	361.3	363.6	366.5	368.0	369.7	371.2
175°	354.9	354.9	356.3	358.4	357.7	357.7	359.1	360.5	361.1	362.6	362.6
177.5°	354.9	354.9	355.4	356.6	355.4	355.4	356.0	356.6	357.1	357.1	357.7
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1090.9	1090.2	1087.5	1087.2	1087.5	1090.2	1090.9	1091.7	1092.9	1096.6	1092.1
5°	1007.8	1005.4	1004.0	1009.2	1004.0	1005.4	1007.8	1010.6	1015.4	1015.8	1020.6
7.5°	945.0	943.2	939.0	937.7	939.0	943.2	945.0	946.8	951.5	955.6	962.6
10°	904.8	902.9	899.2	898.2	899.2	902.9	904.8	909.6	914.4	919.5	924.3
12.5°	866.1	862.4	861.6	862.6	861.6	862.4	866.1	872.4	884.8	884.7	885.6
15°	814.8	812.9	807.6	809.0	807.6	812.9	814.8	820.9	826.6	833.7	840.8
17.5°	764.1	761.8	755.5	761.1	755.5	761.8	764.1	767.4	774.7	784.8	795.5
20°	732.3	728.4	725.1	724.6	725.1	728.4	732.3	735.6	743.6	752.2	760.2
22.5°	701.9	698.5	698.2	695.1	698.2	698.5	701.9	707.1	715.2	719.9	727.5
25°	664.0	660.7	659.7	657.3	659.7	660.7	664.0	667.7	673.0	676.7	685.3
27.5°	634.8	633.2	631.5	632.2	631.5	633.2	634.8	635.3	637.7	642.7	647.6
30°	617.0	616.5	615.5	615.5	615.5	616.5	617.0	615.5	618.0	620.3	624.1
32.5°	602.2	602.1	602.7	602.7	602.7	602.1	602.2	600.0	600.8	601.7	603.6
35°	581.4	582.8	583.8	582.4	583.8	582.8	581.4	579.5	578.1	574.8	575.8
37.5°	562.7	564.1	565.4	567.0	565.4	564.1	562.7	558.7	555.4	552.4	549.0
40°	548.2	551.5	552.5	554.9	552.5	551.5	548.2	543.9	540.2	536.8	533.1
42.5°	534.6	538.2	540.7	541.2	540.7	538.2	534.6	530.3	524.6	520.5	515.2
45°	513.6	517.4	520.8	520.8	520.8	517.4	513.6	506.5	500.3	494.2	488.9
47.5°	491.9	497.4	500.7	501.6	500.7	497.4	491.9	484.6	476.0	468.3	460.8
50°	477.1	483.8	487.1	489.5	487.1	483.8	477.1	469.0	460.0	450.5	441.5
52.5°	462.7	469.3	473.8	475.0	473.8	469.3	462.7	452.7	441.8	431.6	423.7
55°	437.7	447.2	452.5	454.3	452.5	447.2	437.7	426.9	416.4	403.6	392.2
57.5°	414.2	422.9	429.0	430.4	429.0	422.9	414.2	401.4	387.9	374.3	362.1
60°	396.0	405.5	413.0	414.5	413.0	405.5	396.0	383.2	369.0	355.7	340.5
62.5°	377.4	387.3	394.1	397.8	394.1	387.3	377.4	363.8	348.5	333.7	318.5
65°	345.3	355.2	361.9	363.3	361.9	355.2	345.3	332.0	315.8	300.2	287.4
67.5°	310.1	320.1	324.5	327.3	324.5	320.1	310.1	297.7	281.7	265.5	250.9
70°	285.5	293.6	298.3	300.7	298.3	293.6	285.5	272.2	259.0	242.4	226.7
72.5°	257.4	265.8	271.3	271.8	271.3	265.8	257.4	246.0	232.0	216.5	202.8
75°	214.4	221.9	224.8	224.8	224.8	221.9	214.4	203.5	192.1	179.8	165.9
77.5°	169.7	173.6	177.2	177.9	177.2	173.6	169.7	161.8	152.4	140.1	129.7
80°	140.9	143.2	146.1	146.1	146.1	143.2	140.9	133.8	124.8	114.3	106.2
82.5°	111.3	113.2	116.1	115.7	116.1	113.2	111.3	105.7	98.2	91.1	83.8
85°	67.3	71.6	71.2	70.2	71.2	71.6	67.3	68.3	61.2	56.4	49.8
87.5°	33.3	33.8	34.8	35.6	34.8	33.8	33.3	32.0	28.6	26.6	24.9
90°	14.6	15.3	14.6	14.6	14.6	15.3	14.6	13.9	13.9	13.3	12.6
92.5°	59.8	56.1	53.7	53.7	53.7	56.1	59.8	68.0	82.0	103.1	137.0
95°	213.4	191.7	179.2	170.1	179.2	191.7	213.4	247.5	315.1	408.6	516.7
97.5°	532.2	490.2	469.2	454.8	469.2	490.2	532.2	582.2	655.0	723.2	763.3
100°	708.4	665.8	645.0	639.4	645.0	665.8	708.4	769.1	820.6	854.8	840.9
102.5°	857.4	826.5	804.5	800.0	804.5	826.5	857.4	894.6	916.1	906.2	837.0
105°	1000.6	995.0	985.3	981.1	985.3	995.0	1000.6	999.2	970.5	901.5	781.0
107.5°	1023.6	1039.5	1046.4	1048.2	1046.4	1039.5	1023.6	989.1	926.9	829.7	701.3
110°	1001.2	1030.6	1043.1	1049.4	1043.1	1030.6	1001.2	951.7	875.0	773.9	653.4



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	953.2	988.7	1006.3	1016.5	1006.3	988.7	953.2	897.1	820.4	724.9	618.2
115°	872.3	914.1	936.4	942.0	936.4	914.1	872.3	817.2	750.2	668.7	582.9
117.5°	804.5	839.6	862.2	866.6	862.2	839.6	804.5	757.5	700.7	636.6	565.6
120°	767.7	798.3	816.5	824.1	816.5	798.3	767.7	727.9	678.4	622.7	557.8
122.5°	741.5	767.7	783.0	790.7	783.0	767.7	741.5	707.8	664.5	613.7	551.1
125°	714.0	734.2	747.4	751.6	747.4	734.2	714.0	686.1	647.7	599.7	539.7
127.5°	695.4	713.5	724.6	728.8	724.6	713.5	695.4	667.4	631.0	583.0	525.8
130°	682.6	700.1	711.2	715.4	711.2	700.1	682.6	654.0	617.1	569.6	514.6
132.5°	665.8	685.5	696.2	700.3	696.2	685.5	665.8	637.8	600.9	554.6	502.8
135°	637.3	656.8	668.0	672.2	668.0	656.8	637.3	609.4	574.5	532.0	486.7
137.5°	603.8	623.0	632.2	637.3	632.2	623.0	603.8	577.7	546.3	510.4	472.1
140°	581.5	596.8	606.6	612.2	606.6	596.8	581.5	557.1	527.8	496.4	463.7
142.5°	558.7	572.8	581.5	585.4	581.5	572.8	558.7	537.0	511.7	484.7	455.8
145°	526.5	538.2	545.3	548.8	545.3	538.2	526.5	509.0	489.5	468.6	444.9
147.5°	499.5	509.7	515.0	516.2	515.0	509.7	499.5	486.7	471.4	454.6	435.8
150°	483.9	492.9	497.1	497.8	497.1	492.9	483.9	472.7	460.2	446.2	430.2
152.5°	470.5	477.9	480.4	481.1	480.4	477.9	470.5	461.0	450.7	437.8	424.1
155°	451.8	457.4	459.5	459.5	459.5	457.4	451.8	444.9	436.5	426.1	414.8
157.5°	435.1	439.3	440.5	440.5	440.5	439.3	435.1	429.8	423.1	414.3	404.9
160°	423.9	428.1	428.8	428.8	428.8	428.1	423.9	419.7	414.2	406.5	398.9
162.5°	413.3	417.5	418.2	417.7	418.2	417.5	413.3	410.3	405.3	399.2	392.7
165°	399.5	402.3	401.6	400.9	401.6	402.3	399.5	396.7	393.2	388.3	384.1
167.5°	386.6	388.3	388.3	387.6	388.3	388.3	386.6	385.1	383.1	379.2	375.9
170°	379.3	380.0	379.3	379.3	379.3	380.0	379.3	377.9	375.9	373.0	371.0
172.5°	372.0	372.7	372.0	371.0	372.0	372.7	372.0	371.2	369.7	368.0	366.5
175°	362.6	364.0	362.6	361.1	362.6	364.0	362.6	362.6	362.6	361.1	360.5
177.5°	357.1	357.7	356.6	355.4	356.6	357.7	357.1	357.7	357.1	357.1	356.6
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1094.4	1095.9	1102.0	1107.7	1114.5	1119.5	1122.8	1126.6	1134.6	1141.0	1147.1
5°	1025.3	1027.7	1040.0	1048.6	1063.3	1076.0	1086.0	1096.9	1109.7	1127.3	1143.4
7.5°	964.6	973.3	986.8	1000.7	1015.7	1032.4	1047.0	1063.5	1085.6	1109.6	1134.5
10°	930.0	940.0	954.2	970.3	984.5	1004.0	1022.0	1041.4	1066.6	1096.0	1125.4
12.5°	895.5	911.9	922.7	941.8	957.3	973.2	992.4	1017.9	1047.2	1078.2	1113.7
15°	852.2	861.2	882.1	892.5	914.4	939.0	958.0	983.6	1012.0	1052.8	1092.7
17.5°	802.4	814.2	830.8	850.7	875.7	895.0	918.6	944.9	980.8	1021.4	1071.2
20°	769.7	779.6	800.0	821.9	848.5	868.8	893.9	919.5	956.5	999.7	1051.9
22.5°	740.5	750.1	771.6	791.9	817.7	842.7	868.9	898.7	934.2	979.6	1032.9
25°	695.3	708.0	727.0	747.9	772.6	801.0	829.5	856.0	893.9	941.8	998.8
27.5°	655.1	665.4	679.1	702.8	730.8	758.3	786.6	819.9	856.4	907.0	966.2
30°	629.3	638.8	652.6	674.4	700.4	729.9	759.3	791.5	829.5	879.8	940.0
32.5°	608.9	616.1	628.3	647.8	671.6	702.6	731.6	765.0	804.8	854.3	913.0
35°	578.5	584.8	589.5	608.0	629.3	657.8	687.2	722.7	761.2	808.2	866.9
37.5°	548.8	551.0	557.9	570.1	590.8	616.9	644.2	679.2	718.5	766.2	819.3
40°	530.7	531.6	535.9	547.2	565.3	590.0	616.5	651.1	688.6	733.7	786.3
42.5°	512.8	512.3	516.2	524.1	541.0	563.4	589.6	621.2	658.6	700.3	749.8
45°	484.6	484.6	483.8	490.4	504.1	525.9	547.8	578.1	609.4	650.2	692.0
47.5°	455.3	452.6	453.4	456.9	468.4	486.4	508.4	533.2	560.9	595.4	632.0
50°	436.3	432.5	431.1	434.9	445.3	460.9	481.8	503.6	529.8	560.1	591.4
52.5°	415.4	411.6	409.1	411.7	421.4	436.0	454.9	474.0	497.5	522.2	549.3
55°	383.2	378.9	377.5	378.4	385.6	396.9	413.0	430.6	448.2	468.6	487.5
57.5°	351.4	344.4	343.0	342.6	347.5	357.9	371.4	386.6	399.4	411.7	431.9
60°	330.6	322.0	319.1	318.7	322.5	331.0	343.4	358.6	367.6	376.0	393.6
62.5°	308.2	300.0	293.7	294.4	297.8	305.9	316.8	327.8	333.8	343.0	354.9
65°	273.7	263.2	258.5	257.1	259.0	265.6	274.1	281.2	287.8	291.7	303.0
67.5°	239.2	230.4	223.4	221.7	220.8	225.3	232.4	236.7	241.4	244.7	251.5
70°	214.8	207.2	198.7	195.8	195.4	199.2	205.8	206.3	212.9	214.4	221.5
72.5°	190.9	181.5	175.6	172.7	170.8	174.2	178.5	179.8	183.3	185.9	189.6
75°	153.6	146.5	140.9	136.6	135.2	137.1	137.1	139.5	141.8	143.2	147.5
77.5°	120.9	112.8	106.0	103.6	101.8	100.7	101.7	103.1	101.9	104.4	105.4
80°	98.2	89.6	84.4	83.5	80.6	78.3	77.8	79.2	77.3	78.3	81.1
82.5°	75.8	70.3	64.6	63.8	60.1	58.9	58.4	57.6	57.6	57.4	58.0
85°	45.0	41.7	37.9	35.6	34.2	31.7	31.7	30.9	29.9	28.9	29.4
87.5°	20.6	20.0	17.7	16.4	15.6	13.3	13.3	11.9	11.5	10.7	10.0
90°	11.9	12.6	11.1	9.7	9.7	5.6	5.6	4.9	4.2	2.1	0.7
92.5°	184.2	221.1	193.6	140.8	86.8	51.3	36.8	26.7	18.1	11.6	7.9
95°	584.3	568.3	428.8	262.2	147.8	87.1	57.9	41.1	32.1	25.1	23.0
97.5°	734.1	598.5	401.4	235.7	141.2	94.5	70.0	55.6	47.3	41.3	41.3
100°	739.0	560.6	364.0	221.8	142.9	101.8	79.5	66.3	57.9	53.0	53.0
102.5°	697.2	513.2	338.9	217.8	148.5	111.3	90.1	77.4	69.6	65.3	64.1
105°	621.3	457.4	317.3	219.6	161.8	128.3	108.1	95.5	87.1	83.6	81.6
107.5°	559.9	426.1	313.3	230.0	177.3	146.6	126.6	114.6	105.7	102.2	100.9
110°	529.2	415.5	314.4	237.7	189.0	158.3	139.5	126.9	118.5	115.0	113.7



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.9	410.5	317.8	246.1	200.1	170.6	151.7	139.2	131.3	127.3	125.9
115°	495.7	407.9	324.2	259.4	217.6	189.7	170.9	157.6	150.6	145.7	143.7
117.5°	488.5	407.2	331.1	272.9	234.4	207.9	188.4	176.0	168.4	164.0	162.0
120°	484.6	407.2	336.1	282.4	246.1	219.6	200.1	188.2	180.6	175.7	174.3
122.5°	480.1	406.6	341.1	291.3	257.3	230.8	211.8	198.9	191.7	186.9	185.5
125°	472.7	405.8	348.7	304.7	272.6	247.5	228.0	214.7	207.1	202.9	200.1
127.5°	462.8	404.3	354.6	316.3	286.9	262.6	242.9	229.1	220.3	215.3	213.1
130°	456.7	403.7	359.1	323.5	296.3	272.6	252.4	239.2	228.7	223.1	220.3
132.5°	451.1	403.1	363.0	330.7	304.2	280.4	261.4	247.0	237.1	229.8	227.6
135°	442.7	402.3	368.8	340.3	315.1	292.1	274.0	259.4	247.5	240.6	237.7
137.5°	435.5	402.2	372.3	347.0	323.5	302.0	284.7	269.6	258.2	250.6	248.0
140°	431.6	401.6	375.1	351.4	329.1	308.2	291.4	276.8	264.9	257.3	255.2
142.5°	428.3	401.6	377.4	354.7	334.1	313.8	297.6	283.5	272.2	265.1	263.0
145°	422.5	400.2	378.6	358.4	339.6	321.5	306.1	292.8	283.1	276.1	274.0
147.5°	417.4	397.7	379.3	361.6	345.2	328.1	314.3	303.3	293.3	287.1	286.4
150°	413.5	396.0	379.3	363.3	347.9	332.6	319.3	308.9	300.5	295.0	294.3
152.5°	409.0	393.2	378.2	364.4	350.2	336.5	324.4	315.0	307.2	301.7	301.5
155°	402.3	389.1	376.5	365.3	353.5	341.6	331.2	323.5	316.6	312.4	311.7
157.5°	395.5	384.8	374.7	365.3	355.9	345.8	337.6	330.9	325.5	321.6	321.6
160°	390.5	381.4	373.0	365.3	357.0	348.7	341.0	335.4	330.5	327.7	327.7
162.5°	386.0	378.1	371.4	365.3	358.1	350.3	344.3	339.3	334.9	332.7	333.3
165°	378.6	373.0	368.2	364.0	358.4	352.1	347.9	344.5	341.0	339.6	339.6
167.5°	371.9	368.0	364.8	362.3	358.3	353.7	350.4	348.5	345.8	345.2	345.8
170°	367.5	364.6	362.6	361.1	357.7	354.2	352.1	350.7	348.7	347.9	348.7
172.5°	363.6	361.3	360.3	360.1	357.1	354.7	353.2	352.4	350.9	350.7	351.4
175°	359.1	357.7	357.7	358.4	356.3	354.9	354.9	354.2	353.5	353.5	354.2
177.5°	356.0	355.4	355.4	356.6	355.4	354.9	354.9	354.9	354.4	354.9	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1152.4	1156.2	1161.2	1169.5	1172.5	1176.3	1181.6	1181.2	1182.8	1188.5	1200.6
5°	1156.7	1171.4	1185.6	1202.7	1220.8	1232.5	1248.7	1258.6	1268.6	1281.4	1303.2
7.5°	1158.4	1181.7	1207.8	1237.8	1264.4	1295.2	1319.2	1341.8	1362.1	1389.2	1415.1
10°	1155.7	1187.0	1220.8	1258.6	1299.0	1333.1	1364.0	1399.0	1428.9	1461.6	1491.0
12.5°	1150.8	1188.6	1233.6	1276.1	1323.2	1373.7	1412.1	1447.6	1487.4	1525.0	1570.3
15°	1139.6	1191.3	1243.9	1299.9	1363.0	1421.3	1476.8	1522.8	1565.5	1621.9	1681.2
17.5°	1125.4	1181.2	1247.6	1315.3	1381.2	1447.9	1516.5	1585.7	1639.6	1709.7	1756.0
20°	1112.1	1176.6	1244.9	1325.5	1391.4	1474.4	1542.7	1609.6	1683.6	1753.3	1808.7
22.5°	1093.5	1164.1	1236.5	1316.8	1403.6	1486.6	1565.5	1638.1	1712.0	1787.8	1855.0
25°	1069.9	1133.9	1219.8	1310.8	1397.1	1487.2	1577.8	1668.8	1748.6	1828.7	1891.3
27.5°	1029.7	1110.5	1190.4	1284.4	1380.4	1482.3	1579.1	1674.5	1757.9	1823.8	1862.6
30°	1009.2	1079.4	1166.2	1260.5	1364.4	1474.0	1574.9	1668.4	1746.1	1798.8	1814.5
32.5°	978.8	1051.3	1136.2	1233.9	1343.9	1456.5	1561.7	1649.8	1714.7	1742.3	1723.4
35°	933.8	999.3	1085.0	1185.2	1299.4	1419.4	1523.3	1597.8	1630.9	1604.8	1539.9
37.5°	879.8	944.6	1030.8	1129.1	1247.3	1369.3	1463.2	1516.8	1505.8	1440.9	1344.1
40°	841.8	902.5	984.5	1090.7	1206.0	1328.4	1410.9	1439.8	1409.4	1316.5	1213.6
42.5°	799.7	858.9	941.3	1043.7	1165.8	1278.6	1350.6	1352.9	1302.1	1191.0	1087.6
45°	735.6	792.0	869.8	976.5	1089.3	1195.6	1243.0	1219.8	1125.9	1018.7	914.8
47.5°	672.3	721.2	797.9	899.2	1006.4	1095.8	1119.3	1077.5	977.4	873.3	777.1
50°	626.0	675.3	747.4	844.2	947.5	1024.8	1036.3	980.7	882.6	777.8	702.4
52.5°	581.6	630.5	700.0	789.5	884.2	953.9	954.3	890.1	792.3	698.8	628.7
55°	516.5	560.5	623.1	703.3	787.7	842.2	829.0	762.6	677.7	596.6	535.4
57.5°	453.7	492.0	549.7	616.6	691.0	735.9	713.9	650.0	574.2	505.4	459.1
60°	413.0	449.6	498.9	562.0	624.6	659.7	638.8	580.9	511.2	455.8	415.4
62.5°	373.6	404.5	451.8	506.6	564.6	590.7	572.0	515.0	454.7	404.6	371.8
65°	317.7	342.9	380.8	427.8	470.0	492.2	476.6	423.5	377.5	341.4	315.4
67.5°	265.6	285.2	314.0	351.6	387.4	399.5	385.3	348.3	309.3	280.4	262.1
70°	229.5	248.1	272.2	301.1	332.4	345.3	331.0	301.6	269.8	243.3	225.2
72.5°	198.0	212.4	232.7	257.5	282.0	294.8	285.1	256.8	230.0	210.3	194.9
75°	150.8	163.2	177.4	194.9	213.9	222.4	213.9	194.5	175.9	161.2	150.3
77.5°	109.7	116.3	127.2	140.4	152.2	158.8	151.4	138.2	126.9	116.8	111.5
80°	83.5	88.2	95.8	106.2	114.3	120.5	115.7	104.8	95.8	89.2	86.8
82.5°	60.7	63.9	68.8	76.6	82.0	85.2	83.1	75.2	71.5	65.6	63.2
85°	29.9	31.7	35.1	37.5	42.2	42.7	43.2	39.9	36.6	35.1	33.2
87.5°	10.7	11.5	12.8	14.0	15.5	16.8	16.4	16.7	15.4	14.9	13.6
90°	2.1	4.2	4.9	5.6	5.6	9.7	9.7	11.1	12.6	11.9	12.6
92.5°	11.6	18.1	26.7	36.8	51.3	86.8	140.8	193.6	221.1	184.2	137.0
95°	25.1	32.1	41.1	57.9	87.1	147.8	262.2	428.8	568.3	584.3	516.7
97.5°	41.3	47.3	55.6	70.0	94.5	141.2	235.7	401.4	598.5	734.1	763.3
100°	53.0	57.9	66.3	79.5	101.8	142.9	221.8	364.0	560.6	739.0	840.9
102.5°	65.3	69.6	77.4	90.1	111.3	148.5	217.8	338.9	513.2	697.2	837.0
105°	83.6	87.1	95.5	108.1	128.3	161.8	219.6	317.3	457.4	621.3	781.0
107.5°	102.2	105.7	114.6	126.6	146.6	177.3	230.0	313.3	426.1	559.9	701.3
110°	115.0	118.5	126.9	139.5	158.3	189.0	237.7	314.4	415.5	529.2	653.4



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	131.3	139.2	151.7	170.6	200.1	246.1	317.8	410.5	511.9	618.2
115°	145.7	150.6	157.6	170.9	189.7	217.6	259.4	324.2	407.9	495.7	582.9
117.5°	164.0	168.4	176.0	188.4	207.9	234.4	272.9	331.1	407.2	488.5	565.6
120°	175.7	180.6	188.2	200.1	219.6	246.1	282.4	336.1	407.2	484.6	557.8
122.5°	186.9	191.7	198.9	211.8	230.8	257.3	291.3	341.1	406.6	480.1	551.1
125°	202.9	207.1	214.7	228.0	247.5	272.6	304.7	348.7	405.8	472.7	539.7
127.5°	215.3	220.3	229.1	242.9	262.6	286.9	316.3	354.6	404.3	462.8	525.8
130°	223.1	228.7	239.2	252.4	272.6	296.3	323.5	359.1	403.7	456.7	514.6
132.5°	229.8	237.1	247.0	261.4	280.4	304.2	330.7	363.0	403.1	451.1	502.8
135°	240.6	247.5	259.4	274.0	292.1	315.1	340.3	368.8	402.3	442.7	486.7
137.5°	250.6	258.2	269.6	284.7	302.0	323.5	347.0	372.3	402.2	435.5	472.1
140°	257.3	264.9	276.8	291.4	308.2	329.1	351.4	375.1	401.6	431.6	463.7
142.5°	265.1	272.2	283.5	297.6	313.8	334.1	354.7	377.4	401.6	428.3	455.8
145°	276.1	283.1	292.8	306.1	321.5	339.6	358.4	378.6	400.2	422.5	444.9
147.5°	287.1	293.3	303.3	314.3	328.1	345.2	361.6	379.3	397.7	417.4	435.8
150°	295.0	300.5	308.9	319.3	332.6	347.9	363.3	379.3	396.0	413.5	430.2
152.5°	301.7	307.2	315.0	324.4	336.5	350.2	364.4	378.2	393.2	409.0	424.1
155°	312.4	316.6	323.5	331.2	341.6	353.5	365.3	376.5	389.1	402.3	414.8
157.5°	321.6	325.5	330.9	337.6	345.8	355.9	365.3	374.7	384.8	395.5	404.9
160°	327.7	330.5	335.4	341.0	348.7	357.0	365.3	373.0	381.4	390.5	398.9
162.5°	332.7	334.9	339.3	344.3	350.3	358.1	365.3	371.4	378.1	386.0	392.7
165°	339.6	341.0	344.5	347.9	352.1	358.4	364.0	368.2	373.0	378.6	384.1
167.5°	345.2	345.8	348.5	350.4	353.7	358.3	362.3	364.8	368.0	371.9	375.9
170°	347.9	348.7	350.7	352.1	354.2	357.7	361.1	362.6	364.6	367.5	371.0
172.5°	350.7	350.9	352.4	353.2	354.7	357.1	360.1	360.3	361.3	363.6	366.5
175°	353.5	353.5	354.2	354.9	354.9	356.3	358.4	357.7	357.7	359.1	360.5
177.5°	354.9	354.4	354.9	354.9	354.9	355.4	356.6	355.4	355.4	356.0	356.6
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9	1144.9
2.5°	1206.7	1207.5	1210.9	1213.5	1214.2	1218.1	1218.4
5°	1312.7	1320.8	1336.4	1337.8	1340.2	1352.5	1343.1
7.5°	1437.0	1457.4	1471.1	1483.2	1487.6	1492.9	1491.8
10°	1516.6	1547.0	1562.2	1586.4	1587.3	1593.5	1589.7
12.5°	1596.7	1632.0	1659.7	1664.1	1684.4	1687.6	1692.9
15°	1710.1	1747.6	1786.0	1799.7	1827.7	1834.4	1844.9
17.5°	1816.8	1855.0	1882.0	1917.5	1929.0	1944.4	1933.9
20°	1875.2	1916.9	1951.1	1979.1	1990.9	1999.4	1998.5
22.5°	1910.5	1952.6	1980.2	2001.4	2012.5	2016.2	2015.9
25°	1932.5	1956.8	1965.2	1973.4	1961.1	1956.8	1958.6
27.5°	1871.1	1864.8	1842.5	1813.3	1783.0	1758.9	1745.8
30°	1786.5	1749.5	1715.8	1657.0	1626.7	1608.6	1592.5
32.5°	1666.6	1608.0	1543.2	1489.3	1454.8	1428.1	1424.1
35°	1461.2	1373.0	1293.8	1227.8	1193.6	1164.8	1158.1
37.5°	1242.2	1150.6	1079.3	1021.3	984.5	964.1	945.0
40°	1096.9	1018.2	948.0	898.7	870.8	856.0	844.2
42.5°	985.0	913.1	843.3	805.7	780.4	771.4	764.5
45°	830.4	763.6	715.2	686.7	672.0	656.8	649.7
47.5°	706.6	652.2	620.3	596.1	580.4	571.4	566.9
50°	636.4	591.8	563.4	544.9	530.7	523.5	519.8
52.5°	574.2	537.6	513.7	499.0	489.4	484.1	482.6
55°	494.6	466.6	451.5	438.7	431.6	426.9	424.9
57.5°	430.0	408.4	396.1	385.6	382.8	378.8	377.5
60°	387.4	370.9	360.4	353.3	351.0	346.2	347.1
62.5°	349.9	336.4	327.4	323.3	320.2	316.2	317.5
65°	296.0	286.0	281.2	277.4	273.7	271.3	273.1
67.5°	248.3	241.5	235.1	232.8	231.0	230.6	228.5
70°	217.2	211.5	205.8	204.4	204.4	202.5	202.1
72.5°	187.3	183.1	179.2	178.3	176.7	177.5	175.5
75°	144.6	141.3	139.9	138.5	138.0	138.0	136.6
77.5°	106.9	104.4	102.2	102.2	100.4	99.8	99.6
80°	81.1	80.2	78.3	78.3	77.3	77.8	76.9
82.5°	61.0	59.7	59.3	58.5	57.2	57.2	56.4
85°	32.7	31.3	30.9	29.4	28.4	29.4	28.4
87.5°	14.0	13.8	13.4	12.8	12.6	12.4	11.2
90°	13.3	13.9	13.9	14.6	15.3	14.6	14.6
92.5°	103.1	82.0	68.0	59.8	56.1	53.7	53.7
95°	408.6	315.1	247.5	213.4	191.7	179.2	170.1
97.5°	723.2	655.0	582.2	532.2	490.2	469.2	454.8
100°	854.8	820.6	769.1	708.4	665.8	645.0	639.4
102.5°	906.2	916.1	894.6	857.4	826.5	804.5	800.0
105°	901.5	970.5	999.2	1000.6	995.0	985.3	981.1
107.5°	829.7	926.9	989.1	1023.6	1039.5	1046.4	1048.2
110°	773.9	875.0	951.7	1001.2	1030.6	1043.1	1049.4



TEST NUMBER: P332600-940

CATALOG NUMBER: SA4XXDIP-C795D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	724.9	820.4	897.1	953.2	988.7	1006.3	1016.5
115°	668.7	750.2	817.2	872.3	914.1	936.4	942.0
117.5°	636.6	700.7	757.5	804.5	839.6	862.2	866.6
120°	622.7	678.4	727.9	767.7	798.3	816.5	824.1
122.5°	613.7	664.5	707.8	741.5	767.7	783.0	790.7
125°	599.7	647.7	686.1	714.0	734.2	747.4	751.6
127.5°	583.0	631.0	667.4	695.4	713.5	724.6	728.8
130°	569.6	617.1	654.0	682.6	700.1	711.2	715.4
132.5°	554.6	600.9	637.8	665.8	685.5	696.2	700.3
135°	532.0	574.5	609.4	637.3	656.8	668.0	672.2
137.5°	510.4	546.3	577.7	603.8	623.0	632.2	637.3
140°	496.4	527.8	557.1	581.5	596.8	606.6	612.2
142.5°	484.7	511.7	537.0	558.7	572.8	581.5	585.4
145°	468.6	489.5	509.0	526.5	538.2	545.3	548.8
147.5°	454.6	471.4	486.7	499.5	509.7	515.0	516.2
150°	446.2	460.2	472.7	483.9	492.9	497.1	497.8
152.5°	437.8	450.7	461.0	470.5	477.9	480.4	481.1
155°	426.1	436.5	444.9	451.8	457.4	459.5	459.5
157.5°	414.3	423.1	429.8	435.1	439.3	440.5	440.5
160°	406.5	414.2	419.7	423.9	428.1	428.8	428.8
162.5°	399.2	405.3	410.3	413.3	417.5	418.2	417.7
165°	388.3	393.2	396.7	399.5	402.3	401.6	400.9
167.5°	379.2	383.1	385.1	386.6	388.3	388.3	387.6
170°	373.0	375.9	377.9	379.3	380.0	379.3	379.3
172.5°	368.0	369.7	371.2	372.0	372.7	372.0	371.0
175°	361.1	362.6	362.6	362.6	364.0	362.6	361.1
177.5°	357.1	357.1	357.7	357.1	357.7	356.6	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9

(END OF REPORT)