

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332953-930

Luminaire Tested: **SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332953-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6018.3 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.8
10°-20°	296.7	4.9
20°-30°	428.4	7.1
30°-40°	485.6	8.1
40°-50°	468.9	7.8
50°-60°	389.9	6.5
60°-70°	269.3	4.5
70°-80°	136.5	2.3
80°-90°	38.7	0.6
90°-100°	80.8	1.3
100°-110°	239.3	4.0
110°-120°	406.2	6.7
120°-130°	535.6	8.9
130°-140°	601.5	10.0
140°-150°	591.0	9.8
150°-160°	497.1	8.3
160°-170°	330.7	5.5
170°-180°	115.8	1.9
0°-30°	831.5	13.8
0°-40°	1317.1	21.9
0°-60°	2176.0	36.2
0°-90°	2620.4	43.5
90°-120°	726.2	12.1
90°-150°	2454.3	40.8
90°-180°	3398.0	56.5
0°-180°	6018.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	3	13	21	26	28	6
95°	57	65	72	75	75	63
105°	221	222	225	228	231	234
115°	413	413	411	410	409	407
125°	601	601	600	599	597	536
135°	776	781	782	780	777	600
145°	942	946	947	946	944	590
155°	1080	1080	1079	1082	1079	497
165°	1176	1173	1171	1176	1173	331
175°	1223	1218	1217	1223	1217	116
180°	1225	1225	1225	1225	1225	



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.6	15.7	15.0	14.2	13.5	13.1	13.4	13.5	13.7	13.9	13.9
90°	2.9	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1
92.5°	20.3	22.9	25.6	28.2	30.9	32.8	34.0	35.1	36.4	37.5	38.2
95°	56.8	58.7	60.7	62.5	64.4	66.1	67.6	69.1	70.5	72.0	72.6
97.5°	99.3	100.8	102.3	103.8	105.3	107.0	108.7	110.4	112.1	113.8	114.6
100°	132.6	133.5	134.3	135.1	136.0	137.4	139.3	141.1	143.0	145.0	145.4
102.5°	167.5	167.8	168.1	168.4	168.8	169.8	171.5	173.3	175.0	176.8	177.3
105°	220.7	220.9	221.1	221.4	221.5	222.1	222.9	223.7	224.6	225.4	226.1
107.5°	276.5	276.9	277.1	277.4	277.6	277.8	277.9	278.0	278.2	278.3	278.9
110°	314.5	314.9	315.3	315.8	316.2	316.3	316.1	315.8	315.6	315.4	315.0



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.8	354.0	354.1	354.2	354.2	354.1	353.7	353.4	352.9	352.5	352.5
115°	412.9	412.9	412.9	412.9	412.9	412.8	412.4	412.0	411.5	411.1	410.9
117.5°	468.7	468.9	469.0	469.2	469.4	469.3	469.0	468.7	468.4	468.1	467.4
120°	505.8	506.6	507.5	508.3	509.2	509.3	508.7	508.0	507.4	506.8	505.7
122.5°	544.5	544.8	545.1	545.4	545.8	545.8	545.5	545.3	544.9	544.6	544.0
125°	601.4	601.4	601.4	601.4	601.4	601.4	601.2	601.0	600.7	600.5	600.1
127.5°	653.2	653.9	654.4	655.1	655.7	655.9	655.5	655.2	654.8	654.5	654.1
130°	689.6	690.2	690.8	691.5	692.1	692.4	692.4	692.4	692.4	692.4	692.0
132.5°	726.7	727.2	727.7	728.1	728.6	728.7	728.6	728.4	728.2	728.1	727.6
135°	775.8	777.1	778.3	779.6	780.8	781.5	781.5	781.5	781.5	781.5	781.1
137.5°	829.2	829.8	830.4	831.0	831.5	832.0	832.3	832.7	833.0	833.3	832.8
140°	864.8	865.2	865.7	866.1	866.5	866.7	866.7	866.7	866.7	866.7	866.5
142.5°	897.4	897.8	898.2	898.6	899.1	899.2	899.0	898.9	898.7	898.5	898.5
145°	942.5	943.3	944.2	945.0	945.8	946.4	946.6	946.8	947.0	947.2	947.0
147.5°	987.2	988.2	989.2	990.2	991.2	991.6	991.5	991.3	991.2	991.0	990.8
150°	1014.5	1015.3	1016.2	1017.0	1017.8	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2
152.5°	1040.2	1040.7	1041.2	1041.7	1042.3	1042.6	1042.8	1042.9	1043.1	1043.3	1043.7
155°	1079.8	1079.8	1079.8	1079.8	1079.8	1079.7	1079.5	1079.3	1079.0	1078.9	1079.7
157.5°	1113.1	1112.8	1112.4	1112.1	1111.7	1111.4	1111.4	1111.3	1111.3	1111.3	1111.9
160°	1132.9	1132.7	1132.5	1132.2	1132.0	1131.8	1131.6	1131.4	1131.1	1131.0	1131.6
162.5°	1151.0	1150.5	1150.0	1149.4	1148.8	1148.5	1148.3	1148.1	1147.9	1147.6	1148.8
165°	1175.5	1174.8	1174.2	1173.6	1173.0	1172.4	1172.0	1171.6	1171.2	1170.8	1172.0
167.5°	1194.3	1193.4	1192.5	1191.6	1190.7	1190.3	1190.3	1190.3	1190.4	1190.4	1191.7
170°	1204.8	1203.8	1202.7	1201.7	1200.6	1200.2	1200.4	1200.6	1200.9	1201.1	1202.3
172.5°	1212.4	1211.5	1210.6	1209.7	1208.9	1208.4	1208.5	1208.6	1208.6	1208.7	1210.1
175°	1222.9	1221.8	1220.7	1219.7	1218.6	1218.0	1217.8	1217.6	1217.4	1217.2	1218.6
177.5°	1226.3	1225.4	1224.6	1223.8	1222.9	1222.5	1222.5	1222.5	1222.5	1222.5	1223.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	14.1	14.2	14.3	14.4	14.7	14.9	15.2	15.4
90°	23.4	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	39.1	39.8	40.5	41.0	41.3	41.6	41.8	42.1
95°	73.2	73.9	74.5	74.8	74.8	74.8	74.8	74.8
97.5°	115.4	116.1	116.9	117.2	117.2	117.2	117.2	117.2
100°	145.8	146.2	146.6	146.8	146.8	146.8	146.8	146.8
102.5°	177.9	178.6	179.1	179.4	179.7	179.9	180.0	180.2
105°	226.7	227.3	228.0	228.6	229.3	229.8	230.5	231.1
107.5°	279.5	280.1	280.6	281.0	280.9	280.9	280.8	280.8
110°	314.5	314.1	313.7	313.8	314.5	315.1	315.8	316.3



TEST NUMBER: P332953-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.4	352.3	352.2	352.2	352.4	352.5	352.6	352.8
115°	410.7	410.4	410.3	410.0	409.9	409.6	409.4	409.2
117.5°	466.7	465.9	465.2	464.7	464.2	463.8	463.4	463.0
120°	504.7	503.6	502.6	502.2	502.6	503.0	503.5	503.9
122.5°	543.2	542.5	541.8	541.0	540.3	539.6	538.7	538.0
125°	599.7	599.2	598.8	598.4	598.0	597.6	597.1	596.7
127.5°	653.7	653.3	652.8	652.5	652.2	651.8	651.4	651.1
130°	691.5	691.1	690.7	690.1	689.3	688.4	687.5	686.7
132.5°	727.2	726.8	726.4	725.9	725.6	725.3	725.0	724.6
135°	780.6	780.2	779.8	779.3	778.6	778.0	777.3	776.7
137.5°	832.3	831.7	831.2	831.0	831.1	831.2	831.4	831.4
140°	866.3	866.1	865.8	865.7	865.4	865.2	865.0	864.8
142.5°	898.5	898.4	898.4	898.3	898.3	898.2	898.2	898.1
145°	946.8	946.6	946.4	945.9	945.3	944.7	944.0	943.5
147.5°	990.7	990.5	990.3	990.1	989.9	989.7	989.4	989.3
150°	1018.2	1018.2	1018.2	1018.1	1017.9	1017.7	1017.5	1017.3
152.5°	1044.2	1044.8	1045.3	1045.3	1044.7	1044.2	1043.6	1043.1
155°	1080.6	1081.4	1082.2	1082.2	1081.4	1080.6	1079.7	1078.9
157.5°	1112.6	1113.1	1113.8	1113.8	1113.0	1112.3	1111.6	1110.9
160°	1132.2	1132.9	1133.5	1133.3	1132.2	1131.1	1130.2	1129.1
162.5°	1149.9	1151.0	1152.2	1152.3	1151.2	1150.1	1149.1	1148.0
165°	1173.3	1174.5	1175.8	1176.0	1175.2	1174.4	1173.5	1172.6
167.5°	1192.9	1194.3	1195.5	1195.5	1194.2	1192.9	1191.6	1190.3
170°	1203.6	1204.8	1206.2	1206.0	1204.5	1203.1	1201.6	1200.1
172.5°	1211.5	1212.9	1214.4	1214.4	1212.8	1211.4	1209.9	1208.4
175°	1220.1	1221.6	1223.0	1223.0	1221.6	1220.1	1218.6	1217.2
177.5°	1224.8	1226.0	1227.2	1227.1	1225.7	1224.4	1223.0	1221.7
180°	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7	1224.7

(END OF REPORT)