

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332975-940

Luminaire Tested: **SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332975-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7165.5 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332975-940  
CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	29	25	45	34	28	24	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12352	12352	12352	12352
5°	14327	12388	10950	12388
10°	16948	12336	9773	12336
15°	19578	12221	8398	12221
20°	21798	12064	7594	12064
25°	22502	11909	7050	11909
30°	19699	11723	6723	11723
35°	15334	11446	6525	11446
40°	11499	11129	6418	11129
45°	9079	10620	6361	10620
50°	7665	10034	6179	10034
55°	6681	9388	5847	9388
60°	6011	8719	5176	8719
65°	5299	7996	4451	7996
70°	4773	7246	4015	7246
75°	3999	6422	3425	6422
80°	3384	5472	3208	5472
85°	2862	4279	2862	4279



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.2	2.1
10°-20°	447.2	6.2
20°-30°	699.4	9.8
30°-40°	777.5	10.9
40°-50°	689.9	9.6
50°-60°	537.6	7.5
60°-70°	351.9	4.9
70°-80°	173.1	2.4
80°-90°	45.2	0.6
90°-100°	327.3	4.6
100°-110°	681.1	9.5
110°-120°	610.1	8.5
120°-130°	513.2	7.2
130°-140°	427.9	6.0
140°-150°	326.9	4.6
150°-160°	229.8	3.2
160°-170°	135.2	1.9
170°-180°	44.0	0.6
0°-30°	1294.9	18.1
0°-40°	2072.4	28.9
0°-60°	3299.8	46.1
0°-90°	3870.0	54.0
90°-120°	1618.5	22.6
90°-150°	2886.5	40.3
90°-180°	3295.0	46.0
0°-180°	7165.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1530	1530	1530	1530	1530	
5°	1768	1529	1351	1529	1768	179
15°	2342	1462	1005	1462	2342	666
25°	2526	1337	792	1337	2526	1121
35°	1556	1161	662	1161	1556	975
45°	795	930	557	930	795	630
55°	475	667	415	667	475	432
65°	277	419	233	419	277	279
75°	128	206	110	206	128	141
85°	31	46	31	46	31	35
90°	19	1	19	1	19	17
95°	217	29	217	29	217	337
105°	1252	104	1252	104	1252	1238
115°	1203	183	1203	183	1203	1194
125°	960	256	960	256	960	872
135°	858	304	858	304	858	662
145°	701	350	701	350	701	444
155°	587	398	587	398	587	274
165°	512	434	512	434	512	147
175°	461	452	461	452	461	45
180°	453	453	453	453	453	



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1613.8	1618.3	1613.8	1613.4	1608.5	1607.0	1605.0	1598.6	1586.7	1579.8	1581.3
5°	1768.0	1783.3	1774.8	1773.5	1760.0	1746.4	1737.8	1718.1	1697.1	1682.9	1671.2
7.5°	1946.2	1955.1	1949.7	1941.1	1919.1	1906.7	1886.7	1860.6	1823.1	1794.3	1768.1
10°	2067.5	2074.9	2072.5	2056.5	2040.4	2007.8	1989.2	1952.9	1905.4	1867.9	1832.6
12.5°	2186.9	2194.8	2173.1	2173.8	2143.5	2117.7	2088.4	2042.6	1987.8	1939.3	1895.3
15°	2342.5	2332.6	2332.6	2320.3	2286.3	2250.7	2220.4	2172.4	2103.3	2045.3	1984.3
17.5°	2464.3	2467.7	2462.7	2433.6	2407.0	2370.0	2314.6	2258.5	2194.4	2116.7	2054.2
20°	2537.3	2537.3	2531.7	2512.0	2477.5	2438.0	2378.3	2317.2	2235.9	2157.6	2087.3
22.5°	2566.9	2568.8	2562.3	2546.0	2515.0	2476.5	2425.5	2363.6	2279.7	2191.6	2104.5
25°	2526.2	2537.9	2539.1	2534.8	2525.6	2502.1	2458.4	2394.9	2319.7	2224.1	2130.4
27.5°	2319.3	2334.1	2347.1	2368.4	2396.7	2411.5	2413.5	2381.2	2315.6	2223.7	2129.3
30°	2113.2	2125.5	2165.6	2218.0	2258.6	2295.6	2327.7	2336.3	2299.4	2216.7	2117.5
32.5°	1884.4	1901.1	1941.2	1997.5	2065.3	2128.0	2199.9	2236.7	2235.7	2186.1	2094.3
35°	1555.9	1568.3	1605.3	1664.4	1745.8	1838.9	1952.9	2041.7	2102.0	2097.7	2041.7
37.5°	1254.8	1268.7	1306.1	1355.2	1434.1	1549.3	1659.7	1782.0	1893.7	1956.5	1937.7
40°	1091.1	1091.7	1128.1	1178.7	1252.6	1353.1	1473.3	1608.9	1733.4	1835.1	1854.8
42.5°	961.9	962.0	986.1	1040.5	1093.9	1188.4	1303.1	1437.8	1583.5	1701.0	1753.3
45°	795.2	800.8	820.5	853.2	895.1	975.2	1067.0	1192.2	1355.6	1494.9	1581.8
47.5°	673.4	681.5	694.1	720.8	754.1	807.5	883.5	996.0	1128.8	1282.1	1405.8
50°	610.3	611.5	627.5	642.3	671.3	713.8	780.4	874.1	996.1	1143.5	1280.9
52.5°	556.1	555.8	565.4	584.2	607.7	640.9	694.6	779.9	888.1	1020.2	1162.1
55°	474.7	477.8	485.2	499.9	517.8	541.3	583.8	647.9	733.0	845.8	974.6
57.5°	412.8	414.4	420.2	426.4	442.8	459.9	491.8	536.3	608.1	700.4	820.5
60°	372.3	372.9	374.8	384.1	397.0	413.0	434.6	472.2	532.6	617.1	712.0
62.5°	332.9	333.9	336.8	343.6	353.6	364.7	387.3	417.5	467.5	539.7	625.2
65°	277.4	278.0	282.3	284.8	292.8	302.6	319.3	339.7	374.2	434.6	499.4
67.5°	231.8	231.8	232.0	235.3	240.9	247.4	257.4	273.7	299.7	336.8	393.9
70°	202.2	202.2	203.4	205.3	208.4	213.9	219.5	231.8	250.9	281.1	324.9
72.5°	174.6	175.0	176.3	176.6	178.3	182.8	186.9	194.8	209.0	231.8	267.2
75°	128.2	130.1	133.1	135.6	138.7	138.1	142.4	147.3	151.7	165.2	185.6
77.5°	95.4	94.4	94.8	96.9	97.3	97.9	100.9	104.8	108.0	114.4	121.7
80°	72.8	72.8	74.5	75.2	74.5	75.2	78.3	80.2	81.4	83.8	90.6
82.5°	55.0	56.0	55.4	56.0	56.4	57.0	59.6	59.9	61.2	62.2	65.0
85°	30.9	31.5	32.0	30.9	30.9	30.9	32.0	32.6	33.9	33.3	34.5
87.5°	14.6	14.1	14.8	14.6	14.9	14.4	14.7	15.5	14.4	15.1	14.7
90°	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1	15.2	16.1	14.3
92.5°	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9	235.2	282.4	247.1
95°	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6	746.0	725.5	547.5
97.5°	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6	937.2	764.1	512.4
100°	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6	943.6	715.7	464.7
102.5°	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6	890.2	655.2	432.7
105°	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0	793.2	584.0	405.0
107.5°	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4	714.8	544.1	400.0
110°	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1	675.6	530.6	401.4



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3	653.6	524.1	405.7
115°	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2	632.9	520.8	413.9
117.5°	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1	623.7	519.9	422.7
120°	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1	618.7	519.9	429.1
122.5°	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6	613.0	519.2	435.5
125°	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0	603.6	518.1	445.1
127.5°	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2	590.9	516.1	452.7
130°	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0	583.1	515.4	458.4
132.5°	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0	576.0	514.7	463.4
135°	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3	565.3	513.6	470.9
137.5°	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7	556.0	513.4	475.4
140°	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0	551.1	512.7	478.9
142.5°	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0	546.8	512.7	481.8
145°	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9	539.5	511.0	483.4
147.5°	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3	532.9	507.7	484.3
150°	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3	527.9	505.6	484.3
152.5°	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4	522.2	502.0	482.9
155°	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7	513.6	496.8	480.7
157.5°	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0	504.9	491.2	478.4
160°	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2	498.6	487.0	476.3
162.5°	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3	492.8	482.7	474.1
165°	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5	483.4	476.3	470.0
167.5°	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0	474.8	469.8	465.7
170°	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6	469.1	465.6	462.9
172.5°	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9	464.1	461.3	460.0
175°	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2	458.4	456.6	456.6
177.5°	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2	454.5	453.8	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1576.4	1569.5	1566.0	1558.1	1548.7	1543.8	1539.4	1532.9	1524.6	1515.7	1509.3
5°	1656.4	1641.6	1623.1	1600.9	1581.2	1562.1	1545.4	1528.7	1509.7	1490.0	1470.3
7.5°	1738.5	1709.4	1677.9	1641.6	1606.2	1574.0	1544.4	1516.1	1484.0	1455.3	1429.1
10°	1795.7	1756.2	1712.4	1666.3	1620.0	1579.9	1540.5	1504.8	1465.3	1430.1	1400.5
12.5°	1842.1	1795.7	1743.0	1685.5	1629.9	1581.4	1536.1	1489.4	1444.6	1406.5	1367.0
15°	1919.0	1855.5	1784.6	1715.6	1643.4	1577.4	1516.4	1462.2	1411.0	1357.5	1319.8
17.5°	1971.8	1896.6	1810.4	1727.4	1642.2	1564.4	1494.0	1429.4	1370.4	1315.6	1270.9
20°	2003.4	1920.2	1824.7	1730.4	1634.8	1551.6	1475.8	1404.3	1343.3	1284.1	1237.8
22.5°	2021.2	1929.1	1824.7	1725.9	1626.9	1536.8	1453.6	1379.1	1312.7	1253.5	1202.3
25°	2026.9	1928.2	1821.6	1708.2	1599.6	1504.1	1417.8	1337.0	1263.1	1203.9	1149.7
27.5°	2019.0	1902.8	1793.6	1677.2	1565.3	1464.5	1373.9	1289.1	1215.0	1151.6	1095.9
30°	2007.2	1882.6	1765.5	1644.7	1531.2	1434.5	1338.9	1257.6	1180.4	1114.5	1058.5
32.5°	1981.5	1858.0	1732.0	1608.2	1493.3	1393.6	1302.9	1221.0	1145.5	1078.1	1018.5
35°	1930.7	1805.5	1668.7	1541.8	1428.9	1325.3	1240.3	1161.4	1089.2	1017.2	954.2
37.5°	1863.8	1735.9	1599.8	1460.7	1347.8	1250.0	1172.0	1097.9	1027.5	961.6	892.0
40°	1800.6	1684.1	1543.6	1405.5	1289.6	1195.2	1123.2	1056.0	985.1	919.7	850.1
42.5°	1724.2	1625.0	1482.9	1344.3	1229.9	1139.1	1071.8	1006.1	941.6	878.3	805.7
45°	1596.6	1521.3	1388.2	1255.1	1139.8	1049.8	988.2	930.2	873.5	813.1	744.7
47.5°	1450.4	1399.5	1284.5	1148.2	1041.5	960.6	901.0	853.6	805.7	745.3	685.3
50°	1348.8	1316.1	1205.1	1080.7	978.9	904.3	843.3	798.9	758.8	700.9	647.3
52.5°	1240.3	1222.9	1129.2	1010.1	911.9	838.7	786.6	746.6	706.1	658.0	607.8
55°	1075.0	1084.3	1004.8	901.9	809.4	747.8	700.3	667.0	632.5	591.8	552.9
57.5°	906.2	940.0	886.5	796.2	709.5	652.6	616.8	588.8	559.8	526.1	492.9
60°	805.0	833.4	803.3	723.7	647.9	594.9	561.6	540.0	511.0	480.2	455.0
62.5°	706.4	736.7	718.9	654.7	584.2	538.7	509.3	489.2	467.6	440.8	414.5
65°	582.6	602.3	593.6	549.3	499.4	460.5	433.4	418.6	398.9	379.2	355.7
67.5°	446.2	484.3	479.2	455.7	412.5	382.2	364.4	351.3	333.4	318.7	302.8
70°	366.8	401.9	401.3	382.2	358.7	330.4	318.1	307.0	291.0	276.8	263.9
72.5°	300.2	332.4	337.2	322.5	306.5	285.1	273.2	265.6	250.0	240.3	229.8
75°	210.2	233.6	239.8	239.8	232.4	221.3	210.8	205.9	194.8	186.2	180.0
77.5°	137.9	152.7	162.3	164.4	165.6	161.8	153.3	149.8	141.2	138.2	132.3
80°	97.4	107.3	118.3	122.1	125.1	123.9	120.2	117.7	109.8	106.6	104.2
82.5°	67.3	72.8	81.9	90.0	89.2	92.4	89.2	87.2	81.1	80.0	77.6
85°	35.1	35.8	37.0	42.5	45.7	46.8	47.4	46.2	44.4	44.4	40.0
87.5°	14.4	13.8	13.7	13.7	14.1	15.9	16.8	16.9	15.8	14.9	13.6
90°	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9	2.7	5.4	6.2
92.5°	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2	14.8	23.2	34.0
95°	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3	32.0	40.9	52.5
97.5°	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7	52.7	60.4	71.1
100°	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7	67.7	73.9	84.5
102.5°	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9	83.3	88.8	98.8
105°	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2	106.8	111.3	122.0
107.5°	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8	130.5	134.9	146.3
110°	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1	146.9	151.3	162.0





TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8	162.6	167.7	177.7
115°	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4	186.0	192.3	201.2
117.5°	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9	209.4	214.9	224.7
120°	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6	224.4	230.6	240.3
122.5°	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8	238.5	244.8	253.9
125°	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5	259.0	264.4	274.2
127.5°	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1	274.9	281.3	292.5
130°	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3	284.9	291.9	305.3
132.5°	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5	293.4	302.6	315.3
135°	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5	307.1	316.0	331.2
137.5°	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6	319.9	329.8	344.1
140°	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8	328.5	338.3	353.4
142.5°	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8	338.5	347.5	361.9
145°	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8	352.5	361.4	373.9
147.5°	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7	366.6	374.4	387.3
150°	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7	376.6	383.7	394.4
152.5°	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0	385.1	392.3	402.2
155°	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9	398.8	404.1	413.0
157.5°	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5	410.5	415.5	422.5
160°	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4	418.4	422.0	428.2
162.5°	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5	424.8	427.7	433.2
165°	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5	433.5	435.3	439.8
167.5°	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6	440.7	441.6	445.0
170°	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1	444.3	445.1	447.8
172.5°	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6	447.8	447.9	449.9
175°	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2	451.3	451.3	452.2
177.5°	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8	453.1	452.4	453.1
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1502.4	1497.4	1491.0	1483.6	1474.8	1466.9	1463.5	1466.4	1467.8	1463.9	1463.5
5°	1456.7	1441.3	1428.9	1410.4	1395.6	1383.3	1374.7	1371.0	1372.2	1362.4	1359.9
7.5°	1405.2	1387.0	1366.8	1344.8	1324.4	1306.3	1296.7	1291.6	1281.1	1276.7	1269.2
10°	1372.2	1347.6	1327.8	1301.9	1278.5	1257.0	1246.4	1237.8	1227.4	1222.4	1211.9
12.5°	1338.2	1309.6	1287.9	1261.0	1237.1	1211.0	1201.0	1185.1	1168.7	1158.3	1144.9
15°	1290.2	1255.7	1229.2	1197.1	1168.8	1139.2	1112.7	1083.1	1072.0	1048.6	1035.0
17.5°	1234.1	1199.1	1166.3	1123.3	1079.5	1042.8	1014.5	986.1	969.2	954.2	947.4
20°	1197.1	1165.1	1119.5	1069.5	1020.8	980.2	957.3	938.9	920.3	909.9	902.5
22.5°	1162.1	1121.1	1068.2	1014.3	965.6	933.8	914.4	895.5	880.4	870.4	860.6
25°	1103.4	1049.8	993.7	932.1	898.8	871.0	850.1	834.6	825.5	812.4	807.5
27.5°	1043.1	978.2	916.3	874.9	840.2	814.8	796.6	785.0	773.3	765.0	758.6
30°	996.8	930.9	875.4	835.9	800.8	779.8	765.0	751.4	742.2	735.4	730.5
32.5°	950.9	884.9	838.4	795.9	768.2	747.8	732.0	721.8	714.6	705.8	702.8
35°	884.6	826.0	785.3	747.2	718.8	700.3	688.0	677.4	671.3	668.9	667.0
37.5°	820.8	772.9	729.2	697.9	672.5	658.0	643.5	638.3	634.1	629.6	631.6
40°	780.4	735.4	696.6	663.3	642.9	627.0	618.3	612.2	608.4	608.4	608.4
42.5°	745.4	701.4	663.5	633.7	613.3	599.8	590.2	585.0	583.8	583.3	586.2
45°	691.1	650.3	612.2	587.5	570.2	556.6	551.1	546.8	546.8	549.3	549.8
47.5°	637.1	599.1	568.4	540.7	525.0	516.5	511.7	509.4	509.7	512.1	515.0
50°	604.1	566.5	536.3	511.7	496.9	488.8	484.6	483.3	484.6	484.6	488.8
52.5°	568.1	534.5	504.7	484.0	467.3	459.8	457.4	455.7	456.4	458.4	460.2
55°	515.3	485.2	456.8	437.0	424.7	419.8	414.3	414.8	413.7	414.8	414.8
57.5°	462.4	435.3	408.9	393.3	382.5	375.3	369.3	371.0	369.2	368.9	367.9
60°	428.5	398.9	377.9	363.7	351.3	345.2	339.7	340.9	339.0	337.8	335.4
62.5°	391.5	366.8	346.8	333.1	323.2	316.1	310.6	309.3	305.1	300.9	295.4
65°	337.8	317.4	299.6	286.7	277.4	271.9	267.5	263.9	254.6	244.7	239.8
67.5°	285.7	271.0	254.3	243.3	235.9	228.5	220.3	214.0	205.4	200.0	196.9
70°	252.1	237.9	223.7	213.3	205.3	198.5	189.2	184.9	178.8	176.3	173.3
72.5°	220.1	206.9	193.7	184.2	175.7	170.4	163.1	158.8	156.0	155.1	152.0
75°	171.4	160.9	151.1	142.4	135.6	131.9	128.9	125.7	124.5	119.0	115.9
77.5°	125.0	118.2	111.9	105.8	100.9	98.5	92.6	89.0	86.9	84.4	83.7
80°	97.4	92.5	86.3	82.6	75.8	73.4	70.9	70.3	69.6	69.0	68.4
82.5°	73.2	68.3	62.2	59.9	58.1	56.6	55.1	54.5	53.9	54.2	54.1
85°	37.0	34.5	34.5	33.9	33.3	32.6	32.0	32.0	31.5	32.0	31.5
87.5°	13.7	13.3	14.4	13.4	14.2	14.5	13.9	14.1	14.7	13.9	13.9
90°	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1	16.9	17.8	17.8
92.5°	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9	131.6	104.7	86.9
95°	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6	521.7	402.3	316.0
97.5°	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6	923.3	836.2	743.3
100°	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6	1091.4	1047.8	981.9
102.5°	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6	1156.9	1169.6	1142.1
105°	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0	1151.0	1239.1	1275.7
107.5°	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4	1059.4	1183.5	1262.8
110°	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1	988.1	1117.2	1215.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3	925.4	1047.4	1145.3
115°	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2	853.7	957.9	1043.3
117.5°	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1	812.8	894.7	967.1
120°	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1	795.0	866.2	929.3
122.5°	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6	783.5	848.4	903.7
125°	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0	765.5	827.0	875.9
127.5°	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2	744.4	805.7	852.1
130°	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0	727.3	787.8	835.0
132.5°	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0	708.1	767.1	814.4
135°	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3	679.2	733.5	778.0
137.5°	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7	651.7	697.4	737.6
140°	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0	633.8	673.9	711.2
142.5°	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0	618.8	653.3	685.6
145°	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9	598.2	624.9	649.9
147.5°	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3	580.4	601.8	621.3
150°	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3	569.7	587.5	603.6
152.5°	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4	559.0	575.4	588.6
155°	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7	543.9	557.2	567.9
157.5°	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0	529.0	540.2	548.8
160°	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2	519.0	528.8	535.9
162.5°	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3	509.7	517.4	523.8
165°	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5	495.9	502.0	506.5
167.5°	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0	484.1	489.1	491.8
170°	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6	476.3	479.8	482.5
172.5°	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9	469.8	472.0	473.9
175°	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2	461.1	462.9	462.9
177.5°	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2	455.9	455.9	456.6
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1460.4	1461.4	1458.0	1457.1	1458.0	1461.4	1460.4	1463.5	1463.9	1467.8	1466.4
5°	1355.0	1353.7	1350.6	1351.2	1350.6	1353.7	1355.0	1359.9	1362.4	1372.2	1371.0
7.5°	1264.7	1259.9	1261.2	1256.3	1261.2	1259.9	1264.7	1269.2	1276.7	1281.1	1291.6
10°	1209.4	1202.7	1197.1	1192.2	1197.1	1202.7	1209.4	1211.9	1222.4	1227.4	1237.8
12.5°	1134.0	1128.2	1120.7	1122.2	1120.7	1128.2	1134.0	1144.9	1158.3	1168.7	1185.1
15°	1027.0	1017.7	1003.0	1004.8	1003.0	1017.7	1027.0	1035.0	1048.6	1072.0	1083.1
17.5°	936.4	936.5	929.7	931.3	929.7	936.5	936.4	947.4	954.2	969.2	986.1
20°	889.6	885.2	885.8	884.0	885.8	885.2	889.6	902.5	909.9	920.3	938.9
22.5°	857.0	851.7	847.4	843.6	847.4	851.7	857.0	860.6	870.4	880.4	895.5
25°	802.0	798.3	792.7	791.5	792.7	798.3	802.0	807.5	812.4	825.5	834.6
27.5°	753.7	753.0	750.7	747.9	750.7	753.0	753.7	758.6	765.0	773.3	785.0
30°	725.6	724.3	723.1	721.2	723.1	724.3	725.6	730.5	735.4	742.2	751.4
32.5°	700.4	699.6	698.4	698.6	698.4	699.6	700.4	702.8	705.8	714.6	721.8
35°	664.5	663.9	662.7	662.1	662.7	663.9	664.5	667.0	668.9	671.3	677.4
37.5°	631.0	632.6	631.9	631.7	631.9	632.6	631.0	631.6	629.6	634.1	638.3
40°	607.8	608.4	609.7	609.0	609.7	608.4	607.8	608.4	608.4	608.4	612.2
42.5°	588.6	588.7	590.4	588.4	590.4	588.7	588.6	586.2	583.3	583.8	585.0
45°	554.2	557.9	557.2	557.2	557.2	557.9	554.2	549.8	549.3	546.8	546.8
47.5°	516.6	519.8	520.7	520.5	520.7	519.8	516.6	515.0	512.1	509.7	509.4
50°	492.0	490.7	492.6	492.0	492.6	490.7	492.0	488.8	484.6	484.6	483.3
52.5°	461.8	462.1	462.0	461.4	462.0	462.1	461.8	460.2	458.4	456.4	455.7
55°	415.4	416.1	414.8	415.4	414.8	416.1	415.4	414.8	414.8	413.7	414.8
57.5°	365.2	362.2	363.5	361.9	363.5	362.2	365.2	367.9	368.9	369.2	371.0
60°	329.2	324.2	323.0	320.6	323.0	324.2	329.2	335.4	337.8	339.0	340.9
62.5°	288.7	285.3	281.1	283.0	281.1	285.3	288.7	295.4	300.9	305.1	309.3
65°	234.9	232.4	230.5	233.0	230.5	232.4	234.9	239.8	244.7	254.6	263.9
67.5°	194.4	193.1	193.1	191.8	193.1	193.1	194.4	196.9	200.0	205.4	214.0
70°	173.3	171.4	171.4	170.1	171.4	171.4	173.3	173.3	176.3	178.8	184.9
72.5°	151.5	149.6	150.2	149.5	150.2	149.6	151.5	152.0	155.1	156.0	158.8
75°	112.2	109.1	109.1	109.8	109.1	109.1	112.2	115.9	119.0	124.5	125.7
77.5°	83.7	83.1	84.0	82.8	84.0	83.1	83.7	83.7	84.4	86.9	89.0
80°	68.4	67.8	67.2	69.0	67.2	67.8	68.4	68.4	69.0	69.6	70.3
82.5°	53.1	53.1	52.9	55.2	52.9	53.1	53.1	54.1	54.2	53.9	54.5
85°	32.0	30.9	32.0	30.9	32.0	30.9	32.0	31.5	32.0	31.5	32.0
87.5°	15.1	14.8	14.1	14.6	14.1	14.8	15.1	13.9	13.9	14.7	14.1
90°	18.7	19.6	18.7	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1
92.5°	76.4	71.6	68.6	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9
95°	272.4	244.8	228.8	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6
97.5°	679.4	625.8	599.1	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6
100°	904.5	850.2	823.4	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6
102.5°	1094.6	1055.3	1027.2	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6
105°	1277.5	1270.3	1257.8	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0
107.5°	1306.8	1327.1	1336.1	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4
110°	1278.4	1315.7	1331.8	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.1	1262.3	1284.8	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3
115°	1113.7	1167.1	1195.5	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2
117.5°	1027.2	1072.0	1100.8	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1
120°	980.1	1019.3	1042.4	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1
122.5°	946.6	980.1	999.7	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6
125°	911.6	937.4	954.3	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0
127.5°	887.9	910.9	925.1	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2
130°	871.5	893.8	908.0	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0
132.5°	850.2	875.2	888.8	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0
135°	813.7	838.6	852.8	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3
137.5°	770.9	795.5	807.3	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7
140°	742.4	762.1	774.5	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0
142.5°	713.2	731.4	742.4	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0
145°	672.1	687.2	696.2	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9
147.5°	637.8	650.8	657.5	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3
150°	617.8	629.4	634.7	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3
152.5°	600.7	610.1	613.3	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4
155°	576.8	584.0	586.7	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7
157.5°	555.4	560.8	562.4	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0
160°	541.3	546.6	547.5	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2
162.5°	527.7	533.1	534.0	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3
165°	510.1	513.6	512.7	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5
167.5°	493.6	495.9	495.7	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0
170°	484.3	485.2	484.3	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6
172.5°	475.0	475.9	475.0	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9
175°	462.9	464.7	462.9	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2
177.5°	455.9	456.6	455.2	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332975-940  
 CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1463.5	1466.9	1474.8	1483.6	1491.0	1497.4	1502.4	1509.3	1515.7	1524.6	1532.9
5°	1374.7	1383.3	1395.6	1410.4	1428.9	1441.3	1456.7	1470.3	1490.0	1509.7	1528.7
7.5°	1296.7	1306.3	1324.4	1344.8	1366.8	1387.0	1405.2	1429.1	1455.3	1484.0	1516.1
10°	1246.4	1257.0	1278.5	1301.9	1327.8	1347.6	1372.2	1400.5	1430.1	1465.3	1504.8
12.5°	1201.0	1211.0	1237.1	1261.0	1287.9	1309.6	1338.2	1367.0	1406.5	1444.6	1489.4
15°	1112.7	1139.2	1168.8	1197.1	1229.2	1255.7	1290.2	1319.8	1357.5	1411.0	1462.2
17.5°	1014.5	1042.8	1079.5	1123.3	1166.3	1199.1	1234.1	1270.9	1315.6	1370.4	1429.4
20°	957.3	980.2	1020.8	1069.5	1119.5	1165.1	1197.1	1237.8	1284.1	1343.3	1404.3
22.5°	914.4	933.8	965.6	1014.3	1068.2	1121.1	1162.1	1202.3	1253.5	1312.7	1379.1
25°	850.1	871.0	898.8	932.1	993.7	1049.8	1103.4	1149.7	1203.9	1263.1	1337.0
27.5°	796.6	814.8	840.2	874.9	916.3	978.2	1043.1	1095.9	1151.6	1215.0	1289.1
30°	765.0	779.8	800.8	835.9	875.4	930.9	996.8	1058.5	1114.5	1180.4	1257.6
32.5°	732.0	747.8	768.2	795.9	838.4	884.9	950.9	1018.5	1078.1	1145.5	1221.0
35°	688.0	700.3	718.8	747.2	785.3	826.0	884.6	954.2	1017.2	1089.2	1161.4
37.5°	643.5	658.0	672.5	697.9	729.2	772.9	820.8	892.0	961.6	1027.5	1097.9
40°	618.3	627.0	642.9	663.3	696.6	735.4	780.4	850.1	919.7	985.1	1056.0
42.5°	590.2	599.8	613.3	633.7	663.5	701.4	745.4	805.7	878.3	941.6	1006.1
45°	551.1	556.6	570.2	587.5	612.2	650.3	691.1	744.7	813.1	873.5	930.2
47.5°	511.7	516.5	525.0	540.7	568.4	599.1	637.1	685.3	745.3	805.7	853.6
50°	484.6	488.8	496.9	511.7	536.3	566.5	604.1	647.3	700.9	758.8	798.9
52.5°	457.4	459.8	467.3	484.0	504.7	534.5	568.1	607.8	658.0	706.1	746.6
55°	414.3	419.8	424.7	437.0	456.8	485.2	515.3	552.9	591.8	632.5	667.0
57.5°	369.3	375.3	382.5	393.3	408.9	435.3	462.4	492.9	526.1	559.8	588.8
60°	339.7	345.2	351.3	363.7	377.9	398.9	428.5	455.0	480.2	511.0	540.0
62.5°	310.6	316.1	323.2	333.1	346.8	366.8	391.5	414.5	440.8	467.6	489.2
65°	267.5	271.9	277.4	286.7	299.6	317.4	337.8	355.7	379.2	398.9	418.6
67.5°	220.3	228.5	235.9	243.3	254.3	271.0	285.7	302.8	318.7	333.4	351.3
70°	189.2	198.5	205.3	213.3	223.7	237.9	252.1	263.9	276.8	291.0	307.0
72.5°	163.1	170.4	175.7	184.2	193.7	206.9	220.1	229.8	240.3	250.0	265.6
75°	128.9	131.9	135.6	142.4	151.1	160.9	171.4	180.0	186.2	194.8	205.9
77.5°	92.6	98.5	100.9	105.8	111.9	118.2	125.0	132.3	138.2	141.2	149.8
80°	70.9	73.4	75.8	82.6	86.3	92.5	97.4	104.2	106.6	109.8	117.7
82.5°	55.1	56.6	58.1	59.9	62.2	68.3	73.2	77.6	80.0	81.1	87.2
85°	32.0	32.6	33.3	33.9	34.5	34.5	37.0	40.0	44.4	44.4	46.2
87.5°	13.9	14.5	14.2	13.4	14.4	13.3	13.7	13.6	14.9	15.8	16.9
90°	15.2	16.1	14.3	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9
92.5°	235.2	282.4	247.1	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2
95°	746.0	725.5	547.5	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3
97.5°	937.2	764.1	512.4	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7
100°	943.6	715.7	464.7	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7
102.5°	890.2	655.2	432.7	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9
105°	793.2	584.0	405.0	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2
107.5°	714.8	544.1	400.0	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8
110°	675.6	530.6	401.4	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	653.6	524.1	405.7	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8
115°	632.9	520.8	413.9	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4
117.5°	623.7	519.9	422.7	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9
120°	618.7	519.9	429.1	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6
122.5°	613.0	519.2	435.5	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8
125°	603.6	518.1	445.1	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5
127.5°	590.9	516.1	452.7	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1
130°	583.1	515.4	458.4	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3
132.5°	576.0	514.7	463.4	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5
135°	565.3	513.6	470.9	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5
137.5°	556.0	513.4	475.4	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6
140°	551.1	512.7	478.9	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8
142.5°	546.8	512.7	481.8	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8
145°	539.5	511.0	483.4	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8
147.5°	532.9	507.7	484.3	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7
150°	527.9	505.6	484.3	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7
152.5°	522.2	502.0	482.9	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0
155°	513.6	496.8	480.7	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9
157.5°	504.9	491.2	478.4	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5
160°	498.6	487.0	476.3	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4
162.5°	492.8	482.7	474.1	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5
165°	483.4	476.3	470.0	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5
167.5°	474.8	469.8	465.7	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6
170°	469.1	465.6	462.9	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1
172.5°	464.1	461.3	460.0	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6
175°	458.4	456.6	456.6	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2
177.5°	454.5	453.8	453.8	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1





TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1539.4	1543.8	1548.7	1558.1	1566.0	1569.5	1576.4	1581.3	1579.8	1586.7	1598.6
5°	1545.4	1562.1	1581.2	1600.9	1623.1	1641.6	1656.4	1671.2	1682.9	1697.1	1718.1
7.5°	1544.4	1574.0	1606.2	1641.6	1677.9	1709.4	1738.5	1768.1	1794.3	1823.1	1860.6
10°	1540.5	1579.9	1620.0	1666.3	1712.4	1756.2	1795.7	1832.6	1867.9	1905.4	1952.9
12.5°	1536.1	1581.4	1629.9	1685.5	1743.0	1795.7	1842.1	1895.3	1939.3	1987.8	2042.6
15°	1516.4	1577.4	1643.4	1715.6	1784.6	1855.5	1919.0	1984.3	2045.3	2103.3	2172.4
17.5°	1494.0	1564.4	1642.2	1727.4	1810.4	1896.6	1971.8	2054.2	2116.7	2194.4	2258.5
20°	1475.8	1551.6	1634.8	1730.4	1824.7	1920.2	2003.4	2087.3	2157.6	2235.9	2317.2
22.5°	1453.6	1536.8	1626.9	1725.9	1824.7	1929.1	2021.2	2104.5	2191.6	2279.7	2363.6
25°	1417.8	1504.1	1599.6	1708.2	1821.6	1928.2	2026.9	2130.4	2224.1	2319.7	2394.9
27.5°	1373.9	1464.5	1565.3	1677.2	1793.6	1902.8	2019.0	2129.3	2223.7	2315.6	2381.2
30°	1338.9	1434.5	1531.2	1644.7	1765.5	1882.6	2007.2	2117.5	2216.7	2299.4	2336.3
32.5°	1302.9	1393.6	1493.3	1608.2	1732.0	1858.0	1981.5	2094.3	2186.1	2235.7	2236.7
35°	1240.3	1325.3	1428.9	1541.8	1668.7	1805.5	1930.7	2041.7	2097.7	2102.0	2041.7
37.5°	1172.0	1250.0	1347.8	1460.7	1599.8	1735.9	1863.8	1937.7	1956.5	1893.7	1782.0
40°	1123.2	1195.2	1289.6	1405.5	1543.6	1684.1	1800.6	1854.8	1835.1	1733.4	1608.9
42.5°	1071.8	1139.1	1229.9	1344.3	1482.9	1625.0	1724.2	1753.3	1701.0	1583.5	1437.8
45°	988.2	1049.8	1139.8	1255.1	1388.2	1521.3	1596.6	1581.8	1494.9	1355.6	1192.2
47.5°	901.0	960.6	1041.5	1148.2	1284.5	1399.5	1450.4	1405.8	1282.1	1128.8	996.0
50°	843.3	904.3	978.9	1080.7	1205.1	1316.1	1348.8	1280.9	1143.5	996.1	874.1
52.5°	786.6	838.7	911.9	1010.1	1129.2	1222.9	1240.3	1162.1	1020.2	888.1	779.9
55°	700.3	747.8	809.4	901.9	1004.8	1084.3	1075.0	974.6	845.8	733.0	647.9
57.5°	616.8	652.6	709.5	796.2	886.5	940.0	906.2	820.5	700.4	608.1	536.3
60°	561.6	594.9	647.9	723.7	803.3	833.4	805.0	712.0	617.1	532.6	472.2
62.5°	509.3	538.7	584.2	654.7	718.9	736.7	706.4	625.2	539.7	467.5	417.5
65°	433.4	460.5	499.4	549.3	593.6	602.3	582.6	499.4	434.6	374.2	339.7
67.5°	364.4	382.2	412.5	455.7	479.2	484.3	446.2	393.9	336.8	299.7	273.7
70°	318.1	330.4	358.7	382.2	401.3	401.9	366.8	324.9	281.1	250.9	231.8
72.5°	273.2	285.1	306.5	322.5	337.2	332.4	300.2	267.2	231.8	209.0	194.8
75°	210.8	221.3	232.4	239.8	239.8	233.6	210.2	185.6	165.2	151.7	147.3
77.5°	153.3	161.8	165.6	164.4	162.3	152.7	137.9	121.7	114.4	108.0	104.8
80°	120.2	123.9	125.1	122.1	118.3	107.3	97.4	90.6	83.8	81.4	80.2
82.5°	89.2	92.4	89.2	90.0	81.9	72.8	67.3	65.0	62.2	61.2	59.9
85°	47.4	46.8	45.7	42.5	37.0	35.8	35.1	34.5	33.3	33.9	32.6
87.5°	16.8	15.9	14.1	13.7	13.7	13.8	14.4	14.7	15.1	14.4	15.5
90°	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1
92.5°	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9
95°	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6
97.5°	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6
100°	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6
102.5°	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6
105°	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0
107.5°	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4
110°	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1





TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3
115°	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2
117.5°	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1
120°	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1
122.5°	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6
125°	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0
127.5°	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2
130°	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0
132.5°	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0
135°	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3
137.5°	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7
140°	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0
142.5°	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0
145°	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9
147.5°	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3
150°	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3
152.5°	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4
155°	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7
157.5°	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0
160°	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2
162.5°	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3
165°	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5
167.5°	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0
170°	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6
172.5°	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9
175°	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2
177.5°	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1605.0	1607.0	1608.5	1613.4	1613.8	1618.3	1613.8
5°	1737.8	1746.4	1760.0	1773.5	1774.8	1783.3	1768.0
7.5°	1886.7	1906.7	1919.1	1941.1	1949.7	1955.1	1946.2
10°	1989.2	2007.8	2040.4	2056.5	2072.5	2074.9	2067.5
12.5°	2088.4	2117.7	2143.5	2173.8	2173.1	2194.8	2186.9
15°	2220.4	2250.7	2286.3	2320.3	2332.6	2332.6	2342.5
17.5°	2314.6	2370.0	2407.0	2433.6	2462.7	2467.7	2464.3
20°	2378.3	2438.0	2477.5	2512.0	2531.7	2537.3	2537.3
22.5°	2425.5	2476.5	2515.0	2546.0	2562.3	2568.8	2566.9
25°	2458.4	2502.1	2525.6	2534.8	2539.1	2537.9	2526.2
27.5°	2413.5	2411.5	2396.7	2368.4	2347.1	2334.1	2319.3
30°	2327.7	2295.6	2258.6	2218.0	2165.6	2125.5	2113.2
32.5°	2199.9	2128.0	2065.3	1997.5	1941.2	1901.1	1884.4
35°	1952.9	1838.9	1745.8	1664.4	1605.3	1568.3	1555.9
37.5°	1659.7	1549.3	1434.1	1355.2	1306.1	1268.7	1254.8
40°	1473.3	1353.1	1252.6	1178.7	1128.1	1091.7	1091.1
42.5°	1303.1	1188.4	1093.9	1040.5	986.1	962.0	961.9
45°	1067.0	975.2	895.1	853.2	820.5	800.8	795.2
47.5°	883.5	807.5	754.1	720.8	694.1	681.5	673.4
50°	780.4	713.8	671.3	642.3	627.5	611.5	610.3
52.5°	694.6	640.9	607.7	584.2	565.4	555.8	556.1
55°	583.8	541.3	517.8	499.9	485.2	477.8	474.7
57.5°	491.8	459.9	442.8	426.4	420.2	414.4	412.8
60°	434.6	413.0	397.0	384.1	374.8	372.9	372.3
62.5°	387.3	364.7	353.6	343.6	336.8	333.9	332.9
65°	319.3	302.6	292.8	284.8	282.3	278.0	277.4
67.5°	257.4	247.4	240.9	235.3	232.0	231.8	231.8
70°	219.5	213.9	208.4	205.3	203.4	202.2	202.2
72.5°	186.9	182.8	178.3	176.6	176.3	175.0	174.6
75°	142.4	138.1	138.7	135.6	133.1	130.1	128.2
77.5°	100.9	97.9	97.3	96.9	94.8	94.4	95.4
80°	78.3	75.2	74.5	75.2	74.5	72.8	72.8
82.5°	59.6	57.0	56.4	56.0	55.4	56.0	55.0
85°	32.0	30.9	30.9	30.9	32.0	31.5	30.9
87.5°	14.7	14.4	14.9	14.6	14.8	14.1	14.6
90°	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8



TEST NUMBER: P332975-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)